

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P879558

Luminaire Tested: **MEM2-HTN-VA-160-730-U-MQ**

Issue Date: 10/01/2024



Test Information

Test Method: LM-79-08
Report Number: P879558
Test Lab: INNOVATION CENTER(G3)
Issue Date: 10/01/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: MEM2-HTN-VA-160-730-U-MQ
Description: EPIC MODERN TALL HOUSING 160W 70CRI 3000K VISUAL COMFORT FIXTURE w/
TYPE V MEDIUM DISTRIBUTION OPTIC
Light Source: (1) 3000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17257.5 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type V - Short
BUG Rating: B4 - U0 - G3

Input Watts (W): 156
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.995
Total Harmonic Distortion (THDi): 6.6%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

REPORT NUMBER: P879558
 CATALOG NUMBER: MEM2-HTN-VA-160-730-U-MQ

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 15.5 fc
 Type V - Short - N/A

REPORT NUMBER: P879558
CATALOG NUMBER: MEM2-HTN-VA-160-730-U-MQ

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 57.5-Deg Vertical

REPORT NUMBER: P879558
 CATALOG NUMBER: MEM2-HTN-VA-160-730-U-MQ


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	8628.7	0.0	8628.7
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	8628.7	0.0	8628.7
	% Fixture	50.0	0.0	50.0
Total	Lumens	17257.5	0.0	17257.5
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	327.7	1.9
10°-20°	939.4	5.4
20°-30°	1509.6	8.7
30°-40°	2046.4	11.9
40°-50°	2613.5	15.1
50°-60°	3257.6	18.9
60°-70°	3319.4	19.2
70°-80°	2459.5	14.3
80°-90°	784.3	4.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	17257.5	100.0
0°-180°	17257.5	100.0




REPORT NUMBER: P879558
 CATALOG NUMBER: MEM2-HTN-VA-160-730-U-MQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1388.4	8.0			
FM	(30°-60°)	3958.7	22.9			
FH	(60°-80°)	2889.5	16.7			G2/5000
FVH	(80°-90°)	392.1	2.3			G3/500
BL	(0°-30°)	1388.4	8.0	B3/2500		
BM	(30°-60°)	3958.7	22.9	B3/5000		
BH	(60°-80°)	2889.5	16.7	B4/5000		G2/5000
BVH	(80°-90°)	392.1	2.3			G3/500
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G3
 Type V Short





REPORT NUMBER: P879558

CATALOG NUMBER: MEM2-HTN-VA-160-730-U-MQ

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	3491.1	3491.1	3491.1	3491.1	3491.1	3491.1	3491.1	3491.1	3491.1	3491.1	3491.1
2.5°	3485.1	3485.1	3484.2	3484.2	3483.4	3484.2	3485.1	3485.1	3484.2	3483.4	3482.5
5°	3460.2	3461.0	3461.0	3459.3	3457.6	3457.6	3457.6	3458.4	3456.7	3457.6	3456.7
7.5°	3424.1	3421.5	3424.1	3423.2	3424.1	3421.5	3425.8	3424.1	3421.5	3423.2	3423.2
10°	3383.7	3384.6	3385.4	3384.6	3387.1	3386.3	3385.4	3384.6	3382.8	3384.6	3382.0
12.5°	3345.9	3346.8	3349.3	3350.2	3352.8	3351.9	3352.8	3351.1	3350.2	3346.8	3345.9
15°	3309.8	3311.6	3315.0	3317.6	3320.1	3321.0	3319.3	3318.4	3314.1	3311.6	3309.8
17.5°	3279.8	3279.8	3284.9	3289.2	3293.5	3294.4	3293.5	3289.2	3283.2	3277.2	3278.0
20°	3259.1	3259.1	3265.2	3272.0	3278.0	3279.8	3277.2	3269.5	3260.0	3255.7	3254.9
22.5°	3249.7	3250.6	3256.6	3264.3	3272.9	3274.6	3269.5	3260.0	3249.7	3242.0	3241.1
25°	3250.6	3248.8	3254.0	3266.0	3275.5	3277.2	3272.9	3260.0	3248.0	3241.1	3238.5
27.5°	3248.0	3248.8	3254.9	3266.9	3278.9	3282.3	3275.5	3260.0	3243.7	3237.7	3236.0
30°	3247.1	3248.0	3249.7	3269.5	3283.2	3289.2	3278.9	3258.3	3244.5	3235.1	3234.2
32.5°	3243.7	3239.4	3251.4	3263.4	3280.6	3288.4	3278.0	3259.1	3236.8	3229.9	3226.5
35°	3229.9	3234.2	3244.5	3265.2	3284.9	3290.1	3278.0	3254.9	3235.1	3221.4	3220.5
37.5°	3227.4	3227.4	3243.7	3265.2	3284.9	3292.7	3282.3	3256.6	3229.1	3211.9	3211.9
40°	3223.9	3223.1	3244.5	3271.2	3296.9	3307.3	3293.5	3261.7	3228.2	3211.9	3203.3
42.5°	3233.4	3238.5	3263.4	3302.1	3334.7	3351.9	3332.2	3296.9	3257.4	3226.5	3225.6
45°	3278.0	3289.2	3315.0	3380.3	3424.1	3444.7	3421.5	3360.5	3298.7	3257.4	3254.9
47.5°	3347.6	3344.2	3405.2	3473.9	3538.3	3560.7	3527.2	3455.9	3366.5	3316.7	3303.8
50°	3395.7	3404.3	3467.0	3566.7	3662.9	3688.7	3639.7	3547.8	3450.7	3382.0	3370.0
52.5°	3461.0	3462.7	3542.6	3668.9	3767.7	3796.0	3748.8	3634.5	3504.0	3418.1	3412.1
55°	3468.8	3497.1	3594.2	3731.6	3850.2	3883.7	3825.2	3703.3	3551.2	3444.7	3434.4
57.5°	3462.7	3454.1	3571.8	3729.9	3841.6	3888.8	3831.3	3696.4	3533.2	3420.6	3393.2
60°	3339.0	3375.1	3504.8	3659.5	3802.9	3850.2	3783.2	3645.7	3467.0	3343.3	3332.2
62.5°	3254.9	3270.3	3388.9	3596.7	3714.4	3761.7	3710.1	3548.6	3357.9	3229.1	3213.6
65°	3123.4	3135.4	3274.6	3445.6	3609.6	3651.7	3585.6	3449.9	3245.4	3103.7	3075.3
67.5°	2913.8	2946.5	3083.9	3301.2	3414.6	3486.8	3427.5	3236.8	3051.3	2912.1	2891.5
70°	2669.9	2713.7	2855.4	3033.2	3222.2	3258.3	3176.7	3047.0	2839.1	2690.5	2654.4
72.5°	2434.5	2437.9	2570.2	2779.0	2898.4	2965.4	2919.0	2748.0	2544.4	2418.2	2395.8
75°	2105.5	2106.3	2251.5	2422.5	2573.6	2617.5	2543.6	2423.3	2242.1	2100.3	2086.6
77.5°	1724.1	1747.3	1876.1	2041.0	2160.5	2224.0	2171.6	2035.9	1866.7	1745.5	1731.8
80°	1352.1	1381.3	1472.4	1620.1	1723.2	1779.0	1722.3	1603.8	1475.0	1356.4	1358.1
82.5°	954.4	975.9	1061.8	1162.3	1262.8	1304.0	1280.0	1192.3	1074.6	970.7	942.4
85°	532.6	560.1	617.6	706.1	773.1	826.4	796.3	727.6	625.4	560.1	558.4
87.5°	156.3	169.2	192.4	251.7	315.3	338.5	331.6	314.4	275.7	247.4	229.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2407-176-20

Test Date: 10/23/2024

Luminaire Tested: MEM2-HTN-VA-160-740-U-WQ

Data in this report applies to families of products including MEM2-HTN-VA-160-740-U-WQ


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-176-20
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/23/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Streetworks
 Catalog Number: **MEM2-HTN-VA-1B-740-U-WQ**
 Description: EPIC MODERN VISUAL COMFORT 160W WAVESTREAM WIDE

Spectral Parameters

CCT (K): 3834
 CIE u': 0.2270
 CIE v': 0.5077
 Duv: 0.0024
 CIE x: 0.3900
 CIE y: 0.3877
 CIE z: 0.2223
 Peak Wavelength (nm): 585
 Dominant Wavelength (nm): 578
 Purity: 33.41599
 Rf: 74.4
 Rg: 93.6

CRI (Ra):	71.3		
R1:	67.4	R9:	-37.8
R2:	78.6	R10:	50.1
R3:	88.2	R11:	65.6
R4:	70.0	R12:	44.1
R5:	67.5	R13:	69.2
R6:	70.1	R14:	93.3
R7:	80.0	R15:	59.4
R8:	48.5		



Test Conditions


Stabilization Time: 30M
 Operation Time: 1H 30M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2407-176-20


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/22/2024	10/22/2025
DC Power Source	IN0208	10/22/2024	10/22/2025
Sphere Thermometer	IN0085	10/22/2024	10/22/2025
Room Thermometer	IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2407-176-20

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3834K
 CIE x = 0.3900
 CIE y = 0.3877
 Duv = 0.0024

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-176-20

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	169	NR	620	731	NR	750	20	NR	880	0	NR
365	0	NR	495	219	NR	625	668	NR	755	17	NR	885	0	NR
370	0	NR	500	285	NR	630	611	NR	760	15	NR	890	0	NR
375	0	NR	505	362	NR	635	550	NR	765	13	NR	895	0	NR
380	0	NR	510	435	NR	640	495	NR	770	11	NR	900	0	NR
385	0	NR	515	508	NR	645	440	NR	775	10	NR	905	0	NR
390	1	NR	520	565	NR	650	390	NR	780	8	NR	910	0	NR
395	3	NR	525	612	NR	655	343	NR	785	7	NR	915	0	NR
400	6	NR	530	652	NR	660	299	NR	790	6	NR	920	0	NR
405	10	NR	535	687	NR	665	261	NR	795	5	NR	925	0	NR
410	20	NR	540	720	NR	670	226	NR	800	5	NR	930	0	NR
415	40	NR	545	755	NR	675	195	NR	805	4	NR	935	0	NR
420	80	NR	550	789	NR	680	169	NR	810	3	NR	940	0	NR
425	152	NR	555	828	NR	685	146	NR	815	3	NR	945	0	NR
430	266	NR	560	867	NR	690	126	NR	820	3	NR	950	0	NR
435	435	NR	565	905	NR	695	108	NR	825	2	NR	955	0	NR
440	641	NR	570	942	NR	700	92	NR	830	2	NR	960	0	NR
445	869	NR	575	972	NR	705	79	NR	835	2	NR	965	0	NR
450	894	NR	580	991	NR	710	67	NR	840	2	NR	970	0	NR
455	640	NR	585	1000	NR	715	56	NR	845	1	NR	975	0	NR
460	413	NR	590	996	NR	720	47	NR	850	1	NR	980	0	NR
465	300	NR	595	975	NR	725	40	NR	855	1	NR	985	0	NR
470	208	NR	600	946	NR	730	33	NR	860	1	NR	990	0	NR
475	154	NR	605	903	NR	735	29	NR	865	1	NR	995	0	NR
480	139	NR	610	854	NR	740	25	NR	870	1	NR	1000	0	NR
485	144	NR	615	793	NR	745	22	NR	875	0	NR			

REPORT NUMBER: SP1-2407-176-20

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.47

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	169	NR	620	731	NR	750	20	NR	880	0	NR
365	0	NR	495	219	NR	625	668	NR	755	17	NR	885	0	NR
370	0	NR	500	285	NR	630	611	NR	760	15	NR	890	0	NR
375	0	NR	505	362	NR	635	550	NR	765	13	NR	895	0	NR
380	0	NR	510	435	NR	640	495	NR	770	11	NR	900	0	NR
385	0	NR	515	508	NR	645	440	NR	775	10	NR	905	0	NR
390	1	NR	520	565	NR	650	390	NR	780	8	NR	910	0	NR
395	3	NR	525	612	NR	655	343	NR	785	7	NR	915	0	NR
400	6	NR	530	652	NR	660	299	NR	790	6	NR	920	0	NR
405	10	NR	535	687	NR	665	261	NR	795	5	NR	925	0	NR
410	20	NR	540	720	NR	670	226	NR	800	5	NR	930	0	NR
415	40	NR	545	755	NR	675	195	NR	805	4	NR	935	0	NR
420	80	NR	550	789	NR	680	169	NR	810	3	NR	940	0	NR
425	152	NR	555	828	NR	685	146	NR	815	3	NR	945	0	NR
430	266	NR	560	867	NR	690	126	NR	820	3	NR	950	0	NR
435	435	NR	565	905	NR	695	108	NR	825	2	NR	955	0	NR
440	641	NR	570	942	NR	700	92	NR	830	2	NR	960	0	NR
445	869	NR	575	972	NR	705	79	NR	835	2	NR	965	0	NR
450	894	NR	580	991	NR	710	67	NR	840	2	NR	970	0	NR
455	640	NR	585	1000	NR	715	56	NR	845	1	NR	975	0	NR
460	413	NR	590	996	NR	720	47	NR	850	1	NR	980	0	NR
465	300	NR	595	975	NR	725	40	NR	855	1	NR	985	0	NR
470	208	NR	600	946	NR	730	33	NR	860	1	NR	990	0	NR
475	154	NR	605	903	NR	735	29	NR	865	1	NR	995	0	NR
480	139	NR	610	854	NR	740	25	NR	870	1	NR	1000	0	NR
485	144	NR	615	793	NR	745	22	NR	875	0	NR			

REPORT NUMBER: SP1-2407-176-20

Melanopic Flux vs. Wavelength




Melanopic Lumens: NR

M/P: 2.83





λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	169	NR	620	731	NR	750	20	NR	880	0	NR
365	0	NR	495	219	NR	625	668	NR	755	17	NR	885	0	NR
370	0	NR	500	285	NR	630	611	NR	760	15	NR	890	0	NR
375	0	NR	505	362	NR	635	550	NR	765	13	NR	895	0	NR
380	0	NR	510	435	NR	640	495	NR	770	11	NR	900	0	NR
385	0	NR	515	508	NR	645	440	NR	775	10	NR	905	0	NR
390	1	NR	520	565	NR	650	390	NR	780	8	NR	910	0	NR
395	3	NR	525	612	NR	655	343	NR	785	7	NR	915	0	NR
400	6	NR	530	652	NR	660	299	NR	790	6	NR	920	0	NR
405	10	NR	535	687	NR	665	261	NR	795	5	NR	925	0	NR
410	20	NR	540	720	NR	670	226	NR	800	5	NR	930	0	NR
415	40	NR	545	755	NR	675	195	NR	805	4	NR	935	0	NR
420	80	NR	550	789	NR	680	169	NR	810	3	NR	940	0	NR
425	152	NR	555	828	NR	685	146	NR	815	3	NR	945	0	NR
430	266	NR	560	867	NR	690	126	NR	820	3	NR	950	0	NR
435	435	NR	565	905	NR	695	108	NR	825	2	NR	955	0	NR
440	641	NR	570	942	NR	700	92	NR	830	2	NR	960	0	NR
445	869	NR	575	972	NR	705	79	NR	835	2	NR	965	0	NR
450	894	NR	580	991	NR	710	67	NR	840	2	NR	970	0	NR
455	640	NR	585	1000	NR	715	56	NR	845	1	NR	975	0	NR
460	413	NR	590	996	NR	720	47	NR	850	1	NR	980	0	NR
465	300	NR	595	975	NR	725	40	NR	855	1	NR	985	0	NR
470	208	NR	600	946	NR	730	33	NR	860	1	NR	990	0	NR
475	154	NR	605	903	NR	735	29	NR	865	1	NR	995	0	NR
480	139	NR	610	854	NR	740	25	NR	870	1	NR	1000	0	NR
485	144	NR	615	793	NR	745	22	NR	875	0	NR			

Summary

$R_f = 74.4$
 $R_g = 93.6$
 $CIE R_a = 71.3$
 $R_g = -37.8$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 85	CES26 = 63	CES51 = 88	CES76 = 54
CES02 = 61	CES27 = 88	CES52 = 87	CES77 = 72
CES03 = 30	CES28 = 83	CES53 = 77	CES78 = 57
CES04 = 70	CES29 = 65	CES54 = 84	CES79 = 83
CES05 = 47	CES30 = 79	CES55 = 83	CES80 = 80
CES06 = 50	CES31 = 69	CES56 = 73	CES81 = 78
CES07 = 40	CES32 = 62	CES57 = 72	CES82 = 92
CES08 = 39	CES33 = 76	CES58 = 74	CES83 = 90
CES09 = 29	CES34 = 72	CES59 = 85	CES84 = 87
CES10 = 74	CES35 = 85	CES60 = 90	CES85 = 79
CES11 = 57	CES36 = 95	CES61 = 83	CES86 = 70
CES12 = 63	CES37 = 80	CES62 = 88	CES87 = 77
CES13 = 42	CES38 = 89	CES63 = 74	CES88 = 79
CES14 = 74	CES39 = 96	CES64 = 67	CES89 = 70
CES15 = 71	CES40 = 91	CES65 = 63	CES90 = 78
CES16 = 46	CES41 = 92	CES66 = 61	CES91 = 79
CES17 = 49	CES42 = 83	CES67 = 58	CES92 = 59
CES18 = 56	CES43 = 78	CES68 = 66	CES93 = 75
CES19 = 72	CES44 = 99	CES69 = 75	CES94 = 52
CES20 = 65	CES45 = 86	CES70 = 59	CES95 = 67
CES21 = 86	CES46 = 82	CES71 = 54	CES96 = 76
CES22 = 78	CES47 = 85	CES72 = 84	CES97 = 85
CES23 = 92	CES48 = 75	CES73 = 50	CES98 = 75
CES24 = 91	CES49 = 81	CES74 = 96	CES99 = 62
CES25 = 72	CES50 = 88	CES75 = 55	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)