

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P879598

Luminaire Tested: **MEM2-HTN-VA-180-735-U-CQ**

Issue Date: 10/01/2024



Test Information

Test Method: LM-79-08
Report Number: P879598
Test Lab: INNOVATION CENTER(G3)
Issue Date: 10/01/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: MEM2-HTN-VA-180-735-U-CQ
Description: EPIC MODERN TALL HOUSING 180W 70CRI 3500K VISUAL COMFORT FIXTURE w/
TYPE V CONCENTRATED DISTRIBUTION OPTIC
Light Source: (1) 3500K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15114.1 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type V - Short
BUG Rating: B3 - U0 - G2

Input Watts (W): 170
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.995
Total Harmonic Distortion (THDi): 5.9%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

REPORT NUMBER: P879598
 CATALOG NUMBER: MEM2-HTN-VA-180-735-U-CQ

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 16.8 fc
 Type V - Short - N/A

REPORT NUMBER: P879598
CATALOG NUMBER: MEM2-HTN-VA-180-735-U-CQ

Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral - - - Horizontal Cone Through 0-Deg Vertical

REPORT NUMBER: P879598

CATALOG NUMBER: MEM2-HTN-VA-180-735-U-CQ


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 7557.0 | 0.0 | 7557.0 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Street Side | Lumens | 7557.0 | 0.0 | 7557.0 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Total | Lumens | 15114.1 | 0.0 | 15114.1 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

Coefficient of Utilization

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 355.5 | 2.4 |
| 10°-20° | 1025.8 | 6.8 |
| 20°-30° | 1642.4 | 10.9 |
| 30°-40° | 2224.8 | 14.7 |
| 40°-50° | 2747.5 | 18.2 |
| 50°-60° | 2951.9 | 19.5 |
| 60°-70° | 2482.3 | 16.4 |
| 70°-80° | 1386.1 | 9.2 |
| 80°-90° | 297.8 | 2.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 15114.1 | 100.0 |
| 0°-180° | 15114.1 | 100.0 |



REPORT NUMBER: P879598


CATALOG NUMBER: MEM2-HTN-VA-180-735-U-CQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1511.8 | 10.0 | | | |
| FM (30°-60°) | 3962.1 | 26.2 | | | |
| FH (60°-80°) | 1934.2 | 12.8 | | | G2/5000 |
| FVH (80°-90°) | 148.9 | 1.0 | | | G2/225 |
| BL (0°-30°) | 1511.8 | 10.0 | B3/2500 | | |
| BM (30°-60°) | 3962.1 | 26.2 | B3/5000 | | |
| BH (60°-80°) | 1934.2 | 12.8 | B3/2500 | | G2/5000 |
| BVH (80°-90°) | 148.9 | 1.0 | | | G2/225 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G2

Type V Short





REPORT NUMBER: P879598

CATALOG NUMBER: MEM2-HTN-VA-180-735-U-CQ

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 90° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3772.6 | 3772.6 | 3772.6 | 3772.6 | 3772.6 | 3772.6 | 3772.6 | 3772.6 | 3772.6 | 3772.6 | 3772.6 |
| 2.5° | 3761.4 | 3765.2 | 3764.2 | 3764.2 | 3764.2 | 3766.1 | 3766.1 | 3766.1 | 3767.0 | 3767.0 | 3768.0 |
| 5° | 3739.9 | 3742.7 | 3742.7 | 3742.7 | 3744.5 | 3745.5 | 3745.5 | 3746.4 | 3748.3 | 3747.3 | 3746.4 |
| 7.5° | 3710.8 | 3713.6 | 3713.6 | 3713.6 | 3715.5 | 3717.4 | 3717.4 | 3716.4 | 3719.2 | 3719.2 | 3718.3 |
| 10° | 3679.9 | 3680.8 | 3681.8 | 3683.6 | 3686.4 | 3687.4 | 3686.4 | 3686.4 | 3685.5 | 3686.4 | 3686.4 |
| 12.5° | 3643.3 | 3648.0 | 3649.0 | 3650.8 | 3655.5 | 3656.5 | 3656.5 | 3655.5 | 3654.6 | 3654.6 | 3653.6 |
| 15° | 3610.5 | 3612.4 | 3615.2 | 3619.0 | 3624.6 | 3626.5 | 3627.4 | 3624.6 | 3621.8 | 3620.8 | 3621.8 |
| 17.5° | 3580.5 | 3583.4 | 3587.1 | 3590.9 | 3598.4 | 3602.1 | 3602.1 | 3598.4 | 3594.6 | 3592.7 | 3592.7 |
| 20° | 3556.2 | 3559.0 | 3563.7 | 3569.3 | 3579.6 | 3584.3 | 3582.4 | 3578.7 | 3572.1 | 3569.3 | 3570.2 |
| 22.5° | 3540.3 | 3544.0 | 3547.8 | 3556.2 | 3567.4 | 3573.1 | 3571.2 | 3564.6 | 3557.1 | 3552.4 | 3552.4 |
| 25° | 3527.1 | 3529.9 | 3535.6 | 3546.8 | 3559.0 | 3565.6 | 3562.7 | 3554.3 | 3544.0 | 3538.4 | 3537.4 |
| 27.5° | 3512.1 | 3515.9 | 3523.4 | 3538.4 | 3553.4 | 3559.0 | 3557.1 | 3544.9 | 3532.8 | 3525.3 | 3523.4 |
| 30° | 3498.1 | 3501.8 | 3512.1 | 3529.0 | 3547.8 | 3556.2 | 3551.5 | 3538.4 | 3523.4 | 3514.0 | 3513.1 |
| 32.5° | 3488.7 | 3493.4 | 3505.6 | 3527.1 | 3549.6 | 3561.8 | 3557.1 | 3541.2 | 3521.5 | 3509.3 | 3508.4 |
| 35° | 3485.0 | 3489.7 | 3507.5 | 3533.7 | 3561.8 | 3578.7 | 3572.1 | 3552.4 | 3528.1 | 3513.1 | 3511.2 |
| 37.5° | 3485.9 | 3491.5 | 3514.0 | 3548.7 | 3584.3 | 3602.1 | 3593.7 | 3568.4 | 3537.4 | 3516.8 | 3514.0 |
| 40° | 3489.7 | 3496.2 | 3525.3 | 3568.4 | 3610.5 | 3627.4 | 3614.3 | 3576.8 | 3534.6 | 3505.6 | 3500.0 |
| 42.5° | 3494.3 | 3504.6 | 3540.3 | 3590.9 | 3634.9 | 3649.0 | 3625.5 | 3570.2 | 3511.2 | 3473.7 | 3469.0 |
| 45° | 3493.4 | 3501.8 | 3543.1 | 3603.0 | 3649.9 | 3657.4 | 3619.0 | 3549.6 | 3480.3 | 3431.6 | 3427.8 |
| 47.5° | 3477.5 | 3485.9 | 3532.8 | 3599.3 | 3645.2 | 3647.1 | 3601.2 | 3521.5 | 3440.0 | 3383.8 | 3378.1 |
| 50° | 3427.8 | 3439.1 | 3491.5 | 3564.6 | 3616.2 | 3617.1 | 3566.5 | 3478.4 | 3383.8 | 3318.2 | 3308.8 |
| 52.5° | 3351.9 | 3360.3 | 3421.2 | 3500.0 | 3558.1 | 3565.6 | 3510.3 | 3408.1 | 3300.4 | 3230.1 | 3223.5 |
| 55° | 3233.8 | 3250.7 | 3315.4 | 3397.8 | 3461.5 | 3470.0 | 3414.7 | 3304.1 | 3193.5 | 3113.0 | 3105.5 |
| 57.5° | 3097.0 | 3099.8 | 3168.2 | 3258.2 | 3324.7 | 3334.1 | 3274.1 | 3161.7 | 3046.4 | 2971.5 | 2952.7 |
| 60° | 2904.0 | 2915.2 | 2979.9 | 3068.0 | 3138.3 | 3150.4 | 3093.3 | 2984.6 | 2864.6 | 2779.4 | 2778.4 |
| 62.5° | 2681.0 | 2694.1 | 2759.7 | 2853.4 | 2924.6 | 2936.8 | 2875.9 | 2770.0 | 2650.0 | 2576.9 | 2550.7 |
| 65° | 2439.2 | 2442.9 | 2508.5 | 2601.3 | 2666.0 | 2672.5 | 2624.7 | 2524.5 | 2400.8 | 2325.8 | 2308.9 |
| 67.5° | 2167.4 | 2171.2 | 2221.8 | 2308.9 | 2378.3 | 2387.7 | 2338.9 | 2247.1 | 2135.6 | 2056.9 | 2048.4 |
| 70° | 1866.6 | 1867.6 | 1917.2 | 1988.5 | 2057.8 | 2077.5 | 2033.4 | 1945.4 | 1838.5 | 1775.8 | 1758.9 |
| 72.5° | 1549.9 | 1558.3 | 1602.4 | 1676.4 | 1735.5 | 1740.1 | 1704.5 | 1628.6 | 1541.5 | 1489.9 | 1480.6 |
| 75° | 1260.4 | 1254.7 | 1292.2 | 1337.2 | 1383.1 | 1398.1 | 1369.1 | 1317.5 | 1236.9 | 1192.0 | 1201.3 |
| 77.5° | 946.4 | 948.3 | 977.4 | 1018.6 | 1047.6 | 1073.9 | 1041.1 | 1016.7 | 952.1 | 900.5 | 902.4 |
| 80° | 669.1 | 667.2 | 694.4 | 714.0 | 746.8 | 750.6 | 732.8 | 700.0 | 658.8 | 637.2 | 635.3 |
| 82.5° | 423.6 | 415.1 | 435.7 | 461.0 | 475.1 | 468.5 | 472.3 | 450.7 | 417.9 | 406.7 | 396.4 |
| 85° | 216.5 | 214.6 | 225.8 | 235.2 | 245.5 | 245.5 | 239.9 | 223.0 | 216.5 | 203.3 | 199.6 |
| 87.5° | 74.0 | 76.8 | 80.6 | 77.8 | 82.5 | 80.6 | 78.7 | 66.5 | 59.0 | 55.3 | 51.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2407-176-8

Test Date: 09/25/2024

Luminaire Tested: MEM2-HTN-VA-130-735-U-RW

Data in this report applies to families of products including MEM2-HTN-VA-130-735-U-RW


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-176-8
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 09/27/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Streetworks
 Catalog Number: **MEM2-HTN-VA-130-735-U-RW**
 Description: EPIC MODERN VISUAL COMFORT 130W WAVESTREAM RECTANGULAR WIDE

Spectral Parameters

CCT (K): 3468
 CIE u': 0.2356
 CIE v': 0.5145
 Duv: 0.0020
 CIE x: 0.4092
 CIE y: 0.3972
 CIE z: 0.1936
 Peak Wavelength (nm): 590
 Dominant Wavelength (nm): 580
 Purity: 42.03411
 R_f: 74.1
 R_g: 93.4

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 70.6 | | |
| R1: | 66.2 | R9: | -41.3 |
| R2: | 79.1 | R10: | 52.2 |
| R3: | 90.8 | R11: | 63.6 |
| R4: | 68.4 | R12: | 47.5 |
| R5: | 66.3 | R13: | 68.3 |
| R6: | 71.1 | R14: | 94.8 |
| R7: | 78.4 | R15: | 57.6 |
| R8: | 44.5 | | |



Test Conditions


Stabilization Time: 46M
 Operation Time: 1H 46M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-176-8


| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-176-8

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2407-176-8

Photopic Flux vs. Wavelength



Photopic Lumens: NR

| λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) |
|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|
| 360 | 0 | NR | 490 | 164 | NR | 620 | 749 | NR | 750 | 20 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 209 | NR | 625 | 686 | NR | 755 | 17 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 265 | NR | 630 | 624 | NR | 760 | 15 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 325 | NR | 635 | 566 | NR | 765 | 13 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 384 | NR | 640 | 508 | NR | 770 | 11 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 439 | NR | 645 | 452 | NR | 775 | 10 | NR | 905 | 0 | NR |
| 390 | 1 | NR | 520 | 485 | NR | 650 | 401 | NR | 780 | 8 | NR | 910 | 0 | NR |
| 395 | 3 | NR | 525 | 526 | NR | 655 | 353 | NR | 785 | 7 | NR | 915 | 0 | NR |
| 400 | 6 | NR | 530 | 562 | NR | 660 | 308 | NR | 790 | 6 | NR | 920 | 0 | NR |
| 405 | 11 | NR | 535 | 598 | NR | 665 | 268 | NR | 795 | 5 | NR | 925 | 0 | NR |
| 410 | 24 | NR | 540 | 633 | NR | 670 | 232 | NR | 800 | 5 | NR | 930 | 0 | NR |
| 415 | 48 | NR | 545 | 674 | NR | 675 | 200 | NR | 805 | 4 | NR | 935 | 0 | NR |
| 420 | 91 | NR | 550 | 715 | NR | 680 | 174 | NR | 810 | 3 | NR | 940 | 0 | NR |
| 425 | 166 | NR | 555 | 761 | NR | 685 | 149 | NR | 815 | 3 | NR | 945 | 0 | NR |
| 430 | 276 | NR | 560 | 812 | NR | 690 | 129 | NR | 820 | 3 | NR | 950 | 0 | NR |
| 435 | 420 | NR | 565 | 860 | NR | 695 | 110 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 568 | NR | 570 | 908 | NR | 700 | 94 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 675 | NR | 575 | 948 | NR | 705 | 80 | NR | 835 | 2 | NR | 965 | 0 | NR |
| 450 | 629 | NR | 580 | 978 | NR | 710 | 68 | NR | 840 | 2 | NR | 970 | 0 | NR |
| 455 | 443 | NR | 585 | 994 | NR | 715 | 58 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 299 | NR | 590 | 1000 | NR | 720 | 48 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 217 | NR | 595 | 985 | NR | 725 | 40 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 157 | NR | 600 | 959 | NR | 730 | 34 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 127 | NR | 605 | 918 | NR | 735 | 29 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 123 | NR | 610 | 869 | NR | 740 | 25 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 135 | NR | 615 | 810 | NR | 745 | 22 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2407-176-8

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.35

| λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) |
|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|
| 360 | 0 | NR | 490 | 164 | NR | 620 | 749 | NR | 750 | 20 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 209 | NR | 625 | 686 | NR | 755 | 17 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 265 | NR | 630 | 624 | NR | 760 | 15 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 325 | NR | 635 | 566 | NR | 765 | 13 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 384 | NR | 640 | 508 | NR | 770 | 11 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 439 | NR | 645 | 452 | NR | 775 | 10 | NR | 905 | 0 | NR |
| 390 | 1 | NR | 520 | 485 | NR | 650 | 401 | NR | 780 | 8 | NR | 910 | 0 | NR |
| 395 | 3 | NR | 525 | 526 | NR | 655 | 353 | NR | 785 | 7 | NR | 915 | 0 | NR |
| 400 | 6 | NR | 530 | 562 | NR | 660 | 308 | NR | 790 | 6 | NR | 920 | 0 | NR |
| 405 | 11 | NR | 535 | 598 | NR | 665 | 268 | NR | 795 | 5 | NR | 925 | 0 | NR |
| 410 | 24 | NR | 540 | 633 | NR | 670 | 232 | NR | 800 | 5 | NR | 930 | 0 | NR |
| 415 | 48 | NR | 545 | 674 | NR | 675 | 200 | NR | 805 | 4 | NR | 935 | 0 | NR |
| 420 | 91 | NR | 550 | 715 | NR | 680 | 174 | NR | 810 | 3 | NR | 940 | 0 | NR |
| 425 | 166 | NR | 555 | 761 | NR | 685 | 149 | NR | 815 | 3 | NR | 945 | 0 | NR |
| 430 | 276 | NR | 560 | 812 | NR | 690 | 129 | NR | 820 | 3 | NR | 950 | 0 | NR |
| 435 | 420 | NR | 565 | 860 | NR | 695 | 110 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 568 | NR | 570 | 908 | NR | 700 | 94 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 675 | NR | 575 | 948 | NR | 705 | 80 | NR | 835 | 2 | NR | 965 | 0 | NR |
| 450 | 629 | NR | 580 | 978 | NR | 710 | 68 | NR | 840 | 2 | NR | 970 | 0 | NR |
| 455 | 443 | NR | 585 | 994 | NR | 715 | 58 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 299 | NR | 590 | 1000 | NR | 720 | 48 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 217 | NR | 595 | 985 | NR | 725 | 40 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 157 | NR | 600 | 959 | NR | 730 | 34 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 127 | NR | 605 | 918 | NR | 735 | 29 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 123 | NR | 610 | 869 | NR | 740 | 25 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 135 | NR | 615 | 810 | NR | 745 | 22 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2407-176-8

Melanopic Flux vs. Wavelength




Melanopic Lumens: NR

M/P: 2.54

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 164 | NR | 620 | 749 | NR | 750 | 20 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 209 | NR | 625 | 686 | NR | 755 | 17 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 265 | NR | 630 | 624 | NR | 760 | 15 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 325 | NR | 635 | 566 | NR | 765 | 13 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 384 | NR | 640 | 508 | NR | 770 | 11 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 439 | NR | 645 | 452 | NR | 775 | 10 | NR | 905 | 0 | NR |
| 390 | 1 | NR | 520 | 485 | NR | 650 | 401 | NR | 780 | 8 | NR | 910 | 0 | NR |
| 395 | 3 | NR | 525 | 526 | NR | 655 | 353 | NR | 785 | 7 | NR | 915 | 0 | NR |
| 400 | 6 | NR | 530 | 562 | NR | 660 | 308 | NR | 790 | 6 | NR | 920 | 0 | NR |
| 405 | 11 | NR | 535 | 598 | NR | 665 | 268 | NR | 795 | 5 | NR | 925 | 0 | NR |
| 410 | 24 | NR | 540 | 633 | NR | 670 | 232 | NR | 800 | 5 | NR | 930 | 0 | NR |
| 415 | 48 | NR | 545 | 674 | NR | 675 | 200 | NR | 805 | 4 | NR | 935 | 0 | NR |
| 420 | 91 | NR | 550 | 715 | NR | 680 | 174 | NR | 810 | 3 | NR | 940 | 0 | NR |
| 425 | 166 | NR | 555 | 761 | NR | 685 | 149 | NR | 815 | 3 | NR | 945 | 0 | NR |
| 430 | 276 | NR | 560 | 812 | NR | 690 | 129 | NR | 820 | 3 | NR | 950 | 0 | NR |
| 435 | 420 | NR | 565 | 860 | NR | 695 | 110 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 568 | NR | 570 | 908 | NR | 700 | 94 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 675 | NR | 575 | 948 | NR | 705 | 80 | NR | 835 | 2 | NR | 965 | 0 | NR |
| 450 | 629 | NR | 580 | 978 | NR | 710 | 68 | NR | 840 | 2 | NR | 970 | 0 | NR |
| 455 | 443 | NR | 585 | 994 | NR | 715 | 58 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 299 | NR | 590 | 1000 | NR | 720 | 48 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 217 | NR | 595 | 985 | NR | 725 | 40 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 157 | NR | 600 | 959 | NR | 730 | 34 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 127 | NR | 605 | 918 | NR | 735 | 29 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 123 | NR | 610 | 869 | NR | 740 | 25 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 135 | NR | 615 | 810 | NR | 745 | 22 | NR | 875 | 0 | NR | | | |

Summary

$R_f = 74.1$
 $R_g = 93.4$
 $CIE R_a = 70.6$
 $R_9 = -41.3$




Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)



| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 63 | CES51 = 87 | CES76 = 55 |
| CES02 = 61 | CES27 = 86 | CES52 = 86 | CES77 = 75 |
| CES03 = 31 | CES28 = 84 | CES53 = 76 | CES78 = 59 |
| CES04 = 70 | CES29 = 62 | CES54 = 83 | CES79 = 84 |
| CES05 = 48 | CES30 = 72 | CES55 = 82 | CES80 = 82 |
| CES06 = 51 | CES31 = 67 | CES56 = 72 | CES81 = 76 |
| CES07 = 40 | CES32 = 62 | CES57 = 71 | CES82 = 93 |
| CES08 = 39 | CES33 = 72 | CES58 = 73 | CES83 = 89 |
| CES09 = 29 | CES34 = 73 | CES59 = 85 | CES84 = 88 |
| CES10 = 75 | CES35 = 86 | CES60 = 92 | CES85 = 80 |
| CES11 = 58 | CES36 = 98 | CES61 = 83 | CES86 = 67 |
| CES12 = 64 | CES37 = 82 | CES62 = 88 | CES87 = 78 |
| CES13 = 42 | CES38 = 81 | CES63 = 74 | CES88 = 77 |
| CES14 = 74 | CES39 = 95 | CES64 = 68 | CES89 = 69 |
| CES15 = 71 | CES40 = 91 | CES65 = 64 | CES90 = 76 |
| CES16 = 47 | CES41 = 89 | CES66 = 63 | CES91 = 87 |
| CES17 = 50 | CES42 = 84 | CES67 = 61 | CES92 = 59 |
| CES18 = 56 | CES43 = 78 | CES68 = 68 | CES93 = 76 |
| CES19 = 72 | CES44 = 99 | CES69 = 77 | CES94 = 50 |
| CES20 = 65 | CES45 = 85 | CES70 = 61 | CES95 = 68 |
| CES21 = 87 | CES46 = 81 | CES71 = 58 | CES96 = 76 |
| CES22 = 79 | CES47 = 82 | CES72 = 85 | CES97 = 83 |
| CES23 = 92 | CES48 = 70 | CES73 = 52 | CES98 = 74 |
| CES24 = 91 | CES49 = 79 | CES74 = 98 | CES99 = 61 |
| CES25 = 72 | CES50 = 86 | CES75 = 60 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)