

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P879619

Luminaire Tested: **MEM2-HSN-VA-180-740-U-CQ**

Issue Date: 10/01/2024



Test Information

Test Method: LM-79-08
Report Number: P879619
Test Lab: INNOVATION CENTER(G3)
Issue Date: 10/01/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: MEM2-HSN-VA-180-740-U-CQ
Description: EPIC MODERN SHORT HOUSING 180W 70CRI 4000K VISUAL COMFORT FIXTURE
w/ TYPE V CONCENTRATED DISTRIBUTION OPTIC
Light Source: (1) 4000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15983.6 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type V - Short
BUG Rating: B3 - U0 - G2

Input Watts (W): 170
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.995
Total Harmonic Distortion (THDi): 5.9%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

REPORT NUMBER: P879619
 CATALOG NUMBER: MEM2-HSN-VA-180-740-U-CQ

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 17.7 fc
 Type V - Short - N/A

REPORT NUMBER: P879619
CATALOG NUMBER: MEM2-HSN-VA-180-740-U-CQ

Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral - - - Horizontal Cone Through 0-Deg Vertical

REPORT NUMBER: P879619

CATALOG NUMBER: MEM2-HSN-VA-180-740-U-CQ


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 7991.8 | 0.0 | 7991.8 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Street Side | Lumens | 7991.8 | 0.0 | 7991.8 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Total | Lumens | 15983.6 | 0.0 | 15983.6 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

Coefficient of Utilization

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 376.0 | 2.4 |
| 10°-20° | 1084.8 | 6.8 |
| 20°-30° | 1736.9 | 10.9 |
| 30°-40° | 2352.8 | 14.7 |
| 40°-50° | 2905.5 | 18.2 |
| 50°-60° | 3121.7 | 19.5 |
| 60°-70° | 2625.1 | 16.4 |
| 70°-80° | 1465.9 | 9.2 |
| 80°-90° | 315.0 | 2.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 15983.6 | 100.0 |
| 0°-180° | 15983.6 | 100.0 |



REPORT NUMBER: P879619


CATALOG NUMBER: MEM2-HSN-VA-180-740-U-CQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1598.8 | 10.0 | | | |
| FM (30°-60°) | 4190.0 | 26.2 | | | |
| FH (60°-80°) | 2045.5 | 12.8 | | | G2/5000 |
| FVH (80°-90°) | 157.5 | 1.0 | | | G2/225 |
| BL (0°-30°) | 1598.8 | 10.0 | B3/2500 | | |
| BM (30°-60°) | 4190.0 | 26.2 | B3/5000 | | |
| BH (60°-80°) | 2045.5 | 12.8 | B3/2500 | | G2/5000 |
| BVH (80°-90°) | 157.5 | 1.0 | | | G2/225 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G2

Type V Short





REPORT NUMBER: P879619

CATALOG NUMBER: MEM2-HSN-VA-180-740-U-CQ

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 90° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3989.7 | 3989.7 | 3989.7 | 3989.7 | 3989.7 | 3989.7 | 3989.7 | 3989.7 | 3989.7 | 3989.7 | 3989.7 |
| 2.5° | 3977.8 | 3981.8 | 3980.8 | 3980.8 | 3980.8 | 3982.8 | 3982.8 | 3982.8 | 3983.7 | 3983.7 | 3984.7 |
| 5° | 3955.0 | 3958.0 | 3958.0 | 3958.0 | 3960.0 | 3960.9 | 3960.9 | 3961.9 | 3963.9 | 3962.9 | 3961.9 |
| 7.5° | 3924.3 | 3927.3 | 3927.3 | 3927.3 | 3929.2 | 3931.2 | 3931.2 | 3930.2 | 3933.2 | 3933.2 | 3932.2 |
| 10° | 3891.6 | 3892.6 | 3893.6 | 3895.5 | 3898.5 | 3899.5 | 3898.5 | 3898.5 | 3897.5 | 3898.5 | 3898.5 |
| 12.5° | 3852.9 | 3857.9 | 3858.9 | 3860.9 | 3865.8 | 3866.8 | 3866.8 | 3865.8 | 3864.8 | 3864.8 | 3863.8 |
| 15° | 3818.2 | 3820.2 | 3823.2 | 3827.2 | 3833.1 | 3835.1 | 3836.1 | 3833.1 | 3830.1 | 3829.1 | 3830.1 |
| 17.5° | 3786.5 | 3789.5 | 3793.5 | 3797.4 | 3805.4 | 3809.3 | 3809.3 | 3805.4 | 3801.4 | 3799.4 | 3799.4 |
| 20° | 3760.8 | 3763.7 | 3768.7 | 3774.6 | 3785.5 | 3790.5 | 3788.5 | 3784.6 | 3777.6 | 3774.6 | 3775.6 |
| 22.5° | 3743.9 | 3747.9 | 3751.9 | 3760.8 | 3772.7 | 3778.6 | 3776.6 | 3769.7 | 3761.8 | 3756.8 | 3756.8 |
| 25° | 3730.1 | 3733.0 | 3739.0 | 3750.9 | 3763.7 | 3770.7 | 3767.7 | 3758.8 | 3747.9 | 3741.9 | 3741.0 |
| 27.5° | 3714.2 | 3718.2 | 3726.1 | 3741.9 | 3757.8 | 3763.7 | 3761.8 | 3748.9 | 3736.0 | 3728.1 | 3726.1 |
| 30° | 3699.3 | 3703.3 | 3714.2 | 3732.0 | 3751.9 | 3760.8 | 3755.8 | 3741.9 | 3726.1 | 3716.2 | 3715.2 |
| 32.5° | 3689.4 | 3694.4 | 3707.3 | 3730.1 | 3753.8 | 3766.7 | 3761.8 | 3744.9 | 3724.1 | 3711.2 | 3710.2 |
| 35° | 3685.5 | 3690.4 | 3709.2 | 3737.0 | 3766.7 | 3784.6 | 3777.6 | 3756.8 | 3731.0 | 3715.2 | 3713.2 |
| 37.5° | 3686.4 | 3692.4 | 3716.2 | 3752.8 | 3790.5 | 3809.3 | 3800.4 | 3773.7 | 3741.0 | 3719.2 | 3716.2 |
| 40° | 3690.4 | 3697.3 | 3728.1 | 3773.7 | 3818.2 | 3836.1 | 3822.2 | 3782.6 | 3738.0 | 3707.3 | 3701.3 |
| 42.5° | 3695.4 | 3706.3 | 3743.9 | 3797.4 | 3844.0 | 3858.9 | 3834.1 | 3775.6 | 3713.2 | 3673.6 | 3668.6 |
| 45° | 3694.4 | 3703.3 | 3746.9 | 3810.3 | 3859.9 | 3867.8 | 3827.2 | 3753.8 | 3680.5 | 3629.0 | 3625.0 |
| 47.5° | 3677.5 | 3686.4 | 3736.0 | 3806.4 | 3854.9 | 3856.9 | 3808.3 | 3724.1 | 3637.9 | 3578.4 | 3572.5 |
| 50° | 3625.0 | 3636.9 | 3692.4 | 3769.7 | 3824.2 | 3825.2 | 3771.7 | 3678.5 | 3578.4 | 3509.1 | 3499.2 |
| 52.5° | 3544.7 | 3553.7 | 3618.1 | 3701.3 | 3762.8 | 3770.7 | 3712.2 | 3604.2 | 3490.2 | 3415.9 | 3409.0 |
| 55° | 3419.9 | 3437.7 | 3506.1 | 3593.3 | 3660.7 | 3669.6 | 3611.1 | 3494.2 | 3377.3 | 3292.0 | 3284.1 |
| 57.5° | 3275.2 | 3278.2 | 3350.5 | 3445.6 | 3516.0 | 3525.9 | 3462.5 | 3343.6 | 3221.7 | 3142.4 | 3122.6 |
| 60° | 3071.0 | 3082.9 | 3151.3 | 3244.5 | 3318.8 | 3331.7 | 3271.2 | 3156.3 | 3029.4 | 2939.2 | 2938.3 |
| 62.5° | 2835.2 | 2849.1 | 2918.4 | 3017.5 | 3092.9 | 3105.7 | 3041.3 | 2929.3 | 2802.5 | 2725.2 | 2697.4 |
| 65° | 2579.5 | 2583.5 | 2652.9 | 2751.0 | 2819.3 | 2826.3 | 2775.7 | 2669.7 | 2538.9 | 2459.6 | 2441.8 |
| 67.5° | 2292.1 | 2296.1 | 2349.6 | 2441.8 | 2515.1 | 2525.0 | 2473.5 | 2376.4 | 2258.4 | 2175.2 | 2166.3 |
| 70° | 1974.0 | 1975.0 | 2027.5 | 2102.9 | 2176.2 | 2197.0 | 2150.4 | 2057.3 | 1944.3 | 1877.9 | 1860.1 |
| 72.5° | 1639.1 | 1648.0 | 1694.6 | 1772.9 | 1835.3 | 1840.3 | 1802.6 | 1722.3 | 1630.2 | 1575.7 | 1565.7 |
| 75° | 1332.9 | 1326.9 | 1366.6 | 1414.1 | 1462.7 | 1478.5 | 1447.8 | 1393.3 | 1308.1 | 1260.5 | 1270.4 |
| 77.5° | 1000.9 | 1002.9 | 1033.6 | 1077.2 | 1107.9 | 1135.7 | 1101.0 | 1075.2 | 1006.8 | 952.3 | 954.3 |
| 80° | 707.6 | 705.6 | 734.3 | 755.1 | 789.8 | 793.8 | 774.9 | 740.3 | 696.7 | 673.9 | 671.9 |
| 82.5° | 447.9 | 439.0 | 460.8 | 487.6 | 502.4 | 495.5 | 499.5 | 476.7 | 442.0 | 430.1 | 419.2 |
| 85° | 228.9 | 226.9 | 238.8 | 248.7 | 259.6 | 259.6 | 253.7 | 235.9 | 228.9 | 215.0 | 211.1 |
| 87.5° | 78.3 | 81.3 | 85.2 | 82.3 | 87.2 | 85.2 | 83.2 | 70.4 | 62.4 | 58.5 | 54.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2407-176-9

Test Date: 09/25/2024

Luminaire Tested: MEM2-HTN-VA-130-740-U-RW

Data in this report applies to families of products including MEM2-HTN-VA-130-740-U-RW

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-176-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 09/27/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Streetworks
 Catalog Number: **MEM2-HTN-VA-130-740-U-RW**
 Description: EPIC MODERN VISUAL COMFORT 130W WAVESTREAM RECTANGULAR WIDE

Spectral Parameters

CCT (K): 3887
 CIE u': 0.2262
 CIE v': 0.5060
 Duv: 0.0018
 CIE x: 0.3870
 CIE y: 0.3847
 CIE z: 0.2283
 Peak Wavelength (nm): 583
 Dominant Wavelength (nm): 578
 Purity: 31.59626
 Rf: 74.5
 Rg: 93.5

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.4 | | |
| R1: | 67.6 | R9: | -36.8 |
| R2: | 78.8 | R10: | 50.4 |
| R3: | 88.2 | R11: | 65.0 |
| R4: | 69.8 | R12: | 44.4 |
| R5: | 67.7 | R13: | 69.4 |
| R6: | 70.3 | R14: | 93.3 |
| R7: | 80.1 | R15: | 59.9 |
| R8: | 49.0 | | |



Test Conditions

Stabilization Time: 50M
 Operation Time: 1H 50M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-176-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-176-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-176-9

Photopic Flux vs. Wavelength




Photopic Lumens: NR

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 177 | NR | 620 | 727 | NR | 750 | 21 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 222 | NR | 625 | 666 | NR | 755 | 18 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 286 | NR | 630 | 606 | NR | 760 | 16 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 359 | NR | 635 | 549 | NR | 765 | 14 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 433 | NR | 640 | 493 | NR | 770 | 12 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 505 | NR | 645 | 440 | NR | 775 | 10 | NR | 905 | 0 | NR |
| 390 | 1 | NR | 520 | 562 | NR | 650 | 390 | NR | 780 | 9 | NR | 910 | 0 | NR |
| 395 | 3 | NR | 525 | 613 | NR | 655 | 344 | NR | 785 | 8 | NR | 915 | 0 | NR |
| 400 | 6 | NR | 530 | 654 | NR | 660 | 301 | NR | 790 | 7 | NR | 920 | 0 | NR |
| 405 | 11 | NR | 535 | 692 | NR | 665 | 263 | NR | 795 | 6 | NR | 925 | 0 | NR |
| 410 | 23 | NR | 540 | 726 | NR | 670 | 228 | NR | 800 | 5 | NR | 930 | 0 | NR |
| 415 | 45 | NR | 545 | 763 | NR | 675 | 198 | NR | 805 | 4 | NR | 935 | 0 | NR |
| 420 | 88 | NR | 550 | 798 | NR | 680 | 172 | NR | 810 | 4 | NR | 940 | 0 | NR |
| 425 | 164 | NR | 555 | 837 | NR | 685 | 148 | NR | 815 | 3 | NR | 945 | 0 | NR |
| 430 | 281 | NR | 560 | 878 | NR | 690 | 128 | NR | 820 | 3 | NR | 950 | 0 | NR |
| 435 | 447 | NR | 565 | 915 | NR | 695 | 110 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 642 | NR | 570 | 948 | NR | 700 | 95 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 838 | NR | 575 | 976 | NR | 705 | 81 | NR | 835 | 2 | NR | 965 | 0 | NR |
| 450 | 907 | NR | 580 | 995 | NR | 710 | 69 | NR | 840 | 2 | NR | 970 | 0 | NR |
| 455 | 710 | NR | 585 | 1000 | NR | 715 | 58 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 465 | NR | 590 | 995 | NR | 720 | 49 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 330 | NR | 595 | 972 | NR | 725 | 41 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 236 | NR | 600 | 941 | NR | 730 | 35 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 174 | NR | 605 | 898 | NR | 735 | 30 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 152 | NR | 610 | 848 | NR | 740 | 26 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 155 | NR | 615 | 788 | NR | 745 | 23 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2407-176-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.49

| λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) |
|----------------|--------------------------|----------------------|----------------|--------------------------|----------------------|----------------|--------------------------|----------------------|----------------|--------------------------|----------------------|----------------|--------------------------|----------------------|
| 360 | 0 | NR | 490 | 177 | NR | 620 | 727 | NR | 750 | 21 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 222 | NR | 625 | 666 | NR | 755 | 18 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 286 | NR | 630 | 606 | NR | 760 | 16 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 359 | NR | 635 | 549 | NR | 765 | 14 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 433 | NR | 640 | 493 | NR | 770 | 12 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 505 | NR | 645 | 440 | NR | 775 | 10 | NR | 905 | 0 | NR |
| 390 | 1 | NR | 520 | 562 | NR | 650 | 390 | NR | 780 | 9 | NR | 910 | 0 | NR |
| 395 | 3 | NR | 525 | 613 | NR | 655 | 344 | NR | 785 | 8 | NR | 915 | 0 | NR |
| 400 | 6 | NR | 530 | 654 | NR | 660 | 301 | NR | 790 | 7 | NR | 920 | 0 | NR |
| 405 | 11 | NR | 535 | 692 | NR | 665 | 263 | NR | 795 | 6 | NR | 925 | 0 | NR |
| 410 | 23 | NR | 540 | 726 | NR | 670 | 228 | NR | 800 | 5 | NR | 930 | 0 | NR |
| 415 | 45 | NR | 545 | 763 | NR | 675 | 198 | NR | 805 | 4 | NR | 935 | 0 | NR |
| 420 | 88 | NR | 550 | 798 | NR | 680 | 172 | NR | 810 | 4 | NR | 940 | 0 | NR |
| 425 | 164 | NR | 555 | 837 | NR | 685 | 148 | NR | 815 | 3 | NR | 945 | 0 | NR |
| 430 | 281 | NR | 560 | 878 | NR | 690 | 128 | NR | 820 | 3 | NR | 950 | 0 | NR |
| 435 | 447 | NR | 565 | 915 | NR | 695 | 110 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 642 | NR | 570 | 948 | NR | 700 | 95 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 838 | NR | 575 | 976 | NR | 705 | 81 | NR | 835 | 2 | NR | 965 | 0 | NR |
| 450 | 907 | NR | 580 | 995 | NR | 710 | 69 | NR | 840 | 2 | NR | 970 | 0 | NR |
| 455 | 710 | NR | 585 | 1000 | NR | 715 | 58 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 465 | NR | 590 | 995 | NR | 720 | 49 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 330 | NR | 595 | 972 | NR | 725 | 41 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 236 | NR | 600 | 941 | NR | 730 | 35 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 174 | NR | 605 | 898 | NR | 735 | 30 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 152 | NR | 610 | 848 | NR | 740 | 26 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 155 | NR | 615 | 788 | NR | 745 | 23 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2407-176-9

Melanopic Flux vs. Wavelength




Melanopic Lumens: NR

M/P: 2.89


| λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) |
|----------------|--------------------------|----------------------|----------------|--------------------------|----------------------|----------------|--------------------------|----------------------|----------------|--------------------------|----------------------|----------------|--------------------------|----------------------|
| 360 | 0 | NR | 490 | 177 | NR | 620 | 727 | NR | 750 | 21 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 222 | NR | 625 | 666 | NR | 755 | 18 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 286 | NR | 630 | 606 | NR | 760 | 16 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 359 | NR | 635 | 549 | NR | 765 | 14 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 433 | NR | 640 | 493 | NR | 770 | 12 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 505 | NR | 645 | 440 | NR | 775 | 10 | NR | 905 | 0 | NR |
| 390 | 1 | NR | 520 | 562 | NR | 650 | 390 | NR | 780 | 9 | NR | 910 | 0 | NR |
| 395 | 3 | NR | 525 | 613 | NR | 655 | 344 | NR | 785 | 8 | NR | 915 | 0 | NR |
| 400 | 6 | NR | 530 | 654 | NR | 660 | 301 | NR | 790 | 7 | NR | 920 | 0 | NR |
| 405 | 11 | NR | 535 | 692 | NR | 665 | 263 | NR | 795 | 6 | NR | 925 | 0 | NR |
| 410 | 23 | NR | 540 | 726 | NR | 670 | 228 | NR | 800 | 5 | NR | 930 | 0 | NR |
| 415 | 45 | NR | 545 | 763 | NR | 675 | 198 | NR | 805 | 4 | NR | 935 | 0 | NR |
| 420 | 88 | NR | 550 | 798 | NR | 680 | 172 | NR | 810 | 4 | NR | 940 | 0 | NR |
| 425 | 164 | NR | 555 | 837 | NR | 685 | 148 | NR | 815 | 3 | NR | 945 | 0 | NR |
| 430 | 281 | NR | 560 | 878 | NR | 690 | 128 | NR | 820 | 3 | NR | 950 | 0 | NR |
| 435 | 447 | NR | 565 | 915 | NR | 695 | 110 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 642 | NR | 570 | 948 | NR | 700 | 95 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 838 | NR | 575 | 976 | NR | 705 | 81 | NR | 835 | 2 | NR | 965 | 0 | NR |
| 450 | 907 | NR | 580 | 995 | NR | 710 | 69 | NR | 840 | 2 | NR | 970 | 0 | NR |
| 455 | 710 | NR | 585 | 1000 | NR | 715 | 58 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 465 | NR | 590 | 995 | NR | 720 | 49 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 330 | NR | 595 | 972 | NR | 725 | 41 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 236 | NR | 600 | 941 | NR | 730 | 35 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 174 | NR | 605 | 898 | NR | 735 | 30 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 152 | NR | 610 | 848 | NR | 740 | 26 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 155 | NR | 615 | 788 | NR | 745 | 23 | NR | 875 | 0 | NR | | | |

Summary

$R_f = 74.5$
 $R_g = 93.5$
 $CIE R_a = 71.4$
 $R_g = -36.8$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 63 | CES51 = 88 | CES76 = 54 |
| CES02 = 61 | CES27 = 88 | CES52 = 87 | CES77 = 72 |
| CES03 = 30 | CES28 = 82 | CES53 = 77 | CES78 = 57 |
| CES04 = 70 | CES29 = 66 | CES54 = 84 | CES79 = 83 |
| CES05 = 47 | CES30 = 81 | CES55 = 83 | CES80 = 80 |
| CES06 = 50 | CES31 = 70 | CES56 = 73 | CES81 = 78 |
| CES07 = 40 | CES32 = 63 | CES57 = 73 | CES82 = 92 |
| CES08 = 39 | CES33 = 77 | CES58 = 74 | CES83 = 90 |
| CES09 = 29 | CES34 = 72 | CES59 = 85 | CES84 = 87 |
| CES10 = 74 | CES35 = 85 | CES60 = 90 | CES85 = 79 |
| CES11 = 57 | CES36 = 94 | CES61 = 82 | CES86 = 71 |
| CES12 = 63 | CES37 = 80 | CES62 = 87 | CES87 = 77 |
| CES13 = 42 | CES38 = 90 | CES63 = 74 | CES88 = 80 |
| CES14 = 74 | CES39 = 96 | CES64 = 66 | CES89 = 71 |
| CES15 = 71 | CES40 = 92 | CES65 = 63 | CES90 = 79 |
| CES16 = 46 | CES41 = 93 | CES66 = 60 | CES91 = 78 |
| CES17 = 49 | CES42 = 83 | CES67 = 57 | CES92 = 59 |
| CES18 = 56 | CES43 = 79 | CES68 = 65 | CES93 = 75 |
| CES19 = 72 | CES44 = 99 | CES69 = 74 | CES94 = 52 |
| CES20 = 65 | CES45 = 86 | CES70 = 58 | CES95 = 67 |
| CES21 = 86 | CES46 = 83 | CES71 = 53 | CES96 = 77 |
| CES22 = 78 | CES47 = 86 | CES72 = 84 | CES97 = 85 |
| CES23 = 92 | CES48 = 76 | CES73 = 49 | CES98 = 75 |
| CES24 = 91 | CES49 = 81 | CES74 = 95 | CES99 = 62 |
| CES25 = 72 | CES50 = 88 | CES75 = 55 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)