

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P879599

Luminaire Tested: **MEM2-HTN-VA-130-740-U-CQ**

Issue Date: 10/01/2024



Test Information

Test Method: LM-79-08
Report Number: P879599
Test Lab: INNOVATION CENTER(G3)
Issue Date: 10/01/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: MEM2-HTN-VA-130-740-U-CQ
Description: EPIC MODERN TALL HOUSING 130W 70CRI 4000K VISUAL COMFORT FIXTURE w/
TYPE V CONCENTRATED DISTRIBUTION OPTIC
Light Source: (1) 4000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12493.1 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Luminous Opening: Circular (Dia: 1.12' x H: 0')
IES Classification: Type V - Short
BUG Rating: B3 - U0 - G2

Input Watts (W): 130
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.995
Total Harmonic Distortion (THDi): 8.1%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

REPORT NUMBER: P879599
 CATALOG NUMBER: MEM2-HTN-VA-130-740-U-CQ

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 13.9 fc
 Type V - Short - N/A

REPORT NUMBER: P879599
CATALOG NUMBER: MEM2-HTN-VA-130-740-U-CQ

Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral - - - Horizontal Cone Through 0-Deg Vertical

REPORT NUMBER: P879599
 CATALOG NUMBER: MEM2-HTN-VA-130-740-U-CQ


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 6246.5 | 0.0 | 6246.5 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Street Side | Lumens | 6246.5 | 0.0 | 6246.5 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Total | Lumens | 12493.1 | 0.0 | 12493.1 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

Coefficient of Utilization

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 293.9 | 2.4 |
| 10°-20° | 847.9 | 6.8 |
| 20°-30° | 1357.6 | 10.9 |
| 30°-40° | 1839.0 | 14.7 |
| 40°-50° | 2271.0 | 18.2 |
| 50°-60° | 2440.0 | 19.5 |
| 60°-70° | 2051.9 | 16.4 |
| 70°-80° | 1145.7 | 9.2 |
| 80°-90° | 246.2 | 2.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 12493.1 | 100.0 |
| 0°-180° | 12493.1 | 100.0 |



REPORT NUMBER: P879599


CATALOG NUMBER: MEM2-HTN-VA-130-740-U-CQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1249.7 | 10.0 | | | |
| FM (30°-60°) | 3275.0 | 26.2 | | | |
| FH (60°-80°) | 1598.8 | 12.8 | | | G1/1800 |
| FVH (80°-90°) | 123.1 | 1.0 | | | G2/225 |
| BL (0°-30°) | 1249.7 | 10.0 | B3/2500 | | |
| BM (30°-60°) | 3275.0 | 26.2 | B3/5000 | | |
| BH (60°-80°) | 1598.8 | 12.8 | B3/2500 | | G1/1800 |
| BVH (80°-90°) | 123.1 | 1.0 | | | G2/225 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G2

Type V Short





REPORT NUMBER: P879599

CATALOG NUMBER: MEM2-HTN-VA-130-740-U-CQ

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 90° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3118.4 | 3118.4 | 3118.4 | 3118.4 | 3118.4 | 3118.4 | 3118.4 | 3118.4 | 3118.4 | 3118.4 | 3118.4 |
| 2.5° | 3109.1 | 3112.2 | 3111.5 | 3111.5 | 3111.5 | 3113.0 | 3113.0 | 3113.0 | 3113.8 | 3113.8 | 3114.5 |
| 5° | 3091.3 | 3093.6 | 3093.6 | 3093.6 | 3095.2 | 3096.0 | 3096.0 | 3096.7 | 3098.3 | 3097.5 | 3096.7 |
| 7.5° | 3067.3 | 3069.6 | 3069.6 | 3069.6 | 3071.2 | 3072.7 | 3072.7 | 3071.9 | 3074.3 | 3074.3 | 3073.5 |
| 10° | 3041.7 | 3042.5 | 3043.3 | 3044.8 | 3047.2 | 3047.9 | 3047.2 | 3047.2 | 3046.4 | 3047.2 | 3047.2 |
| 12.5° | 3011.5 | 3015.4 | 3016.2 | 3017.7 | 3021.6 | 3022.4 | 3022.4 | 3021.6 | 3020.8 | 3020.8 | 3020.1 |
| 15° | 2984.4 | 2986.0 | 2988.3 | 2991.4 | 2996.0 | 2997.6 | 2998.4 | 2996.0 | 2993.7 | 2992.9 | 2993.7 |
| 17.5° | 2959.6 | 2962.0 | 2965.1 | 2968.2 | 2974.4 | 2977.5 | 2977.5 | 2974.4 | 2971.3 | 2969.7 | 2969.7 |
| 20° | 2939.5 | 2941.8 | 2945.7 | 2950.3 | 2958.9 | 2962.7 | 2961.2 | 2958.1 | 2952.7 | 2950.3 | 2951.1 |
| 22.5° | 2926.3 | 2929.4 | 2932.5 | 2939.5 | 2948.8 | 2953.4 | 2951.9 | 2946.5 | 2940.3 | 2936.4 | 2936.4 |
| 25° | 2915.5 | 2917.8 | 2922.5 | 2931.8 | 2941.8 | 2947.2 | 2944.9 | 2937.9 | 2929.4 | 2924.8 | 2924.0 |
| 27.5° | 2903.1 | 2906.2 | 2912.4 | 2924.8 | 2937.2 | 2941.8 | 2940.3 | 2930.2 | 2920.1 | 2913.9 | 2912.4 |
| 30° | 2891.5 | 2894.6 | 2903.1 | 2917.0 | 2932.5 | 2939.5 | 2935.6 | 2924.8 | 2912.4 | 2904.6 | 2903.9 |
| 32.5° | 2883.7 | 2887.6 | 2897.7 | 2915.5 | 2934.1 | 2944.1 | 2940.3 | 2927.1 | 2910.8 | 2900.8 | 2900.0 |
| 35° | 2880.6 | 2884.5 | 2899.2 | 2920.9 | 2944.1 | 2958.1 | 2952.7 | 2936.4 | 2916.3 | 2903.9 | 2902.3 |
| 37.5° | 2881.4 | 2886.1 | 2904.6 | 2933.3 | 2962.7 | 2977.5 | 2970.5 | 2949.6 | 2924.0 | 2907.0 | 2904.6 |
| 40° | 2884.5 | 2889.9 | 2913.9 | 2949.6 | 2984.4 | 2998.4 | 2987.5 | 2956.5 | 2921.7 | 2897.7 | 2893.0 |
| 42.5° | 2888.4 | 2896.9 | 2926.3 | 2968.2 | 3004.6 | 3016.2 | 2996.8 | 2951.1 | 2902.3 | 2871.3 | 2867.5 |
| 45° | 2887.6 | 2894.6 | 2928.7 | 2978.2 | 3017.0 | 3023.2 | 2991.4 | 2934.1 | 2876.8 | 2836.5 | 2833.4 |
| 47.5° | 2874.4 | 2881.4 | 2920.1 | 2975.1 | 3013.1 | 3014.6 | 2976.7 | 2910.8 | 2843.4 | 2797.0 | 2792.3 |
| 50° | 2833.4 | 2842.7 | 2886.1 | 2946.5 | 2989.1 | 2989.8 | 2948.0 | 2875.2 | 2797.0 | 2742.8 | 2735.0 |
| 52.5° | 2770.6 | 2777.6 | 2828.0 | 2893.0 | 2941.0 | 2947.2 | 2901.5 | 2817.1 | 2728.0 | 2669.9 | 2664.5 |
| 55° | 2673.0 | 2687.0 | 2740.4 | 2808.6 | 2861.3 | 2868.2 | 2822.5 | 2731.1 | 2639.7 | 2573.1 | 2566.9 |
| 57.5° | 2560.0 | 2562.3 | 2618.8 | 2693.2 | 2748.2 | 2755.9 | 2706.4 | 2613.4 | 2518.1 | 2456.2 | 2440.7 |
| 60° | 2400.4 | 2409.7 | 2463.1 | 2535.9 | 2594.0 | 2604.1 | 2556.9 | 2467.0 | 2367.9 | 2297.4 | 2296.6 |
| 62.5° | 2216.0 | 2226.9 | 2281.1 | 2358.6 | 2417.4 | 2427.5 | 2377.2 | 2289.6 | 2190.5 | 2130.1 | 2108.4 |
| 65° | 2016.2 | 2019.3 | 2073.5 | 2150.2 | 2203.7 | 2209.1 | 2169.6 | 2086.7 | 1984.5 | 1922.5 | 1908.5 |
| 67.5° | 1791.6 | 1794.7 | 1836.5 | 1908.5 | 1965.9 | 1973.6 | 1933.3 | 1857.4 | 1765.2 | 1700.2 | 1693.2 |
| 70° | 1542.9 | 1543.7 | 1584.8 | 1643.6 | 1701.0 | 1717.2 | 1680.8 | 1608.0 | 1519.7 | 1467.8 | 1453.9 |
| 72.5° | 1281.1 | 1288.1 | 1324.5 | 1385.7 | 1434.5 | 1438.4 | 1408.9 | 1346.2 | 1274.2 | 1231.6 | 1223.8 |
| 75° | 1041.8 | 1037.2 | 1068.1 | 1105.3 | 1143.3 | 1155.7 | 1131.6 | 1089.0 | 1022.4 | 985.3 | 993.0 |
| 77.5° | 782.3 | 783.9 | 807.9 | 842.0 | 866.0 | 887.7 | 860.5 | 840.4 | 787.0 | 744.4 | 745.9 |
| 80° | 553.0 | 551.5 | 574.0 | 590.2 | 617.3 | 620.4 | 605.7 | 578.6 | 544.5 | 526.7 | 525.2 |
| 82.5° | 350.1 | 343.1 | 360.2 | 381.1 | 392.7 | 387.3 | 390.4 | 372.6 | 345.5 | 336.2 | 327.6 |
| 85° | 178.9 | 177.4 | 186.7 | 194.4 | 202.9 | 202.9 | 198.3 | 184.3 | 178.9 | 168.1 | 165.0 |
| 87.5° | 61.2 | 63.5 | 66.6 | 64.3 | 68.2 | 66.6 | 65.1 | 55.0 | 48.8 | 45.7 | 42.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2407-176-9

Test Date: 09/25/2024

Luminaire Tested: MEM2-HTN-VA-130-740-U-RW

Data in this report applies to families of products including MEM2-HTN-VA-130-740-U-RW

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-176-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 09/27/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Streetworks
 Catalog Number: **MEM2-HTN-VA-130-740-U-RW**
 Description: EPIC MODERN VISUAL COMFORT 130W WAVESTREAM RECTANGULAR WIDE

Spectral Parameters

CCT (K): 3887
 CIE u': 0.2262
 CIE v': 0.5060
 Duv: 0.0018
 CIE x: 0.3870
 CIE y: 0.3847
 CIE z: 0.2283
 Peak Wavelength (nm): 583
 Dominant Wavelength (nm): 578
 Purity: 31.59626
 Rf: 74.5
 Rg: 93.5

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.4 | | |
| R1: | 67.6 | R9: | -36.8 |
| R2: | 78.8 | R10: | 50.4 |
| R3: | 88.2 | R11: | 65.0 |
| R4: | 69.8 | R12: | 44.4 |
| R5: | 67.7 | R13: | 69.4 |
| R6: | 70.3 | R14: | 93.3 |
| R7: | 80.1 | R15: | 59.9 |
| R8: | 49.0 | | |



Test Conditions

Stabilization Time: 50M
 Operation Time: 1H 50M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-176-9

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-176-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 3887K
 CIE x = 0.3870
 CIE y = 0.3847
 Duv = 0.0018

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-176-9

Photopic Flux vs. Wavelength




Photopic Luminous Efficacy Function

Photopic Lumens: NR

| λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) |
|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|
| 360 | 0 | NR | 490 | 177 | NR | 620 | 727 | NR | 750 | 21 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 222 | NR | 625 | 666 | NR | 755 | 18 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 286 | NR | 630 | 606 | NR | 760 | 16 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 359 | NR | 635 | 549 | NR | 765 | 14 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 433 | NR | 640 | 493 | NR | 770 | 12 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 505 | NR | 645 | 440 | NR | 775 | 10 | NR | 905 | 0 | NR |
| 390 | 1 | NR | 520 | 562 | NR | 650 | 390 | NR | 780 | 9 | NR | 910 | 0 | NR |
| 395 | 3 | NR | 525 | 613 | NR | 655 | 344 | NR | 785 | 8 | NR | 915 | 0 | NR |
| 400 | 6 | NR | 530 | 654 | NR | 660 | 301 | NR | 790 | 7 | NR | 920 | 0 | NR |
| 405 | 11 | NR | 535 | 692 | NR | 665 | 263 | NR | 795 | 6 | NR | 925 | 0 | NR |
| 410 | 23 | NR | 540 | 726 | NR | 670 | 228 | NR | 800 | 5 | NR | 930 | 0 | NR |
| 415 | 45 | NR | 545 | 763 | NR | 675 | 198 | NR | 805 | 4 | NR | 935 | 0 | NR |
| 420 | 88 | NR | 550 | 798 | NR | 680 | 172 | NR | 810 | 4 | NR | 940 | 0 | NR |
| 425 | 164 | NR | 555 | 837 | NR | 685 | 148 | NR | 815 | 3 | NR | 945 | 0 | NR |
| 430 | 281 | NR | 560 | 878 | NR | 690 | 128 | NR | 820 | 3 | NR | 950 | 0 | NR |
| 435 | 447 | NR | 565 | 915 | NR | 695 | 110 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 642 | NR | 570 | 948 | NR | 700 | 95 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 838 | NR | 575 | 976 | NR | 705 | 81 | NR | 835 | 2 | NR | 965 | 0 | NR |
| 450 | 907 | NR | 580 | 995 | NR | 710 | 69 | NR | 840 | 2 | NR | 970 | 0 | NR |
| 455 | 710 | NR | 585 | 1000 | NR | 715 | 58 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 465 | NR | 590 | 995 | NR | 720 | 49 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 330 | NR | 595 | 972 | NR | 725 | 41 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 236 | NR | 600 | 941 | NR | 730 | 35 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 174 | NR | 605 | 898 | NR | 735 | 30 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 152 | NR | 610 | 848 | NR | 740 | 26 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 155 | NR | 615 | 788 | NR | 745 | 23 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2407-176-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.49

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 177 | NR | 620 | 727 | NR | 750 | 21 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 222 | NR | 625 | 666 | NR | 755 | 18 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 286 | NR | 630 | 606 | NR | 760 | 16 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 359 | NR | 635 | 549 | NR | 765 | 14 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 433 | NR | 640 | 493 | NR | 770 | 12 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 505 | NR | 645 | 440 | NR | 775 | 10 | NR | 905 | 0 | NR |
| 390 | 1 | NR | 520 | 562 | NR | 650 | 390 | NR | 780 | 9 | NR | 910 | 0 | NR |
| 395 | 3 | NR | 525 | 613 | NR | 655 | 344 | NR | 785 | 8 | NR | 915 | 0 | NR |
| 400 | 6 | NR | 530 | 654 | NR | 660 | 301 | NR | 790 | 7 | NR | 920 | 0 | NR |
| 405 | 11 | NR | 535 | 692 | NR | 665 | 263 | NR | 795 | 6 | NR | 925 | 0 | NR |
| 410 | 23 | NR | 540 | 726 | NR | 670 | 228 | NR | 800 | 5 | NR | 930 | 0 | NR |
| 415 | 45 | NR | 545 | 763 | NR | 675 | 198 | NR | 805 | 4 | NR | 935 | 0 | NR |
| 420 | 88 | NR | 550 | 798 | NR | 680 | 172 | NR | 810 | 4 | NR | 940 | 0 | NR |
| 425 | 164 | NR | 555 | 837 | NR | 685 | 148 | NR | 815 | 3 | NR | 945 | 0 | NR |
| 430 | 281 | NR | 560 | 878 | NR | 690 | 128 | NR | 820 | 3 | NR | 950 | 0 | NR |
| 435 | 447 | NR | 565 | 915 | NR | 695 | 110 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 642 | NR | 570 | 948 | NR | 700 | 95 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 838 | NR | 575 | 976 | NR | 705 | 81 | NR | 835 | 2 | NR | 965 | 0 | NR |
| 450 | 907 | NR | 580 | 995 | NR | 710 | 69 | NR | 840 | 2 | NR | 970 | 0 | NR |
| 455 | 710 | NR | 585 | 1000 | NR | 715 | 58 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 465 | NR | 590 | 995 | NR | 720 | 49 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 330 | NR | 595 | 972 | NR | 725 | 41 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 236 | NR | 600 | 941 | NR | 730 | 35 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 174 | NR | 605 | 898 | NR | 735 | 30 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 152 | NR | 610 | 848 | NR | 740 | 26 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 155 | NR | 615 | 788 | NR | 745 | 23 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2407-176-9

Melanopic Flux vs. Wavelength




Melanopic Lumens: NR

M/P: 2.89

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 177 | NR | 620 | 727 | NR | 750 | 21 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 222 | NR | 625 | 666 | NR | 755 | 18 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 286 | NR | 630 | 606 | NR | 760 | 16 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 359 | NR | 635 | 549 | NR | 765 | 14 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 433 | NR | 640 | 493 | NR | 770 | 12 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 505 | NR | 645 | 440 | NR | 775 | 10 | NR | 905 | 0 | NR |
| 390 | 1 | NR | 520 | 562 | NR | 650 | 390 | NR | 780 | 9 | NR | 910 | 0 | NR |
| 395 | 3 | NR | 525 | 613 | NR | 655 | 344 | NR | 785 | 8 | NR | 915 | 0 | NR |
| 400 | 6 | NR | 530 | 654 | NR | 660 | 301 | NR | 790 | 7 | NR | 920 | 0 | NR |
| 405 | 11 | NR | 535 | 692 | NR | 665 | 263 | NR | 795 | 6 | NR | 925 | 0 | NR |
| 410 | 23 | NR | 540 | 726 | NR | 670 | 228 | NR | 800 | 5 | NR | 930 | 0 | NR |
| 415 | 45 | NR | 545 | 763 | NR | 675 | 198 | NR | 805 | 4 | NR | 935 | 0 | NR |
| 420 | 88 | NR | 550 | 798 | NR | 680 | 172 | NR | 810 | 4 | NR | 940 | 0 | NR |
| 425 | 164 | NR | 555 | 837 | NR | 685 | 148 | NR | 815 | 3 | NR | 945 | 0 | NR |
| 430 | 281 | NR | 560 | 878 | NR | 690 | 128 | NR | 820 | 3 | NR | 950 | 0 | NR |
| 435 | 447 | NR | 565 | 915 | NR | 695 | 110 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 642 | NR | 570 | 948 | NR | 700 | 95 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 838 | NR | 575 | 976 | NR | 705 | 81 | NR | 835 | 2 | NR | 965 | 0 | NR |
| 450 | 907 | NR | 580 | 995 | NR | 710 | 69 | NR | 840 | 2 | NR | 970 | 0 | NR |
| 455 | 710 | NR | 585 | 1000 | NR | 715 | 58 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 465 | NR | 590 | 995 | NR | 720 | 49 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 330 | NR | 595 | 972 | NR | 725 | 41 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 236 | NR | 600 | 941 | NR | 730 | 35 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 174 | NR | 605 | 898 | NR | 735 | 30 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 152 | NR | 610 | 848 | NR | 740 | 26 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 155 | NR | 615 | 788 | NR | 745 | 23 | NR | 875 | 0 | NR | | | |

Summary

$R_f = 74.5$
 $R_g = 93.5$
 $CIE R_a = 71.4$
 $R_g = -36.8$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 63 | CES51 = 88 | CES76 = 54 |
| CES02 = 61 | CES27 = 88 | CES52 = 87 | CES77 = 72 |
| CES03 = 30 | CES28 = 82 | CES53 = 77 | CES78 = 57 |
| CES04 = 70 | CES29 = 66 | CES54 = 84 | CES79 = 83 |
| CES05 = 47 | CES30 = 81 | CES55 = 83 | CES80 = 80 |
| CES06 = 50 | CES31 = 70 | CES56 = 73 | CES81 = 78 |
| CES07 = 40 | CES32 = 63 | CES57 = 73 | CES82 = 92 |
| CES08 = 39 | CES33 = 77 | CES58 = 74 | CES83 = 90 |
| CES09 = 29 | CES34 = 72 | CES59 = 85 | CES84 = 87 |
| CES10 = 74 | CES35 = 85 | CES60 = 90 | CES85 = 79 |
| CES11 = 57 | CES36 = 94 | CES61 = 82 | CES86 = 71 |
| CES12 = 63 | CES37 = 80 | CES62 = 87 | CES87 = 77 |
| CES13 = 42 | CES38 = 90 | CES63 = 74 | CES88 = 80 |
| CES14 = 74 | CES39 = 96 | CES64 = 66 | CES89 = 71 |
| CES15 = 71 | CES40 = 92 | CES65 = 63 | CES90 = 79 |
| CES16 = 46 | CES41 = 93 | CES66 = 60 | CES91 = 78 |
| CES17 = 49 | CES42 = 83 | CES67 = 57 | CES92 = 59 |
| CES18 = 56 | CES43 = 79 | CES68 = 65 | CES93 = 75 |
| CES19 = 72 | CES44 = 99 | CES69 = 74 | CES94 = 52 |
| CES20 = 65 | CES45 = 86 | CES70 = 58 | CES95 = 67 |
| CES21 = 86 | CES46 = 83 | CES71 = 53 | CES96 = 77 |
| CES22 = 78 | CES47 = 86 | CES72 = 84 | CES97 = 85 |
| CES23 = 92 | CES48 = 76 | CES73 = 49 | CES98 = 75 |
| CES24 = 91 | CES49 = 81 | CES74 = 95 | CES99 = 62 |
| CES25 = 72 | CES50 = 88 | CES75 = 55 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)