

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P212590

Luminaire Tested: **MPB-AF-D-U-SYM-7060-600**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P212590  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25988)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: MPB-AF-D-U-SYM-7060-600  
Description: BRECKENRIDGE LED POST-TOP LUMINAIRE  
(1) 70 CRI, 5700K, 615mA LIGHTSQUARE WITH 16 LEDS AND SYMMETRIC OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3282 lumens  
Efficiency: N/A  
Efficacy: 96.5 lumens/watt  
Luminous Opening: Vertical Cylinder (Dia: 1' x H: 0.62')  
IES Classification: Type V - Short - Non-Cutoff  
BUG Rating: B1 - U3 - G2

Input Watts (W): 34  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P212590

CATALOG NUMBER: MPB-AF-D-U-SYM-7060-600

### Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 3.5 fc  
 Type V - Short - Non-Cutoff

REPORT NUMBER: P212590

CATALOG NUMBER: MPB-AF-D-U-SYM-7060-600

### Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral

- - - Horizontal Cone Through 50-Deg Vertical



REPORT NUMBER: P212590

CATALOG NUMBER: MPB-AF-D-U-SYM-7060-600


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1334.0	307.0	1641.0
	% Fixture	40.6	9.4	50.0
<b>Street Side</b>	Lumens	1334.0	307.0	1641.0
	% Fixture	40.6	9.4	50.0
<b>Total</b>	Lumens	2668.0	614.0	3282.0
	% Fixture	81.3	18.7	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	31.8	1.0
10°-20°	110.1	3.4
20°-30°	195.3	6.0
30°-40°	332.7	10.1
40°-50°	543.3	16.6
50°-60°	569.3	17.3
60°-70°	357.9	10.9
70°-80°	305.1	9.3
80°-90°	222.5	6.8
90°-100°	154.8	4.7
100°-110°	133.5	4.1
110°-120°	150.3	4.6
120°-130°	121.4	3.7
130°-140°	46.6	1.4
140°-150°	7.2	0.2
150°-160°	0.3	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2668.0	81.3
0°-180°	3282.0	100.0



REPORT NUMBER: P212590


CATALOG NUMBER: MPB-AF-D-U-SYM-7060-600

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	168.6	5.1			
FM (30°-60°)	722.6	22.0			
FH (60°-80°)	331.5	10.1			G0/660
FVH (80°-90°)	111.3	3.4			G2/225
BL (0°-30°)	168.6	5.1	B1/500		
BM (30°-60°)	722.6	22.0	B1/1000		
BH (60°-80°)	331.5	10.1	B1/500		G0/660
BVH (80°-90°)	111.3	3.4			G2/225
UL (90°-100°)	154.8	4.7		U3/500	
UH (100°-180°)	307.0	9.4		U3/500	

**BUG Rating: B1-U3-G2**

Type V Short





REPORT NUMBER: P212590

CATALOG NUMBER: MPB-AF-D-U-SYM-7060-600

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	305.9
2.5°	299.1
5°	313.4
7.5°	341.0
10°	367.0
12.5°	382.1
15°	389.6
17.5°	393.8
20°	398.9
22.5°	406.4
25°	416.5
27.5°	432.4
30°	453.3
32.5°	484.3
35°	522.9
37.5°	564.8
40°	614.2
42.5°	662.0
45°	710.6
47.5°	741.6
50°	753.3
52.5°	726.5
55°	657.8
57.5°	562.3
60°	453.3
62.5°	384.6
65°	346.9
67.5°	328.5
70°	317.6
72.5°	306.7
75°	292.4
77.5°	272.3
80°	248.9
82.5°	223.7
85°	201.9
87.5°	182.7
90°	166.8
92.5°	152.5
95°	139.9
97.5°	129.9
100°	123.2
102.5°	121.5
105°	124.0
107.5°	129.9
110°	135.7



REPORT NUMBER: P212590

CATALOG NUMBER: MPB-AF-D-U-SYM-7060-600

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	143.3
115°	152.5
117.5°	160.9
120°	163.4
122.5°	155.9
125°	135.7
127.5°	116.5
130°	97.2
132.5°	77.9
135°	57.8
137.5°	39.4
140°	26.0
142.5°	15.9
145°	9.2
147.5°	5.0
150°	2.5
152.5°	0.8
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)