

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P868201

Luminaire Tested: **MEM2-HSN-SA-90-722-U-5MQ**

Issue Date: 08/21/2024



Test Information

Test Method: LM-79-08
Report Number: P868201
Test Lab: INNOVATION CENTER(G3)
Issue Date: 08/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: MEM2-HSN-SA-90-722-U-5MQ
Description: EPIC MODERN SHORT HOUSING DISCRETE LED ARRAYS 90W 70CRI 2200K
FITURE w/ TYPE V SQUARE MEDIUM DISTRIBUTION OPTIC
Light Source: (20) 2200K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11467.2 lumens
Efficiency: N/A
Efficacy: 127.4 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 0.33' x H: 0')
IES Classification: Type V - Short
BUG Rating: B3 - U0 - G2

Input Watts (W): 90
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.99
Total Harmonic Distortion (THDi): 6.20%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

REPORT NUMBER: P868201
 CATALOG NUMBER: MEM2-HSN-SA-90-722-U-5MQ

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 3.6 fc
 Type V - Short - N/A

REPORT NUMBER: P868201
CATALOG NUMBER: MEM2-HSN-SA-90-722-U-5MQ

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P868201

CATALOG NUMBER: MEM2-HSN-SA-90-722-U-5MQ


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 5733.6 | 0.0 | 5733.6 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Street Side | Lumens | 5733.6 | 0.0 | 5733.6 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Total | Lumens | 11467.2 | 0.0 | 11467.2 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 137.0 | 1.2 |
| 10°-20° | 417.0 | 3.6 |
| 20°-30° | 733.6 | 6.4 |
| 30°-40° | 1186.3 | 10.3 |
| 40°-50° | 1847.9 | 16.1 |
| 50°-60° | 2702.1 | 23.6 |
| 60°-70° | 3111.6 | 27.1 |
| 70°-80° | 1270.8 | 11.1 |
| 80°-90° | 60.8 | 0.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 11467.2 | 100.0 |
| 0°-180° | 11467.2 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P868201


CATALOG NUMBER: MEM2-HSN-SA-90-722-U-5MQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 643.8 | 5.6 | | | |
| FM (30°-60°) | 2868.2 | 25.0 | | | |
| FH (60°-80°) | 2191.2 | 19.1 | | | G2/5000 |
| FVH (80°-90°) | 30.4 | 0.3 | | | G1/100 |
| BL (0°-30°) | 643.8 | 5.6 | B2/1000 | | |
| BM (30°-60°) | 2868.2 | 25.0 | B3/5000 | | |
| BH (60°-80°) | 2191.2 | 19.1 | B3/2500 | | G2/5000 |
| BVH (80°-90°) | 30.4 | 0.3 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G2

Type V Short





REPORT NUMBER: P868201

CATALOG NUMBER: MEM2-HSN-SA-90-722-U-5MQ

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 90° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1424.9 | 1424.9 | 1424.9 | 1424.9 | 1424.9 | 1424.9 | 1424.9 | 1424.9 | 1424.9 | 1424.9 | 1424.9 |
| 2.5° | 1429.3 | 1429.3 | 1427.1 | 1427.1 | 1422.7 | 1427.1 | 1424.9 | 1427.1 | 1424.9 | 1424.9 | 1427.1 |
| 5° | 1433.7 | 1433.7 | 1429.3 | 1431.5 | 1427.1 | 1429.3 | 1427.1 | 1431.5 | 1429.3 | 1427.1 | 1431.5 |
| 7.5° | 1440.3 | 1440.3 | 1435.9 | 1438.1 | 1433.7 | 1435.9 | 1433.7 | 1438.1 | 1435.9 | 1435.9 | 1438.1 |
| 10° | 1446.9 | 1449.1 | 1444.7 | 1442.5 | 1442.5 | 1444.7 | 1446.9 | 1449.1 | 1446.9 | 1446.9 | 1451.3 |
| 12.5° | 1457.9 | 1460.1 | 1455.7 | 1453.5 | 1453.5 | 1455.7 | 1457.9 | 1462.3 | 1455.7 | 1455.7 | 1455.7 |
| 15° | 1468.9 | 1468.9 | 1466.7 | 1464.5 | 1466.7 | 1468.9 | 1468.9 | 1473.3 | 1468.9 | 1464.5 | 1464.5 |
| 17.5° | 1473.3 | 1475.5 | 1473.3 | 1477.7 | 1479.9 | 1482.1 | 1484.3 | 1484.3 | 1477.7 | 1475.5 | 1475.5 |
| 20° | 1488.7 | 1490.9 | 1486.5 | 1488.7 | 1495.3 | 1504.1 | 1504.1 | 1504.1 | 1504.1 | 1497.5 | 1497.5 |
| 22.5° | 1515.2 | 1517.4 | 1515.2 | 1515.2 | 1524.0 | 1532.8 | 1532.8 | 1539.4 | 1530.6 | 1526.2 | 1526.2 |
| 25° | 1559.2 | 1559.2 | 1557.0 | 1559.2 | 1563.6 | 1568.0 | 1576.8 | 1581.2 | 1581.2 | 1579.0 | 1581.2 |
| 27.5° | 1612.1 | 1614.3 | 1612.1 | 1612.1 | 1609.9 | 1618.7 | 1631.9 | 1638.5 | 1640.7 | 1642.9 | 1642.9 |
| 30° | 1682.5 | 1686.9 | 1684.7 | 1686.9 | 1691.3 | 1697.9 | 1702.4 | 1704.6 | 1704.6 | 1700.2 | 1700.2 |
| 32.5° | 1759.6 | 1764.0 | 1759.6 | 1770.6 | 1786.0 | 1786.0 | 1781.6 | 1790.4 | 1783.8 | 1779.4 | 1775.0 |
| 35° | 1849.9 | 1849.9 | 1854.3 | 1858.7 | 1880.7 | 1891.7 | 1891.7 | 1887.3 | 1874.1 | 1867.5 | 1871.9 |
| 37.5° | 1953.4 | 1955.6 | 1960.0 | 1962.2 | 1982.0 | 2001.9 | 1999.7 | 1988.6 | 1973.2 | 1955.6 | 1955.6 |
| 40° | 2076.7 | 2072.3 | 2074.5 | 2090.0 | 2105.4 | 2129.6 | 2131.8 | 2116.4 | 2090.0 | 2072.3 | 2072.3 |
| 42.5° | 2189.1 | 2191.3 | 2200.1 | 2219.9 | 2255.1 | 2274.9 | 2263.9 | 2237.5 | 2208.9 | 2186.9 | 2184.6 |
| 45° | 2308.0 | 2305.8 | 2330.0 | 2371.8 | 2418.1 | 2442.3 | 2424.7 | 2387.3 | 2343.2 | 2314.6 | 2314.6 |
| 47.5° | 2429.1 | 2426.9 | 2466.5 | 2534.8 | 2594.3 | 2614.1 | 2596.5 | 2548.0 | 2488.6 | 2446.7 | 2440.1 |
| 50° | 2554.6 | 2563.4 | 2605.3 | 2702.2 | 2779.3 | 2801.3 | 2779.3 | 2715.4 | 2636.1 | 2581.1 | 2572.2 |
| 52.5° | 2697.8 | 2704.4 | 2759.4 | 2865.2 | 2959.8 | 3010.5 | 2977.5 | 2882.8 | 2781.5 | 2715.4 | 2706.6 |
| 55° | 2829.9 | 2834.3 | 2913.6 | 3041.3 | 3158.1 | 3226.3 | 3173.5 | 3052.3 | 2924.6 | 2840.9 | 2832.1 |
| 57.5° | 2922.4 | 2933.4 | 3034.7 | 3199.9 | 3349.6 | 3428.9 | 3349.6 | 3219.7 | 3050.1 | 2946.6 | 2940.0 |
| 60° | 2981.9 | 2999.5 | 3116.2 | 3323.2 | 3530.2 | 3616.1 | 3534.6 | 3354.1 | 3144.8 | 3010.5 | 3003.9 |
| 62.5° | 2951.0 | 2975.3 | 3125.0 | 3395.9 | 3684.4 | 3776.9 | 3671.2 | 3417.9 | 3133.8 | 2964.3 | 2946.6 |
| 65° | 2735.2 | 2752.8 | 2964.3 | 3343.0 | 3741.7 | 3884.8 | 3693.2 | 3347.4 | 2984.1 | 2796.9 | 2761.6 |
| 67.5° | 2288.2 | 2319.0 | 2598.7 | 3087.6 | 3618.3 | 3783.5 | 3541.2 | 3094.2 | 2655.9 | 2426.9 | 2387.3 |
| 70° | 1757.4 | 1812.5 | 2118.6 | 2649.3 | 3232.9 | 3420.1 | 3153.6 | 2611.9 | 2096.6 | 1863.1 | 1790.4 |
| 72.5° | 1015.2 | 1101.1 | 1550.4 | 2067.9 | 2572.2 | 2713.2 | 2338.8 | 1825.7 | 1391.8 | 1226.7 | 1206.8 |
| 75° | 336.9 | 367.8 | 737.8 | 1191.4 | 1640.7 | 1711.2 | 1462.3 | 1151.8 | 916.1 | 784.0 | 790.6 |
| 77.5° | 165.2 | 165.2 | 222.4 | 436.0 | 746.6 | 880.9 | 799.4 | 557.2 | 400.8 | 303.9 | 295.1 |
| 80° | 132.1 | 132.1 | 154.2 | 213.6 | 251.1 | 295.1 | 251.1 | 182.8 | 149.8 | 136.5 | 143.1 |
| 82.5° | 63.9 | 61.7 | 72.7 | 103.5 | 105.7 | 101.3 | 94.7 | 94.7 | 90.3 | 83.7 | 81.5 |
| 85° | 4.4 | 4.4 | 8.8 | 19.8 | 33.0 | 44.0 | 50.7 | 48.4 | 46.2 | 39.6 | 44.0 |
| 87.5° | 2.2 | 2.2 | 2.2 | 2.2 | 2.2 | 2.2 | 2.2 | 4.4 | 4.4 | 4.4 | 4.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Streetworks

Report Number: SP1-2407-157-2

Test Date: 08/07/2024

Luminaire Tested: MEM2-HTN-SA-30-722-U-5WQ-2

Data in this report applies to families of products including MEM2-HTN-SA-30-722-U-5WQ-2

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-157-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/20/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Streetworks
 Catalog Number: **MEM2-HTN-SA-30-722-U-5WQ-2**
 Description: Epic Modern Light Square 30W 5WQ Optic and Flare Trim

Spectral Parameters

CCT (K): 2253
 CIE u': 0.2868
 CIE v': 0.5332
 Duv: -0.0014
 CIE x: 0.4974
 CIE y: 0.4110
 CIE z: 0.0915
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 587
 Purity: 72.69432
 Rf: 76.9
 Rg: 92.7

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 70.6 | | |
| R1: | 68.4 | R9: | -36.0 |
| R2: | 88.7 | R10: | 78.2 |
| R3: | 85.4 | R11: | 61.0 |
| R4: | 63.5 | R12: | 74.2 |
| R5: | 69.0 | R13: | 72.8 |
| R6: | 88.9 | R14: | 92.2 |
| R7: | 68.5 | R15: | 58.0 |
| R8: | 32.0 | | |



Test Conditions

Stabilization Time: 29M
 Operation Time: 1H 29M
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2407-157-2

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-157-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2200K 4-step quadrangle

REPORT NUMBER: SP1-2407-157-2

Photopic Flux vs. Wavelength



Photopic Lumens: NR

| λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) |
|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|
| 360 | 0 | NR | 490 | 117 | NR | 620 | 896 | NR | 750 | 20 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 137 | NR | 625 | 838 | NR | 755 | 17 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 160 | NR | 630 | 774 | NR | 760 | 14 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 183 | NR | 635 | 704 | NR | 765 | 12 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 202 | NR | 640 | 635 | NR | 770 | 10 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 219 | NR | 645 | 565 | NR | 775 | 9 | NR | 905 | 0 | NR |
| 390 | 0 | NR | 520 | 235 | NR | 650 | 501 | NR | 780 | 7 | NR | 910 | 0 | NR |
| 395 | 0 | NR | 525 | 249 | NR | 655 | 440 | NR | 785 | 6 | NR | 915 | 0 | NR |
| 400 | 0 | NR | 530 | 263 | NR | 660 | 383 | NR | 790 | 5 | NR | 920 | 0 | NR |
| 405 | 0 | NR | 535 | 281 | NR | 665 | 332 | NR | 795 | 5 | NR | 925 | 0 | NR |
| 410 | 1 | NR | 540 | 302 | NR | 670 | 286 | NR | 800 | 4 | NR | 930 | 0 | NR |
| 415 | 3 | NR | 545 | 331 | NR | 675 | 245 | NR | 805 | 3 | NR | 935 | 0 | NR |
| 420 | 6 | NR | 550 | 366 | NR | 680 | 210 | NR | 810 | 3 | NR | 940 | 0 | NR |
| 425 | 12 | NR | 555 | 411 | NR | 685 | 178 | NR | 815 | 3 | NR | 945 | 0 | NR |
| 430 | 21 | NR | 560 | 469 | NR | 690 | 152 | NR | 820 | 2 | NR | 950 | 0 | NR |
| 435 | 38 | NR | 565 | 536 | NR | 695 | 129 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 66 | NR | 570 | 614 | NR | 700 | 109 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 122 | NR | 575 | 701 | NR | 705 | 92 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 215 | NR | 580 | 785 | NR | 710 | 77 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 236 | NR | 585 | 863 | NR | 715 | 66 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 170 | NR | 590 | 928 | NR | 720 | 55 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 148 | NR | 595 | 971 | NR | 725 | 47 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 132 | NR | 600 | 994 | NR | 730 | 40 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 104 | NR | 605 | 996 | NR | 735 | 33 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 97 | NR | 610 | 979 | NR | 740 | 28 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 105 | NR | 615 | 943 | NR | 745 | 24 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2407-157-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR S/P: 0.96

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 117 | NR | 620 | 896 | NR | 750 | 20 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 137 | NR | 625 | 838 | NR | 755 | 17 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 160 | NR | 630 | 774 | NR | 760 | 14 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 183 | NR | 635 | 704 | NR | 765 | 12 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 202 | NR | 640 | 635 | NR | 770 | 10 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 219 | NR | 645 | 565 | NR | 775 | 9 | NR | 905 | 0 | NR |
| 390 | 0 | NR | 520 | 235 | NR | 650 | 501 | NR | 780 | 7 | NR | 910 | 0 | NR |
| 395 | 0 | NR | 525 | 249 | NR | 655 | 440 | NR | 785 | 6 | NR | 915 | 0 | NR |
| 400 | 0 | NR | 530 | 263 | NR | 660 | 383 | NR | 790 | 5 | NR | 920 | 0 | NR |
| 405 | 0 | NR | 535 | 281 | NR | 665 | 332 | NR | 795 | 5 | NR | 925 | 0 | NR |
| 410 | 1 | NR | 540 | 302 | NR | 670 | 286 | NR | 800 | 4 | NR | 930 | 0 | NR |
| 415 | 3 | NR | 545 | 331 | NR | 675 | 245 | NR | 805 | 3 | NR | 935 | 0 | NR |
| 420 | 6 | NR | 550 | 366 | NR | 680 | 210 | NR | 810 | 3 | NR | 940 | 0 | NR |
| 425 | 12 | NR | 555 | 411 | NR | 685 | 178 | NR | 815 | 3 | NR | 945 | 0 | NR |
| 430 | 21 | NR | 560 | 469 | NR | 690 | 152 | NR | 820 | 2 | NR | 950 | 0 | NR |
| 435 | 38 | NR | 565 | 536 | NR | 695 | 129 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 66 | NR | 570 | 614 | NR | 700 | 109 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 122 | NR | 575 | 701 | NR | 705 | 92 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 215 | NR | 580 | 785 | NR | 710 | 77 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 236 | NR | 585 | 863 | NR | 715 | 66 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 170 | NR | 590 | 928 | NR | 720 | 55 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 148 | NR | 595 | 971 | NR | 725 | 47 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 132 | NR | 600 | 994 | NR | 730 | 40 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 104 | NR | 605 | 996 | NR | 735 | 33 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 97 | NR | 610 | 979 | NR | 740 | 28 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 105 | NR | 615 | 943 | NR | 745 | 24 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2407-157-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 1.71

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 117 | NR | 620 | 896 | NR | 750 | 20 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 137 | NR | 625 | 838 | NR | 755 | 17 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 160 | NR | 630 | 774 | NR | 760 | 14 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 183 | NR | 635 | 704 | NR | 765 | 12 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 202 | NR | 640 | 635 | NR | 770 | 10 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 219 | NR | 645 | 565 | NR | 775 | 9 | NR | 905 | 0 | NR |
| 390 | 0 | NR | 520 | 235 | NR | 650 | 501 | NR | 780 | 7 | NR | 910 | 0 | NR |
| 395 | 0 | NR | 525 | 249 | NR | 655 | 440 | NR | 785 | 6 | NR | 915 | 0 | NR |
| 400 | 0 | NR | 530 | 263 | NR | 660 | 383 | NR | 790 | 5 | NR | 920 | 0 | NR |
| 405 | 0 | NR | 535 | 281 | NR | 665 | 332 | NR | 795 | 5 | NR | 925 | 0 | NR |
| 410 | 1 | NR | 540 | 302 | NR | 670 | 286 | NR | 800 | 4 | NR | 930 | 0 | NR |
| 415 | 3 | NR | 545 | 331 | NR | 675 | 245 | NR | 805 | 3 | NR | 935 | 0 | NR |
| 420 | 6 | NR | 550 | 366 | NR | 680 | 210 | NR | 810 | 3 | NR | 940 | 0 | NR |
| 425 | 12 | NR | 555 | 411 | NR | 685 | 178 | NR | 815 | 3 | NR | 945 | 0 | NR |
| 430 | 21 | NR | 560 | 469 | NR | 690 | 152 | NR | 820 | 2 | NR | 950 | 0 | NR |
| 435 | 38 | NR | 565 | 536 | NR | 695 | 129 | NR | 825 | 2 | NR | 955 | 0 | NR |
| 440 | 66 | NR | 570 | 614 | NR | 700 | 109 | NR | 830 | 2 | NR | 960 | 0 | NR |
| 445 | 122 | NR | 575 | 701 | NR | 705 | 92 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 215 | NR | 580 | 785 | NR | 710 | 77 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 236 | NR | 585 | 863 | NR | 715 | 66 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 170 | NR | 590 | 928 | NR | 720 | 55 | NR | 850 | 1 | NR | 980 | 0 | NR |
| 465 | 148 | NR | 595 | 971 | NR | 725 | 47 | NR | 855 | 1 | NR | 985 | 0 | NR |
| 470 | 132 | NR | 600 | 994 | NR | 730 | 40 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 104 | NR | 605 | 996 | NR | 735 | 33 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 97 | NR | 610 | 979 | NR | 740 | 28 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 105 | NR | 615 | 943 | NR | 745 | 24 | NR | 875 | 0 | NR | | | |

Summary

$R_f = 76.9$
 $R_g = 92.7$
 $CIE R_a = 70.6$
 $R_9 = -36.0$




Color Vector Graphics





Individual Sample Fidelity Index ($R_{f,i}$)



| | | | |
|------------|------------|------------|------------|
| CES01 = 87 | CES26 = 76 | CES51 = 88 | CES76 = 78 |
| CES02 = 65 | CES27 = 94 | CES52 = 85 | CES77 = 75 |
| CES03 = 32 | CES28 = 93 | CES53 = 80 | CES78 = 79 |
| CES04 = 72 | CES29 = 81 | CES54 = 86 | CES79 = 82 |
| CES05 = 51 | CES30 = 91 | CES55 = 83 | CES80 = 81 |
| CES06 = 52 | CES31 = 83 | CES56 = 77 | CES81 = 51 |
| CES07 = 44 | CES32 = 75 | CES57 = 75 | CES82 = 92 |
| CES08 = 42 | CES33 = 88 | CES58 = 76 | CES83 = 88 |
| CES09 = 29 | CES34 = 88 | CES59 = 84 | CES84 = 90 |
| CES10 = 79 | CES35 = 94 | CES60 = 91 | CES85 = 65 |
| CES11 = 62 | CES36 = 90 | CES61 = 82 | CES86 = 48 |
| CES12 = 68 | CES37 = 97 | CES62 = 91 | CES87 = 76 |
| CES13 = 45 | CES38 = 98 | CES63 = 86 | CES88 = 78 |
| CES14 = 75 | CES39 = 97 | CES64 = 70 | CES89 = 61 |
| CES15 = 72 | CES40 = 94 | CES65 = 71 | CES90 = 80 |
| CES16 = 48 | CES41 = 95 | CES66 = 71 | CES91 = 80 |
| CES17 = 51 | CES42 = 89 | CES67 = 70 | CES92 = 51 |
| CES18 = 57 | CES43 = 80 | CES68 = 74 | CES93 = 68 |
| CES19 = 74 | CES44 = 99 | CES69 = 84 | CES94 = 44 |
| CES20 = 68 | CES45 = 83 | CES70 = 72 | CES95 = 66 |
| CES21 = 88 | CES46 = 81 | CES71 = 75 | CES96 = 75 |
| CES22 = 81 | CES47 = 88 | CES72 = 89 | CES97 = 76 |
| CES23 = 92 | CES48 = 73 | CES73 = 68 | CES98 = 72 |
| CES24 = 92 | CES49 = 82 | CES74 = 85 | CES99 = 63 |
| CES25 = 73 | CES50 = 87 | CES75 = 80 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)