

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P598556

Luminaire Tested: **PMM-SA4C-835-U-SLR**

Issue Date: 5/27/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P598556  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1910-543-24)  
Test Lab: INNOVATIONS CENTER  
Issue Date: 5/27/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: PMM-SA4C-835-U-SLR  
Description: MESA POST TOP DECORATIVE LUMINAIRE. (4) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR RIGHT OPTICS.  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 16993 lumens  
Efficiency: N/A  
Efficacy: 75.5 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B3 - U0 - G3


Input Watts (W): 225  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P598556  
 CATALOG NUMBER: PMM-SA4C-835-U-SLR

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 7.2 fc  
 Type IV - Short - N/A

REPORT NUMBER: P598556  
CATALOG NUMBER: PMM-SA4C-835-U-SLR

### Luminous Intensity Polar Plot



REPORT NUMBER: P598556

CATALOG NUMBER: PMM-SA4C-835-U-SLR


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 3291.2   | 0.0    | 3291.2  |
|                    | % Fixture | 19.4     | 0.0    | 19.4    |
| <b>Street Side</b> | Lumens    | 13701.8  | 0.0    | 13701.8 |
|                    | % Fixture | 80.6     | 0.0    | 80.6    |
| <b>Total</b>       | Lumens    | 16993.0  | 0.0    | 16993.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 205.5   | 1.2       |
| 10°-20°   | 597.1   | 3.5       |
| 20°-30°   | 1054.1  | 6.2       |
| 30°-40°   | 1641.6  | 9.7       |
| 40°-50°   | 2702.7  | 15.9      |
| 50°-60°   | 3857.7  | 22.7      |
| 60°-70°   | 4090.5  | 24.1      |
| 70°-80°   | 2259.3  | 13.3      |
| 80°-90°   | 584.6   | 3.4       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 16993.0 | 100.0     |
| 0°-180°   | 16993.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P598556


CATALOG NUMBER: PMM-SA4C-835-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 1300.2 | 7.7       |                         |      |         |
| FM   | (30°-60°)   | 6587.6 | 38.8      |                         |      |         |
| FH   | (60°-80°)   | 5317.2 | 31.3      |                         |      | G3/7500 |
| FVH  | (80°-90°)   | 496.8  | 2.9       |                         |      | G3/500  |
| BL   | (0°-30°)    | 556.4  | 3.3       | B2/1000                 |      |         |
| BM   | (30°-60°)   | 1614.4 | 9.5       | B2/2500                 |      |         |
| BH   | (60°-80°)   | 1032.7 | 6.1       | B3/2500                 |      | G3/2500 |
| BVH  | (80°-90°)   | 87.7   | 0.5       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G3**

Type IV Short





REPORT NUMBER: P598556

CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (FULL):**

|        | 0°      | 2.5°    | 5°      | 7.5°   | 10°    | 12.5°  | 15°    | 17.5°  | 20°    | 22.5°  | 25°    |
|--------|---------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1792.3  | 1792.3  | 1792.3  | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 |
| 2.5°   | 2400.2  | 2415.1  | 2429.1  | 2401.0 | 2373.0 | 2344.1 | 2316.1 | 2274.0 | 2231.1 | 2189.1 | 2146.2 |
| 5°     | 2882.7  | 2828.3  | 2773.0  | 2750.8 | 2729.3 | 2707.0 | 2684.8 | 2664.1 | 2643.5 | 2622.1 | 2601.5 |
| 7.5°   | 3033.7  | 2956.1  | 2877.8  | 2844.8 | 2811.8 | 2778.0 | 2745.0 | 2670.7 | 2596.5 | 2521.5 | 2447.2 |
| 10°    | 2867.9  | 2787.0  | 2705.4  | 2673.2 | 2640.2 | 2608.1 | 2575.1 | 2484.3 | 2394.4 | 2303.7 | 2213.0 |
| 12.5°  | 3001.5  | 2919.0  | 2835.7  | 2733.4 | 2631.2 | 2528.1 | 2425.8 | 2375.5 | 2325.1 | 2274.0 | 2223.7 |
| 15°    | 3130.2  | 3018.8  | 2906.6  | 2804.4 | 2702.1 | 2599.0 | 2496.7 | 2396.1 | 2295.5 | 2194.8 | 2094.2 |
| 17.5°  | 3600.3  | 3414.7  | 3229.1  | 3044.4 | 2858.8 | 2674.0 | 2488.5 | 2372.2 | 2255.0 | 2138.7 | 2021.6 |
| 20°    | 4173.6  | 3915.4  | 3656.4  | 3376.0 | 3094.7 | 2814.3 | 2533.0 | 2386.2 | 2240.2 | 2093.4 | 1946.6 |
| 22.5°  | 4855.7  | 4529.9  | 4204.1  | 3850.2 | 3496.4 | 3141.7 | 2787.9 | 2575.1 | 2362.3 | 2148.6 | 1935.8 |
| 25°    | 5397.6  | 5084.1  | 4770.7  | 4322.0 | 3873.3 | 3424.6 | 2975.9 | 2734.3 | 2492.6 | 2250.1 | 2008.4 |
| 27.5°  | 5923.8  | 5424.8  | 4925.0  | 4411.1 | 3898.1 | 3384.2 | 2870.3 | 2646.8 | 2423.3 | 2199.8 | 1976.3 |
| 30°    | 6368.4  | 5972.5  | 5576.6  | 4906.0 | 4235.4 | 3564.0 | 2893.4 | 2618.8 | 2344.1 | 2069.5 | 1794.8 |
| 32.5°  | 7019.2  | 6454.2  | 5888.3  | 5188.9 | 4489.5 | 3790.0 | 3090.6 | 2739.2 | 2387.8 | 2036.5 | 1685.1 |
| 35°    | 7780.5  | 7193.2  | 6605.9  | 5740.7 | 4876.3 | 4011.1 | 3145.8 | 2773.8 | 2401.0 | 2029.0 | 1656.2 |
| 37.5°  | 9200.0  | 8164.8  | 7128.9  | 6184.4 | 5240.0 | 4294.8 | 3350.4 | 2918.2 | 2486.0 | 2053.0 | 1620.8 |
| 40°    | 9982.7  | 9025.9  | 8069.1  | 6892.1 | 5715.1 | 4537.3 | 3360.3 | 2918.2 | 2475.3 | 2033.2 | 1590.2 |
| 42.5°  | 11026.1 | 9816.1  | 8605.3  | 7332.6 | 6060.7 | 4788.0 | 3515.4 | 3025.4 | 2535.5 | 2044.7 | 1554.8 |
| 45°    | 11662.0 | 10313.5 | 8964.1  | 7604.0 | 6243.8 | 4883.7 | 3523.6 | 3026.2 | 2528.9 | 2031.5 | 1534.2 |
| 47.5°  | 12072.0 | 10777.0 | 9481.2  | 8017.2 | 6553.1 | 5088.3 | 3624.2 | 3096.3 | 2567.6 | 2039.8 | 1511.1 |
| 50°    | 12460.4 | 11177.9 | 9894.5  | 8374.3 | 6855.0 | 5334.9 | 3814.8 | 3238.2 | 2661.7 | 2084.3 | 1507.8 |
| 52.5°  | 12937.2 | 11756.1 | 10574.1 | 8943.4 | 7312.0 | 5681.3 | 4049.8 | 3422.1 | 2794.5 | 2166.8 | 1539.1 |
| 55°    | 13630.9 | 12467.0 | 11302.4 | 9552.2 | 7801.1 | 6050.8 | 4299.7 | 3602.8 | 2906.6 | 2209.7 | 1512.7 |
| 57.5°  | 14080.4 | 12900.1 | 11719.8 | 9934.9 | 8150.0 | 6364.3 | 4579.4 | 3807.3 | 3035.3 | 2262.5 | 1490.4 |
| 60°    | 13931.1 | 12713.7 | 11495.4 | 9793.8 | 8092.2 | 6390.7 | 4689.1 | 3855.2 | 3022.1 | 2188.2 | 1354.3 |
| 62.5°  | 13271.2 | 11977.1 | 10683.0 | 9158.7 | 7635.3 | 6111.0 | 4586.8 | 3738.9 | 2891.8 | 2043.9 | 1196.0 |
| 65°    | 12349.1 | 11011.3 | 9672.6  | 8297.6 | 6922.7 | 5547.7 | 4172.7 | 3403.2 | 2632.8 | 1863.3 | 1092.9 |
| 67.5°  | 11217.5 | 9822.7  | 8427.1  | 7209.7 | 5992.3 | 4774.0 | 3556.6 | 2913.2 | 2270.7 | 1627.4 | 984.0  |
| 70°    | 9798.0  | 8427.1  | 7056.3  | 6003.0 | 4949.7 | 3896.4 | 2843.1 | 2359.0 | 1875.6 | 1391.5 | 907.3  |
| 72.5°  | 7875.3  | 6692.5  | 5509.8  | 4680.8 | 3851.9 | 3022.9 | 2194.0 | 1857.5 | 1521.8 | 1185.3 | 848.7  |
| 75°    | 5601.3  | 4906.0  | 4210.7  | 3565.7 | 2920.7 | 2274.8 | 1629.8 | 1412.1 | 1194.3 | 976.6  | 758.8  |
| 77.5°  | 3980.5  | 3570.6  | 3160.7  | 2655.1 | 2149.5 | 1643.9 | 1138.2 | 1010.4 | 883.4  | 755.5  | 627.7  |
| 80°    | 2942.9  | 2600.6  | 2258.3  | 1877.3 | 1496.2 | 1115.1 | 734.1  | 671.4  | 609.5  | 546.9  | 484.2  |
| 82.5°  | 1937.5  | 1783.2  | 1628.2  | 1326.3 | 1024.4 | 722.5  | 420.7  | 397.6  | 374.5  | 351.4  | 328.3  |
| 85°    | 867.7   | 916.4   | 964.2   | 779.4  | 593.9  | 409.1  | 223.5  | 212.8  | 202.1  | 191.4  | 180.6  |
| 87.5°  | 83.3    | 122.9   | 162.5   | 139.4  | 115.5  | 92.4   | 68.5   | 67.6   | 67.6   | 66.8   | 66.0   |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P598556  
 CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 2.5° | 5°  | 7.5° | 10° | 12.5° | 15° | 17.5° | 20° | 22.5° | 25° |
|--------|-----|------|-----|------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |





REPORT NUMBER: P598556

CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 27.5°  | 30°    | 32.5°  | 35°    | 37.5°  | 40°    | 42.5°  | 45°    | 47.5°  | 50°    | 52.5°  |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 |
| 2.5°   | 2157.7 | 2169.3 | 2180.8 | 2192.4 | 2180.0 | 2167.6 | 2154.4 | 2142.0 | 2126.4 | 2110.7 | 2094.2 |
| 5°     | 2566.8 | 2531.4 | 2496.7 | 2461.2 | 2408.5 | 2355.7 | 2302.1 | 2249.3 | 2242.7 | 2235.2 | 2228.6 |
| 7.5°   | 2382.1 | 2317.7 | 2252.6 | 2187.4 | 2104.9 | 2023.3 | 1940.8 | 1858.3 | 1833.6 | 1808.8 | 1784.1 |
| 10°    | 2169.3 | 2124.7 | 2081.0 | 2036.5 | 1985.3 | 1934.2 | 1882.2 | 1831.1 | 1763.5 | 1695.0 | 1627.4 |
| 12.5°  | 2151.1 | 2078.5 | 2005.1 | 1932.5 | 1901.2 | 1869.9 | 1838.5 | 1807.2 | 1747.8 | 1688.4 | 1628.2 |
| 15°    | 2035.6 | 1976.3 | 1917.7 | 1858.3 | 1812.9 | 1767.6 | 1722.2 | 1676.8 | 1629.0 | 1580.3 | 1532.5 |
| 17.5°  | 1954.0 | 1886.3 | 1818.7 | 1751.1 | 1699.1 | 1647.2 | 1594.4 | 1542.4 | 1484.7 | 1426.1 | 1368.4 |
| 20°    | 1869.0 | 1792.3 | 1714.8 | 1637.3 | 1571.3 | 1506.1 | 1440.1 | 1374.1 | 1310.6 | 1247.9 | 1184.4 |
| 22.5°  | 1834.4 | 1732.9 | 1631.5 | 1530.0 | 1460.7 | 1390.6 | 1321.4 | 1251.2 | 1192.7 | 1134.1 | 1075.6 |
| 25°    | 1887.2 | 1766.7 | 1645.5 | 1524.3 | 1431.1 | 1337.0 | 1243.8 | 1149.8 | 1101.1 | 1052.5 | 1003.0 |
| 27.5°  | 1825.3 | 1673.5 | 1522.6 | 1370.8 | 1271.0 | 1170.4 | 1070.6 | 970.0  | 962.6  | 955.1  | 946.9  |
| 30°    | 1635.6 | 1476.4 | 1317.2 | 1158.0 | 1066.5 | 974.1  | 882.5  | 790.2  | 772.8  | 754.7  | 737.4  |
| 32.5°  | 1522.6 | 1360.1 | 1197.6 | 1035.1 | 953.5  | 871.0  | 789.3  | 706.9  | 687.1  | 667.3  | 647.5  |
| 35°    | 1479.7 | 1303.2 | 1126.7 | 950.2  | 880.1  | 810.0  | 739.9  | 669.7  | 655.7  | 642.5  | 628.5  |
| 37.5°  | 1445.1 | 1270.2 | 1094.5 | 918.8  | 851.2  | 783.6  | 715.1  | 647.5  | 636.8  | 626.0  | 615.3  |
| 40°    | 1412.1 | 1234.7 | 1056.6 | 878.4  | 818.2  | 758.8  | 698.6  | 638.4  | 631.8  | 625.2  | 617.8  |
| 42.5°  | 1382.4 | 1210.0 | 1036.8 | 864.4  | 810.8  | 758.0  | 704.4  | 650.8  | 644.2  | 637.6  | 631.0  |
| 45°    | 1365.9 | 1197.6 | 1029.4 | 861.1  | 822.3  | 783.6  | 744.0  | 705.2  | 689.5  | 673.9  | 657.4  |
| 47.5°  | 1353.5 | 1196.0 | 1038.4 | 880.9  | 840.5  | 800.1  | 759.7  | 719.2  | 705.2  | 691.2  | 676.3  |
| 50°    | 1356.0 | 1205.1 | 1053.3 | 901.5  | 852.9  | 803.4  | 754.7  | 705.2  | 703.6  | 701.9  | 700.3  |
| 52.5°  | 1378.3 | 1218.2 | 1057.4 | 896.6  | 843.8  | 791.0  | 737.4  | 684.6  | 695.3  | 705.2  | 715.9  |
| 55°    | 1346.1 | 1179.5 | 1012.0 | 845.4  | 795.1  | 745.6  | 695.3  | 645.0  | 659.0  | 672.2  | 686.2  |
| 57.5°  | 1309.8 | 1129.2 | 948.5  | 767.9  | 730.0  | 692.0  | 653.3  | 615.3  | 630.2  | 645.8  | 660.7  |
| 60°    | 1189.4 | 1024.4 | 859.5  | 694.5  | 668.9  | 643.4  | 617.8  | 592.2  | 598.8  | 605.4  | 612.0  |
| 62.5°  | 1057.4 | 918.0  | 779.4  | 640.1  | 620.3  | 599.6  | 579.8  | 559.2  | 559.2  | 560.0  | 560.0  |
| 65°    | 973.3  | 853.7  | 734.1  | 614.5  | 592.2  | 569.9  | 546.9  | 524.6  | 521.3  | 518.0  | 514.7  |
| 67.5°  | 889.1  | 795.1  | 700.3  | 605.4  | 573.2  | 541.9  | 509.7  | 477.6  | 473.4  | 470.1  | 466.0  |
| 70°    | 823.2  | 739.0  | 654.9  | 570.8  | 534.5  | 499.0  | 462.7  | 426.4  | 423.1  | 420.7  | 417.4  |
| 72.5°  | 769.6  | 691.2  | 612.0  | 532.8  | 494.9  | 456.1  | 418.2  | 379.4  | 376.9  | 374.5  | 371.2  |
| 75°    | 688.7  | 619.4  | 549.3  | 479.2  | 442.1  | 405.8  | 368.7  | 331.6  | 328.3  | 325.8  | 322.5  |
| 77.5°  | 569.9  | 511.4  | 453.6  | 395.1  | 366.2  | 338.2  | 309.3  | 280.4  | 278.8  | 277.1  | 274.7  |
| 80°    | 438.8  | 393.4  | 347.2  | 301.9  | 282.9  | 263.1  | 244.1  | 224.3  | 223.5  | 222.7  | 221.0  |
| 82.5°  | 301.1  | 273.8  | 246.6  | 219.4  | 205.4  | 190.5  | 176.5  | 161.7  | 162.5  | 163.3  | 164.1  |
| 85°    | 171.6  | 161.7  | 152.6  | 142.7  | 131.1  | 120.4  | 108.9  | 97.3   | 99.8   | 102.3  | 103.9  |
| 87.5°  | 62.7   | 59.4   | 56.1   | 52.8   | 47.0   | 42.1   | 36.3   | 30.5   | 32.2   | 34.6   | 36.3   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P598556

CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30° | 32.5° | 35° | 37.5° | 40° | 42.5° | 45° | 47.5° | 50° | 52.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |



REPORT NUMBER: P598556

CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 55°    | 57.5°  | 60°    | 62.5°  | 65°    | 67.5°  | 70°    | 72.5°  | 75°    | 77.5°  | 80°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 |
| 2.5°   | 2078.5 | 2053.8 | 2029.0 | 2004.3 | 1979.6 | 1928.4 | 1878.1 | 1827.0 | 1775.8 | 1807.2 | 1839.3 |
| 5°     | 2221.2 | 2179.2 | 2136.3 | 2094.2 | 2051.3 | 2027.4 | 2003.5 | 1979.6 | 1955.6 | 1968.0 | 1981.2 |
| 7.5°   | 1759.3 | 1734.6 | 1709.0 | 1684.3 | 1658.7 | 1648.0 | 1638.1 | 1627.4 | 1616.6 | 1647.2 | 1677.7 |
| 10°    | 1558.9 | 1524.3 | 1489.6 | 1454.1 | 1419.5 | 1398.9 | 1378.3 | 1357.6 | 1337.0 | 1345.3 | 1353.5 |
| 12.5°  | 1568.8 | 1517.7 | 1466.5 | 1415.4 | 1364.2 | 1333.7 | 1303.2 | 1272.7 | 1242.2 | 1249.6 | 1257.0 |
| 15°    | 1483.8 | 1431.1 | 1378.3 | 1325.5 | 1272.7 | 1237.2 | 1200.9 | 1165.5 | 1129.2 | 1116.8 | 1103.6 |
| 17.5°  | 1309.8 | 1252.1 | 1194.3 | 1136.6 | 1078.9 | 1054.9 | 1031.0 | 1007.1 | 983.2  | 970.0  | 956.8  |
| 20°    | 1120.9 | 1067.3 | 1013.7 | 960.1  | 906.5  | 890.0  | 873.5  | 856.2  | 839.7  | 831.4  | 822.3  |
| 22.5°  | 1017.0 | 984.0  | 950.2  | 917.2  | 883.4  | 864.4  | 846.3  | 827.3  | 808.3  | 799.2  | 789.3  |
| 25°    | 954.3  | 960.9  | 968.3  | 974.9  | 981.5  | 973.3  | 964.2  | 956.0  | 946.9  | 950.2  | 952.7  |
| 27.5°  | 939.5  | 953.5  | 968.3  | 982.4  | 996.4  | 1003.8 | 1011.2 | 1018.6 | 1026.1 | 1028.5 | 1031.0 |
| 30°    | 719.2  | 726.7  | 733.3  | 740.7  | 747.3  | 767.9  | 788.5  | 808.3  | 828.9  | 861.1  | 894.1  |
| 32.5°  | 627.7  | 625.2  | 622.7  | 619.4  | 617.0  | 621.9  | 626.9  | 631.0  | 635.9  | 647.5  | 659.9  |
| 35°    | 614.5  | 608.7  | 602.1  | 596.3  | 589.7  | 592.2  | 594.7  | 597.2  | 599.6  | 608.7  | 617.8  |
| 37.5°  | 604.6  | 602.1  | 600.5  | 598.0  | 595.5  | 601.3  | 606.2  | 612.0  | 617.0  | 624.4  | 631.8  |
| 40°    | 611.2  | 610.4  | 609.5  | 607.9  | 607.1  | 610.4  | 613.7  | 617.0  | 620.3  | 630.2  | 640.1  |
| 42.5°  | 624.4  | 624.4  | 623.6  | 623.6  | 622.7  | 626.0  | 628.5  | 631.8  | 634.3  | 640.1  | 645.8  |
| 45°    | 641.7  | 640.1  | 639.2  | 637.6  | 635.9  | 635.1  | 635.1  | 634.3  | 633.5  | 636.8  | 640.9  |
| 47.5°  | 662.3  | 656.6  | 650.0  | 644.2  | 637.6  | 635.9  | 633.5  | 631.8  | 629.3  | 631.0  | 632.6  |
| 50°    | 698.6  | 682.9  | 668.1  | 652.4  | 636.8  | 632.6  | 628.5  | 624.4  | 620.3  | 619.4  | 619.4  |
| 52.5°  | 725.8  | 702.7  | 679.6  | 656.6  | 633.5  | 626.0  | 618.6  | 611.2  | 603.8  | 602.1  | 601.3  |
| 55°    | 699.4  | 682.1  | 665.6  | 648.3  | 631.0  | 620.3  | 608.7  | 598.0  | 586.4  | 584.0  | 581.5  |
| 57.5°  | 675.5  | 664.8  | 654.1  | 643.4  | 632.6  | 621.9  | 610.4  | 599.6  | 588.1  | 582.3  | 576.5  |
| 60°    | 618.6  | 618.6  | 619.4  | 619.4  | 619.4  | 607.9  | 596.3  | 584.8  | 573.2  | 567.5  | 562.5  |
| 62.5°  | 560.0  | 569.1  | 577.4  | 586.4  | 594.7  | 579.0  | 562.5  | 546.9  | 530.4  | 526.2  | 522.9  |
| 65°    | 511.4  | 513.9  | 517.2  | 519.6  | 522.1  | 509.7  | 497.4  | 485.0  | 472.6  | 470.1  | 466.8  |
| 67.5°  | 461.9  | 461.1  | 460.2  | 458.6  | 457.8  | 450.3  | 442.1  | 434.7  | 426.4  | 423.1  | 419.8  |
| 70°    | 414.1  | 413.2  | 412.4  | 410.8  | 409.9  | 403.3  | 396.7  | 390.1  | 383.5  | 381.1  | 378.6  |
| 72.5°  | 368.7  | 367.9  | 366.2  | 365.4  | 363.7  | 358.0  | 353.0  | 347.2  | 341.5  | 338.2  | 334.9  |
| 75°    | 319.2  | 317.6  | 315.9  | 314.3  | 312.6  | 307.7  | 302.7  | 296.9  | 292.0  | 288.7  | 285.4  |
| 77.5°  | 273.0  | 270.5  | 268.1  | 264.8  | 262.3  | 258.2  | 253.2  | 249.1  | 244.1  | 240.0  | 236.7  |
| 80°    | 220.2  | 218.6  | 216.9  | 214.5  | 212.8  | 208.7  | 204.6  | 199.6  | 195.5  | 190.5  | 186.4  |
| 82.5°  | 165.0  | 164.1  | 162.5  | 161.7  | 160.0  | 155.9  | 151.8  | 147.6  | 143.5  | 138.6  | 133.6  |
| 85°    | 106.4  | 105.6  | 104.8  | 103.9  | 103.1  | 99.8   | 97.3   | 94.0   | 90.7   | 85.8   | 81.7   |
| 87.5°  | 37.9   | 36.3   | 35.5   | 33.8   | 32.2   | 31.3   | 29.7   | 28.9   | 27.2   | 24.7   | 22.3   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P598556

CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 55° | 57.5° | 60° | 62.5° | 65° | 67.5° | 70° | 72.5° | 75° | 77.5° | 80° |
|--------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |



REPORT NUMBER: P598556

CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 82.5°  | 85°    | 87.5°  | 90°    | 92.5°  | 95°    | 97.5°  | 100°   | 102.5° | 105°   | 107.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 |
| 2.5°   | 1870.7 | 1902.0 | 1902.8 | 1902.8 | 1917.7 | 1931.7 | 1902.8 | 1874.0 | 1844.3 | 1815.4 | 1786.5 |
| 5°     | 1993.6 | 2005.9 | 2002.6 | 1998.5 | 1980.4 | 1962.2 | 1943.3 | 1924.3 | 1905.3 | 1886.3 | 1887.2 |
| 7.5°   | 1708.2 | 1738.7 | 1763.5 | 1787.4 | 1764.3 | 1741.2 | 1728.8 | 1716.4 | 1704.1 | 1691.7 | 1690.0 |
| 10°    | 1360.9 | 1369.2 | 1379.1 | 1388.2 | 1374.1 | 1359.3 | 1384.0 | 1408.8 | 1432.7 | 1457.4 | 1430.2 |
| 12.5°  | 1264.4 | 1271.9 | 1254.5 | 1236.4 | 1230.6 | 1224.8 | 1219.1 | 1212.5 | 1206.7 | 1200.1 | 1196.8 |
| 15°    | 1091.2 | 1078.0 | 1064.8 | 1050.8 | 1047.5 | 1043.4 | 1039.3 | 1034.3 | 1030.2 | 1025.2 | 1010.4 |
| 17.5°  | 943.6  | 930.4  | 908.1  | 885.0  | 876.0  | 866.1  | 863.6  | 861.1  | 857.8  | 855.3  | 841.3  |
| 20°    | 814.1  | 805.0  | 799.2  | 792.6  | 783.6  | 774.5  | 765.4  | 756.4  | 746.5  | 737.4  | 724.2  |
| 22.5°  | 780.3  | 770.4  | 763.0  | 754.7  | 753.1  | 751.4  | 734.9  | 717.6  | 701.1  | 683.8  | 676.3  |
| 25°    | 956.0  | 958.4  | 913.1  | 866.9  | 862.8  | 858.6  | 828.9  | 798.4  | 768.7  | 738.2  | 712.6  |
| 27.5°  | 1032.7 | 1035.1 | 1033.5 | 1031.8 | 1018.6 | 1004.6 | 954.3  | 903.2  | 852.9  | 801.7  | 765.4  |
| 30°    | 926.3  | 958.4  | 970.8  | 983.2  | 974.1  | 964.2  | 911.4  | 859.5  | 806.7  | 753.9  | 730.0  |
| 32.5°  | 671.4  | 682.9  | 703.6  | 723.4  | 734.1  | 744.0  | 727.5  | 711.0  | 694.5  | 678.0  | 673.9  |
| 35°    | 626.0  | 635.1  | 639.2  | 643.4  | 636.8  | 630.2  | 617.8  | 605.4  | 592.2  | 579.8  | 577.4  |
| 37.5°  | 638.4  | 645.8  | 654.1  | 662.3  | 644.2  | 625.2  | 611.2  | 598.0  | 584.0  | 569.9  | 558.4  |
| 40°    | 650.0  | 659.9  | 664.8  | 669.7  | 651.6  | 633.5  | 616.1  | 599.6  | 582.3  | 565.0  | 553.4  |
| 42.5°  | 651.6  | 657.4  | 666.4  | 675.5  | 650.0  | 623.6  | 607.9  | 591.4  | 575.7  | 559.2  | 547.7  |
| 45°    | 644.2  | 647.5  | 655.7  | 664.0  | 634.3  | 603.8  | 589.7  | 574.9  | 560.9  | 546.0  | 536.1  |
| 47.5°  | 633.5  | 635.1  | 641.7  | 647.5  | 616.1  | 584.0  | 570.8  | 557.6  | 543.6  | 530.4  | 520.5  |
| 50°    | 618.6  | 617.8  | 622.7  | 626.9  | 594.7  | 562.5  | 549.3  | 537.0  | 523.8  | 510.6  | 502.3  |
| 52.5°  | 599.6  | 598.0  | 602.9  | 607.1  | 573.2  | 539.4  | 527.9  | 517.2  | 505.6  | 494.1  | 487.5  |
| 55°    | 578.2  | 575.7  | 579.8  | 584.0  | 551.0  | 517.2  | 507.3  | 496.5  | 486.6  | 475.9  | 470.1  |
| 57.5°  | 569.9  | 564.2  | 566.6  | 569.1  | 532.0  | 494.9  | 485.0  | 475.1  | 465.2  | 455.3  | 451.2  |
| 60°    | 556.7  | 551.0  | 553.4  | 555.1  | 515.5  | 475.1  | 466.0  | 456.1  | 447.0  | 437.2  | 433.0  |
| 62.5°  | 518.8  | 514.7  | 518.0  | 521.3  | 485.8  | 449.5  | 441.3  | 433.9  | 425.6  | 417.4  | 411.6  |
| 65°    | 464.4  | 461.1  | 467.7  | 474.3  | 443.7  | 413.2  | 408.3  | 403.3  | 397.6  | 392.6  | 386.8  |
| 67.5°  | 416.5  | 413.2  | 419.8  | 426.4  | 404.2  | 381.9  | 376.9  | 372.0  | 367.0  | 362.1  | 358.8  |
| 70°    | 376.1  | 373.6  | 379.4  | 385.2  | 366.2  | 347.2  | 342.3  | 338.2  | 333.2  | 328.3  | 325.8  |
| 72.5°  | 330.7  | 327.5  | 334.9  | 341.5  | 325.8  | 309.3  | 305.2  | 300.2  | 296.1  | 291.2  | 289.5  |
| 75°    | 282.1  | 278.8  | 285.4  | 291.2  | 280.4  | 268.9  | 264.8  | 260.6  | 256.5  | 252.4  | 251.6  |
| 77.5°  | 232.6  | 228.5  | 235.1  | 240.8  | 234.2  | 226.8  | 223.5  | 219.4  | 216.1  | 212.0  | 212.0  |
| 80°    | 181.5  | 176.5  | 181.5  | 185.6  | 183.1  | 180.6  | 178.2  | 174.9  | 172.4  | 169.1  | 169.9  |
| 82.5°  | 128.7  | 123.7  | 126.2  | 128.7  | 130.3  | 132.0  | 132.0  | 132.0  | 132.0  | 132.0  | 132.0  |
| 85°    | 76.7   | 71.8   | 72.6   | 73.4   | 75.9   | 78.4   | 79.2   | 80.0   | 80.8   | 81.7   | 82.5   |
| 87.5°  | 19.8   | 17.3   | 15.7   | 13.2   | 15.7   | 17.3   | 19.0   | 19.8   | 21.4   | 22.3   | 22.3   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P598556  
 CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85° | 87.5° | 90° | 92.5° | 95° | 97.5° | 100° | 102.5° | 105° | 107.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|------|--------|------|--------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P598556  
 CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 110°   | 112.5° | 115°   | 117.5° | 120°   | 122.5° | 125°   | 127.5° | 130°   | 132.5° | 135°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 |
| 2.5°   | 1757.7 | 1728.0 | 1699.1 | 1717.3 | 1734.6 | 1752.7 | 1770.0 | 1770.9 | 1770.9 | 1771.7 | 1771.7 |
| 5°     | 1888.8 | 1889.6 | 1890.5 | 1873.2 | 1856.7 | 1839.3 | 1822.0 | 1812.9 | 1803.9 | 1794.0 | 1784.9 |
| 7.5°   | 1687.6 | 1685.9 | 1683.4 | 1666.9 | 1650.5 | 1634.0 | 1617.5 | 1577.9 | 1537.5 | 1497.9 | 1457.4 |
| 10°    | 1402.2 | 1375.0 | 1346.9 | 1340.3 | 1334.5 | 1327.9 | 1321.4 | 1310.6 | 1300.7 | 1290.0 | 1279.3 |
| 12.5°  | 1193.5 | 1190.2 | 1186.9 | 1169.6 | 1152.3 | 1134.1 | 1116.8 | 1116.8 | 1116.8 | 1116.8 | 1116.8 |
| 15°    | 994.7  | 979.9  | 964.2  | 956.0  | 946.9  | 938.6  | 929.6  | 925.4  | 921.3  | 917.2  | 913.1  |
| 17.5°  | 826.5  | 812.4  | 797.6  | 795.9  | 794.3  | 792.6  | 791.0  | 786.9  | 782.7  | 778.6  | 774.5  |
| 20°    | 711.0  | 697.8  | 684.6  | 689.5  | 694.5  | 698.6  | 703.6  | 699.4  | 695.3  | 690.4  | 686.2  |
| 22.5°  | 668.1  | 660.7  | 652.4  | 648.3  | 644.2  | 639.2  | 635.1  | 635.1  | 635.9  | 635.9  | 635.9  |
| 25°    | 687.9  | 662.3  | 636.8  | 624.4  | 612.0  | 598.8  | 586.4  | 581.5  | 577.4  | 572.4  | 567.5  |
| 27.5°  | 729.1  | 692.0  | 655.7  | 634.3  | 612.8  | 591.4  | 569.9  | 560.9  | 551.0  | 541.9  | 532.0  |
| 30°    | 705.2  | 681.3  | 656.6  | 631.8  | 607.1  | 582.3  | 557.6  | 546.0  | 534.5  | 522.1  | 510.6  |
| 32.5°  | 669.7  | 664.8  | 660.7  | 637.6  | 614.5  | 590.6  | 567.5  | 562.5  | 558.4  | 553.4  | 548.5  |
| 35°    | 574.1  | 571.6  | 568.3  | 562.5  | 556.7  | 551.0  | 545.2  | 538.6  | 532.0  | 525.4  | 518.8  |
| 37.5°  | 547.7  | 536.1  | 524.6  | 522.1  | 519.6  | 517.2  | 514.7  | 512.2  | 509.7  | 506.4  | 504.0  |
| 40°    | 541.9  | 530.4  | 518.8  | 514.7  | 510.6  | 505.6  | 501.5  | 502.3  | 504.0  | 504.8  | 505.6  |
| 42.5°  | 535.3  | 523.8  | 511.4  | 508.1  | 504.8  | 501.5  | 498.2  | 499.0  | 500.7  | 501.5  | 502.3  |
| 45°    | 527.1  | 517.2  | 507.3  | 501.5  | 496.5  | 490.8  | 485.0  | 489.9  | 494.9  | 499.0  | 504.0  |
| 47.5°  | 510.6  | 499.8  | 489.9  | 486.6  | 483.3  | 479.2  | 475.9  | 480.9  | 485.8  | 489.9  | 494.9  |
| 50°    | 493.2  | 485.0  | 475.9  | 475.1  | 474.3  | 472.6  | 471.8  | 475.1  | 478.4  | 481.7  | 485.0  |
| 52.5°  | 480.0  | 473.4  | 466.0  | 466.0  | 465.2  | 465.2  | 464.4  | 467.7  | 471.0  | 473.4  | 476.7  |
| 55°    | 465.2  | 459.4  | 453.6  | 454.5  | 456.1  | 456.9  | 457.8  | 461.1  | 465.2  | 468.5  | 471.8  |
| 57.5°  | 446.2  | 442.1  | 437.2  | 440.5  | 442.9  | 446.2  | 448.7  | 451.2  | 454.5  | 456.9  | 459.4  |
| 60°    | 428.1  | 424.0  | 419.0  | 422.3  | 426.4  | 429.7  | 433.0  | 435.5  | 438.0  | 440.5  | 442.9  |
| 62.5°  | 405.8  | 399.2  | 393.4  | 398.4  | 402.5  | 407.5  | 411.6  | 413.2  | 415.7  | 417.4  | 419.0  |
| 65°    | 381.9  | 376.1  | 370.3  | 373.6  | 376.9  | 379.4  | 382.7  | 385.2  | 387.7  | 390.1  | 392.6  |
| 67.5°  | 354.7  | 351.4  | 347.2  | 349.7  | 352.2  | 354.7  | 357.1  | 358.0  | 358.0  | 358.8  | 358.8  |
| 70°    | 322.5  | 320.0  | 316.7  | 318.4  | 320.9  | 322.5  | 324.2  | 324.2  | 324.2  | 323.3  | 323.3  |
| 72.5°  | 288.7  | 287.0  | 285.4  | 286.2  | 287.9  | 288.7  | 289.5  | 288.7  | 287.9  | 287.0  | 286.2  |
| 75°    | 250.7  | 249.9  | 249.1  | 249.9  | 251.6  | 252.4  | 253.2  | 252.4  | 250.7  | 249.9  | 248.3  |
| 77.5°  | 212.8  | 212.8  | 212.8  | 212.8  | 213.6  | 213.6  | 213.6  | 212.0  | 210.3  | 208.7  | 207.0  |
| 80°    | 170.7  | 171.6  | 172.4  | 172.4  | 172.4  | 172.4  | 172.4  | 170.7  | 169.1  | 166.6  | 165.0  |
| 82.5°  | 132.0  | 132.0  | 132.0  | 132.0  | 132.8  | 132.8  | 132.8  | 128.7  | 125.4  | 121.2  | 117.1  |
| 85°    | 82.5   | 83.3   | 83.3   | 84.1   | 85.0   | 85.0   | 85.8   | 80.0   | 75.1   | 69.3   | 63.5   |
| 87.5°  | 22.3   | 22.3   | 22.3   | 22.3   | 22.3   | 21.4   | 21.4   | 16.5   | 10.7   | 5.8    | 0.0    |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P598556  
 CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° | 135° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |





REPORT NUMBER: P598556

CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140°   | 142.5° | 145°   | 147.5° | 150°   | 152.5° | 155°   | 157.5° | 160°   | 162.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 |
| 2.5°   | 1776.6 | 1781.6 | 1785.7 | 1790.7 | 1791.5 | 1792.3 | 1792.3 | 1793.1 | 1775.8 | 1758.5 | 1740.4 |
| 5°     | 1797.3 | 1808.8 | 1821.2 | 1832.7 | 1830.3 | 1827.8 | 1825.3 | 1822.8 | 1817.9 | 1813.8 | 1808.8 |
| 7.5°   | 1448.4 | 1440.1 | 1431.1 | 1422.0 | 1429.4 | 1436.8 | 1444.2 | 1451.7 | 1455.0 | 1458.3 | 1460.7 |
| 10°    | 1258.7 | 1238.0 | 1217.4 | 1196.8 | 1185.3 | 1172.9 | 1161.3 | 1149.0 | 1147.3 | 1146.5 | 1144.8 |
| 12.5°  | 1095.4 | 1073.1 | 1051.6 | 1029.4 | 1022.8 | 1015.3 | 1008.7 | 1001.3 | 1007.9 | 1014.5 | 1020.3 |
| 15°    | 904.0  | 895.7  | 886.7  | 877.6  | 885.0  | 892.4  | 899.9  | 907.3  | 913.9  | 919.7  | 926.3  |
| 17.5°  | 770.4  | 767.1  | 763.0  | 758.8  | 765.4  | 772.8  | 779.4  | 786.0  | 800.9  | 815.7  | 830.6  |
| 20°    | 682.9  | 680.5  | 677.2  | 673.9  | 671.4  | 668.1  | 665.6  | 662.3  | 683.8  | 704.4  | 725.8  |
| 22.5°  | 631.0  | 626.0  | 621.1  | 616.1  | 617.0  | 617.8  | 617.8  | 618.6  | 635.9  | 654.1  | 671.4  |
| 25°    | 565.8  | 564.2  | 562.5  | 560.9  | 565.8  | 570.8  | 574.9  | 579.8  | 595.5  | 611.2  | 626.0  |
| 27.5°  | 532.8  | 533.7  | 534.5  | 535.3  | 541.9  | 549.3  | 555.9  | 562.5  | 573.2  | 584.0  | 594.7  |
| 30°    | 514.7  | 519.6  | 523.8  | 527.9  | 530.4  | 532.8  | 535.3  | 537.8  | 548.5  | 558.4  | 569.1  |
| 32.5°  | 541.9  | 535.3  | 527.9  | 521.3  | 524.6  | 528.7  | 532.0  | 535.3  | 545.2  | 555.1  | 565.0  |
| 35°    | 516.3  | 513.0  | 510.6  | 507.3  | 511.4  | 515.5  | 518.8  | 522.9  | 532.0  | 540.3  | 549.3  |
| 37.5°  | 503.1  | 502.3  | 501.5  | 500.7  | 503.1  | 505.6  | 507.3  | 509.7  | 518.0  | 526.2  | 533.7  |
| 40°    | 502.3  | 498.2  | 494.9  | 490.8  | 493.2  | 495.7  | 497.4  | 499.8  | 509.7  | 519.6  | 529.5  |
| 42.5°  | 497.4  | 492.4  | 486.6  | 481.7  | 484.2  | 487.5  | 489.9  | 492.4  | 503.1  | 513.0  | 523.8  |
| 45°    | 496.5  | 489.1  | 480.9  | 473.4  | 476.7  | 480.0  | 483.3  | 486.6  | 494.9  | 503.1  | 510.6  |
| 47.5°  | 487.5  | 480.0  | 472.6  | 465.2  | 466.8  | 468.5  | 469.3  | 471.0  | 478.4  | 485.0  | 492.4  |
| 50°    | 480.0  | 474.3  | 469.3  | 463.5  | 461.1  | 459.4  | 456.9  | 454.5  | 460.2  | 466.0  | 471.8  |
| 52.5°  | 471.0  | 465.2  | 458.6  | 452.8  | 449.5  | 446.2  | 442.9  | 439.6  | 444.6  | 448.7  | 453.6  |
| 55°    | 465.2  | 457.8  | 451.2  | 443.7  | 439.6  | 435.5  | 431.4  | 427.3  | 430.6  | 433.0  | 436.3  |
| 57.5°  | 452.8  | 446.2  | 438.8  | 432.2  | 427.3  | 422.3  | 416.5  | 411.6  | 413.2  | 414.9  | 416.5  |
| 60°    | 436.3  | 428.9  | 422.3  | 414.9  | 409.1  | 403.3  | 396.7  | 391.0  | 391.8  | 393.4  | 394.3  |
| 62.5°  | 412.4  | 405.8  | 398.4  | 391.8  | 385.2  | 379.4  | 372.8  | 366.2  | 367.9  | 368.7  | 370.3  |
| 65°    | 386.0  | 378.6  | 372.0  | 364.6  | 358.8  | 353.0  | 346.4  | 340.6  | 342.3  | 343.9  | 344.8  |
| 67.5°  | 353.8  | 348.1  | 343.1  | 337.3  | 332.4  | 326.6  | 321.7  | 315.9  | 316.7  | 317.6  | 318.4  |
| 70°    | 319.2  | 314.3  | 310.1  | 305.2  | 301.1  | 296.9  | 292.8  | 288.7  | 288.7  | 289.5  | 289.5  |
| 72.5°  | 282.1  | 278.0  | 273.8  | 269.7  | 265.6  | 262.3  | 258.2  | 254.0  | 255.7  | 257.3  | 258.2  |
| 75°    | 244.1  | 240.8  | 236.7  | 232.6  | 229.3  | 226.0  | 221.9  | 218.6  | 220.2  | 221.9  | 222.7  |
| 77.5°  | 204.6  | 202.1  | 198.8  | 196.3  | 193.0  | 189.7  | 185.6  | 182.3  | 183.9  | 185.6  | 186.4  |
| 80°    | 163.3  | 161.7  | 159.2  | 157.5  | 154.2  | 150.9  | 147.6  | 144.3  | 145.2  | 145.2  | 146.0  |
| 82.5°  | 117.9  | 118.8  | 118.8  | 119.6  | 117.1  | 113.8  | 111.3  | 108.1  | 108.1  | 108.1  | 107.2  |
| 85°    | 66.0   | 69.3   | 71.8   | 74.2   | 71.8   | 69.3   | 66.8   | 64.3   | 63.5   | 63.5   | 62.7   |
| 87.5°  | 2.5    | 4.1    | 6.6    | 8.2    | 7.4    | 6.6    | 4.9    | 4.1    | 4.9    | 5.8    | 5.8    |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P598556  
 CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° | 162.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P598556

CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 165°   | 167.5° | 170°   | 172.5° | 175°   | 177.5° | 180°   | 182.5° | 185°   | 187.5° | 190°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 |
| 2.5°   | 1723.0 | 1737.1 | 1751.1 | 1765.1 | 1779.1 | 1800.6 | 1822.0 | 1844.3 | 1866.6 | 1854.2 | 1841.0 |
| 5°     | 1803.9 | 1812.1 | 1821.2 | 1829.4 | 1837.7 | 1861.6 | 1884.7 | 1913.6 | 1941.6 | 1938.3 | 1934.2 |
| 7.5°   | 1464.0 | 1475.6 | 1487.1 | 1497.9 | 1509.4 | 1545.7 | 1582.0 | 1612.5 | 1643.0 | 1638.9 | 1634.0 |
| 10°    | 1143.2 | 1167.1 | 1191.9 | 1215.8 | 1239.7 | 1269.4 | 1298.3 | 1323.8 | 1349.4 | 1392.3 | 1434.3 |
| 12.5°  | 1026.9 | 1064.0 | 1101.1 | 1138.2 | 1175.4 | 1196.8 | 1217.4 | 1250.4 | 1283.4 | 1306.5 | 1330.4 |
| 15°    | 932.0  | 966.7  | 1001.3 | 1036.0 | 1070.6 | 1072.3 | 1073.9 | 1108.5 | 1143.2 | 1163.0 | 1182.0 |
| 17.5°  | 845.4  | 864.4  | 883.4  | 901.5  | 920.5  | 913.9  | 907.3  | 923.8  | 939.5  | 947.7  | 956.8  |
| 20°    | 746.5  | 759.7  | 772.8  | 786.0  | 799.2  | 808.3  | 816.6  | 826.5  | 835.5  | 827.3  | 818.2  |
| 22.5°  | 688.7  | 708.5  | 729.1  | 748.9  | 768.7  | 774.5  | 779.4  | 773.7  | 767.9  | 765.4  | 763.0  |
| 25°    | 641.7  | 665.6  | 690.4  | 714.3  | 738.2  | 749.8  | 761.3  | 766.3  | 770.4  | 761.3  | 752.2  |
| 27.5°  | 605.4  | 634.3  | 662.3  | 691.2  | 719.2  | 739.9  | 760.5  | 766.3  | 771.2  | 764.6  | 757.2  |
| 30°    | 579.0  | 610.4  | 641.7  | 673.0  | 704.4  | 735.7  | 766.3  | 793.5  | 819.9  | 817.4  | 814.9  |
| 32.5°  | 574.9  | 596.3  | 617.8  | 639.2  | 660.7  | 680.5  | 699.4  | 701.1  | 701.9  | 695.3  | 687.9  |
| 35°    | 557.6  | 571.6  | 585.6  | 599.6  | 613.7  | 626.0  | 637.6  | 635.9  | 634.3  | 627.7  | 621.1  |
| 37.5°  | 541.9  | 555.9  | 570.8  | 584.8  | 598.8  | 620.3  | 640.9  | 636.8  | 631.8  | 625.2  | 618.6  |
| 40°    | 539.4  | 555.1  | 570.8  | 585.6  | 601.3  | 621.1  | 640.9  | 636.8  | 632.6  | 624.4  | 616.1  |
| 42.5°  | 533.7  | 549.3  | 564.2  | 579.8  | 594.7  | 618.6  | 641.7  | 634.3  | 626.0  | 619.4  | 612.8  |
| 45°    | 518.8  | 532.8  | 546.9  | 560.9  | 574.9  | 600.5  | 626.0  | 617.0  | 607.9  | 605.4  | 602.1  |
| 47.5°  | 499.0  | 513.0  | 527.1  | 541.1  | 555.1  | 580.7  | 605.4  | 598.0  | 589.7  | 588.9  | 587.3  |
| 50°    | 477.6  | 490.8  | 504.8  | 518.0  | 531.2  | 556.7  | 581.5  | 574.9  | 568.3  | 569.1  | 569.1  |
| 52.5°  | 457.8  | 470.1  | 481.7  | 494.1  | 505.6  | 531.2  | 555.9  | 551.0  | 545.2  | 546.9  | 547.7  |
| 55°    | 438.8  | 448.7  | 458.6  | 468.5  | 478.4  | 503.1  | 527.9  | 520.5  | 513.0  | 515.5  | 518.0  |
| 57.5°  | 418.2  | 426.4  | 434.7  | 442.1  | 450.3  | 475.1  | 499.0  | 490.8  | 481.7  | 485.8  | 489.1  |
| 60°    | 395.1  | 402.5  | 409.9  | 416.5  | 424.0  | 446.2  | 467.7  | 460.2  | 452.0  | 457.8  | 462.7  |
| 62.5°  | 371.2  | 376.9  | 382.7  | 388.5  | 394.3  | 414.9  | 435.5  | 429.7  | 424.0  | 430.6  | 436.3  |
| 65°    | 346.4  | 350.5  | 355.5  | 359.6  | 363.7  | 383.5  | 402.5  | 398.4  | 394.3  | 400.0  | 405.8  |
| 67.5°  | 319.2  | 322.5  | 326.6  | 329.9  | 333.2  | 351.4  | 369.5  | 365.4  | 360.4  | 365.4  | 369.5  |
| 70°    | 289.5  | 292.8  | 295.3  | 298.6  | 301.1  | 317.6  | 334.0  | 328.3  | 321.7  | 326.6  | 330.7  |
| 72.5°  | 259.8  | 261.5  | 263.9  | 265.6  | 267.2  | 279.6  | 292.0  | 287.0  | 282.1  | 287.0  | 291.2  |
| 75°    | 224.3  | 226.0  | 227.6  | 229.3  | 230.9  | 241.7  | 251.6  | 245.8  | 239.2  | 244.1  | 249.1  |
| 77.5°  | 188.1  | 188.9  | 190.5  | 191.4  | 192.2  | 199.6  | 206.2  | 200.4  | 193.8  | 199.6  | 205.4  |
| 80°    | 146.0  | 146.8  | 147.6  | 147.6  | 148.5  | 150.9  | 153.4  | 149.3  | 144.3  | 151.8  | 159.2  |
| 82.5°  | 107.2  | 106.4  | 106.4  | 105.6  | 104.8  | 104.8  | 103.9  | 101.5  | 98.2   | 104.8  | 111.3  |
| 85°    | 61.9   | 61.0   | 59.4   | 58.6   | 56.9   | 54.4   | 52.0   | 51.1   | 50.3   | 56.1   | 61.9   |
| 87.5°  | 6.6    | 5.8    | 4.1    | 3.3    | 1.6    | 0.8    | 0.0    | 0.0    | 0.0    | 3.3    | 7.4    |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P598556  
 CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° | 190° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P598556

CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195°   | 197.5° | 200°   | 202.5° | 205°   | 207.5° | 210°   | 212.5° | 215°   | 217.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 |
| 2.5°   | 1828.6 | 1815.4 | 1803.0 | 1790.7 | 1778.3 | 1765.9 | 1789.0 | 1812.1 | 1835.2 | 1858.3 | 1878.9 |
| 5°     | 1930.9 | 1926.8 | 1916.0 | 1906.1 | 1895.4 | 1884.7 | 1890.5 | 1897.1 | 1902.8 | 1908.6 | 1921.0 |
| 7.5°   | 1629.8 | 1624.9 | 1648.0 | 1670.2 | 1693.3 | 1715.6 | 1721.4 | 1726.3 | 1732.1 | 1737.1 | 1733.8 |
| 10°    | 1477.2 | 1519.3 | 1530.0 | 1539.9 | 1550.6 | 1560.5 | 1577.0 | 1593.5 | 1609.2 | 1625.7 | 1634.8 |
| 12.5°  | 1353.5 | 1376.6 | 1414.6 | 1453.3 | 1491.3 | 1529.2 | 1553.9 | 1578.7 | 1603.4 | 1628.2 | 1679.3 |
| 15°    | 1201.8 | 1220.7 | 1249.6 | 1278.5 | 1307.3 | 1336.2 | 1371.7 | 1408.0 | 1443.4 | 1478.9 | 1535.0 |
| 17.5°  | 965.0  | 973.3  | 994.7  | 1016.2 | 1036.8 | 1058.2 | 1106.1 | 1153.1 | 1200.9 | 1247.9 | 1312.3 |
| 20°    | 810.0  | 800.9  | 800.9  | 801.7  | 801.7  | 801.7  | 849.6  | 896.6  | 944.4  | 991.4  | 1076.4 |
| 22.5°  | 759.7  | 757.2  | 748.1  | 738.2  | 729.1  | 719.2  | 744.0  | 769.6  | 794.3  | 819.0  | 888.3  |
| 25°    | 742.3  | 733.3  | 721.7  | 710.2  | 698.6  | 687.1  | 702.7  | 718.4  | 734.1  | 749.8  | 804.2  |
| 27.5°  | 750.6  | 743.2  | 748.9  | 753.9  | 759.7  | 764.6  | 769.6  | 774.5  | 779.4  | 784.4  | 803.4  |
| 30°    | 812.4  | 810.0  | 819.0  | 827.3  | 836.4  | 844.6  | 833.1  | 822.3  | 810.8  | 799.2  | 805.8  |
| 32.5°  | 681.3  | 673.9  | 670.6  | 667.3  | 664.0  | 660.7  | 659.9  | 659.0  | 657.4  | 656.6  | 671.4  |
| 35°    | 614.5  | 607.9  | 602.9  | 598.0  | 592.2  | 587.3  | 589.7  | 591.4  | 593.9  | 595.5  | 612.0  |
| 37.5°  | 612.0  | 605.4  | 599.6  | 593.9  | 587.3  | 581.5  | 584.0  | 587.3  | 589.7  | 592.2  | 604.6  |
| 40°    | 607.9  | 599.6  | 596.3  | 593.0  | 589.7  | 586.4  | 588.1  | 589.7  | 590.6  | 592.2  | 601.3  |
| 42.5°  | 605.4  | 598.8  | 597.2  | 595.5  | 593.9  | 592.2  | 593.9  | 595.5  | 596.3  | 598.0  | 608.7  |
| 45°    | 599.6  | 596.3  | 598.0  | 599.6  | 601.3  | 602.9  | 602.9  | 602.9  | 602.9  | 602.9  | 614.5  |
| 47.5°  | 586.4  | 584.8  | 589.7  | 594.7  | 599.6  | 604.6  | 612.8  | 621.1  | 628.5  | 636.8  | 639.2  |
| 50°    | 569.9  | 569.9  | 578.2  | 586.4  | 593.9  | 602.1  | 621.9  | 640.9  | 660.7  | 679.6  | 667.3  |
| 52.5°  | 549.3  | 550.2  | 562.5  | 574.1  | 586.4  | 598.0  | 616.1  | 634.3  | 651.6  | 669.7  | 651.6  |
| 55°    | 519.6  | 522.1  | 537.8  | 552.6  | 568.3  | 583.1  | 597.2  | 611.2  | 625.2  | 639.2  | 620.3  |
| 57.5°  | 493.2  | 496.5  | 513.0  | 528.7  | 545.2  | 560.9  | 569.1  | 578.2  | 586.4  | 594.7  | 582.3  |
| 60°    | 468.5  | 473.4  | 494.9  | 516.3  | 537.0  | 558.4  | 551.8  | 545.2  | 537.8  | 531.2  | 530.4  |
| 62.5°  | 442.9  | 448.7  | 468.5  | 488.3  | 507.3  | 527.1  | 517.2  | 507.3  | 496.5  | 486.6  | 490.8  |
| 65°    | 410.8  | 416.5  | 425.6  | 434.7  | 442.9  | 452.0  | 451.2  | 451.2  | 450.3  | 449.5  | 457.8  |
| 67.5°  | 374.5  | 378.6  | 384.4  | 389.3  | 395.1  | 400.0  | 403.3  | 407.5  | 410.8  | 414.1  | 424.0  |
| 70°    | 335.7  | 339.8  | 345.6  | 350.5  | 356.3  | 361.3  | 365.4  | 369.5  | 372.8  | 376.9  | 386.8  |
| 72.5°  | 296.1  | 300.2  | 306.0  | 311.8  | 316.7  | 322.5  | 325.8  | 329.1  | 331.6  | 334.9  | 343.1  |
| 75°    | 254.0  | 259.0  | 264.8  | 269.7  | 275.5  | 280.4  | 282.9  | 285.4  | 287.9  | 290.3  | 297.8  |
| 77.5°  | 211.2  | 216.9  | 222.7  | 228.5  | 234.2  | 240.0  | 240.8  | 241.7  | 242.5  | 243.3  | 249.9  |
| 80°    | 165.8  | 173.2  | 179.0  | 184.8  | 190.5  | 196.3  | 196.3  | 196.3  | 196.3  | 196.3  | 199.6  |
| 82.5°  | 117.9  | 124.5  | 131.1  | 136.9  | 143.5  | 149.3  | 149.3  | 148.5  | 148.5  | 147.6  | 147.6  |
| 85°    | 67.6   | 73.4   | 77.5   | 82.5   | 86.6   | 90.7   | 90.7   | 90.7   | 89.9   | 89.9   | 88.3   |
| 87.5°  | 10.7   | 14.0   | 15.7   | 18.1   | 19.8   | 21.4   | 20.6   | 20.6   | 19.8   | 19.0   | 16.5   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P598556  
 CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° | 217.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P598556

CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 220°   | 222.5° | 225°   | 227.5° | 230°   | 232.5° | 235°   | 237.5° | 240°   | 242.5° | 245°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 |
| 2.5°   | 1899.5 | 1920.2 | 1940.8 | 1937.5 | 1934.2 | 1930.9 | 1927.6 | 1940.0 | 1951.5 | 1963.9 | 1975.4 |
| 5°     | 1932.5 | 1944.9 | 1956.5 | 1965.5 | 1974.6 | 1983.7 | 1992.7 | 2034.8 | 2076.1 | 2118.1 | 2159.4 |
| 7.5°   | 1730.5 | 1726.3 | 1723.0 | 1761.8 | 1801.4 | 1840.2 | 1878.9 | 1932.5 | 1986.1 | 2039.8 | 2093.4 |
| 10°    | 1643.9 | 1652.9 | 1662.0 | 1677.7 | 1694.2 | 1709.8 | 1725.5 | 1778.3 | 1831.1 | 1883.9 | 1936.7 |
| 12.5°  | 1729.6 | 1780.8 | 1831.1 | 1843.5 | 1856.7 | 1869.0 | 1881.4 | 1892.1 | 1902.8 | 1912.7 | 1923.5 |
| 15°    | 1591.1 | 1647.2 | 1703.2 | 1735.4 | 1767.6 | 1798.9 | 1831.1 | 1911.9 | 1991.9 | 2072.8 | 2152.8 |
| 17.5°  | 1375.8 | 1440.1 | 1503.6 | 1582.8 | 1662.0 | 1741.2 | 1820.4 | 1894.6 | 1968.8 | 2042.2 | 2116.5 |
| 20°    | 1161.3 | 1245.5 | 1330.4 | 1417.0 | 1502.8 | 1589.4 | 1675.2 | 1747.8 | 1820.4 | 1892.1 | 1964.7 |
| 22.5°  | 956.8  | 1026.1 | 1094.5 | 1200.1 | 1304.9 | 1410.4 | 1515.2 | 1650.5 | 1784.9 | 1920.2 | 2054.6 |
| 25°    | 857.8  | 912.2  | 965.9  | 1074.7 | 1183.6 | 1291.7 | 1400.5 | 1576.2 | 1751.1 | 1926.8 | 2101.6 |
| 27.5°  | 823.2  | 842.1  | 861.1  | 960.1  | 1058.2 | 1157.2 | 1255.4 | 1445.1 | 1634.8 | 1823.7 | 2013.4 |
| 30°    | 812.4  | 819.0  | 825.6  | 903.2  | 980.7  | 1058.2 | 1135.8 | 1323.0 | 1511.1 | 1698.3 | 1885.5 |
| 32.5°  | 685.4  | 700.3  | 714.3  | 790.2  | 865.2  | 941.1  | 1016.2 | 1205.1 | 1393.1 | 1582.0 | 1770.0 |
| 35°    | 628.5  | 645.0  | 661.5  | 735.7  | 810.0  | 883.4  | 957.6  | 1156.4 | 1356.0 | 1554.8 | 1753.6 |
| 37.5°  | 617.0  | 629.3  | 641.7  | 725.8  | 810.0  | 894.1  | 978.2  | 1179.5 | 1380.7 | 1582.0 | 1783.2 |
| 40°    | 611.2  | 620.3  | 629.3  | 711.0  | 793.5  | 875.1  | 956.8  | 1167.9 | 1378.3 | 1589.4 | 1799.7 |
| 42.5°  | 618.6  | 629.3  | 639.2  | 713.5  | 786.9  | 861.1  | 934.5  | 1153.1 | 1370.8 | 1589.4 | 1807.2 |
| 45°    | 625.2  | 636.8  | 647.5  | 716.8  | 786.0  | 855.3  | 924.6  | 1158.0 | 1390.6 | 1624.1 | 1856.7 |
| 47.5°  | 640.9  | 643.4  | 645.0  | 705.2  | 764.6  | 824.8  | 884.2  | 1121.7 | 1359.3 | 1596.0 | 1833.6 |
| 50°    | 654.1  | 641.7  | 628.5  | 691.2  | 753.1  | 815.7  | 877.6  | 1102.8 | 1327.9 | 1552.3 | 1777.5 |
| 52.5°  | 633.5  | 614.5  | 596.3  | 664.0  | 731.6  | 798.4  | 866.1  | 1091.2 | 1317.2 | 1542.4 | 1767.6 |
| 55°    | 602.1  | 583.1  | 564.2  | 632.6  | 701.1  | 769.6  | 838.0  | 1062.4 | 1287.5 | 1511.9 | 1736.2 |
| 57.5°  | 570.8  | 558.4  | 546.0  | 602.1  | 659.0  | 715.1  | 771.2  | 1014.5 | 1257.0 | 1500.3 | 1742.8 |
| 60°    | 529.5  | 527.9  | 527.1  | 570.8  | 615.3  | 659.0  | 702.7  | 941.1  | 1178.7 | 1417.0 | 1654.6 |
| 62.5°  | 494.1  | 498.2  | 501.5  | 537.0  | 572.4  | 607.1  | 642.5  | 872.7  | 1103.6 | 1333.7 | 1563.8 |
| 65°    | 466.8  | 475.1  | 483.3  | 523.8  | 564.2  | 603.8  | 644.2  | 837.2  | 1030.2 | 1223.2 | 1416.2 |
| 67.5°  | 433.9  | 443.7  | 453.6  | 506.4  | 559.2  | 612.0  | 664.8  | 824.0  | 983.2  | 1142.4 | 1301.6 |
| 70°    | 395.9  | 405.8  | 414.9  | 482.5  | 549.3  | 617.0  | 683.8  | 824.8  | 966.7  | 1107.7 | 1248.8 |
| 72.5°  | 351.4  | 359.6  | 367.9  | 440.5  | 513.0  | 585.6  | 658.2  | 777.8  | 897.4  | 1016.2 | 1135.8 |
| 75°    | 306.0  | 313.4  | 320.9  | 383.5  | 446.2  | 508.9  | 571.6  | 664.0  | 755.5  | 847.9  | 939.5  |
| 77.5°  | 255.7  | 262.3  | 268.1  | 310.1  | 352.2  | 394.3  | 436.3  | 507.3  | 577.4  | 648.3  | 718.4  |
| 80°    | 202.9  | 206.2  | 209.5  | 234.2  | 258.2  | 282.9  | 306.8  | 353.8  | 400.9  | 447.0  | 494.1  |
| 82.5°  | 148.5  | 148.5  | 148.5  | 164.1  | 180.6  | 196.3  | 212.0  | 235.9  | 259.0  | 282.9  | 306.0  |
| 85°    | 86.6   | 84.1   | 82.5   | 93.2   | 103.9  | 114.6  | 125.4  | 135.3  | 145.2  | 155.1  | 165.0  |
| 87.5°  | 14.0   | 10.7   | 8.2    | 14.8   | 21.4   | 28.0   | 34.6   | 37.9   | 42.1   | 45.4   | 48.7   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P598556

CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° | 245° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |





REPORT NUMBER: P598556

CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°   | 252.5° | 255°   | 257.5° | 260°   | 262.5°  | 265°    | 267.5°  | 270°    | 272.5°  |
|--------|--------|--------|--------|--------|--------|--------|---------|---------|---------|---------|---------|
| 0°     | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3 | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  |
| 2.5°   | 1947.4 | 1920.2 | 1892.1 | 1864.1 | 1905.3 | 1946.6 | 1987.8  | 2029.0  | 2138.7  | 2203.9  | 2208.0  |
| 5°     | 2194.0 | 2228.6 | 2263.3 | 2297.9 | 2332.6 | 2367.2 | 2401.0  | 2435.7  | 2613.8  | 2723.5  | 2744.2  |
| 7.5°   | 2150.3 | 2208.0 | 2264.9 | 2321.8 | 2420.0 | 2518.2 | 2616.3  | 2714.5  | 2865.4  | 2974.3  | 3046.0  |
| 10°    | 2007.6 | 2078.5 | 2149.5 | 2220.4 | 2336.7 | 2453.8 | 2570.1  | 2686.4  | 2846.4  | 2989.9  | 3058.4  |
| 12.5°  | 2036.5 | 2149.5 | 2261.6 | 2374.6 | 2475.3 | 2576.7 | 2677.3  | 2778.0  | 2888.5  | 2942.9  | 3067.5  |
| 15°    | 2231.1 | 2309.5 | 2387.8 | 2466.2 | 2618.0 | 2768.9 | 2920.7  | 3071.6  | 3134.3  | 3258.8  | 3371.0  |
| 17.5°  | 2260.8 | 2404.3 | 2548.7 | 2692.2 | 2877.8 | 3063.4 | 3248.9  | 3434.5  | 3550.8  | 3711.7  | 3846.9  |
| 20°    | 2168.4 | 2371.3 | 2575.1 | 2778.0 | 3017.2 | 3257.2 | 3496.4  | 3735.6  | 3883.2  | 4018.5  | 4228.0  |
| 22.5°  | 2279.0 | 2503.3 | 2726.8 | 2951.2 | 3268.7 | 3585.5 | 3903.0  | 4219.7  | 4528.2  | 4830.1  | 4972.0  |
| 25°    | 2401.0 | 2701.3 | 3000.7 | 3300.1 | 3696.8 | 4092.7 | 4489.5  | 4885.4  | 5282.1  | 5565.0  | 5728.3  |
| 27.5°  | 2315.2 | 2616.3 | 2918.2 | 3219.2 | 3710.0 | 4201.6 | 4692.4  | 5183.1  | 5607.9  | 5948.6  | 6088.8  |
| 30°    | 2255.0 | 2624.6 | 2994.1 | 3363.6 | 3939.3 | 4515.0 | 5090.7  | 5666.5  | 6059.1  | 6439.3  | 6645.5  |
| 32.5°  | 2244.3 | 2718.6 | 3192.0 | 3666.3 | 4336.9 | 5006.6 | 5677.2  | 6346.9  | 6607.6  | 6944.9  | 7222.9  |
| 35°    | 2274.0 | 2795.3 | 3315.7 | 3836.2 | 4604.9 | 5373.7 | 6141.6  | 6910.3  | 7280.6  | 7614.7  | 7858.0  |
| 37.5°  | 2364.7 | 2946.2 | 3526.9 | 4108.4 | 5034.7 | 5961.7 | 6888.0  | 7814.3  | 8435.4  | 9046.5  | 9155.4  |
| 40°    | 2415.9 | 3032.8 | 3649.0 | 4265.1 | 5342.3 | 6419.5 | 7496.7  | 8573.9  | 9288.2  | 9958.8  | 10004.2 |
| 42.5°  | 2476.1 | 3145.0 | 3813.1 | 4482.0 | 5676.4 | 6871.5 | 8065.8  | 9260.2  | 10144.4 | 10865.3 | 10886.7 |
| 45°    | 2545.4 | 3233.3 | 3922.0 | 4609.9 | 5857.0 | 7103.3 | 8350.4  | 9596.7  | 10665.7 | 11541.6 | 11328.0 |
| 47.5°  | 2572.6 | 3312.4 | 4051.5 | 4790.5 | 6120.1 | 7448.9 | 8778.5  | 10107.3 | 11066.5 | 11863.3 | 11658.7 |
| 50°    | 2583.3 | 3390.0 | 4195.8 | 5001.7 | 6379.1 | 7757.4 | 9134.8  | 10512.2 | 11488.0 | 12265.0 | 11951.5 |
| 52.5°  | 2650.1 | 3532.7 | 4415.2 | 5297.8 | 6732.9 | 8168.1 | 9603.3  | 11038.5 | 11998.6 | 12745.0 | 12355.7 |
| 55°    | 2740.0 | 3743.8 | 4746.8 | 5750.6 | 7236.1 | 8720.7 | 10206.2 | 11690.9 | 12654.3 | 13348.8 | 12866.3 |
| 57.5°  | 2823.3 | 3904.7 | 4985.2 | 6065.7 | 7604.8 | 9144.7 | 10683.8 | 12222.9 | 13198.7 | 13885.7 | 13418.1 |
| 60°    | 2782.9 | 3911.3 | 5039.6 | 6168.0 | 7680.7 | 9192.5 | 10705.2 | 12217.1 | 13324.9 | 14148.8 | 13909.6 |
| 62.5°  | 2660.8 | 3757.8 | 4854.0 | 5951.0 | 7387.0 | 8822.2 | 10258.2 | 11693.4 | 12990.0 | 14046.6 | 14035.8 |
| 65°    | 2425.8 | 3435.3 | 4444.1 | 5453.7 | 6782.4 | 8112.0 | 9440.8  | 10769.6 | 12298.0 | 13581.4 | 13664.7 |
| 67.5°  | 2139.6 | 2977.6 | 3815.6 | 4653.6 | 5904.8 | 7156.1 | 8407.3  | 9658.6  | 11292.5 | 12708.7 | 12780.5 |
| 70°    | 1862.4 | 2476.9 | 3090.6 | 3704.2 | 4802.9 | 5901.5 | 6999.4  | 8098.0  | 9748.5  | 11181.2 | 11247.1 |
| 72.5°  | 1537.5 | 1939.1 | 2340.0 | 2741.7 | 3631.7 | 4521.6 | 5410.8  | 6300.7  | 7749.9  | 8851.9  | 9223.9  |
| 75°    | 1177.8 | 1416.2 | 1654.6 | 1892.9 | 2613.0 | 3333.1 | 4052.3  | 4772.4  | 5735.7  | 6549.0  | 6968.0  |
| 77.5°  | 842.1  | 965.9  | 1089.6 | 1213.3 | 1825.3 | 2437.3 | 3048.5  | 3660.5  | 4167.0  | 4628.0  | 4910.9  |
| 80°    | 552.6  | 610.4  | 668.9  | 726.7  | 1235.6 | 1744.5 | 2252.6  | 2761.5  | 3070.0  | 3317.4  | 3460.1  |
| 82.5°  | 334.9  | 363.7  | 391.8  | 420.7  | 833.1  | 1245.5 | 1657.0  | 2069.5  | 2246.0  | 2363.9  | 2490.9  |
| 85°    | 180.6  | 196.3  | 212.0  | 227.6  | 492.4  | 756.4  | 1021.1  | 1285.1  | 1302.4  | 1316.4  | 1505.3  |
| 87.5°  | 52.8   | 57.7   | 61.9   | 66.0   | 108.9  | 152.6  | 195.5   | 238.4   | 148.5   | 92.4    | 189.7   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P598556  
 CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° | 272.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P598556

CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 275°    | 277.5°  | 280°    | 282.5°  | 285°    | 287.5°  | 290°    | 292.5°  | 295°    | 297.5°  | 300°    |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  |
| 2.5°   | 2184.1  | 2173.4  | 2162.7  | 2151.1  | 2140.4  | 2095.0  | 2050.5  | 2005.1  | 1959.8  | 2003.5  | 2046.4  |
| 5°     | 2720.2  | 2753.2  | 2785.4  | 2818.4  | 2851.4  | 2853.9  | 2855.5  | 2858.0  | 2859.6  | 2867.9  | 2876.1  |
| 7.5°   | 3106.2  | 3164.8  | 3222.5  | 3281.1  | 3339.7  | 3385.0  | 3430.4  | 3476.6  | 3522.0  | 3480.7  | 3439.5  |
| 10°    | 3139.2  | 3263.0  | 3386.7  | 3510.4  | 3634.1  | 3656.4  | 3677.8  | 3700.1  | 3722.4  | 3752.1  | 3780.9  |
| 12.5°  | 3172.2  | 3323.2  | 3473.3  | 3624.2  | 3775.2  | 3841.2  | 3906.3  | 3972.3  | 4037.5  | 4069.6  | 4101.0  |
| 15°    | 3521.1  | 3610.2  | 3698.5  | 3787.5  | 3875.8  | 3921.2  | 3965.7  | 4011.1  | 4056.4  | 4083.6  | 4110.0  |
| 17.5°  | 3969.8  | 4002.8  | 4035.0  | 4068.0  | 4101.0  | 4131.5  | 4162.0  | 4192.5  | 4223.0  | 4228.0  | 4232.9  |
| 20°    | 4378.9  | 4385.5  | 4391.3  | 4397.9  | 4403.7  | 4339.3  | 4275.8  | 4211.5  | 4147.2  | 4158.7  | 4169.4  |
| 22.5°  | 4992.6  | 4956.3  | 4920.8  | 4884.5  | 4849.1  | 4727.8  | 4607.4  | 4486.2  | 4365.7  | 4313.8  | 4262.6  |
| 25°    | 5916.4  | 5824.0  | 5731.6  | 5639.2  | 5546.9  | 5353.9  | 5161.7  | 4968.7  | 4776.5  | 4663.5  | 4551.3  |
| 27.5°  | 6214.1  | 6012.9  | 5812.5  | 5611.2  | 5409.9  | 5264.0  | 5118.8  | 4972.8  | 4827.6  | 4648.6  | 4469.7  |
| 30°    | 6816.3  | 6498.7  | 6182.0  | 5864.4  | 5546.9  | 5405.8  | 5264.8  | 5122.9  | 4981.9  | 4798.8  | 4616.5  |
| 32.5°  | 7349.9  | 7020.0  | 6690.1  | 6359.3  | 6029.4  | 5762.1  | 5494.9  | 5227.7  | 4960.4  | 4836.7  | 4713.0  |
| 35°    | 7967.7  | 7552.8  | 7137.9  | 6723.1  | 6308.2  | 6078.9  | 5850.4  | 5621.1  | 5392.6  | 5205.4  | 5019.0  |
| 37.5°  | 8867.6  | 8426.3  | 7985.0  | 7542.9  | 7101.6  | 6791.5  | 6482.2  | 6172.1  | 5862.8  | 5759.7  | 5657.4  |
| 40°    | 9725.4  | 9204.1  | 8683.6  | 8162.3  | 7641.9  | 7404.3  | 7166.8  | 6928.4  | 6690.9  | 6516.8  | 6342.8  |
| 42.5°  | 10443.8 | 9928.3  | 9413.6  | 8898.1  | 8383.4  | 8210.2  | 8037.8  | 7864.6  | 7692.2  | 7548.7  | 7405.2  |
| 45°    | 10690.4 | 10269.7 | 9849.9  | 9429.3  | 9008.6  | 8947.6  | 8887.4  | 8826.3  | 8766.1  | 8659.7  | 8553.3  |
| 47.5°  | 11087.1 | 10658.2 | 10230.2 | 9801.3  | 9372.3  | 9394.6  | 9416.9  | 9440.0  | 9462.3  | 9468.0  | 9473.0  |
| 50°    | 11320.6 | 10913.1 | 10506.5 | 10099.0 | 9692.4  | 9800.4  | 9907.7  | 10015.7 | 10123.8 | 10368.7 | 10612.9 |
| 52.5°  | 11661.2 | 11261.2 | 10862.0 | 10461.9 | 10061.9 | 10245.0 | 10427.3 | 10610.4 | 10792.7 | 11135.8 | 11478.9 |
| 55°    | 12088.5 | 11705.7 | 11323.9 | 10941.1 | 10559.3 | 10737.4 | 10914.7 | 11092.9 | 11270.2 | 11652.1 | 12034.0 |
| 57.5°  | 12655.1 | 12245.2 | 11836.1 | 11426.1 | 11017.0 | 11181.2 | 11344.5 | 11508.6 | 11671.9 | 12034.8 | 12397.8 |
| 60°    | 13300.1 | 12854.7 | 12409.3 | 11963.1 | 11517.7 | 11563.1 | 11607.6 | 11653.0 | 11697.5 | 12090.9 | 12483.5 |
| 62.5°  | 13616.8 | 13204.4 | 12792.8 | 12380.4 | 11968.0 | 11841.8 | 11715.6 | 11588.6 | 11462.4 | 11814.6 | 12166.0 |
| 65°    | 13342.2 | 13058.4 | 12775.5 | 12491.8 | 12208.1 | 11985.4 | 11763.5 | 11540.8 | 11318.1 | 11538.3 | 11757.7 |
| 67.5°  | 12467.9 | 12307.0 | 12147.0 | 11986.2 | 11825.3 | 11451.7 | 11078.1 | 10703.6 | 10330.0 | 10344.8 | 10358.8 |
| 70°    | 11050.8 | 11008.0 | 10965.9 | 10923.0 | 10880.1 | 10318.4 | 9757.5  | 9195.8  | 8634.1  | 8548.4  | 8462.6  |
| 72.5°  | 9255.2  | 9283.3  | 9310.5  | 9338.5  | 9366.6  | 8762.8  | 8159.0  | 7555.3  | 6951.5  | 6808.8  | 6666.1  |
| 75°    | 7168.4  | 7323.5  | 7478.6  | 7634.5  | 7789.5  | 7212.2  | 6634.8  | 6056.6  | 5479.2  | 5303.5  | 5127.9  |
| 77.5°  | 5065.2  | 5354.7  | 5643.4  | 5932.9  | 6222.4  | 5700.3  | 5179.0  | 4656.9  | 4134.8  | 4021.0  | 3907.1  |
| 80°    | 3531.8  | 3673.7  | 3815.6  | 3957.5  | 4099.3  | 3837.0  | 3574.7  | 3312.4  | 3050.2  | 3081.5  | 3112.0  |
| 82.5°  | 2572.6  | 2605.6  | 2637.8  | 2670.7  | 2703.7  | 2596.5  | 2489.3  | 2381.2  | 2274.0  | 2355.7  | 2437.3  |
| 85°    | 1648.0  | 1765.9  | 1883.0  | 2001.0  | 2118.1  | 1999.3  | 1880.6  | 1761.0  | 1642.2  | 1696.6  | 1751.1  |
| 87.5°  | 368.7   | 583.1   | 797.6   | 1012.9  | 1227.3  | 1111.8  | 997.2   | 881.7   | 766.3   | 714.3   | 663.1   |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P598556

CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° | 300° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P598556

CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 302.5°  | 305°    | 307.5°  | 310°    | 312.5°  | 315°    | 317.5°  | 320°    | 322.5°  | 325°    | 327.5°  |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  |
| 2.5°   | 2090.1  | 2133.8  | 2120.6  | 2108.2  | 2095.0  | 2081.8  | 2105.7  | 2129.7  | 2154.4  | 2178.3  | 2170.1  |
| 5°     | 2885.2  | 2893.4  | 2815.1  | 2737.6  | 2659.2  | 2580.8  | 2629.5  | 2678.2  | 2726.8  | 2775.5  | 2758.2  |
| 7.5°   | 3398.2  | 3357.0  | 3311.6  | 3266.3  | 3220.1  | 3174.7  | 3164.8  | 3154.9  | 3144.2  | 3134.3  | 3121.1  |
| 10°    | 3810.6  | 3839.5  | 3809.8  | 3780.9  | 3751.2  | 3721.6  | 3652.3  | 3583.0  | 3512.9  | 3443.6  | 3414.7  |
| 12.5°  | 4133.1  | 4165.3  | 4172.7  | 4179.3  | 4186.8  | 4194.2  | 4116.6  | 4039.9  | 3962.4  | 3884.9  | 3814.8  |
| 15°    | 4137.3  | 4164.5  | 4188.4  | 4211.5  | 4235.4  | 4258.5  | 4210.7  | 4163.7  | 4115.8  | 4068.0  | 4045.7  |
| 17.5°  | 4238.7  | 4243.7  | 4223.9  | 4204.9  | 4185.1  | 4166.1  | 4147.2  | 4129.0  | 4110.0  | 4091.9  | 4056.4  |
| 20°    | 4181.0  | 4192.5  | 4190.0  | 4187.6  | 4184.3  | 4181.8  | 4183.5  | 4184.3  | 4185.9  | 4186.8  | 4167.0  |
| 22.5°  | 4210.7  | 4158.7  | 4169.4  | 4179.3  | 4190.0  | 4199.9  | 4229.6  | 4259.3  | 4289.9  | 4319.5  | 4398.7  |
| 25°    | 4438.3  | 4325.3  | 4308.0  | 4291.5  | 4274.2  | 4257.7  | 4335.2  | 4411.9  | 4489.5  | 4567.0  | 4695.7  |
| 27.5°  | 4289.9  | 4110.9  | 4071.3  | 4031.7  | 3992.1  | 3952.5  | 4070.5  | 4187.6  | 4305.5  | 4423.5  | 4554.6  |
| 30°    | 4433.4  | 4251.1  | 4163.7  | 4076.2  | 3988.0  | 3900.5  | 4013.5  | 4125.7  | 4238.7  | 4350.9  | 4496.1  |
| 32.5°  | 4589.3  | 4465.5  | 4407.0  | 4349.2  | 4290.7  | 4232.9  | 4242.0  | 4251.1  | 4260.2  | 4269.2  | 4473.8  |
| 35°    | 4831.8  | 4644.5  | 4586.8  | 4529.0  | 4471.3  | 4413.6  | 4510.1  | 4605.8  | 4702.3  | 4797.9  | 4971.1  |
| 37.5°  | 5554.3  | 5451.2  | 5347.3  | 5243.3  | 5138.6  | 5034.7  | 5091.6  | 5148.5  | 5205.4  | 5262.3  | 5425.6  |
| 40°    | 6168.8  | 5994.7  | 5977.4  | 5960.9  | 5943.6  | 5926.3  | 5931.2  | 5935.4  | 5940.3  | 5945.3  | 6084.6  |
| 42.5°  | 7260.8  | 7117.3  | 7029.1  | 6940.8  | 6852.5  | 6764.3  | 6758.5  | 6752.7  | 6746.1  | 6740.4  | 6845.1  |
| 45°    | 8446.1  | 8339.7  | 8273.7  | 8207.7  | 8140.9  | 8074.9  | 7970.2  | 7865.4  | 7759.8  | 7655.1  | 7746.6  |
| 47.5°  | 9478.8  | 9484.5  | 9604.1  | 9722.9  | 9842.5  | 9962.1  | 9783.1  | 9604.1  | 9425.1  | 9246.2  | 9128.2  |
| 50°    | 10857.8 | 11102.0 | 11130.9 | 11158.9 | 11187.8 | 11216.6 | 10913.1 | 10610.4 | 10306.9 | 10003.3 | 9879.6  |
| 52.5°  | 11822.9 | 12166.0 | 12121.5 | 12077.7 | 12033.2 | 11988.7 | 11813.0 | 11638.1 | 11462.4 | 11286.7 | 11017.0 |
| 55°    | 12416.7 | 12798.6 | 12764.8 | 12731.8 | 12698.0 | 12664.2 | 12536.3 | 12408.5 | 12280.6 | 12152.8 | 11856.7 |
| 57.5°  | 12760.7 | 13123.6 | 13133.5 | 13143.4 | 13153.3 | 13163.2 | 13129.4 | 13095.6 | 13061.7 | 13027.9 | 12642.7 |
| 60°    | 12877.0 | 13270.4 | 13274.5 | 13277.8 | 13282.0 | 13285.3 | 13231.6 | 13178.0 | 13123.6 | 13070.0 | 12818.4 |
| 62.5°  | 12518.2 | 12869.6 | 12885.2 | 12900.1 | 12915.7 | 12931.4 | 12894.3 | 12857.2 | 12820.1 | 12783.0 | 12596.5 |
| 65°    | 11977.9 | 12198.2 | 12202.3 | 12205.6 | 12209.7 | 12213.8 | 12119.8 | 12026.6 | 11932.6 | 11838.5 | 11794.0 |
| 67.5°  | 10373.7 | 10388.5 | 10475.9 | 10563.4 | 10650.8 | 10738.2 | 10745.7 | 10753.1 | 10761.3 | 10768.8 | 10704.4 |
| 70°    | 8376.8  | 8291.0  | 8385.9  | 8480.7  | 8575.6  | 8670.4  | 8710.8  | 8751.3  | 8792.5  | 8832.9  | 8862.6  |
| 72.5°  | 6522.6  | 6379.9  | 6450.0  | 6520.1  | 6591.1  | 6661.2  | 6601.0  | 6540.8  | 6480.6  | 6420.3  | 6610.9  |
| 75°    | 4952.2  | 4776.5  | 4767.4  | 4759.2  | 4750.1  | 4741.8  | 4711.3  | 4680.8  | 4649.5  | 4619.0  | 4797.1  |
| 77.5°  | 3792.5  | 3678.7  | 3684.4  | 3689.4  | 3695.2  | 3700.1  | 3668.8  | 3638.2  | 3606.9  | 3575.6  | 3644.0  |
| 80°    | 3143.4  | 3173.9  | 3174.7  | 3175.5  | 3176.4  | 3177.2  | 3147.5  | 3118.6  | 3088.9  | 3059.2  | 3009.7  |
| 82.5°  | 2519.8  | 2601.5  | 2600.6  | 2600.6  | 2599.8  | 2599.0  | 2597.3  | 2595.7  | 2593.2  | 2591.6  | 2510.7  |
| 85°    | 1805.5  | 1860.0  | 1803.9  | 1747.8  | 1691.7  | 1635.6  | 1676.8  | 1718.1  | 1760.2  | 1801.4  | 1767.6  |
| 87.5°  | 611.2   | 560.0   | 493.2   | 427.3   | 360.4   | 293.6   | 365.4   | 437.2   | 509.7   | 581.5   | 622.7   |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P598556  
 CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305° | 307.5° | 310° | 312.5° | 315° | 317.5° | 320° | 322.5° | 325° | 327.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P598556

CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 330°    | 332.5°  | 335°    | 337.5°  | 340°    | 342.5°  | 345°    | 347.5°  | 350°    | 352.5°  | 355°    |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  | 1792.3  |
| 2.5°   | 2162.7  | 2154.4  | 2147.0  | 2095.0  | 2042.2  | 1990.3  | 1937.5  | 2033.2  | 2129.7  | 2225.3  | 2321.0  |
| 5°     | 2741.7  | 2724.4  | 2707.9  | 2703.7  | 2699.6  | 2694.7  | 2690.5  | 2739.2  | 2787.9  | 2835.7  | 2884.4  |
| 7.5°   | 3107.9  | 3094.7  | 3081.5  | 3046.9  | 3013.0  | 2978.4  | 2943.8  | 2973.5  | 3002.3  | 3032.0  | 3060.9  |
| 10°    | 3386.7  | 3357.8  | 3328.9  | 3253.9  | 3179.7  | 3104.6  | 3029.5  | 3007.3  | 2985.0  | 2962.7  | 2940.5  |
| 12.5°  | 3744.7  | 3673.7  | 3603.6  | 3518.7  | 3432.9  | 3347.9  | 3262.1  | 3250.6  | 3239.0  | 3228.3  | 3216.8  |
| 15°    | 4024.3  | 4002.0  | 3979.7  | 3912.1  | 3844.5  | 3776.8  | 3709.2  | 3618.5  | 3526.9  | 3436.2  | 3345.4  |
| 17.5°  | 4021.8  | 3986.3  | 3951.7  | 4042.4  | 4132.3  | 4223.0  | 4312.9  | 4216.4  | 4119.1  | 4022.6  | 3926.1  |
| 20°    | 4147.2  | 4126.5  | 4106.7  | 4274.2  | 4440.8  | 4608.2  | 4774.8  | 4722.1  | 4668.4  | 4615.7  | 4562.0  |
| 22.5°  | 4477.1  | 4556.3  | 4634.6  | 4778.1  | 4920.8  | 5064.4  | 5207.0  | 5267.3  | 5327.5  | 5387.7  | 5447.9  |
| 25°    | 4823.5  | 4952.2  | 5080.8  | 5294.5  | 5507.3  | 5720.9  | 5934.5  | 5977.4  | 6020.3  | 6063.2  | 6106.1  |
| 27.5°  | 4684.9  | 4816.1  | 4947.2  | 5108.9  | 5269.7  | 5431.4  | 5592.2  | 5780.3  | 5969.2  | 6157.2  | 6345.3  |
| 30°    | 4640.4  | 4785.6  | 4929.9  | 5151.8  | 5372.8  | 5594.7  | 5816.6  | 6075.6  | 6334.6  | 6592.7  | 6851.7  |
| 32.5°  | 4677.5  | 4882.1  | 5086.6  | 5386.9  | 5686.3  | 5986.5  | 6286.7  | 6558.9  | 6831.9  | 7104.1  | 7376.3  |
| 35°    | 5143.5  | 5316.7  | 5489.1  | 5824.8  | 6160.5  | 6496.2  | 6831.9  | 7151.1  | 7470.3  | 7788.7  | 8107.9  |
| 37.5°  | 5588.1  | 5751.4  | 5914.7  | 6257.9  | 6600.2  | 6943.3  | 7286.4  | 7790.4  | 8295.1  | 8799.1  | 9303.1  |
| 40°    | 6223.2  | 6362.6  | 6501.2  | 6794.8  | 7088.4  | 7382.1  | 7675.7  | 8283.6  | 8891.5  | 9499.4  | 10107.3 |
| 42.5°  | 6949.0  | 7053.8  | 7157.7  | 7462.1  | 7766.4  | 8070.8  | 8375.2  | 9036.7  | 9699.0  | 10360.5 | 11022.0 |
| 45°    | 7837.4  | 7928.9  | 8020.5  | 8230.0  | 8439.5  | 8649.8  | 8859.3  | 9541.4  | 10223.6 | 10905.7 | 11587.8 |
| 47.5°  | 9010.3  | 8892.3  | 8774.4  | 8877.5  | 8980.6  | 9083.7  | 9186.8  | 9861.5  | 10536.2 | 11210.0 | 11884.7 |
| 50°    | 9755.9  | 9632.2  | 9508.4  | 9517.5  | 9525.8  | 9534.8  | 9543.9  | 10173.2 | 10802.6 | 11431.1 | 12060.4 |
| 52.5°  | 10747.3 | 10476.8 | 10207.1 | 10204.6 | 10202.1 | 10198.8 | 10196.3 | 10744.8 | 11294.2 | 11842.7 | 12391.2 |
| 55°    | 11560.6 | 11264.5 | 10968.4 | 10910.6 | 10852.9 | 10794.3 | 10736.6 | 11279.3 | 11821.2 | 12363.9 | 12905.8 |
| 57.5°  | 12257.5 | 11871.5 | 11486.3 | 11395.6 | 11304.9 | 11214.2 | 11123.4 | 11708.2 | 12293.8 | 12878.6 | 13463.4 |
| 60°    | 12567.7 | 12316.1 | 12065.4 | 11954.0 | 11842.7 | 11731.3 | 11620.0 | 12118.2 | 12616.3 | 13113.7 | 13611.9 |
| 62.5°  | 12411.0 | 12224.6 | 12039.0 | 12064.5 | 12090.1 | 12115.7 | 12141.2 | 12425.8 | 12711.2 | 12995.8 | 13280.3 |
| 65°    | 11750.3 | 11705.7 | 11662.0 | 11868.2 | 12074.4 | 12280.6 | 12486.8 | 12491.0 | 12495.1 | 12499.2 | 12503.3 |
| 67.5°  | 10640.1 | 10575.8 | 10511.4 | 10940.3 | 11368.4 | 11797.3 | 12226.2 | 12022.5 | 11818.7 | 11615.8 | 11412.1 |
| 70°    | 8891.5  | 8921.2  | 8950.0  | 9534.0  | 10117.2 | 10701.1 | 11285.1 | 10989.8 | 10693.7 | 10398.4 | 10102.3 |
| 72.5°  | 6801.4  | 6992.8  | 7183.3  | 7788.7  | 8394.1  | 8999.5  | 9604.9  | 9267.6  | 8929.4  | 8592.1  | 8253.9  |
| 75°    | 4975.3  | 5153.4  | 5331.6  | 5929.6  | 6527.6  | 7126.4  | 7724.4  | 7323.5  | 6922.7  | 6522.6  | 6121.8  |
| 77.5°  | 3712.5  | 3781.8  | 3850.2  | 4347.6  | 4844.1  | 5341.5  | 5838.0  | 5435.5  | 5033.0  | 4631.3  | 4228.8  |
| 80°    | 2961.1  | 2911.6  | 2862.9  | 3138.4  | 3413.9  | 3689.4  | 3964.9  | 3679.5  | 3393.3  | 3107.9  | 2822.5  |
| 82.5°  | 2430.7  | 2349.9  | 2269.9  | 2372.2  | 2474.4  | 2577.5  | 2679.8  | 2451.3  | 2222.9  | 1994.4  | 1765.9  |
| 85°    | 1733.8  | 1699.9  | 1666.1  | 1695.8  | 1724.7  | 1754.4  | 1784.1  | 1561.4  | 1338.7  | 1116.8  | 894.1   |
| 87.5°  | 663.1   | 704.4   | 745.6   | 792.6   | 838.8   | 885.8   | 932.0   | 730.0   | 527.9   | 326.6   | 124.5   |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P598556

CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 330° | 332.5° | 335° | 337.5° | 340° | 342.5° | 345° | 347.5° | 350° | 352.5° | 355° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |





REPORT NUMBER: P598556  
 CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 357.5°  | 360°    |
|--------|---------|---------|
| 0°     | 1792.3  | 1792.3  |
| 2.5°   | 2360.6  | 2400.2  |
| 5°     | 2883.5  | 2882.7  |
| 7.5°   | 3047.7  | 3033.7  |
| 10°    | 2904.2  | 2867.9  |
| 12.5°  | 3109.5  | 3001.5  |
| 15°    | 3238.2  | 3130.2  |
| 17.5°  | 3763.6  | 3600.3  |
| 20°    | 4368.2  | 4173.6  |
| 22.5°  | 5151.8  | 4855.7  |
| 25°    | 5752.2  | 5397.6  |
| 27.5°  | 6135.0  | 5923.8  |
| 30°    | 6610.1  | 6368.4  |
| 32.5°  | 7198.1  | 7019.2  |
| 35°    | 7944.6  | 7780.5  |
| 37.5°  | 9251.9  | 9200.0  |
| 40°    | 10045.4 | 9982.7  |
| 42.5°  | 11024.4 | 11026.1 |
| 45°    | 11624.9 | 11662.0 |
| 47.5°  | 11978.8 | 12072.0 |
| 50°    | 12260.8 | 12460.4 |
| 52.5°  | 12664.2 | 12937.2 |
| 55°    | 13268.8 | 13630.9 |
| 57.5°  | 13771.9 | 14080.4 |
| 60°    | 13771.9 | 13931.1 |
| 62.5°  | 13276.2 | 13271.2 |
| 65°    | 12426.6 | 12349.1 |
| 67.5°  | 11314.8 | 11217.5 |
| 70°    | 9950.5  | 9798.0  |
| 72.5°  | 8065.0  | 7875.3  |
| 75°    | 5861.9  | 5601.3  |
| 77.5°  | 4105.1  | 3980.5  |
| 80°    | 2882.7  | 2942.9  |
| 82.5°  | 1851.7  | 1937.5  |
| 85°    | 880.9   | 867.7   |
| 87.5°  | 103.9   | 83.3    |
| 90°    | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     |



REPORT NUMBER: P598556  
CATALOG NUMBER: PMM-SA4C-835-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

(END OF REPORT)