

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P366941

Luminaire Tested: **PMM-SA1C-750-U-SLR-HSS**

Issue Date: 12/2/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P366941  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1910-543-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/2/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: PMM-SA1C-750-U-SLR-HSS  
Description: MESA POST TOP DECORATIVE LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4575 lumens  
Efficiency: N/A  
Efficacy: 77.5 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G1


Input Watts (W): 59  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.4 fc  
 Type IV - Short - N/A

REPORT NUMBER: P366941  
CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 270-Deg Lateral    - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P366941

CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 764.0    | 0.0    | 764.0  |
|                    | % Fixture | 16.7     | 0.0    | 16.7   |
| <b>Street Side</b> | Lumens    | 3811.0   | 0.0    | 3811.0 |
|                    | % Fixture | 83.3     | 0.0    | 83.3   |
| <b>Total</b>       | Lumens    | 4575.0   | 0.0    | 4575.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 61.6   | 1.3       |
| 10°-20°   | 160.9  | 3.5       |
| 20°-30°   | 260.1  | 5.7       |
| 30°-40°   | 435.6  | 9.5       |
| 40°-50°   | 712.1  | 15.6      |
| 50°-60°   | 1054.1 | 23.0      |
| 60°-70°   | 1210.1 | 26.5      |
| 70°-80°   | 598.3  | 13.1      |
| 80°-90°   | 82.2   | 1.8       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 4575.0 | 100.0     |
| 0°-180°   | 4575.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P366941


CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 356.4  | 7.8       |                         |      |         |
| FM (30°-60°)   | 1821.1 | 39.8      |                         |      |         |
| FH (60°-80°)   | 1555.7 | 34.0      |                         |      | G1/1800 |
| FVH (80°-90°)  | 77.8   | 1.7       |                         |      | G1/100  |
| BL (0°-30°)    | 126.2  | 2.8       | B1/500                  |      |         |
| BM (30°-60°)   | 380.7  | 8.3       | B1/1000                 |      |         |
| BH (60°-80°)   | 252.8  | 5.5       | B1/500                  |      | G1/500  |
| BVH (80°-90°)  | 4.4    | 0.1       |                         |      | G0/10   |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G1**

Type IV Short





REPORT NUMBER: P366941

CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°     | 7.5°   | 10°    | 12.5°  | 15°   | 17.5° | 20°   | 22.5° | 25°   |
|--------|--------|--------|--------|--------|--------|--------|-------|-------|-------|-------|-------|
| 0°     | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3 | 551.3 | 551.3 | 551.3 | 551.3 |
| 2.5°   | 731.0  | 740.1  | 749.0  | 732.0  | 715.1  | 698.1  | 681.2 | 666.1 | 650.9 | 635.5 | 620.4 |
| 5°     | 940.7  | 924.0  | 907.3  | 884.3  | 861.4  | 838.4  | 815.5 | 804.8 | 794.1 | 783.4 | 772.7 |
| 7.5°   | 1013.7 | 984.0  | 954.0  | 933.6  | 913.5  | 893.2  | 872.9 | 840.8 | 808.4 | 776.4 | 744.0 |
| 10°    | 956.3  | 924.8  | 892.9  | 875.2  | 857.5  | 839.7  | 822.0 | 782.1 | 741.9 | 702.0 | 661.9 |
| 12.5°  | 982.7  | 948.5  | 914.3  | 877.8  | 841.3  | 804.8  | 768.3 | 737.8 | 707.0 | 676.5 | 645.7 |
| 15°    | 1000.9 | 961.8  | 922.4  | 880.7  | 839.0  | 797.2  | 755.5 | 719.5 | 683.8 | 647.8 | 611.8 |
| 17.5°  | 1108.1 | 1052.0 | 996.0  | 931.8  | 867.6  | 803.5  | 739.3 | 697.6 | 656.1 | 614.4 | 572.7 |
| 20°    | 1245.8 | 1166.3 | 1086.4 | 999.6  | 912.8  | 825.9  | 739.1 | 687.2 | 635.3 | 583.4 | 531.5 |
| 22.5°  | 1405.9 | 1306.6 | 1206.9 | 1099.7 | 992.8  | 885.6  | 778.5 | 703.9 | 629.3 | 554.7 | 480.1 |
| 25°    | 1567.1 | 1477.4 | 1387.7 | 1243.4 | 1099.2 | 954.8  | 810.5 | 715.9 | 620.9 | 526.3 | 431.3 |
| 27.5°  | 1858.1 | 1697.7 | 1537.4 | 1353.8 | 1170.4 | 986.8  | 803.2 | 694.7 | 586.3 | 477.5 | 369.0 |
| 30°    | 2048.5 | 1925.1 | 1801.5 | 1559.0 | 1316.7 | 1074.2 | 831.7 | 694.2 | 556.8 | 419.1 | 281.7 |
| 32.5°  | 2276.2 | 2095.7 | 1915.0 | 1651.8 | 1388.7 | 1125.6 | 862.4 | 701.0 | 539.3 | 377.9 | 216.2 |
| 35°    | 2532.0 | 2335.6 | 2139.3 | 1806.0 | 1472.7 | 1139.1 | 805.8 | 649.4 | 492.9 | 336.4 | 179.9 |
| 37.5°  | 2984.0 | 2655.4 | 2326.8 | 1938.2 | 1549.4 | 1160.8 | 771.9 | 615.7 | 459.3 | 303.0 | 146.6 |
| 40°    | 3240.6 | 2926.8 | 2613.1 | 2127.5 | 1641.9 | 1156.3 | 670.8 | 532.0 | 393.5 | 254.8 | 116.1 |
| 42.5°  | 3574.4 | 3176.4 | 2778.2 | 2235.5 | 1692.8 | 1150.1 | 607.4 | 479.1 | 350.8 | 222.2 | 93.9  |
| 45°    | 3772.3 | 3321.4 | 2870.5 | 2282.4 | 1694.3 | 1106.3 | 518.2 | 407.1 | 296.0 | 184.9 | 73.8  |
| 47.5°  | 3897.2 | 3445.0 | 2992.8 | 2361.4 | 1730.3 | 1099.0 | 467.6 | 365.4 | 263.1 | 160.9 | 58.7  |
| 50°    | 3960.6 | 3507.1 | 3053.3 | 2404.5 | 1755.6 | 1106.5 | 457.7 | 356.0 | 254.0 | 152.3 | 50.3  |
| 52.5°  | 4026.6 | 3589.2 | 3151.6 | 2479.1 | 1806.5 | 1133.9 | 461.3 | 357.5 | 254.0 | 150.2 | 46.4  |
| 55°    | 4159.9 | 3728.5 | 3296.9 | 2586.0 | 1875.1 | 1164.2 | 453.3 | 351.0 | 248.8 | 146.3 | 44.1  |
| 57.5°  | 4323.6 | 3862.6 | 3401.2 | 2664.2 | 1927.2 | 1190.2 | 453.3 | 350.5 | 247.7 | 144.7 | 42.0  |
| 60°    | 4292.6 | 3792.1 | 3291.4 | 2576.3 | 1861.3 | 1145.9 | 430.8 | 333.0 | 235.5 | 137.7 | 39.9  |
| 62.5°  | 4079.5 | 3536.3 | 2992.8 | 2332.0 | 1670.9 | 1010.0 | 348.9 | 271.0 | 193.0 | 114.7 | 36.8  |
| 65°    | 3829.2 | 3252.6 | 2675.7 | 2067.5 | 1459.1 | 851.0  | 242.5 | 190.4 | 138.0 | 85.8  | 33.4  |
| 67.5°  | 3527.7 | 2912.8 | 2297.8 | 1756.9 | 1216.3 | 675.4  | 134.6 | 108.5 | 82.4  | 56.1  | 30.0  |
| 70°    | 3004.6 | 2369.8 | 1734.8 | 1319.1 | 903.6  | 487.9  | 72.2  | 61.0  | 49.8  | 38.6  | 27.4  |
| 72.5°  | 2255.6 | 1674.0 | 1092.4 | 829.8  | 567.5  | 304.9  | 42.2  | 38.1  | 33.6  | 29.5  | 25.0  |
| 75°    | 1534.7 | 1099.0 | 663.2  | 504.9  | 346.8  | 188.6  | 30.3  | 28.2  | 25.8  | 23.7  | 21.4  |
| 77.5°  | 1043.4 | 754.7  | 466.0  | 355.7  | 245.4  | 135.1  | 24.8  | 23.5  | 22.2  | 20.6  | 19.3  |
| 80°    | 651.5  | 445.9  | 240.4  | 185.2  | 129.6  | 74.3   | 18.8  | 18.0  | 17.2  | 16.2  | 15.4  |
| 82.5°  | 455.6  | 272.5  | 89.5   | 69.9   | 50.3   | 30.5   | 11.0  | 11.2  | 11.5  | 11.5  | 11.7  |
| 85°    | 191.2  | 103.3  | 15.4   | 13.0   | 10.7   | 8.3    | 6.0   | 6.5   | 7.3   | 7.8   | 8.3   |
| 87.5°  | 3.4    | 1.8    | 0.0    | 0.5    | 1.3    | 1.8    | 2.3   | 3.1   | 3.7   | 4.4   | 5.0   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 2.5° | 5°  | 7.5° | 10° | 12.5° | 15° | 17.5° | 20° | 22.5° | 25° |
|--------|-----|------|-----|------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |





REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30°   | 32.5° | 35°   | 37.5° | 40°   | 42.5° | 45°   | 47.5° | 50°   | 52.5° |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 551.3 | 551.3 | 551.3 | 551.3 | 551.3 | 551.3 | 551.3 | 551.3 | 551.3 | 551.3 | 551.3 |
| 2.5°   | 624.3 | 628.2 | 631.9 | 635.8 | 632.7 | 629.8 | 626.7 | 623.5 | 618.9 | 614.4 | 609.7 |
| 5°     | 759.7 | 746.6 | 733.6 | 720.6 | 700.7 | 680.9 | 660.8 | 641.0 | 638.7 | 636.3 | 633.7 |
| 7.5°   | 713.5 | 683.0 | 652.2 | 621.7 | 593.0 | 564.3 | 535.7 | 507.0 | 498.1 | 489.5 | 480.6 |
| 10°    | 638.4 | 614.9 | 591.2 | 567.7 | 547.1 | 526.3 | 505.7 | 484.8 | 463.2 | 441.5 | 419.6 |
| 12.5°  | 621.2 | 596.7 | 571.9 | 547.4 | 528.6 | 509.8 | 491.1 | 472.3 | 448.0 | 423.8 | 399.5 |
| 15°    | 585.2 | 558.6 | 532.0 | 505.4 | 480.4 | 455.3 | 430.0 | 405.0 | 375.8 | 346.6 | 317.4 |
| 17.5°  | 541.1 | 509.8 | 478.3 | 446.7 | 413.9 | 381.0 | 348.2 | 315.3 | 281.7 | 248.3 | 214.6 |
| 20°    | 488.7 | 445.9 | 402.9 | 360.2 | 319.5 | 278.8 | 237.8 | 197.2 | 176.0 | 155.2 | 134.0 |
| 22.5°  | 424.8 | 369.3 | 314.0 | 258.4 | 225.1 | 191.4 | 158.0 | 124.4 | 115.3 | 106.1 | 97.0  |
| 25°    | 368.5 | 305.6 | 242.8 | 179.9 | 158.8 | 137.7 | 116.6 | 95.4  | 91.3  | 86.8  | 82.7  |
| 27.5°  | 309.8 | 250.9 | 191.7 | 132.5 | 120.5 | 108.2 | 96.2  | 84.0  | 81.1  | 78.5  | 75.6  |
| 30°    | 237.6 | 193.5 | 149.2 | 105.1 | 97.3  | 89.5  | 81.4  | 73.5  | 72.2  | 70.7  | 69.4  |
| 32.5°  | 184.1 | 151.8 | 119.7 | 87.4  | 82.9  | 78.5  | 74.1  | 69.6  | 67.5  | 65.5  | 63.1  |
| 35°    | 153.9 | 128.0 | 102.0 | 75.9  | 72.8  | 69.4  | 66.2  | 62.9  | 60.8  | 58.4  | 56.3  |
| 37.5°  | 127.5 | 108.7 | 89.7  | 70.7  | 67.3  | 63.9  | 60.2  | 56.9  | 55.3  | 53.7  | 52.2  |
| 40°    | 105.1 | 94.1  | 83.2  | 72.2  | 67.3  | 62.3  | 57.4  | 52.4  | 51.1  | 49.8  | 48.5  |
| 42.5°  | 86.8  | 79.8  | 72.5  | 65.5  | 61.8  | 58.4  | 54.8  | 51.1  | 49.3  | 47.2  | 45.4  |
| 45°    | 70.2  | 66.2  | 62.6  | 58.7  | 58.9  | 59.2  | 59.2  | 59.5  | 54.8  | 49.8  | 45.1  |
| 47.5°  | 56.9  | 55.0  | 52.9  | 51.1  | 53.2  | 55.3  | 57.1  | 59.2  | 54.2  | 49.3  | 44.1  |
| 50°    | 48.8  | 47.5  | 45.9  | 44.3  | 46.4  | 48.8  | 50.9  | 52.9  | 50.9  | 49.0  | 46.9  |
| 52.5°  | 44.6  | 42.8  | 40.9  | 39.1  | 39.9  | 40.9  | 41.7  | 42.5  | 42.5  | 42.5  | 42.5  |
| 55°    | 42.0  | 40.2  | 38.1  | 36.0  | 35.2  | 34.2  | 33.4  | 32.3  | 31.0  | 30.0  | 28.7  |
| 57.5°  | 39.9  | 37.8  | 35.5  | 33.4  | 32.1  | 30.5  | 29.2  | 27.6  | 26.3  | 24.8  | 23.5  |
| 60°    | 37.8  | 35.7  | 33.4  | 31.3  | 30.0  | 28.7  | 27.1  | 25.8  | 24.3  | 22.9  | 21.4  |
| 62.5°  | 34.9  | 33.1  | 31.3  | 29.5  | 28.2  | 27.1  | 25.8  | 24.5  | 22.9  | 21.4  | 19.6  |
| 65°    | 31.8  | 30.5  | 28.9  | 27.4  | 26.1  | 24.8  | 23.5  | 22.2  | 20.6  | 19.3  | 17.7  |
| 67.5°  | 28.9  | 27.6  | 26.6  | 25.3  | 23.7  | 22.4  | 20.9  | 19.3  | 18.3  | 17.2  | 15.9  |
| 70°    | 26.6  | 25.6  | 24.8  | 23.7  | 22.2  | 20.9  | 19.3  | 17.7  | 17.0  | 15.9  | 15.1  |
| 72.5°  | 24.3  | 23.5  | 22.4  | 21.6  | 20.3  | 19.0  | 17.7  | 16.4  | 15.6  | 14.9  | 14.1  |
| 75°    | 20.9  | 20.3  | 19.8  | 19.3  | 18.0  | 16.7  | 15.1  | 13.8  | 13.6  | 13.3  | 13.0  |
| 77.5°  | 18.8  | 18.5  | 18.0  | 17.5  | 16.2  | 14.9  | 13.6  | 12.3  | 12.5  | 12.8  | 12.8  |
| 80°    | 15.4  | 15.4  | 15.1  | 15.1  | 14.1  | 13.0  | 11.7  | 10.7  | 11.2  | 12.0  | 12.5  |
| 82.5°  | 11.7  | 11.7  | 11.7  | 11.7  | 10.7  | 9.6   | 8.6   | 7.6   | 8.3   | 8.9   | 9.6   |
| 85°    | 8.1   | 7.8   | 7.6   | 7.3   | 6.5   | 6.0   | 5.2   | 4.4   | 5.5   | 6.3   | 7.3   |
| 87.5°  | 5.0   | 5.2   | 5.2   | 5.2   | 4.7   | 3.9   | 3.4   | 2.6   | 3.1   | 3.4   | 3.9   |
| 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30° | 32.5° | 35° | 37.5° | 40° | 42.5° | 45° | 47.5° | 50° | 52.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |



REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 55°   | 57.5° | 60°   | 62.5° | 65°   | 67.5° | 70°   | 72.5° | 75°   | 77.5° | 80°   |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 551.3 | 551.3 | 551.3 | 551.3 | 551.3 | 551.3 | 551.3 | 551.3 | 551.3 | 551.3 | 551.3 |
| 2.5°   | 605.0 | 597.2 | 589.4 | 581.3 | 573.5 | 555.2 | 537.0 | 518.7 | 500.5 | 514.0 | 527.3 |
| 5°     | 631.4 | 616.2 | 600.9 | 585.7 | 570.3 | 563.6 | 557.0 | 550.3 | 543.5 | 544.5 | 545.8 |
| 7.5°   | 471.8 | 461.9 | 451.9 | 441.8 | 431.9 | 429.8 | 428.0 | 425.9 | 423.8 | 428.2 | 432.4 |
| 10°    | 398.0 | 384.1 | 370.1 | 356.2 | 342.2 | 334.6 | 327.0 | 319.5 | 311.9 | 311.1 | 310.1 |
| 12.5°  | 375.3 | 354.2 | 333.3 | 312.2 | 291.0 | 274.6 | 258.2 | 241.8 | 225.3 | 226.6 | 227.9 |
| 15°    | 288.2 | 267.0 | 246.2 | 225.1 | 203.9 | 190.6 | 177.1 | 163.8 | 150.2 | 146.3 | 142.4 |
| 17.5°  | 181.0 | 165.3 | 149.7 | 133.8 | 118.1 | 113.7 | 109.5 | 105.1 | 100.7 | 99.4  | 98.1  |
| 20°    | 112.9 | 106.1 | 99.4  | 92.3  | 85.5  | 84.5  | 83.5  | 82.4  | 81.4  | 82.1  | 82.9  |
| 22.5°  | 87.9  | 85.0  | 81.9  | 79.0  | 75.9  | 74.8  | 73.8  | 72.8  | 71.7  | 72.5  | 73.0  |
| 25°    | 78.2  | 76.2  | 74.1  | 72.0  | 69.9  | 68.8  | 67.5  | 66.5  | 65.2  | 65.7  | 66.5  |
| 27.5°  | 72.8  | 70.9  | 69.1  | 67.3  | 65.5  | 63.6  | 62.1  | 60.2  | 58.4  | 59.5  | 60.2  |
| 30°    | 67.8  | 65.7  | 63.9  | 61.8  | 59.7  | 57.9  | 56.1  | 54.0  | 52.2  | 53.2  | 54.2  |
| 32.5°  | 61.0  | 59.2  | 57.1  | 55.3  | 53.2  | 52.2  | 51.1  | 49.8  | 48.8  | 49.5  | 50.1  |
| 35°    | 54.0  | 52.4  | 51.1  | 49.5  | 48.0  | 46.9  | 46.2  | 45.1  | 44.1  | 44.3  | 44.9  |
| 37.5°  | 50.6  | 48.8  | 46.9  | 45.1  | 43.3  | 42.8  | 42.2  | 41.5  | 40.9  | 40.9  | 40.9  |
| 40°    | 47.2  | 45.4  | 43.6  | 41.5  | 39.6  | 38.9  | 38.1  | 37.3  | 36.5  | 36.5  | 36.5  |
| 42.5°  | 43.3  | 41.5  | 39.6  | 37.8  | 36.0  | 35.2  | 34.2  | 33.4  | 32.3  | 32.3  | 32.3  |
| 45°    | 40.2  | 38.3  | 36.8  | 34.9  | 33.1  | 31.8  | 30.5  | 28.9  | 27.6  | 27.4  | 27.1  |
| 47.5°  | 39.1  | 36.5  | 33.9  | 31.3  | 28.7  | 27.4  | 26.1  | 24.5  | 23.2  | 22.9  | 22.7  |
| 50°    | 44.9  | 39.6  | 34.4  | 29.2  | 24.0  | 22.9  | 21.9  | 20.9  | 19.8  | 19.3  | 19.0  |
| 52.5°  | 42.5  | 37.0  | 31.6  | 26.1  | 20.6  | 19.8  | 19.0  | 18.3  | 17.5  | 17.0  | 16.4  |
| 55°    | 27.4  | 25.0  | 22.9  | 20.6  | 18.3  | 17.7  | 17.2  | 16.4  | 15.9  | 15.4  | 14.9  |
| 57.5°  | 21.9  | 20.6  | 19.6  | 18.3  | 17.0  | 16.4  | 15.9  | 15.1  | 14.6  | 13.8  | 13.3  |
| 60°    | 19.8  | 18.8  | 17.7  | 16.7  | 15.6  | 15.1  | 14.6  | 14.1  | 13.6  | 12.8  | 12.3  |
| 62.5°  | 18.0  | 17.2  | 16.4  | 15.6  | 14.9  | 14.3  | 13.8  | 13.3  | 12.8  | 12.0  | 11.2  |
| 65°    | 16.2  | 15.6  | 15.1  | 14.6  | 14.1  | 13.6  | 13.0  | 12.3  | 11.7  | 11.0  | 10.2  |
| 67.5°  | 14.9  | 14.6  | 14.3  | 14.1  | 13.8  | 13.3  | 12.5  | 12.0  | 11.2  | 10.4  | 9.4   |
| 70°    | 14.1  | 14.1  | 14.1  | 13.8  | 13.8  | 13.3  | 12.5  | 12.0  | 11.2  | 10.2  | 9.4   |
| 72.5°  | 13.3  | 13.6  | 13.8  | 13.8  | 14.1  | 13.3  | 12.5  | 11.7  | 11.0  | 9.9   | 9.1   |
| 75°    | 12.8  | 13.0  | 13.3  | 13.3  | 13.6  | 13.0  | 12.5  | 11.7  | 11.2  | 10.2  | 9.1   |
| 77.5°  | 13.0  | 13.3  | 13.3  | 13.6  | 13.6  | 13.0  | 12.5  | 11.7  | 11.2  | 9.9   | 8.6   |
| 80°    | 13.0  | 12.8  | 12.5  | 12.0  | 11.7  | 10.7  | 9.6   | 8.3   | 7.3   | 5.7   | 4.4   |
| 82.5°  | 10.2  | 9.6   | 9.4   | 8.9   | 8.3   | 7.3   | 6.3   | 5.2   | 4.2   | 3.1   | 2.1   |
| 85°    | 8.1   | 7.6   | 7.3   | 6.8   | 6.3   | 5.5   | 4.4   | 3.7   | 2.6   | 2.1   | 1.3   |
| 87.5°  | 4.2   | 3.9   | 3.4   | 3.1   | 2.6   | 2.1   | 1.3   | 0.8   | 0.0   | 0.0   | 0.0   |
| 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 55° | 57.5° | 60° | 62.5° | 65° | 67.5° | 70° | 72.5° | 75° | 77.5° | 80° |
|--------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |



REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85°   | 87.5° | 90°   | 92.5° | 95°   | 97.5° | 100°  | 102.5° | 105°  | 107.5° |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|--------|-------|--------|
| 0°     | 551.3 | 551.3 | 551.3 | 551.3 | 551.3 | 551.3 | 551.3 | 551.3 | 551.3  | 551.3 | 551.3  |
| 2.5°   | 540.9 | 554.2 | 552.4 | 550.5 | 559.1 | 567.7 | 561.5 | 555.5 | 549.2  | 543.0 | 529.9  |
| 5°     | 546.9 | 547.9 | 546.1 | 544.0 | 544.3 | 544.5 | 540.4 | 536.2 | 532.0  | 527.8 | 527.1  |
| 7.5°   | 436.8 | 441.0 | 446.7 | 452.2 | 452.5 | 452.5 | 449.3 | 446.2 | 442.8  | 439.7 | 441.3  |
| 10°    | 309.3 | 308.3 | 309.8 | 311.4 | 311.1 | 310.6 | 318.9 | 327.3 | 335.4  | 343.7 | 337.7  |
| 12.5°  | 229.0 | 230.3 | 223.8 | 217.2 | 219.6 | 221.7 | 223.0 | 224.3 | 225.6  | 226.9 | 230.5  |
| 15°    | 138.5 | 134.6 | 129.9 | 125.2 | 127.5 | 129.6 | 132.0 | 134.0 | 136.4  | 138.5 | 140.8  |
| 17.5°  | 96.5  | 95.2  | 93.1  | 90.8  | 91.0  | 91.3  | 91.5  | 91.8  | 91.8   | 92.1  | 92.6   |
| 20°    | 83.7  | 84.5  | 82.9  | 81.1  | 80.6  | 79.8  | 79.3  | 78.8  | 78.0   | 77.5  | 76.7   |
| 22.5°  | 73.8  | 74.3  | 74.6  | 74.6  | 73.5  | 72.2  | 71.2  | 70.4  | 69.4   | 68.3  | 67.8   |
| 25°    | 67.0  | 67.5  | 67.0  | 66.2  | 65.7  | 65.2  | 64.7  | 63.9  | 63.4   | 62.6  | 62.3   |
| 27.5°  | 61.3  | 62.1  | 62.1  | 61.8  | 61.3  | 60.5  | 59.2  | 58.2  | 56.9   | 55.5  | 55.8   |
| 30°    | 55.3  | 56.3  | 56.3  | 56.1  | 55.8  | 55.5  | 54.2  | 52.9  | 51.6   | 50.3  | 50.9   |
| 32.5°  | 50.9  | 51.4  | 51.1  | 50.9  | 50.9  | 50.6  | 49.5  | 48.8  | 47.7   | 46.7  | 46.7   |
| 35°    | 45.1  | 45.4  | 45.4  | 45.4  | 45.4  | 45.1  | 44.3  | 43.6  | 42.8   | 42.0  | 42.2   |
| 37.5°  | 40.9  | 40.9  | 41.7  | 42.2  | 41.7  | 41.2  | 40.7  | 39.9  | 39.4   | 38.6  | 38.6   |
| 40°    | 36.2  | 36.2  | 37.0  | 37.6  | 37.0  | 36.5  | 36.2  | 35.7  | 35.5   | 34.9  | 34.9   |
| 42.5°  | 32.1  | 32.1  | 32.9  | 33.4  | 33.4  | 33.1  | 32.6  | 32.1  | 31.6   | 31.0  | 31.3   |
| 45°    | 26.9  | 26.6  | 27.9  | 28.9  | 28.4  | 27.9  | 27.9  | 27.6  | 27.6   | 27.4  | 27.6   |
| 47.5°  | 22.2  | 21.9  | 22.9  | 24.0  | 23.7  | 23.2  | 23.2  | 23.2  | 23.2   | 23.2  | 23.5   |
| 50°    | 18.5  | 18.0  | 19.0  | 19.8  | 19.6  | 19.0  | 19.0  | 19.3  | 19.3   | 19.3  | 19.6   |
| 52.5°  | 15.9  | 15.4  | 16.2  | 16.7  | 16.4  | 16.2  | 16.2  | 16.4  | 16.4   | 16.4  | 16.7   |
| 55°    | 14.1  | 13.6  | 14.3  | 14.9  | 14.6  | 14.1  | 14.3  | 14.3  | 14.6   | 14.6  | 14.6   |
| 57.5°  | 12.5  | 11.7  | 12.3  | 12.8  | 12.8  | 12.5  | 12.8  | 12.8  | 13.0   | 13.0  | 13.0   |
| 60°    | 11.5  | 10.7  | 11.2  | 11.5  | 11.5  | 11.2  | 11.5  | 11.5  | 11.7   | 11.7  | 11.7   |
| 62.5°  | 10.2  | 9.4   | 9.9   | 10.2  | 10.2  | 9.9   | 10.2  | 10.2  | 10.4   | 10.4  | 10.4   |
| 65°    | 9.1   | 8.3   | 8.6   | 8.9   | 8.9   | 8.9   | 9.1   | 9.1   | 9.4    | 9.4   | 9.4    |
| 67.5°  | 8.6   | 7.6   | 7.8   | 8.1   | 8.1   | 8.1   | 8.3   | 8.3   | 8.6    | 8.6   | 8.9    |
| 70°    | 8.3   | 7.3   | 7.6   | 7.6   | 7.8   | 7.8   | 7.8   | 8.1   | 8.1    | 8.1   | 8.1    |
| 72.5°  | 8.1   | 7.0   | 7.0   | 7.0   | 7.3   | 7.3   | 7.3   | 7.6   | 7.6    | 7.6   | 7.6    |
| 75°    | 8.1   | 7.0   | 6.8   | 6.5   | 6.8   | 6.8   | 6.8   | 7.0   | 7.0    | 7.0   | 7.0    |
| 77.5°  | 7.0   | 5.7   | 5.2   | 4.4   | 5.2   | 5.7   | 6.0   | 6.0   | 6.3    | 6.3   | 6.3    |
| 80°    | 2.9   | 1.3   | 0.8   | 0.0   | 0.3   | 0.5   | 0.8   | 1.0   | 1.3    | 1.6   | 1.8    |
| 82.5°  | 1.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 85°    | 0.8   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |



REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85° | 87.5° | 90° | 92.5° | 95° | 97.5° | 100° | 102.5° | 105° | 107.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|------|--------|------|--------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 110°  | 112.5° | 115°  | 117.5° | 120°  | 122.5° | 125°  | 127.5° | 130°  | 132.5° | 135°  |
|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0°     | 551.3 | 551.3  | 551.3 | 551.3  | 551.3 | 551.3  | 551.3 | 551.3  | 551.3 | 551.3  | 551.3 |
| 2.5°   | 516.9 | 503.8  | 490.8 | 497.1  | 503.3 | 509.6  | 515.8 | 515.3  | 514.5 | 514.0  | 513.2 |
| 5°     | 526.5 | 525.8  | 525.0 | 521.3  | 517.9 | 514.3  | 510.6 | 509.8  | 508.8 | 508.0  | 507.0 |
| 7.5°   | 442.8 | 444.1  | 445.7 | 441.5  | 437.3 | 433.2  | 429.0 | 418.3  | 407.6 | 396.7  | 386.0 |
| 10°    | 331.7 | 325.5  | 319.5 | 318.9  | 318.4 | 317.9  | 317.4 | 316.3  | 315.3 | 314.0  | 312.9 |
| 12.5°  | 234.4 | 238.1  | 241.8 | 240.4  | 239.1 | 237.6  | 236.3 | 238.1  | 240.2 | 242.0  | 243.8 |
| 15°    | 142.9 | 145.3  | 147.3 | 152.0  | 156.7 | 161.4  | 166.1 | 167.9  | 170.0 | 171.9  | 173.7 |
| 17.5°  | 93.1  | 93.4   | 93.9  | 99.1   | 104.1 | 109.3  | 114.2 | 117.6  | 121.0 | 124.1  | 127.5 |
| 20°    | 75.9  | 75.1   | 74.3  | 77.2   | 80.1  | 82.9   | 85.8  | 88.9   | 92.1  | 95.2   | 98.3  |
| 22.5°  | 67.5  | 67.0   | 66.5  | 67.5   | 68.6  | 69.4   | 70.4  | 72.8   | 75.4  | 77.7   | 80.1  |
| 25°    | 62.1  | 61.5   | 61.3  | 61.8   | 62.3  | 62.9   | 63.4  | 64.7   | 66.0  | 67.3   | 68.6  |
| 27.5°  | 55.8  | 56.1   | 56.1  | 56.6   | 56.9  | 57.4   | 57.6  | 58.2   | 58.9  | 59.5   | 60.0  |
| 30°    | 51.1  | 51.6   | 51.9  | 52.4   | 52.7  | 53.2   | 53.5  | 53.2   | 52.9  | 52.7   | 52.4  |
| 32.5°  | 46.7  | 46.4   | 46.4  | 46.9   | 47.2  | 47.7   | 48.0  | 48.5   | 49.0  | 49.3   | 49.8  |
| 35°    | 42.2  | 42.5   | 42.5  | 42.5   | 42.8  | 42.8   | 42.8  | 43.3   | 44.1  | 44.6   | 45.1  |
| 37.5°  | 38.3  | 38.3   | 38.1  | 38.9   | 39.4  | 40.2   | 40.7  | 41.2   | 42.0  | 42.5   | 43.0  |
| 40°    | 34.9  | 34.9   | 34.9  | 35.5   | 36.0  | 36.2   | 36.8  | 38.1   | 39.4  | 40.7   | 42.0  |
| 42.5°  | 31.3  | 31.6   | 31.6  | 32.1   | 32.6  | 32.9   | 33.4  | 34.4   | 35.2  | 36.2   | 37.0  |
| 45°    | 27.9  | 28.2   | 28.4  | 28.9   | 29.2  | 29.7   | 30.0  | 30.5   | 30.8  | 31.3   | 31.6  |
| 47.5°  | 24.0  | 24.3   | 24.5  | 25.0   | 25.3  | 25.8   | 26.1  | 25.8   | 25.8  | 25.6   | 25.3  |
| 50°    | 20.1  | 20.3   | 20.6  | 21.4   | 21.9  | 22.7   | 23.2  | 22.7   | 22.2  | 21.4   | 20.9  |
| 52.5°  | 17.0  | 17.0   | 17.2  | 17.7   | 18.3  | 18.5   | 19.0  | 18.8   | 18.5  | 18.3   | 18.0  |
| 55°    | 14.6  | 14.6   | 14.6  | 14.9   | 15.1  | 15.4   | 15.6  | 15.9   | 15.9  | 16.2   | 16.2  |
| 57.5°  | 13.0  | 12.8   | 12.8  | 13.0   | 13.3  | 13.3   | 13.6  | 13.8   | 13.8  | 14.1   | 14.1  |
| 60°    | 11.7  | 11.5   | 11.5  | 11.7   | 12.0  | 12.3   | 12.5  | 12.5   | 12.5  | 12.3   | 12.3  |
| 62.5°  | 10.4  | 10.4   | 10.4  | 10.7   | 10.7  | 11.0   | 11.0  | 11.0   | 11.2  | 11.2   | 11.2  |
| 65°    | 9.6   | 9.6    | 9.6   | 9.6    | 9.6   | 9.4    | 9.4   | 9.6    | 9.6   | 9.9    | 9.9   |
| 67.5°  | 8.9   | 9.1    | 9.1   | 8.9    | 8.6   | 8.3    | 8.1   | 8.3    | 8.3   | 8.6    | 8.6   |
| 70°    | 8.1   | 8.1    | 8.1   | 7.8    | 7.6   | 7.3    | 7.0   | 7.0    | 7.0   | 6.8    | 6.8   |
| 72.5°  | 7.6   | 7.3    | 7.3   | 7.0    | 6.5   | 6.3    | 5.7   | 5.5    | 5.5   | 5.2    | 5.0   |
| 75°    | 7.0   | 6.8    | 6.8   | 6.3    | 5.7   | 5.2    | 4.7   | 4.4    | 3.9   | 3.7    | 3.1   |
| 77.5°  | 6.3   | 6.3    | 6.3   | 5.5    | 5.0   | 4.2    | 3.4   | 2.9    | 2.3   | 1.6    | 1.0   |
| 80°    | 2.1   | 2.3    | 2.6   | 2.3    | 2.3   | 2.1    | 1.8   | 1.3    | 1.0   | 0.5    | 0.0   |
| 82.5°  | 0.3   | 0.3    | 0.3   | 0.3    | 0.3   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 85°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 87.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° | 135° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |





REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140°  | 142.5° | 145°  | 147.5° | 150°  | 152.5° | 155°  | 157.5° | 160°  | 162.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0°     | 551.3  | 551.3 | 551.3  | 551.3 | 551.3  | 551.3 | 551.3  | 551.3 | 551.3  | 551.3 | 551.3  |
| 2.5°   | 516.1  | 519.0 | 521.8  | 524.7 | 525.0  | 525.2 | 525.5  | 525.8 | 519.2  | 512.5 | 505.9  |
| 5°     | 512.2  | 517.7 | 522.9  | 528.1 | 525.2  | 522.4 | 519.5  | 516.6 | 516.4  | 516.4 | 516.1  |
| 7.5°   | 386.8  | 387.3 | 388.1  | 388.6 | 389.6  | 390.7 | 391.4  | 392.5 | 396.7  | 400.8 | 404.7  |
| 10°    | 309.6  | 306.2 | 302.5  | 299.1 | 296.5  | 293.6 | 291.0  | 288.2 | 290.3  | 292.6 | 294.7  |
| 12.5°  | 241.0  | 238.1 | 235.0  | 232.1 | 231.1  | 230.0 | 228.7  | 227.7 | 234.4  | 241.2 | 247.7  |
| 15°    | 173.2  | 172.6 | 171.9  | 171.3 | 174.7  | 178.1 | 181.5  | 184.9 | 190.6  | 196.1 | 201.9  |
| 17.5°  | 128.8  | 130.1 | 131.4  | 132.7 | 134.8  | 136.9 | 138.7  | 140.8 | 145.0  | 149.4 | 153.6  |
| 20°    | 99.9   | 101.7 | 103.3  | 104.8 | 104.3  | 103.8 | 103.0  | 102.5 | 105.9  | 109.3 | 112.4  |
| 22.5°  | 81.6   | 82.9  | 84.5   | 85.8  | 86.1   | 86.3  | 86.6   | 86.8  | 88.9   | 90.8  | 92.8   |
| 25°    | 69.9   | 71.5  | 72.8   | 74.1  | 74.3   | 74.6  | 74.8   | 75.1  | 77.7   | 80.3  | 82.7   |
| 27.5°  | 61.8   | 63.4  | 65.2   | 66.8  | 67.3   | 67.8  | 68.3   | 68.8  | 70.4   | 71.7  | 73.3   |
| 30°    | 54.5   | 56.6  | 58.7   | 60.8  | 61.5   | 62.3  | 63.1   | 63.9  | 65.5   | 67.3  | 68.8   |
| 32.5°  | 50.9   | 52.2  | 53.2   | 54.2  | 56.1   | 57.6  | 59.5   | 61.0  | 62.9   | 64.9  | 66.8   |
| 35°    | 46.7   | 48.0  | 49.5   | 50.9  | 52.2   | 53.5  | 54.5   | 55.8  | 56.9   | 57.9  | 58.7   |
| 37.5°  | 44.1   | 45.4  | 46.4   | 47.5  | 48.0   | 48.5  | 48.8   | 49.3  | 49.8   | 50.3  | 50.6   |
| 40°    | 42.0   | 41.7  | 41.7   | 41.5  | 42.0   | 42.8  | 43.3   | 43.8  | 45.4   | 46.7  | 48.2   |
| 42.5°  | 36.5   | 35.7  | 35.2   | 34.4  | 35.7   | 36.8  | 38.1   | 39.1  | 41.2   | 43.3  | 45.4   |
| 45°    | 31.0   | 30.5  | 29.7   | 29.2  | 31.0   | 32.9  | 34.7   | 36.5  | 38.9   | 40.9  | 43.3   |
| 47.5°  | 25.6   | 25.8  | 25.8   | 26.1  | 27.9   | 29.7  | 31.3   | 33.1  | 35.5   | 37.8  | 40.2   |
| 50°    | 21.4   | 21.9  | 22.4   | 22.9  | 24.8   | 26.3  | 28.2   | 29.7  | 32.3   | 34.7  | 37.3   |
| 52.5°  | 18.8   | 19.6  | 20.1   | 20.9  | 22.4   | 24.3  | 25.8   | 27.4  | 29.7   | 32.1  | 34.4   |
| 55°    | 17.0   | 18.0  | 18.8   | 19.6  | 20.9   | 22.2  | 23.5   | 24.8  | 27.1   | 29.5  | 31.6   |
| 57.5°  | 14.9   | 15.6  | 16.4   | 17.2  | 18.5   | 19.8  | 20.9   | 22.2  | 24.3   | 26.6  | 28.7   |
| 60°    | 13.0   | 13.6  | 14.3   | 14.9  | 15.9   | 17.2  | 18.3   | 19.3  | 21.4   | 23.5  | 25.3   |
| 62.5°  | 11.5   | 12.0  | 12.3   | 12.5  | 13.6   | 14.6  | 15.6   | 16.7  | 18.5   | 20.6  | 22.4   |
| 65°    | 10.2   | 10.4  | 10.4   | 10.7  | 11.5   | 12.5  | 13.3   | 14.1  | 16.2   | 18.0  | 20.1   |
| 67.5°  | 8.6    | 8.9   | 8.9    | 8.9   | 9.6    | 10.4  | 11.2   | 12.0  | 13.8   | 15.9  | 17.7   |
| 70°    | 6.8    | 7.0   | 7.0    | 7.0   | 7.8    | 8.9   | 9.6    | 10.4  | 12.0   | 13.6  | 15.1   |
| 72.5°  | 5.2    | 5.2   | 5.5    | 5.5   | 6.3    | 7.3   | 8.1    | 8.9   | 10.2   | 11.5  | 12.8   |
| 75°    | 3.4    | 3.7   | 3.7    | 3.9   | 4.7    | 5.7   | 6.5    | 7.3   | 8.6    | 9.9   | 11.0   |
| 77.5°  | 1.3    | 1.8   | 2.1    | 2.3   | 3.1    | 3.9   | 4.7    | 5.5   | 6.5    | 7.8   | 8.9    |
| 80°    | 0.0    | 0.3   | 0.3    | 0.3   | 0.8    | 1.0   | 1.6    | 1.8   | 2.6    | 3.7   | 4.4    |
| 82.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 85°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 87.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |



REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° | 162.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 165°  | 167.5° | 170°  | 172.5° | 175°  | 177.5° | 180°  | 182.5° | 185°  | 187.5° | 190°  |
|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0°     | 551.3 | 551.3  | 551.3 | 551.3  | 551.3 | 551.3  | 551.3 | 551.3  | 551.3 | 551.3  | 551.3 |
| 2.5°   | 499.2 | 513.5  | 527.8 | 542.2  | 556.5 | 574.3  | 592.0 | 594.6  | 597.2 | 594.1  | 591.2 |
| 5°     | 515.8 | 522.9  | 529.7 | 536.7  | 543.5 | 563.8  | 583.9 | 584.2  | 584.2 | 584.4  | 584.4 |
| 7.5°   | 408.9 | 414.9  | 420.9 | 426.7  | 432.6 | 445.9  | 459.3 | 464.2  | 468.9 | 467.9  | 466.8 |
| 10°    | 296.8 | 304.6  | 312.2 | 320.0  | 327.6 | 339.8  | 352.1 | 356.8  | 361.2 | 375.5  | 390.1 |
| 12.5°  | 254.5 | 262.1  | 269.7 | 277.0  | 284.5 | 297.0  | 309.6 | 318.7  | 327.6 | 336.4  | 345.3 |
| 15°    | 207.3 | 213.3  | 219.6 | 225.6  | 231.6 | 237.3  | 243.1 | 254.3  | 265.2 | 274.1  | 283.0 |
| 17.5°  | 157.8 | 160.4  | 162.7 | 165.3  | 167.7 | 170.3  | 172.9 | 177.6  | 182.0 | 189.9  | 197.4 |
| 20°    | 115.8 | 117.9  | 120.0 | 121.8  | 123.9 | 126.5  | 129.1 | 132.5  | 135.6 | 137.4  | 139.0 |
| 22.5°  | 94.7  | 97.8   | 100.9 | 103.8  | 106.9 | 108.7  | 110.6 | 111.6  | 112.7 | 113.4  | 114.2 |
| 25°    | 85.3  | 88.1   | 90.8  | 93.6   | 96.2  | 97.0   | 97.8  | 99.9   | 102.0 | 102.0  | 102.0 |
| 27.5°  | 74.6  | 78.5   | 82.7  | 86.6   | 90.5  | 91.5   | 92.3  | 93.1   | 93.6  | 92.6   | 91.3  |
| 30°    | 70.4  | 74.3   | 78.2  | 81.9   | 85.8  | 87.4   | 88.7  | 89.5   | 90.2  | 88.9   | 87.6  |
| 32.5°  | 68.6  | 72.2   | 75.6  | 79.3   | 82.7  | 84.8   | 86.6  | 88.7   | 90.5  | 90.8   | 91.3  |
| 35°    | 59.7  | 62.1   | 64.7  | 67.0   | 69.4  | 70.4   | 71.5  | 72.2   | 72.8  | 72.8   | 72.8  |
| 37.5°  | 51.1  | 54.2   | 57.6  | 60.8   | 63.9  | 66.2   | 68.6  | 68.8   | 68.8  | 69.4   | 70.2  |
| 40°    | 49.5  | 52.7   | 55.8  | 58.7   | 61.8  | 64.4   | 66.8  | 67.0   | 67.3  | 67.8   | 68.3  |
| 42.5°  | 47.5  | 50.9   | 54.2  | 57.6   | 61.0  | 63.6   | 66.0  | 66.0   | 65.7  | 66.5   | 67.0  |
| 45°    | 45.4  | 48.8   | 51.9  | 55.3   | 58.4  | 61.8   | 64.9  | 64.2   | 63.1  | 64.4   | 65.5  |
| 47.5°  | 42.5  | 46.2   | 49.8  | 53.2   | 56.9  | 60.0   | 62.9  | 62.3   | 61.5  | 62.9   | 64.2  |
| 50°    | 39.6  | 43.3   | 46.9  | 50.6   | 54.2  | 57.6   | 60.8  | 60.2   | 59.7  | 61.3   | 62.6  |
| 52.5°  | 36.8  | 40.4   | 44.3  | 48.0   | 51.6  | 54.5   | 57.1  | 56.9   | 56.6  | 58.2   | 60.0  |
| 55°    | 33.9  | 37.3   | 40.9  | 44.3   | 47.7  | 50.9   | 53.7  | 53.2   | 52.7  | 54.0   | 55.3  |
| 57.5°  | 30.8  | 34.2   | 37.3  | 40.7   | 43.8  | 46.4   | 48.8  | 48.0   | 47.2  | 48.8   | 50.3  |
| 60°    | 27.4  | 30.5   | 33.6  | 36.5   | 39.6  | 41.7   | 43.6  | 43.0   | 42.2  | 43.8   | 45.4  |
| 62.5°  | 24.3  | 27.1   | 30.0  | 32.6   | 35.5  | 37.0   | 38.6  | 38.1   | 37.6  | 39.1   | 40.9  |
| 65°    | 21.9  | 24.3   | 26.3  | 28.7   | 30.8  | 32.3   | 33.9  | 33.1   | 32.3  | 34.2   | 35.7  |
| 67.5°  | 19.6  | 21.4   | 23.5  | 25.3   | 27.1  | 28.4   | 29.7  | 29.2   | 28.4  | 29.7   | 31.0  |
| 70°    | 16.7  | 18.5   | 20.3  | 21.9   | 23.7  | 25.0   | 26.3  | 25.6   | 24.5  | 25.8   | 27.1  |
| 72.5°  | 14.1  | 15.6   | 17.2  | 18.5   | 20.1  | 21.1   | 22.2  | 21.4   | 20.6  | 21.6   | 22.7  |
| 75°    | 12.3  | 13.6   | 14.9  | 15.9   | 17.2  | 17.7   | 18.3  | 18.0   | 17.5  | 18.5   | 19.3  |
| 77.5°  | 9.9   | 11.0   | 12.3  | 13.3   | 14.3  | 14.3   | 14.3  | 14.6   | 14.6  | 15.6   | 17.0  |
| 80°    | 5.2   | 6.3    | 7.3   | 8.1    | 9.1   | 9.1    | 8.9   | 9.4    | 9.6   | 11.0   | 12.3  |
| 82.5°  | 0.0   | 0.8    | 1.6   | 2.3    | 3.1   | 2.9    | 2.3   | 2.6    | 2.6   | 3.1    | 3.7   |
| 85°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.3    | 0.5   |
| 87.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° | 190° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195°  | 197.5° | 200°  | 202.5° | 205°  | 207.5° | 210°  | 212.5° | 215°  | 217.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0°     | 551.3  | 551.3 | 551.3  | 551.3 | 551.3  | 551.3 | 551.3  | 551.3 | 551.3  | 551.3 | 551.3  |
| 2.5°   | 588.1  | 585.0 | 582.9  | 581.0 | 579.0  | 576.9 | 579.5  | 582.1 | 584.4  | 587.0 | 594.9  |
| 5°     | 584.7  | 584.7 | 582.9  | 581.0 | 579.2  | 577.4 | 581.3  | 585.0 | 588.9  | 592.5 | 592.3  |
| 7.5°   | 465.5  | 464.5 | 475.4  | 486.1 | 497.1  | 507.8 | 510.6  | 513.5 | 516.1  | 519.0 | 518.2  |
| 10°    | 404.5  | 418.8 | 423.5  | 428.2 | 432.9  | 437.6 | 443.3  | 449.1 | 454.8  | 460.6 | 462.6  |
| 12.5°  | 354.2  | 363.0 | 378.1  | 393.0 | 408.1  | 423.0 | 430.6  | 438.4 | 445.9  | 453.5 | 468.4  |
| 15°    | 291.8  | 300.7 | 313.7  | 326.8 | 339.8  | 352.8 | 364.8  | 377.1 | 389.1  | 401.1 | 419.1  |
| 17.5°  | 205.2  | 212.8 | 222.7  | 232.6 | 242.3  | 252.2 | 270.7  | 289.2 | 307.7  | 326.2 | 345.3  |
| 20°    | 140.8  | 142.4 | 147.1  | 152.0 | 156.7  | 161.4 | 178.1  | 195.1 | 211.8  | 228.5 | 253.5  |
| 22.5°  | 114.7  | 115.5 | 117.9  | 120.2 | 122.3  | 124.7 | 133.3  | 142.1 | 150.7  | 159.3 | 179.7  |
| 25°    | 101.7  | 101.7 | 103.3  | 104.8 | 106.4  | 108.0 | 112.7  | 117.4 | 121.8  | 126.5 | 139.5  |
| 27.5°  | 90.2   | 88.9  | 91.3   | 93.6  | 96.0   | 98.3  | 101.7  | 105.4 | 108.7  | 112.1 | 121.0  |
| 30°    | 86.3   | 85.0  | 87.9   | 90.8  | 93.6   | 96.5  | 99.9   | 103.3 | 106.4  | 109.8 | 115.8  |
| 32.5°  | 91.5   | 91.8  | 92.8   | 93.9  | 94.7   | 95.7  | 97.3   | 99.1  | 100.7  | 102.2 | 107.4  |
| 35°    | 72.8   | 72.8  | 74.6   | 76.4  | 78.0   | 79.8  | 82.7   | 85.5  | 88.4   | 91.3  | 96.8   |
| 37.5°  | 70.7   | 71.2  | 72.8   | 74.6  | 76.2   | 77.7  | 81.4   | 85.3  | 88.9   | 92.6  | 97.0   |
| 40°    | 68.6   | 69.1  | 71.2   | 73.3  | 75.4   | 77.5  | 81.1   | 84.5  | 88.1   | 91.5  | 95.7   |
| 42.5°  | 67.8   | 68.3  | 70.9   | 73.8  | 76.4   | 79.0  | 82.1   | 85.3  | 88.1   | 91.3  | 97.0   |
| 45°    | 66.8   | 67.8  | 70.9   | 74.3  | 77.5   | 80.6  | 83.5   | 86.3  | 89.2   | 92.1  | 99.1   |
| 47.5°  | 65.2   | 66.5  | 70.2   | 73.5  | 77.2   | 80.6  | 86.1   | 91.8  | 97.3   | 102.8 | 106.1  |
| 50°    | 64.2   | 65.5  | 69.4   | 73.3  | 77.2   | 81.1  | 90.0   | 98.8  | 107.4  | 116.3 | 114.5  |
| 52.5°  | 61.5   | 63.1  | 68.1   | 73.0  | 78.0   | 82.9  | 90.8   | 98.6  | 106.4  | 114.2 | 110.6  |
| 55°    | 56.6   | 57.9  | 63.6   | 69.4  | 74.8   | 80.6  | 86.3   | 92.1  | 97.5   | 103.3 | 99.1   |
| 57.5°  | 51.6   | 53.2  | 58.7   | 64.2  | 69.4   | 74.8  | 77.7   | 80.6  | 83.5   | 86.3  | 84.8   |
| 60°    | 46.9   | 48.5  | 55.8   | 63.1  | 70.4   | 77.7  | 75.1   | 72.5  | 69.6   | 67.0  | 68.8   |
| 62.5°  | 42.5   | 44.1  | 51.1   | 57.9  | 64.9   | 71.7  | 68.1   | 64.4  | 60.8   | 57.1  | 60.0   |
| 65°    | 37.6   | 39.1  | 41.7   | 44.6  | 47.2   | 49.8  | 49.5   | 49.0  | 48.8   | 48.2  | 51.4   |
| 67.5°  | 32.3   | 33.6  | 34.9   | 36.5  | 37.8   | 39.1  | 39.9   | 40.9  | 41.7   | 42.5  | 45.1   |
| 70°    | 28.2   | 29.5  | 31.0   | 32.3  | 33.9   | 35.2  | 35.7   | 36.2  | 36.5   | 37.0  | 39.4   |
| 72.5°  | 23.5   | 24.5  | 26.6   | 28.7  | 30.5   | 32.6  | 32.9   | 32.9  | 33.1   | 33.1  | 34.9   |
| 75°    | 20.3   | 21.1  | 22.7   | 24.3  | 25.6   | 27.1  | 27.9   | 28.7  | 29.2   | 30.0  | 31.0   |
| 77.5°  | 18.0   | 19.0  | 19.6   | 19.8  | 20.3   | 20.6  | 21.1   | 21.6  | 22.2   | 22.7  | 22.9   |
| 80°    | 13.3   | 14.6  | 15.1   | 15.4  | 15.9   | 16.2  | 16.2   | 15.9  | 15.9   | 15.6  | 15.9   |
| 82.5°  | 4.2    | 4.7   | 5.5    | 6.3   | 7.0    | 7.8   | 8.1    | 8.3   | 8.3    | 8.6   | 8.3    |
| 85°    | 0.8    | 1.0   | 1.6    | 2.1   | 2.3    | 2.9   | 2.6    | 2.1   | 1.8    | 1.3   | 1.0    |
| 87.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |



REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° | 217.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 220°  | 222.5° | 225°  | 227.5° | 230°  | 232.5° | 235°  | 237.5° | 240°  | 242.5° | 245°  |
|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0°     | 551.3 | 551.3  | 551.3 | 551.3  | 551.3 | 551.3  | 551.3 | 551.3  | 551.3 | 551.3  | 551.3 |
| 2.5°   | 602.7 | 610.2  | 618.1 | 614.9  | 611.8 | 608.7  | 605.6 | 606.1  | 606.9 | 607.4  | 607.9 |
| 5°     | 592.0 | 591.5  | 591.2 | 600.1  | 609.2 | 618.1  | 626.9 | 636.6  | 646.5 | 656.1  | 665.8 |
| 7.5°   | 517.4 | 516.4  | 515.6 | 527.1  | 538.5 | 550.0  | 561.5 | 574.8  | 588.3 | 601.6  | 614.9 |
| 10°    | 464.7 | 466.8  | 468.9 | 473.6  | 478.5 | 483.2  | 487.9 | 500.7  | 513.5 | 526.0  | 538.8 |
| 12.5°  | 483.2 | 497.8  | 512.7 | 515.6  | 518.2 | 521.1  | 523.7 | 525.5  | 527.3 | 529.1  | 531.0 |
| 15°    | 437.3 | 455.3  | 473.3 | 480.9  | 488.2 | 495.8  | 503.1 | 522.4  | 541.4 | 560.7  | 579.7 |
| 17.5°  | 364.3 | 383.1  | 402.1 | 424.8  | 447.5 | 470.2  | 492.9 | 513.8  | 534.6 | 555.5  | 576.3 |
| 20°    | 278.8 | 303.8  | 328.9 | 357.5  | 386.5 | 415.2  | 443.9 | 464.7  | 485.3 | 506.2  | 526.8 |
| 22.5°  | 200.3 | 220.6  | 241.0 | 275.7  | 310.1 | 344.8  | 379.2 | 415.4  | 451.9 | 488.2  | 524.4 |
| 25°    | 152.6 | 165.3  | 178.4 | 212.5  | 246.7 | 280.6  | 314.8 | 364.6  | 414.4 | 464.2  | 514.0 |
| 27.5°  | 129.6 | 138.5  | 147.1 | 177.9  | 208.6 | 239.1  | 269.9 | 329.1  | 388.3 | 447.5  | 506.7 |
| 30°    | 122.0 | 128.0  | 134.0 | 160.1  | 186.5 | 212.5  | 238.6 | 298.6  | 358.6 | 418.6  | 478.5 |
| 32.5°  | 112.7 | 117.6  | 122.8 | 145.8  | 168.7 | 191.4  | 214.4 | 273.0  | 331.7 | 390.1  | 448.8 |
| 35°    | 102.0 | 107.4  | 112.7 | 135.6  | 158.6 | 181.2  | 204.2 | 265.0  | 325.7 | 386.5  | 447.3 |
| 37.5°  | 101.2 | 105.6  | 109.8 | 136.4  | 163.3 | 189.9  | 216.5 | 277.2  | 338.0 | 398.5  | 459.3 |
| 40°    | 100.1 | 104.3  | 108.5 | 135.6  | 162.5 | 189.6  | 216.5 | 280.1  | 343.7 | 407.4  | 471.0 |
| 42.5°  | 102.8 | 108.2  | 114.0 | 138.0  | 162.0 | 185.7  | 209.7 | 276.7  | 343.7 | 410.5  | 477.5 |
| 45°    | 106.4 | 113.4  | 120.5 | 142.4  | 164.3 | 186.2  | 208.1 | 280.9  | 353.6 | 426.1  | 498.9 |
| 47.5°  | 109.8 | 113.2  | 116.6 | 137.4  | 158.0 | 178.9  | 199.5 | 273.8  | 348.2 | 422.5  | 496.8 |
| 50°    | 112.9 | 111.1  | 109.3 | 132.2  | 155.2 | 177.9  | 200.8 | 271.7  | 342.4 | 413.4  | 484.0 |
| 52.5°  | 106.7 | 103.0  | 99.1  | 123.6  | 148.1 | 172.4  | 196.9 | 268.4  | 339.8 | 411.3  | 482.7 |
| 55°    | 94.9  | 90.8   | 86.6  | 110.8  | 134.8 | 159.1  | 183.1 | 254.3  | 325.5 | 396.7  | 467.9 |
| 57.5°  | 82.9  | 81.4   | 79.5  | 98.1   | 116.6 | 134.8  | 153.3 | 232.4  | 311.6 | 390.7  | 469.7 |
| 60°    | 70.7  | 72.2   | 74.1  | 87.4   | 100.7 | 113.7  | 127.0 | 204.5  | 281.7 | 359.1  | 436.3 |
| 62.5°  | 62.6  | 65.5   | 68.1  | 79.3   | 90.8  | 102.0  | 113.2 | 186.2  | 259.2 | 332.2  | 405.3 |
| 65°    | 54.8  | 57.9   | 61.0  | 74.3   | 87.9  | 101.2  | 114.5 | 176.3  | 238.1 | 299.9  | 361.7 |
| 67.5°  | 47.7  | 50.1   | 52.7  | 70.2   | 87.6  | 105.1  | 122.6 | 173.2  | 223.5 | 274.1  | 324.4 |
| 70°    | 41.7  | 43.8   | 46.2  | 66.5   | 86.8  | 107.2  | 127.5 | 170.6  | 213.8 | 256.9  | 299.9 |
| 72.5°  | 36.8  | 38.6   | 40.4  | 61.0   | 81.6  | 102.2  | 122.8 | 161.2  | 199.2 | 237.6  | 275.7 |
| 75°    | 32.1  | 32.9   | 33.9  | 51.4   | 68.6  | 86.1   | 103.3 | 128.8  | 154.6 | 180.2  | 205.8 |
| 77.5°  | 23.2  | 23.2   | 23.5  | 28.7   | 33.6  | 38.9   | 43.8  | 59.7   | 75.6  | 91.3   | 107.2 |
| 80°    | 15.9  | 16.2   | 16.2  | 18.3   | 20.1  | 22.2   | 24.0  | 27.4   | 30.5  | 33.9   | 37.0  |
| 82.5°  | 8.1   | 7.6    | 7.3   | 9.4    | 11.5  | 13.6   | 15.6  | 16.4   | 17.0  | 17.7   | 18.3  |
| 85°    | 0.8   | 0.3    | 0.0   | 1.3    | 2.6   | 3.9    | 5.2   | 6.3    | 7.3   | 8.3    | 9.4   |
| 87.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° | 245° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |





REPORT NUMBER: P366941

CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°   | 252.5° | 255°   | 257.5° | 260°   | 262.5° | 265°   | 267.5° | 270°   | 272.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  |
| 2.5°   | 605.8  | 603.7  | 601.6  | 599.6  | 612.3  | 625.4  | 638.2  | 650.9  | 687.2  | 710.9  | 708.3  |
| 5°     | 675.2  | 684.6  | 694.0  | 703.3  | 718.5  | 733.9  | 749.0  | 764.1  | 817.8  | 850.7  | 855.4  |
| 7.5°   | 629.5  | 643.9  | 658.5  | 672.8  | 702.0  | 731.0  | 760.2  | 789.1  | 833.2  | 867.4  | 886.7  |
| 10°    | 555.2  | 571.7  | 587.8  | 604.2  | 637.1  | 670.2  | 703.1  | 735.9  | 785.5  | 832.7  | 857.0  |
| 12.5°  | 556.8  | 582.6  | 608.4  | 634.2  | 662.9  | 691.6  | 720.0  | 748.7  | 779.0  | 794.9  | 829.0  |
| 15°    | 600.1  | 620.4  | 640.8  | 661.1  | 698.7  | 736.2  | 773.5  | 811.1  | 829.0  | 867.4  | 907.3  |
| 17.5°  | 616.0  | 655.9  | 695.5  | 735.2  | 782.1  | 828.8  | 875.7  | 922.4  | 956.3  | 1009.5 | 1050.7 |
| 20°    | 586.5  | 646.2  | 705.7  | 765.4  | 829.8  | 894.2  | 958.7  | 1023.1 | 1060.1 | 1110.7 | 1174.3 |
| 22.5°  | 587.8  | 651.2  | 714.3  | 777.7  | 866.6  | 955.3  | 1044.2 | 1132.9 | 1232.2 | 1329.8 | 1360.8 |
| 25°    | 596.9  | 679.9  | 762.5  | 845.5  | 948.2  | 1051.0 | 1153.7 | 1256.5 | 1376.4 | 1478.9 | 1520.1 |
| 27.5°  | 600.1  | 693.4  | 786.5  | 879.9  | 1025.9 | 1172.0 | 1318.0 | 1464.1 | 1607.2 | 1723.0 | 1767.1 |
| 30°    | 592.5  | 706.7  | 820.7  | 934.7  | 1113.8 | 1293.0 | 1472.2 | 1651.3 | 1787.2 | 1922.0 | 1976.8 |
| 32.5°  | 594.3  | 739.9  | 885.4  | 1030.9 | 1241.9 | 1453.1 | 1664.1 | 1875.1 | 1961.9 | 2083.4 | 2179.9 |
| 35°    | 606.9  | 766.5  | 925.8  | 1085.4 | 1318.8 | 1552.2 | 1785.6 | 2019.0 | 2161.4 | 2289.7 | 2371.6 |
| 37.5°  | 636.1  | 812.9  | 989.4  | 1166.3 | 1453.1 | 1740.2 | 2027.1 | 2314.0 | 2534.4 | 2754.7 | 2792.3 |
| 40°    | 657.7  | 844.4  | 1031.2 | 1217.9 | 1550.9 | 1883.9 | 2217.0 | 2550.0 | 2799.3 | 3038.5 | 3064.0 |
| 42.5°  | 682.2  | 886.7  | 1091.4 | 1295.9 | 1668.3 | 2040.7 | 2413.1 | 2785.5 | 3074.2 | 3318.0 | 3335.0 |
| 45°    | 709.1  | 919.5  | 1129.7 | 1339.9 | 1730.1 | 2120.0 | 2510.1 | 2900.0 | 3237.2 | 3520.4 | 3456.5 |
| 47.5°  | 721.9  | 946.9  | 1172.0 | 1397.0 | 1815.4 | 2233.4 | 2651.7 | 3069.8 | 3372.3 | 3622.1 | 3547.5 |
| 50°    | 731.8  | 979.3  | 1227.0 | 1474.5 | 1913.2 | 2351.8 | 2790.4 | 3229.1 | 3532.4 | 3762.9 | 3646.1 |
| 52.5°  | 759.7  | 1036.4 | 1313.3 | 1590.0 | 2056.6 | 2522.9 | 2989.4 | 3455.7 | 3749.1 | 3960.9 | 3797.1 |
| 55°    | 786.8  | 1105.5 | 1424.4 | 1743.1 | 2244.9 | 2746.9 | 3248.7 | 3750.4 | 4042.5 | 4224.0 | 4001.6 |
| 57.5°  | 821.0  | 1172.5 | 1523.8 | 1875.1 | 2411.8 | 2948.5 | 3484.9 | 4021.6 | 4307.2 | 4507.7 | 4276.7 |
| 60°    | 812.1  | 1187.6 | 1563.4 | 1939.0 | 2485.6 | 3032.2 | 3578.8 | 4125.4 | 4464.7 | 4711.2 | 4554.4 |
| 62.5°  | 777.7  | 1150.1 | 1522.2 | 1894.6 | 2431.6 | 2968.3 | 3505.3 | 4042.0 | 4448.5 | 4782.4 | 4729.7 |
| 65°    | 708.0  | 1054.1 | 1400.4 | 1746.5 | 2259.2 | 2772.2 | 3284.9 | 3797.6 | 4299.4 | 4724.2 | 4743.0 |
| 67.5°  | 616.5  | 908.6  | 1200.4 | 1492.5 | 1970.8 | 2449.1 | 2927.1 | 3405.4 | 3997.6 | 4493.1 | 4549.0 |
| 70°    | 519.5  | 738.8  | 958.4  | 1177.7 | 1598.6 | 2019.6 | 2440.2 | 2861.1 | 3476.8 | 3975.5 | 4080.8 |
| 72.5°  | 416.5  | 557.6  | 698.4  | 839.2  | 1143.0 | 1446.6 | 1750.4 | 2054.0 | 2595.6 | 2982.6 | 3166.5 |
| 75°    | 269.9  | 334.1  | 398.2  | 462.4  | 664.8  | 866.9  | 1069.2 | 1271.3 | 1631.0 | 1916.0 | 2123.9 |
| 77.5°  | 120.2  | 133.3  | 146.0  | 159.1  | 315.3  | 471.5  | 627.7  | 783.9  | 940.1  | 1112.3 | 1161.0 |
| 80°    | 43.0   | 48.8   | 54.8   | 60.5   | 137.2  | 214.1  | 290.8  | 367.5  | 443.1  | 532.0  | 553.7  |
| 82.5°  | 18.0   | 18.0   | 17.7   | 17.5   | 44.9   | 72.2   | 99.6   | 127.0  | 146.8  | 168.7  | 172.9  |
| 85°    | 7.3    | 5.5    | 3.4    | 1.3    | 5.7    | 10.4   | 14.9   | 19.3   | 31.0   | 28.2   | 52.2   |
| 87.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° | 272.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P366941

CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 275°   | 277.5° | 280°   | 282.5° | 285°   | 287.5° | 290°   | 292.5° | 295°   | 297.5° | 300°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  |
| 2.5°   | 698.4  | 697.9  | 697.4  | 696.8  | 696.3  | 686.9  | 677.8  | 668.4  | 659.3  | 670.8  | 682.2  |
| 5°     | 847.8  | 861.4  | 874.9  | 888.8  | 902.3  | 906.2  | 910.2  | 914.1  | 918.0  | 926.3  | 934.7  |
| 7.5°   | 902.9  | 925.8  | 948.5  | 971.4  | 994.1  | 1015.3 | 1036.1 | 1057.2 | 1078.4 | 1073.1 | 1067.9 |
| 10°    | 883.8  | 925.3  | 966.7  | 1008.5 | 1049.9 | 1059.1 | 1068.2 | 1077.6 | 1086.7 | 1110.4 | 1134.2 |
| 12.5°  | 863.2  | 913.0  | 962.8  | 1012.6 | 1062.5 | 1090.1 | 1117.5 | 1145.1 | 1172.8 | 1196.8 | 1220.8 |
| 15°    | 961.0  | 992.8  | 1024.6 | 1056.7 | 1088.5 | 1112.8 | 1136.8 | 1161.0 | 1185.0 | 1201.7 | 1218.1 |
| 17.5°  | 1089.6 | 1105.2 | 1120.9 | 1136.8 | 1152.4 | 1171.5 | 1190.5 | 1209.5 | 1228.6 | 1238.5 | 1248.4 |
| 20°    | 1225.4 | 1232.2 | 1239.0 | 1245.8 | 1252.6 | 1237.4 | 1222.3 | 1207.2 | 1192.1 | 1201.5 | 1210.6 |
| 22.5°  | 1361.8 | 1364.2 | 1366.8 | 1369.1 | 1371.5 | 1336.3 | 1301.1 | 1265.9 | 1230.7 | 1215.8 | 1200.9 |
| 25°    | 1571.8 | 1554.6 | 1537.4 | 1520.1 | 1502.9 | 1461.2 | 1419.5 | 1377.8 | 1336.0 | 1299.3 | 1262.5 |
| 27.5°  | 1799.2 | 1740.8 | 1682.6 | 1624.2 | 1566.0 | 1524.3 | 1482.6 | 1440.9 | 1399.1 | 1343.8 | 1288.6 |
| 30°    | 2028.4 | 1934.3 | 1840.4 | 1746.2 | 1652.4 | 1602.8 | 1553.3 | 1503.5 | 1453.9 | 1398.6 | 1343.6 |
| 32.5°  | 2238.6 | 2125.4 | 2012.3 | 1898.8 | 1785.6 | 1702.2 | 1618.7 | 1535.3 | 1451.8 | 1413.2 | 1374.6 |
| 35°    | 2412.8 | 2279.0 | 2145.3 | 2011.2 | 1877.4 | 1794.8 | 1712.1 | 1629.4 | 1546.7 | 1489.4 | 1432.3 |
| 37.5°  | 2710.6 | 2560.2 | 2409.7 | 2259.2 | 2108.7 | 1995.8 | 1883.2 | 1770.2 | 1657.3 | 1619.0 | 1580.6 |
| 40°    | 2985.3 | 2795.7 | 2606.1 | 2416.5 | 2226.9 | 2132.2 | 2037.8 | 1943.1 | 1848.7 | 1785.9 | 1723.3 |
| 42.5°  | 3203.5 | 3003.8 | 2804.3 | 2604.5 | 2404.7 | 2311.1 | 2217.8 | 2124.1 | 2030.5 | 1988.5 | 1946.8 |
| 45°    | 3250.7 | 3062.5 | 2874.4 | 2686.1 | 2497.8 | 2443.3 | 2389.1 | 2334.6 | 2280.3 | 2251.4 | 2222.7 |
| 47.5°  | 3343.8 | 3139.6 | 2935.7 | 2731.5 | 2527.3 | 2502.8 | 2478.3 | 2453.5 | 2429.0 | 2442.8 | 2456.6 |
| 50°    | 3396.0 | 3187.6 | 2979.3 | 2770.9 | 2562.5 | 2569.6 | 2576.3 | 2583.4 | 2590.4 | 2688.5 | 2786.3 |
| 52.5°  | 3497.2 | 3286.7 | 3076.3 | 2865.8 | 2655.4 | 2699.7 | 2743.8 | 2788.1 | 2832.2 | 2967.3 | 3102.1 |
| 55°    | 3677.9 | 3471.1 | 3264.3 | 3057.2 | 2850.4 | 2908.8 | 2967.3 | 3025.9 | 3084.4 | 3227.8 | 3371.0 |
| 57.5°  | 3945.7 | 3740.5 | 3535.5 | 3330.3 | 3125.3 | 3183.5 | 3241.6 | 3299.8 | 3357.9 | 3487.5 | 3616.9 |
| 60°    | 4282.9 | 4072.2 | 3861.8 | 3651.1 | 3440.6 | 3462.5 | 3484.1 | 3506.1 | 3528.0 | 3667.2 | 3806.2 |
| 62.5°  | 4545.6 | 4351.8 | 4158.3 | 3964.5 | 3771.0 | 3746.8 | 3722.8 | 3698.5 | 3674.5 | 3780.4 | 3886.0 |
| 65°    | 4606.6 | 4470.2 | 4334.1 | 4197.7 | 4061.3 | 3986.7 | 3912.4 | 3837.8 | 3763.2 | 3806.0 | 3848.7 |
| 67.5°  | 4431.9 | 4339.8 | 4248.0 | 4155.9 | 4063.9 | 3908.2 | 3752.5 | 3596.5 | 3440.9 | 3418.2 | 3395.5 |
| 70°    | 4026.3 | 3976.0 | 3925.9 | 3875.6 | 3825.5 | 3585.6 | 3345.9 | 3106.0 | 2866.3 | 2808.7 | 2751.1 |
| 72.5°  | 3177.2 | 3208.5 | 3239.8 | 3271.3 | 3302.6 | 3045.8 | 2789.1 | 2532.3 | 2275.4 | 2202.4 | 2129.6 |
| 75°    | 2240.4 | 2346.6 | 2452.7 | 2558.9 | 2665.0 | 2430.8 | 2196.9 | 1962.7 | 1728.5 | 1658.4 | 1588.5 |
| 77.5°  | 1214.8 | 1413.7 | 1612.7 | 1811.7 | 2010.7 | 1817.4 | 1624.5 | 1431.2 | 1238.0 | 1189.2 | 1140.7 |
| 80°    | 575.8  | 690.6  | 805.1  | 919.8  | 1034.6 | 991.0  | 947.4  | 903.6  | 860.1  | 870.8  | 881.5  |
| 82.5°  | 176.6  | 259.5  | 342.4  | 425.3  | 508.3  | 514.8  | 521.1  | 527.6  | 534.1  | 550.3  | 566.2  |
| 85°    | 59.2   | 81.1   | 103.0  | 124.9  | 146.8  | 185.4  | 224.0  | 262.9  | 301.5  | 276.4  | 251.7  |
| 87.5°  | 0.0    | 0.8    | 1.3    | 2.1    | 2.6    | 8.1    | 13.6   | 19.0   | 24.5   | 21.1   | 18.0   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° | 300° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P366941

CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305°   | 307.5° | 310°   | 312.5° | 315°   | 317.5° | 320°   | 322.5° | 325°   | 327.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  |
| 2.5°   | 694.0  | 705.4  | 705.7  | 706.2  | 706.5  | 706.7  | 708.0  | 709.3  | 710.9  | 712.2  | 703.6  |
| 5°     | 943.3  | 951.6  | 936.2  | 920.8  | 905.2  | 889.8  | 903.6  | 917.5  | 931.3  | 945.1  | 939.1  |
| 7.5°   | 1062.5 | 1057.2 | 1055.4 | 1053.9 | 1052.0 | 1050.5 | 1055.7 | 1060.9 | 1066.1 | 1071.3 | 1070.8 |
| 10°    | 1157.9 | 1181.6 | 1187.4 | 1193.1 | 1199.1 | 1204.8 | 1192.9 | 1180.9 | 1168.9 | 1156.9 | 1151.9 |
| 12.5°  | 1244.7 | 1268.7 | 1287.8 | 1306.8 | 1326.1 | 1345.2 | 1327.9 | 1311.0 | 1293.8 | 1276.8 | 1260.7 |
| 15°    | 1234.8 | 1251.3 | 1266.9 | 1282.6 | 1298.2 | 1313.9 | 1308.1 | 1302.6 | 1296.9 | 1291.2 | 1288.6 |
| 17.5°  | 1258.6 | 1268.5 | 1264.8 | 1261.2 | 1257.3 | 1253.6 | 1251.8 | 1250.2 | 1248.4 | 1246.6 | 1240.3 |
| 20°    | 1220.0 | 1229.4 | 1227.0 | 1224.9 | 1222.6 | 1220.2 | 1218.7 | 1217.1 | 1215.5 | 1214.0 | 1209.0 |
| 22.5°  | 1186.1 | 1171.2 | 1167.3 | 1163.6 | 1159.7 | 1156.1 | 1156.6 | 1157.1 | 1157.4 | 1157.9 | 1180.3 |
| 25°    | 1225.7 | 1188.9 | 1174.6 | 1160.3 | 1145.6 | 1131.3 | 1137.8 | 1144.1 | 1150.6 | 1157.1 | 1189.5 |
| 27.5°  | 1233.0 | 1177.7 | 1154.8 | 1131.8 | 1108.9 | 1085.9 | 1109.4 | 1132.9 | 1156.3 | 1179.8 | 1232.2 |
| 30°    | 1288.3 | 1233.3 | 1201.2 | 1169.4 | 1137.3 | 1105.5 | 1135.5 | 1165.5 | 1195.5 | 1225.4 | 1282.3 |
| 32.5°  | 1335.8 | 1297.2 | 1274.2 | 1251.3 | 1228.3 | 1205.4 | 1206.7 | 1207.7 | 1209.0 | 1210.3 | 1290.4 |
| 35°    | 1374.9 | 1317.8 | 1296.9 | 1276.3 | 1255.4 | 1234.8 | 1265.9 | 1296.9 | 1327.9 | 1359.0 | 1431.0 |
| 37.5°  | 1542.3 | 1504.0 | 1465.6 | 1427.6 | 1389.2 | 1351.2 | 1375.9 | 1400.7 | 1425.7 | 1450.5 | 1530.1 |
| 40°    | 1660.4 | 1597.9 | 1587.9 | 1578.3 | 1568.4 | 1558.7 | 1571.5 | 1584.0 | 1596.8 | 1609.6 | 1679.2 |
| 42.5°  | 1904.8 | 1862.8 | 1836.0 | 1809.4 | 1782.5 | 1755.9 | 1766.1 | 1776.2 | 1786.7 | 1796.8 | 1862.8 |
| 45°    | 2193.8 | 2164.8 | 2147.1 | 2129.3 | 2111.4 | 2093.6 | 2078.2 | 2063.1 | 2047.7 | 2032.6 | 2099.6 |
| 47.5°  | 2470.5 | 2484.3 | 2523.4 | 2562.3 | 2601.4 | 2640.2 | 2608.4 | 2576.6 | 2544.5 | 2512.7 | 2513.0 |
| 50°    | 2884.3 | 2982.1 | 3001.9 | 3021.5 | 3041.3 | 3060.9 | 2993.1 | 2925.3 | 2857.2 | 2789.4 | 2781.3 |
| 52.5°  | 3237.2 | 3372.0 | 3379.0 | 3386.1 | 3393.4 | 3400.4 | 3373.1 | 3345.7 | 3318.0 | 3290.6 | 3217.9 |
| 55°    | 3514.4 | 3657.6 | 3667.2 | 3676.6 | 3686.3 | 3695.6 | 3671.7 | 3647.9 | 3623.9 | 3599.9 | 3526.4 |
| 57.5°  | 3746.5 | 3875.9 | 3881.6 | 3887.1 | 3892.8 | 3898.5 | 3900.4 | 3902.2 | 3904.3 | 3906.1 | 3806.7 |
| 60°    | 3945.5 | 4084.7 | 4073.3 | 4062.1 | 4050.6 | 4039.4 | 4022.2 | 4004.9 | 3987.7 | 3970.5 | 3906.4 |
| 62.5°  | 3991.9 | 4097.8 | 4080.1 | 4062.6 | 4044.8 | 4027.4 | 4012.8 | 3998.4 | 3983.8 | 3969.2 | 3928.3 |
| 65°    | 3891.5 | 3934.3 | 3916.0 | 3897.8 | 3879.2 | 3861.0 | 3851.6 | 3842.5 | 3833.1 | 3823.7 | 3818.5 |
| 67.5°  | 3372.5 | 3349.8 | 3371.5 | 3393.1 | 3414.8 | 3436.4 | 3465.9 | 3495.4 | 3525.1 | 3554.6 | 3537.3 |
| 70°    | 2693.2 | 2635.5 | 2659.5 | 2683.3 | 2707.3 | 2731.0 | 2775.6 | 2820.2 | 2865.0 | 2909.6 | 2897.6 |
| 72.5°  | 2056.6 | 1983.6 | 1987.0 | 1990.3 | 1994.0 | 1997.4 | 1996.1 | 1995.0 | 1993.7 | 1992.4 | 2013.3 |
| 75°    | 1518.3 | 1448.2 | 1415.0 | 1381.9 | 1348.8 | 1315.7 | 1307.6 | 1299.5 | 1291.4 | 1283.3 | 1322.2 |
| 77.5°  | 1091.9 | 1043.4 | 1020.7 | 998.3  | 975.6  | 953.2  | 964.7  | 976.1  | 987.9  | 999.3  | 1012.9 |
| 80°    | 892.4  | 903.1  | 885.6  | 868.4  | 851.0  | 833.5  | 846.5  | 859.3  | 872.3  | 885.4  | 845.0  |
| 82.5°  | 582.3  | 598.3  | 544.5  | 490.8  | 437.1  | 383.4  | 416.0  | 448.6  | 481.4  | 514.0  | 497.3  |
| 85°    | 226.6  | 201.9  | 172.1  | 142.7  | 112.9  | 83.2   | 108.2  | 133.3  | 158.3  | 183.3  | 200.0  |
| 87.5°  | 14.6   | 11.5   | 9.1    | 6.8    | 4.2    | 1.8    | 3.9    | 6.0    | 8.3    | 10.4   | 17.5   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305° | 307.5° | 310° | 312.5° | 315° | 317.5° | 320° | 322.5° | 325° | 327.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P366941

CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 330°   | 332.5° | 335°   | 337.5° | 340°   | 342.5° | 345°   | 347.5° | 350°   | 352.5° | 355°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  | 551.3  |
| 2.5°   | 695.3  | 686.7  | 678.3  | 661.9  | 645.5  | 629.0  | 612.6  | 635.5  | 658.5  | 681.4  | 704.4  |
| 5°     | 933.4  | 927.4  | 921.6  | 923.2  | 924.8  | 926.6  | 928.1  | 931.5  | 934.9  | 938.1  | 941.4  |
| 7.5°   | 1070.5 | 1070.0 | 1069.5 | 1057.5 | 1045.5 | 1033.2 | 1021.3 | 1027.2 | 1033.2 | 1039.2 | 1045.2 |
| 10°    | 1147.2 | 1142.3 | 1137.3 | 1111.0 | 1084.6 | 1058.0 | 1031.7 | 1020.2 | 1008.5 | 997.0  | 985.5  |
| 12.5°  | 1244.5 | 1228.1 | 1211.9 | 1183.7 | 1155.8 | 1127.7 | 1099.5 | 1089.1 | 1078.4 | 1067.9 | 1057.2 |
| 15°    | 1286.2 | 1283.6 | 1281.3 | 1261.2 | 1240.8 | 1220.8 | 1200.4 | 1164.7 | 1128.7 | 1093.0 | 1057.2 |
| 17.5°  | 1234.1 | 1227.5 | 1221.3 | 1253.1 | 1284.6 | 1316.5 | 1348.3 | 1311.2 | 1274.2 | 1237.2 | 1200.2 |
| 20°    | 1204.1 | 1199.1 | 1194.2 | 1253.4 | 1312.3 | 1371.5 | 1430.4 | 1414.0 | 1397.3 | 1380.9 | 1364.5 |
| 22.5°  | 1202.8 | 1225.4 | 1247.9 | 1299.8 | 1351.4 | 1403.3 | 1454.9 | 1483.4 | 1512.1 | 1540.5 | 1568.9 |
| 25°    | 1221.8 | 1254.4 | 1286.7 | 1372.8 | 1458.9 | 1545.2 | 1631.2 | 1663.8 | 1696.2 | 1728.8 | 1761.1 |
| 27.5°  | 1284.4 | 1336.8 | 1389.0 | 1464.1 | 1539.2 | 1614.5 | 1689.7 | 1760.9 | 1832.3 | 1903.5 | 1974.7 |
| 30°    | 1338.9 | 1395.7 | 1452.6 | 1542.0 | 1631.2 | 1720.7 | 1809.9 | 1899.1 | 1988.3 | 2077.4 | 2166.6 |
| 32.5°  | 1370.4 | 1450.8 | 1530.8 | 1639.6 | 1748.1 | 1856.8 | 1965.6 | 2063.4 | 2161.2 | 2258.7 | 2356.5 |
| 35°    | 1502.9 | 1575.2 | 1647.1 | 1767.4 | 1887.6 | 2008.1 | 2128.3 | 2249.3 | 2370.3 | 2491.1 | 2612.1 |
| 37.5°  | 1609.6 | 1689.4 | 1768.9 | 1900.4 | 2031.5 | 2163.0 | 2294.4 | 2461.6 | 2629.0 | 2796.2 | 2963.4 |
| 40°    | 1748.9 | 1818.5 | 1888.1 | 2011.2 | 2134.0 | 2257.1 | 2380.2 | 2592.2 | 2804.3 | 3016.0 | 3228.1 |
| 42.5°  | 1928.5 | 1994.5 | 2060.5 | 2192.2 | 2323.9 | 2455.6 | 2587.3 | 2822.0 | 3056.7 | 3291.2 | 3525.9 |
| 45°    | 2166.6 | 2233.9 | 2300.9 | 2405.8 | 2510.6 | 2615.5 | 2720.3 | 2969.9 | 3219.2 | 3468.8 | 3718.1 |
| 47.5°  | 2513.2 | 2513.5 | 2513.7 | 2589.4 | 2665.0 | 2740.9 | 2816.5 | 3067.9 | 3319.1 | 3570.5 | 3821.6 |
| 50°    | 2773.2 | 2764.9 | 2756.8 | 2795.9 | 2834.8 | 2873.9 | 2913.0 | 3144.3 | 3375.9 | 3607.2 | 3838.6 |
| 52.5°  | 3145.4 | 3072.6 | 3000.1 | 3023.3 | 3046.3 | 3069.5 | 3092.4 | 3288.3 | 3484.4 | 3680.3 | 3876.1 |
| 55°    | 3453.1 | 3379.6 | 3306.0 | 3297.4 | 3288.8 | 3280.2 | 3271.6 | 3451.8 | 3632.0 | 3812.2 | 3992.4 |
| 57.5°  | 3707.6 | 3608.3 | 3509.2 | 3489.4 | 3469.8 | 3450.0 | 3430.2 | 3620.3 | 3810.1 | 4000.2 | 4190.1 |
| 60°    | 3842.5 | 3778.3 | 3714.2 | 3701.4 | 3688.3 | 3675.6 | 3662.5 | 3818.5 | 3974.4 | 4130.4 | 4286.3 |
| 62.5°  | 3887.6 | 3846.6 | 3806.0 | 3830.0 | 3853.9 | 3878.2 | 3902.2 | 3970.8 | 4039.1 | 4107.7 | 4176.0 |
| 65°    | 3813.5 | 3808.3 | 3803.1 | 3852.4 | 3901.4 | 3950.7 | 4000.0 | 3983.0 | 3965.8 | 3948.9 | 3931.9 |
| 67.5°  | 3520.4 | 3503.2 | 3486.2 | 3594.5 | 3702.4 | 3810.7 | 3918.9 | 3836.7 | 3754.3 | 3672.2 | 3590.0 |
| 70°    | 2885.6 | 2873.4 | 2861.4 | 3017.3 | 3173.3 | 3329.5 | 3485.5 | 3385.8 | 3286.2 | 3186.6 | 3087.0 |
| 72.5°  | 2033.9 | 2054.8 | 2075.6 | 2259.5 | 2443.1 | 2626.9 | 2810.5 | 2710.1 | 2609.7 | 2509.3 | 2408.9 |
| 75°    | 1360.8 | 1399.7 | 1438.5 | 1627.8 | 1817.2 | 2006.8 | 2196.1 | 2078.2 | 1960.4 | 1842.5 | 1724.6 |
| 77.5°  | 1026.5 | 1040.0 | 1053.6 | 1173.3 | 1293.0 | 1413.0 | 1532.7 | 1435.4 | 1337.8 | 1240.6 | 1143.0 |
| 80°    | 804.5  | 763.9  | 723.4  | 762.8  | 802.2  | 841.6  | 880.9  | 822.8  | 764.6  | 706.7  | 648.6  |
| 82.5°  | 480.6  | 463.9  | 447.3  | 468.6  | 489.8  | 511.1  | 532.5  | 507.5  | 482.2  | 457.2  | 431.9  |
| 85°    | 216.5  | 233.1  | 249.6  | 271.2  | 292.6  | 314.3  | 335.9  | 301.0  | 266.0  | 231.1  | 196.1  |
| 87.5°  | 24.3   | 31.3   | 38.3   | 47.5   | 56.6   | 65.7   | 74.8   | 58.4   | 41.7   | 25.3   | 8.9    |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 330° | 332.5° | 335° | 337.5° | 340° | 342.5° | 345° | 347.5° | 350° | 352.5° | 355° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |





REPORT NUMBER: P366941  
 CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360°   |
|--------|--------|--------|
| 0°     | 551.3  | 551.3  |
| 2.5°   | 717.7  | 731.0  |
| 5°     | 941.2  | 940.7  |
| 7.5°   | 1029.6 | 1013.7 |
| 10°    | 970.9  | 956.3  |
| 12.5°  | 1019.9 | 982.7  |
| 15°    | 1029.1 | 1000.9 |
| 17.5°  | 1154.3 | 1108.1 |
| 20°    | 1305.3 | 1245.8 |
| 22.5°  | 1487.5 | 1405.9 |
| 25°    | 1664.1 | 1567.1 |
| 27.5°  | 1916.5 | 1858.1 |
| 30°    | 2107.7 | 2048.5 |
| 32.5°  | 2316.3 | 2276.2 |
| 35°    | 2572.2 | 2532.0 |
| 37.5°  | 2973.8 | 2984.0 |
| 40°    | 3234.3 | 3240.6 |
| 42.5°  | 3550.1 | 3574.4 |
| 45°    | 3745.2 | 3772.3 |
| 47.5°  | 3859.4 | 3897.2 |
| 50°    | 3899.6 | 3960.6 |
| 52.5°  | 3951.5 | 4026.6 |
| 55°    | 4076.1 | 4159.9 |
| 57.5°  | 4256.9 | 4323.6 |
| 60°    | 4289.5 | 4292.6 |
| 62.5°  | 4127.8 | 4079.5 |
| 65°    | 3880.5 | 3829.2 |
| 67.5°  | 3559.0 | 3527.7 |
| 70°    | 3045.8 | 3004.6 |
| 72.5°  | 2332.2 | 2255.6 |
| 75°    | 1629.7 | 1534.7 |
| 77.5°  | 1093.2 | 1043.4 |
| 80°    | 650.1  | 651.5  |
| 82.5°  | 443.9  | 455.6  |
| 85°    | 193.8  | 191.2  |
| 87.5°  | 6.3    | 3.4    |
| 90°    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    |



REPORT NUMBER: P366941  
CATALOG NUMBER: PMM-SA1C-750-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

(END OF REPORT)