

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P559835

Luminaire Tested: **SDL-PA1-100-730-U-T2U-HSS-A**

Issue Date: 7/26/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P559835  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/26/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: SDL-PA1-100-730-U-T2U-HSS-A  
Description: Springdale  
(1) 70 CRI, 3000K, 1200mA LIGHT ENGINE WITH 24 LEDS AND TYPE II U OPTICS,  
HOUSE SIDE SHIELD AND CLEARPANELS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6387.4 lumens  
Efficiency: N/A  
Efficacy: 68.1 lumens/watt  
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')  
IES Classification: Type II - Short  
BUG Rating: B1 - U3 - G2


Input Watts (W): 93.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P559835  
 CATALOG NUMBER: SDL-PA1-100-730-U-T2U-HSS-A

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 12.9 fc  
 Type II - Short - N/A

REPORT NUMBER: P559835  
CATALOG NUMBER: SDL-PA1-100-730-U-T2U-HSS-A

### Luminous Intensity Polar Plot



— Vertical Plane Through 67.5-Deg Lateral    - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P559835  
 CATALOG NUMBER: SDL-PA1-100-730-U-T2U-HSS-A


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	999.5	74.5	1074.0
	% Fixture	15.6	1.2	16.8
<b>Street Side</b>	Lumens	5234.3	79.2	5313.4
	% Fixture	81.9	1.2	83.2
<b>Total</b>	Lumens	6233.8	153.6	6387.4
	% Fixture	97.6	2.4	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	75.7	1.2
10°-20°	144.4	2.3
20°-30°	217.9	3.4
30°-40°	501.7	7.9
40°-50°	1118.3	17.5
50°-60°	1664.1	26.1
60°-70°	1484.1	23.2
70°-80°	833.1	13.0
80°-90°	194.5	3.0
90°-100°	106.8	1.7
100°-110°	24.6	0.4
110°-120°	9.6	0.2
120°-130°	6.4	0.1
130°-140°	3.3	0.1
140°-150°	1.6	0.0
150°-160°	1.3	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-90°	6233.8	97.6
0°-180°	6387.4	100.0

**Coefficient of Utilization**



REPORT NUMBER: P559835


CATALOG NUMBER: SDL-PA1-100-730-U-T2U-HSS-A

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	289.0	4.5			
FM (30°-60°)	2908.4	45.5			
FH (60°-80°)	1924.0	30.1			G2/5000
FVH (80°-90°)	112.9	1.8			G2/225
BL (0°-30°)	149.0	2.3	B1/500		
BM (30°-60°)	375.7	5.9	B1/1000		
BH (60°-80°)	393.3	6.2	B1/500		G1/500
BVH (80°-90°)	81.6	1.3			G1/100
UL (90°-100°)	106.8	1.7		U3/500	
UH (100°-180°)	46.9	0.7		U2/50	

**BUG Rating: B1-U3-G2**

Type II Short





REPORT NUMBER: P559835

CATALOG NUMBER: SDL-PA1-100-730-U-T2U-HSS-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	67.5°	75°	85°
0°	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3
2.5°	835.3	883.0	934.2	968.3	975.1	985.3	985.3	981.9	981.9	978.5	978.5
5°	811.4	808.0	811.4	818.3	814.9	814.9	814.9	951.2	961.5	968.3	968.3
7.5°	698.9	716.0	770.5	791.0	797.8	804.6	804.6	794.4	756.9	838.7	848.9
10°	760.3	756.9	756.9	763.7	712.6	692.1	623.9	613.7	613.7	641.0	729.6
12.5°	637.6	675.1	726.2	746.7	688.7	610.3	593.2	606.9	603.5	528.5	617.1
15°	722.8	722.8	716.0	702.3	542.1	606.9	511.4	511.4	583.0	627.3	705.8
17.5°	586.4	603.5	688.7	678.5	596.7	456.9	596.7	548.9	589.8	552.3	593.2
20°	719.4	716.0	719.4	548.9	606.9	627.3	596.7	535.3	487.5	641.0	709.2
22.5°	593.2	586.4	620.5	678.5	572.8	651.2	545.5	651.2	634.2	569.4	511.4
25°	767.1	763.7	770.5	600.1	671.7	583.0	671.7	583.0	610.3	729.6	746.7
27.5°	692.1	688.7	678.5	733.0	637.6	736.4	634.2	712.6	733.0	791.0	917.1
30°	975.1	961.5	927.4	736.4	750.1	709.2	750.1	876.2	944.4	1060.3	1097.8
32.5°	1421.7	1350.1	1125.1	975.1	794.4	906.9	848.9	1029.6	1094.4	1152.4	1183.1
35°	1837.7	1807.0	1643.3	1288.8	968.3	1002.4	958.1	1152.4	1189.9	1312.6	1305.8
37.5°	2407.1	2355.9	2103.6	1663.8	1217.2	1203.5	1091.0	1312.6	1339.9	1517.2	1483.1
40°	2833.2	2792.3	2594.6	2066.1	1547.9	1428.6	1275.1	1534.2	1503.6	1742.2	1694.5
42.5°	3242.4	3218.5	3065.1	2526.4	1912.7	1776.3	1466.1	1807.0	1800.2	2008.2	1967.2
45°	3573.1	3545.8	3446.9	2938.9	2332.1	2335.5	1766.1	2107.0	2154.8	2352.5	2246.8
47.5°	3767.4	3709.5	3637.9	3266.2	2754.8	2870.7	2209.3	2448.0	2563.9	2734.4	2574.1
50°	3723.1	3665.1	3672.0	3474.2	3143.5	3331.0	2683.2	2809.4	3041.2	3174.2	2857.1
52.5°	3368.5	3334.4	3446.9	3436.7	3341.2	3753.8	3235.6	3201.5	3429.9	3518.5	3146.9
55°	2863.9	2816.2	3027.6	3177.6	3341.2	4016.3	3747.0	3637.9	3845.8	3832.2	3344.7
57.5°	2175.2	2192.3	2430.9	2666.2	3068.5	4067.5	4125.4	4111.8	4207.2	4091.3	3501.5
60°	1486.5	1496.7	1834.3	2100.2	2516.2	3798.1	4248.2	4503.9	4493.6	4309.5	3678.8
62.5°	934.2	930.8	1186.5	1605.8	1810.4	3092.4	4200.4	4800.5	4763.0	4473.2	3815.2
65°	538.7	552.3	644.4	1063.7	1258.1	2110.4	3924.3	5090.3	4984.6	4619.8	3961.8
67.5°	330.7	340.9	385.3	576.2	821.7	1166.0	3337.8	5161.9	5168.7	4739.1	4040.2
70°	279.6	283.0	303.4	354.6	572.8	654.6	2246.8	4827.8	5025.5	4766.4	4016.3
72.5°	235.3	238.7	269.3	310.3	426.2	463.7	1009.2	3989.0	4364.1	4558.4	3842.4
75°	173.9	177.3	221.6	283.0	310.3	371.6	552.3	2642.3	2996.9	3603.8	3276.5
77.5°	112.5	115.9	156.8	228.4	262.5	293.2	446.6	1234.2	1561.5	2083.2	2069.5
80°	75.0	75.0	92.1	160.2	208.0	238.7	388.7	610.3	695.5	859.2	804.6
82.5°	47.7	47.7	58.0	98.9	133.0	238.7	364.8	436.4	422.8	429.6	381.9
85°	20.5	20.5	30.7	54.6	71.6	156.8	327.3	375.0	358.0	358.0	340.9
87.5°	6.8	6.8	10.2	17.0	23.9	47.7	252.3	300.0	289.8	300.0	323.9
90°	6.8	6.8	3.4	6.8	6.8	34.1	204.6	296.6	289.8	303.4	334.1
92.5°	10.2	10.2	3.4	3.4	6.8	27.3	160.2	306.8	296.6	317.1	347.8
95°	17.0	17.0	6.8	3.4	10.2	23.9	98.9	272.8	296.6	313.7	354.6
97.5°	20.5	20.5	6.8	6.8	10.2	20.5	51.1	221.6	228.4	238.7	279.6
100°	27.3	27.3	6.8	6.8	6.8	17.0	27.3	115.9	119.3	85.2	136.4
102.5°	27.3	27.3	6.8	6.8	6.8	10.2	13.6	51.1	47.7	17.0	17.0
105°	30.7	30.7	10.2	6.8	6.8	6.8	6.8	17.0	17.0	10.2	20.5
107.5°	30.7	30.7	10.2	10.2	6.8	6.8	3.4	6.8	10.2	10.2	20.5



REPORT NUMBER: P559835  
 CATALOG NUMBER: SDL-PA1-100-730-U-T2U-HSS-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	45°	55°	65°	67.5°	75°	85°
112.5°	17.0	17.0	6.8	10.2	6.8	3.4	3.4	3.4	6.8	13.6	34.1
115°	6.8	6.8	3.4	6.8	3.4	3.4	3.4	6.8	6.8	10.2	27.3
117.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	6.8	3.4	10.2	23.9
120°	3.4	3.4	0.0	3.4	3.4	3.4	3.4	3.4	3.4	13.6	23.9
122.5°	3.4	3.4	3.4	3.4	3.4	0.0	3.4	3.4	3.4	13.6	23.9
125°	3.4	3.4	3.4	3.4	3.4	0.0	3.4	3.4	3.4	10.2	20.5
127.5°	3.4	3.4	3.4	3.4	3.4	0.0	3.4	3.4	3.4	6.8	20.5
130°	3.4	3.4	3.4	3.4	3.4	0.0	3.4	3.4	3.4	6.8	13.6
132.5°	3.4	3.4	3.4	3.4	3.4	0.0	3.4	3.4	3.4	6.8	10.2
135°	3.4	3.4	3.4	3.4	3.4	0.0	3.4	3.4	3.4	3.4	6.8
137.5°	3.4	3.4	3.4	3.4	3.4	0.0	3.4	3.4	3.4	3.4	3.4
140°	0.0	0.0	0.0	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
142.5°	0.0	0.0	0.0	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
145°	0.0	0.0	0.0	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
147.5°	0.0	0.0	0.0	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
150°	3.4	3.4	6.8	6.8	3.4	0.0	6.8	3.4	3.4	3.4	3.4
152.5°	6.8	6.8	6.8	6.8	3.4	0.0	3.4	6.8	3.4	3.4	3.4
155°	6.8	6.8	3.4	3.4	3.4	0.0	3.4	3.4	3.4	6.8	10.2
157.5°	0.0	0.0	0.0	0.0	3.4	0.0	3.4	3.4	0.0	0.0	3.4
160°	0.0	0.0	0.0	0.0	3.4	0.0	3.4	3.4	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P559835

CATALOG NUMBER: SDL-PA1-100-730-U-T2U-HSS-A

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3	985.3
2.5°	975.1	975.1	971.7	971.7	961.5	958.1	913.7	866.0	828.5	831.9	831.9
5°	964.9	958.1	947.8	879.6	794.4	780.8	780.8	773.9	770.5	773.9	773.9
7.5°	842.1	835.3	794.4	760.3	763.7	756.9	743.3	739.8	681.9	623.9	620.5
10°	726.2	716.0	606.9	583.0	579.6	603.5	661.4	641.0	620.5	596.7	606.9
12.5°	606.9	603.5	504.6	559.1	487.5	501.2	514.8	494.4	422.8	340.9	351.2
15°	702.3	692.1	572.8	463.7	416.0	419.4	276.2	265.9	214.8	194.3	184.1
17.5°	521.6	572.8	501.2	463.7	419.4	218.2	177.3	136.4	122.7	98.9	102.3
20°	698.9	685.3	572.8	433.0	323.9	184.1	98.9	78.4	95.5	98.9	98.9
22.5°	494.4	480.7	484.1	460.3	228.4	105.7	75.0	78.4	71.6	68.2	68.2
25°	726.2	702.3	586.4	351.2	170.5	68.2	71.6	54.6	64.8	64.8	64.8
27.5°	883.0	801.2	617.1	340.9	95.5	68.2	51.1	54.6	44.3	44.3	44.3
30°	1056.9	1009.2	808.0	317.1	75.0	54.6	47.7	37.5	40.9	40.9	40.9
32.5°	1135.3	1070.6	808.0	252.3	64.8	51.1	37.5	34.1	34.1	37.5	37.5
35°	1247.9	1179.7	804.6	167.1	54.6	40.9	30.7	30.7	30.7	30.7	30.7
37.5°	1418.3	1319.5	818.3	105.7	44.3	34.1	23.9	27.3	27.3	58.0	58.0
40°	1609.3	1496.7	780.8	75.0	37.5	27.3	20.5	34.1	47.7	51.1	51.1
42.5°	1851.3	1728.6	726.2	64.8	34.1	20.5	17.0	27.3	40.9	64.8	64.8
45°	2141.1	1957.0	651.2	58.0	27.3	17.0	17.0	34.1	51.1	61.4	61.4
47.5°	2400.2	2178.6	521.6	54.6	23.9	13.6	23.9	37.5	44.3	71.6	71.6
50°	2703.7	2410.5	398.9	47.7	20.5	13.6	37.5	40.9	51.1	64.8	64.8
52.5°	2928.7	2604.8	303.4	44.3	20.5	10.2	37.5	37.5	58.0	75.0	75.0
55°	3109.4	2710.5	218.2	37.5	17.0	10.2	44.3	47.7	51.1	58.0	58.0
57.5°	3249.2	2785.5	170.5	34.1	17.0	23.9	54.6	61.4	54.6	58.0	58.0
60°	3409.4	2823.0	126.1	30.7	13.6	23.9	64.8	81.8	61.4	88.6	85.2
62.5°	3556.0	2850.3	102.3	30.7	13.6	27.3	71.6	102.3	81.8	119.3	122.7
65°	3740.1	2884.4	85.2	23.9	13.6	37.5	85.2	136.4	109.1	156.8	163.7
67.5°	3862.9	2904.8	71.6	23.9	13.6	44.3	119.3	177.3	136.4	197.7	204.6
70°	3876.5	2829.8	58.0	23.9	13.6	68.2	163.7	214.8	170.5	252.3	255.7
72.5°	3699.2	2615.0	47.7	27.3	13.6	75.0	190.9	248.9	201.2	334.1	337.5
75°	2990.1	1834.3	44.3	27.3	13.6	95.5	208.0	272.8	225.0	347.8	354.6
77.5°	1837.7	848.9	40.9	30.7	20.5	105.7	211.4	289.8	235.3	347.8	358.0
80°	712.6	419.4	37.5	34.1	47.7	119.3	228.4	293.2	235.3	323.9	337.5
82.5°	330.7	245.5	37.5	37.5	61.4	122.7	225.0	272.8	218.2	289.8	286.4
85°	296.6	242.1	40.9	40.9	64.8	105.7	177.3	231.8	187.5	228.4	228.4
87.5°	289.8	238.7	44.3	51.1	64.8	61.4	136.4	197.7	160.2	170.5	170.5
90°	296.6	248.9	47.7	58.0	54.6	34.1	109.1	163.7	122.7	109.1	105.7
92.5°	317.1	252.3	58.0	68.2	51.1	27.3	92.1	133.0	88.6	71.6	68.2
95°	334.1	259.1	71.6	81.8	54.6	23.9	81.8	105.7	64.8	44.3	40.9
97.5°	279.6	201.2	81.8	88.6	54.6	23.9	71.6	85.2	51.1	23.9	23.9
100°	119.3	88.6	85.2	95.5	51.1	20.5	61.4	68.2	34.1	10.2	13.6
102.5°	23.9	27.3	75.0	88.6	40.9	13.6	40.9	40.9	23.9	3.4	6.8
105°	23.9	20.5	47.7	75.0	23.9	6.8	17.0	23.9	10.2	3.4	3.4
107.5°	23.9	23.9	17.0	37.5	10.2	6.8	6.8	10.2	6.8	3.4	3.4



REPORT NUMBER: P559835  
 CATALOG NUMBER: SDL-PA1-100-730-U-T2U-HSS-A

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	34.1	30.7	6.8	10.2	10.2	6.8	3.4	3.4	6.8	23.9	27.3
115°	30.7	27.3	10.2	10.2	6.8	6.8	3.4	3.4	6.8	27.3	30.7
117.5°	23.9	23.9	10.2	6.8	6.8	6.8	3.4	3.4	6.8	27.3	27.3
120°	27.3	23.9	10.2	6.8	3.4	3.4	3.4	3.4	6.8	20.5	20.5
122.5°	27.3	23.9	10.2	6.8	3.4	3.4	3.4	3.4	6.8	20.5	23.9
125°	23.9	20.5	10.2	6.8	3.4	3.4	3.4	3.4	10.2	20.5	20.5
127.5°	20.5	17.0	6.8	3.4	3.4	3.4	3.4	3.4	10.2	17.0	17.0
130°	13.6	13.6	6.8	3.4	3.4	3.4	3.4	3.4	10.2	13.6	13.6
132.5°	10.2	10.2	6.8	3.4	3.4	3.4	3.4	3.4	6.8	13.6	13.6
135°	10.2	6.8	6.8	3.4	3.4	3.4	3.4	3.4	6.8	10.2	10.2
137.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	6.8	6.8
140°	3.4	3.4	3.4	3.4	3.4	3.4	0.0	0.0	0.0	3.4	3.4
142.5°	3.4	3.4	3.4	3.4	3.4	3.4	0.0	0.0	0.0	3.4	3.4
145°	3.4	3.4	3.4	3.4	3.4	3.4	0.0	0.0	0.0	3.4	3.4
147.5°	3.4	3.4	3.4	3.4	3.4	3.4	0.0	0.0	0.0	3.4	3.4
150°	3.4	3.4	3.4	3.4	3.4	0.0	0.0	0.0	0.0	3.4	3.4
152.5°	3.4	3.4	6.8	3.4	3.4	0.0	0.0	0.0	0.0	3.4	3.4
155°	10.2	10.2	10.2	3.4	3.4	0.0	0.0	0.0	0.0	3.4	3.4
157.5°	3.4	3.4	3.4	3.4	3.4	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	3.4	3.4	3.4	3.4	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245982

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



--- HS — SS

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



u





110° | 23.9 23.9 10.2 10.2 6.8 3.4 3.4 3.4 6.8 10.2 23.9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





110°	27.3	23.9	6.8	10.2	6.8	6.8	6.8	6.8	3.4	17.0	20.5
------	------	------	-----	------	-----	-----	-----	-----	-----	------	------

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)