

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P560713

Luminaire Tested: **SDL-PA1-60-730-U-T2R**

Issue Date: 7/26/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P560713  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/26/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: SDL-PA1-60-730-U-T2R  
Description: Springdale  
(1) 70 CRI, 3000K, 800mA LIGHT ENGINE WITH 24 LEDS AND TYPE II R OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6762.7 lumens  
Efficiency: N/A  
Efficacy: 108.4 lumens/watt  
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')  
IES Classification: Type II - Medium  
BUG Rating: B1 - U0 - G2

Input Watts (W): 62.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT






REPORT NUMBER: P560713  
 CATALOG NUMBER: SDL-PA1-60-730-U-T2R

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 15.4 fc  
 Type II - Medium - N/A

REPORT NUMBER: P560713  
CATALOG NUMBER: SDL-PA1-60-730-U-T2R

### Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral    - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P560713

CATALOG NUMBER: SDL-PA1-60-730-U-T2R


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1028.7	0.0	1028.7
	% Fixture	15.2	0.0	15.2
<b>Street Side</b>	Lumens	5734.0	0.0	5734.0
	% Fixture	84.8	0.0	84.8
<b>Total</b>	Lumens	6762.7	0.0	6762.7
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.8	1.2
10°-20°	214.8	3.2
20°-30°	392.8	5.8
30°-40°	797.3	11.8
40°-50°	1223.7	18.1
50°-60°	1475.3	21.8
60°-70°	1426.7	21.1
70°-80°	989.7	14.6
80°-90°	161.6	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	6762.7	100.0
0°-180°	6762.7	100.0

**Coefficient of Utilization**



REPORT NUMBER: P560713


CATALOG NUMBER: SDL-PA1-60-730-U-T2R

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	480.7	7.1			
FM (30°-60°)	3024.5	44.7			
FH (60°-80°)	2107.8	31.2			G2/5000
FVH (80°-90°)	121.0	1.8			G2/225
BL (0°-30°)	207.7	3.1	B1/500		
BM (30°-60°)	471.9	7.0	B1/1000		
BH (60°-80°)	308.6	4.6	B1/500		G1/500
BVH (80°-90°)	40.6	0.6			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G2**

Type II Medium





REPORT NUMBER: P560713

CATALOG NUMBER: SDL-PA1-60-730-U-T2R

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	77.5°	85°
0°	977.3	977.3	977.3	977.3	977.3	977.3	977.3	977.3	977.3	977.3	977.3
2.5°	1014.6	1111.6	1064.4	1119.1	1146.4	1129.0	1114.1	1076.8	1044.5	1032.0	999.7
5°	1119.1	1116.6	1104.2	1099.2	1076.8	1049.5	1027.1	1151.4	1106.7	1084.3	1027.1
7.5°	992.3	1076.8	1139.0	1171.3	1171.3	1139.0	1104.2	952.5	1029.6	1009.7	927.6
10°	1245.9	1245.9	1243.4	1245.9	1022.1	1076.8	925.1	860.5	833.1	897.8	833.1
12.5°	1059.4	1151.4	1255.9	1293.2	1191.2	1017.1	947.5	910.2	713.7	698.8	738.6
15°	1245.9	1253.4	1263.3	1111.6	945.0	1079.3	825.6	818.2	945.0	922.6	932.6
17.5°	999.7	1009.7	1226.0	1198.7	1099.2	818.2	1029.6	920.1	872.9	843.0	840.6
20°	1260.8	1265.8	1263.3	947.5	1014.6	1114.1	1066.9	810.7	1017.1	1029.6	1042.0
22.5°	1066.9	1069.4	1081.8	1206.1	1027.1	1161.4	962.4	1208.6	997.2	1027.1	775.9
25°	1434.9	1434.9	1390.2	1086.8	1243.4	1059.4	1171.3	1039.5	1308.1	1273.3	1166.3
27.5°	1337.9	1328.0	1275.8	1345.4	1121.6	1340.4	1158.9	1305.6	1420.0	1370.3	1415.0
30°	1880.1	1892.5	1825.4	1397.6	1365.3	1285.7	1335.4	1546.8	1932.3	1904.9	1701.0
32.5°	2516.7	2399.8	2093.9	1810.4	1492.1	1569.2	1492.1	1825.4	2069.1	2074.0	1800.5
35°	2825.1	2815.1	2683.3	2136.2	1715.9	1715.9	1673.7	1904.9	2245.6	2213.3	1907.4
37.5°	3071.3	3056.4	2964.3	2414.7	1917.4	1907.4	1770.6	2026.8	2447.1	2365.0	2024.3
40°	3280.2	3260.3	3180.7	2608.7	2136.2	2089.0	1890.0	2166.1	2603.7	2611.2	2136.2
42.5°	3419.4	3412.0	3354.8	2785.3	2317.8	2233.2	2049.2	2345.1	2770.4	2812.6	2275.5
45°	3528.9	3526.4	3476.6	2979.3	2447.1	2365.0	2218.3	2479.4	2999.2	3024.0	2424.7
47.5°	3541.3	3551.2	3551.2	3076.3	2536.6	2481.9	2392.4	2598.8	3290.1	3237.9	2598.8
50°	3412.0	3421.9	3484.1	3237.9	2613.7	2578.9	2541.6	2743.0	3556.2	3479.1	2782.8
52.5°	3081.2	3103.6	3272.7	3158.3	2653.5	2651.0	2680.8	2929.5	3827.3	3745.2	3026.5
55°	2370.0	2384.9	2805.2	2924.6	2641.1	2668.4	2785.3	3160.8	4163.0	4090.9	3282.7
57.5°	1810.4	1852.7	2116.3	2481.9	2504.3	2653.5	2852.4	3322.5	4434.1	4362.0	3518.9
60°	1457.3	1487.1	1641.3	1962.1	2210.8	2588.8	2944.5	3523.9	4697.7	4662.9	3772.6
62.5°	1141.5	1161.4	1268.3	1479.7	1795.5	2437.1	3001.6	3742.7	5001.1	4983.7	4103.3
65°	818.2	838.1	932.6	1071.8	1387.7	2151.1	2974.3	3951.6	5408.9	5391.5	4424.1
67.5°	596.8	601.8	664.0	758.5	984.8	1740.8	2840.0	4083.4	5806.8	5772.0	4670.3
70°	460.1	465.0	494.9	529.7	629.2	1318.0	2526.7	3984.0	6040.6	5980.9	4707.6
72.5°	373.0	373.0	385.5	402.9	430.2	860.5	1984.5	3593.5	5931.2	5814.3	4396.8
75°	313.3	313.3	320.8	315.8	300.9	537.2	1380.2	3001.6	5431.3	5284.6	3827.3
77.5°	263.6	261.1	261.1	263.6	233.8	365.6	843.0	2312.8	4389.3	4247.6	2837.5
80°	216.4	216.4	216.4	216.4	191.5	261.1	502.3	1534.4	2521.7	2200.9	1300.6
82.5°	159.2	161.6	169.1	169.1	159.2	191.5	261.1	641.6	862.9	763.5	460.1
85°	74.6	77.1	99.5	104.4	102.0	94.5	136.8	288.5	402.9	365.6	106.9
87.5°	2.5	2.5	9.9	22.4	19.9	14.9	27.4	39.8	14.9	17.4	12.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P560713  
 CATALOG NUMBER: SDL-PA1-60-730-U-T2R

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	77.5°	85°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P560713  
 CATALOG NUMBER: SDL-PA1-60-730-U-T2R

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	977.3	977.3	977.3	977.3	977.3	977.3	977.3	977.3	977.3	977.3	977.3
2.5°	977.3	955.0	902.7	858.0	810.7	778.4	706.3	654.0	626.7	621.7	629.2
5°	982.3	932.6	828.1	696.3	596.8	572.0	562.0	559.5	557.1	557.1	557.1
7.5°	865.4	800.8	644.1	547.1	562.0	562.0	562.0	554.6	509.8	489.9	489.9
10°	763.5	678.9	480.0	442.7	445.1	467.5	527.2	589.4	601.8	604.3	606.8
12.5°	661.5	579.4	407.8	430.2	388.0	460.1	544.6	606.8	547.1	517.3	517.3
15°	833.1	716.2	472.5	378.0	383.0	460.1	415.3	562.0	601.8	604.3	606.8
17.5°	751.0	631.7	440.2	397.9	420.3	350.6	475.0	532.2	489.9	484.9	480.0
20°	912.7	751.0	460.1	395.4	392.9	425.3	402.9	402.9	547.1	547.1	547.1
22.5°	676.4	557.1	447.6	445.1	375.5	420.3	400.4	447.6	430.2	422.8	422.8
25°	992.3	785.8	489.9	390.4	402.9	370.5	412.8	368.1	455.1	460.1	460.1
27.5°	1191.2	922.6	532.2	432.7	370.5	397.9	340.7	370.5	350.6	353.1	353.1
30°	1420.0	1081.8	661.5	452.6	380.5	328.3	338.2	320.8	380.5	373.0	370.5
32.5°	1482.2	1091.7	636.6	480.0	370.5	330.8	305.9	330.8	353.1	385.5	385.5
35°	1554.3	1101.7	601.8	457.6	363.1	308.4	303.4	330.8	358.1	348.2	348.2
37.5°	1621.4	1109.1	574.5	430.2	333.2	300.9	300.9	305.9	333.2	318.3	318.3
40°	1698.5	1111.6	542.1	400.4	308.4	295.9	278.5	283.5	286.0	276.0	273.6
42.5°	1785.6	1109.1	504.8	373.0	286.0	276.0	263.6	263.6	271.1	268.6	266.1
45°	1880.1	1106.7	465.0	340.7	261.1	248.7	241.2	271.1	283.5	283.5	278.5
47.5°	1994.5	1106.7	427.7	303.4	243.7	223.8	218.8	251.2	276.0	281.0	286.0
50°	2126.3	1101.7	392.9	276.0	226.3	208.9	216.4	248.7	268.6	276.0	273.6
52.5°	2297.9	1091.7	363.1	253.7	213.9	191.5	203.9	241.2	266.1	268.6	266.1
55°	2447.1	1056.9	333.2	243.7	203.9	181.5	196.5	238.7	261.1	261.1	261.1
57.5°	2573.9	1007.2	308.4	236.3	201.4	179.1	194.0	236.3	251.2	258.6	258.6
60°	2728.1	945.0	291.0	233.8	198.9	176.6	191.5	233.8	246.2	256.1	256.1
62.5°	2887.3	892.8	281.0	233.8	191.5	179.1	191.5	233.8	243.7	256.1	253.7
65°	3016.6	825.6	271.1	238.7	189.0	179.1	191.5	233.8	241.2	253.7	253.7
67.5°	3009.1	733.6	258.6	251.2	191.5	181.5	191.5	231.3	236.3	253.7	248.7
70°	2840.0	626.7	238.7	248.7	198.9	181.5	189.0	223.8	226.3	248.7	241.2
72.5°	2534.1	507.3	211.4	233.8	198.9	184.0	184.0	213.9	213.9	238.7	223.8
75°	2121.3	390.4	174.1	206.4	189.0	189.0	174.1	201.4	196.5	211.4	196.5
77.5°	1581.6	295.9	134.3	171.6	171.6	186.5	166.6	186.5	179.1	181.5	174.1
80°	659.0	179.1	102.0	134.3	146.7	181.5	159.2	169.1	151.7	151.7	146.7
82.5°	273.6	114.4	69.6	84.6	99.5	161.6	151.7	144.2	124.3	114.4	106.9
85°	99.5	62.2	47.3	57.2	64.7	111.9	109.4	92.0	72.1	79.6	64.7
87.5°	7.5	9.9	9.9	12.4	12.4	14.9	24.9	24.9	14.9	12.4	7.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P560713  
 CATALOG NUMBER: SDL-PA1-60-730-U-T2R

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245982

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



--- HS    — SS

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



u





110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
------	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
------	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----	-----

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)