

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P560883

Luminaire Tested: **SDL-PA1-70-730-U-SL3-HSS-A**

Issue Date: 7/26/2021

Test Information

Test Method: LM-79-08
Report Number: P560883
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/26/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: SDL-PA1-70-730-U-SL3-HSS-A
Description: Springdale
(1) 70 CRI, 3000K, 930mA LIGHT ENGINE WITH 24 LEDS AND TYPE III SPILL LIGHT ELIMINATOR OPTICS, HOUSE SIDE SHIELD AND CLEAR PANELS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6078.4 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')
IES Classification: Type IV - Medium
BUG Rating: B1 - U3 - G2


Input Watts (W): 72.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P560883
 CATALOG NUMBER: SDL-PA1-70-730-U-SL3-HSS-A

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 16.1 fc
 Type IV - Medium - N/A

REPORT NUMBER: P560883
CATALOG NUMBER: SDL-PA1-70-730-U-SL3-HSS-A

Luminous Intensity Polar Plot



— Vertical Plane Through 60-Deg Lateral - - - Horizontal Cone Through 75-Deg Vertical

REPORT NUMBER: P560883
 CATALOG NUMBER: SDL-PA1-70-730-U-SL3-HSS-A

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	628.2	81.9	710.0
	% Fixture	10.3	1.3	11.7
Street Side	Lumens	5282.8	85.6	5368.4
	% Fixture	86.9	1.4	88.3
Total	Lumens	5911.0	167.5	6078.4
	% Fixture	97.2	2.8	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.5	1.8
10°-20°	182.9	3.0
20°-30°	258.6	4.3
30°-40°	464.7	7.6
40°-50°	783.0	12.9
50°-60°	1217.9	20.0
60°-70°	1437.2	23.6
70°-80°	1165.8	19.2
80°-90°	289.4	4.8
90°-100°	116.8	1.9
100°-110°	27.0	0.4
110°-120°	8.4	0.1
120°-130°	7.5	0.1
130°-140°	4.0	0.1
140°-150°	1.9	0.0
150°-160°	1.6	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-90°	5911.0	97.2
0°-180°	6078.4	100.0

Coefficient of Utilization



REPORT NUMBER: P560883


CATALOG NUMBER: SDL-PA1-70-730-U-SL3-HSS-A

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	416.4	6.8			
FM (30°-60°)	2259.1	37.2			
FH (60°-80°)	2389.7	39.3			G2/5000
FVH (80°-90°)	217.6	3.6			G2/225
BL (0°-30°)	136.6	2.2	B1/500		
BM (30°-60°)	206.5	3.4	B0/220		
BH (60°-80°)	213.3	3.5	B1/500		G1/500
BVH (80°-90°)	71.8	1.2			G1/100
UL (90°-100°)	116.8	1.9		U3/500	
UH (100°-180°)	50.6	0.8		U3/500	

BUG Rating: B1-U3-G2

Type IV Medium





REPORT NUMBER: P560883

CATALOG NUMBER: SDL-PA1-70-730-U-SL3-HSS-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	60°	65°	75°	85°
0°	1606.8	1606.8	1606.8	1606.8	1606.8	1606.8	1606.8	1606.8	1606.8	1606.8	1606.8
2.5°	1511.3	1626.5	1592.8	1699.5	1713.6	1707.9	1702.3	1688.3	1674.2	1648.9	1609.6
5°	1449.5	1460.7	1452.3	1472.0	1474.8	1483.2	1469.2	1547.8	1679.8	1646.1	1584.3
7.5°	1191.1	1309.0	1323.1	1359.6	1393.3	1427.0	1446.7	1443.9	1275.3	1432.6	1362.4
10°	1216.3	1233.2	1230.4	1255.7	1227.6	1179.8	1075.9	1078.7	1078.7	1112.4	1148.9
12.5°	963.5	1014.1	1137.7	1177.0	1092.7	994.4	1002.8	1022.5	1036.6	879.2	969.1
15°	1092.7	1095.6	1098.4	1098.4	823.1	941.0	820.3	741.6	848.3	1039.4	1056.2
17.5°	856.8	848.3	988.8	977.6	907.3	699.5	910.1	929.8	893.3	873.6	879.2
20°	1005.7	1005.7	997.2	795.0	837.1	901.7	780.9	778.1	823.1	1022.5	1033.7
22.5°	814.6	806.2	851.2	884.9	795.0	859.6	769.7	865.2	957.9	904.5	738.8
25°	1019.7	1019.7	986.0	766.9	823.1	738.8	854.0	733.2	814.6	1106.8	1053.4
27.5°	943.9	918.6	839.9	870.8	738.8	859.6	786.5	890.5	941.0	1146.1	1227.6
30°	1219.2	1210.7	1120.8	876.4	839.9	789.4	845.5	896.1	1084.3	1486.0	1418.6
32.5°	1626.5	1581.5	1275.3	1084.3	882.1	935.4	901.7	1053.4	1191.1	1519.7	1438.3
35°	1736.0	1702.3	1556.2	1317.5	988.8	988.8	969.1	1075.9	1222.0	1592.8	1480.4
37.5°	1772.5	1769.7	1719.2	1441.1	1134.9	1137.7	1025.3	1129.3	1283.8	1691.1	1542.2
40°	1795.0	1800.6	1851.2	1570.3	1289.4	1283.8	1129.3	1205.1	1379.3	1797.8	1654.6
42.5°	1890.5	1921.4	1983.2	1713.6	1435.5	1438.3	1255.7	1325.9	1505.7	1974.8	1809.1
45°	2104.0	2112.4	2149.0	1910.2	1573.1	1592.8	1415.8	1488.8	1660.2	2168.6	1983.2
47.5°	2427.1	2427.1	2365.3	2064.7	1736.0	1764.1	1584.3	1660.2	1842.8	2452.3	2185.5
50°	2713.6	2691.1	2556.3	2247.3	1868.1	1929.9	1806.3	1893.3	1997.3	2668.6	2438.3
52.5°	2893.4	2884.9	2719.2	2370.9	2008.5	2112.4	1988.8	2101.2	2177.1	2893.4	2665.8
55°	2868.1	2868.1	2761.3	2435.5	2137.7	2278.2	2224.8	2365.3	2393.4	3106.9	2831.6
57.5°	2772.6	2786.6	2736.1	2460.8	2163.0	2435.5	2466.4	2598.4	2646.2	3230.5	2935.5
60°	2578.8	2606.8	2660.2	2494.5	2261.3	2612.5	2713.6	2831.6	2921.5	3323.2	3022.6
62.5°	2216.4	2252.9	2441.1	2491.7	2337.2	2795.1	2924.3	3028.2	3112.5	3373.7	3084.4
65°	1679.8	1747.3	2019.7	2311.9	2331.6	3008.5	3095.6	3196.8	3278.2	3424.3	3244.5
67.5°	1073.1	1075.9	1370.8	1910.2	2174.2	3309.1	3326.0	3376.5	3429.9	3564.8	3472.1
70°	553.4	581.5	721.9	1219.2	1781.0	3370.9	3901.8	3828.8	3747.3	3870.9	3767.0
72.5°	368.0	398.9	474.7	657.3	1118.0	3039.4	4528.3	4730.5	4371.0	4098.5	3508.6
75°	207.9	224.7	317.4	519.7	691.0	1963.6	4458.0	5180.0	4764.2	3682.7	2820.3
77.5°	92.7	98.3	143.3	407.3	592.7	957.9	3508.6	4328.8	4163.1	3070.3	2033.8
80°	50.6	50.6	67.4	188.2	502.8	721.9	2328.7	3014.2	2831.6	1851.2	924.2
82.5°	28.1	30.9	39.3	89.9	306.2	660.1	1472.0	1890.5	1494.4	508.4	373.6
85°	11.2	11.2	16.9	47.8	112.4	559.0	806.2	898.9	604.0	258.4	289.3
87.5°	5.6	5.6	5.6	16.9	36.5	143.3	264.1	283.7	221.9	205.1	250.0
90°	8.4	8.4	5.6	5.6	25.3	151.7	221.9	233.2	182.6	205.1	252.8
92.5°	11.2	8.4	5.6	5.6	19.7	151.7	252.8	250.0	182.6	205.1	261.2
95°	14.0	11.2	5.6	5.6	19.7	134.8	303.4	272.5	196.6	207.9	275.3
97.5°	14.0	14.0	5.6	5.6	19.7	103.9	320.2	275.3	171.4	134.8	188.2
100°	16.9	16.9	5.6	5.6	22.5	61.8	221.9	205.1	120.8	44.9	53.4
102.5°	19.7	19.7	5.6	5.6	14.0	30.9	106.7	103.9	67.4	11.2	19.7
105°	19.7	22.5	5.6	5.6	5.6	14.0	39.3	47.8	33.7	11.2	19.7
107.5°	22.5	25.3	5.6	5.6	5.6	8.4	16.9	16.9	11.2	11.2	19.7



REPORT NUMBER: P560883
 CATALOG NUMBER: SDL-PA1-70-730-U-SL3-HSS-A

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	60°	65°	75°	85°
112.5°	16.9	16.9	2.8	5.6	5.6	5.6	2.8	5.6	5.6	8.4	16.9
115°	8.4	5.6	2.8	5.6	2.8	5.6	2.8	5.6	8.4	8.4	19.7
117.5°	2.8	2.8	2.8	2.8	2.8	5.6	2.8	5.6	5.6	14.0	25.3
120°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	5.6	5.6	19.7	30.9
122.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	5.6	5.6	19.7	36.5
125°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	5.6	5.6	14.0	33.7
127.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	5.6	5.6	14.0	28.1
130°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	5.6	5.6	11.2	25.3
132.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	5.6	11.2	19.7
135°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	5.6	14.0
137.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	5.6
140°	2.8	0.0	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
142.5°	2.8	0.0	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.8
145°	2.8	2.8	2.8	2.8	5.6	2.8	2.8	2.8	2.8	2.8	2.8
147.5°	2.8	2.8	2.8	5.6	5.6	2.8	2.8	2.8	2.8	2.8	2.8
150°	11.2	11.2	11.2	8.4	5.6	2.8	8.4	5.6	2.8	2.8	2.8
152.5°	8.4	8.4	14.0	5.6	2.8	2.8	2.8	8.4	8.4	2.8	2.8
155°	8.4	8.4	5.6	2.8	2.8	2.8	2.8	2.8	2.8	8.4	11.2
157.5°	2.8	2.8	2.8	0.0	2.8	2.8	2.8	2.8	2.8	5.6	2.8
160°	0.0	0.0	0.0	0.0	2.8	2.8	2.8	2.8	2.8	2.8	2.8
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P560883

CATALOG NUMBER: SDL-PA1-70-730-U-SL3-HSS-A

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1606.8	1606.8	1606.8	1606.8	1606.8	1606.8	1606.8	1606.8	1606.8	1606.8	1606.8
2.5°	1595.6	1578.7	1533.8	1491.6	1441.1	1410.2	1303.4	1182.6	1157.4	1151.7	1132.1
5°	1556.2	1519.7	1432.6	1247.2	1061.8	977.6	938.2	907.3	865.2	856.8	845.5
7.5°	1320.3	1258.5	1123.6	896.1	868.0	789.4	724.7	671.4	556.2	525.3	508.4
10°	1098.4	1045.0	766.9	651.7	592.7	533.7	463.5	410.1	362.4	339.9	331.5
12.5°	887.7	834.3	573.1	516.9	368.0	303.4	264.1	219.1	182.6	162.9	162.9
15°	983.2	896.1	592.7	368.0	241.6	179.8	132.0	118.0	137.6	140.5	140.5
17.5°	803.4	716.3	466.3	286.5	177.0	98.3	106.7	120.8	132.0	115.2	118.0
20°	924.2	803.4	469.1	216.3	112.4	95.5	98.3	89.9	120.8	123.6	123.6
22.5°	699.5	632.0	353.9	171.4	87.1	89.9	84.3	101.1	112.4	98.3	95.5
25°	904.5	744.4	359.6	109.6	87.1	73.0	87.1	78.7	103.9	106.7	106.7
27.5°	1036.6	834.3	314.6	95.5	73.0	78.7	70.2	81.5	78.7	78.7	78.7
30°	1177.0	910.1	306.2	92.7	70.2	64.6	67.4	64.6	75.8	78.7	78.7
32.5°	1177.0	870.8	233.2	92.7	67.4	61.8	53.4	59.0	61.8	67.4	70.2
35°	1185.4	837.1	171.4	84.3	61.8	53.4	47.8	47.8	53.4	56.2	56.2
37.5°	1210.7	814.6	132.0	78.7	56.2	47.8	39.3	42.1	73.0	81.5	81.5
40°	1281.0	814.6	112.4	73.0	50.6	42.1	33.7	53.4	61.8	73.0	73.0
42.5°	1390.5	825.9	106.7	70.2	44.9	36.5	28.1	42.1	75.8	87.1	89.9
45°	1505.7	848.3	101.1	67.4	42.1	30.9	33.7	50.6	59.0	78.7	78.7
47.5°	1665.8	896.1	98.3	64.6	39.3	25.3	30.9	50.6	64.6	84.3	84.3
50°	1840.0	946.7	92.7	61.8	33.7	22.5	47.8	42.1	53.4	87.1	87.1
52.5°	2019.7	1005.7	89.9	59.0	30.9	30.9	53.4	50.6	64.6	84.3	87.1
55°	2177.1	1053.4	84.3	59.0	28.1	28.1	56.2	50.6	59.0	78.7	81.5
57.5°	2252.9	1061.8	81.5	56.2	25.3	28.1	53.4	61.8	53.4	64.6	70.2
60°	2348.4	1084.3	73.0	50.6	22.5	36.5	61.8	81.5	73.0	84.3	89.9
62.5°	2438.3	1101.2	64.6	44.9	19.7	39.3	81.5	98.3	78.7	98.3	109.6
65°	2604.0	1137.7	53.4	36.5	16.9	44.9	92.7	118.0	87.1	115.2	115.2
67.5°	2834.4	1196.7	42.1	30.9	16.9	50.6	95.5	134.8	103.9	126.4	123.6
70°	2924.3	1101.2	36.5	28.1	16.9	59.0	103.9	146.1	109.6	140.5	140.5
72.5°	2550.7	795.0	30.9	28.1	28.1	67.4	129.2	160.1	120.8	177.0	174.2
75°	1969.2	500.0	30.9	28.1	33.7	84.3	146.1	171.4	129.2	196.6	193.8
77.5°	1311.9	236.0	30.9	30.9	39.3	92.7	157.3	182.6	143.3	219.1	216.3
80°	514.1	129.2	33.7	33.7	47.8	98.3	168.5	188.2	148.9	236.0	233.2
82.5°	247.2	89.9	33.7	33.7	64.6	109.6	179.8	196.6	154.5	238.8	236.0
85°	210.7	84.3	30.9	36.5	78.7	137.6	191.0	193.8	157.3	227.5	227.5
87.5°	188.2	81.5	30.9	36.5	106.7	160.1	199.4	191.0	168.5	221.9	221.9
90°	193.8	87.1	33.7	42.1	120.8	162.9	202.3	191.0	162.9	205.1	205.1
92.5°	207.9	92.7	36.5	44.9	120.8	151.7	188.2	171.4	151.7	174.2	171.4
95°	219.1	98.3	39.3	50.6	106.7	118.0	157.3	137.6	126.4	134.8	134.8
97.5°	168.5	75.8	44.9	56.2	81.5	70.2	98.3	89.9	67.4	56.2	56.2
100°	44.9	25.3	47.8	56.2	56.2	47.8	73.0	67.4	44.9	19.7	19.7
102.5°	16.9	16.9	44.9	53.4	44.9	36.5	53.4	50.6	36.5	5.6	5.6
105°	16.9	14.0	28.1	42.1	28.1	19.7	28.1	33.7	22.5	5.6	5.6
107.5°	16.9	14.0	16.9	25.3	11.2	8.4	11.2	11.2	11.2	2.8	5.6



REPORT NUMBER: P560883
 CATALOG NUMBER: SDL-PA1-70-730-U-SL3-HSS-A

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	16.9	14.0	8.4	11.2	8.4	8.4	5.6	5.6	8.4	16.9	16.9
115°	16.9	14.0	8.4	8.4	5.6	8.4	5.6	2.8	8.4	19.7	22.5
117.5°	22.5	14.0	5.6	5.6	5.6	5.6	5.6	2.8	8.4	25.3	28.1
120°	28.1	16.9	5.6	5.6	5.6	2.8	5.6	2.8	11.2	25.3	28.1
122.5°	30.9	19.7	5.6	5.6	5.6	2.8	2.8	5.6	11.2	25.3	25.3
125°	30.9	19.7	5.6	5.6	2.8	2.8	2.8	2.8	11.2	25.3	28.1
127.5°	25.3	16.9	5.6	5.6	2.8	2.8	2.8	2.8	11.2	22.5	25.3
130°	22.5	16.9	5.6	5.6	2.8	2.8	2.8	2.8	11.2	19.7	22.5
132.5°	16.9	14.0	5.6	2.8	2.8	2.8	2.8	2.8	11.2	16.9	19.7
135°	14.0	8.4	5.6	2.8	2.8	2.8	2.8	2.8	8.4	16.9	16.9
137.5°	5.6	5.6	2.8	2.8	2.8	2.8	2.8	2.8	5.6	8.4	8.4
140°	5.6	5.6	2.8	2.8	2.8	2.8	2.8	2.8	2.8	5.6	5.6
142.5°	2.8	5.6	2.8	2.8	2.8	2.8	0.0	2.8	2.8	2.8	2.8
145°	2.8	5.6	2.8	2.8	2.8	2.8	0.0	2.8	2.8	2.8	2.8
147.5°	2.8	5.6	2.8	2.8	2.8	2.8	0.0	2.8	2.8	2.8	2.8
150°	2.8	5.6	2.8	2.8	2.8	2.8	0.0	2.8	2.8	2.8	5.6
152.5°	2.8	5.6	2.8	2.8	2.8	0.0	0.0	2.8	2.8	2.8	2.8
155°	11.2	8.4	5.6	2.8	2.8	0.0	0.0	0.0	2.8	2.8	2.8
157.5°	2.8	2.8	2.8	2.8	2.8	0.0	0.0	0.0	2.8	2.8	2.8
160°	2.8	2.8	2.8	2.8	2.8	0.0	0.0	0.0	2.8	2.8	2.8
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245982

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



--- HS — SS

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



u



110°	22.5	22.5	5.6	5.6	5.6	5.6	5.6	5.6	5.6	11.2	19.7
------	------	------	-----	-----	-----	-----	-----	-----	-----	------	------

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





110°	16.9	14.0	8.4	11.2	8.4	8.4	8.4	5.6	5.6	11.2	11.2
------	------	------	-----	------	-----	-----	-----	-----	-----	------	------

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)