

Scaled data based on original data using
LM-35-02 Approved Method for Photometric Testing of Floodlights Using High Intensity
Discharge or Incandescent Filament Lamps

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: STREETWORKS

Report Number: P210015

Luminaire Tested: **EGL91PW*55**

Issue Date:

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-35-02
Report Number: P210015
DATA PRORATED FROM REPORT 764991
Test Lab:
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: EGL91PW*55
Description: EAGLE SPORTS FLOODLIGHT - 5H x 5V
Light Source: 1000 WATT PULSE START METAL HALIDE, CLEAR, BT-56, UNIVERSAL
Ballast/Driver: -

Luminaire Equipment:	<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
	AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
	AS-5443-2	Good	REFLECTOR
	AS-5443-3	Good	REFLECTOR
	AS-5443-4	Good	REFLECTOR

Summary

Lumens per Lamp:	110000 (1 lamp)	NEMA Type:	5H x 5V
Luminaire Lumens:	83680.4 lumens	Max Intensity:	135266.4 candela
Efficiency:	76.1%	Max Intensity Angle:	0°H x 0°V
Efficacy:	83.7 lumens/watt		
Luminous Opening:	Point Source (0' x 0' x 0')		


Beam Angle (50%):	37°H x 37°V	Field Angle (10%):	88.9°H x 88.9°V
Beam Lumens:	25777.1 lumens	Field Lumens:	73715.2 lumens
Beam Efficiency:	30.8%	Field Efficiency:	88.1%

Input Watts (W): 1000
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P210015
CATALOG NUMBER: EGL91PW*55


Iso-Candela Plot






REPORT NUMBER: P210015
 CATALOG NUMBER: EGL91PW*55

Lumen Table



REPORT NUMBER: P210015
CATALOG NUMBER: EGL91PW*55

Luminous Intensity Polar Plot




— Vertical Distribution Through 0-Deg - - - Horizontal Distribution Through 0-Deg



REPORT NUMBER: P210015
 CATALOG NUMBER: EGL91PW*55

Luminous Intensity Plot



Beam:
 H Angle: 37°
 V Angle: 37°
 Lumens: 25777.1
 Efficiency: 30.8%

Field:
 H Angle: 88.9°
 V Angle: 88.9°
 Lumens: 73715.2
 Efficiency: 88.1%

Spill:
 Lumens: 9965.3
 Efficiency: 11.9%

— Vertical Distribution through 0-Deg
 - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P210015
 CATALOG NUMBER: EGL91PW*55

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-80°	-72°	-64°	-56°	-48°	-40°	-32°	-24°	-16°	-8°
90°	0.0	1.4	0.0	0.7	0.0	0.7	0.7	0.0	2.1	2.8	2.8
80°	0.7	98.6	105.7	115.0	126.3	136.3	144.8	149.0	153.3	156.8	158.3
72°	0.7	105.7	125.6	142.6	156.1	168.2	183.1	203.0	226.4	247.0	261.2
64°	0.7	115.0	142.6	165.4	195.2	241.3	306.6	376.1	461.3	551.4	628.8
56°	0.7	126.3	156.1	195.2	263.3	381.8	567.0	1107.1	2253.9	3394.4	4165.1
48°	0.7	136.3	168.2	241.3	381.8	744.5	1606.7	3654.1	6447.4	8909.3	10500.4
40°	0.0	144.8	183.1	306.6	567.0	1606.7	4648.4	10115.8	13339.9	15077.2	15951.5
32°	0.0	149.0	203.0	376.1	1107.1	3654.1	10112.2	13874.2	18070.6	23011.4	27717.3
24°	0.0	153.3	226.4	461.3	2253.9	6447.4	13338.4	18070.6	27226.9	38449.8	48403.7
16°	0.7	156.8	247.0	551.4	3394.4	8909.3	15075.0	23011.4	38449.8	55256.4	68495.5
8°	0.7	158.3	261.2	628.8	4165.1	10500.4	15951.5	27717.3	48403.7	68495.5	84126.9
0°	0.7	159.7	269.0	664.3	4506.5	11210.8	16446.8	29964.8	52725.7	74407.8	97092.7
-8°	0.7	158.3	261.2	628.8	4165.1	10500.4	15951.5	27717.3	48403.7	68495.5	84126.9
-16°	0.7	156.8	247.0	551.4	3394.4	8909.3	15075.0	23011.4	38449.8	55256.4	68495.5
-24°	0.0	153.3	226.4	461.3	2253.9	6447.4	13338.4	18070.6	27226.9	38449.8	48403.7
-32°	0.0	149.0	203.0	376.1	1107.1	3654.1	10112.2	13874.2	18070.6	23011.4	27717.3
-40°	0.0	144.8	183.1	306.6	567.0	1606.0	4647.7	10112.2	13338.4	15075.0	15951.5
-48°	0.7	136.3	168.2	241.3	381.8	744.5	1606.7	3654.1	6447.4	8909.3	10500.4
-56°	0.7	126.3	156.1	195.2	263.3	381.8	567.0	1107.1	2253.9	3394.4	4165.1
-64°	0.7	115.0	142.6	165.4	195.2	241.3	306.6	376.1	461.3	551.4	628.8
-72°	0.7	105.7	125.6	142.6	156.1	168.2	183.1	203.0	226.4	247.0	261.2
-80°	0.7	98.6	105.7	115.0	126.3	136.3	144.8	149.0	153.3	156.8	158.3
-90°	0.0	0.7	0.0	0.7	0.0	0.7	0.7	0.0	1.4	2.8	2.1



REPORT NUMBER: P210015
 CATALOG NUMBER: EGL91PW*55

CANDELA DISTRIBUTION (continued):

	0°	8°	16°	24°	32°	40°	48°	56°	64°	72°	80°
90°	0.7	2.8	2.8	2.1	0.0	0.7	0.7	0.0	0.7	0.0	1.4
80°	159.7	158.3	156.8	153.3	149.0	144.8	136.3	126.3	115.0	105.7	98.6
72°	269.0	261.2	247.0	226.4	203.0	183.1	168.2	156.1	142.6	125.6	105.7
64°	664.3	628.8	551.4	461.3	376.1	306.6	241.3	195.2	165.4	142.6	115.0
56°	4506.5	4165.1	3394.4	2253.9	1107.1	567.0	381.8	263.3	195.2	156.1	126.3
48°	11210.8	10500.4	8909.3	6447.4	3654.1	1606.7	744.5	381.8	241.3	168.2	136.3
40°	16446.8	15951.5	15077.2	13339.9	10115.8	4649.1	1606.7	567.0	306.6	183.1	144.8
32°	29964.8	27717.3	23011.4	18070.6	13874.2	10115.1	3654.1	1107.1	376.1	203.0	149.0
24°	52725.7	48403.7	38449.8	27226.9	18070.6	13339.9	6447.4	2253.9	461.3	226.4	153.3
16°	74407.8	68495.5	55256.4	38449.8	23011.4	15077.2	8909.3	3394.4	551.4	247.0	156.8
8°	97092.7	84126.9	68495.5	48403.7	27717.3	15951.5	10500.4	4165.1	628.8	261.2	158.3
0°	135266.4	97092.7	74407.8	52725.7	29964.8	16446.8	11210.8	4506.5	664.3	269.0	159.7
-8°	97092.7	84126.9	68495.5	48403.7	27717.3	15951.5	10500.4	4165.1	628.8	261.2	158.3
-16°	74407.8	68495.5	55256.4	38449.8	23011.4	15077.2	8909.3	3394.4	551.4	247.0	156.8
-24°	52725.7	48403.7	38449.8	27226.9	18070.6	13339.9	6447.4	2253.9	461.3	226.4	153.3
-32°	29964.8	27717.3	23011.4	18070.6	13874.2	10115.1	3654.1	1107.1	376.1	203.0	149.0
-40°	16446.8	15951.5	15075.0	13338.4	10112.2	4648.4	1606.0	567.0	306.6	183.1	144.8
-48°	11210.8	10500.4	8909.3	6447.4	3654.1	1606.7	744.5	381.8	241.3	168.2	136.3
-56°	4506.5	4165.1	3394.4	2253.9	1107.1	567.0	381.8	263.3	195.2	156.1	126.3
-64°	664.3	628.8	551.4	461.3	376.1	306.6	241.3	195.2	165.4	142.6	115.0
-72°	269.0	261.2	247.0	226.4	203.0	183.1	168.2	156.1	142.6	125.6	105.7
-80°	159.7	158.3	156.8	153.3	149.0	144.8	136.3	126.3	115.0	105.7	98.6
-90°	0.7	2.1	2.8	1.4	0.0	0.7	0.7	0.0	0.7	0.0	0.7



REPORT NUMBER: P210015
CATALOG NUMBER: EGL91PW*55

CANDELA DISTRIBUTION (continued):

	90°
90°	0.0
80°	0.7
72°	0.7
64°	0.7
56°	0.7
48°	0.7
40°	0.7
32°	0.0
24°	0.0
16°	0.7
8°	0.7
0°	0.7
-8°	0.7
-16°	0.7
-24°	0.0
-32°	0.0
-40°	0.7
-48°	0.7
-56°	0.7
-64°	0.7
-72°	0.7
-80°	0.7
-90°	0.0

(END OF REPORT)







Horizontal Angle (degrees)



Horizontal Angle (degrees)

