

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P366897

Luminaire Tested: **PMM-SA1C-730-U-SLR-HSS**

Issue Date: 12/2/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P366897  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1910-543-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/2/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: PMM-SA1C-730-U-SLR-HSS  
Description: MESA POST TOP DECORATIVE LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4167 lumens  
Efficiency: N/A  
Efficacy: 70.6 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G1  
  
Input Watts (W): 59  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P366897  
 CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.1 fc  
 Type IV - Short - N/A

REPORT NUMBER: P366897  
CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 270-Deg Lateral    - - - Horizontal Cone Through 62.5-Deg Vertical

REPORT NUMBER: P366897  
 CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 695.8    | 0.0    | 695.8  |
|                    | % Fixture | 16.7     | 0.0    | 16.7   |
| <b>Street Side</b> | Lumens    | 3471.2   | 0.0    | 3471.2 |
|                    | % Fixture | 83.3     | 0.0    | 83.3   |
| <b>Total</b>       | Lumens    | 4167.0   | 0.0    | 4167.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 56.1   | 1.3       |
| 10°-20°   | 146.6  | 3.5       |
| 20°-30°   | 236.9  | 5.7       |
| 30°-40°   | 396.7  | 9.5       |
| 40°-50°   | 648.6  | 15.6      |
| 50°-60°   | 960.1  | 23.0      |
| 60°-70°   | 1102.2 | 26.5      |
| 70°-80°   | 545.0  | 13.1      |
| 80°-90°   | 74.9   | 1.8       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 4167.0 | 100.0     |
| 0°-180°   | 4167.0 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P366897  
 CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 324.6  | 7.8       |                         |      |         |
| FM (30°-60°)   | 1658.7 | 39.8      |                         |      |         |
| FH (60°-80°)   | 1417.0 | 34.0      |                         |      | G1/1800 |
| FVH (80°-90°)  | 70.9   | 1.7       |                         |      | G1/100  |
| BL (0°-30°)    | 114.9  | 2.8       | B1/500                  |      |         |
| BM (30°-60°)   | 346.7  | 8.3       | B1/1000                 |      |         |
| BH (60°-80°)   | 230.2  | 5.5       | B1/500                  |      | G1/500  |
| BVH (80°-90°)  | 4.0    | 0.1       |                         |      | G0/10   |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G1**  
 Type IV Short





REPORT NUMBER: P366897

CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°     | 7.5°   | 10°    | 12.5°  | 15°   | 17.5° | 20°   | 22.5° | 25°   |
|--------|--------|--------|--------|--------|--------|--------|-------|-------|-------|-------|-------|
| 0°     | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1 | 502.1 | 502.1 | 502.1 | 502.1 |
| 2.5°   | 665.8  | 674.1  | 682.2  | 666.8  | 651.3  | 635.9  | 620.4 | 606.7 | 592.9 | 578.9 | 565.1 |
| 5°     | 856.8  | 841.6  | 826.4  | 805.5  | 784.6  | 763.7  | 742.8 | 733.0 | 723.3 | 713.5 | 703.8 |
| 7.5°   | 923.3  | 896.2  | 868.9  | 850.4  | 832.1  | 813.5  | 795.0 | 765.8 | 736.3 | 707.1 | 677.7 |
| 10°    | 871.0  | 842.3  | 813.3  | 797.2  | 781.0  | 764.9  | 748.7 | 712.4 | 675.8 | 639.4 | 602.9 |
| 12.5°  | 895.0  | 863.9  | 832.8  | 799.5  | 766.3  | 733.0  | 699.8 | 672.0 | 643.9 | 616.2 | 588.1 |
| 15°    | 911.6  | 876.0  | 840.2  | 802.1  | 764.1  | 726.1  | 688.1 | 655.4 | 622.8 | 590.0 | 557.3 |
| 17.5°  | 1009.3 | 958.2  | 907.1  | 848.7  | 790.3  | 731.8  | 673.4 | 635.4 | 597.6 | 559.6 | 521.6 |
| 20°    | 1134.7 | 1062.2 | 989.6  | 910.5  | 831.4  | 752.3  | 673.2 | 625.9 | 578.6 | 531.4 | 484.1 |
| 22.5°  | 1280.5 | 1190.0 | 1099.3 | 1001.7 | 904.3  | 806.7  | 709.0 | 641.1 | 573.2 | 505.2 | 437.3 |
| 25°    | 1427.3 | 1345.6 | 1263.9 | 1132.6 | 1001.2 | 869.6  | 738.3 | 652.0 | 565.6 | 479.3 | 392.9 |
| 27.5°  | 1692.4 | 1546.3 | 1400.3 | 1233.0 | 1066.0 | 898.8  | 731.6 | 632.8 | 534.0 | 434.9 | 336.1 |
| 30°    | 1865.8 | 1753.5 | 1640.9 | 1420.0 | 1199.3 | 978.4  | 757.5 | 632.3 | 507.1 | 381.7 | 256.5 |
| 32.5°  | 2073.2 | 1908.8 | 1744.2 | 1504.5 | 1264.9 | 1025.2 | 785.5 | 638.5 | 491.2 | 344.2 | 196.9 |
| 35°    | 2306.2 | 2127.3 | 1948.5 | 1644.9 | 1341.3 | 1037.5 | 734.0 | 591.5 | 448.9 | 306.4 | 163.9 |
| 37.5°  | 2717.8 | 2418.6 | 2119.3 | 1765.3 | 1411.2 | 1057.3 | 703.1 | 560.8 | 418.3 | 276.0 | 133.5 |
| 40°    | 2951.6 | 2665.8 | 2380.1 | 1937.8 | 1495.5 | 1053.2 | 610.9 | 484.6 | 358.4 | 232.1 | 105.7 |
| 42.5°  | 3255.6 | 2893.1 | 2530.4 | 2036.1 | 1541.8 | 1047.5 | 553.2 | 436.3 | 319.5 | 202.4 | 85.5  |
| 45°    | 3435.9 | 3025.2 | 2614.5 | 2078.9 | 1543.2 | 1007.6 | 472.0 | 370.8 | 269.6 | 168.4 | 67.2  |
| 47.5°  | 3549.7 | 3137.8 | 2725.9 | 2150.9 | 1576.0 | 1001.0 | 425.9 | 332.8 | 239.7 | 146.6 | 53.4  |
| 50°    | 3607.4 | 3194.3 | 2781.0 | 2190.0 | 1599.1 | 1007.8 | 416.9 | 324.2 | 231.4 | 138.7 | 45.8  |
| 52.5°  | 3667.5 | 3269.2 | 2870.6 | 2258.0 | 1645.4 | 1032.8 | 420.2 | 325.7 | 231.4 | 136.8 | 42.3  |
| 55°    | 3788.9 | 3396.0 | 3002.9 | 2355.4 | 1707.9 | 1060.3 | 412.8 | 319.7 | 226.6 | 133.3 | 40.1  |
| 57.5°  | 3938.0 | 3518.1 | 3097.9 | 2426.6 | 1755.4 | 1084.1 | 412.8 | 319.2 | 225.7 | 131.8 | 38.2  |
| 60°    | 3909.8 | 3454.0 | 2997.9 | 2346.6 | 1695.3 | 1043.7 | 392.4 | 303.3 | 214.5 | 125.4 | 36.3  |
| 62.5°  | 3715.7 | 3220.9 | 2725.9 | 2124.0 | 1521.9 | 920.0  | 317.8 | 246.8 | 175.8 | 104.5 | 33.5  |
| 65°    | 3487.7 | 2962.5 | 2437.1 | 1883.2 | 1329.0 | 775.1  | 220.9 | 173.4 | 125.7 | 78.1  | 30.4  |
| 67.5°  | 3213.1 | 2653.0 | 2092.9 | 1600.3 | 1107.9 | 615.2  | 122.6 | 98.8  | 75.1  | 51.1  | 27.3  |
| 70°    | 2736.6 | 2158.5 | 1580.1 | 1201.4 | 823.0  | 444.4  | 65.8  | 55.6  | 45.4  | 35.2  | 24.9  |
| 72.5°  | 2054.4 | 1524.7 | 995.0  | 755.8  | 516.9  | 277.7  | 38.5  | 34.7  | 30.6  | 26.8  | 22.8  |
| 75°    | 1397.9 | 1001.0 | 604.0  | 459.9  | 315.9  | 171.7  | 27.6  | 25.7  | 23.5  | 21.6  | 19.5  |
| 77.5°  | 950.4  | 687.4  | 424.5  | 324.0  | 223.5  | 123.0  | 22.6  | 21.4  | 20.2  | 18.8  | 17.6  |
| 80°    | 593.4  | 406.2  | 219.0  | 168.6  | 118.1  | 67.7   | 17.1  | 16.4  | 15.7  | 14.7  | 14.0  |
| 82.5°  | 415.0  | 248.2  | 81.5   | 63.7   | 45.8   | 27.8   | 10.0  | 10.2  | 10.5  | 10.5  | 10.7  |
| 85°    | 174.1  | 94.1   | 14.0   | 11.9   | 9.7    | 7.6    | 5.5   | 5.9   | 6.7   | 7.1   | 7.6   |
| 87.5°  | 3.1    | 1.7    | 0.0    | 0.5    | 1.2    | 1.7    | 2.1   | 2.9   | 3.3   | 4.0   | 4.5   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P366897  
 CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 2.5° | 5°  | 7.5° | 10° | 12.5° | 15° | 17.5° | 20° | 22.5° | 25° |
|--------|-----|------|-----|------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |





REPORT NUMBER: P366897

CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30°   | 32.5° | 35°   | 37.5° | 40°   | 42.5° | 45°   | 47.5° | 50°   | 52.5° |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 502.1 | 502.1 | 502.1 | 502.1 | 502.1 | 502.1 | 502.1 | 502.1 | 502.1 | 502.1 | 502.1 |
| 2.5°   | 568.7 | 572.2 | 575.5 | 579.1 | 576.3 | 573.6 | 570.8 | 567.9 | 563.7 | 559.6 | 555.4 |
| 5°     | 691.9 | 680.1 | 668.2 | 656.3 | 638.2 | 620.2 | 601.9 | 583.9 | 581.7 | 579.6 | 577.2 |
| 7.5°   | 649.9 | 622.1 | 594.1 | 566.3 | 540.1 | 514.0 | 487.9 | 461.8 | 453.7 | 445.8 | 437.8 |
| 10°    | 581.5 | 560.1 | 538.5 | 517.1 | 498.3 | 479.3 | 460.6 | 441.6 | 421.9 | 402.1 | 382.2 |
| 12.5°  | 565.8 | 543.5 | 520.9 | 498.6 | 481.5 | 464.4 | 447.3 | 430.2 | 408.1 | 386.0 | 363.9 |
| 15°    | 533.0 | 508.8 | 484.6 | 460.3 | 437.5 | 414.7 | 391.7 | 368.9 | 342.3 | 315.7 | 289.1 |
| 17.5°  | 492.9 | 464.4 | 435.6 | 406.9 | 377.0 | 347.0 | 317.1 | 287.2 | 256.5 | 226.1 | 195.5 |
| 20°    | 445.1 | 406.2 | 367.0 | 328.0 | 291.0 | 253.9 | 216.6 | 179.6 | 160.3 | 141.3 | 122.1 |
| 22.5°  | 386.9 | 336.3 | 286.0 | 235.4 | 205.0 | 174.3 | 143.9 | 113.3 | 105.0 | 96.7  | 88.4  |
| 25°    | 335.6 | 278.4 | 221.1 | 163.9 | 144.7 | 125.4 | 106.2 | 86.9  | 83.1  | 79.1  | 75.3  |
| 27.5°  | 282.2 | 228.5 | 174.6 | 120.7 | 109.7 | 98.6  | 87.6  | 76.5  | 73.9  | 71.5  | 68.9  |
| 30°    | 216.4 | 176.2 | 135.9 | 95.7  | 88.6  | 81.5  | 74.1  | 67.0  | 65.8  | 64.4  | 63.2  |
| 32.5°  | 167.7 | 138.2 | 109.0 | 79.6  | 75.5  | 71.5  | 67.5  | 63.4  | 61.5  | 59.6  | 57.5  |
| 35°    | 140.1 | 116.6 | 92.9  | 69.1  | 66.3  | 63.2  | 60.3  | 57.2  | 55.3  | 53.2  | 51.3  |
| 37.5°  | 116.2 | 99.1  | 81.7  | 64.4  | 61.3  | 58.2  | 54.9  | 51.8  | 50.4  | 48.9  | 47.5  |
| 40°    | 95.7  | 85.7  | 75.8  | 65.8  | 61.3  | 56.8  | 52.3  | 47.7  | 46.6  | 45.4  | 44.2  |
| 42.5°  | 79.1  | 72.7  | 66.0  | 59.6  | 56.3  | 53.2  | 49.9  | 46.6  | 44.9  | 43.0  | 41.3  |
| 45°    | 63.9  | 60.3  | 57.0  | 53.4  | 53.7  | 53.9  | 53.9  | 54.2  | 49.9  | 45.4  | 41.1  |
| 47.5°  | 51.8  | 50.1  | 48.2  | 46.6  | 48.5  | 50.4  | 52.0  | 53.9  | 49.4  | 44.9  | 40.1  |
| 50°    | 44.4  | 43.2  | 41.8  | 40.4  | 42.3  | 44.4  | 46.3  | 48.2  | 46.3  | 44.7  | 42.8  |
| 52.5°  | 40.6  | 39.0  | 37.3  | 35.6  | 36.3  | 37.3  | 38.0  | 38.7  | 38.7  | 38.7  | 38.7  |
| 55°    | 38.2  | 36.6  | 34.7  | 32.8  | 32.1  | 31.1  | 30.4  | 29.5  | 28.3  | 27.3  | 26.1  |
| 57.5°  | 36.3  | 34.4  | 32.3  | 30.4  | 29.2  | 27.8  | 26.6  | 25.2  | 24.0  | 22.6  | 21.4  |
| 60°    | 34.4  | 32.5  | 30.4  | 28.5  | 27.3  | 26.1  | 24.7  | 23.5  | 22.1  | 20.9  | 19.5  |
| 62.5°  | 31.8  | 30.2  | 28.5  | 26.8  | 25.7  | 24.7  | 23.5  | 22.3  | 20.9  | 19.5  | 17.8  |
| 65°    | 29.0  | 27.8  | 26.4  | 24.9  | 23.8  | 22.6  | 21.4  | 20.2  | 18.8  | 17.6  | 16.2  |
| 67.5°  | 26.4  | 25.2  | 24.2  | 23.0  | 21.6  | 20.4  | 19.0  | 17.6  | 16.6  | 15.7  | 14.5  |
| 70°    | 24.2  | 23.3  | 22.6  | 21.6  | 20.2  | 19.0  | 17.6  | 16.2  | 15.4  | 14.5  | 13.8  |
| 72.5°  | 22.1  | 21.4  | 20.4  | 19.7  | 18.5  | 17.3  | 16.2  | 15.0  | 14.3  | 13.5  | 12.8  |
| 75°    | 19.0  | 18.5  | 18.1  | 17.6  | 16.4  | 15.2  | 13.8  | 12.6  | 12.4  | 12.1  | 11.9  |
| 77.5°  | 17.1  | 16.9  | 16.4  | 15.9  | 14.7  | 13.5  | 12.4  | 11.2  | 11.4  | 11.6  | 11.6  |
| 80°    | 14.0  | 14.0  | 13.8  | 13.8  | 12.8  | 11.9  | 10.7  | 9.7   | 10.2  | 10.9  | 11.4  |
| 82.5°  | 10.7  | 10.7  | 10.7  | 10.7  | 9.7   | 8.8   | 7.8   | 6.9   | 7.6   | 8.1   | 8.8   |
| 85°    | 7.4   | 7.1   | 6.9   | 6.7   | 5.9   | 5.5   | 4.8   | 4.0   | 5.0   | 5.7   | 6.7   |
| 87.5°  | 4.5   | 4.8   | 4.8   | 4.8   | 4.3   | 3.6   | 3.1   | 2.4   | 2.9   | 3.1   | 3.6   |
| 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P366897  
 CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30° | 32.5° | 35° | 37.5° | 40° | 42.5° | 45° | 47.5° | 50° | 52.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |



REPORT NUMBER: P366897

CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 55°   | 57.5° | 60°   | 62.5° | 65°   | 67.5° | 70°   | 72.5° | 75°   | 77.5° | 80°   |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 502.1 | 502.1 | 502.1 | 502.1 | 502.1 | 502.1 | 502.1 | 502.1 | 502.1 | 502.1 | 502.1 |
| 2.5°   | 551.1 | 543.9 | 536.8 | 529.5 | 522.3 | 505.7 | 489.1 | 472.5 | 455.8 | 468.2 | 480.3 |
| 5°     | 575.1 | 561.3 | 547.3 | 533.5 | 519.5 | 513.3 | 507.4 | 501.2 | 495.0 | 496.0 | 497.2 |
| 7.5°   | 429.7 | 420.7 | 411.6 | 402.4 | 393.4 | 391.5 | 389.8 | 387.9 | 386.0 | 390.0 | 393.8 |
| 10°    | 362.5 | 349.9 | 337.1 | 324.5 | 311.6 | 304.8 | 297.9 | 291.0 | 284.1 | 283.4 | 282.4 |
| 12.5°  | 341.8 | 322.6 | 303.6 | 284.3 | 265.1 | 250.1 | 235.2 | 220.2 | 205.2 | 206.4 | 207.6 |
| 15°    | 262.5 | 243.2 | 224.2 | 205.0 | 185.8 | 173.6 | 161.3 | 149.2 | 136.8 | 133.3 | 129.7 |
| 17.5°  | 164.8 | 150.6 | 136.3 | 121.9 | 107.6 | 103.6 | 99.8  | 95.7  | 91.7  | 90.5  | 89.3  |
| 20°    | 102.9 | 96.7  | 90.5  | 84.1  | 77.9  | 77.0  | 76.0  | 75.1  | 74.1  | 74.8  | 75.5  |
| 22.5°  | 80.0  | 77.4  | 74.6  | 72.0  | 69.1  | 68.2  | 67.2  | 66.3  | 65.3  | 66.0  | 66.5  |
| 25°    | 71.3  | 69.4  | 67.5  | 65.6  | 63.7  | 62.7  | 61.5  | 60.6  | 59.4  | 59.9  | 60.6  |
| 27.5°  | 66.3  | 64.6  | 62.9  | 61.3  | 59.6  | 58.0  | 56.5  | 54.9  | 53.2  | 54.2  | 54.9  |
| 30°    | 61.8  | 59.9  | 58.2  | 56.3  | 54.4  | 52.7  | 51.1  | 49.2  | 47.5  | 48.5  | 49.4  |
| 32.5°  | 55.6  | 53.9  | 52.0  | 50.4  | 48.5  | 47.5  | 46.6  | 45.4  | 44.4  | 45.1  | 45.6  |
| 35°    | 49.2  | 47.7  | 46.6  | 45.1  | 43.7  | 42.8  | 42.0  | 41.1  | 40.1  | 40.4  | 40.9  |
| 37.5°  | 46.1  | 44.4  | 42.8  | 41.1  | 39.4  | 39.0  | 38.5  | 37.8  | 37.3  | 37.3  | 37.3  |
| 40°    | 43.0  | 41.3  | 39.7  | 37.8  | 36.1  | 35.4  | 34.7  | 34.0  | 33.3  | 33.3  | 33.3  |
| 42.5°  | 39.4  | 37.8  | 36.1  | 34.4  | 32.8  | 32.1  | 31.1  | 30.4  | 29.5  | 29.5  | 29.5  |
| 45°    | 36.6  | 34.9  | 33.5  | 31.8  | 30.2  | 29.0  | 27.8  | 26.4  | 25.2  | 24.9  | 24.7  |
| 47.5°  | 35.6  | 33.3  | 30.9  | 28.5  | 26.1  | 24.9  | 23.8  | 22.3  | 21.1  | 20.9  | 20.7  |
| 50°    | 40.9  | 36.1  | 31.4  | 26.6  | 21.9  | 20.9  | 20.0  | 19.0  | 18.1  | 17.6  | 17.3  |
| 52.5°  | 38.7  | 33.7  | 28.7  | 23.8  | 18.8  | 18.1  | 17.3  | 16.6  | 15.9  | 15.4  | 15.0  |
| 55°    | 24.9  | 22.8  | 20.9  | 18.8  | 16.6  | 16.2  | 15.7  | 15.0  | 14.5  | 14.0  | 13.5  |
| 57.5°  | 20.0  | 18.8  | 17.8  | 16.6  | 15.4  | 15.0  | 14.5  | 13.8  | 13.3  | 12.6  | 12.1  |
| 60°    | 18.1  | 17.1  | 16.2  | 15.2  | 14.3  | 13.8  | 13.3  | 12.8  | 12.4  | 11.6  | 11.2  |
| 62.5°  | 16.4  | 15.7  | 15.0  | 14.3  | 13.5  | 13.1  | 12.6  | 12.1  | 11.6  | 10.9  | 10.2  |
| 65°    | 14.7  | 14.3  | 13.8  | 13.3  | 12.8  | 12.4  | 11.9  | 11.2  | 10.7  | 10.0  | 9.3   |
| 67.5°  | 13.5  | 13.3  | 13.1  | 12.8  | 12.6  | 12.1  | 11.4  | 10.9  | 10.2  | 9.5   | 8.6   |
| 70°    | 12.8  | 12.8  | 12.8  | 12.6  | 12.6  | 12.1  | 11.4  | 10.9  | 10.2  | 9.3   | 8.6   |
| 72.5°  | 12.1  | 12.4  | 12.6  | 12.6  | 12.8  | 12.1  | 11.4  | 10.7  | 10.0  | 9.0   | 8.3   |
| 75°    | 11.6  | 11.9  | 12.1  | 12.1  | 12.4  | 11.9  | 11.4  | 10.7  | 10.2  | 9.3   | 8.3   |
| 77.5°  | 11.9  | 12.1  | 12.1  | 12.4  | 12.4  | 11.9  | 11.4  | 10.7  | 10.2  | 9.0   | 7.8   |
| 80°    | 11.9  | 11.6  | 11.4  | 10.9  | 10.7  | 9.7   | 8.8   | 7.6   | 6.7   | 5.2   | 4.0   |
| 82.5°  | 9.3   | 8.8   | 8.6   | 8.1   | 7.6   | 6.7   | 5.7   | 4.8   | 3.8   | 2.9   | 1.9   |
| 85°    | 7.4   | 6.9   | 6.7   | 6.2   | 5.7   | 5.0   | 4.0   | 3.3   | 2.4   | 1.9   | 1.2   |
| 87.5°  | 3.8   | 3.6   | 3.1   | 2.9   | 2.4   | 1.9   | 1.2   | 0.7   | 0.0   | 0.0   | 0.0   |
| 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P366897  
 CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 55° | 57.5° | 60° | 62.5° | 65° | 67.5° | 70° | 72.5° | 75° | 77.5° | 80° |
|--------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |



REPORT NUMBER: P366897

CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85°   | 87.5° | 90°   | 92.5° | 95°   | 97.5° | 100°  | 102.5° | 105°  | 107.5° |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|--------|-------|--------|
| 0°     | 502.1 | 502.1 | 502.1 | 502.1 | 502.1 | 502.1 | 502.1 | 502.1 | 502.1  | 502.1 | 502.1  |
| 2.5°   | 492.6 | 504.8 | 503.1 | 501.4 | 509.3 | 517.1 | 511.4 | 505.9 | 500.2  | 494.5 | 482.7  |
| 5°     | 498.1 | 499.1 | 497.4 | 495.5 | 495.7 | 496.0 | 492.2 | 488.4 | 484.6  | 480.8 | 480.1  |
| 7.5°   | 397.9 | 401.7 | 406.9 | 411.9 | 412.1 | 412.1 | 409.3 | 406.4 | 403.3  | 400.5 | 401.9  |
| 10°    | 281.7 | 280.8 | 282.2 | 283.6 | 283.4 | 282.9 | 290.5 | 298.1 | 305.5  | 313.1 | 307.6  |
| 12.5°  | 208.6 | 209.7 | 203.8 | 197.9 | 200.0 | 201.9 | 203.1 | 204.3 | 205.5  | 206.7 | 210.0  |
| 15°    | 126.1 | 122.6 | 118.3 | 114.0 | 116.2 | 118.1 | 120.2 | 122.1 | 124.2  | 126.1 | 128.3  |
| 17.5°  | 87.9  | 86.7  | 84.8  | 82.7  | 82.9  | 83.1  | 83.4  | 83.6  | 83.6   | 83.8  | 84.3   |
| 20°    | 76.2  | 77.0  | 75.5  | 73.9  | 73.4  | 72.7  | 72.2  | 71.7  | 71.0   | 70.5  | 69.8   |
| 22.5°  | 67.2  | 67.7  | 67.9  | 67.9  | 67.0  | 65.8  | 64.8  | 64.1  | 63.2   | 62.2  | 61.8   |
| 25°    | 61.0  | 61.5  | 61.0  | 60.3  | 59.9  | 59.4  | 58.9  | 58.2  | 57.7   | 57.0  | 56.8   |
| 27.5°  | 55.8  | 56.5  | 56.5  | 56.3  | 55.8  | 55.1  | 53.9  | 53.0  | 51.8   | 50.6  | 50.8   |
| 30°    | 50.4  | 51.3  | 51.3  | 51.1  | 50.8  | 50.6  | 49.4  | 48.2  | 47.0   | 45.8  | 46.3   |
| 32.5°  | 46.3  | 46.8  | 46.6  | 46.3  | 46.3  | 46.1  | 45.1  | 44.4  | 43.5   | 42.5  | 42.5   |
| 35°    | 41.1  | 41.3  | 41.3  | 41.3  | 41.3  | 41.1  | 40.4  | 39.7  | 39.0   | 38.2  | 38.5   |
| 37.5°  | 37.3  | 37.3  | 38.0  | 38.5  | 38.0  | 37.5  | 37.1  | 36.3  | 35.9   | 35.2  | 35.2   |
| 40°    | 33.0  | 33.0  | 33.7  | 34.2  | 33.7  | 33.3  | 33.0  | 32.5  | 32.3   | 31.8  | 31.8   |
| 42.5°  | 29.2  | 29.2  | 29.9  | 30.4  | 30.4  | 30.2  | 29.7  | 29.2  | 28.7   | 28.3  | 28.5   |
| 45°    | 24.5  | 24.2  | 25.4  | 26.4  | 25.9  | 25.4  | 25.4  | 25.2  | 25.2   | 24.9  | 25.2   |
| 47.5°  | 20.2  | 20.0  | 20.9  | 21.9  | 21.6  | 21.1  | 21.1  | 21.1  | 21.1   | 21.1  | 21.4   |
| 50°    | 16.9  | 16.4  | 17.3  | 18.1  | 17.8  | 17.3  | 17.3  | 17.6  | 17.6   | 17.6  | 17.8   |
| 52.5°  | 14.5  | 14.0  | 14.7  | 15.2  | 15.0  | 14.7  | 14.7  | 15.0  | 15.0   | 15.0  | 15.2   |
| 55°    | 12.8  | 12.4  | 13.1  | 13.5  | 13.3  | 12.8  | 13.1  | 13.1  | 13.3   | 13.3  | 13.3   |
| 57.5°  | 11.4  | 10.7  | 11.2  | 11.6  | 11.6  | 11.4  | 11.6  | 11.6  | 11.9   | 11.9  | 11.9   |
| 60°    | 10.5  | 9.7   | 10.2  | 10.5  | 10.5  | 10.2  | 10.5  | 10.5  | 10.7   | 10.7  | 10.7   |
| 62.5°  | 9.3   | 8.6   | 9.0   | 9.3   | 9.3   | 9.0   | 9.3   | 9.3   | 9.5    | 9.5   | 9.5    |
| 65°    | 8.3   | 7.6   | 7.8   | 8.1   | 8.1   | 8.1   | 8.3   | 8.3   | 8.6    | 8.6   | 8.6    |
| 67.5°  | 7.8   | 6.9   | 7.1   | 7.4   | 7.4   | 7.4   | 7.6   | 7.6   | 7.8    | 7.8   | 8.1    |
| 70°    | 7.6   | 6.7   | 6.9   | 6.9   | 7.1   | 7.1   | 7.1   | 7.4   | 7.4    | 7.4   | 7.4    |
| 72.5°  | 7.4   | 6.4   | 6.4   | 6.4   | 6.7   | 6.7   | 6.7   | 6.9   | 6.9    | 6.9   | 6.9    |
| 75°    | 7.4   | 6.4   | 6.2   | 5.9   | 6.2   | 6.2   | 6.2   | 6.4   | 6.4    | 6.4   | 6.4    |
| 77.5°  | 6.4   | 5.2   | 4.8   | 4.0   | 4.8   | 5.2   | 5.5   | 5.5   | 5.7    | 5.7   | 5.7    |
| 80°    | 2.6   | 1.2   | 0.7   | 0.0   | 0.2   | 0.5   | 0.7   | 1.0   | 1.2    | 1.4   | 1.7    |
| 82.5°  | 1.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 85°    | 0.7   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |



REPORT NUMBER: P366897  
 CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85° | 87.5° | 90° | 92.5° | 95° | 97.5° | 100° | 102.5° | 105° | 107.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|------|--------|------|--------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P366897

CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 110°  | 112.5° | 115°  | 117.5° | 120°  | 122.5° | 125°  | 127.5° | 130°  | 132.5° | 135°  |
|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0°     | 502.1 | 502.1  | 502.1 | 502.1  | 502.1 | 502.1  | 502.1 | 502.1  | 502.1 | 502.1  | 502.1 |
| 2.5°   | 470.8 | 458.9  | 447.0 | 452.7  | 458.4 | 464.1  | 469.8 | 469.4  | 468.7 | 468.2  | 467.5 |
| 5°     | 479.6 | 478.9  | 478.2 | 474.8  | 471.7 | 468.4  | 465.1 | 464.4  | 463.4 | 462.7  | 461.8 |
| 7.5°   | 403.3 | 404.5  | 405.9 | 402.1  | 398.3 | 394.5  | 390.7 | 381.0  | 371.3 | 361.3  | 351.5 |
| 10°    | 302.1 | 296.4  | 291.0 | 290.5  | 290.0 | 289.6  | 289.1 | 288.1  | 287.2 | 286.0  | 285.0 |
| 12.5°  | 213.5 | 216.9  | 220.2 | 219.0  | 217.8 | 216.4  | 215.2 | 216.9  | 218.8 | 220.4  | 222.1 |
| 15°    | 130.2 | 132.3  | 134.2 | 138.5  | 142.8 | 147.0  | 151.3 | 153.0  | 154.9 | 156.5  | 158.2 |
| 17.5°  | 84.8  | 85.0   | 85.5  | 90.3   | 94.8  | 99.5   | 104.0 | 107.1  | 110.2 | 113.1  | 116.2 |
| 20°    | 69.1  | 68.4   | 67.7  | 70.3   | 72.9  | 75.5   | 78.1  | 81.0   | 83.8  | 86.7   | 89.5  |
| 22.5°  | 61.5  | 61.0   | 60.6  | 61.5   | 62.5  | 63.2   | 64.1  | 66.3   | 68.6  | 70.8   | 72.9  |
| 25°    | 56.5  | 56.1   | 55.8  | 56.3   | 56.8  | 57.2   | 57.7  | 58.9   | 60.1  | 61.3   | 62.5  |
| 27.5°  | 50.8  | 51.1   | 51.1  | 51.5   | 51.8  | 52.3   | 52.5  | 53.0   | 53.7  | 54.2   | 54.6  |
| 30°    | 46.6  | 47.0   | 47.3  | 47.7   | 48.0  | 48.5   | 48.7  | 48.5   | 48.2  | 48.0   | 47.7  |
| 32.5°  | 42.5  | 42.3   | 42.3  | 42.8   | 43.0  | 43.5   | 43.7  | 44.2   | 44.7  | 44.9   | 45.4  |
| 35°    | 38.5  | 38.7   | 38.7  | 38.7   | 39.0  | 39.0   | 39.0  | 39.4   | 40.1  | 40.6   | 41.1  |
| 37.5°  | 34.9  | 34.9   | 34.7  | 35.4   | 35.9  | 36.6   | 37.1  | 37.5   | 38.2  | 38.7   | 39.2  |
| 40°    | 31.8  | 31.8   | 31.8  | 32.3   | 32.8  | 33.0   | 33.5  | 34.7   | 35.9  | 37.1   | 38.2  |
| 42.5°  | 28.5  | 28.7   | 28.7  | 29.2   | 29.7  | 29.9   | 30.4  | 31.4   | 32.1  | 33.0   | 33.7  |
| 45°    | 25.4  | 25.7   | 25.9  | 26.4   | 26.6  | 27.1   | 27.3  | 27.8   | 28.0  | 28.5   | 28.7  |
| 47.5°  | 21.9  | 22.1   | 22.3  | 22.8   | 23.0  | 23.5   | 23.8  | 23.5   | 23.5  | 23.3   | 23.0  |
| 50°    | 18.3  | 18.5   | 18.8  | 19.5   | 20.0  | 20.7   | 21.1  | 20.7   | 20.2  | 19.5   | 19.0  |
| 52.5°  | 15.4  | 15.4   | 15.7  | 16.2   | 16.6  | 16.9   | 17.3  | 17.1   | 16.9  | 16.6   | 16.4  |
| 55°    | 13.3  | 13.3   | 13.3  | 13.5   | 13.8  | 14.0   | 14.3  | 14.5   | 14.5  | 14.7   | 14.7  |
| 57.5°  | 11.9  | 11.6   | 11.6  | 11.9   | 12.1  | 12.1   | 12.4  | 12.6   | 12.6  | 12.8   | 12.8  |
| 60°    | 10.7  | 10.5   | 10.5  | 10.7   | 10.9  | 11.2   | 11.4  | 11.4   | 11.4  | 11.2   | 11.2  |
| 62.5°  | 9.5   | 9.5    | 9.5   | 9.7    | 9.7   | 10.0   | 10.0  | 10.0   | 10.2  | 10.2   | 10.2  |
| 65°    | 8.8   | 8.8    | 8.8   | 8.8    | 8.8   | 8.6    | 8.6   | 8.8    | 8.8   | 9.0    | 9.0   |
| 67.5°  | 8.1   | 8.3    | 8.3   | 8.1    | 7.8   | 7.6    | 7.4   | 7.6    | 7.6   | 7.8    | 7.8   |
| 70°    | 7.4   | 7.4    | 7.4   | 7.1    | 6.9   | 6.7    | 6.4   | 6.4    | 6.4   | 6.2    | 6.2   |
| 72.5°  | 6.9   | 6.7    | 6.7   | 6.4    | 5.9   | 5.7    | 5.2   | 5.0    | 5.0   | 4.8    | 4.5   |
| 75°    | 6.4   | 6.2    | 6.2   | 5.7    | 5.2   | 4.8    | 4.3   | 4.0    | 3.6   | 3.3    | 2.9   |
| 77.5°  | 5.7   | 5.7    | 5.7   | 5.0    | 4.5   | 3.8    | 3.1   | 2.6    | 2.1   | 1.4    | 1.0   |
| 80°    | 1.9   | 2.1    | 2.4   | 2.1    | 2.1   | 1.9    | 1.7   | 1.2    | 1.0   | 0.5    | 0.0   |
| 82.5°  | 0.2   | 0.2    | 0.2   | 0.2    | 0.2   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 85°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 87.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P366897  
 CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° | 135° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |





REPORT NUMBER: P366897

CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140°  | 142.5° | 145°  | 147.5° | 150°  | 152.5° | 155°  | 157.5° | 160°  | 162.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0°     | 502.1  | 502.1 | 502.1  | 502.1 | 502.1  | 502.1 | 502.1  | 502.1 | 502.1  | 502.1 | 502.1  |
| 2.5°   | 470.1  | 472.7 | 475.3  | 477.9 | 478.2  | 478.4 | 478.6  | 478.9 | 472.9  | 466.8 | 460.8  |
| 5°     | 466.5  | 471.5 | 476.3  | 481.0 | 478.4  | 475.8 | 473.2  | 470.6 | 470.3  | 470.3 | 470.1  |
| 7.5°   | 352.3  | 352.7 | 353.4  | 353.9 | 354.9  | 355.8 | 356.5  | 357.5 | 361.3  | 365.1 | 368.6  |
| 10°    | 282.0  | 278.9 | 275.5  | 272.4 | 270.1  | 267.5 | 265.1  | 262.5 | 264.4  | 266.5 | 268.4  |
| 12.5°  | 219.5  | 216.9 | 214.0  | 211.4 | 210.5  | 209.5 | 208.3  | 207.4 | 213.5  | 219.7 | 225.7  |
| 15°    | 157.7  | 157.2 | 156.5  | 156.1 | 159.1  | 162.2 | 165.3  | 168.4 | 173.6  | 178.6 | 183.8  |
| 17.5°  | 117.3  | 118.5 | 119.7  | 120.9 | 122.8  | 124.7 | 126.4  | 128.3 | 132.1  | 136.1 | 139.9  |
| 20°    | 91.0   | 92.6  | 94.1   | 95.5  | 95.0   | 94.5  | 93.8   | 93.4  | 96.4   | 99.5  | 102.4  |
| 22.5°  | 74.3   | 75.5  | 77.0   | 78.1  | 78.4   | 78.6  | 78.9   | 79.1  | 81.0   | 82.7  | 84.6   |
| 25°    | 63.7   | 65.1  | 66.3   | 67.5  | 67.7   | 67.9  | 68.2   | 68.4  | 70.8   | 73.2  | 75.3   |
| 27.5°  | 56.3   | 57.7  | 59.4   | 60.8  | 61.3   | 61.8  | 62.2   | 62.7  | 64.1   | 65.3  | 66.7   |
| 30°    | 49.6   | 51.5  | 53.4   | 55.3  | 56.1   | 56.8  | 57.5   | 58.2  | 59.6   | 61.3  | 62.7   |
| 32.5°  | 46.3   | 47.5  | 48.5   | 49.4  | 51.1   | 52.5  | 54.2   | 55.6  | 57.2   | 59.1  | 60.8   |
| 35°    | 42.5   | 43.7  | 45.1   | 46.3  | 47.5   | 48.7  | 49.6   | 50.8  | 51.8   | 52.7  | 53.4   |
| 37.5°  | 40.1   | 41.3  | 42.3   | 43.2  | 43.7   | 44.2  | 44.4   | 44.9  | 45.4   | 45.8  | 46.1   |
| 40°    | 38.2   | 38.0  | 38.0   | 37.8  | 38.2   | 39.0  | 39.4   | 39.9  | 41.3   | 42.5  | 43.9   |
| 42.5°  | 33.3   | 32.5  | 32.1   | 31.4  | 32.5   | 33.5  | 34.7   | 35.6  | 37.5   | 39.4  | 41.3   |
| 45°    | 28.3   | 27.8  | 27.1   | 26.6  | 28.3   | 29.9  | 31.6   | 33.3  | 35.4   | 37.3  | 39.4   |
| 47.5°  | 23.3   | 23.5  | 23.5   | 23.8  | 25.4   | 27.1  | 28.5   | 30.2  | 32.3   | 34.4  | 36.6   |
| 50°    | 19.5   | 20.0  | 20.4   | 20.9  | 22.6   | 24.0  | 25.7   | 27.1  | 29.5   | 31.6  | 34.0   |
| 52.5°  | 17.1   | 17.8  | 18.3   | 19.0  | 20.4   | 22.1  | 23.5   | 24.9  | 27.1   | 29.2  | 31.4   |
| 55°    | 15.4   | 16.4  | 17.1   | 17.8  | 19.0   | 20.2  | 21.4   | 22.6  | 24.7   | 26.8  | 28.7   |
| 57.5°  | 13.5   | 14.3  | 15.0   | 15.7  | 16.9   | 18.1  | 19.0   | 20.2  | 22.1   | 24.2  | 26.1   |
| 60°    | 11.9   | 12.4  | 13.1   | 13.5  | 14.5   | 15.7  | 16.6   | 17.6  | 19.5   | 21.4  | 23.0   |
| 62.5°  | 10.5   | 10.9  | 11.2   | 11.4  | 12.4   | 13.3  | 14.3   | 15.2  | 16.9   | 18.8  | 20.4   |
| 65°    | 9.3    | 9.5   | 9.5    | 9.7   | 10.5   | 11.4  | 12.1   | 12.8  | 14.7   | 16.4  | 18.3   |
| 67.5°  | 7.8    | 8.1   | 8.1    | 8.1   | 8.8    | 9.5   | 10.2   | 10.9  | 12.6   | 14.5  | 16.2   |
| 70°    | 6.2    | 6.4   | 6.4    | 6.4   | 7.1    | 8.1   | 8.8    | 9.5   | 10.9   | 12.4  | 13.8   |
| 72.5°  | 4.8    | 4.8   | 5.0    | 5.0   | 5.7    | 6.7   | 7.4    | 8.1   | 9.3    | 10.5  | 11.6   |
| 75°    | 3.1    | 3.3   | 3.3    | 3.6   | 4.3    | 5.2   | 5.9    | 6.7   | 7.8    | 9.0   | 10.0   |
| 77.5°  | 1.2    | 1.7   | 1.9    | 2.1   | 2.9    | 3.6   | 4.3    | 5.0   | 5.9    | 7.1   | 8.1    |
| 80°    | 0.0    | 0.2   | 0.2    | 0.2   | 0.7    | 1.0   | 1.4    | 1.7   | 2.4    | 3.3   | 4.0    |
| 82.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 85°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 87.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |



REPORT NUMBER: P366897  
 CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° | 162.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P366897

CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 165°  | 167.5° | 170°  | 172.5° | 175°  | 177.5° | 180°  | 182.5° | 185°  | 187.5° | 190°  |
|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0°     | 502.1 | 502.1  | 502.1 | 502.1  | 502.1 | 502.1  | 502.1 | 502.1  | 502.1 | 502.1  | 502.1 |
| 2.5°   | 454.6 | 467.7  | 480.8 | 493.8  | 506.9 | 523.0  | 539.2 | 541.6  | 543.9 | 541.1  | 538.5 |
| 5°     | 469.8 | 476.3  | 482.4 | 488.8  | 495.0 | 513.5  | 531.8 | 532.1  | 532.1 | 532.3  | 532.3 |
| 7.5°   | 372.5 | 377.9  | 383.4 | 388.6  | 394.1 | 406.2  | 418.3 | 422.8  | 427.1 | 426.1  | 425.2 |
| 10°    | 270.3 | 277.4  | 284.3 | 291.5  | 298.3 | 309.5  | 320.7 | 324.9  | 329.0 | 342.0  | 355.3 |
| 12.5°  | 231.8 | 238.7  | 245.6 | 252.3  | 259.1 | 270.5  | 282.0 | 290.3  | 298.3 | 306.4  | 314.5 |
| 15°    | 188.8 | 194.3  | 200.0 | 205.5  | 210.9 | 216.2  | 221.4 | 231.6  | 241.6 | 249.6  | 257.7 |
| 17.5°  | 143.7 | 146.1  | 148.2 | 150.6  | 152.7 | 155.1  | 157.5 | 161.8  | 165.8 | 172.9  | 179.8 |
| 20°    | 105.5 | 107.4  | 109.3 | 110.9  | 112.8 | 115.2  | 117.6 | 120.7  | 123.5 | 125.2  | 126.6 |
| 22.5°  | 86.2  | 89.1   | 91.9  | 94.5   | 97.4  | 99.1   | 100.7 | 101.7  | 102.6 | 103.3  | 104.0 |
| 25°    | 77.7  | 80.3   | 82.7  | 85.3   | 87.6  | 88.4   | 89.1  | 91.0   | 92.9  | 92.9   | 92.9  |
| 27.5°  | 67.9  | 71.5   | 75.3  | 78.9   | 82.4  | 83.4   | 84.1  | 84.8   | 85.3  | 84.3   | 83.1  |
| 30°    | 64.1  | 67.7   | 71.3  | 74.6   | 78.1  | 79.6   | 80.8  | 81.5   | 82.2  | 81.0   | 79.8  |
| 32.5°  | 62.5  | 65.8   | 68.9  | 72.2   | 75.3  | 77.2   | 78.9  | 80.8   | 82.4  | 82.7   | 83.1  |
| 35°    | 54.4  | 56.5   | 58.9  | 61.0   | 63.2  | 64.1   | 65.1  | 65.8   | 66.3  | 66.3   | 66.3  |
| 37.5°  | 46.6  | 49.4   | 52.5  | 55.3   | 58.2  | 60.3   | 62.5  | 62.7   | 62.7  | 63.2   | 63.9  |
| 40°    | 45.1  | 48.0   | 50.8  | 53.4   | 56.3  | 58.7   | 60.8  | 61.0   | 61.3  | 61.8   | 62.2  |
| 42.5°  | 43.2  | 46.3   | 49.4  | 52.5   | 55.6  | 58.0   | 60.1  | 60.1   | 59.9  | 60.6   | 61.0  |
| 45°    | 41.3  | 44.4   | 47.3  | 50.4   | 53.2  | 56.3   | 59.1  | 58.4   | 57.5  | 58.7   | 59.6  |
| 47.5°  | 38.7  | 42.0   | 45.4  | 48.5   | 51.8  | 54.6   | 57.2  | 56.8   | 56.1  | 57.2   | 58.4  |
| 50°    | 36.1  | 39.4   | 42.8  | 46.1   | 49.4  | 52.5   | 55.3  | 54.9   | 54.4  | 55.8   | 57.0  |
| 52.5°  | 33.5  | 36.8   | 40.4  | 43.7   | 47.0  | 49.6   | 52.0  | 51.8   | 51.5  | 53.0   | 54.6  |
| 55°    | 30.9  | 34.0   | 37.3  | 40.4   | 43.5  | 46.3   | 48.9  | 48.5   | 48.0  | 49.2   | 50.4  |
| 57.5°  | 28.0  | 31.1   | 34.0  | 37.1   | 39.9  | 42.3   | 44.4  | 43.7   | 43.0  | 44.4   | 45.8  |
| 60°    | 24.9  | 27.8   | 30.6  | 33.3   | 36.1  | 38.0   | 39.7  | 39.2   | 38.5  | 39.9   | 41.3  |
| 62.5°  | 22.1  | 24.7   | 27.3  | 29.7   | 32.3  | 33.7   | 35.2  | 34.7   | 34.2  | 35.6   | 37.3  |
| 65°    | 20.0  | 22.1   | 24.0  | 26.1   | 28.0  | 29.5   | 30.9  | 30.2   | 29.5  | 31.1   | 32.5  |
| 67.5°  | 17.8  | 19.5   | 21.4  | 23.0   | 24.7  | 25.9   | 27.1  | 26.6   | 25.9  | 27.1   | 28.3  |
| 70°    | 15.2  | 16.9   | 18.5  | 20.0   | 21.6  | 22.8   | 24.0  | 23.3   | 22.3  | 23.5   | 24.7  |
| 72.5°  | 12.8  | 14.3   | 15.7  | 16.9   | 18.3  | 19.2   | 20.2  | 19.5   | 18.8  | 19.7   | 20.7  |
| 75°    | 11.2  | 12.4   | 13.5  | 14.5   | 15.7  | 16.2   | 16.6  | 16.4   | 15.9  | 16.9   | 17.6  |
| 77.5°  | 9.0   | 10.0   | 11.2  | 12.1   | 13.1  | 13.1   | 13.1  | 13.3   | 13.3  | 14.3   | 15.4  |
| 80°    | 4.8   | 5.7    | 6.7   | 7.4    | 8.3   | 8.3    | 8.1   | 8.6    | 8.8   | 10.0   | 11.2  |
| 82.5°  | 0.0   | 0.7    | 1.4   | 2.1    | 2.9   | 2.6    | 2.1   | 2.4    | 2.4   | 2.9    | 3.3   |
| 85°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.2    | 0.5   |
| 87.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P366897  
 CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° | 190° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P366897

CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195°  | 197.5° | 200°  | 202.5° | 205°  | 207.5° | 210°  | 212.5° | 215°  | 217.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0°     | 502.1  | 502.1 | 502.1  | 502.1 | 502.1  | 502.1 | 502.1  | 502.1 | 502.1  | 502.1 | 502.1  |
| 2.5°   | 535.6  | 532.8 | 530.9  | 529.2 | 527.3  | 525.4 | 527.8  | 530.2 | 532.3  | 534.7 | 541.8  |
| 5°     | 532.5  | 532.5 | 530.9  | 529.2 | 527.6  | 525.9 | 529.5  | 532.8 | 536.3  | 539.7 | 539.4  |
| 7.5°   | 424.0  | 423.0 | 433.0  | 442.8 | 452.7  | 462.5 | 465.1  | 467.7 | 470.1  | 472.7 | 472.0  |
| 10°    | 368.4  | 381.5 | 385.8  | 390.0 | 394.3  | 398.6 | 403.8  | 409.0 | 414.3  | 419.5 | 421.4  |
| 12.5°  | 322.6  | 330.6 | 344.4  | 358.0 | 371.7  | 385.3 | 392.2  | 399.3 | 406.2  | 413.1 | 426.6  |
| 15°    | 265.8  | 273.9 | 285.8  | 297.6 | 309.5  | 321.4 | 332.3  | 343.5 | 354.4  | 365.3 | 381.7  |
| 17.5°  | 186.9  | 193.8 | 202.9  | 211.9 | 220.7  | 229.7 | 246.6  | 263.4 | 280.3  | 297.2 | 314.5  |
| 20°    | 128.3  | 129.7 | 134.0  | 138.5 | 142.8  | 147.0 | 162.2  | 177.7 | 192.9  | 208.1 | 230.9  |
| 22.5°  | 104.5  | 105.2 | 107.4  | 109.5 | 111.4  | 113.5 | 121.4  | 129.5 | 137.3  | 145.1 | 163.7  |
| 25°    | 92.6   | 92.6  | 94.1   | 95.5  | 96.9   | 98.3  | 102.6  | 106.9 | 110.9  | 115.2 | 127.1  |
| 27.5°  | 82.2   | 81.0  | 83.1   | 85.3  | 87.4   | 89.5  | 92.6   | 96.0  | 99.1   | 102.1 | 110.2  |
| 30°    | 78.6   | 77.4  | 80.0   | 82.7  | 85.3   | 87.9  | 91.0   | 94.1  | 96.9   | 100.0 | 105.5  |
| 32.5°  | 83.4   | 83.6  | 84.6   | 85.5  | 86.2   | 87.2  | 88.6   | 90.3  | 91.7   | 93.1  | 97.9   |
| 35°    | 66.3   | 66.3  | 67.9   | 69.6  | 71.0   | 72.7  | 75.3   | 77.9  | 80.5   | 83.1  | 88.1   |
| 37.5°  | 64.4   | 64.8  | 66.3   | 67.9  | 69.4   | 70.8  | 74.1   | 77.7  | 81.0   | 84.3  | 88.4   |
| 40°    | 62.5   | 62.9  | 64.8   | 66.7  | 68.6   | 70.5  | 73.9   | 77.0  | 80.3   | 83.4  | 87.2   |
| 42.5°  | 61.8   | 62.2  | 64.6   | 67.2  | 69.6   | 72.0  | 74.8   | 77.7  | 80.3   | 83.1  | 88.4   |
| 45°    | 60.8   | 61.8  | 64.6   | 67.7  | 70.5   | 73.4  | 76.0   | 78.6  | 81.2   | 83.8  | 90.3   |
| 47.5°  | 59.4   | 60.6  | 63.9   | 67.0  | 70.3   | 73.4  | 78.4   | 83.6  | 88.6   | 93.6  | 96.7   |
| 50°    | 58.4   | 59.6  | 63.2   | 66.7  | 70.3   | 73.9  | 81.9   | 90.0  | 97.9   | 105.9 | 104.3  |
| 52.5°  | 56.1   | 57.5  | 62.0   | 66.5  | 71.0   | 75.5  | 82.7   | 89.8  | 96.9   | 104.0 | 100.7  |
| 55°    | 51.5   | 52.7  | 58.0   | 63.2  | 68.2   | 73.4  | 78.6   | 83.8  | 88.8   | 94.1  | 90.3   |
| 57.5°  | 47.0   | 48.5  | 53.4   | 58.4  | 63.2   | 68.2  | 70.8   | 73.4  | 76.0   | 78.6  | 77.2   |
| 60°    | 42.8   | 44.2  | 50.8   | 57.5  | 64.1   | 70.8  | 68.4   | 66.0  | 63.4   | 61.0  | 62.7   |
| 62.5°  | 38.7   | 40.1  | 46.6   | 52.7  | 59.1   | 65.3  | 62.0   | 58.7  | 55.3   | 52.0  | 54.6   |
| 65°    | 34.2   | 35.6  | 38.0   | 40.6  | 43.0   | 45.4  | 45.1   | 44.7  | 44.4   | 43.9  | 46.8   |
| 67.5°  | 29.5   | 30.6  | 31.8   | 33.3  | 34.4   | 35.6  | 36.3   | 37.3  | 38.0   | 38.7  | 41.1   |
| 70°    | 25.7   | 26.8  | 28.3   | 29.5  | 30.9   | 32.1  | 32.5   | 33.0  | 33.3   | 33.7  | 35.9   |
| 72.5°  | 21.4   | 22.3  | 24.2   | 26.1  | 27.8   | 29.7  | 29.9   | 29.9  | 30.2   | 30.2  | 31.8   |
| 75°    | 18.5   | 19.2  | 20.7   | 22.1  | 23.3   | 24.7  | 25.4   | 26.1  | 26.6   | 27.3  | 28.3   |
| 77.5°  | 16.4   | 17.3  | 17.8   | 18.1  | 18.5   | 18.8  | 19.2   | 19.7  | 20.2   | 20.7  | 20.9   |
| 80°    | 12.1   | 13.3  | 13.8   | 14.0  | 14.5   | 14.7  | 14.7   | 14.5  | 14.5   | 14.3  | 14.5   |
| 82.5°  | 3.8    | 4.3   | 5.0    | 5.7   | 6.4    | 7.1   | 7.4    | 7.6   | 7.6    | 7.8   | 7.6    |
| 85°    | 0.7    | 1.0   | 1.4    | 1.9   | 2.1    | 2.6   | 2.4    | 1.9   | 1.7    | 1.2   | 1.0    |
| 87.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |



REPORT NUMBER: P366897  
 CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° | 217.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P366897

CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 220°  | 222.5° | 225°  | 227.5° | 230°  | 232.5° | 235°  | 237.5° | 240°  | 242.5° | 245°  |
|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0°     | 502.1 | 502.1  | 502.1 | 502.1  | 502.1 | 502.1  | 502.1 | 502.1  | 502.1 | 502.1  | 502.1 |
| 2.5°   | 548.9 | 555.8  | 563.0 | 560.1  | 557.3 | 554.4  | 551.5 | 552.0  | 552.7 | 553.2  | 553.7 |
| 5°     | 539.2 | 538.7  | 538.5 | 546.6  | 554.9 | 563.0  | 571.0 | 579.8  | 588.8 | 597.6  | 606.4 |
| 7.5°   | 471.3 | 470.3  | 469.6 | 480.1  | 490.5 | 501.0  | 511.4 | 523.5  | 535.9 | 548.0  | 560.1 |
| 10°    | 423.3 | 425.2  | 427.1 | 431.4  | 435.9 | 440.1  | 444.4 | 456.1  | 467.7 | 479.1  | 490.7 |
| 12.5°  | 440.1 | 453.4  | 467.0 | 469.6  | 472.0 | 474.6  | 477.0 | 478.6  | 480.3 | 482.0  | 483.6 |
| 15°    | 398.3 | 414.7  | 431.1 | 438.0  | 444.7 | 451.5  | 458.2 | 475.8  | 493.1 | 510.7  | 528.0 |
| 17.5°  | 331.8 | 348.9  | 366.3 | 386.9  | 407.6 | 428.3  | 448.9 | 467.9  | 486.9 | 505.9  | 524.9 |
| 20°    | 253.9 | 276.7  | 299.5 | 325.7  | 352.0 | 378.2  | 404.3 | 423.3  | 442.0 | 461.0  | 479.8 |
| 22.5°  | 182.4 | 201.0  | 219.5 | 251.1  | 282.4 | 314.0  | 345.4 | 378.4  | 411.6 | 444.7  | 477.7 |
| 25°    | 139.0 | 150.6  | 162.5 | 193.6  | 224.7 | 255.6  | 286.7 | 332.1  | 377.4 | 422.8  | 468.2 |
| 27.5°  | 118.1 | 126.1  | 134.0 | 162.0  | 190.0 | 217.8  | 245.8 | 299.8  | 353.7 | 407.6  | 461.5 |
| 30°    | 111.2 | 116.6  | 122.1 | 145.8  | 169.8 | 193.6  | 217.3 | 272.0  | 326.6 | 381.2  | 435.9 |
| 32.5°  | 102.6 | 107.1  | 111.9 | 132.8  | 153.7 | 174.3  | 195.3 | 248.7  | 302.1 | 355.3  | 408.8 |
| 35°    | 92.9  | 97.9   | 102.6 | 123.5  | 144.4 | 165.1  | 186.0 | 241.3  | 296.7 | 352.0  | 407.4 |
| 37.5°  | 92.2  | 96.2   | 100.0 | 124.2  | 148.7 | 172.9  | 197.2 | 252.5  | 307.8 | 362.9  | 418.3 |
| 40°    | 91.2  | 95.0   | 98.8  | 123.5  | 148.0 | 172.7  | 197.2 | 255.1  | 313.1 | 371.0  | 429.0 |
| 42.5°  | 93.6  | 98.6   | 103.8 | 125.7  | 147.5 | 169.1  | 191.0 | 252.0  | 313.1 | 373.9  | 434.9 |
| 45°    | 96.9  | 103.3  | 109.7 | 129.7  | 149.6 | 169.6  | 189.6 | 255.8  | 322.1 | 388.1  | 454.4 |
| 47.5°  | 100.0 | 103.1  | 106.2 | 125.2  | 143.9 | 162.9  | 181.7 | 249.4  | 317.1 | 384.8  | 452.5 |
| 50°    | 102.9 | 101.2  | 99.5  | 120.4  | 141.3 | 162.0  | 182.9 | 247.5  | 311.9 | 376.5  | 440.9 |
| 52.5°  | 97.2  | 93.8   | 90.3  | 112.6  | 134.9 | 157.0  | 179.3 | 244.4  | 309.5 | 374.6  | 439.7 |
| 55°    | 86.5  | 82.7   | 78.9  | 101.0  | 122.8 | 144.9  | 166.7 | 231.6  | 296.4 | 361.3  | 426.1 |
| 57.5°  | 75.5  | 74.1   | 72.4  | 89.3   | 106.2 | 122.8  | 139.7 | 211.6  | 283.9 | 355.8  | 427.8 |
| 60°    | 64.4  | 65.8   | 67.5  | 79.6   | 91.7  | 103.6  | 115.7 | 186.2  | 256.5 | 327.1  | 397.4 |
| 62.5°  | 57.0  | 59.6   | 62.0  | 72.2   | 82.7  | 92.9   | 103.1 | 169.6  | 236.1 | 302.6  | 369.1 |
| 65°    | 49.9  | 52.7   | 55.6  | 67.7   | 80.0  | 92.2   | 104.3 | 160.6  | 216.9 | 273.2  | 329.5 |
| 67.5°  | 43.5  | 45.6   | 48.0  | 63.9   | 79.8  | 95.7   | 111.6 | 157.7  | 203.6 | 249.6  | 295.5 |
| 70°    | 38.0  | 39.9   | 42.0  | 60.6   | 79.1  | 97.6   | 116.2 | 155.3  | 194.8 | 234.0  | 273.2 |
| 72.5°  | 33.5  | 35.2   | 36.8  | 55.6   | 74.3  | 93.1   | 111.9 | 146.8  | 181.5 | 216.4  | 251.1 |
| 75°    | 29.2  | 29.9   | 30.9  | 46.8   | 62.5  | 78.4   | 94.1  | 117.3  | 140.9 | 164.1  | 187.4 |
| 77.5°  | 21.1  | 21.1   | 21.4  | 26.1   | 30.6  | 35.4   | 39.9  | 54.4   | 68.9  | 83.1   | 97.6  |
| 80°    | 14.5  | 14.7   | 14.7  | 16.6   | 18.3  | 20.2   | 21.9  | 24.9   | 27.8  | 30.9   | 33.7  |
| 82.5°  | 7.4   | 6.9    | 6.7   | 8.6    | 10.5  | 12.4   | 14.3  | 15.0   | 15.4  | 16.2   | 16.6  |
| 85°    | 0.7   | 0.2    | 0.0   | 1.2    | 2.4   | 3.6    | 4.8   | 5.7    | 6.7   | 7.6    | 8.6   |
| 87.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P366897  
 CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° | 245° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |





REPORT NUMBER: P366897

CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°   | 252.5° | 255°   | 257.5° | 260°   | 262.5° | 265°   | 267.5° | 270°   | 272.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  |
| 2.5°   | 551.8  | 549.9  | 548.0  | 546.1  | 557.7  | 569.6  | 581.2  | 592.9  | 625.9  | 647.5  | 645.1  |
| 5°     | 615.0  | 623.5  | 632.1  | 640.6  | 654.4  | 668.4  | 682.2  | 696.0  | 744.9  | 774.8  | 779.1  |
| 7.5°   | 573.4  | 586.5  | 599.8  | 612.8  | 639.4  | 665.8  | 692.4  | 718.8  | 758.9  | 790.0  | 807.6  |
| 10°    | 505.7  | 520.7  | 535.4  | 550.4  | 580.3  | 610.5  | 640.4  | 670.3  | 715.4  | 758.4  | 780.5  |
| 12.5°  | 507.1  | 530.6  | 554.2  | 577.7  | 603.8  | 629.9  | 655.8  | 682.0  | 709.5  | 724.0  | 755.1  |
| 15°    | 546.6  | 565.1  | 583.6  | 602.1  | 636.3  | 670.6  | 704.5  | 738.7  | 755.1  | 790.0  | 826.4  |
| 17.5°  | 561.1  | 597.4  | 633.5  | 669.6  | 712.4  | 754.9  | 797.6  | 840.2  | 871.0  | 919.5  | 957.0  |
| 20°    | 534.2  | 588.6  | 642.8  | 697.2  | 755.8  | 814.5  | 873.2  | 931.8  | 965.6  | 1011.6 | 1069.6 |
| 22.5°  | 535.4  | 593.1  | 650.6  | 708.3  | 789.3  | 870.1  | 951.1  | 1031.8 | 1122.3 | 1211.2 | 1239.4 |
| 25°    | 543.7  | 619.2  | 694.5  | 770.1  | 863.7  | 957.3  | 1050.8 | 1144.4 | 1253.7 | 1347.0 | 1384.6 |
| 27.5°  | 546.6  | 631.6  | 716.4  | 801.4  | 934.5  | 1067.5 | 1200.5 | 1333.5 | 1463.9 | 1569.4 | 1609.5 |
| 30°    | 539.7  | 643.7  | 747.5  | 851.3  | 1014.5 | 1177.7 | 1340.9 | 1504.1 | 1627.8 | 1750.6 | 1800.5 |
| 32.5°  | 541.3  | 673.9  | 806.4  | 939.0  | 1131.1 | 1323.5 | 1515.7 | 1707.9 | 1787.0 | 1897.6 | 1985.5 |
| 35°    | 552.7  | 698.1  | 843.2  | 988.6  | 1201.2 | 1413.8 | 1626.4 | 1839.0 | 1968.7 | 2085.5 | 2160.1 |
| 37.5°  | 579.3  | 740.4  | 901.2  | 1062.2 | 1323.5 | 1585.1 | 1846.3 | 2107.6 | 2308.3 | 2509.1 | 2543.3 |
| 40°    | 599.1  | 769.1  | 939.2  | 1109.3 | 1412.6 | 1715.9 | 2019.3 | 2322.6 | 2549.7 | 2767.5 | 2790.8 |
| 42.5°  | 621.4  | 807.6  | 994.1  | 1180.3 | 1519.5 | 1858.7 | 2197.9 | 2537.1 | 2800.0 | 3022.1 | 3037.6 |
| 45°    | 645.8  | 837.5  | 1029.0 | 1220.4 | 1575.8 | 1930.9 | 2286.2 | 2641.4 | 2948.5 | 3206.4 | 3148.3 |
| 47.5°  | 657.5  | 862.5  | 1067.5 | 1272.5 | 1653.5 | 2034.2 | 2415.2 | 2796.0 | 3071.5 | 3299.1 | 3231.2 |
| 50°    | 666.5  | 891.9  | 1117.6 | 1343.0 | 1742.5 | 2142.1 | 2541.6 | 2941.1 | 3217.4 | 3427.4 | 3320.9 |
| 52.5°  | 691.9  | 944.0  | 1196.2 | 1448.2 | 1873.2 | 2297.9 | 2722.8 | 3147.5 | 3414.8 | 3607.6 | 3458.5 |
| 55°    | 716.6  | 1006.9 | 1297.4 | 1587.7 | 2044.7 | 2501.9 | 2958.9 | 3416.0 | 3682.0 | 3847.3 | 3644.7 |
| 57.5°  | 747.8  | 1067.9 | 1387.9 | 1707.9 | 2196.7 | 2685.5 | 3174.1 | 3663.0 | 3923.1 | 4105.7 | 3895.3 |
| 60°    | 739.7  | 1081.7 | 1424.0 | 1766.1 | 2263.9 | 2761.8 | 3259.7 | 3757.5 | 4066.6 | 4291.0 | 4148.3 |
| 62.5°  | 708.3  | 1047.5 | 1386.5 | 1725.7 | 2214.8 | 2703.6 | 3192.7 | 3681.5 | 4051.8 | 4355.9 | 4307.9 |
| 65°    | 644.9  | 960.1  | 1275.5 | 1590.8 | 2057.7 | 2525.0 | 2992.0 | 3458.9 | 3916.0 | 4302.9 | 4320.0 |
| 67.5°  | 561.5  | 827.6  | 1093.4 | 1359.4 | 1795.0 | 2230.7 | 2666.1 | 3101.7 | 3641.1 | 4092.4 | 4143.3 |
| 70°    | 473.2  | 672.9  | 872.9  | 1072.7 | 1456.1 | 1839.4 | 2222.6 | 2606.0 | 3166.8 | 3620.9 | 3716.9 |
| 72.5°  | 379.3  | 507.8  | 636.1  | 764.4  | 1041.1 | 1317.6 | 1594.3 | 1870.8 | 2364.2 | 2716.7 | 2884.1 |
| 75°    | 245.8  | 304.3  | 362.7  | 421.1  | 605.5  | 789.6  | 973.9  | 1158.0 | 1485.5 | 1745.1 | 1934.5 |
| 77.5°  | 109.5  | 121.4  | 133.0  | 144.9  | 287.2  | 429.5  | 571.7  | 714.0  | 856.3  | 1013.1 | 1057.5 |
| 80°    | 39.2   | 44.4   | 49.9   | 55.1   | 124.9  | 195.0  | 264.8  | 334.7  | 403.6  | 484.6  | 504.3  |
| 82.5°  | 16.4   | 16.4   | 16.2   | 15.9   | 40.9   | 65.8   | 90.7   | 115.7  | 133.7  | 153.7  | 157.5  |
| 85°    | 6.7    | 5.0    | 3.1    | 1.2    | 5.2    | 9.5    | 13.5   | 17.6   | 28.3   | 25.7   | 47.5   |
| 87.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P366897  
 CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° | 272.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P366897

CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 275°   | 277.5° | 280°   | 282.5° | 285°   | 287.5° | 290°   | 292.5° | 295°   | 297.5° | 300°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  |
| 2.5°   | 636.1  | 635.6  | 635.2  | 634.7  | 634.2  | 625.7  | 617.3  | 608.8  | 600.5  | 610.9  | 621.4  |
| 5°     | 772.2  | 784.6  | 796.9  | 809.5  | 821.9  | 825.4  | 829.0  | 832.6  | 836.1  | 843.7  | 851.3  |
| 7.5°   | 822.3  | 843.2  | 863.9  | 884.8  | 905.5  | 924.7  | 943.7  | 963.0  | 982.2  | 977.4  | 972.7  |
| 10°    | 805.0  | 842.8  | 880.5  | 918.5  | 956.3  | 964.6  | 972.9  | 981.5  | 989.8  | 1011.4 | 1033.0 |
| 12.5°  | 786.2  | 831.6  | 877.0  | 922.3  | 967.7  | 992.9  | 1017.8 | 1043.0 | 1068.2 | 1090.0 | 1111.9 |
| 15°    | 875.3  | 904.3  | 933.3  | 962.5  | 991.5  | 1013.5 | 1035.4 | 1057.5 | 1079.3 | 1094.5 | 1109.5 |
| 17.5°  | 992.4  | 1006.7 | 1020.9 | 1035.4 | 1049.7 | 1067.0 | 1084.3 | 1101.7 | 1119.0 | 1128.0 | 1137.1 |
| 20°    | 1116.2 | 1122.3 | 1128.5 | 1134.7 | 1140.9 | 1127.1 | 1113.3 | 1099.5 | 1085.8 | 1094.3 | 1102.6 |
| 22.5°  | 1240.4 | 1242.5 | 1244.9 | 1247.0 | 1249.2 | 1217.1 | 1185.0 | 1153.0 | 1120.9 | 1107.4 | 1093.8 |
| 25°    | 1431.6 | 1415.9 | 1400.3 | 1384.6 | 1368.9 | 1330.9 | 1292.9 | 1254.9 | 1216.9 | 1183.4 | 1149.9 |
| 27.5°  | 1638.7 | 1585.5 | 1532.6 | 1479.4 | 1426.4 | 1388.4 | 1350.4 | 1312.4 | 1274.4 | 1224.0 | 1173.6 |
| 30°    | 1847.5 | 1761.8 | 1676.3 | 1590.5 | 1505.0 | 1459.9 | 1414.7 | 1369.4 | 1324.2 | 1273.9 | 1223.8 |
| 32.5°  | 2039.0 | 1935.9 | 1832.8 | 1729.5 | 1626.4 | 1550.4 | 1474.4 | 1398.4 | 1322.3 | 1287.2 | 1252.0 |
| 35°    | 2197.6 | 2075.8 | 1953.9 | 1831.8 | 1710.0 | 1634.7 | 1559.4 | 1484.1 | 1408.8 | 1356.5 | 1304.5 |
| 37.5°  | 2468.9 | 2331.9 | 2194.8 | 2057.7 | 1920.7 | 1817.8 | 1715.2 | 1612.4 | 1509.5 | 1474.6 | 1439.7 |
| 40°    | 2719.0 | 2546.3 | 2373.7 | 2201.0 | 2028.3 | 1942.1 | 1856.1 | 1769.9 | 1683.9 | 1626.6 | 1569.6 |
| 42.5°  | 2917.8 | 2735.9 | 2554.2 | 2372.2 | 2190.3 | 2105.0 | 2020.0 | 1934.7 | 1849.4 | 1811.2 | 1773.2 |
| 45°    | 2960.8 | 2789.3 | 2618.1 | 2446.6 | 2275.1 | 2225.4 | 2176.0 | 2126.4 | 2077.0 | 2050.6 | 2024.5 |
| 47.5°  | 3045.6 | 2859.6 | 2673.9 | 2487.9 | 2301.9 | 2279.6 | 2257.3 | 2234.7 | 2212.4 | 2225.0 | 2237.6 |
| 50°    | 3093.1 | 2903.4 | 2713.6 | 2523.8 | 2334.0 | 2340.4 | 2346.6 | 2353.0 | 2359.4 | 2448.7 | 2537.8 |
| 52.5°  | 3185.3 | 2993.6 | 2801.9 | 2610.2 | 2418.6 | 2458.9 | 2499.1 | 2539.5 | 2579.6 | 2702.6 | 2825.4 |
| 55°    | 3349.9 | 3161.6 | 2973.2 | 2784.6 | 2596.2 | 2649.4 | 2702.6 | 2756.1 | 2809.3 | 2939.9 | 3070.3 |
| 57.5°  | 3593.9 | 3406.9 | 3220.2 | 3033.3 | 2846.6 | 2899.6 | 2952.5 | 3005.5 | 3058.5 | 3176.5 | 3294.3 |
| 60°    | 3901.0 | 3709.1 | 3517.4 | 3325.5 | 3133.8 | 3153.7 | 3173.4 | 3193.4 | 3213.3 | 3340.2 | 3466.8 |
| 62.5°  | 4140.2 | 3963.7 | 3787.5 | 3611.0 | 3434.7 | 3412.6 | 3390.8 | 3368.7 | 3346.8 | 3443.3 | 3539.5 |
| 65°    | 4195.8 | 4071.5 | 3947.5 | 3823.3 | 3699.1 | 3631.2 | 3563.5 | 3495.5 | 3427.6 | 3466.5 | 3505.5 |
| 67.5°  | 4036.6 | 3952.8 | 3869.2 | 3785.3 | 3701.5 | 3559.7 | 3417.9 | 3275.8 | 3134.0 | 3113.3 | 3092.7 |
| 70°    | 3667.3 | 3621.4 | 3575.8 | 3530.0 | 3484.4 | 3265.8 | 3047.5 | 2829.0 | 2610.7 | 2558.2 | 2505.7 |
| 72.5°  | 2893.9 | 2922.4 | 2950.9 | 2979.6 | 3008.1 | 2774.1 | 2540.4 | 2306.4 | 2072.5 | 2006.0 | 1939.7 |
| 75°    | 2040.6 | 2137.3 | 2234.0 | 2330.7 | 2427.3 | 2214.0 | 2001.0 | 1787.7 | 1574.4 | 1510.5 | 1446.8 |
| 77.5°  | 1106.4 | 1287.7 | 1468.9 | 1650.1 | 1831.4 | 1655.4 | 1479.6 | 1303.6 | 1127.6 | 1083.1 | 1039.0 |
| 80°    | 524.5  | 629.0  | 733.3  | 837.8  | 942.3  | 902.6  | 863.0  | 823.0  | 783.4  | 793.1  | 802.9  |
| 82.5°  | 160.8  | 236.3  | 311.9  | 387.4  | 463.0  | 468.9  | 474.6  | 480.5  | 486.5  | 501.2  | 515.7  |
| 85°    | 53.9   | 73.9   | 93.8   | 113.8  | 133.7  | 168.9  | 204.0  | 239.4  | 274.6  | 251.8  | 229.2  |
| 87.5°  | 0.0    | 0.7    | 1.2    | 1.9    | 2.4    | 7.4    | 12.4   | 17.3   | 22.3   | 19.2   | 16.4   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P366897  
 CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° | 300° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P366897

CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305°   | 307.5° | 310°   | 312.5° | 315°   | 317.5° | 320°   | 322.5° | 325°   | 327.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  |
| 2.5°   | 632.1  | 642.5  | 642.8  | 643.2  | 643.5  | 643.7  | 644.9  | 646.1  | 647.5  | 648.7  | 640.9  |
| 5°     | 859.2  | 866.8  | 852.7  | 838.7  | 824.5  | 810.5  | 823.0  | 835.6  | 848.2  | 860.8  | 855.4  |
| 7.5°   | 967.7  | 963.0  | 961.3  | 959.9  | 958.2  | 956.8  | 961.5  | 966.3  | 971.0  | 975.8  | 975.3  |
| 10°    | 1054.6 | 1076.3 | 1081.5 | 1086.7 | 1092.2 | 1097.4 | 1086.5 | 1075.5 | 1064.6 | 1053.7 | 1049.2 |
| 12.5°  | 1133.7 | 1155.6 | 1172.9 | 1190.3 | 1207.9 | 1225.2 | 1209.5 | 1194.1 | 1178.4 | 1163.0 | 1148.2 |
| 15°    | 1124.7 | 1139.7 | 1153.9 | 1168.2 | 1182.4 | 1196.7 | 1191.5 | 1186.5 | 1181.2 | 1176.0 | 1173.6 |
| 17.5°  | 1146.3 | 1155.4 | 1152.0 | 1148.7 | 1145.1 | 1141.8 | 1140.2 | 1138.7 | 1137.1 | 1135.4 | 1129.7 |
| 20°    | 1111.2 | 1119.7 | 1117.6 | 1115.7 | 1113.6 | 1111.4 | 1110.0 | 1108.6 | 1107.1 | 1105.7 | 1101.2 |
| 22.5°  | 1080.3 | 1066.8 | 1063.2 | 1059.9 | 1056.3 | 1053.0 | 1053.5 | 1053.9 | 1054.2 | 1054.6 | 1075.1 |
| 25°    | 1116.4 | 1082.9 | 1069.8 | 1056.8 | 1043.5 | 1030.4 | 1036.4 | 1042.1 | 1048.0 | 1053.9 | 1083.4 |
| 27.5°  | 1123.1 | 1072.7 | 1051.8 | 1030.9 | 1010.0 | 989.1  | 1010.5 | 1031.8 | 1053.2 | 1074.6 | 1122.3 |
| 30°    | 1173.4 | 1123.3 | 1094.1 | 1065.1 | 1035.9 | 1006.9 | 1034.2 | 1061.5 | 1088.8 | 1116.2 | 1167.9 |
| 32.5°  | 1216.6 | 1181.5 | 1160.6 | 1139.7 | 1118.8 | 1097.9 | 1099.1 | 1100.0 | 1101.2 | 1102.4 | 1175.3 |
| 35°    | 1252.3 | 1200.3 | 1181.2 | 1162.5 | 1143.5 | 1124.7 | 1153.0 | 1181.2 | 1209.5 | 1237.8 | 1303.3 |
| 37.5°  | 1404.8 | 1369.8 | 1334.9 | 1300.3 | 1265.3 | 1230.7 | 1253.2 | 1275.8 | 1298.6 | 1321.2 | 1393.6 |
| 40°    | 1512.4 | 1455.4 | 1446.3 | 1437.5 | 1428.5 | 1419.7 | 1431.4 | 1442.8 | 1454.4 | 1466.0 | 1529.5 |
| 42.5°  | 1734.9 | 1696.7 | 1672.2 | 1648.0 | 1623.5 | 1599.3 | 1608.6 | 1617.8 | 1627.3 | 1636.6 | 1696.7 |
| 45°    | 1998.1 | 1971.8 | 1955.6 | 1939.5 | 1923.1 | 1906.9 | 1892.9 | 1879.1 | 1865.1 | 1851.3 | 1912.4 |
| 47.5°  | 2250.1 | 2262.7 | 2298.4 | 2333.8 | 2369.4 | 2404.8 | 2375.8 | 2346.8 | 2317.6 | 2288.6 | 2288.9 |
| 50°    | 2627.1 | 2716.2 | 2734.2 | 2752.0 | 2770.1 | 2787.9 | 2726.2 | 2664.4 | 2602.4 | 2540.6 | 2533.3 |
| 52.5°  | 2948.5 | 3071.3 | 3077.7 | 3084.1 | 3090.8 | 3097.2 | 3072.2 | 3047.3 | 3022.1 | 2997.2 | 2930.9 |
| 55°    | 3201.0 | 3331.4 | 3340.2 | 3348.7 | 3357.5 | 3366.1 | 3344.2 | 3322.6 | 3300.7 | 3278.9 | 3211.9 |
| 57.5°  | 3412.4 | 3530.2 | 3535.4 | 3540.4 | 3545.6 | 3550.9 | 3552.5 | 3554.2 | 3556.1 | 3557.8 | 3467.3 |
| 60°    | 3593.6 | 3720.5 | 3710.0 | 3699.8 | 3689.3 | 3679.1 | 3663.5 | 3647.8 | 3632.1 | 3616.4 | 3558.0 |
| 62.5°  | 3635.9 | 3732.3 | 3716.2 | 3700.3 | 3684.1 | 3668.2 | 3654.9 | 3641.8 | 3628.5 | 3615.2 | 3577.9 |
| 65°    | 3544.5 | 3583.4 | 3566.8 | 3550.2 | 3533.3 | 3516.7 | 3508.1 | 3499.8 | 3491.2 | 3482.7 | 3477.9 |
| 67.5°  | 3071.8 | 3051.1 | 3070.8 | 3090.5 | 3110.2 | 3130.0 | 3156.8 | 3183.6 | 3210.7 | 3237.6 | 3221.9 |
| 70°    | 2453.0 | 2400.5 | 2422.4 | 2444.0 | 2465.8 | 2487.4 | 2528.1 | 2568.7 | 2609.5 | 2650.1 | 2639.2 |
| 72.5°  | 1873.2 | 1806.7 | 1809.8 | 1812.8 | 1816.2 | 1819.3 | 1818.1 | 1817.1 | 1815.9 | 1814.7 | 1833.7 |
| 75°    | 1382.9 | 1319.0 | 1288.8 | 1258.7 | 1228.5 | 1198.3 | 1191.0 | 1183.6 | 1176.3 | 1168.9 | 1204.3 |
| 77.5°  | 994.5  | 950.4  | 929.7  | 909.3  | 888.6  | 868.2  | 878.6  | 889.1  | 899.8  | 910.2  | 922.6  |
| 80°    | 812.8  | 822.6  | 806.7  | 791.0  | 775.1  | 759.2  | 771.0  | 782.7  | 794.5  | 806.4  | 769.6  |
| 82.5°  | 530.4  | 544.9  | 496.0  | 447.0  | 398.1  | 349.2  | 378.9  | 408.6  | 438.5  | 468.2  | 453.0  |
| 85°    | 206.4  | 183.8  | 156.8  | 129.9  | 102.9  | 75.8   | 98.6   | 121.4  | 144.2  | 167.0  | 182.2  |
| 87.5°  | 13.3   | 10.5   | 8.3    | 6.2    | 3.8    | 1.7    | 3.6    | 5.5    | 7.6    | 9.5    | 15.9   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P366897  
 CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305° | 307.5° | 310° | 312.5° | 315° | 317.5° | 320° | 322.5° | 325° | 327.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P366897

CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 330°   | 332.5° | 335°   | 337.5° | 340°   | 342.5° | 345°   | 347.5° | 350°   | 352.5° | 355°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  | 502.1  |
| 2.5°   | 633.3  | 625.4  | 617.8  | 602.9  | 587.9  | 572.9  | 558.0  | 578.9  | 599.8  | 620.7  | 641.6  |
| 5°     | 850.1  | 844.7  | 839.4  | 840.9  | 842.3  | 844.0  | 845.4  | 848.5  | 851.6  | 854.4  | 857.5  |
| 7.5°   | 975.1  | 974.6  | 974.1  | 963.2  | 952.3  | 941.1  | 930.2  | 935.6  | 941.1  | 946.6  | 952.0  |
| 10°    | 1044.9 | 1040.4 | 1035.9 | 1011.9 | 987.9  | 963.7  | 939.7  | 929.2  | 918.5  | 908.1  | 897.6  |
| 12.5°  | 1133.5 | 1118.5 | 1103.8 | 1078.2 | 1052.7 | 1027.1 | 1001.4 | 991.9  | 982.2  | 972.7  | 963.0  |
| 15°    | 1171.5 | 1169.1 | 1167.0 | 1148.7 | 1130.2 | 1111.9 | 1093.4 | 1060.8 | 1028.0 | 995.5  | 963.0  |
| 17.5°  | 1124.0 | 1118.1 | 1112.4 | 1141.3 | 1170.1 | 1199.1 | 1228.0 | 1194.3 | 1160.6 | 1126.9 | 1093.1 |
| 20°    | 1096.7 | 1092.2 | 1087.7 | 1141.6 | 1195.3 | 1249.2 | 1302.9 | 1287.9 | 1272.7 | 1257.7 | 1242.8 |
| 22.5°  | 1095.5 | 1116.2 | 1136.6 | 1183.9 | 1230.9 | 1278.2 | 1325.2 | 1351.1 | 1377.2 | 1403.1 | 1429.0 |
| 25°    | 1112.8 | 1142.5 | 1172.0 | 1250.4 | 1328.8 | 1407.4 | 1485.8 | 1515.5 | 1544.9 | 1574.6 | 1604.1 |
| 27.5°  | 1169.8 | 1217.6 | 1265.1 | 1333.5 | 1401.9 | 1470.6 | 1539.0 | 1603.8 | 1668.9 | 1733.7 | 1798.6 |
| 30°    | 1219.5 | 1271.3 | 1323.1 | 1404.5 | 1485.8 | 1567.2 | 1648.5 | 1729.7 | 1810.9 | 1892.2 | 1973.4 |
| 32.5°  | 1248.2 | 1321.4 | 1394.3 | 1493.4 | 1592.2 | 1691.2 | 1790.3 | 1879.4 | 1968.4 | 2057.3 | 2146.3 |
| 35°    | 1368.9 | 1434.7 | 1500.3 | 1609.8 | 1719.3 | 1829.0 | 1938.5 | 2048.7 | 2158.9 | 2268.9 | 2379.1 |
| 37.5°  | 1466.0 | 1538.7 | 1611.2 | 1730.9 | 1850.4 | 1970.1 | 2089.8 | 2242.1 | 2394.6 | 2546.8 | 2699.1 |
| 40°    | 1592.9 | 1656.3 | 1719.7 | 1831.8 | 1943.7 | 2055.8 | 2168.0 | 2361.1 | 2554.2 | 2747.1 | 2940.2 |
| 42.5°  | 1756.6 | 1816.6 | 1876.7 | 1996.7 | 2116.6 | 2236.6 | 2356.6 | 2570.3 | 2784.1 | 2997.7 | 3211.4 |
| 45°    | 1973.4 | 2034.7 | 2095.7 | 2191.2 | 2286.7 | 2382.2 | 2477.7 | 2705.0 | 2932.1 | 3159.4 | 3386.5 |
| 47.5°  | 2289.1 | 2289.3 | 2289.6 | 2358.5 | 2427.3 | 2496.5 | 2565.3 | 2794.3 | 3023.1 | 3252.1 | 3480.8 |
| 50°    | 2525.9 | 2518.3 | 2511.0 | 2546.6 | 2582.0 | 2617.6 | 2653.2 | 2863.9 | 3074.9 | 3285.5 | 3496.2 |
| 52.5°  | 2864.9 | 2798.6 | 2732.6 | 2753.7 | 2774.6 | 2795.8 | 2816.7 | 2995.0 | 3173.7 | 3352.1 | 3530.4 |
| 55°    | 3145.2 | 3078.2 | 3011.2 | 3003.4 | 2995.5 | 2987.7 | 2979.8 | 3144.0 | 3308.1 | 3472.2 | 3636.4 |
| 57.5°  | 3377.0 | 3286.5 | 3196.2 | 3178.2 | 3160.4 | 3142.3 | 3124.3 | 3297.4 | 3470.3 | 3643.5 | 3816.4 |
| 60°    | 3499.8 | 3441.4 | 3382.9 | 3371.3 | 3359.4 | 3347.8 | 3335.9 | 3477.9 | 3620.0 | 3762.0 | 3904.1 |
| 62.5°  | 3540.9 | 3503.6 | 3466.5 | 3488.4 | 3510.3 | 3532.3 | 3554.2 | 3616.7 | 3678.9 | 3741.4 | 3803.6 |
| 65°    | 3473.4 | 3468.7 | 3463.9 | 3508.8 | 3553.5 | 3598.4 | 3643.3 | 3627.8 | 3612.2 | 3596.7 | 3581.3 |
| 67.5°  | 3206.4 | 3190.8 | 3175.3 | 3273.9 | 3372.2 | 3470.8 | 3569.4 | 3494.6 | 3419.5 | 3344.7 | 3269.9 |
| 70°    | 2628.3 | 2617.1 | 2606.2 | 2748.2 | 2890.3 | 3032.6 | 3174.6 | 3083.9 | 2993.1 | 2902.4 | 2811.7 |
| 72.5°  | 1852.5 | 1871.5 | 1890.5 | 2058.0 | 2225.2 | 2392.7 | 2559.9 | 2468.4 | 2377.0 | 2285.5 | 2194.1 |
| 75°    | 1239.4 | 1274.8 | 1310.2 | 1482.7 | 1655.1 | 1827.8 | 2000.3 | 1892.9 | 1785.5 | 1678.2 | 1570.8 |
| 77.5°  | 934.9  | 947.3  | 959.6  | 1068.7 | 1177.7 | 1286.9 | 1396.0 | 1307.4 | 1218.5 | 1129.9 | 1041.1 |
| 80°    | 732.8  | 695.7  | 658.9  | 694.8  | 730.6  | 766.5  | 802.4  | 749.4  | 696.4  | 643.7  | 590.7  |
| 82.5°  | 437.8  | 422.6  | 407.4  | 426.8  | 446.1  | 465.6  | 485.0  | 462.2  | 439.2  | 416.4  | 393.4  |
| 85°    | 197.2  | 212.4  | 227.3  | 247.0  | 266.5  | 286.2  | 305.9  | 274.1  | 242.3  | 210.5  | 178.6  |
| 87.5°  | 22.1   | 28.5   | 34.9   | 43.2   | 51.5   | 59.9   | 68.2   | 53.2   | 38.0   | 23.0   | 8.1    |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P366897  
 CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 330° | 332.5° | 335° | 337.5° | 340° | 342.5° | 345° | 347.5° | 350° | 352.5° | 355° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |





REPORT NUMBER: P366897  
 CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360°   |
|--------|--------|--------|
| 0°     | 502.1  | 502.1  |
| 2.5°   | 653.7  | 665.8  |
| 5°     | 857.3  | 856.8  |
| 7.5°   | 937.8  | 923.3  |
| 10°    | 884.3  | 871.0  |
| 12.5°  | 929.0  | 895.0  |
| 15°    | 937.3  | 911.6  |
| 17.5°  | 1051.3 | 1009.3 |
| 20°    | 1188.8 | 1134.7 |
| 22.5°  | 1354.9 | 1280.5 |
| 25°    | 1515.7 | 1427.3 |
| 27.5°  | 1745.6 | 1692.4 |
| 30°    | 1919.7 | 1865.8 |
| 32.5°  | 2109.8 | 2073.2 |
| 35°    | 2342.8 | 2306.2 |
| 37.5°  | 2708.6 | 2717.8 |
| 40°    | 2945.9 | 2951.6 |
| 42.5°  | 3233.5 | 3255.6 |
| 45°    | 3411.2 | 3435.9 |
| 47.5°  | 3515.2 | 3549.7 |
| 50°    | 3551.8 | 3607.4 |
| 52.5°  | 3599.1 | 3667.5 |
| 55°    | 3712.6 | 3788.9 |
| 57.5°  | 3877.2 | 3938.0 |
| 60°    | 3906.9 | 3909.8 |
| 62.5°  | 3759.7 | 3715.7 |
| 65°    | 3534.5 | 3487.7 |
| 67.5°  | 3241.6 | 3213.1 |
| 70°    | 2774.1 | 2736.6 |
| 72.5°  | 2124.3 | 2054.4 |
| 75°    | 1484.3 | 1397.9 |
| 77.5°  | 995.7  | 950.4  |
| 80°    | 592.2  | 593.4  |
| 82.5°  | 404.3  | 415.0  |
| 85°    | 176.5  | 174.1  |
| 87.5°  | 5.7    | 3.1    |
| 90°    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    |



REPORT NUMBER: P366897  
CATALOG NUMBER: PMM-SA1C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

(END OF REPORT)