

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P367953

Luminaire Tested: **PMM-SA3C-730-U-SLR-HSS**

Issue Date: 12/2/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P367953  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1910-543-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 12/2/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: PMM-SA3C-730-U-SLR-HSS  
Description: MESA POST TOP DECORATIVE LUMINAIRE. (3) LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 12095 lumens  
Efficiency: N/A  
Efficacy: 72.9 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B2 - U0 - G2  
  
Input Watts (W): 166  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 6.2 fc  
 Type IV - Short - N/A

REPORT NUMBER: P367953  
CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

### Luminous Intensity Polar Plot



REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 2019.7   | 0.0    | 2019.7  |
|                    | % Fixture | 16.7     | 0.0    | 16.7    |
| <b>Street Side</b> | Lumens    | 10075.3  | 0.0    | 10075.3 |
|                    | % Fixture | 83.3     | 0.0    | 83.3    |
| <b>Total</b>       | Lumens    | 12095.0  | 0.0    | 12095.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 162.9   | 1.3       |
| 10°-20°   | 425.4   | 3.5       |
| 20°-30°   | 687.6   | 5.7       |
| 30°-40°   | 1151.6  | 9.5       |
| 40°-50°   | 1882.5  | 15.6      |
| 50°-60°   | 2786.8  | 23.0      |
| 60°-70°   | 3199.3  | 26.5      |
| 70°-80°   | 1581.8  | 13.1      |
| 80°-90°   | 217.3   | 1.8       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 12095.0 | 100.0     |
| 0°-180°   | 12095.0 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 942.3  | 7.8       |                         |      |         |
| FM (30°-60°)   | 4814.4 | 39.8      |                         |      |         |
| FH (60°-80°)   | 4112.9 | 34.0      |                         |      | G2/5000 |
| FVH (80°-90°)  | 205.7  | 1.7       |                         |      | G2/225  |
| BL (0°-30°)    | 333.5  | 2.8       | B1/500                  |      |         |
| BM (30°-60°)   | 1006.4 | 8.3       | B2/2500                 |      |         |
| BH (60°-80°)   | 668.2  | 5.5       | B2/1000                 |      | G2/1000 |
| BVH (80°-90°)  | 11.6   | 0.1       |                         |      | G1/100  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G2**  
 Type IV Short





REPORT NUMBER: P367953

CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (FULL):**

|        | 0°      | 2.5°    | 5°     | 7.5°   | 10°    | 12.5°  | 15°    | 17.5°  | 20°    | 22.5°  | 25°    |
|--------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1457.5  | 1457.5  | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 |
| 2.5°   | 1932.5  | 1956.7  | 1980.1 | 1935.3 | 1890.5 | 1845.7 | 1800.9 | 1760.9 | 1720.9 | 1680.2 | 1640.2 |
| 5°     | 2486.9  | 2442.7  | 2398.6 | 2337.9 | 2277.3 | 2216.6 | 2155.9 | 2127.7 | 2099.4 | 2071.1 | 2042.8 |
| 7.5°   | 2679.9  | 2601.3  | 2522.0 | 2468.2 | 2415.2 | 2361.4 | 2307.6 | 2222.8 | 2137.3 | 2052.5 | 1967.0 |
| 10°    | 2528.2  | 2444.8  | 2360.7 | 2313.8 | 2266.9 | 2220.0 | 2173.2 | 2067.7 | 1961.5 | 1856.0 | 1749.8 |
| 12.5°  | 2597.9  | 2507.5  | 2417.2 | 2320.7 | 2224.2 | 2127.7 | 2031.1 | 1950.5 | 1869.1 | 1788.4 | 1707.1 |
| 15°    | 2646.1  | 2542.7  | 2438.6 | 2328.3 | 2218.0 | 2107.7 | 1997.3 | 1902.2 | 1807.7 | 1712.6 | 1617.5 |
| 17.5°  | 2929.5  | 2781.3  | 2633.0 | 2463.4 | 2293.8 | 2124.2 | 1954.6 | 1844.3 | 1734.7 | 1624.4 | 1514.0 |
| 20°    | 3293.5  | 3083.2  | 2872.3 | 2642.7 | 2413.1 | 2183.5 | 1953.9 | 1816.7 | 1679.5 | 1542.3 | 1405.1 |
| 22.5°  | 3716.8  | 3454.2  | 3190.8 | 2907.4 | 2624.7 | 2341.4 | 2058.0 | 1860.8 | 1663.7 | 1466.5 | 1269.3 |
| 25°    | 4142.9  | 3905.8  | 3668.6 | 3287.3 | 2906.0 | 2524.1 | 2142.8 | 1892.5 | 1641.6 | 1391.3 | 1140.4 |
| 27.5°  | 4912.4  | 4488.3  | 4064.3 | 3579.0 | 3094.3 | 2608.9 | 2123.5 | 1836.7 | 1549.9 | 1262.4 | 975.6  |
| 30°    | 5415.7  | 5089.5  | 4762.7 | 4121.6 | 3481.0 | 2839.9 | 2198.7 | 1835.3 | 1472.0 | 1108.0 | 744.6  |
| 32.5°  | 6017.5  | 5540.4  | 5062.7 | 4367.0 | 3671.3 | 2975.7 | 2280.0 | 1853.3 | 1425.8 | 999.0  | 571.6  |
| 35°    | 6693.9  | 6174.7  | 5655.6 | 4774.5 | 3893.3 | 3011.5 | 2130.4 | 1716.7 | 1303.1 | 889.4  | 475.7  |
| 37.5°  | 7888.7  | 7020.0  | 6151.3 | 5124.0 | 4096.0 | 3068.8 | 2040.8 | 1627.8 | 1214.1 | 801.1  | 387.5  |
| 40°    | 8567.1  | 7737.7  | 6908.3 | 5624.6 | 4340.8 | 3057.0 | 1773.3 | 1406.5 | 1040.4 | 673.6  | 306.8  |
| 42.5°  | 9449.6  | 8397.5  | 7344.7 | 5910.0 | 4475.2 | 3040.5 | 1605.7 | 1266.5 | 927.3  | 587.4  | 248.2  |
| 45°    | 9972.9  | 8780.9  | 7588.8 | 6034.1 | 4479.4 | 2924.7 | 1369.9 | 1076.2 | 782.5  | 488.8  | 195.1  |
| 47.5°  | 10303.2 | 9107.7  | 7912.2 | 6243.0 | 4574.5 | 2905.4 | 1236.2 | 965.9  | 695.7  | 425.4  | 155.1  |
| 50°    | 10470.7 | 9271.8  | 8072.1 | 6356.8 | 4641.4 | 2925.4 | 1210.0 | 941.1  | 671.5  | 402.6  | 133.1  |
| 52.5°  | 10645.2 | 9488.9  | 8332.0 | 6553.9 | 4775.8 | 2997.7 | 1219.6 | 945.2  | 671.5  | 397.1  | 122.7  |
| 55°    | 10997.5 | 9857.1  | 8716.1 | 6836.6 | 4957.2 | 3077.7 | 1198.3 | 928.0  | 657.7  | 386.8  | 116.5  |
| 57.5°  | 11430.4 | 10211.5 | 8991.8 | 7043.5 | 5095.1 | 3146.7 | 1198.3 | 926.6  | 655.0  | 382.6  | 111.0  |
| 60°    | 11348.4 | 10025.3 | 8701.6 | 6811.1 | 4920.6 | 3029.5 | 1139.0 | 880.4  | 622.6  | 364.0  | 105.5  |
| 62.5°  | 10785.1 | 9349.0  | 7912.2 | 6165.1 | 4417.3 | 2670.3 | 922.5  | 716.3  | 510.2  | 303.4  | 97.2   |
| 65°    | 10123.2 | 8598.9  | 7073.8 | 5466.0 | 3857.5 | 2249.7 | 641.2  | 503.3  | 364.7  | 226.8  | 88.3   |
| 67.5°  | 9326.2  | 7700.5  | 6074.8 | 4644.8 | 3215.6 | 1785.7 | 355.8  | 286.8  | 217.9  | 148.2  | 79.3   |
| 70°    | 7943.2  | 6265.1  | 4586.2 | 3487.3 | 2389.0 | 1290.0 | 191.0  | 161.3  | 131.7  | 102.0  | 72.4   |
| 72.5°  | 5963.1  | 4425.6  | 2888.1 | 2193.8 | 1500.3 | 806.0  | 111.7  | 100.7  | 88.9   | 77.9   | 66.2   |
| 75°    | 4057.4  | 2905.4  | 1753.3 | 1334.8 | 917.0  | 498.5  | 80.0   | 74.5   | 68.3   | 62.7   | 56.5   |
| 77.5°  | 2758.5  | 1995.3  | 1232.1 | 940.4  | 648.8  | 357.1  | 65.5   | 62.1   | 58.6   | 54.5   | 51.0   |
| 80°    | 1722.3  | 1179.0  | 635.7  | 489.5  | 342.7  | 196.5  | 49.6   | 47.6   | 45.5   | 42.7   | 40.7   |
| 82.5°  | 1204.5  | 720.5   | 236.5  | 184.8  | 133.1  | 80.7   | 29.0   | 29.6   | 30.3   | 30.3   | 31.0   |
| 85°    | 505.4   | 273.0   | 40.7   | 34.5   | 28.3   | 22.1   | 15.9   | 17.2   | 19.3   | 20.7   | 22.1   |
| 87.5°  | 9.0     | 4.8     | 0.0    | 1.4    | 3.4    | 4.8    | 6.2    | 8.3    | 9.7    | 11.7   | 13.1   |
| 90°    | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 2.5° | 5°  | 7.5° | 10° | 12.5° | 15° | 17.5° | 20° | 22.5° | 25° |
|--------|-----|------|-----|------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |





REPORT NUMBER: P367953

CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 27.5°  | 30°    | 32.5°  | 35°    | 37.5°  | 40°    | 42.5°  | 45°    | 47.5°  | 50°    | 52.5°  |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 |
| 2.5°   | 1650.6 | 1660.9 | 1670.5 | 1680.9 | 1672.6 | 1665.0 | 1656.8 | 1648.5 | 1636.1 | 1624.4 | 1611.9 |
| 5°     | 2008.4 | 1973.9 | 1939.4 | 1905.0 | 1852.6 | 1800.2 | 1747.1 | 1694.7 | 1688.5 | 1682.3 | 1675.4 |
| 7.5°   | 1886.3 | 1805.7 | 1724.3 | 1643.7 | 1567.8 | 1492.0 | 1416.1 | 1340.3 | 1316.9 | 1294.1 | 1270.7 |
| 10°    | 1687.8 | 1625.7 | 1563.0 | 1500.9 | 1446.5 | 1391.3 | 1336.8 | 1281.7 | 1224.5 | 1167.2 | 1109.3 |
| 12.5°  | 1642.3 | 1577.5 | 1512.0 | 1447.2 | 1397.5 | 1347.9 | 1298.2 | 1248.6 | 1184.5 | 1120.4 | 1056.2 |
| 15°    | 1547.1 | 1476.8 | 1406.5 | 1336.2 | 1270.0 | 1203.8 | 1136.9 | 1070.7 | 993.5  | 916.3  | 839.1  |
| 17.5°  | 1430.6 | 1347.9 | 1264.5 | 1181.0 | 1094.2 | 1007.3 | 920.4  | 833.5  | 744.6  | 656.4  | 567.4  |
| 20°    | 1292.0 | 1179.0 | 1065.2 | 952.1  | 844.6  | 737.0  | 628.8  | 521.2  | 465.4  | 410.2  | 354.4  |
| 22.5°  | 1123.1 | 976.3  | 830.1  | 683.2  | 595.0  | 506.1  | 417.8  | 328.9  | 304.7  | 280.6  | 256.5  |
| 25°    | 974.2  | 808.0  | 641.9  | 475.7  | 419.9  | 364.0  | 308.2  | 252.3  | 241.3  | 229.6  | 218.6  |
| 27.5°  | 819.1  | 663.3  | 506.7  | 350.2  | 318.5  | 286.1  | 254.4  | 222.0  | 214.4  | 207.5  | 199.9  |
| 30°    | 628.1  | 511.6  | 394.4  | 277.8  | 257.2  | 236.5  | 215.1  | 194.4  | 191.0  | 186.8  | 183.4  |
| 32.5°  | 486.8  | 401.3  | 316.5  | 231.0  | 219.2  | 207.5  | 195.8  | 184.1  | 178.6  | 173.1  | 166.8  |
| 35°    | 406.8  | 338.5  | 269.6  | 200.6  | 192.4  | 183.4  | 175.1  | 166.2  | 160.6  | 154.4  | 148.9  |
| 37.5°  | 337.1  | 287.5  | 237.2  | 186.8  | 177.9  | 168.9  | 159.3  | 150.3  | 146.2  | 142.0  | 137.9  |
| 40°    | 277.8  | 248.9  | 219.9  | 191.0  | 177.9  | 164.8  | 151.7  | 138.6  | 135.1  | 131.7  | 128.2  |
| 42.5°  | 229.6  | 211.0  | 191.7  | 173.1  | 163.4  | 154.4  | 144.8  | 135.1  | 130.3  | 124.8  | 120.0  |
| 45°    | 185.5  | 175.1  | 165.5  | 155.1  | 155.8  | 156.5  | 156.5  | 157.2  | 144.8  | 131.7  | 119.3  |
| 47.5°  | 150.3  | 145.5  | 140.0  | 135.1  | 140.6  | 146.2  | 151.0  | 156.5  | 143.4  | 130.3  | 116.5  |
| 50°    | 128.9  | 125.5  | 121.3  | 117.2  | 122.7  | 128.9  | 134.4  | 140.0  | 134.4  | 129.6  | 124.1  |
| 52.5°  | 117.9  | 113.1  | 108.2  | 103.4  | 105.5  | 108.2  | 110.3  | 112.4  | 112.4  | 112.4  | 112.4  |
| 55°    | 111.0  | 106.2  | 100.7  | 95.1   | 93.1   | 90.3   | 88.3   | 85.5   | 82.0   | 79.3   | 75.8   |
| 57.5°  | 105.5  | 100.0  | 93.8   | 88.3   | 84.8   | 80.7   | 77.2   | 73.1   | 69.6   | 65.5   | 62.1   |
| 60°    | 100.0  | 94.5   | 88.3   | 82.7   | 79.3   | 75.8   | 71.7   | 68.3   | 64.1   | 60.7   | 56.5   |
| 62.5°  | 92.4   | 87.6   | 82.7   | 77.9   | 74.5   | 71.7   | 68.3   | 64.8   | 60.7   | 56.5   | 51.7   |
| 65°    | 84.1   | 80.7   | 76.5   | 72.4   | 68.9   | 65.5   | 62.1   | 58.6   | 54.5   | 51.0   | 46.9   |
| 67.5°  | 76.5   | 73.1   | 70.3   | 66.9   | 62.7   | 59.3   | 55.2   | 51.0   | 48.3   | 45.5   | 42.1   |
| 70°    | 70.3   | 67.6   | 65.5   | 62.7   | 58.6   | 55.2   | 51.0   | 46.9   | 44.8   | 42.1   | 40.0   |
| 72.5°  | 64.1   | 62.1   | 59.3   | 57.2   | 53.8   | 50.3   | 46.9   | 43.4   | 41.4   | 39.3   | 37.2   |
| 75°    | 55.2   | 53.8   | 52.4   | 51.0   | 47.6   | 44.1   | 40.0   | 36.5   | 35.9   | 35.2   | 34.5   |
| 77.5°  | 49.6   | 49.0   | 47.6   | 46.2   | 42.7   | 39.3   | 35.9   | 32.4   | 33.1   | 33.8   | 33.8   |
| 80°    | 40.7   | 40.7   | 40.0   | 40.0   | 37.2   | 34.5   | 31.0   | 28.3   | 29.6   | 31.7   | 33.1   |
| 82.5°  | 31.0   | 31.0   | 31.0   | 31.0   | 28.3   | 25.5   | 22.8   | 20.0   | 22.1   | 23.4   | 25.5   |
| 85°    | 21.4   | 20.7   | 20.0   | 19.3   | 17.2   | 15.9   | 13.8   | 11.7   | 14.5   | 16.5   | 19.3   |
| 87.5°  | 13.1   | 13.8   | 13.8   | 13.8   | 12.4   | 10.3   | 9.0    | 6.9    | 8.3    | 9.0    | 10.3   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30° | 32.5° | 35° | 37.5° | 40° | 42.5° | 45° | 47.5° | 50° | 52.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |



REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 55°    | 57.5°  | 60°    | 62.5°  | 65°    | 67.5°  | 70°    | 72.5°  | 75°    | 77.5°  | 80°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 |
| 2.5°   | 1599.5 | 1578.8 | 1558.2 | 1536.8 | 1516.1 | 1467.8 | 1419.6 | 1371.3 | 1323.1 | 1358.9 | 1394.1 |
| 5°     | 1669.2 | 1629.2 | 1588.5 | 1548.5 | 1507.8 | 1489.9 | 1472.7 | 1454.7 | 1436.8 | 1439.6 | 1443.0 |
| 7.5°   | 1247.2 | 1221.0 | 1194.8 | 1167.9 | 1141.7 | 1136.2 | 1131.4 | 1125.9 | 1120.4 | 1132.1 | 1143.1 |
| 10°    | 1052.1 | 1015.6 | 978.3  | 941.8  | 904.6  | 884.6  | 864.6  | 844.6  | 824.6  | 822.5  | 819.8  |
| 12.5°  | 992.1  | 936.3  | 881.1  | 825.3  | 769.4  | 726.0  | 682.6  | 639.1  | 595.7  | 599.1  | 602.6  |
| 15°    | 761.8  | 706.0  | 650.8  | 595.0  | 539.2  | 504.0  | 468.1  | 433.0  | 397.1  | 386.8  | 376.4  |
| 17.5°  | 478.5  | 437.1  | 395.7  | 353.7  | 312.3  | 300.6  | 289.6  | 277.8  | 266.1  | 262.7  | 259.2  |
| 20°    | 298.5  | 280.6  | 262.7  | 244.1  | 226.1  | 223.4  | 220.6  | 217.9  | 215.1  | 217.2  | 219.2  |
| 22.5°  | 232.3  | 224.8  | 216.5  | 208.9  | 200.6  | 197.9  | 195.1  | 192.4  | 189.6  | 191.7  | 193.0  |
| 25°    | 206.8  | 201.3  | 195.8  | 190.3  | 184.8  | 182.0  | 178.6  | 175.8  | 172.4  | 173.7  | 175.8  |
| 27.5°  | 192.4  | 187.5  | 182.7  | 177.9  | 173.1  | 168.2  | 164.1  | 159.3  | 154.4  | 157.2  | 159.3  |
| 30°    | 179.3  | 173.7  | 168.9  | 163.4  | 157.9  | 153.1  | 148.2  | 142.7  | 137.9  | 140.6  | 143.4  |
| 32.5°  | 161.3  | 156.5  | 151.0  | 146.2  | 140.6  | 137.9  | 135.1  | 131.7  | 128.9  | 131.0  | 132.4  |
| 35°    | 142.7  | 138.6  | 135.1  | 131.0  | 126.9  | 124.1  | 122.0  | 119.3  | 116.5  | 117.2  | 118.6  |
| 37.5°  | 133.8  | 128.9  | 124.1  | 119.3  | 114.4  | 113.1  | 111.7  | 109.6  | 108.2  | 108.2  | 108.2  |
| 40°    | 124.8  | 120.0  | 115.1  | 109.6  | 104.8  | 102.7  | 100.7  | 98.6   | 96.5   | 96.5   | 96.5   |
| 42.5°  | 114.4  | 109.6  | 104.8  | 100.0  | 95.1   | 93.1   | 90.3   | 88.3   | 85.5   | 85.5   | 85.5   |
| 45°    | 106.2  | 101.3  | 97.2   | 92.4   | 87.6   | 84.1   | 80.7   | 76.5   | 73.1   | 72.4   | 71.7   |
| 47.5°  | 103.4  | 96.5   | 89.6   | 82.7   | 75.8   | 72.4   | 68.9   | 64.8   | 61.4   | 60.7   | 60.0   |
| 50°    | 118.6  | 104.8  | 91.0   | 77.2   | 63.4   | 60.7   | 57.9   | 55.2   | 52.4   | 51.0   | 50.3   |
| 52.5°  | 112.4  | 97.9   | 83.4   | 68.9   | 54.5   | 52.4   | 50.3   | 48.3   | 46.2   | 44.8   | 43.4   |
| 55°    | 72.4   | 66.2   | 60.7   | 54.5   | 48.3   | 46.9   | 45.5   | 43.4   | 42.1   | 40.7   | 39.3   |
| 57.5°  | 57.9   | 54.5   | 51.7   | 48.3   | 44.8   | 43.4   | 42.1   | 40.0   | 38.6   | 36.5   | 35.2   |
| 60°    | 52.4   | 49.6   | 46.9   | 44.1   | 41.4   | 40.0   | 38.6   | 37.2   | 35.9   | 33.8   | 32.4   |
| 62.5°  | 47.6   | 45.5   | 43.4   | 41.4   | 39.3   | 37.9   | 36.5   | 35.2   | 33.8   | 31.7   | 29.6   |
| 65°    | 42.7   | 41.4   | 40.0   | 38.6   | 37.2   | 35.9   | 34.5   | 32.4   | 31.0   | 29.0   | 26.9   |
| 67.5°  | 39.3   | 38.6   | 37.9   | 37.2   | 36.5   | 35.2   | 33.1   | 31.7   | 29.6   | 27.6   | 24.8   |
| 70°    | 37.2   | 37.2   | 37.2   | 36.5   | 36.5   | 35.2   | 33.1   | 31.7   | 29.6   | 26.9   | 24.8   |
| 72.5°  | 35.2   | 35.9   | 36.5   | 36.5   | 37.2   | 35.2   | 33.1   | 31.0   | 29.0   | 26.2   | 24.1   |
| 75°    | 33.8   | 34.5   | 35.2   | 35.2   | 35.9   | 34.5   | 33.1   | 31.0   | 29.6   | 26.9   | 24.1   |
| 77.5°  | 34.5   | 35.2   | 35.2   | 35.9   | 35.9   | 34.5   | 33.1   | 31.0   | 29.6   | 26.2   | 22.8   |
| 80°    | 34.5   | 33.8   | 33.1   | 31.7   | 31.0   | 28.3   | 25.5   | 22.1   | 19.3   | 15.2   | 11.7   |
| 82.5°  | 26.9   | 25.5   | 24.8   | 23.4   | 22.1   | 19.3   | 16.5   | 13.8   | 11.0   | 8.3    | 5.5    |
| 85°    | 21.4   | 20.0   | 19.3   | 17.9   | 16.5   | 14.5   | 11.7   | 9.7    | 6.9    | 5.5    | 3.4    |
| 87.5°  | 11.0   | 10.3   | 9.0    | 8.3    | 6.9    | 5.5    | 3.4    | 2.1    | 0.0    | 0.0    | 0.0    |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 55° | 57.5° | 60° | 62.5° | 65° | 67.5° | 70° | 72.5° | 75° | 77.5° | 80° |
|--------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |



REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 82.5°  | 85°    | 87.5°  | 90°    | 92.5°  | 95°    | 97.5°  | 100°   | 102.5° | 105°   | 107.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 |
| 2.5°   | 1429.9 | 1465.1 | 1460.3 | 1455.4 | 1478.2 | 1500.9 | 1484.4 | 1468.5 | 1452.0 | 1435.4 | 1401.0 |
| 5°     | 1445.8 | 1448.5 | 1443.7 | 1438.2 | 1438.9 | 1439.6 | 1428.5 | 1417.5 | 1406.5 | 1395.5 | 1393.4 |
| 7.5°   | 1154.8 | 1165.9 | 1181.0 | 1195.5 | 1196.2 | 1196.2 | 1187.9 | 1179.7 | 1170.7 | 1162.4 | 1166.6 |
| 10°    | 817.7  | 814.9  | 819.1  | 823.2  | 822.5  | 821.1  | 843.2  | 865.3  | 886.6  | 908.7  | 892.8  |
| 12.5°  | 605.3  | 608.8  | 591.6  | 574.3  | 580.5  | 586.0  | 589.5  | 592.9  | 596.4  | 599.8  | 609.5  |
| 15°    | 366.1  | 355.8  | 343.3  | 330.9  | 337.1  | 342.7  | 348.9  | 354.4  | 360.6  | 366.1  | 372.3  |
| 17.5°  | 255.1  | 251.7  | 246.1  | 239.9  | 240.6  | 241.3  | 242.0  | 242.7  | 242.7  | 243.4  | 244.8  |
| 20°    | 221.3  | 223.4  | 219.2  | 214.4  | 213.0  | 211.0  | 209.6  | 208.2  | 206.1  | 204.8  | 202.7  |
| 22.5°  | 195.1  | 196.5  | 197.2  | 197.2  | 194.4  | 191.0  | 188.2  | 186.2  | 183.4  | 180.6  | 179.3  |
| 25°    | 177.2  | 178.6  | 177.2  | 175.1  | 173.7  | 172.4  | 171.0  | 168.9  | 167.5  | 165.5  | 164.8  |
| 27.5°  | 162.0  | 164.1  | 164.1  | 163.4  | 162.0  | 160.0  | 156.5  | 153.7  | 150.3  | 146.9  | 147.5  |
| 30°    | 146.2  | 148.9  | 148.9  | 148.2  | 147.5  | 146.9  | 143.4  | 140.0  | 136.5  | 133.1  | 134.4  |
| 32.5°  | 134.4  | 135.8  | 135.1  | 134.4  | 134.4  | 133.8  | 131.0  | 128.9  | 126.2  | 123.4  | 123.4  |
| 35°    | 119.3  | 120.0  | 120.0  | 120.0  | 120.0  | 119.3  | 117.2  | 115.1  | 113.1  | 111.0  | 111.7  |
| 37.5°  | 108.2  | 108.2  | 110.3  | 111.7  | 110.3  | 108.9  | 107.6  | 105.5  | 104.1  | 102.0  | 102.0  |
| 40°    | 95.8   | 95.8   | 97.9   | 99.3   | 97.9   | 96.5   | 95.8   | 94.5   | 93.8   | 92.4   | 92.4   |
| 42.5°  | 84.8   | 84.8   | 86.9   | 88.3   | 88.3   | 87.6   | 86.2   | 84.8   | 83.4   | 82.0   | 82.7   |
| 45°    | 71.0   | 70.3   | 73.8   | 76.5   | 75.2   | 73.8   | 73.8   | 73.1   | 73.1   | 72.4   | 73.1   |
| 47.5°  | 58.6   | 57.9   | 60.7   | 63.4   | 62.7   | 61.4   | 61.4   | 61.4   | 61.4   | 61.4   | 62.1   |
| 50°    | 49.0   | 47.6   | 50.3   | 52.4   | 51.7   | 50.3   | 50.3   | 51.0   | 51.0   | 51.0   | 51.7   |
| 52.5°  | 42.1   | 40.7   | 42.7   | 44.1   | 43.4   | 42.7   | 42.7   | 43.4   | 43.4   | 43.4   | 44.1   |
| 55°    | 37.2   | 35.9   | 37.9   | 39.3   | 38.6   | 37.2   | 37.9   | 37.9   | 38.6   | 38.6   | 38.6   |
| 57.5°  | 33.1   | 31.0   | 32.4   | 33.8   | 33.8   | 33.1   | 33.8   | 33.8   | 34.5   | 34.5   | 34.5   |
| 60°    | 30.3   | 28.3   | 29.6   | 30.3   | 30.3   | 29.6   | 30.3   | 30.3   | 31.0   | 31.0   | 31.0   |
| 62.5°  | 26.9   | 24.8   | 26.2   | 26.9   | 26.9   | 26.2   | 26.9   | 26.9   | 27.6   | 27.6   | 27.6   |
| 65°    | 24.1   | 22.1   | 22.8   | 23.4   | 23.4   | 23.4   | 24.1   | 24.1   | 24.8   | 24.8   | 24.8   |
| 67.5°  | 22.8   | 20.0   | 20.7   | 21.4   | 21.4   | 21.4   | 22.1   | 22.1   | 22.8   | 22.8   | 23.4   |
| 70°    | 22.1   | 19.3   | 20.0   | 20.0   | 20.7   | 20.7   | 20.7   | 21.4   | 21.4   | 21.4   | 21.4   |
| 72.5°  | 21.4   | 18.6   | 18.6   | 18.6   | 19.3   | 19.3   | 19.3   | 20.0   | 20.0   | 20.0   | 20.0   |
| 75°    | 21.4   | 18.6   | 17.9   | 17.2   | 17.9   | 17.9   | 17.9   | 18.6   | 18.6   | 18.6   | 18.6   |
| 77.5°  | 18.6   | 15.2   | 13.8   | 11.7   | 13.8   | 15.2   | 15.9   | 15.9   | 16.5   | 16.5   | 16.5   |
| 80°    | 7.6    | 3.4    | 2.1    | 0.0    | 0.7    | 1.4    | 2.1    | 2.8    | 3.4    | 4.1    | 4.8    |
| 82.5°  | 2.8    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°    | 2.1    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85° | 87.5° | 90° | 92.5° | 95° | 97.5° | 100° | 102.5° | 105° | 107.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|------|--------|------|--------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 110°   | 112.5° | 115°   | 117.5° | 120°   | 122.5° | 125°   | 127.5° | 130°   | 132.5° | 135°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 |
| 2.5°   | 1366.5 | 1332.0 | 1297.6 | 1314.1 | 1330.6 | 1347.2 | 1363.7 | 1362.4 | 1360.3 | 1358.9 | 1356.8 |
| 5°     | 1392.0 | 1389.9 | 1387.9 | 1378.2 | 1369.3 | 1359.6 | 1349.9 | 1347.9 | 1345.1 | 1343.1 | 1340.3 |
| 7.5°   | 1170.7 | 1174.1 | 1178.3 | 1167.2 | 1156.2 | 1145.2 | 1134.2 | 1105.9 | 1077.6 | 1048.7 | 1020.4 |
| 10°    | 877.0  | 860.4  | 844.6  | 843.2  | 841.8  | 840.4  | 839.1  | 836.3  | 833.5  | 830.1  | 827.3  |
| 12.5°  | 619.8  | 629.5  | 639.1  | 635.7  | 632.2  | 628.1  | 624.6  | 629.5  | 635.0  | 639.8  | 644.6  |
| 15°    | 377.8  | 384.0  | 389.5  | 402.0  | 414.4  | 426.8  | 439.2  | 444.0  | 449.5  | 454.3  | 459.2  |
| 17.5°  | 246.1  | 246.8  | 248.2  | 262.0  | 275.1  | 288.9  | 302.0  | 310.9  | 319.9  | 328.2  | 337.1  |
| 20°    | 200.6  | 198.6  | 196.5  | 204.1  | 211.7  | 219.2  | 226.8  | 235.1  | 243.4  | 251.7  | 259.9  |
| 22.5°  | 178.6  | 177.2  | 175.8  | 178.6  | 181.3  | 183.4  | 186.2  | 192.4  | 199.3  | 205.5  | 211.7  |
| 25°    | 164.1  | 162.7  | 162.0  | 163.4  | 164.8  | 166.2  | 167.5  | 171.0  | 174.4  | 177.9  | 181.3  |
| 27.5°  | 147.5  | 148.2  | 148.2  | 149.6  | 150.3  | 151.7  | 152.4  | 153.7  | 155.8  | 157.2  | 158.6  |
| 30°    | 135.1  | 136.5  | 137.2  | 138.6  | 139.3  | 140.6  | 141.3  | 140.6  | 140.0  | 139.3  | 138.6  |
| 32.5°  | 123.4  | 122.7  | 122.7  | 124.1  | 124.8  | 126.2  | 126.9  | 128.2  | 129.6  | 130.3  | 131.7  |
| 35°    | 111.7  | 112.4  | 112.4  | 112.4  | 113.1  | 113.1  | 113.1  | 114.4  | 116.5  | 117.9  | 119.3  |
| 37.5°  | 101.3  | 101.3  | 100.7  | 102.7  | 104.1  | 106.2  | 107.6  | 108.9  | 111.0  | 112.4  | 113.8  |
| 40°    | 92.4   | 92.4   | 92.4   | 93.8   | 95.1   | 95.8   | 97.2   | 100.7  | 104.1  | 107.6  | 111.0  |
| 42.5°  | 82.7   | 83.4   | 83.4   | 84.8   | 86.2   | 86.9   | 88.3   | 91.0   | 93.1   | 95.8   | 97.9   |
| 45°    | 73.8   | 74.5   | 75.2   | 76.5   | 77.2   | 78.6   | 79.3   | 80.7   | 81.4   | 82.7   | 83.4   |
| 47.5°  | 63.4   | 64.1   | 64.8   | 66.2   | 66.9   | 68.3   | 68.9   | 68.3   | 68.3   | 67.6   | 66.9   |
| 50°    | 53.1   | 53.8   | 54.5   | 56.5   | 57.9   | 60.0   | 61.4   | 60.0   | 58.6   | 56.5   | 55.2   |
| 52.5°  | 44.8   | 44.8   | 45.5   | 46.9   | 48.3   | 49.0   | 50.3   | 49.6   | 49.0   | 48.3   | 47.6   |
| 55°    | 38.6   | 38.6   | 38.6   | 39.3   | 40.0   | 40.7   | 41.4   | 42.1   | 42.1   | 42.7   | 42.7   |
| 57.5°  | 34.5   | 33.8   | 33.8   | 34.5   | 35.2   | 35.2   | 35.9   | 36.5   | 36.5   | 37.2   | 37.2   |
| 60°    | 31.0   | 30.3   | 30.3   | 31.0   | 31.7   | 32.4   | 33.1   | 33.1   | 33.1   | 32.4   | 32.4   |
| 62.5°  | 27.6   | 27.6   | 27.6   | 28.3   | 28.3   | 29.0   | 29.0   | 29.0   | 29.6   | 29.6   | 29.6   |
| 65°    | 25.5   | 25.5   | 25.5   | 25.5   | 25.5   | 24.8   | 24.8   | 25.5   | 25.5   | 26.2   | 26.2   |
| 67.5°  | 23.4   | 24.1   | 24.1   | 23.4   | 22.8   | 22.1   | 21.4   | 22.1   | 22.1   | 22.8   | 22.8   |
| 70°    | 21.4   | 21.4   | 21.4   | 20.7   | 20.0   | 19.3   | 18.6   | 18.6   | 18.6   | 17.9   | 17.9   |
| 72.5°  | 20.0   | 19.3   | 19.3   | 18.6   | 17.2   | 16.5   | 15.2   | 14.5   | 14.5   | 13.8   | 13.1   |
| 75°    | 18.6   | 17.9   | 17.9   | 16.5   | 15.2   | 13.8   | 12.4   | 11.7   | 10.3   | 9.7    | 8.3    |
| 77.5°  | 16.5   | 16.5   | 16.5   | 14.5   | 13.1   | 11.0   | 9.0    | 7.6    | 6.2    | 4.1    | 2.8    |
| 80°    | 5.5    | 6.2    | 6.9    | 6.2    | 6.2    | 5.5    | 4.8    | 3.4    | 2.8    | 1.4    | 0.0    |
| 82.5°  | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° | 135° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |





REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140°   | 142.5° | 145°   | 147.5° | 150°   | 152.5° | 155°   | 157.5° | 160°   | 162.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 |
| 2.5°   | 1364.4 | 1372.0 | 1379.6 | 1387.2 | 1387.9 | 1388.6 | 1389.2 | 1389.9 | 1372.7 | 1354.8 | 1337.5 |
| 5°     | 1354.1 | 1368.6 | 1382.4 | 1396.1 | 1388.6 | 1381.0 | 1373.4 | 1365.8 | 1365.1 | 1365.1 | 1364.4 |
| 7.5°   | 1022.5 | 1023.8 | 1025.9 | 1027.3 | 1030.0 | 1032.8 | 1034.9 | 1037.6 | 1048.7 | 1059.7 | 1070.0 |
| 10°    | 818.4  | 809.4  | 799.8  | 790.8  | 783.9  | 776.3  | 769.4  | 761.8  | 767.4  | 773.6  | 779.1  |
| 12.5°  | 637.1  | 629.5  | 621.2  | 613.6  | 610.9  | 608.1  | 604.7  | 601.9  | 619.8  | 637.7  | 655.0  |
| 15°    | 457.8  | 456.4  | 454.3  | 453.0  | 461.9  | 470.9  | 479.9  | 488.8  | 504.0  | 518.5  | 533.6  |
| 17.5°  | 340.6  | 344.0  | 347.5  | 350.9  | 356.4  | 362.0  | 366.8  | 372.3  | 383.3  | 395.1  | 406.1  |
| 20°    | 264.1  | 268.9  | 273.0  | 277.2  | 275.8  | 274.4  | 272.3  | 271.0  | 279.9  | 288.9  | 297.2  |
| 22.5°  | 215.8  | 219.2  | 223.4  | 226.8  | 227.5  | 228.2  | 228.9  | 229.6  | 235.1  | 239.9  | 245.4  |
| 25°    | 184.8  | 188.9  | 192.4  | 195.8  | 196.5  | 197.2  | 197.9  | 198.6  | 205.5  | 212.4  | 218.6  |
| 27.5°  | 163.4  | 167.5  | 172.4  | 176.5  | 177.9  | 179.3  | 180.6  | 182.0  | 186.2  | 189.6  | 193.7  |
| 30°    | 144.1  | 149.6  | 155.1  | 160.6  | 162.7  | 164.8  | 166.8  | 168.9  | 173.1  | 177.9  | 182.0  |
| 32.5°  | 134.4  | 137.9  | 140.6  | 143.4  | 148.2  | 152.4  | 157.2  | 161.3  | 166.2  | 171.7  | 176.5  |
| 35°    | 123.4  | 126.9  | 131.0  | 134.4  | 137.9  | 141.3  | 144.1  | 147.5  | 150.3  | 153.1  | 155.1  |
| 37.5°  | 116.5  | 120.0  | 122.7  | 125.5  | 126.9  | 128.2  | 128.9  | 130.3  | 131.7  | 133.1  | 133.8  |
| 40°    | 111.0  | 110.3  | 110.3  | 109.6  | 111.0  | 113.1  | 114.4  | 115.8  | 120.0  | 123.4  | 127.5  |
| 42.5°  | 96.5   | 94.5   | 93.1   | 91.0   | 94.5   | 97.2   | 100.7  | 103.4  | 108.9  | 114.4  | 120.0  |
| 45°    | 82.0   | 80.7   | 78.6   | 77.2   | 82.0   | 86.9   | 91.7   | 96.5   | 102.7  | 108.2  | 114.4  |
| 47.5°  | 67.6   | 68.3   | 68.3   | 68.9   | 73.8   | 78.6   | 82.7   | 87.6   | 93.8   | 100.0  | 106.2  |
| 50°    | 56.5   | 57.9   | 59.3   | 60.7   | 65.5   | 69.6   | 74.5   | 78.6   | 85.5   | 91.7   | 98.6   |
| 52.5°  | 49.6   | 51.7   | 53.1   | 55.2   | 59.3   | 64.1   | 68.3   | 72.4   | 78.6   | 84.8   | 91.0   |
| 55°    | 44.8   | 47.6   | 49.6   | 51.7   | 55.2   | 58.6   | 62.1   | 65.5   | 71.7   | 77.9   | 83.4   |
| 57.5°  | 39.3   | 41.4   | 43.4   | 45.5   | 49.0   | 52.4   | 55.2   | 58.6   | 64.1   | 70.3   | 75.8   |
| 60°    | 34.5   | 35.9   | 37.9   | 39.3   | 42.1   | 45.5   | 48.3   | 51.0   | 56.5   | 62.1   | 66.9   |
| 62.5°  | 30.3   | 31.7   | 32.4   | 33.1   | 35.9   | 38.6   | 41.4   | 44.1   | 49.0   | 54.5   | 59.3   |
| 65°    | 26.9   | 27.6   | 27.6   | 28.3   | 30.3   | 33.1   | 35.2   | 37.2   | 42.7   | 47.6   | 53.1   |
| 67.5°  | 22.8   | 23.4   | 23.4   | 23.4   | 25.5   | 27.6   | 29.6   | 31.7   | 36.5   | 42.1   | 46.9   |
| 70°    | 17.9   | 18.6   | 18.6   | 18.6   | 20.7   | 23.4   | 25.5   | 27.6   | 31.7   | 35.9   | 40.0   |
| 72.5°  | 13.8   | 13.8   | 14.5   | 14.5   | 16.5   | 19.3   | 21.4   | 23.4   | 26.9   | 30.3   | 33.8   |
| 75°    | 9.0    | 9.7    | 9.7    | 10.3   | 12.4   | 15.2   | 17.2   | 19.3   | 22.8   | 26.2   | 29.0   |
| 77.5°  | 3.4    | 4.8    | 5.5    | 6.2    | 8.3    | 10.3   | 12.4   | 14.5   | 17.2   | 20.7   | 23.4   |
| 80°    | 0.0    | 0.7    | 0.7    | 0.7    | 2.1    | 2.8    | 4.1    | 4.8    | 6.9    | 9.7    | 11.7   |
| 82.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° | 162.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 165°   | 167.5° | 170°   | 172.5° | 175°   | 177.5° | 180°   | 182.5° | 185°   | 187.5° | 190°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 |
| 2.5°   | 1319.6 | 1357.5 | 1395.5 | 1433.4 | 1471.3 | 1518.2 | 1565.1 | 1572.0 | 1578.8 | 1570.6 | 1563.0 |
| 5°     | 1363.7 | 1382.4 | 1400.3 | 1418.9 | 1436.8 | 1490.6 | 1543.7 | 1544.4 | 1544.4 | 1545.1 | 1545.1 |
| 7.5°   | 1081.1 | 1096.9 | 1112.8 | 1127.9 | 1143.8 | 1179.0 | 1214.1 | 1227.2 | 1239.6 | 1236.9 | 1234.1 |
| 10°    | 784.6  | 805.3  | 825.3  | 846.0  | 866.0  | 898.4  | 930.8  | 943.2  | 954.9  | 992.8  | 1031.4 |
| 12.5°  | 672.9  | 692.9  | 712.9  | 732.2  | 752.2  | 785.3  | 818.4  | 842.5  | 866.0  | 889.4  | 912.8  |
| 15°    | 548.1  | 564.0  | 580.5  | 596.4  | 612.2  | 627.4  | 642.6  | 672.2  | 701.2  | 724.6  | 748.1  |
| 17.5°  | 417.1  | 424.0  | 430.2  | 437.1  | 443.3  | 450.2  | 457.1  | 469.5  | 481.2  | 501.9  | 521.9  |
| 20°    | 306.1  | 311.6  | 317.1  | 322.0  | 327.5  | 334.4  | 341.3  | 350.2  | 358.5  | 363.3  | 367.5  |
| 22.5°  | 250.3  | 258.5  | 266.8  | 274.4  | 282.7  | 287.5  | 292.3  | 295.1  | 297.8  | 299.9  | 302.0  |
| 25°    | 225.5  | 233.0  | 239.9  | 247.5  | 254.4  | 256.5  | 258.5  | 264.1  | 269.6  | 269.6  | 269.6  |
| 27.5°  | 197.2  | 207.5  | 218.6  | 228.9  | 239.2  | 242.0  | 244.1  | 246.1  | 247.5  | 244.8  | 241.3  |
| 30°    | 186.2  | 196.5  | 206.8  | 216.5  | 226.8  | 231.0  | 234.4  | 236.5  | 238.6  | 235.1  | 231.7  |
| 32.5°  | 181.3  | 191.0  | 199.9  | 209.6  | 218.6  | 224.1  | 228.9  | 234.4  | 239.2  | 239.9  | 241.3  |
| 35°    | 157.9  | 164.1  | 171.0  | 177.2  | 183.4  | 186.2  | 188.9  | 191.0  | 192.4  | 192.4  | 192.4  |
| 37.5°  | 135.1  | 143.4  | 152.4  | 160.6  | 168.9  | 175.1  | 181.3  | 182.0  | 182.0  | 183.4  | 185.5  |
| 40°    | 131.0  | 139.3  | 147.5  | 155.1  | 163.4  | 170.3  | 176.5  | 177.2  | 177.9  | 179.3  | 180.6  |
| 42.5°  | 125.5  | 134.4  | 143.4  | 152.4  | 161.3  | 168.2  | 174.4  | 174.4  | 173.7  | 175.8  | 177.2  |
| 45°    | 120.0  | 128.9  | 137.2  | 146.2  | 154.4  | 163.4  | 171.7  | 169.6  | 166.8  | 170.3  | 173.1  |
| 47.5°  | 112.4  | 122.0  | 131.7  | 140.6  | 150.3  | 158.6  | 166.2  | 164.8  | 162.7  | 166.2  | 169.6  |
| 50°    | 104.8  | 114.4  | 124.1  | 133.8  | 143.4  | 152.4  | 160.6  | 159.3  | 157.9  | 162.0  | 165.5  |
| 52.5°  | 97.2   | 106.9  | 117.2  | 126.9  | 136.5  | 144.1  | 151.0  | 150.3  | 149.6  | 153.7  | 158.6  |
| 55°    | 89.6   | 98.6   | 108.2  | 117.2  | 126.2  | 134.4  | 142.0  | 140.6  | 139.3  | 142.7  | 146.2  |
| 57.5°  | 81.4   | 90.3   | 98.6   | 107.6  | 115.8  | 122.7  | 128.9  | 126.9  | 124.8  | 128.9  | 133.1  |
| 60°    | 72.4   | 80.7   | 88.9   | 96.5   | 104.8  | 110.3  | 115.1  | 113.8  | 111.7  | 115.8  | 120.0  |
| 62.5°  | 64.1   | 71.7   | 79.3   | 86.2   | 93.8   | 97.9   | 102.0  | 100.7  | 99.3   | 103.4  | 108.2  |
| 65°    | 57.9   | 64.1   | 69.6   | 75.8   | 81.4   | 85.5   | 89.6   | 87.6   | 85.5   | 90.3   | 94.5   |
| 67.5°  | 51.7   | 56.5   | 62.1   | 66.9   | 71.7   | 75.2   | 78.6   | 77.2   | 75.2   | 78.6   | 82.0   |
| 70°    | 44.1   | 49.0   | 53.8   | 57.9   | 62.7   | 66.2   | 69.6   | 67.6   | 64.8   | 68.3   | 71.7   |
| 72.5°  | 37.2   | 41.4   | 45.5   | 49.0   | 53.1   | 55.8   | 58.6   | 56.5   | 54.5   | 57.2   | 60.0   |
| 75°    | 32.4   | 35.9   | 39.3   | 42.1   | 45.5   | 46.9   | 48.3   | 47.6   | 46.2   | 49.0   | 51.0   |
| 77.5°  | 26.2   | 29.0   | 32.4   | 35.2   | 37.9   | 37.9   | 37.9   | 38.6   | 38.6   | 41.4   | 44.8   |
| 80°    | 13.8   | 16.5   | 19.3   | 21.4   | 24.1   | 24.1   | 23.4   | 24.8   | 25.5   | 29.0   | 32.4   |
| 82.5°  | 0.0    | 2.1    | 4.1    | 6.2    | 8.3    | 7.6    | 6.2    | 6.9    | 6.9    | 8.3    | 9.7    |
| 85°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.7    | 1.4    |
| 87.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° | 190° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P367953

CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195°   | 197.5° | 200°   | 202.5° | 205°   | 207.5° | 210°   | 212.5° | 215°   | 217.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 |
| 2.5°   | 1554.7 | 1546.4 | 1540.9 | 1536.1 | 1530.6 | 1525.1 | 1532.0 | 1538.9 | 1545.1 | 1552.0 | 1572.6 |
| 5°     | 1545.8 | 1545.8 | 1540.9 | 1536.1 | 1531.3 | 1526.4 | 1536.8 | 1546.4 | 1556.8 | 1566.4 | 1565.7 |
| 7.5°   | 1230.7 | 1227.9 | 1256.9 | 1285.1 | 1314.1 | 1342.4 | 1349.9 | 1357.5 | 1364.4 | 1372.0 | 1369.9 |
| 10°    | 1069.3 | 1107.3 | 1119.7 | 1132.1 | 1144.5 | 1156.9 | 1172.1 | 1187.2 | 1202.4 | 1217.6 | 1223.1 |
| 12.5°  | 936.3  | 959.7  | 999.7  | 1039.0 | 1079.0 | 1118.3 | 1138.3 | 1159.0 | 1179.0 | 1199.0 | 1238.3 |
| 15°    | 771.5  | 794.9  | 829.4  | 863.9  | 898.4  | 932.8  | 964.5  | 996.9  | 1028.7 | 1060.4 | 1108.0 |
| 17.5°  | 542.6  | 562.6  | 588.8  | 615.0  | 640.5  | 666.7  | 715.7  | 764.6  | 813.6  | 862.5  | 912.8  |
| 20°    | 372.3  | 376.4  | 388.9  | 402.0  | 414.4  | 426.8  | 470.9  | 515.7  | 559.8  | 604.0  | 670.1  |
| 22.5°  | 303.4  | 305.4  | 311.6  | 317.8  | 323.4  | 329.6  | 352.3  | 375.8  | 398.5  | 421.3  | 475.0  |
| 25°    | 268.9  | 268.9  | 273.0  | 277.2  | 281.3  | 285.4  | 297.8  | 310.3  | 322.0  | 334.4  | 368.9  |
| 27.5°  | 238.6  | 235.1  | 241.3  | 247.5  | 253.7  | 259.9  | 268.9  | 278.5  | 287.5  | 296.5  | 319.9  |
| 30°    | 228.2  | 224.8  | 232.3  | 239.9  | 247.5  | 255.1  | 264.1  | 273.0  | 281.3  | 290.3  | 306.1  |
| 32.5°  | 242.0  | 242.7  | 245.4  | 248.2  | 250.3  | 253.0  | 257.2  | 262.0  | 266.1  | 270.3  | 284.1  |
| 35°    | 192.4  | 192.4  | 197.2  | 202.0  | 206.1  | 211.0  | 218.6  | 226.1  | 233.7  | 241.3  | 255.8  |
| 37.5°  | 186.8  | 188.2  | 192.4  | 197.2  | 201.3  | 205.5  | 215.1  | 225.5  | 235.1  | 244.8  | 256.5  |
| 40°    | 181.3  | 182.7  | 188.2  | 193.7  | 199.3  | 204.8  | 214.4  | 223.4  | 233.0  | 242.0  | 253.0  |
| 42.5°  | 179.3  | 180.6  | 187.5  | 195.1  | 202.0  | 208.9  | 217.2  | 225.5  | 233.0  | 241.3  | 256.5  |
| 45°    | 176.5  | 179.3  | 187.5  | 196.5  | 204.8  | 213.0  | 220.6  | 228.2  | 235.8  | 243.4  | 262.0  |
| 47.5°  | 172.4  | 175.8  | 185.5  | 194.4  | 204.1  | 213.0  | 227.5  | 242.7  | 257.2  | 271.6  | 280.6  |
| 50°    | 169.6  | 173.1  | 183.4  | 193.7  | 204.1  | 214.4  | 237.9  | 261.3  | 284.1  | 307.5  | 302.7  |
| 52.5°  | 162.7  | 166.8  | 179.9  | 193.0  | 206.1  | 219.2  | 239.9  | 260.6  | 281.3  | 302.0  | 292.3  |
| 55°    | 149.6  | 153.1  | 168.2  | 183.4  | 197.9  | 213.0  | 228.2  | 243.4  | 257.9  | 273.0  | 262.0  |
| 57.5°  | 136.5  | 140.6  | 155.1  | 169.6  | 183.4  | 197.9  | 205.5  | 213.0  | 220.6  | 228.2  | 224.1  |
| 60°    | 124.1  | 128.2  | 147.5  | 166.8  | 186.2  | 205.5  | 198.6  | 191.7  | 184.1  | 177.2  | 182.0  |
| 62.5°  | 112.4  | 116.5  | 135.1  | 153.1  | 171.7  | 189.6  | 179.9  | 170.3  | 160.6  | 151.0  | 158.6  |
| 65°    | 99.3   | 103.4  | 110.3  | 117.9  | 124.8  | 131.7  | 131.0  | 129.6  | 128.9  | 127.5  | 135.8  |
| 67.5°  | 85.5   | 88.9   | 92.4   | 96.5   | 100.0  | 103.4  | 105.5  | 108.2  | 110.3  | 112.4  | 119.3  |
| 70°    | 74.5   | 77.9   | 82.0   | 85.5   | 89.6   | 93.1   | 94.5   | 95.8   | 96.5   | 97.9   | 104.1  |
| 72.5°  | 62.1   | 64.8   | 70.3   | 75.8   | 80.7   | 86.2   | 86.9   | 86.9   | 87.6   | 87.6   | 92.4   |
| 75°    | 53.8   | 55.8   | 60.0   | 64.1   | 67.6   | 71.7   | 73.8   | 75.8   | 77.2   | 79.3   | 82.0   |
| 77.5°  | 47.6   | 50.3   | 51.7   | 52.4   | 53.8   | 54.5   | 55.8   | 57.2   | 58.6   | 60.0   | 60.7   |
| 80°    | 35.2   | 38.6   | 40.0   | 40.7   | 42.1   | 42.7   | 42.7   | 42.1   | 42.1   | 41.4   | 42.1   |
| 82.5°  | 11.0   | 12.4   | 14.5   | 16.5   | 18.6   | 20.7   | 21.4   | 22.1   | 22.1   | 22.8   | 22.1   |
| 85°    | 2.1    | 2.8    | 4.1    | 5.5    | 6.2    | 7.6    | 6.9    | 5.5    | 4.8    | 3.4    | 2.8    |
| 87.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° | 217.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P367953

CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 220°   | 222.5° | 225°   | 227.5° | 230°   | 232.5° | 235°   | 237.5° | 240°   | 242.5° | 245°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 |
| 2.5°   | 1593.3 | 1613.3 | 1634.0 | 1625.7 | 1617.5 | 1609.2 | 1600.9 | 1602.3 | 1604.4 | 1605.7 | 1607.1 |
| 5°     | 1565.1 | 1563.7 | 1563.0 | 1586.4 | 1610.6 | 1634.0 | 1657.4 | 1683.0 | 1709.2 | 1734.7 | 1760.2 |
| 7.5°   | 1367.9 | 1365.1 | 1363.0 | 1393.4 | 1423.7 | 1454.1 | 1484.4 | 1519.6 | 1555.4 | 1590.6 | 1625.7 |
| 10°    | 1228.6 | 1234.1 | 1239.6 | 1252.0 | 1265.1 | 1277.6 | 1290.0 | 1323.8 | 1357.5 | 1390.6 | 1424.4 |
| 12.5°  | 1277.6 | 1316.2 | 1355.5 | 1363.0 | 1369.9 | 1377.5 | 1384.4 | 1389.2 | 1394.1 | 1398.9 | 1403.7 |
| 15°    | 1156.2 | 1203.8 | 1251.4 | 1271.4 | 1290.7 | 1310.7 | 1330.0 | 1381.0 | 1431.3 | 1482.3 | 1532.7 |
| 17.5°  | 963.2  | 1012.8 | 1063.1 | 1123.1 | 1183.1 | 1243.1 | 1303.1 | 1358.2 | 1413.4 | 1468.5 | 1523.7 |
| 20°    | 737.0  | 803.2  | 869.4  | 945.2  | 1021.8 | 1097.6 | 1173.4 | 1228.6 | 1283.1 | 1338.2 | 1392.7 |
| 22.5°  | 529.5  | 583.3  | 637.1  | 728.8  | 819.8  | 911.5  | 1002.5 | 1098.3 | 1194.8 | 1290.7 | 1386.5 |
| 25°    | 403.3  | 437.1  | 471.6  | 561.9  | 652.2  | 741.9  | 832.2  | 963.9  | 1095.5 | 1227.2 | 1358.9 |
| 27.5°  | 342.7  | 366.1  | 388.9  | 470.2  | 551.6  | 632.2  | 713.6  | 870.1  | 1026.6 | 1183.1 | 1339.6 |
| 30°    | 322.7  | 338.5  | 354.4  | 423.3  | 493.0  | 561.9  | 630.8  | 789.4  | 948.0  | 1106.6 | 1265.1 |
| 32.5°  | 297.8  | 310.9  | 324.7  | 385.4  | 446.1  | 506.1  | 566.7  | 721.9  | 877.0  | 1031.4 | 1186.5 |
| 35°    | 269.6  | 284.1  | 297.8  | 358.5  | 419.2  | 479.2  | 539.8  | 700.5  | 861.1  | 1021.8 | 1182.4 |
| 37.5°  | 267.5  | 279.2  | 290.3  | 360.6  | 431.6  | 501.9  | 572.2  | 732.9  | 893.5  | 1053.5 | 1214.1 |
| 40°    | 264.8  | 275.8  | 286.8  | 358.5  | 429.5  | 501.2  | 572.2  | 740.5  | 908.7  | 1076.9 | 1245.2 |
| 42.5°  | 271.6  | 286.1  | 301.3  | 364.7  | 428.2  | 490.9  | 554.3  | 731.5  | 908.7  | 1085.2 | 1262.4 |
| 45°    | 281.3  | 299.9  | 318.5  | 376.4  | 434.4  | 492.3  | 550.2  | 742.5  | 934.9  | 1126.6 | 1318.9 |
| 47.5°  | 290.3  | 299.2  | 308.2  | 363.3  | 417.8  | 473.0  | 527.4  | 723.9  | 920.4  | 1116.9 | 1313.4 |
| 50°    | 298.5  | 293.7  | 288.9  | 349.6  | 410.2  | 470.2  | 530.9  | 718.4  | 905.3  | 1092.8 | 1279.6 |
| 52.5°  | 282.0  | 272.3  | 262.0  | 326.8  | 391.6  | 455.7  | 520.5  | 709.4  | 898.4  | 1087.3 | 1276.2 |
| 55°    | 251.0  | 239.9  | 228.9  | 293.0  | 356.4  | 420.6  | 484.0  | 672.2  | 860.4  | 1048.7 | 1236.9 |
| 57.5°  | 219.2  | 215.1  | 210.3  | 259.2  | 308.2  | 356.4  | 405.4  | 614.3  | 823.9  | 1032.8 | 1241.7 |
| 60°    | 186.8  | 191.0  | 195.8  | 231.0  | 266.1  | 300.6  | 335.8  | 540.5  | 744.6  | 949.4  | 1153.5 |
| 62.5°  | 165.5  | 173.1  | 179.9  | 209.6  | 239.9  | 269.6  | 299.2  | 492.3  | 685.3  | 878.4  | 1071.4 |
| 65°    | 144.8  | 153.1  | 161.3  | 196.5  | 232.3  | 267.5  | 302.7  | 466.1  | 629.5  | 792.9  | 956.3  |
| 67.5°  | 126.2  | 132.4  | 139.3  | 185.5  | 231.7  | 277.8  | 324.0  | 457.8  | 590.9  | 724.6  | 857.7  |
| 70°    | 110.3  | 115.8  | 122.0  | 175.8  | 229.6  | 283.4  | 337.1  | 450.9  | 565.4  | 679.1  | 792.9  |
| 72.5°  | 97.2   | 102.0  | 106.9  | 161.3  | 215.8  | 270.3  | 324.7  | 426.1  | 526.7  | 628.1  | 728.8  |
| 75°    | 84.8   | 86.9   | 89.6   | 135.8  | 181.3  | 227.5  | 273.0  | 340.6  | 408.8  | 476.4  | 544.0  |
| 77.5°  | 61.4   | 61.4   | 62.1   | 75.8   | 88.9   | 102.7  | 115.8  | 157.9  | 199.9  | 241.3  | 283.4  |
| 80°    | 42.1   | 42.7   | 42.7   | 48.3   | 53.1   | 58.6   | 63.4   | 72.4   | 80.7   | 89.6   | 97.9   |
| 82.5°  | 21.4   | 20.0   | 19.3   | 24.8   | 30.3   | 35.9   | 41.4   | 43.4   | 44.8   | 46.9   | 48.3   |
| 85°    | 2.1    | 0.7    | 0.0    | 3.4    | 6.9    | 10.3   | 13.8   | 16.5   | 19.3   | 22.1   | 24.8   |
| 87.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° | 245° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |





REPORT NUMBER: P367953

CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°   | 252.5° | 255°   | 257.5° | 260°   | 262.5° | 265°    | 267.5°  | 270°    | 272.5°  |
|--------|--------|--------|--------|--------|--------|--------|--------|---------|---------|---------|---------|
| 0°     | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5 | 1457.5  | 1457.5  | 1457.5  | 1457.5  |
| 2.5°   | 1601.6 | 1596.1 | 1590.6 | 1585.1 | 1618.8 | 1653.3 | 1687.1 | 1720.9  | 1816.7  | 1879.4  | 1872.6  |
| 5°     | 1785.0 | 1809.8 | 1834.6 | 1859.5 | 1899.4 | 1940.1 | 1980.1 | 2020.1  | 2162.1  | 2249.0  | 2261.4  |
| 7.5°   | 1664.3 | 1702.3 | 1740.9 | 1778.8 | 1856.0 | 1932.5 | 2009.8 | 2086.3  | 2202.8  | 2293.1  | 2344.1  |
| 10°    | 1467.8 | 1511.3 | 1554.0 | 1597.5 | 1684.3 | 1771.9 | 1858.8 | 1945.6  | 2076.6  | 2201.4  | 2265.5  |
| 12.5°  | 1472.0 | 1540.2 | 1608.5 | 1676.8 | 1752.6 | 1828.4 | 1903.6 | 1979.4  | 2059.4  | 2101.5  | 2191.8  |
| 15°    | 1586.4 | 1640.2 | 1694.0 | 1747.8 | 1847.0 | 1946.3 | 2044.9 | 2144.2  | 2191.8  | 2293.1  | 2398.6  |
| 17.5°  | 1628.5 | 1734.0 | 1838.8 | 1943.6 | 2067.7 | 2191.1 | 2315.2 | 2438.6  | 2528.2  | 2668.9  | 2777.8  |
| 20°    | 1550.6 | 1708.5 | 1865.7 | 2023.5 | 2193.8 | 2364.1 | 2534.4 | 2704.7  | 2802.6  | 2936.4  | 3104.6  |
| 22.5°  | 1554.0 | 1721.6 | 1888.4 | 2055.9 | 2291.1 | 2525.5 | 2760.6 | 2995.0  | 3257.7  | 3515.5  | 3597.6  |
| 25°    | 1578.2 | 1797.4 | 2016.0 | 2235.2 | 2506.9 | 2778.5 | 3050.1 | 3321.8  | 3638.9  | 3909.9  | 4018.8  |
| 27.5°  | 1586.4 | 1833.3 | 2079.4 | 2326.2 | 2712.3 | 3098.4 | 3484.5 | 3870.6  | 4249.1  | 4555.2  | 4671.7  |
| 30°    | 1566.4 | 1868.4 | 2169.7 | 2471.0 | 2944.7 | 3418.3 | 3892.0 | 4365.6  | 4724.8  | 5081.3  | 5226.1  |
| 32.5°  | 1571.3 | 1956.0 | 2340.7 | 2725.4 | 3283.2 | 3841.6 | 4399.4 | 4957.2  | 5186.8  | 5508.0  | 5763.1  |
| 35°    | 1604.4 | 2026.3 | 2447.6 | 2869.5 | 3486.6 | 4103.6 | 4720.7 | 5337.7  | 5714.2  | 6053.4  | 6269.9  |
| 37.5°  | 1681.6 | 2149.0 | 2615.8 | 3083.2 | 3841.6 | 4600.7 | 5359.1 | 6117.5  | 6700.1  | 7282.7  | 7382.0  |
| 40°    | 1738.8 | 2232.4 | 2726.1 | 3219.7 | 4100.2 | 4980.6 | 5861.0 | 6741.5  | 7400.6  | 8032.8  | 8100.4  |
| 42.5°  | 1803.6 | 2344.1 | 2885.4 | 3425.9 | 4410.4 | 5395.0 | 6379.5 | 7364.1  | 8127.3  | 8771.9  | 8816.7  |
| 45°    | 1874.6 | 2431.0 | 2986.7 | 3542.4 | 4573.8 | 5604.6 | 6636.0 | 7666.7  | 8558.2  | 9306.9  | 9138.0  |
| 47.5°  | 1908.4 | 2503.4 | 3098.4 | 3693.4 | 4799.3 | 5904.5 | 7010.4 | 8115.6  | 8915.3  | 9575.8  | 9378.6  |
| 50°    | 1934.6 | 2588.9 | 3243.9 | 3898.2 | 5057.8 | 6217.5 | 7377.1 | 8536.8  | 9338.6  | 9948.1  | 9639.2  |
| 52.5°  | 2008.4 | 2739.9 | 3472.1 | 4203.6 | 5437.0 | 6669.8 | 7903.2 | 9135.9  | 9911.6  | 10471.4 | 10038.4 |
| 55°    | 2080.1 | 2922.6 | 3765.8 | 4608.3 | 5934.8 | 7262.0 | 8588.5 | 9915.0  | 10687.2 | 11167.1 | 10579.0 |
| 57.5°  | 2170.4 | 3099.8 | 4028.5 | 4957.2 | 6376.1 | 7795.0 | 9213.2 | 10632.1 | 11387.0 | 11917.2 | 11306.3 |
| 60°    | 2147.0 | 3139.8 | 4133.3 | 5126.1 | 6571.2 | 8016.3 | 9461.4 | 10906.5 | 11803.4 | 12455.0 | 12040.6 |
| 62.5°  | 2055.9 | 3040.5 | 4024.3 | 5008.9 | 6428.5 | 7847.4 | 9266.9 | 10685.8 | 11760.7 | 12643.2 | 12503.9 |
| 65°    | 1871.9 | 2786.8 | 3702.4 | 4617.3 | 5972.7 | 7328.9 | 8684.4 | 10039.8 | 11366.3 | 12489.4 | 12539.1 |
| 67.5°  | 1629.9 | 2402.1 | 3173.6 | 3945.7 | 5210.2 | 6474.7 | 7738.4 | 9002.9  | 10568.6 | 11878.6 | 12026.1 |
| 70°    | 1373.4 | 1953.2 | 2533.7 | 3113.6 | 4226.3 | 5339.1 | 6451.2 | 7564.0  | 9191.8  | 10510.0 | 10788.6 |
| 72.5°  | 1101.1 | 1474.1 | 1846.4 | 2218.7 | 3021.9 | 3824.4 | 4627.6 | 5430.1  | 6862.1  | 7885.3  | 8371.3  |
| 75°    | 713.6  | 883.2  | 1052.8 | 1222.4 | 1757.4 | 2291.7 | 2826.8 | 3361.1  | 4311.8  | 5065.4  | 5614.9  |
| 77.5°  | 317.8  | 352.3  | 386.1  | 420.6  | 833.5  | 1246.5 | 1659.5 | 2072.5  | 2485.5  | 2940.5  | 3069.4  |
| 80°    | 113.8  | 128.9  | 144.8  | 160.0  | 362.7  | 566.0  | 768.7  | 971.4   | 1171.4  | 1406.5  | 1463.7  |
| 82.5°  | 47.6   | 47.6   | 46.9   | 46.2   | 118.6  | 191.0  | 263.4  | 335.8   | 388.2   | 446.1   | 457.1   |
| 85°    | 19.3   | 14.5   | 9.0    | 3.4    | 15.2   | 27.6   | 39.3   | 51.0    | 82.0    | 74.5    | 137.9   |
| 87.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° | 272.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P367953

CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 275°    | 277.5°  | 280°    | 282.5°  | 285°    | 287.5°  | 290°    | 292.5°  | 295°   | 297.5°  | 300°    |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|--------|---------|---------|
| 0°     | 1457.5  | 1457.5  | 1457.5  | 1457.5  | 1457.5  | 1457.5  | 1457.5  | 1457.5  | 1457.5 | 1457.5  | 1457.5  |
| 2.5°   | 1846.4  | 1845.0  | 1843.6  | 1842.2  | 1840.8  | 1816.0  | 1791.9  | 1767.1  | 1742.9 | 1773.3  | 1803.6  |
| 5°     | 2241.4  | 2277.3  | 2313.1  | 2349.7  | 2385.5  | 2395.9  | 2406.2  | 2416.5  | 2426.9 | 2448.9  | 2471.0  |
| 7.5°   | 2386.9  | 2447.6  | 2507.5  | 2568.2  | 2628.2  | 2684.0  | 2739.2  | 2795.0  | 2850.9 | 2837.1  | 2823.3  |
| 10°    | 2336.6  | 2446.2  | 2555.8  | 2666.1  | 2775.7  | 2799.9  | 2824.0  | 2848.8  | 2873.0 | 2935.7  | 2998.4  |
| 12.5°  | 2282.1  | 2413.8  | 2545.5  | 2677.1  | 2808.8  | 2881.9  | 2954.3  | 3027.4  | 3100.5 | 3163.9  | 3227.3  |
| 15°    | 2540.6  | 2624.7  | 2708.9  | 2793.7  | 2877.8  | 2941.9  | 3005.3  | 3069.4  | 3132.9 | 3177.0  | 3220.4  |
| 17.5°  | 2880.5  | 2921.9  | 2963.3  | 3005.3  | 3046.7  | 3097.0  | 3147.4  | 3197.7  | 3248.0 | 3274.2  | 3300.4  |
| 20°    | 3239.7  | 3257.7  | 3275.6  | 3293.5  | 3311.4  | 3271.5  | 3231.5  | 3191.5  | 3151.5 | 3176.3  | 3200.4  |
| 22.5°  | 3600.3  | 3606.5  | 3613.4  | 3619.6  | 3625.8  | 3532.8  | 3439.7  | 3346.6  | 3253.5 | 3214.2  | 3174.9  |
| 25°    | 4155.3  | 4109.8  | 4064.3  | 4018.8  | 3973.3  | 3863.0  | 3752.7  | 3642.4  | 3532.1 | 3434.9  | 3337.6  |
| 27.5°  | 4756.5  | 4602.1  | 4448.4  | 4293.9  | 4140.2  | 4029.9  | 3919.5  | 3809.2  | 3698.9 | 3552.8  | 3406.6  |
| 30°    | 5362.6  | 5113.7  | 4865.5  | 4616.6  | 4368.4  | 4237.4  | 4106.4  | 3974.7  | 3843.7 | 3697.5  | 3552.1  |
| 32.5°  | 5918.3  | 5619.0  | 5319.8  | 5019.9  | 4720.7  | 4500.1  | 4279.4  | 4058.8  | 3838.2 | 3736.1  | 3634.1  |
| 35°    | 6378.8  | 6025.1  | 5671.4  | 5317.1  | 4963.4  | 4744.8  | 4526.3  | 4307.7  | 4089.1 | 3937.5  | 3786.5  |
| 37.5°  | 7166.2  | 6768.4  | 6370.5  | 5972.7  | 5574.9  | 5276.4  | 4978.5  | 4680.0  | 4381.5 | 4280.1  | 4178.8  |
| 40°    | 7892.2  | 7390.9  | 6889.7  | 6388.5  | 5887.2  | 5637.0  | 5387.4  | 5137.1  | 4887.5 | 4721.4  | 4555.9  |
| 42.5°  | 8469.2  | 7941.1  | 7413.7  | 6885.6  | 6357.4  | 6109.9  | 5863.1  | 5615.6  | 5368.1 | 5257.1  | 5146.8  |
| 45°    | 8594.0  | 8096.2  | 7599.2  | 7101.4  | 6603.6  | 6459.5  | 6316.1  | 6172.0  | 6028.6 | 5952.0  | 5876.2  |
| 47.5°  | 8840.2  | 8300.3  | 7761.2  | 7221.3  | 6681.5  | 6616.7  | 6551.9  | 6486.4  | 6421.6 | 6458.1  | 6494.6  |
| 50°    | 8978.1  | 8427.2  | 7876.3  | 7325.4  | 6774.6  | 6793.2  | 6811.1  | 6829.7  | 6848.3 | 7107.6  | 7366.1  |
| 52.5°  | 9245.6  | 8689.2  | 8132.8  | 7576.4  | 7020.0  | 7137.2  | 7253.7  | 7370.9  | 7487.5 | 7844.6  | 8201.0  |
| 55°    | 9723.4  | 9176.6  | 8629.9  | 8082.5  | 7535.7  | 7690.2  | 7844.6  | 7999.7  | 8154.2 | 8533.4  | 8911.9  |
| 57.5°  | 10431.4 | 9888.8  | 9346.9  | 8804.3  | 8262.4  | 8416.2  | 8569.9  | 8723.7  | 8877.4 | 9220.1  | 9562.0  |
| 60°    | 11322.9 | 10765.8 | 10209.4 | 9652.3  | 9096.0  | 9153.9  | 9211.1  | 9269.0  | 9326.9 | 9695.1  | 10062.6 |
| 62.5°  | 12017.2 | 11504.9 | 10993.3 | 10481.1 | 9969.5  | 9905.4  | 9841.9  | 9777.8  | 9714.4 | 9994.3  | 10273.5 |
| 65°    | 12178.5 | 11817.9 | 11458.0 | 11097.4 | 10736.9 | 10539.7 | 10343.2 | 10146.0 | 9948.8 | 10061.9 | 10175.0 |
| 67.5°  | 11716.6 | 11473.2 | 11230.5 | 10987.1 | 10743.8 | 10332.1 | 9920.5  | 9508.2  | 9096.6 | 9036.7  | 8976.7  |
| 70°    | 10644.5 | 10511.4 | 10379.0 | 10246.0 | 10113.6 | 9479.3  | 8845.7  | 8211.4  | 7577.8 | 7425.4  | 7273.0  |
| 72.5°  | 8399.6  | 8482.3  | 8565.1  | 8648.5  | 8731.2  | 8052.1  | 7373.7  | 6694.6  | 6015.5 | 5822.4  | 5630.1  |
| 75°    | 5923.1  | 6203.7  | 6484.3  | 6764.9  | 7045.5  | 6426.4  | 5808.0  | 5188.8  | 4569.7 | 4384.2  | 4199.5  |
| 77.5°  | 3211.5  | 3737.5  | 4263.6  | 4789.6  | 5315.7  | 4804.8  | 4294.6  | 3783.7  | 3272.8 | 3143.9  | 3015.7  |
| 80°    | 1522.3  | 1825.7  | 2128.3  | 2431.7  | 2735.1  | 2619.9  | 2504.8  | 2389.0  | 2273.8 | 2302.1  | 2330.4  |
| 82.5°  | 466.8   | 686.0   | 905.3   | 1124.5  | 1343.7  | 1361.0  | 1377.5  | 1394.8  | 1412.0 | 1454.7  | 1496.8  |
| 85°    | 156.5   | 214.4   | 272.3   | 330.2   | 388.2   | 490.2   | 592.2   | 695.0   | 797.0  | 730.8   | 665.3   |
| 87.5°  | 0.0     | 2.1     | 3.4     | 5.5     | 6.9     | 21.4    | 35.9    | 50.3    | 64.8   | 55.8    | 47.6    |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0     | 0.0     |



REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° | 300° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P367953

CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 302.5°  | 305°    | 307.5°  | 310°    | 312.5°  | 315°    | 317.5°  | 320°    | 322.5°  | 325°    | 327.5°  |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 1457.5  | 1457.5  | 1457.5  | 1457.5  | 1457.5  | 1457.5  | 1457.5  | 1457.5  | 1457.5  | 1457.5  | 1457.5  |
| 2.5°   | 1834.6  | 1865.0  | 1865.7  | 1867.0  | 1867.7  | 1868.4  | 1871.9  | 1875.3  | 1879.4  | 1882.9  | 1860.1  |
| 5°     | 2493.8  | 2515.8  | 2475.1  | 2434.5  | 2393.1  | 2352.4  | 2389.0  | 2425.5  | 2462.0  | 2498.6  | 2482.7  |
| 7.5°   | 2808.8  | 2795.0  | 2790.2  | 2786.1  | 2781.3  | 2777.1  | 2790.9  | 2804.7  | 2818.5  | 2832.3  | 2830.9  |
| 10°    | 3061.2  | 3123.9  | 3139.1  | 3154.2  | 3170.1  | 3185.3  | 3153.6  | 3121.8  | 3090.1  | 3058.4  | 3045.3  |
| 12.5°  | 3290.8  | 3354.2  | 3404.5  | 3454.9  | 3505.9  | 3556.2  | 3510.7  | 3465.9  | 3420.4  | 3375.6  | 3332.8  |
| 15°    | 3264.6  | 3308.0  | 3349.4  | 3390.7  | 3432.1  | 3473.5  | 3458.3  | 3443.8  | 3428.7  | 3413.5  | 3406.6  |
| 17.5°  | 3327.3  | 3353.5  | 3343.8  | 3334.2  | 3323.9  | 3314.2  | 3309.4  | 3305.2  | 3300.4  | 3295.6  | 3279.0  |
| 20°    | 3225.3  | 3250.1  | 3243.9  | 3238.4  | 3232.2  | 3226.0  | 3221.8  | 3217.7  | 3213.5  | 3209.4  | 3196.3  |
| 22.5°  | 3135.6  | 3096.3  | 3086.0  | 3076.3  | 3066.0  | 3056.3  | 3057.7  | 3059.1  | 3059.8  | 3061.2  | 3120.5  |
| 25°    | 3240.4  | 3143.2  | 3105.3  | 3067.4  | 3028.8  | 2990.8  | 3008.1  | 3024.6  | 3041.9  | 3059.1  | 3144.6  |
| 27.5°  | 3259.7  | 3113.6  | 3052.9  | 2992.2  | 2931.6  | 2870.9  | 2932.9  | 2995.0  | 3057.0  | 3119.1  | 3257.7  |
| 30°    | 3405.9  | 3260.4  | 3175.6  | 3091.5  | 3006.7  | 2922.6  | 3001.9  | 3081.2  | 3160.5  | 3239.7  | 3390.0  |
| 32.5°  | 3531.4  | 3429.3  | 3368.7  | 3308.0  | 3247.3  | 3186.7  | 3190.1  | 3192.9  | 3196.3  | 3199.8  | 3411.4  |
| 35°    | 3634.8  | 3483.8  | 3428.7  | 3374.2  | 3319.0  | 3264.6  | 3346.6  | 3428.7  | 3510.7  | 3592.7  | 3783.0  |
| 37.5°  | 4077.4  | 3976.1  | 3874.7  | 3774.1  | 3672.7  | 3572.1  | 3637.6  | 3703.1  | 3769.2  | 3834.7  | 4045.0  |
| 40°    | 4389.7  | 4224.3  | 4198.1  | 4172.6  | 4146.4  | 4120.9  | 4154.6  | 4187.7  | 4221.5  | 4255.3  | 4439.4  |
| 42.5°  | 5035.8  | 4924.8  | 4853.8  | 4783.4  | 4712.4  | 4642.1  | 4669.0  | 4695.9  | 4723.4  | 4750.3  | 4924.8  |
| 45°    | 5799.7  | 5723.2  | 5676.3  | 5629.4  | 5581.8  | 5534.9  | 5494.3  | 5454.3  | 5413.6  | 5373.6  | 5550.8  |
| 47.5°  | 6531.2  | 6567.7  | 6671.1  | 6773.9  | 6877.3  | 6980.0  | 6895.9  | 6811.8  | 6727.0  | 6642.9  | 6643.6  |
| 50°    | 7625.4  | 7883.9  | 7936.3  | 7988.0  | 8040.4  | 8092.1  | 7912.9  | 7733.6  | 7553.6  | 7374.4  | 7353.0  |
| 52.5°  | 8558.2  | 8914.6  | 8933.2  | 8951.9  | 8971.2  | 8989.8  | 8917.4  | 8845.0  | 8771.9  | 8699.5  | 8507.2  |
| 55°    | 9291.1  | 9669.6  | 9695.1  | 9719.9  | 9745.4  | 9770.2  | 9706.8  | 9644.1  | 9580.6  | 9517.2  | 9322.8  |
| 57.5°  | 9904.7  | 10246.7 | 10261.8 | 10276.3 | 10291.5 | 10306.6 | 10311.5 | 10316.3 | 10321.8 | 10326.6 | 10063.9 |
| 60°    | 10430.7 | 10798.9 | 10768.6 | 10738.9 | 10708.6 | 10678.9 | 10633.4 | 10587.9 | 10542.4 | 10496.9 | 10327.3 |
| 62.5°  | 10553.5 | 10833.4 | 10786.5 | 10740.3 | 10693.4 | 10647.2 | 10608.6 | 10570.7 | 10532.1 | 10493.5 | 10385.2 |
| 65°    | 10288.0 | 10401.1 | 10352.8 | 10304.6 | 10255.6 | 10207.4 | 10182.5 | 10158.4 | 10133.6 | 10108.8 | 10095.0 |
| 67.5°  | 8916.0  | 8856.0  | 8913.3  | 8970.5  | 9027.7  | 9084.9  | 9162.8  | 9240.7  | 9319.3  | 9397.2  | 9351.7  |
| 70°    | 7120.0  | 6967.6  | 7031.0  | 7093.8  | 7157.2  | 7220.0  | 7337.9  | 7455.7  | 7574.3  | 7692.2  | 7660.5  |
| 72.5°  | 5437.0  | 5244.0  | 5252.9  | 5261.9  | 5271.6  | 5280.5  | 5277.1  | 5274.3  | 5270.9  | 5267.4  | 5322.6  |
| 75°    | 4014.0  | 3828.5  | 3741.0  | 3653.4  | 3565.9  | 3478.3  | 3456.9  | 3435.5  | 3414.2  | 3392.8  | 3495.5  |
| 77.5°  | 2886.7  | 2758.5  | 2698.5  | 2639.2  | 2579.2  | 2520.0  | 2550.3  | 2580.6  | 2611.6  | 2642.0  | 2677.8  |
| 80°    | 2359.3  | 2387.6  | 2341.4  | 2295.9  | 2249.7  | 2203.5  | 2238.0  | 2271.7  | 2306.2  | 2340.7  | 2233.8  |
| 82.5°  | 1539.5  | 1581.6  | 1439.6  | 1297.6  | 1155.5  | 1013.5  | 1099.7  | 1185.9  | 1272.7  | 1358.9  | 1314.8  |
| 85°    | 599.1   | 533.6   | 455.0   | 377.1   | 298.5   | 219.9   | 286.1   | 352.3   | 418.5   | 484.7   | 528.8   |
| 87.5°  | 38.6    | 30.3    | 24.1    | 17.9    | 11.0    | 4.8     | 10.3    | 15.9    | 22.1    | 27.6    | 46.2    |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305° | 307.5° | 310° | 312.5° | 315° | 317.5° | 320° | 322.5° | 325° | 327.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P367953

CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 330°    | 332.5°  | 335°    | 337.5°  | 340°    | 342.5°  | 345°    | 347.5°  | 350°    | 352.5°  | 355°    |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°     | 1457.5  | 1457.5  | 1457.5  | 1457.5  | 1457.5  | 1457.5  | 1457.5  | 1457.5  | 1457.5  | 1457.5  | 1457.5  |
| 2.5°   | 1838.1  | 1815.3  | 1793.3  | 1749.8  | 1706.4  | 1663.0  | 1619.5  | 1680.2  | 1740.9  | 1801.5  | 1862.2  |
| 5°     | 2467.6  | 2451.7  | 2436.5  | 2440.7  | 2444.8  | 2449.6  | 2453.8  | 2462.7  | 2471.7  | 2480.0  | 2488.9  |
| 7.5°   | 2830.2  | 2828.8  | 2827.4  | 2795.7  | 2764.0  | 2731.6  | 2699.9  | 2715.8  | 2731.6  | 2747.5  | 2763.3  |
| 10°    | 3032.9  | 3019.8  | 3006.7  | 2937.1  | 2867.4  | 2797.1  | 2727.5  | 2697.1  | 2666.1  | 2635.8  | 2605.4  |
| 12.5°  | 3290.1  | 3246.6  | 3203.9  | 3129.4  | 3055.7  | 2981.2  | 2906.7  | 2879.2  | 2850.9  | 2823.3  | 2795.0  |
| 15°    | 3400.4  | 3393.5  | 3387.3  | 3334.2  | 3280.4  | 3227.3  | 3173.6  | 3079.1  | 2984.0  | 2889.5  | 2795.0  |
| 17.5°  | 3262.5  | 3245.3  | 3228.7  | 3312.8  | 3396.2  | 3480.4  | 3564.5  | 3466.6  | 3368.7  | 3270.8  | 3172.9  |
| 20°    | 3183.2  | 3170.1  | 3157.0  | 3313.5  | 3469.3  | 3625.8  | 3781.7  | 3738.2  | 3694.1  | 3650.7  | 3607.2  |
| 22.5°  | 3179.8  | 3239.7  | 3299.0  | 3436.2  | 3572.7  | 3709.9  | 3846.5  | 3921.6  | 3997.4  | 4072.6  | 4147.8  |
| 25°    | 3230.1  | 3316.3  | 3401.8  | 3629.3  | 3856.8  | 4085.0  | 4312.5  | 4398.7  | 4484.2  | 4570.4  | 4655.9  |
| 27.5°  | 3395.6  | 3534.1  | 3672.0  | 3870.6  | 4069.2  | 4268.4  | 4467.0  | 4655.2  | 4844.1  | 5032.3  | 5220.5  |
| 30°    | 3539.7  | 3690.0  | 3840.3  | 4076.7  | 4312.5  | 4549.0  | 4784.8  | 5020.6  | 5256.4  | 5492.2  | 5728.0  |
| 32.5°  | 3623.1  | 3835.4  | 4047.1  | 4334.6  | 4621.4  | 4908.9  | 5196.4  | 5455.0  | 5713.5  | 5971.4  | 6229.9  |
| 35°    | 3973.3  | 4164.3  | 4354.6  | 4672.4  | 4990.3  | 5308.8  | 5626.6  | 5946.5  | 6266.4  | 6585.7  | 6905.6  |
| 37.5°  | 4255.3  | 4466.3  | 4676.6  | 5024.0  | 5370.8  | 5718.3  | 6065.8  | 6507.7  | 6950.4  | 7392.3  | 7834.3  |
| 40°    | 4623.5  | 4807.6  | 4991.6  | 5317.1  | 5641.8  | 5967.2  | 6292.6  | 6853.2  | 7413.7  | 7973.5  | 8534.1  |
| 42.5°  | 5098.5  | 5272.9  | 5447.4  | 5795.5  | 6143.7  | 6491.9  | 6840.1  | 7460.6  | 8081.1  | 8700.9  | 9321.4  |
| 45°    | 5728.0  | 5905.9  | 6083.0  | 6360.2  | 6637.4  | 6914.5  | 7191.7  | 7851.5  | 8510.6  | 9170.4  | 9829.5  |
| 47.5°  | 6644.3  | 6645.0  | 6645.6  | 6845.6  | 7045.5  | 7246.2  | 7446.1  | 8110.7  | 8774.7  | 9439.3  | 10103.2 |
| 50°    | 7331.6  | 7309.6  | 7288.2  | 7391.6  | 7494.4  | 7597.8  | 7701.2  | 8312.7  | 8925.0  | 9536.5  | 10148.1 |
| 52.5°  | 8315.5  | 8123.1  | 7931.5  | 7992.8  | 8053.5  | 8114.9  | 8175.5  | 8693.3  | 9211.8  | 9729.6  | 10247.3 |
| 55°    | 9129.1  | 8934.6  | 8740.2  | 8717.4  | 8694.7  | 8671.9  | 8649.2  | 9125.6  | 9602.0  | 10078.4 | 10554.8 |
| 57.5°  | 9802.0  | 9539.3  | 9277.3  | 9224.9  | 9173.2  | 9120.8  | 9068.4  | 9571.0  | 10072.9 | 10575.5 | 11077.4 |
| 60°    | 10158.4 | 9988.8  | 9819.2  | 9785.4  | 9750.9  | 9717.2  | 9682.7  | 10095.0 | 10507.3 | 10919.6 | 11331.9 |
| 62.5°  | 10277.7 | 10169.4 | 10061.9 | 10125.3 | 10188.7 | 10252.9 | 10316.3 | 10497.6 | 10678.3 | 10859.6 | 11040.2 |
| 65°    | 10081.9 | 10068.1 | 10054.3 | 10184.6 | 10314.2 | 10444.5 | 10574.8 | 10530.0 | 10484.5 | 10439.7 | 10394.9 |
| 67.5°  | 9306.9  | 9261.4  | 9216.6  | 9502.7  | 9788.2  | 10074.3 | 10360.4 | 10143.2 | 9925.4  | 9708.2  | 9491.0  |
| 70°    | 7628.8  | 7596.4  | 7564.7  | 7977.0  | 8389.3  | 8802.2  | 9214.5  | 8951.2  | 8687.8  | 8424.4  | 8161.1  |
| 72.5°  | 5377.0  | 5432.2  | 5487.4  | 5973.4  | 6458.8  | 6944.9  | 7430.2  | 7164.8  | 6899.4  | 6633.9  | 6368.5  |
| 75°    | 3597.6  | 3700.3  | 3803.0  | 4303.6  | 4804.1  | 5305.3  | 5805.9  | 5494.3  | 5182.6  | 4871.0  | 4559.4  |
| 77.5°  | 2713.7  | 2749.5  | 2785.4  | 3101.9  | 3418.3  | 3735.5  | 4051.9  | 3794.8  | 3536.9  | 3279.7  | 3021.9  |
| 80°    | 2127.0  | 2019.4  | 1912.5  | 2016.7  | 2120.8  | 2224.9  | 2329.0  | 2175.2  | 2021.5  | 1868.4  | 1714.7  |
| 82.5°  | 1270.7  | 1226.5  | 1182.4  | 1238.9  | 1294.8  | 1351.3  | 1407.9  | 1341.7  | 1274.8  | 1208.6  | 1141.7  |
| 85°    | 572.2   | 616.4   | 659.8   | 717.0   | 773.6   | 830.8   | 888.0   | 795.6   | 703.2   | 610.9   | 518.5   |
| 87.5°  | 64.1    | 82.7    | 101.3   | 125.5   | 149.6   | 173.7   | 197.9   | 154.4   | 110.3   | 66.9    | 23.4    |
| 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 330° | 332.5° | 335° | 337.5° | 340° | 342.5° | 345° | 347.5° | 350° | 352.5° | 355° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |





REPORT NUMBER: P367953  
 CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 357.5°  | 360°    |
|--------|---------|---------|
| 0°     | 1457.5  | 1457.5  |
| 2.5°   | 1897.4  | 1932.5  |
| 5°     | 2488.2  | 2486.9  |
| 7.5°   | 2722.0  | 2679.9  |
| 10°    | 2566.8  | 2528.2  |
| 12.5°  | 2696.5  | 2597.9  |
| 15°    | 2720.6  | 2646.1  |
| 17.5°  | 3051.5  | 2929.5  |
| 20°    | 3450.7  | 3293.5  |
| 22.5°  | 3932.6  | 3716.8  |
| 25°    | 4399.4  | 4142.9  |
| 27.5°  | 5066.8  | 4912.4  |
| 30°    | 5572.2  | 5415.7  |
| 32.5°  | 6123.7  | 6017.5  |
| 35°    | 6800.1  | 6693.9  |
| 37.5°  | 7861.8  | 7888.7  |
| 40°    | 8550.6  | 8567.1  |
| 42.5°  | 9385.5  | 9449.6  |
| 45°    | 9901.2  | 9972.9  |
| 47.5°  | 10203.2 | 10303.2 |
| 50°    | 10309.4 | 10470.7 |
| 52.5°  | 10446.6 | 10645.2 |
| 55°    | 10776.2 | 10997.5 |
| 57.5°  | 11253.9 | 11430.4 |
| 60°    | 11340.1 | 11348.4 |
| 62.5°  | 10912.7 | 10785.1 |
| 65°    | 10259.1 | 10123.2 |
| 67.5°  | 9409.0  | 9326.2  |
| 70°    | 8052.1  | 7943.2  |
| 72.5°  | 6165.8  | 5963.1  |
| 75°    | 4308.4  | 4057.4  |
| 77.5°  | 2890.2  | 2758.5  |
| 80°    | 1718.8  | 1722.3  |
| 82.5°  | 1173.4  | 1204.5  |
| 85°    | 512.3   | 505.4   |
| 87.5°  | 16.5    | 9.0     |
| 90°    | 0.0     | 0.0     |
| 92.5°  | 0.0     | 0.0     |
| 95°    | 0.0     | 0.0     |
| 97.5°  | 0.0     | 0.0     |
| 100°   | 0.0     | 0.0     |
| 102.5° | 0.0     | 0.0     |
| 105°   | 0.0     | 0.0     |
| 107.5° | 0.0     | 0.0     |
| 110°   | 0.0     | 0.0     |

REPORT NUMBER: P367953  
CATALOG NUMBER: PMM-SA3C-730-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

(END OF REPORT)