

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P561225

Luminaire Tested: **SDL-PA1-90-727-U-T3-HSS-A**

Issue Date: 7/26/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P561225  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/26/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: SDL-PA1-90-727-U-T3-HSS-A  
Description: Springdale  
(1) 70 CRI, 2700K, 1180mA LIGHT ENGINE WITH 24 LEDS AND TYPE III OPTICS,  
HOUSE SIDE SHIELD AND CLEAR PANELS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5964.3 lumens  
Efficiency: N/A  
Efficacy: 64.5 lumens/watt  
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')  
IES Classification: Type IV - Medium  
BUG Rating: B1 - U3 - G2


Input Watts (W): 92.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P561225  
 CATALOG NUMBER: SDL-PA1-90-727-U-T3-HSS-A

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 8.5 fc  
 Type IV - Medium - N/A

REPORT NUMBER: P561225  
CATALOG NUMBER: SDL-PA1-90-727-U-T3-HSS-A

### Luminous Intensity Polar Plot



— Vertical Plane Through 70-Deg Lateral    - - - Horizontal Cone Through 72.5-Deg Vertical



REPORT NUMBER: P561225  
 CATALOG NUMBER: SDL-PA1-90-727-U-T3-HSS-A


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	683.7	96.2	779.8
	% Fixture	11.5	1.6	13.1
<b>Street Side</b>	Lumens	5106.6	77.8	5184.4
	% Fixture	85.6	1.3	86.9
<b>Total</b>	Lumens	5790.3	174.0	5964.3
	% Fixture	97.1	2.9	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.5	0.9
10°-20°	111.7	1.9
20°-30°	180.9	3.0
30°-40°	386.6	6.5
40°-50°	760.0	12.7
50°-60°	1269.1	21.3
60°-70°	1575.1	26.4
70°-80°	1213.1	20.3
80°-90°	237.2	4.0
90°-100°	128.7	2.2
100°-110°	26.6	0.4
110°-120°	7.6	0.1
120°-130°	5.8	0.1
130°-140°	2.7	0.0
140°-150°	1.3	0.0
150°-160°	1.2	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-90°	5790.3	97.1
0°-180°	5964.3	100.0

**Coefficient of Utilization**




REPORT NUMBER: P561225  
 CATALOG NUMBER: SDL-PA1-90-727-U-T3-HSS-A

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	221.2	3.7			
FM (30°-60°)	2150.6	36.1			
FH (60°-80°)	2576.9	43.2			G2/5000
FVH (80°-90°)	157.8	2.6			G2/225
BL (0°-30°)	127.9	2.1	B1/500		
BM (30°-60°)	265.1	4.4	B1/1000		
BH (60°-80°)	211.3	3.5	B1/500		G1/500
BVH (80°-90°)	79.4	1.3			G1/100
UL (90°-100°)	128.7	2.2		U3/500	
UH (100°-180°)	45.3	0.8		U2/50	

**BUG Rating: B1-U3-G2**  
 Type IV Medium





REPORT NUMBER: P561225

CATALOG NUMBER: SDL-PA1-90-727-U-T3-HSS-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	85°
0°	732.6	732.6	732.6	732.6	732.6	732.6	732.6	732.6	732.6	732.6	732.6
2.5°	617.7	686.0	689.1	695.4	701.6	710.9	726.4	726.4	726.4	726.4	729.5
5°	586.7	586.7	586.7	592.9	592.9	599.1	602.2	695.4	704.7	714.0	714.0
7.5°	487.4	533.9	537.0	555.7	577.4	586.7	592.9	586.7	577.4	614.6	630.2
10°	533.9	533.9	533.9	540.1	509.1	493.6	456.3	459.4	462.5	490.5	558.8
12.5°	443.9	471.8	499.8	530.8	490.5	440.8	431.5	456.3	462.5	412.9	490.5
15°	518.4	515.3	515.3	487.4	406.7	440.8	384.9	406.7	459.4	502.9	583.6
17.5°	428.4	416.0	484.3	478.1	434.6	347.7	443.9	440.8	487.4	450.1	502.9
20°	509.1	506.0	506.0	391.1	431.5	468.7	462.5	431.5	484.3	540.1	636.4
22.5°	428.4	422.2	434.6	468.7	428.4	484.3	422.2	533.9	509.1	493.6	462.5
25°	540.1	537.0	537.0	428.4	484.3	443.9	533.9	487.4	589.8	642.6	701.6
27.5°	484.3	484.3	462.5	496.7	462.5	558.8	512.2	614.6	667.4	701.6	847.5
30°	670.5	673.6	636.4	493.6	515.3	524.6	605.3	760.5	875.4	959.2	1049.2
32.5°	965.4	946.8	791.6	673.6	546.4	648.8	670.5	884.7	940.6	1030.6	1108.2
35°	1313.1	1303.8	1167.2	872.3	658.1	695.4	748.1	962.3	1049.2	1139.3	1185.8
37.5°	1552.1	1542.8	1455.9	1111.3	794.7	810.2	816.4	1071.0	1182.7	1272.7	1294.5
40°	1747.7	1732.2	1679.4	1297.6	977.8	946.8	915.8	1220.0	1347.3	1421.8	1431.1
42.5°	2042.6	2017.8	1884.3	1511.8	1164.1	1130.0	1024.4	1350.4	1502.5	1601.8	1608.0
45°	2396.5	2374.8	2188.5	1809.8	1362.8	1353.5	1216.9	1518.0	1698.0	1816.0	1781.8
47.5°	2638.6	2579.6	2474.1	2095.4	1670.1	1589.4	1431.1	1688.7	1909.1	2086.1	1989.8
50°	2859.0	2815.6	2725.5	2412.0	2002.3	1893.6	1654.6	1884.3	2132.6	2294.1	2163.7
52.5°	3063.9	2998.7	2924.2	2647.9	2287.8	2235.1	1875.0	2079.9	2390.3	2523.8	2343.7
55°	3166.4	3063.9	3051.5	2862.1	2508.2	2464.8	2123.3	2322.0	2660.4	2753.5	2514.5
57.5°	2998.7	2995.6	3091.8	2992.5	2688.3	2666.6	2374.8	2582.7	2887.0	2930.4	2682.1
60°	2887.0	2890.1	3036.0	3042.2	2846.6	2859.0	2601.4	2883.9	3054.6	3082.5	2840.4
62.5°	2691.4	2713.1	2933.5	3076.3	2887.0	3042.2	2793.8	3091.8	3234.6	3244.0	3036.0
65°	2446.2	2467.9	2691.4	2983.2	2843.5	3163.2	2955.3	3324.7	3399.2	3405.4	3250.2
67.5°	2160.6	2169.9	2418.2	2741.1	2738.0	3206.7	3054.6	3479.9	3557.5	3576.1	3433.3
70°	1843.9	1831.5	2058.1	2430.6	2511.4	3185.0	3175.7	3632.0	3750.0	3746.8	3560.6
72.5°	1381.4	1440.4	1598.7	1983.6	2176.1	3079.4	3278.1	3737.5	3883.4	3833.8	3433.3
75°	471.8	502.9	931.3	1263.4	1676.3	2796.9	3299.8	3743.7	3874.1	3653.7	2809.4
77.5°	155.2	145.9	208.0	502.9	931.3	1937.1	2902.5	3265.7	3231.5	2840.4	1726.0
80°	74.5	77.6	93.1	176.9	341.5	878.5	1822.2	2067.4	2020.9	1490.0	748.1
82.5°	49.7	52.8	62.1	102.4	192.5	301.1	968.5	943.7	714.0	468.7	307.3
85°	21.7	21.7	31.0	52.8	118.0	198.7	369.4	322.8	291.8	270.1	251.4
87.5°	6.2	6.2	12.4	18.6	40.4	124.2	208.0	195.6	201.8	211.1	239.0
90°	6.2	6.2	6.2	6.2	31.0	130.4	211.1	198.7	198.7	211.1	251.4
92.5°	9.3	9.3	6.2	6.2	27.9	130.4	220.4	189.4	201.8	214.2	270.1
95°	9.3	12.4	6.2	3.1	21.7	133.5	226.6	201.8	220.4	217.3	288.7
97.5°	12.4	12.4	6.2	3.1	12.4	114.9	229.7	164.5	167.6	155.2	226.6
100°	15.5	15.5	6.2	6.2	9.3	59.0	170.7	105.5	65.2	49.7	74.5
102.5°	18.6	18.6	6.2	6.2	6.2	21.7	77.6	62.1	34.1	9.3	18.6
105°	18.6	21.7	6.2	6.2	3.1	9.3	34.1	24.8	12.4	9.3	18.6
107.5°	21.7	21.7	6.2	6.2	3.1	6.2	9.3	9.3	6.2	9.3	18.6



REPORT NUMBER: P561225  
 CATALOG NUMBER: SDL-PA1-90-727-U-T3-HSS-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	45°	55°	65°	70°	75°	85°
112.5°	15.5	15.5	6.2	9.3	3.1	3.1	3.1	6.2	6.2	9.3	18.6
115°	9.3	6.2	3.1	6.2	3.1	3.1	3.1	6.2	6.2	6.2	15.5
117.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	6.2	6.2	9.3	18.6
120°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	6.2	6.2	12.4	21.7
122.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	6.2	12.4	24.8
125°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	6.2	9.3	21.7
127.5°	3.1	3.1	3.1	0.0	3.1	3.1	3.1	3.1	6.2	9.3	18.6
130°	3.1	3.1	3.1	0.0	3.1	3.1	3.1	3.1	3.1	6.2	12.4
132.5°	3.1	3.1	3.1	0.0	3.1	3.1	3.1	3.1	3.1	6.2	12.4
135°	3.1	3.1	3.1	0.0	3.1	3.1	3.1	3.1	3.1	3.1	6.2
137.5°	3.1	3.1	0.0	0.0	3.1	3.1	3.1	3.1	3.1	3.1	3.1
140°	0.0	0.0	0.0	0.0	3.1	3.1	3.1	3.1	3.1	3.1	3.1
142.5°	0.0	0.0	0.0	0.0	3.1	3.1	3.1	3.1	3.1	3.1	3.1
145°	0.0	0.0	0.0	0.0	3.1	3.1	3.1	3.1	3.1	3.1	3.1
147.5°	0.0	0.0	0.0	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
150°	6.2	6.2	6.2	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
152.5°	6.2	6.2	6.2	3.1	3.1	3.1	3.1	6.2	6.2	3.1	3.1
155°	3.1	3.1	3.1	0.0	0.0	3.1	3.1	3.1	3.1	6.2	6.2
157.5°	0.0	3.1	3.1	0.0	0.0	3.1	3.1	3.1	3.1	3.1	3.1
160°	0.0	0.0	0.0	0.0	0.0	3.1	3.1	3.1	3.1	3.1	3.1
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P561225

CATALOG NUMBER: SDL-PA1-90-727-U-T3-HSS-A

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	732.6	732.6	732.6	732.6	732.6	732.6	732.6	732.6	732.6	732.6	732.6
2.5°	729.5	729.5	726.4	732.6	729.5	729.5	689.1	648.8	639.5	642.6	648.8
5°	717.1	717.1	717.1	667.4	611.5	592.9	599.1	599.1	599.1	596.0	602.2
7.5°	633.3	630.2	620.9	565.0	589.8	586.7	583.6	577.4	502.9	484.3	484.3
10°	561.9	561.9	481.2	459.4	459.4	478.1	490.5	471.8	462.5	447.0	443.9
12.5°	493.6	493.6	412.9	459.4	388.0	384.9	375.6	344.6	291.8	254.5	257.7
15°	586.7	586.7	487.4	391.1	325.9	307.3	192.5	180.0	173.8	170.7	167.6
17.5°	499.8	502.9	450.1	388.0	304.2	161.4	136.6	136.6	136.6	130.4	118.0
20°	633.3	633.3	524.6	347.7	229.7	127.3	105.5	93.1	127.3	127.3	127.3
22.5°	459.4	453.2	462.5	353.9	142.8	102.4	86.9	108.6	114.9	96.2	96.2
25°	695.4	686.0	561.9	254.5	118.0	80.7	96.2	83.8	108.6	108.6	108.6
27.5°	856.8	794.7	571.2	232.8	86.9	93.1	77.6	93.1	83.8	80.7	80.7
30°	1030.6	1002.7	689.1	183.2	83.8	77.6	80.7	74.5	86.9	80.7	80.7
32.5°	1086.5	1058.6	624.0	142.8	80.7	74.5	68.3	71.4	68.3	71.4	71.4
35°	1157.9	1130.0	552.6	108.6	74.5	65.2	62.1	62.1	59.0	55.9	55.9
37.5°	1260.3	1213.8	471.8	93.1	68.3	59.0	49.7	46.6	49.7	62.1	65.2
40°	1378.3	1300.7	372.5	83.8	59.0	49.7	37.3	43.5	52.8	52.8	52.8
42.5°	1549.0	1406.2	276.3	77.6	52.8	40.4	27.9	34.1	40.4	55.9	55.9
45°	1698.0	1468.3	195.6	71.4	43.5	31.0	21.7	34.1	43.5	49.7	49.7
47.5°	1871.9	1527.3	145.9	68.3	40.4	21.7	24.8	34.1	34.1	52.8	52.8
50°	2017.8	1539.7	118.0	62.1	31.0	15.5	31.0	31.0	37.3	46.6	46.6
52.5°	2154.4	1552.1	105.5	55.9	24.8	12.4	31.0	31.0	43.5	55.9	55.9
55°	2244.4	1514.9	96.2	49.7	21.7	9.3	34.1	34.1	34.1	43.5	43.5
57.5°	2315.8	1468.3	90.0	43.5	18.6	18.6	37.3	43.5	37.3	43.5	43.5
60°	2362.3	1384.5	77.6	40.4	15.5	18.6	46.6	55.9	43.5	65.2	65.2
62.5°	2446.2	1319.3	68.3	37.3	12.4	18.6	46.6	71.4	55.9	86.9	90.0
65°	2514.5	1260.3	59.0	27.9	12.4	24.8	52.8	90.0	68.3	108.6	111.8
67.5°	2542.4	1188.9	49.7	24.8	12.4	27.9	68.3	111.8	86.9	127.3	127.3
70°	2520.7	1114.4	40.4	24.8	12.4	43.5	90.0	130.4	105.5	155.2	158.3
72.5°	2331.3	949.9	31.0	24.8	9.3	46.6	111.8	155.2	127.3	211.1	217.3
75°	1785.0	602.2	31.0	24.8	12.4	52.8	130.4	180.0	152.1	235.9	245.2
77.5°	1089.6	279.4	31.0	27.9	15.5	65.2	142.8	208.0	167.6	254.5	260.8
80°	484.3	173.8	31.0	31.0	31.0	80.7	167.6	229.7	189.4	270.1	279.4
82.5°	242.1	130.4	27.9	31.0	46.6	96.2	198.7	245.2	195.6	279.4	282.5
85°	208.0	118.0	27.9	34.1	49.7	111.8	214.2	248.3	204.9	276.3	279.4
87.5°	198.7	111.8	34.1	34.1	55.9	118.0	220.4	260.8	211.1	267.0	263.9
90°	208.0	108.6	37.3	40.4	71.4	121.1	223.5	254.5	211.1	251.4	251.4
92.5°	214.2	105.5	40.4	46.6	86.9	136.6	220.4	248.3	211.1	232.8	232.8
95°	220.4	105.5	46.6	52.8	86.9	149.0	211.1	226.6	195.6	208.0	204.9
97.5°	167.6	77.6	55.9	59.0	80.7	114.9	170.7	176.9	127.3	124.2	121.1
100°	59.0	34.1	55.9	65.2	49.7	49.7	102.4	124.2	74.5	46.6	52.8
102.5°	18.6	15.5	49.7	65.2	40.4	18.6	52.8	77.6	55.9	6.2	6.2
105°	18.6	18.6	27.9	52.8	27.9	6.2	18.6	43.5	34.1	6.2	6.2
107.5°	18.6	15.5	12.4	31.0	9.3	6.2	9.3	9.3	9.3	3.1	6.2



REPORT NUMBER: P561225  
 CATALOG NUMBER: SDL-PA1-90-727-U-T3-HSS-A

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	21.7	15.5	6.2	9.3	6.2	6.2	6.2	3.1	6.2	15.5	18.6
115°	18.6	15.5	6.2	6.2	6.2	6.2	3.1	3.1	6.2	18.6	18.6
117.5°	21.7	18.6	6.2	6.2	3.1	6.2	3.1	3.1	6.2	18.6	21.7
120°	24.8	21.7	6.2	6.2	3.1	3.1	3.1	3.1	6.2	15.5	18.6
122.5°	24.8	24.8	6.2	3.1	3.1	3.1	3.1	3.1	9.3	15.5	15.5
125°	21.7	21.7	6.2	3.1	3.1	3.1	3.1	3.1	9.3	15.5	15.5
127.5°	18.6	18.6	6.2	3.1	3.1	3.1	3.1	3.1	6.2	12.4	15.5
130°	15.5	15.5	6.2	3.1	3.1	3.1	0.0	3.1	6.2	12.4	12.4
132.5°	12.4	9.3	6.2	3.1	3.1	3.1	0.0	3.1	6.2	9.3	12.4
135°	9.3	9.3	3.1	3.1	3.1	3.1	0.0	0.0	6.2	6.2	9.3
137.5°	6.2	3.1	3.1	3.1	3.1	0.0	0.0	0.0	3.1	6.2	6.2
140°	3.1	3.1	3.1	3.1	3.1	0.0	0.0	0.0	0.0	3.1	3.1
142.5°	3.1	3.1	3.1	3.1	3.1	0.0	0.0	0.0	0.0	3.1	3.1
145°	3.1	3.1	3.1	3.1	3.1	0.0	0.0	0.0	0.0	3.1	3.1
147.5°	3.1	3.1	3.1	3.1	3.1	0.0	0.0	0.0	0.0	3.1	3.1
150°	3.1	3.1	3.1	3.1	3.1	0.0	0.0	0.0	0.0	3.1	3.1
152.5°	3.1	3.1	3.1	3.1	3.1	0.0	0.0	0.0	3.1	3.1	3.1
155°	6.2	6.2	6.2	3.1	3.1	0.0	0.0	0.0	0.0	3.1	3.1
157.5°	3.1	3.1	3.1	3.1	3.1	0.0	0.0	0.0	0.0	0.0	0.0
160°	3.1	3.1	3.1	3.1	3.1	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245982

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



--- HS — SS

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



u





110° | 21.7 21.7 9.3 6.2 3.1 6.2 3.1 6.2 6.2 9.3 21.7

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





110°	21.7	15.5	6.2	9.3	6.2	6.2	6.2	6.2	6.2	12.4	12.4
------	------	------	-----	-----	-----	-----	-----	-----	-----	------	------

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)