

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P559830

Luminaire Tested: **SDL-PA1-100-730-U-T2R-A**

Issue Date: 7/26/2021

Test Information

Test Method: LM-79-08
Report Number: P559830
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-19)
Test Lab: INNOVATION CENTER
Issue Date: 7/26/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: SDL-PA1-100-730-U-T2R-A
Description: Springdale
(1) 70 CRI, 3000K, 1200mA LIGHT ENGINE WITH 24 LEDS AND TYPE II R OPTICS
AND CLEAR PANELS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7703.8 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')
IES Classification: Type II - Medium
BUG Rating: B1 - U3 - G2


Input Watts (W): 93.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P559830
 CATALOG NUMBER: SDL-PA1-100-730-U-T2R-A

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 16 fc
 Type II - Medium - N/A

REPORT NUMBER: P559830
CATALOG NUMBER: SDL-PA1-100-730-U-T2R-A

Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical



REPORT NUMBER: P559830
 CATALOG NUMBER: SDL-PA1-100-730-U-T2R-A


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1317.0	78.7	1395.7
	% Fixture	17.1	1.0	18.1
Street Side	Lumens	6208.5	99.6	6308.1
	% Fixture	80.6	1.3	81.9
Total	Lumens	7525.5	178.3	7703.8
	% Fixture	97.7	2.3	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.0	1.1
10°-20°	224.7	2.9
20°-30°	405.7	5.3
30°-40°	829.0	10.8
40°-50°	1301.8	16.9
50°-60°	1598.5	20.7
60°-70°	1589.8	20.6
70°-80°	1175.9	15.3
80°-90°	314.2	4.1
90°-100°	116.1	1.5
100°-110°	27.2	0.4
110°-120°	12.8	0.2
120°-130°	11.5	0.1
130°-140°	5.5	0.1
140°-150°	2.7	0.0
150°-160°	2.4	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-90°	7525.5	97.7
0°-180°	7703.8	100.0

Coefficient of Utilization



REPORT NUMBER: P559830


CATALOG NUMBER: SDL-PA1-100-730-U-T2R-A

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	499.3	6.5			
FM (30°-60°)	3193.4	41.5			
FH (60°-80°)	2315.2	30.1			G2/5000
FVH (80°-90°)	200.6	2.6			G2/225
BL (0°-30°)	217.1	2.8	B1/500		
BM (30°-60°)	535.9	7.0	B1/1000		
BH (60°-80°)	450.5	5.8	B1/500		G1/500
BVH (80°-90°)	113.6	1.5			G2/225
UL (90°-100°)	116.1	1.5		U3/500	
UH (100°-180°)	62.2	0.8		U3/500	

BUG Rating: B1-U3-G2

Type II Medium





REPORT NUMBER: P559830

CATALOG NUMBER: SDL-PA1-100-730-U-T2R-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	77.5°	85°
0°	1032.6	1032.6	1032.6	1032.6	1032.6	1032.6	1032.6	1032.6	1032.6	1032.6	1032.6
2.5°	1071.8	1132.0	1159.1	1189.2	1216.3	1201.2	1177.1	1141.0	1107.9	1095.8	1059.7
5°	1183.1	1177.1	1174.1	1165.1	1150.0	1122.9	1089.8	1219.3	1168.1	1147.0	1086.8
7.5°	1041.6	1207.2	1225.3	1243.4	1237.3	1204.2	1162.1	1044.7	1089.8	1062.7	987.5
10°	1273.5	1273.5	1267.4	1273.5	1204.2	1150.0	984.4	915.2	882.1	954.3	885.1
12.5°	1083.8	1180.1	1300.6	1324.6	1219.3	1068.7	999.5	966.4	761.7	752.6	806.8
15°	1261.4	1276.5	1279.5	1285.5	1038.6	1119.9	924.2	858.0	972.4	945.3	954.3
17.5°	1014.6	1029.6	1225.3	1213.3	1116.9	894.1	1080.8	969.4	894.1	861.0	849.0
20°	1276.5	1279.5	1270.5	1026.6	1077.8	1168.1	1011.5	981.4	1089.8	1086.8	1041.6
22.5°	1086.8	1089.8	1122.9	1237.3	1113.9	1180.1	1017.6	1225.3	1032.6	1035.6	803.8
25°	1454.1	1457.1	1427.0	1101.9	1252.4	1107.9	1234.3	1101.9	1318.6	1276.5	1177.1
27.5°	1526.3	1415.0	1300.6	1366.8	1195.2	1375.8	1174.1	1333.7	1433.0	1424.0	1439.0
30°	1935.8	1941.8	1863.5	1496.2	1399.9	1357.8	1354.7	1583.5	1962.9	1977.9	1728.1
32.5°	2622.2	2586.1	2200.7	1845.5	1508.3	1655.8	1520.3	1833.4	2122.4	2113.4	1851.5
35°	2935.3	2899.2	2754.7	2279.0	1743.1	1788.3	1716.0	1950.8	2342.2	2273.0	1974.9
37.5°	3200.2	3194.2	3073.8	2510.8	1980.9	2047.2	1833.4	2095.3	2531.9	2459.6	2101.4
40°	3429.0	3407.9	3302.6	2718.5	2224.8	2227.8	1980.9	2270.0	2700.5	2718.5	2224.8
42.5°	3618.7	3600.6	3513.3	2926.3	2369.3	2387.4	2137.5	2447.6	2926.3	2959.4	2417.5
45°	3697.0	3706.0	3645.8	3112.9	2498.8	2531.9	2324.1	2628.2	3167.1	3194.2	2589.1
47.5°	3754.2	3757.2	3742.1	3266.4	2637.2	2652.3	2507.8	2790.8	3516.3	3462.1	2790.8
50°	3624.7	3612.7	3627.7	3383.9	2757.7	2775.7	2661.3	2959.4	3766.2	3697.0	3001.5
52.5°	3284.5	3299.6	3456.1	3323.6	2796.8	2832.9	2805.8	3106.9	4112.4	4058.2	3302.6
55°	2429.5	2495.7	2947.3	3076.8	2793.8	2857.0	2938.3	3386.9	4476.7	4395.4	3558.5
57.5°	1965.9	1965.9	2230.8	2655.3	2640.3	2842.0	3073.8	3576.5	4765.7	4708.5	3814.4
60°	1577.5	1577.5	1722.0	2107.4	2342.2	2766.7	3212.3	3856.5	5039.7	5006.5	4040.2
62.5°	1237.3	1234.3	1354.7	1571.5	1920.7	2601.1	3284.5	4097.4	5382.9	5376.8	4401.4
65°	894.1	906.2	1008.5	1144.0	1508.3	2291.0	3281.5	4314.1	5795.3	5813.4	4807.8
67.5°	662.3	668.3	725.5	824.9	1035.6	1899.7	3137.0	4464.6	6261.9	6231.8	5066.8
70°	508.8	517.8	541.9	593.1	689.4	1411.9	2787.8	4359.3	6538.9	6481.7	5163.1
72.5°	427.5	430.5	427.5	454.6	460.6	957.4	2233.8	3958.9	6424.5	6334.2	4898.2
75°	364.3	361.3	358.3	364.3	340.2	632.2	1601.6	3350.7	5930.8	5774.2	4326.2
77.5°	313.1	310.1	298.0	301.1	270.9	466.6	1092.8	2628.2	4997.5	4630.2	3251.4
80°	258.9	258.9	249.9	249.9	228.8	355.2	698.4	1812.4	2911.2	2619.2	1691.9
82.5°	201.7	198.7	198.7	204.7	195.7	277.0	457.6	903.2	1201.2	1125.9	791.8
85°	108.4	108.4	123.4	138.5	135.5	168.6	349.2	532.9	710.5	686.4	442.6
87.5°	33.1	33.1	36.1	45.2	48.2	90.3	219.8	258.9	322.1	355.2	349.2
90°	36.1	33.1	24.1	27.1	30.1	66.2	204.7	249.9	325.1	361.3	370.3
92.5°	42.1	39.1	24.1	24.1	30.1	54.2	195.7	243.9	355.2	391.4	400.4
95°	45.2	42.1	24.1	24.1	30.1	48.2	174.6	240.8	379.3	427.5	427.5
97.5°	42.1	39.1	18.1	21.1	27.1	42.1	135.5	198.7	264.9	292.0	337.2
100°	36.1	36.1	12.0	18.1	24.1	30.1	78.3	108.4	78.3	75.3	75.3
102.5°	33.1	33.1	12.0	15.1	18.1	21.1	36.1	57.2	18.1	21.1	27.1
105°	33.1	36.1	9.0	12.0	12.0	12.0	18.1	30.1	15.1	18.1	27.1
107.5°	33.1	36.1	9.0	9.0	12.0	9.0	9.0	12.0	15.1	18.1	30.1



REPORT NUMBER: P559830
 CATALOG NUMBER: SDL-PA1-100-730-U-T2R-A

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	77.5°	85°
112.5°	21.1	21.1	6.0	9.0	9.0	9.0	6.0	9.0	15.1	21.1	30.1
115°	15.1	12.0	6.0	9.0	6.0	9.0	6.0	9.0	15.1	21.1	27.1
117.5°	12.0	9.0	6.0	6.0	6.0	6.0	3.0	9.0	18.1	24.1	33.1
120°	12.0	12.0	6.0	6.0	6.0	6.0	3.0	9.0	27.1	30.1	42.1
122.5°	12.0	12.0	6.0	6.0	6.0	6.0	3.0	6.0	24.1	33.1	45.2
125°	12.0	12.0	6.0	6.0	6.0	6.0	3.0	6.0	21.1	30.1	39.1
127.5°	12.0	12.0	6.0	3.0	6.0	6.0	6.0	6.0	18.1	24.1	33.1
130°	12.0	12.0	6.0	3.0	6.0	6.0	6.0	6.0	15.1	18.1	27.1
132.5°	9.0	9.0	6.0	3.0	6.0	3.0	3.0	6.0	12.0	15.1	21.1
135°	6.0	6.0	6.0	3.0	6.0	3.0	3.0	3.0	6.0	9.0	15.1
137.5°	3.0	6.0	3.0	3.0	6.0	3.0	3.0	3.0	3.0	3.0	6.0
140°	3.0	3.0	3.0	3.0	6.0	3.0	3.0	3.0	3.0	3.0	3.0
142.5°	3.0	3.0	3.0	3.0	6.0	6.0	3.0	3.0	3.0	3.0	3.0
145°	3.0	3.0	3.0	3.0	9.0	6.0	3.0	3.0	3.0	3.0	3.0
147.5°	3.0	3.0	3.0	12.0	9.0	6.0	3.0	3.0	3.0	3.0	3.0
150°	15.1	15.1	15.1	12.0	9.0	6.0	9.0	3.0	3.0	3.0	3.0
152.5°	15.1	15.1	18.1	9.0	6.0	3.0	3.0	12.0	9.0	6.0	6.0
155°	12.0	9.0	9.0	3.0	3.0	3.0	3.0	3.0	9.0	12.0	12.0
157.5°	3.0	3.0	6.0	3.0	3.0	3.0	3.0	3.0	6.0	3.0	3.0
160°	0.0	0.0	0.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P559830
 CATALOG NUMBER: SDL-PA1-100-730-U-T2R-A

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1032.6	1032.6	1032.6	1032.6	1032.6	1032.6	1032.6	1032.6	1032.6	1032.6	1032.6
2.5°	1038.6	1014.6	957.4	915.2	864.0	818.9	779.7	692.4	677.4	668.3	665.3
5°	1038.6	987.5	876.1	740.6	635.2	611.1	599.1	599.1	593.1	596.1	599.1
7.5°	921.2	852.0	683.4	578.0	596.1	596.1	599.1	584.0	535.9	541.9	532.9
10°	806.8	719.5	514.8	469.6	514.8	517.8	587.1	614.2	623.2	626.2	626.2
12.5°	743.6	620.2	445.6	460.6	415.5	475.7	560.0	626.2	569.0	538.9	538.9
15°	855.0	734.6	499.8	403.4	409.4	475.7	424.5	593.1	614.2	620.2	620.2
17.5°	767.7	647.3	457.6	415.5	457.6	391.4	478.7	544.9	520.8	493.7	490.7
20°	921.2	764.7	511.8	406.4	403.4	463.6	424.5	445.6	557.0	560.0	557.0
22.5°	716.5	611.1	454.6	460.6	403.4	442.6	418.5	460.6	439.5	436.5	439.5
25°	993.5	791.8	523.8	397.4	421.5	391.4	421.5	388.4	466.6	472.7	475.7
27.5°	1216.3	945.3	557.0	430.5	367.3	400.4	376.3	388.4	361.3	376.3	382.3
30°	1448.1	1101.9	680.4	475.7	388.4	343.2	349.2	346.2	391.4	388.4	382.3
32.5°	1523.3	1122.9	650.3	496.7	385.4	346.2	319.1	340.2	373.3	400.4	403.4
35°	1598.6	1138.0	626.2	475.7	376.3	325.1	313.1	349.2	376.3	379.3	388.4
37.5°	1685.9	1150.0	602.1	445.6	349.2	319.1	310.1	325.1	385.4	379.3	370.3
40°	1767.2	1156.1	572.0	418.5	319.1	313.1	289.0	325.1	340.2	352.2	358.3
42.5°	1911.7	1192.2	547.9	394.4	298.0	298.0	277.0	304.1	349.2	355.2	352.2
45°	2017.1	1180.1	514.8	373.3	277.0	264.9	270.9	331.2	352.2	388.4	382.3
47.5°	2167.6	1210.2	475.7	340.2	258.9	243.9	255.9	322.1	361.3	388.4	394.4
50°	2315.1	1204.2	442.6	313.1	246.9	231.8	283.0	313.1	355.2	400.4	400.4
52.5°	2507.8	1213.3	427.5	289.0	231.8	231.8	292.0	316.1	364.3	394.4	394.4
55°	2679.4	1180.1	391.4	280.0	228.8	222.8	295.0	328.1	367.3	394.4	397.4
57.5°	2805.8	1113.9	364.3	270.9	225.8	228.8	295.0	355.2	343.2	394.4	403.4
60°	2944.3	1041.6	340.2	270.9	225.8	237.8	304.1	376.3	376.3	412.4	412.4
62.5°	3134.0	996.5	328.1	274.0	219.8	246.9	331.2	409.4	379.3	436.5	439.5
65°	3293.5	936.3	319.1	286.0	222.8	258.9	346.2	436.5	397.4	463.6	460.6
67.5°	3296.6	846.0	307.1	298.0	225.8	267.9	346.2	454.6	418.5	487.7	478.7
70°	3152.0	755.6	289.0	298.0	234.8	277.0	346.2	466.6	421.5	526.8	517.8
72.5°	2842.0	617.2	261.9	286.0	249.9	289.0	364.3	463.6	421.5	569.0	560.0
75°	2417.5	493.7	225.8	261.9	249.9	304.1	376.3	460.6	406.4	541.9	523.8
77.5°	1839.4	403.4	189.7	228.8	237.8	310.1	376.3	454.6	394.4	505.8	493.7
80°	948.3	283.0	153.5	195.7	222.8	304.1	373.3	430.5	352.2	448.6	442.6
82.5°	520.8	207.7	123.4	144.5	186.7	286.0	361.3	388.4	310.1	367.3	352.2
85°	337.2	150.5	99.3	117.4	156.5	237.8	304.1	307.1	219.8	264.9	249.9
87.5°	252.9	87.3	63.2	72.3	108.4	132.5	192.7	198.7	138.5	162.6	153.5
90°	264.9	87.3	66.2	75.3	96.3	99.3	141.5	150.5	108.4	123.4	123.4
92.5°	283.0	87.3	69.2	78.3	87.3	78.3	111.4	123.4	90.3	99.3	96.3
95°	289.0	84.3	75.3	81.3	78.3	63.2	90.3	99.3	75.3	75.3	75.3
97.5°	210.7	60.2	75.3	81.3	72.3	51.2	69.2	78.3	48.2	39.1	39.1
100°	57.2	30.1	72.3	78.3	63.2	42.1	60.2	60.2	30.1	21.1	21.1
102.5°	24.1	24.1	63.2	69.2	48.2	27.1	42.1	42.1	21.1	9.0	9.0
105°	24.1	18.1	45.2	51.2	33.1	15.1	21.1	24.1	15.1	9.0	9.0
107.5°	24.1	18.1	21.1	27.1	15.1	12.0	12.0	12.0	9.0	9.0	9.0



REPORT NUMBER: P559830
 CATALOG NUMBER: SDL-PA1-100-730-U-T2R-A

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	30.1	21.1	12.0	15.1	12.0	9.0	9.0	9.0	12.0	27.1	27.1
115°	27.1	18.1	12.0	12.0	9.0	9.0	6.0	6.0	12.0	33.1	33.1
117.5°	30.1	21.1	12.0	12.0	9.0	6.0	6.0	6.0	15.1	39.1	39.1
120°	36.1	24.1	12.0	9.0	6.0	6.0	6.0	6.0	18.1	42.1	42.1
122.5°	39.1	27.1	12.0	9.0	6.0	3.0	6.0	9.0	21.1	42.1	42.1
125°	33.1	24.1	12.0	9.0	6.0	3.0	6.0	9.0	21.1	39.1	42.1
127.5°	30.1	21.1	12.0	6.0	6.0	3.0	3.0	9.0	18.1	30.1	36.1
130°	24.1	18.1	9.0	6.0	6.0	3.0	3.0	6.0	18.1	27.1	33.1
132.5°	21.1	15.1	9.0	6.0	6.0	3.0	3.0	6.0	18.1	24.1	24.1
135°	15.1	12.0	6.0	6.0	6.0	3.0	6.0	3.0	12.0	21.1	21.1
137.5°	9.0	6.0	6.0	6.0	6.0	3.0	3.0	3.0	9.0	12.0	12.0
140°	3.0	3.0	6.0	6.0	6.0	3.0	3.0	3.0	6.0	6.0	6.0
142.5°	3.0	3.0	6.0	6.0	6.0	3.0	3.0	3.0	6.0	6.0	6.0
145°	3.0	3.0	3.0	6.0	6.0	3.0	3.0	3.0	3.0	3.0	6.0
147.5°	3.0	3.0	3.0	6.0	3.0	3.0	3.0	3.0	3.0	3.0	6.0
150°	3.0	3.0	3.0	6.0	6.0	3.0	3.0	6.0	6.0	6.0	6.0
152.5°	3.0	3.0	6.0	6.0	3.0	3.0	3.0	6.0	6.0	6.0	6.0
155°	9.0	9.0	6.0	6.0	3.0	3.0	0.0	3.0	6.0	6.0	6.0
157.5°	3.0	3.0	6.0	3.0	3.0	3.0	0.0	3.0	3.0	3.0	3.0
160°	3.0	3.0	3.0	3.0	3.0	3.0	0.0	3.0	3.0	3.0	3.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245982

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



--- HS — SS

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



u



110°	30.1	30.1	6.0	9.0	9.0	9.0	6.0	9.0	15.1	21.1	30.1
------	------	------	-----	-----	-----	-----	-----	-----	------	------	------

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





110°	27.1	18.1	12.0	15.1	12.0	9.0	9.0	9.0	9.0	12.0	15.1
------	------	------	------	------	------	-----	-----	-----	-----	------	------

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)