

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P560707

Luminaire Tested: **SDL-PA1-60-730-U-SL3-HSS-A**

Issue Date: 7/26/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P560707  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/26/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: SDL-PA1-60-730-U-SL3-HSS-A  
Description: Springdale  
(1) 70 CRI, 3000K, 800mA LIGHT ENGINE WITH 24 LEDS AND TYPE III SPILL  
LIGHT ELIMINATOR OPTICS, HOUSE SIDE SHIELD AND CLEAR PANELS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5360.7 lumens  
Efficiency: N/A  
Efficacy: 85.9 lumens/watt  
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')  
IES Classification: Type IV - Medium  
BUG Rating: B1 - U3 - G2


Input Watts (W): 62.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P560707  
 CATALOG NUMBER: SDL-PA1-60-730-U-SL3-HSS-A

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 14.2 fc  
 Type IV - Medium - N/A

REPORT NUMBER: P560707  
CATALOG NUMBER: SDL-PA1-60-730-U-SL3-HSS-A

### Luminous Intensity Polar Plot



— Vertical Plane Through 60-Deg Lateral    - - - Horizontal Cone Through 75-Deg Vertical

REPORT NUMBER: P560707  
 CATALOG NUMBER: SDL-PA1-60-730-U-SL3-HSS-A


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	554.0	72.2	626.2
	% Fixture	10.3	1.3	11.7
<b>Street Side</b>	Lumens	4658.9	75.6	4734.5
	% Fixture	86.9	1.4	88.3
<b>Total</b>	Lumens	5212.9	147.8	5360.7
	% Fixture	97.2	2.8	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	98.3	1.8
10°-20°	161.3	3.0
20°-30°	228.0	4.3
30°-40°	409.8	7.6
40°-50°	690.6	12.9
50°-60°	1074.1	20.0
60°-70°	1267.5	23.6
70°-80°	1028.1	19.2
80°-90°	255.3	4.8
90°-100°	103.0	1.9
100°-110°	23.9	0.4
110°-120°	7.5	0.1
120°-130°	6.7	0.1
130°-140°	3.5	0.1
140°-150°	1.7	0.0
150°-160°	1.4	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-90°	5212.9	97.2
0°-180°	5360.7	100.0

**Coefficient of Utilization**




REPORT NUMBER: P560707

CATALOG NUMBER: SDL-PA1-60-730-U-SL3-HSS-A

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	367.2	6.8			
FM (30°-60°)	1992.3	37.2			
FH (60°-80°)	2107.5	39.3			G2/5000
FVH (80°-90°)	191.9	3.6			G2/225
BL (0°-30°)	120.5	2.2	B1/500		
BM (30°-60°)	182.1	3.4	B0/220		
BH (60°-80°)	188.1	3.5	B1/500		G1/500
BVH (80°-90°)	63.3	1.2			G1/100
UL (90°-100°)	103.0	1.9		U3/500	
UH (100°-180°)	44.8	0.8		U2/50	

**BUG Rating: B1-U3-G2**  
 Type IV Medium





REPORT NUMBER: P560707

CATALOG NUMBER: SDL-PA1-60-730-U-SL3-HSS-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	60°	65°	75°	85°
0°	1417.0	1417.0	1417.0	1417.0	1417.0	1417.0	1417.0	1417.0	1417.0	1417.0	1417.0
2.5°	1332.8	1434.4	1404.7	1498.8	1511.2	1506.2	1501.3	1488.9	1476.5	1454.2	1419.5
5°	1278.3	1288.2	1280.8	1298.1	1300.6	1308.0	1295.7	1365.0	1481.5	1451.7	1397.2
7.5°	1050.4	1154.4	1166.8	1199.0	1228.8	1258.5	1275.8	1273.4	1124.7	1263.5	1201.5
10°	1072.7	1087.6	1085.1	1107.4	1082.6	1040.5	948.8	951.3	951.3	981.0	1013.2
12.5°	849.7	894.3	1003.3	1038.0	963.7	877.0	884.4	901.8	914.1	775.4	854.7
15°	963.7	966.2	968.6	968.6	725.9	829.9	723.4	654.0	748.2	916.6	931.5
17.5°	755.6	748.2	872.0	862.1	800.2	616.9	802.7	820.0	787.8	770.5	775.4
20°	886.9	886.9	879.5	701.1	738.3	795.2	688.7	686.2	725.9	901.8	911.7
22.5°	718.4	711.0	750.6	780.4	701.1	758.1	678.8	763.0	844.8	797.7	651.5
25°	899.3	899.3	869.6	676.3	725.9	651.5	753.1	646.6	718.4	976.1	929.0
27.5°	832.4	810.1	740.7	768.0	651.5	758.1	693.7	785.3	829.9	1010.8	1082.6
30°	1075.2	1067.7	988.5	772.9	740.7	696.1	745.7	790.3	956.3	1310.5	1251.1
32.5°	1434.4	1394.8	1124.7	956.3	777.9	825.0	795.2	929.0	1050.4	1340.3	1268.4
35°	1531.0	1501.3	1372.5	1161.9	872.0	872.0	854.7	948.8	1077.7	1404.7	1305.6
37.5°	1563.2	1560.7	1516.1	1270.9	1000.9	1003.3	904.2	995.9	1132.2	1491.4	1360.1
40°	1583.0	1588.0	1632.6	1384.8	1137.1	1132.2	995.9	1062.8	1216.4	1585.5	1459.2
42.5°	1667.3	1694.5	1749.0	1511.2	1265.9	1268.4	1107.4	1169.3	1327.9	1741.6	1595.4
45°	1855.5	1863.0	1895.2	1684.6	1387.3	1404.7	1248.6	1313.0	1464.1	1912.5	1749.0
47.5°	2140.4	2140.4	2085.9	1820.9	1531.0	1555.8	1397.2	1464.1	1625.1	2162.7	1927.4
50°	2393.1	2373.3	2254.4	1981.9	1647.4	1701.9	1592.9	1669.7	1761.4	2353.5	2150.3
52.5°	2551.7	2544.2	2398.1	2090.9	1771.3	1863.0	1754.0	1853.1	1920.0	2551.7	2351.0
55°	2529.4	2529.4	2435.2	2147.9	1885.3	2009.1	1962.1	2085.9	2110.7	2740.0	2497.2
57.5°	2445.2	2457.5	2412.9	2170.2	1907.6	2147.9	2175.1	2291.6	2333.7	2849.0	2588.8
60°	2274.2	2299.0	2346.1	2199.9	1994.3	2303.9	2393.1	2497.2	2576.5	2930.7	2665.6
62.5°	1954.6	1986.8	2152.8	2197.4	2061.2	2465.0	2578.9	2670.6	2744.9	2975.3	2720.1
65°	1481.5	1540.9	1781.2	2038.9	2056.2	2653.3	2730.1	2819.2	2891.1	3019.9	2861.4
67.5°	946.4	948.8	1209.0	1684.6	1917.5	2918.3	2933.2	2977.8	3024.9	3143.8	3062.0
70°	488.0	512.8	636.7	1075.2	1570.6	2972.8	3441.1	3376.6	3304.8	3413.8	3322.1
72.5°	324.5	351.8	418.7	579.7	986.0	2680.5	3993.5	4171.9	3854.8	3614.5	3094.2
75°	183.3	198.2	279.9	458.3	609.4	1731.7	3931.6	4568.3	4201.6	3247.8	2487.3
77.5°	81.8	86.7	126.3	359.2	522.7	844.8	3094.2	3817.6	3671.4	2707.8	1793.6
80°	44.6	44.6	59.5	166.0	443.4	636.7	2053.7	2658.2	2497.2	1632.6	815.1
82.5°	24.8	27.3	34.7	79.3	270.0	582.2	1298.1	1667.3	1318.0	448.4	329.5
85°	9.9	9.9	14.9	42.1	99.1	493.0	711.0	792.8	532.6	227.9	255.2
87.5°	5.0	5.0	5.0	14.9	32.2	126.3	232.9	250.2	195.7	180.8	220.5
90°	7.4	7.4	5.0	5.0	22.3	133.8	195.7	205.6	161.0	180.8	223.0
92.5°	9.9	7.4	5.0	5.0	17.3	133.8	223.0	220.5	161.0	180.8	230.4
95°	12.4	9.9	5.0	5.0	17.3	118.9	267.6	240.3	173.4	183.3	242.8
97.5°	12.4	12.4	5.0	5.0	17.3	91.7	282.4	242.8	151.1	118.9	166.0
100°	14.9	14.9	5.0	5.0	19.8	54.5	195.7	180.8	106.5	39.6	47.1
102.5°	17.3	17.3	5.0	5.0	12.4	27.3	94.1	91.7	59.5	9.9	17.3
105°	17.3	19.8	5.0	5.0	5.0	12.4	34.7	42.1	29.7	9.9	17.3
107.5°	19.8	22.3	5.0	5.0	5.0	7.4	14.9	14.9	9.9	9.9	17.3



REPORT NUMBER: P560707  
 CATALOG NUMBER: SDL-PA1-60-730-U-SL3-HSS-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	45°	55°	60°	65°	75°	85°
112.5°	14.9	14.9	2.5	5.0	5.0	5.0	2.5	5.0	5.0	7.4	14.9
115°	7.4	5.0	2.5	5.0	2.5	5.0	2.5	5.0	7.4	7.4	17.3
117.5°	2.5	2.5	2.5	2.5	2.5	5.0	2.5	5.0	5.0	12.4	22.3
120°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	5.0	5.0	17.3	27.3
122.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	5.0	5.0	17.3	32.2
125°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	5.0	5.0	12.4	29.7
127.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	5.0	5.0	12.4	24.8
130°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	5.0	5.0	9.9	22.3
132.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	5.0	9.9	17.3
135°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	5.0	12.4
137.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	5.0
140°	2.5	0.0	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
142.5°	2.5	0.0	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5
145°	2.5	2.5	2.5	2.5	5.0	2.5	2.5	2.5	2.5	2.5	2.5
147.5°	2.5	2.5	2.5	5.0	5.0	2.5	2.5	2.5	2.5	2.5	2.5
150°	9.9	9.9	9.9	7.4	5.0	2.5	7.4	5.0	2.5	2.5	2.5
152.5°	7.4	7.4	12.4	5.0	2.5	2.5	2.5	7.4	7.4	2.5	2.5
155°	7.4	7.4	5.0	2.5	2.5	2.5	2.5	2.5	2.5	7.4	9.9
157.5°	2.5	2.5	2.5	0.0	2.5	2.5	2.5	2.5	2.5	5.0	2.5
160°	0.0	0.0	0.0	0.0	2.5	2.5	2.5	2.5	2.5	2.5	2.5
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P560707

CATALOG NUMBER: SDL-PA1-60-730-U-SL3-HSS-A

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	1417.0	1417.0	1417.0	1417.0	1417.0	1417.0	1417.0	1417.0	1417.0	1417.0	1417.0
2.5°	1407.1	1392.3	1352.6	1315.5	1270.9	1243.6	1149.5	1043.0	1020.7	1015.7	998.4
5°	1372.5	1340.3	1263.5	1099.9	936.4	862.1	827.4	800.2	763.0	755.6	745.7
7.5°	1164.4	1109.9	990.9	790.3	765.5	696.1	639.2	592.1	490.5	463.3	448.4
10°	968.6	921.6	676.3	574.7	522.7	470.7	408.8	361.7	319.6	299.8	292.3
12.5°	782.8	735.8	505.4	455.8	324.5	267.6	232.9	193.2	161.0	143.7	143.7
15°	867.1	790.3	522.7	324.5	213.1	158.6	116.4	104.0	121.4	123.9	123.9
17.5°	708.5	631.7	411.2	252.7	156.1	86.7	94.1	106.5	116.4	101.6	104.0
20°	815.1	708.5	413.7	190.8	99.1	84.2	86.7	79.3	106.5	109.0	109.0
22.5°	616.9	557.4	312.1	151.1	76.8	79.3	74.3	89.2	99.1	86.7	84.2
25°	797.7	656.5	317.1	96.6	76.8	64.4	76.8	69.4	91.7	94.1	94.1
27.5°	914.1	735.8	277.5	84.2	64.4	69.4	61.9	71.8	69.4	69.4	69.4
30°	1038.0	802.7	270.0	81.8	61.9	57.0	59.5	57.0	66.9	69.4	69.4
32.5°	1038.0	768.0	205.6	81.8	59.5	54.5	47.1	52.0	54.5	59.5	61.9
35°	1045.4	738.3	151.1	74.3	54.5	47.1	42.1	42.1	47.1	49.5	49.5
37.5°	1067.7	718.4	116.4	69.4	49.5	42.1	34.7	37.2	64.4	71.8	71.8
40°	1129.7	718.4	99.1	64.4	44.6	37.2	29.7	47.1	54.5	64.4	64.4
42.5°	1226.3	728.3	94.1	61.9	39.6	32.2	24.8	37.2	66.9	76.8	79.3
45°	1327.9	748.2	89.2	59.5	37.2	27.3	29.7	44.6	52.0	69.4	69.4
47.5°	1469.1	790.3	86.7	57.0	34.7	22.3	27.3	44.6	57.0	74.3	74.3
50°	1622.7	834.9	81.8	54.5	29.7	19.8	42.1	37.2	47.1	76.8	76.8
52.5°	1781.2	886.9	79.3	52.0	27.3	27.3	47.1	44.6	57.0	74.3	76.8
55°	1920.0	929.0	74.3	52.0	24.8	24.8	49.5	44.6	52.0	69.4	71.8
57.5°	1986.8	936.4	71.8	49.5	22.3	24.8	47.1	54.5	47.1	57.0	61.9
60°	2071.1	956.3	64.4	44.6	19.8	32.2	54.5	71.8	64.4	74.3	79.3
62.5°	2150.3	971.1	57.0	39.6	17.3	34.7	71.8	86.7	69.4	86.7	96.6
65°	2296.5	1003.3	47.1	32.2	14.9	39.6	81.8	104.0	76.8	101.6	101.6
67.5°	2499.7	1055.4	37.2	27.3	14.9	44.6	84.2	118.9	91.7	111.5	109.0
70°	2578.9	971.1	32.2	24.8	14.9	52.0	91.7	128.8	96.6	123.9	123.9
72.5°	2249.4	701.1	27.3	24.8	24.8	59.5	114.0	141.2	106.5	156.1	153.6
75°	1736.6	441.0	27.3	24.8	29.7	74.3	128.8	151.1	114.0	173.4	170.9
77.5°	1156.9	208.1	27.3	27.3	34.7	81.8	138.7	161.0	126.3	193.2	190.8
80°	453.4	114.0	29.7	29.7	42.1	86.7	148.6	166.0	131.3	208.1	205.6
82.5°	218.0	79.3	29.7	29.7	57.0	96.6	158.6	173.4	136.3	210.6	208.1
85°	185.8	74.3	27.3	32.2	69.4	121.4	168.5	170.9	138.7	200.7	200.7
87.5°	166.0	71.8	27.3	32.2	94.1	141.2	175.9	168.5	148.6	195.7	195.7
90°	170.9	76.8	29.7	37.2	106.5	143.7	178.4	168.5	143.7	180.8	180.8
92.5°	183.3	81.8	32.2	39.6	106.5	133.8	166.0	151.1	133.8	153.6	151.1
95°	193.2	86.7	34.7	44.6	94.1	104.0	138.7	121.4	111.5	118.9	118.9
97.5°	148.6	66.9	39.6	49.5	71.8	61.9	86.7	79.3	59.5	49.5	49.5
100°	39.6	22.3	42.1	49.5	49.5	42.1	64.4	59.5	39.6	17.3	17.3
102.5°	14.9	14.9	39.6	47.1	39.6	32.2	47.1	44.6	32.2	5.0	5.0
105°	14.9	12.4	24.8	37.2	24.8	17.3	24.8	29.7	19.8	5.0	5.0
107.5°	14.9	12.4	14.9	22.3	9.9	7.4	9.9	9.9	9.9	2.5	5.0



REPORT NUMBER: P560707  
 CATALOG NUMBER: SDL-PA1-60-730-U-SL3-HSS-A

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	14.9	12.4	7.4	9.9	7.4	7.4	5.0	5.0	7.4	14.9	14.9
115°	14.9	12.4	7.4	7.4	5.0	7.4	5.0	2.5	7.4	17.3	19.8
117.5°	19.8	12.4	5.0	5.0	5.0	5.0	5.0	2.5	7.4	22.3	24.8
120°	24.8	14.9	5.0	5.0	5.0	2.5	5.0	2.5	9.9	22.3	24.8
122.5°	27.3	17.3	5.0	5.0	5.0	2.5	2.5	5.0	9.9	22.3	22.3
125°	27.3	17.3	5.0	5.0	2.5	2.5	2.5	2.5	9.9	22.3	24.8
127.5°	22.3	14.9	5.0	5.0	2.5	2.5	2.5	2.5	9.9	19.8	22.3
130°	19.8	14.9	5.0	5.0	2.5	2.5	2.5	2.5	9.9	17.3	19.8
132.5°	14.9	12.4	5.0	2.5	2.5	2.5	2.5	2.5	9.9	14.9	17.3
135°	12.4	7.4	5.0	2.5	2.5	2.5	2.5	2.5	7.4	14.9	14.9
137.5°	5.0	5.0	2.5	2.5	2.5	2.5	2.5	2.5	5.0	7.4	7.4
140°	5.0	5.0	2.5	2.5	2.5	2.5	2.5	2.5	2.5	5.0	5.0
142.5°	2.5	5.0	2.5	2.5	2.5	2.5	0.0	2.5	2.5	2.5	2.5
145°	2.5	5.0	2.5	2.5	2.5	2.5	0.0	2.5	2.5	2.5	2.5
147.5°	2.5	5.0	2.5	2.5	2.5	2.5	0.0	2.5	2.5	2.5	2.5
150°	2.5	5.0	2.5	2.5	2.5	2.5	0.0	2.5	2.5	2.5	5.0
152.5°	2.5	5.0	2.5	2.5	2.5	0.0	0.0	2.5	2.5	2.5	2.5
155°	9.9	7.4	5.0	2.5	2.5	0.0	0.0	0.0	2.5	2.5	2.5
157.5°	2.5	2.5	2.5	2.5	2.5	0.0	0.0	0.0	2.5	2.5	2.5
160°	2.5	2.5	2.5	2.5	2.5	0.0	0.0	0.0	2.5	2.5	2.5
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245982

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





--- HS    — SS

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



u





110°	19.8	19.8	5.0	5.0	5.0	5.0	5.0	5.0	5.0	9.9	17.3
------	------	------	-----	-----	-----	-----	-----	-----	-----	-----	------

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





110°	14.9	12.4	7.4	9.9	7.4	7.4	7.4	5.0	5.0	9.9	9.9
------	------	------	-----	-----	-----	-----	-----	-----	-----	-----	-----

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)