

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P561058

Luminaire Tested: **SDL-PA1-80-730-U-SL3-A**

Issue Date: 7/26/2021

Test Information

Test Method: LM-79-08
Report Number: P561058
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-15)
Test Lab: INNOVATION CENTER
Issue Date: 7/26/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: SDL-PA1-80-730-U-SL3-A
Description: Springdale
(1) 70 CRI, 3000K, 1050mA LIGHT ENGINE WITH 24 LEDS AND TYPE III SPILL
LIGHT ELIMINATOR OPTICS AND CLEAR PANELS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7906.4 lumens
Efficiency: N/A
Efficacy: 96.4 lumens/watt
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')
IES Classification: Type III - Medium
BUG Rating: B2 - U3 - G3


Input Watts (W): 82
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P561058
 CATALOG NUMBER: SDL-PA1-80-730-U-SL3-A

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 20.9 fc
 Type III - Medium - N/A

REPORT NUMBER: P561058
CATALOG NUMBER: SDL-PA1-80-730-U-SL3-A

Luminous Intensity Polar Plot



— Vertical Plane Through 60-Deg Lateral - - - Horizontal Cone Through 75-Deg Vertical

REPORT NUMBER: P561058

CATALOG NUMBER: SDL-PA1-80-730-U-SL3-A


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1388.0	105.3	1493.2
	% Fixture	17.6	1.3	18.9
Street Side	Lumens	6301.8	111.3	6413.1
	% Fixture	79.7	1.4	81.1
Total	Lumens	7689.8	216.6	7906.4
	% Fixture	97.3	2.7	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.6	1.9
10°-20°	273.4	3.5
20°-30°	354.3	4.5
30°-40°	590.5	7.5
40°-50°	945.5	12.0
50°-60°	1451.6	18.4
60°-70°	1813.8	22.9
70°-80°	1654.3	20.9
80°-90°	452.7	5.7
90°-100°	152.0	1.9
100°-110°	34.6	0.4
110°-120°	11.0	0.1
120°-130°	10.2	0.1
130°-140°	4.9	0.1
140°-150°	2.0	0.0
150°-160°	1.8	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-90°	7689.8	97.3
0°-180°	7906.4	100.0

Coefficient of Utilization



REPORT NUMBER: P561058


CATALOG NUMBER: SDL-PA1-80-730-U-SL3-A

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	476.2	6.0			
FM (30°-60°)	2530.9	32.0			
FH (60°-80°)	2953.1	37.4			G2/5000
FVH (80°-90°)	341.6	4.3			G3/500
BL (0°-30°)	305.2	3.9	B1/500		
BM (30°-60°)	456.8	5.8	B1/1000		
BH (60°-80°)	515.0	6.5	B2/1000		G2/1000
BVH (80°-90°)	111.1	1.4			G2/225
UL (90°-100°)	152.0	1.9		U3/500	
UH (100°-180°)	64.6	0.8		U3/500	

BUG Rating: B2-U3-G3

Type III Medium





REPORT NUMBER: P561058

CATALOG NUMBER: SDL-PA1-80-730-U-SL3-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	60°	65°	75°	85°
0°	2087.9	2087.9	2087.9	2087.9	2087.9	2087.9	2087.9	2087.9	2087.9	2087.9	2087.9
2.5°	1751.8	1915.2	1899.8	2026.3	2026.3	2054.0	2066.4	2063.3	2075.6	2087.9	2084.9
5°	1613.0	1616.1	1628.4	1656.2	1665.4	1674.7	1705.5	1813.5	1995.4	2038.6	2038.6
7.5°	1332.3	1406.4	1498.9	1514.3	1569.8	1597.6	1631.5	1637.7	1514.3	1736.4	1757.9
10°	1350.8	1353.9	1347.8	1381.7	1341.6	1326.2	1218.2	1224.4	1236.7	1320.0	1486.5
12.5°	1057.9	1119.5	1252.2	1313.8	1215.1	1107.2	1101.0	1153.5	1175.0	1051.7	1310.7
15°	1209.0	1215.1	1218.2	1221.3	906.7	1051.7	919.1	845.0	946.8	1193.6	1357.0
17.5°	946.8	953.0	1097.9	1094.9	999.3	808.0	999.3	1020.8	980.7	1014.7	1135.0
20°	1110.3	1113.4	1104.1	857.4	875.9	990.0	860.5	857.4	906.7	1168.9	1320.0
22.5°	912.9	900.6	897.5	980.7	891.3	953.0	835.8	968.4	1051.7	1042.4	996.2
25°	1144.2	1141.1	1094.9	854.3	912.9	808.0	977.7	820.4	909.8	1261.4	1320.0
27.5°	1070.2	1027.0	949.9	986.9	851.2	946.8	869.7	993.1	1048.6	1295.3	1529.7
30°	1384.8	1353.9	1264.5	996.2	940.7	872.8	931.4	996.2	1193.6	1668.5	1748.7
32.5°	1828.9	1795.0	1474.2	1221.3	986.9	1033.2	980.7	1168.9	1316.9	1702.4	1764.1
35°	1964.6	1918.3	1761.0	1480.4	1131.9	1097.9	1045.5	1178.1	1335.4	1791.9	1791.9
37.5°	2041.7	2038.6	1964.6	1634.6	1276.8	1258.3	1125.7	1236.7	1409.4	1878.2	1859.7
40°	2054.0	2069.4	2103.4	1770.3	1449.5	1409.4	1230.6	1316.9	1514.3	1983.1	1946.1
42.5°	2155.8	2183.6	2260.7	1949.2	1622.2	1585.2	1353.9	1434.1	1628.4	2137.3	2128.0
45°	2319.3	2347.0	2414.9	2146.5	1773.4	1748.7	1554.4	1603.7	1813.5	2408.7	2322.3
47.5°	2658.5	2664.7	2636.9	2310.0	1936.8	1936.8	1748.7	1795.0	1980.0	2658.5	2575.2
50°	2997.8	2960.7	2837.4	2504.3	2100.3	2146.5	1949.2	2057.1	2168.1	2911.4	2797.3
52.5°	3185.9	3179.7	3013.2	2652.3	2242.2	2331.6	2180.5	2273.0	2340.8	3167.4	3007.0
55°	3192.1	3182.8	3068.7	2723.3	2374.8	2522.8	2411.8	2532.1	2581.4	3367.9	3293.8
57.5°	3090.3	3115.0	3056.4	2763.4	2439.5	2707.9	2692.4	2822.0	2846.6	3605.3	3491.2
60°	2929.9	2926.8	2997.8	2800.4	2538.2	2883.6	2951.5	3084.1	3216.7	3787.3	3667.0
62.5°	2529.0	2556.7	2757.2	2800.4	2646.2	3111.9	3241.4	3380.2	3543.6	3953.8	3824.3
65°	1980.0	1995.4	2310.0	2596.8	2677.0	3417.2	3534.4	3673.2	3845.9	4123.5	4000.1
67.5°	1196.6	1298.4	1569.8	2137.3	2519.7	3784.2	4000.1	4058.7	4157.4	4314.7	4259.2
70°	681.6	712.4	842.0	1344.7	2103.4	3901.4	4857.5	4752.6	4650.8	4687.9	4583.0
72.5°	518.1	536.6	595.2	795.7	1258.3	3445.0	5579.2	5967.8	5529.8	5076.5	4573.7
75°	376.3	394.8	453.4	641.5	826.5	2208.2	5505.1	6569.2	6316.3	5095.0	4135.8
77.5°	234.4	237.5	271.4	545.9	743.3	1107.2	4308.5	5850.6	5961.6	4758.8	3429.5
80°	163.5	166.5	172.7	293.0	684.7	888.2	2892.9	4296.2	4453.5	3312.3	1748.7
82.5°	117.2	123.4	129.5	172.7	444.1	848.1	1801.1	2704.8	2384.0	1199.7	709.3
85°	61.7	67.9	83.3	104.9	178.9	922.1	1079.4	1375.5	1088.7	487.3	422.5
87.5°	24.7	21.6	18.5	27.8	49.3	354.7	419.4	462.6	357.8	274.5	336.2
90°	21.6	18.5	12.3	15.4	21.6	126.4	265.2	296.1	246.7	268.3	339.3
92.5°	21.6	18.5	12.3	12.3	21.6	126.4	317.7	323.8	256.0	274.5	354.7
95°	21.6	21.6	12.3	12.3	21.6	114.1	376.3	370.1	265.2	289.9	376.3
97.5°	21.6	21.6	9.3	12.3	21.6	77.1	388.6	400.9	259.1	206.6	311.5
100°	21.6	21.6	9.3	9.3	18.5	49.3	271.4	293.0	191.2	67.9	77.1
102.5°	21.6	21.6	9.3	9.3	12.3	33.9	120.3	145.0	114.1	21.6	24.7
105°	21.6	24.7	6.2	6.2	9.3	18.5	52.4	58.6	46.3	15.4	27.8
107.5°	24.7	27.8	6.2	6.2	6.2	9.3	18.5	21.6	12.3	12.3	27.8



REPORT NUMBER: P561058

CATALOG NUMBER: SDL-PA1-80-730-U-SL3-A

CANDELA DISTRIBUTION (continued):

	0°	5°	15°	25°	35°	45°	55°	60°	65°	75°	85°
112.5°	21.6	18.5	3.1	6.2	6.2	6.2	6.2	6.2	6.2	12.3	30.8
115°	12.3	9.3	3.1	6.2	6.2	6.2	3.1	6.2	9.3	12.3	27.8
117.5°	12.3	9.3	3.1	3.1	3.1	6.2	3.1	3.1	9.3	15.4	33.9
120°	9.3	9.3	3.1	3.1	3.1	3.1	3.1	6.2	6.2	21.6	46.3
122.5°	9.3	9.3	3.1	3.1	3.1	3.1	3.1	6.2	6.2	21.6	46.3
125°	12.3	12.3	6.2	3.1	3.1	3.1	3.1	6.2	6.2	18.5	43.2
127.5°	9.3	9.3	6.2	3.1	3.1	3.1	3.1	6.2	6.2	15.4	33.9
130°	9.3	9.3	6.2	3.1	3.1	3.1	3.1	6.2	3.1	15.4	27.8
132.5°	9.3	9.3	6.2	3.1	3.1	3.1	3.1	3.1	3.1	9.3	21.6
135°	9.3	9.3	6.2	3.1	3.1	3.1	3.1	3.1	3.1	6.2	15.4
137.5°	6.2	6.2	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	6.2
140°	0.0	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
142.5°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
145°	3.1	3.1	3.1	3.1	6.2	3.1	3.1	3.1	3.1	3.1	3.1
147.5°	3.1	3.1	3.1	6.2	6.2	6.2	3.1	3.1	3.1	3.1	3.1
150°	6.2	6.2	12.3	9.3	6.2	3.1	3.1	3.1	3.1	3.1	3.1
152.5°	12.3	12.3	12.3	9.3	3.1	3.1	6.2	9.3	3.1	3.1	3.1
155°	9.3	9.3	9.3	3.1	3.1	3.1	3.1	3.1	6.2	9.3	9.3
157.5°	0.0	0.0	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
160°	0.0	0.0	0.0	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P561058
 CATALOG NUMBER: SDL-PA1-80-730-U-SL3-A

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2087.9	2087.9	2087.9	2087.9	2087.9	2087.9	2087.9	2087.9	2087.9	2087.9	2087.9
2.5°	2075.6	2081.8	2075.6	2069.4	2063.3	2044.8	1918.3	1764.1	1751.8	1764.1	1757.9
5°	2023.2	2023.2	2020.1	1807.3	1680.8	1643.8	1634.6	1625.3	1606.8	1597.6	1603.7
7.5°	1745.6	1736.4	1628.4	1437.2	1557.5	1514.3	1489.6	1477.3	1292.2	1224.4	1230.6
10°	1458.8	1458.8	1212.1	1144.2	1138.0	1156.5	1283.0	1273.7	1249.1	1233.6	1249.1
12.5°	1258.3	1310.7	962.2	1030.1	835.8	925.2	1011.6	1073.3	885.1	832.7	842.0
15°	1335.4	1316.9	1057.9	808.0	737.1	777.2	623.0	780.3	767.9	743.3	740.2
17.5°	1165.8	1070.2	882.1	758.7	727.9	549.0	533.6	552.1	505.8	462.6	484.2
20°	1267.6	1215.1	934.5	675.4	561.3	499.6	376.3	351.6	447.2	468.8	465.7
22.5°	1057.9	882.1	764.9	672.3	453.4	357.8	283.7	311.5	333.1	354.7	363.9
25°	1242.9	1147.3	835.8	502.7	367.0	262.1	256.0	231.3	348.5	397.9	394.8
27.5°	1434.1	1298.4	805.0	471.9	265.2	225.1	206.6	234.4	243.6	274.5	293.0
30°	1603.7	1440.3	931.4	437.9	222.1	169.6	185.0	191.2	237.5	256.0	256.0
32.5°	1597.6	1400.2	832.7	373.2	182.0	154.2	154.2	182.0	209.7	252.9	256.0
35°	1594.5	1369.3	743.3	289.9	160.4	135.7	141.9	172.7	209.7	234.4	237.5
37.5°	1631.5	1360.1	653.8	234.4	145.0	129.5	135.7	163.5	225.1	249.8	249.8
40°	1687.0	1366.3	564.4	200.5	138.8	126.4	129.5	172.7	203.6	225.1	225.1
42.5°	1856.6	1455.7	487.3	185.0	138.8	123.4	123.4	160.4	206.6	243.6	246.7
45°	1983.1	1526.6	428.7	185.0	135.7	117.2	129.5	160.4	182.0	268.3	286.8
47.5°	2186.6	1656.2	373.2	185.0	135.7	114.1	120.3	157.3	191.2	308.4	320.7
50°	2390.2	1785.7	348.5	185.0	135.7	111.0	135.7	151.1	191.2	320.7	330.0
52.5°	2606.1	1946.1	333.1	185.0	135.7	117.2	148.0	182.0	206.6	286.8	283.7
55°	2828.1	2087.9	323.8	191.2	135.7	117.2	160.4	169.6	175.8	222.1	228.2
57.5°	3034.8	2260.7	342.3	191.2	132.6	123.4	151.1	166.5	154.2	194.3	197.4
60°	3198.2	2417.9	388.6	185.0	129.5	123.4	154.2	182.0	172.7	212.8	219.0
62.5°	3386.4	2584.5	496.5	188.1	129.5	126.4	172.7	197.4	175.8	209.7	222.1
65°	3633.1	2837.4	616.8	206.6	132.6	132.6	175.8	212.8	175.8	206.6	206.6
67.5°	3910.7	3071.8	616.8	240.6	141.9	141.9	175.8	225.1	188.1	206.6	206.6
70°	4114.2	3084.1	508.9	265.2	154.2	151.1	182.0	234.4	191.2	228.2	225.1
72.5°	3889.1	2747.9	422.5	262.1	166.5	157.3	206.6	240.6	194.3	259.1	256.0
75°	3414.1	2266.8	367.0	234.4	151.1	160.4	215.9	246.7	197.4	271.4	265.2
77.5°	2692.4	1653.1	311.5	197.4	132.6	154.2	222.1	252.9	203.6	286.8	283.7
80°	1304.6	829.6	252.9	166.5	120.3	148.0	222.1	249.8	200.5	296.1	296.1
82.5°	589.1	413.3	172.7	114.1	120.3	151.1	228.2	252.9	200.5	289.9	286.8
85°	382.4	283.7	111.0	89.4	120.3	172.7	231.3	240.6	191.2	268.3	268.3
87.5°	286.8	197.4	58.6	55.5	132.6	188.1	231.3	222.1	185.0	252.9	246.7
90°	293.0	209.7	61.7	55.5	141.9	191.2	231.3	219.0	178.9	228.2	228.2
92.5°	317.7	231.3	70.9	61.7	145.0	172.7	219.0	197.4	166.5	197.4	194.3
95°	345.4	259.1	83.3	70.9	126.4	126.4	172.7	160.4	141.9	151.1	151.1
97.5°	252.9	185.0	74.0	77.1	95.6	80.2	114.1	107.9	74.0	67.9	64.8
100°	74.0	61.7	67.9	74.0	67.9	58.6	86.4	83.3	49.3	24.7	24.7
102.5°	27.8	30.8	61.7	67.9	52.4	43.2	61.7	67.9	40.1	6.2	9.3
105°	24.7	21.6	43.2	52.4	30.8	24.7	30.8	43.2	24.7	6.2	6.2
107.5°	27.8	21.6	21.6	27.8	12.3	12.3	12.3	15.4	9.3	6.2	6.2



REPORT NUMBER: P561058

CATALOG NUMBER: SDL-PA1-80-730-U-SL3-A

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	27.8	21.6	12.3	12.3	9.3	9.3	6.2	6.2	9.3	15.4	15.4
115°	30.8	24.7	12.3	9.3	6.2	9.3	6.2	3.1	9.3	21.6	21.6
117.5°	37.0	27.8	9.3	9.3	6.2	6.2	6.2	3.1	9.3	27.8	30.8
120°	46.3	33.9	12.3	6.2	6.2	6.2	6.2	3.1	12.3	30.8	33.9
122.5°	46.3	37.0	12.3	6.2	6.2	3.1	3.1	6.2	12.3	30.8	33.9
125°	43.2	33.9	12.3	6.2	6.2	3.1	3.1	3.1	15.4	30.8	33.9
127.5°	33.9	30.8	12.3	6.2	3.1	3.1	3.1	6.2	12.3	27.8	27.8
130°	27.8	24.7	9.3	6.2	3.1	3.1	3.1	3.1	12.3	21.6	24.7
132.5°	21.6	18.5	9.3	6.2	3.1	3.1	3.1	3.1	12.3	21.6	21.6
135°	15.4	15.4	6.2	3.1	3.1	3.1	3.1	3.1	9.3	15.4	18.5
137.5°	6.2	6.2	6.2	3.1	3.1	3.1	3.1	3.1	6.2	9.3	9.3
140°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	0.0	3.1	6.2	6.2
142.5°	3.1	3.1	3.1	3.1	3.1	3.1	0.0	3.1	3.1	3.1	6.2
145°	3.1	3.1	3.1	3.1	3.1	3.1	0.0	3.1	3.1	3.1	3.1
147.5°	3.1	3.1	3.1	3.1	3.1	3.1	0.0	3.1	3.1	3.1	3.1
150°	3.1	3.1	3.1	3.1	3.1	3.1	0.0	3.1	3.1	3.1	3.1
152.5°	3.1	3.1	3.1	3.1	3.1	3.1	0.0	3.1	3.1	6.2	6.2
155°	9.3	9.3	9.3	6.2	3.1	0.0	0.0	0.0	3.1	3.1	6.2
157.5°	3.1	3.1	3.1	3.1	3.1	3.1	0.0	0.0	3.1	3.1	3.1
160°	3.1	3.1	3.1	3.1	3.1	0.0	0.0	0.0	3.1	3.1	3.1
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245982

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





--- HS — SS

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



u



110°	27.8	27.8	6.2	6.2	6.2	9.3	6.2	6.2	9.3	12.3	30.8
------	------	------	-----	-----	-----	-----	-----	-----	-----	------	------

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





110°	27.8	21.6	12.3	12.3	9.3	9.3	9.3	6.2	6.2	6.2	6.2
------	------	------	------	------	-----	-----	-----	-----	-----	-----	-----

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)