

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P561234

Luminaire Tested: **SDL-PA1-90-730-U-SL3-A**

Issue Date: 7/26/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P561234  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2106-279-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/26/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: SDL-PA1-90-730-U-SL3-A  
Description: Springdale  
(1) 70 CRI, 3000K, 1180mA LIGHT ENGINE WITH 24 LEDS AND TYPE III SPILL  
LIGHT ELIMINATOR OPTICS AND CLEAR PANELS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8664.5 lumens  
Efficiency: N/A  
Efficacy: 93.8 lumens/watt  
Luminous Opening: Rectangular w/ Sides (W: 1.21' x L: 1.21' x H: 0.96')  
IES Classification: Type III - Medium  
BUG Rating: B2 - U3 - G3

Input Watts (W): 92.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




REPORT NUMBER: P561234

CATALOG NUMBER: SDL-PA1-90-730-U-SL3-A

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 22.9 fc  
 Type III - Medium - N/A

REPORT NUMBER: P561234  
CATALOG NUMBER: SDL-PA1-90-730-U-SL3-A

### Luminous Intensity Polar Plot



— Vertical Plane Through 60-Deg Lateral    - - - Horizontal Cone Through 75-Deg Vertical

REPORT NUMBER: P561234

CATALOG NUMBER: SDL-PA1-90-730-U-SL3-A


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	1521.1	115.3	1636.4
	% Fixture	17.6	1.3	18.9
<b>Street Side</b>	Lumens	6906.1	122.0	7028.1
	% Fixture	79.7	1.4	81.1
<b>Total</b>	Lumens	8427.2	237.3	8664.5
	% Fixture	97.3	2.7	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	168.4	1.9
10°-20°	299.6	3.5
20°-30°	388.3	4.5
30°-40°	647.2	7.5
40°-50°	1036.2	12.0
50°-60°	1590.8	18.4
60°-70°	1987.7	22.9
70°-80°	1812.9	20.9
80°-90°	496.1	5.7
90°-100°	166.6	1.9
100°-110°	37.9	0.4
110°-120°	12.0	0.1
120°-130°	11.2	0.1
130°-140°	5.3	0.1
140°-150°	2.2	0.0
150°-160°	2.0	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-90°	8427.2	97.3
0°-180°	8664.5	100.0

**Coefficient of Utilization**



REPORT NUMBER: P561234


CATALOG NUMBER: SDL-PA1-90-730-U-SL3-A

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	521.9	6.0			
FM (30°-60°)	2773.5	32.0			
FH (60°-80°)	3236.3	37.4			G2/5000
FVH (80°-90°)	374.4	4.3			G3/500
BL (0°-30°)	334.4	3.9	B1/500		
BM (30°-60°)	500.6	5.8	B1/1000		
BH (60°-80°)	564.4	6.5	B2/1000		G2/1000
BVH (80°-90°)	121.7	1.4			G2/225
UL (90°-100°)	166.6	1.9		U3/500	
UH (100°-180°)	70.8	0.8		U3/500	

**BUG Rating: B2-U3-G3**

Type III Medium





REPORT NUMBER: P561234

CATALOG NUMBER: SDL-PA1-90-730-U-SL3-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	60°	65°	75°	85°
0°	2288.2	2288.2	2288.2	2288.2	2288.2	2288.2	2288.2	2288.2	2288.2	2288.2	2288.2
2.5°	1919.8	2098.9	2082.0	2220.6	2220.6	2251.0	2264.5	2261.1	2274.6	2288.2	2284.8
5°	1767.7	1771.0	1784.6	1815.0	1825.1	1835.3	1869.1	1987.3	2186.8	2234.1	2234.1
7.5°	1460.1	1541.2	1642.6	1659.5	1720.3	1750.8	1787.9	1794.7	1659.5	1902.9	1926.5
10°	1480.4	1483.8	1477.0	1514.2	1470.2	1453.3	1335.0	1341.8	1355.3	1446.6	1629.1
12.5°	1159.3	1226.9	1372.2	1439.8	1331.7	1213.4	1206.6	1264.1	1287.7	1152.5	1436.4
15°	1324.9	1331.7	1335.0	1338.4	993.7	1152.5	1007.2	926.1	1037.6	1308.0	1487.1
17.5°	1037.6	1044.4	1203.2	1199.8	1095.1	885.5	1095.1	1118.7	1074.8	1112.0	1243.8
20°	1216.7	1220.1	1210.0	939.6	959.9	1084.9	943.0	939.6	993.7	1281.0	1446.6
22.5°	1000.4	986.9	983.5	1074.8	976.8	1044.4	915.9	1061.3	1152.5	1142.4	1091.7
25°	1253.9	1250.5	1199.8	936.2	1000.4	885.5	1071.4	899.0	997.1	1382.4	1446.6
27.5°	1172.8	1125.5	1041.0	1081.6	932.8	1037.6	953.1	1088.3	1149.1	1419.5	1676.4
30°	1517.6	1483.8	1385.7	1091.7	1030.9	956.5	1020.7	1091.7	1308.0	1828.5	1916.4
32.5°	2004.2	1967.1	1615.6	1338.4	1081.6	1132.2	1074.8	1281.0	1443.2	1865.7	1933.3
35°	2153.0	2102.3	1929.9	1622.3	1240.4	1203.2	1145.8	1291.1	1463.5	1963.7	1963.7
37.5°	2237.5	2234.1	2153.0	1791.3	1399.3	1379.0	1233.6	1355.3	1544.6	2058.3	2038.0
40°	2251.0	2267.9	2305.1	1940.0	1588.5	1544.6	1348.6	1443.2	1659.5	2173.2	2132.7
42.5°	2362.5	2392.9	2477.4	2136.1	1777.8	1737.2	1483.8	1571.6	1784.6	2342.2	2332.1
45°	2541.6	2572.1	2646.4	2352.4	1943.4	1916.4	1703.4	1757.5	1987.3	2639.7	2545.0
47.5°	2913.4	2920.2	2889.8	2531.5	2122.5	2122.5	1916.4	1967.1	2169.9	2913.4	2822.2
50°	3285.2	3244.7	3109.5	2744.4	2301.7	2352.4	2136.1	2254.4	2376.0	3190.6	3065.5
52.5°	3491.4	3484.6	3302.1	2906.7	2457.1	2555.2	2389.6	2490.9	2565.3	3471.1	3295.3
55°	3498.1	3488.0	3362.9	2984.4	2602.5	2764.7	2643.0	2774.9	2828.9	3690.8	3609.7
57.5°	3386.6	3413.6	3349.4	3028.3	2673.5	2967.5	2950.6	3092.6	3119.6	3951.0	3826.0
60°	3210.9	3207.5	3285.2	3068.9	2781.6	3160.2	3234.5	3379.8	3525.2	4150.5	4018.6
62.5°	2771.5	2801.9	3021.6	3068.9	2899.9	3410.3	3552.2	3704.3	3883.4	4333.0	4191.0
65°	2169.9	2186.8	2531.5	2845.8	2933.7	3744.9	3873.3	4025.4	4214.7	4518.9	4383.7
67.5°	1311.4	1422.9	1720.3	2342.2	2761.3	4147.1	4383.7	4447.9	4556.0	4728.4	4667.6
70°	746.9	780.7	922.7	1473.6	2305.1	4275.5	5323.3	5208.3	5096.8	5137.4	5022.5
72.5°	567.8	588.1	652.3	872.0	1379.0	3775.3	6114.1	6540.0	6060.1	5563.2	5012.3
75°	412.3	432.6	496.8	703.0	905.8	2420.0	6033.0	7199.1	6921.9	5583.5	4532.4
77.5°	256.9	260.2	297.4	598.2	814.5	1213.4	4721.6	6411.6	6533.2	5215.1	3758.4
80°	179.1	182.5	189.3	321.1	750.3	973.4	3170.3	4708.1	4880.5	3630.0	1916.4
82.5°	128.4	135.2	142.0	189.3	486.7	929.5	1973.8	2964.1	2612.6	1314.8	777.4
85°	67.6	74.4	91.3	114.9	196.0	1010.6	1182.9	1507.4	1193.1	534.0	463.0
87.5°	27.0	23.7	20.3	30.4	54.1	388.7	459.7	507.0	392.1	300.8	368.4
90°	23.7	20.3	13.5	16.9	23.7	138.6	290.7	324.5	270.4	294.0	371.8
92.5°	23.7	20.3	13.5	13.5	23.7	138.6	348.1	354.9	280.5	300.8	388.7
95°	23.7	23.7	13.5	13.5	23.7	125.1	412.3	405.6	290.7	317.7	412.3
97.5°	23.7	23.7	10.1	13.5	23.7	84.5	425.9	439.4	283.9	226.4	341.4
100°	23.7	23.7	10.1	10.1	20.3	54.1	297.4	321.1	209.6	74.4	84.5
102.5°	23.7	23.7	10.1	10.1	13.5	37.2	131.8	158.9	125.1	23.7	27.0
105°	23.7	27.0	6.8	6.8	10.1	20.3	57.5	64.2	50.7	16.9	30.4
107.5°	27.0	30.4	6.8	6.8	6.8	10.1	20.3	23.7	13.5	13.5	30.4



REPORT NUMBER: P561234

CATALOG NUMBER: SDL-PA1-90-730-U-SL3-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	15°	25°	35°	45°	55°	60°	65°	75°	85°
112.5°	23.7	20.3	3.4	6.8	6.8	6.8	6.8	6.8	6.8	13.5	33.8
115°	13.5	10.1	3.4	6.8	6.8	6.8	3.4	6.8	10.1	13.5	30.4
117.5°	13.5	10.1	3.4	3.4	3.4	6.8	3.4	3.4	10.1	16.9	37.2
120°	10.1	10.1	3.4	3.4	3.4	3.4	3.4	6.8	6.8	23.7	50.7
122.5°	10.1	10.1	3.4	3.4	3.4	3.4	3.4	6.8	6.8	23.7	50.7
125°	13.5	13.5	6.8	3.4	3.4	3.4	3.4	6.8	6.8	20.3	47.3
127.5°	10.1	10.1	6.8	3.4	3.4	3.4	3.4	6.8	6.8	16.9	37.2
130°	10.1	10.1	6.8	3.4	3.4	3.4	3.4	6.8	3.4	16.9	30.4
132.5°	10.1	10.1	6.8	3.4	3.4	3.4	3.4	3.4	3.4	10.1	23.7
135°	10.1	10.1	6.8	3.4	3.4	3.4	3.4	3.4	3.4	6.8	16.9
137.5°	6.8	6.8	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	6.8
140°	0.0	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
142.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
145°	3.4	3.4	3.4	3.4	6.8	3.4	3.4	3.4	3.4	3.4	3.4
147.5°	3.4	3.4	3.4	6.8	6.8	6.8	3.4	3.4	3.4	3.4	3.4
150°	6.8	6.8	13.5	10.1	6.8	3.4	3.4	3.4	3.4	3.4	3.4
152.5°	13.5	13.5	13.5	10.1	3.4	3.4	6.8	10.1	3.4	3.4	3.4
155°	10.1	10.1	10.1	3.4	3.4	3.4	3.4	3.4	6.8	10.1	10.1
157.5°	0.0	0.0	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
160°	0.0	0.0	0.0	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P561234  
 CATALOG NUMBER: SDL-PA1-90-730-U-SL3-A

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2288.2	2288.2	2288.2	2288.2	2288.2	2288.2	2288.2	2288.2	2288.2	2288.2	2288.2
2.5°	2274.6	2281.4	2274.6	2267.9	2261.1	2240.8	2102.3	1933.3	1919.8	1933.3	1926.5
5°	2217.2	2217.2	2213.8	1980.6	1842.0	1801.5	1791.3	1781.2	1760.9	1750.8	1757.5
7.5°	1913.0	1902.9	1784.6	1575.0	1706.8	1659.5	1632.5	1618.9	1416.2	1341.8	1348.6
10°	1598.7	1598.7	1328.3	1253.9	1247.2	1267.4	1406.0	1395.9	1368.8	1351.9	1368.8
12.5°	1379.0	1436.4	1054.5	1128.9	915.9	1014.0	1108.6	1176.2	970.0	912.6	922.7
15°	1463.5	1443.2	1159.3	885.5	807.8	851.7	682.7	855.1	841.6	814.5	811.2
17.5°	1277.6	1172.8	966.6	831.4	797.6	601.6	584.7	605.0	554.3	507.0	530.6
20°	1389.1	1331.7	1024.1	740.2	615.1	547.5	412.3	385.3	490.1	513.7	510.4
22.5°	1159.3	966.6	838.2	736.8	496.8	392.1	310.9	341.4	365.0	388.7	398.8
25°	1362.1	1257.3	915.9	550.9	402.2	287.3	280.5	253.5	381.9	436.0	432.6
27.5°	1571.6	1422.9	882.1	517.1	290.7	246.7	226.4	256.9	267.0	300.8	321.1
30°	1757.5	1578.4	1020.7	479.9	243.3	185.9	202.8	209.6	260.2	280.5	280.5
32.5°	1750.8	1534.4	912.6	409.0	199.4	169.0	169.0	199.4	229.8	277.1	280.5
35°	1747.4	1500.7	814.5	317.7	175.8	148.7	155.5	189.3	229.8	256.9	260.2
37.5°	1787.9	1490.5	716.5	256.9	158.9	142.0	148.7	179.1	246.7	273.8	273.8
40°	1848.8	1497.3	618.5	219.7	152.1	138.6	142.0	189.3	223.1	246.7	246.7
42.5°	2034.7	1595.3	534.0	202.8	152.1	135.2	135.2	175.8	226.4	267.0	270.4
45°	2173.2	1673.0	469.8	202.8	148.7	128.4	142.0	175.8	199.4	294.0	314.3
47.5°	2396.3	1815.0	409.0	202.8	148.7	125.1	131.8	172.4	209.6	338.0	351.5
50°	2619.4	1956.9	381.9	202.8	148.7	121.7	148.7	165.6	209.6	351.5	361.6
52.5°	2856.0	2132.7	365.0	202.8	148.7	128.4	162.2	199.4	226.4	314.3	310.9
55°	3099.3	2288.2	354.9	209.6	148.7	128.4	175.8	185.9	192.7	243.3	250.1
57.5°	3325.8	2477.4	375.2	209.6	145.3	135.2	165.6	182.5	169.0	212.9	216.3
60°	3504.9	2649.8	425.9	202.8	142.0	135.2	169.0	199.4	189.3	233.2	240.0
62.5°	3711.1	2832.3	544.2	206.2	142.0	138.6	189.3	216.3	192.7	229.8	243.3
65°	3981.5	3109.5	676.0	226.4	145.3	145.3	192.7	233.2	192.7	226.4	226.4
67.5°	4285.6	3366.3	676.0	263.6	155.5	155.5	192.7	246.7	206.2	226.4	226.4
70°	4508.7	3379.8	557.7	290.7	169.0	165.6	199.4	256.9	209.6	250.1	246.7
72.5°	4262.0	3011.4	463.0	287.3	182.5	172.4	226.4	263.6	212.9	283.9	280.5
75°	3741.5	2484.2	402.2	256.9	165.6	175.8	236.6	270.4	216.3	297.4	290.7
77.5°	2950.6	1811.6	341.4	216.3	145.3	169.0	243.3	277.1	223.1	314.3	310.9
80°	1429.7	909.2	277.1	182.5	131.8	162.2	243.3	273.8	219.7	324.5	324.5
82.5°	645.6	452.9	189.3	125.1	131.8	165.6	250.1	277.1	219.7	317.7	314.3
85°	419.1	310.9	121.7	98.0	131.8	189.3	253.5	263.6	209.6	294.0	294.0
87.5°	314.3	216.3	64.2	60.8	145.3	206.2	253.5	243.3	202.8	277.1	270.4
90°	321.1	229.8	67.6	60.8	155.5	209.6	253.5	240.0	196.0	250.1	250.1
92.5°	348.1	253.5	77.7	67.6	158.9	189.3	240.0	216.3	182.5	216.3	212.9
95°	378.5	283.9	91.3	77.7	138.6	138.6	189.3	175.8	155.5	165.6	165.6
97.5°	277.1	202.8	81.1	84.5	104.8	87.9	125.1	118.3	81.1	74.4	71.0
100°	81.1	67.6	74.4	81.1	74.4	64.2	94.6	91.3	54.1	27.0	27.0
102.5°	30.4	33.8	67.6	74.4	57.5	47.3	67.6	74.4	43.9	6.8	10.1
105°	27.0	23.7	47.3	57.5	33.8	27.0	33.8	47.3	27.0	6.8	6.8
107.5°	30.4	23.7	23.7	30.4	13.5	13.5	13.5	16.9	10.1	6.8	6.8



REPORT NUMBER: P561234

CATALOG NUMBER: SDL-PA1-90-730-U-SL3-A

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
112.5°	30.4	23.7	13.5	13.5	10.1	10.1	6.8	6.8	10.1	16.9	16.9
115°	33.8	27.0	13.5	10.1	6.8	10.1	6.8	3.4	10.1	23.7	23.7
117.5°	40.6	30.4	10.1	10.1	6.8	6.8	6.8	3.4	10.1	30.4	33.8
120°	50.7	37.2	13.5	6.8	6.8	6.8	6.8	3.4	13.5	33.8	37.2
122.5°	50.7	40.6	13.5	6.8	6.8	3.4	3.4	6.8	13.5	33.8	37.2
125°	47.3	37.2	13.5	6.8	6.8	3.4	3.4	3.4	16.9	33.8	37.2
127.5°	37.2	33.8	13.5	6.8	3.4	3.4	3.4	6.8	13.5	30.4	30.4
130°	30.4	27.0	10.1	6.8	3.4	3.4	3.4	3.4	13.5	23.7	27.0
132.5°	23.7	20.3	10.1	6.8	3.4	3.4	3.4	3.4	13.5	23.7	23.7
135°	16.9	16.9	6.8	3.4	3.4	3.4	3.4	3.4	10.1	16.9	20.3
137.5°	6.8	6.8	6.8	3.4	3.4	3.4	3.4	3.4	6.8	10.1	10.1
140°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	0.0	3.4	6.8	6.8
142.5°	3.4	3.4	3.4	3.4	3.4	3.4	0.0	3.4	3.4	3.4	6.8
145°	3.4	3.4	3.4	3.4	3.4	3.4	0.0	3.4	3.4	3.4	3.4
147.5°	3.4	3.4	3.4	3.4	3.4	3.4	0.0	3.4	3.4	3.4	3.4
150°	3.4	3.4	3.4	3.4	3.4	3.4	0.0	3.4	3.4	3.4	3.4
152.5°	3.4	3.4	3.4	3.4	3.4	3.4	0.0	3.4	3.4	6.8	6.8
155°	10.1	10.1	10.1	6.8	3.4	0.0	0.0	0.0	3.4	3.4	6.8
157.5°	3.4	3.4	3.4	3.4	3.4	3.4	0.0	0.0	3.4	3.4	3.4
160°	3.4	3.4	3.4	3.4	3.4	0.0	0.0	0.0	3.4	3.4	3.4
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245982

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



--- HS — SS

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



u





110°	30.4	30.4	6.8	6.8	6.8	10.1	6.8	6.8	10.1	13.5	33.8
------	------	------	-----	-----	-----	------	-----	-----	------	------	------

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





110°	30.4	23.7	13.5	13.5	10.1	10.1	10.1	6.8	6.8	6.8	6.8
------	------	------	------	------	------	------	------	-----	-----	-----	-----

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)