

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P525900

Luminaire Tested: **IFLD-S-SA3B-935-U-22**

Issue Date: 05/27/2021



Test Information

Test Method: LM-79-08
Report Number: P525900
Test Lab: INNOVATION CENTER(G2)
Issue Date: 05/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: IFLD-S-SA3B-935-U-22
Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ 22 distribution lens
Light Source: (48) 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11543.7 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type V - Short
BUG Rating: B5 - U0 - G1

Input Watts (W): 122.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

REPORT NUMBER: P525900
 CATALOG NUMBER: IFLD-S-SA3B-935-U-22

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 428.4 fc
 Type V - Short - N/A

REPORT NUMBER: P525900
CATALOG NUMBER: IFLD-S-SA3B-935-U-22

Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral - - - Horizontal Cone Through 0-Deg Vertical

REPORT NUMBER: P525900

CATALOG NUMBER: IFLD-S-SA3B-935-U-22

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	5771.9	0.0	5771.9
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	5771.9	0.0	5771.9
	% Fixture	50.0	0.0	50.0
Total	Lumens	11543.7	0.0	11543.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	7083.0	61.4
10°-20°	2818.4	24.4
20°-30°	649.9	5.6
30°-40°	246.7	2.1
40°-50°	201.4	1.7
50°-60°	193.4	1.7
60°-70°	185.3	1.6
70°-80°	122.6	1.1
80°-90°	43.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11543.7	100.0
0°-180°	11543.7	100.0

Coefficient of Utilization



REPORT NUMBER: P525900


CATALOG NUMBER: IFLD-S-SA3B-935-U-22

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	5275.6	45.7			
FM (30°-60°)	320.7	2.8			
FH (60°-80°)	153.9	1.3			G0/660
FVH (80°-90°)	21.5	0.2			G1/100
BL (0°-30°)	5275.6	45.7	B5		
BM (30°-60°)	320.7	2.8	B1/1000		
BH (60°-80°)	153.9	1.3	B1/500		G0/660
BVH (80°-90°)	21.5	0.2			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B5-U0-G1

Type V Short



REPORT NUMBER: P525900
CATALOG NUMBER: IFLD-S-SA3B-935-U-22

CANDELA DISTRIBUTION (FULL):

	0°
0°	171378.6
1°	168363.8
2°	159918.9
3°	145413.9
4°	125470.4
5°	102983.0
6°	80963.0
7°	62022.2
8°	46290.9
9°	34512.8
10°	25737.7
12.5°	14027.4
15°	9000.4
17.5°	6073.7
20°	3611.0
22.5°	2008.7
25°	1148.3
27.5°	728.3
30°	525.1
32.5°	428.5
35°	381.1
37.5°	354.0
40°	318.4
42.5°	282.9
45°	252.4
47.5°	237.1
50°	227.0
52.5°	220.2
55°	215.1
57.5°	211.7
60°	204.9
62.5°	199.9
65°	189.7
67.5°	176.1
70°	159.2
72.5°	137.2
75°	115.2
77.5°	94.8
80°	76.2
82.5°	59.3
85°	44.0
87.5°	16.9
90°	0.0

(END OF REPORT)