

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P526005

Luminaire Tested: **IFLD-L-SA7D-950-U-22**

Issue Date: 05/27/2021



Test Information

Test Method: LM-79-08
Report Number: P526005
Test Lab: INNOVATION CENTER(G2)
Issue Date: 05/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: IFLD-L-SA7D-950-U-22
Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ 22 distribution lens
Light Source: (112) 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 36012.9 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type V - Short
BUG Rating: B5 - U0 - G1

Input Watts (W): 422.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

REPORT NUMBER: P526005
 CATALOG NUMBER: IFLD-L-SA7D-950-U-22

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 594.1 fc
 Type V - Short - N/A

REPORT NUMBER: P526005
CATALOG NUMBER: IFLD-L-SA7D-950-U-22

Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral - - - Horizontal Cone Through 0-Deg Vertical

REPORT NUMBER: P526005
 CATALOG NUMBER: IFLD-L-SA7D-950-U-22


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 18006.5 | 0.0 | 18006.5 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Street Side | Lumens | 18006.5 | 0.0 | 18006.5 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Total | Lumens | 36012.9 | 0.0 | 36012.9 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 22096.8 | 61.4 |
| 10°-20° | 8792.6 | 24.4 |
| 20°-30° | 2027.4 | 5.6 |
| 30°-40° | 769.7 | 2.1 |
| 40°-50° | 628.2 | 1.7 |
| 50°-60° | 603.3 | 1.7 |
| 60°-70° | 578.0 | 1.6 |
| 70°-80° | 382.6 | 1.1 |
| 80°-90° | 134.4 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 36012.9 | 100.0 |
| 0°-180° | 36012.9 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P526005
 CATALOG NUMBER: IFLD-L-SA7D-950-U-22

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 16458.4 | 45.7 | | | |
| FM (30°-60°) | 1000.6 | 2.8 | | | |
| FH (60°-80°) | 480.3 | 1.3 | | | G0/660 |
| FVH (80°-90°) | 67.2 | 0.2 | | | G1/100 |
| BL (0°-30°) | 16458.4 | 45.7 | B5 | | |
| BM (30°-60°) | 1000.6 | 2.8 | B2/2500 | | |
| BH (60°-80°) | 480.3 | 1.3 | B1/500 | | G0/660 |
| BVH (80°-90°) | 67.2 | 0.2 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B5-U0-G1

Type V Short





REPORT NUMBER: P526005
CATALOG NUMBER: IFLD-L-SA7D-950-U-22

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|----------|
| 0° | 534647.8 |
| 1° | 525242.6 |
| 2° | 498897.2 |
| 3° | 453646.2 |
| 4° | 391428.7 |
| 5° | 321274.8 |
| 6° | 252579.3 |
| 7° | 193489.8 |
| 8° | 144413.3 |
| 9° | 107669.3 |
| 10° | 80293.6 |
| 12.5° | 43761.0 |
| 15° | 28078.5 |
| 17.5° | 18947.9 |
| 20° | 11265.2 |
| 22.5° | 6266.7 |
| 25° | 3582.5 |
| 27.5° | 2272.1 |
| 30° | 1638.0 |
| 32.5° | 1336.8 |
| 35° | 1188.9 |
| 37.5° | 1104.3 |
| 40° | 993.4 |
| 42.5° | 882.4 |
| 45° | 787.3 |
| 47.5° | 739.7 |
| 50° | 708.0 |
| 52.5° | 686.9 |
| 55° | 671.1 |
| 57.5° | 660.5 |
| 60° | 639.3 |
| 62.5° | 623.5 |
| 65° | 591.8 |
| 67.5° | 549.5 |
| 70° | 496.7 |
| 72.5° | 428.0 |
| 75° | 359.3 |
| 77.5° | 295.9 |
| 80° | 237.8 |
| 82.5° | 184.9 |
| 85° | 137.4 |
| 87.5° | 52.8 |
| 90° | 0.0 |

(END OF REPORT)