

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P525644

Luminaire Tested: **IFLD-S-SA6D-927-U-33**

Issue Date: 05/27/2021



Test Information

Test Method: LM-79-08
Report Number: P525644
Test Lab: INNOVATION CENTER(G2)
Issue Date: 05/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: IFLD-S-SA6D-927-U-33
Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ 33 distribution lens
Light Source: (96) 2700K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 29464 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type V - Short
BUG Rating: B5 - U0 - G1

Input Watts (W): 368.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

REPORT NUMBER: P525644
 CATALOG NUMBER: IFLD-S-SA6D-927-U-33

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 317.5 fc
 Type V - Short - N/A

REPORT NUMBER: P525644
CATALOG NUMBER: IFLD-S-SA6D-927-U-33

Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral - - - Horizontal Cone Through 0-Deg Vertical

REPORT NUMBER: P525644

CATALOG NUMBER: IFLD-S-SA6D-927-U-33

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	14732.0	0.0	14732.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	14732.0	0.0	14732.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	29464.0	0.0	29464.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	14775.8	50.1
10°-20°	9719.1	33.0
20°-30°	2614.2	8.9
30°-40°	649.6	2.2
40°-50°	484.7	1.6
50°-60°	445.7	1.5
60°-70°	408.8	1.4
70°-80°	264.4	0.9
80°-90°	101.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	29464.0	100.0
0°-180°	29464.0	100.0

Coefficient of Utilization




REPORT NUMBER: P525644
 CATALOG NUMBER: IFLD-S-SA6D-927-U-33

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	13554.6	46.0			
FM (30°-60°)	790.0	2.7			
FH (60°-80°)	336.6	1.1			G0/660
FVH (80°-90°)	50.8	0.2			G1/100
BL (0°-30°)	13554.6	46.0	B5		
BM (30°-60°)	790.0	2.7	B1/1000		
BH (60°-80°)	336.6	1.1	B1/500		G0/660
BVH (80°-90°)	50.8	0.2			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B5-U0-G1

Type V Short



REPORT NUMBER: P525644
CATALOG NUMBER: IFLD-S-SA6D-927-U-33

CANDELA DISTRIBUTION (FULL):

0°	
0°	198452.9
1°	197676.3
2°	195719.5
3°	192387.4
4°	187532.3
5°	180772.6
6°	171335.9
7°	158419.6
8°	142040.9
9°	122724.9
10°	103135.6
11°	82092.9
12°	62560.0
13°	46229.0
14°	34596.9
15°	27095.3
17.5°	18161.9
20°	13129.0
22.5°	8655.7
25°	5080.6
27.5°	2850.5
30°	1592.3
32.5°	1162.8
35°	984.9
37.5°	867.7
40°	763.6
42.5°	685.5
45°	616.1
47.5°	568.4
50°	529.3
52.5°	507.6
55°	494.6
57.5°	485.9
60°	472.9
62.5°	446.9
65°	416.5
67.5°	381.8
70°	338.4
72.5°	290.7
75°	247.3
77.5°	208.3
80°	173.5
82.5°	138.8
85°	104.1
87.5°	43.4



REPORT NUMBER: P525644
CATALOG NUMBER: IFLD-S-SA6D-927-U-33

CANDELA DISTRIBUTION (continued):



(END OF REPORT)