

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P525692

Luminaire Tested: **IFLD-L-SA7C-930-U-33**

Issue Date: 05/27/2021



Test Information

Test Method: LM-79-08
Report Number: P525692
Test Lab: INNOVATION CENTER(G2)
Issue Date: 05/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: IFLD-L-SA7C-930-U-33
Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ 33 distribution lens
Light Source: (112) 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 28880.7 lumens
Efficiency: N/A
Efficacy: 78.3 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type V - Short
BUG Rating: B5 - U0 - G1

Input Watts (W): 369
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

REPORT NUMBER: P525692
 CATALOG NUMBER: IFLD-L-SA7C-930-U-33

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 311.2 fc
 Type V - Short - N/A

REPORT NUMBER: P525692
CATALOG NUMBER: IFLD-L-SA7C-930-U-33

Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral - - - Horizontal Cone Through 0-Deg Vertical

REPORT NUMBER: P525692
 CATALOG NUMBER: IFLD-L-SA7C-930-U-33


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 14440.3 | 0.0 | 14440.3 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Street Side | Lumens | 14440.3 | 0.0 | 14440.3 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Total | Lumens | 28880.7 | 0.0 | 28880.7 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 14483.3 | 50.1 |
| 10°-20° | 9526.7 | 33.0 |
| 20°-30° | 2562.5 | 8.9 |
| 30°-40° | 636.7 | 2.2 |
| 40°-50° | 475.1 | 1.6 |
| 50°-60° | 436.9 | 1.5 |
| 60°-70° | 400.7 | 1.4 |
| 70°-80° | 259.2 | 0.9 |
| 80°-90° | 99.5 | 0.3 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 28880.7 | 100.0 |
| 0°-180° | 28880.7 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P525692
 CATALOG NUMBER: IFLD-L-SA7C-930-U-33

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|--------|
| | | | B | U | G |
| FL (0°-30°) | 13286.2 | 46.0 | | | |
| FM (30°-60°) | 774.4 | 2.7 | | | |
| FH (60°-80°) | 330.0 | 1.1 | | | G0/660 |
| FVH (80°-90°) | 49.8 | 0.2 | | | G1/100 |
| BL (0°-30°) | 13286.2 | 46.0 | B5 | | |
| BM (30°-60°) | 774.4 | 2.7 | B1/1000 | | |
| BH (60°-80°) | 330.0 | 1.1 | B1/500 | | G0/660 |
| BVH (80°-90°) | 49.8 | 0.2 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B5-U0-G1

Type V Short





REPORT NUMBER: P525692
CATALOG NUMBER: IFLD-L-SA7C-930-U-33

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|----------|
| 0° | 194523.8 |
| 1° | 193762.6 |
| 2° | 191844.6 |
| 3° | 188578.4 |
| 4° | 183819.5 |
| 5° | 177193.6 |
| 6° | 167943.7 |
| 7° | 155283.1 |
| 8° | 139228.7 |
| 9° | 120295.2 |
| 10° | 101093.7 |
| 11° | 80467.5 |
| 12° | 61321.4 |
| 13° | 45313.8 |
| 14° | 33912.0 |
| 15° | 26558.8 |
| 17.5° | 17802.3 |
| 20° | 12869.0 |
| 22.5° | 8484.4 |
| 25° | 4980.0 |
| 27.5° | 2794.1 |
| 30° | 1560.8 |
| 32.5° | 1139.8 |
| 35° | 965.4 |
| 37.5° | 850.6 |
| 40° | 748.5 |
| 42.5° | 671.9 |
| 45° | 603.9 |
| 47.5° | 557.1 |
| 50° | 518.8 |
| 52.5° | 497.6 |
| 55° | 484.8 |
| 57.5° | 476.3 |
| 60° | 463.6 |
| 62.5° | 438.0 |
| 65° | 408.3 |
| 67.5° | 374.2 |
| 70° | 331.7 |
| 72.5° | 284.9 |
| 75° | 242.4 |
| 77.5° | 204.1 |
| 80° | 170.1 |
| 82.5° | 136.1 |
| 85° | 102.1 |
| 87.5° | 42.5 |



REPORT NUMBER: P525692
CATALOG NUMBER: IFLD-L-SA7C-930-U-33

CANDELA DISTRIBUTION (continued):



(END OF REPORT)