

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P525697

Luminaire Tested: **IFLD-L-SA8C-930-U-33**

Issue Date: 05/27/2021

Test Information

Test Method: LM-79-08
Report Number: P525697
Test Lab: INNOVATION CENTER(G2)
Issue Date: 05/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: IFLD-L-SA8C-930-U-33
Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ 33 distribution lens
Light Source: (128) 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 32467.9 lumens
Efficiency: N/A
Efficacy: 77.2 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type V - Short
BUG Rating: B5 - U0 - G1

Input Watts (W): 420.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

REPORT NUMBER: P525697
 CATALOG NUMBER: IFLD-L-SA8C-930-U-33

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 243 fc
 Type V - Short - N/A

REPORT NUMBER: P525697
CATALOG NUMBER: IFLD-L-SA8C-930-U-33

Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral - - - Horizontal Cone Through 0-Deg Vertical

REPORT NUMBER: P525697

CATALOG NUMBER: IFLD-L-SA8C-930-U-33

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 16233.9 | 0.0 | 16233.9 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Street Side | Lumens | 16233.9 | 0.0 | 16233.9 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Total | Lumens | 32467.9 | 0.0 | 32467.9 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 16282.3 | 50.1 |
| 10°-20° | 10710.0 | 33.0 |
| 20°-30° | 2880.8 | 8.9 |
| 30°-40° | 715.8 | 2.2 |
| 40°-50° | 534.2 | 1.6 |
| 50°-60° | 491.2 | 1.5 |
| 60°-70° | 450.5 | 1.4 |
| 70°-80° | 291.4 | 0.9 |
| 80°-90° | 111.9 | 0.3 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 32467.9 | 100.0 |
| 0°-180° | 32467.9 | 100.0 |

Coefficient of Utilization



REPORT NUMBER: P525697


CATALOG NUMBER: IFLD-L-SA8C-930-U-33

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|------|-------------|---------|-----------|-------------------------|------|--------|
| | | | | B | U | G |
| FL | (0°-30°) | 14936.5 | 46.0 | | | |
| FM | (30°-60°) | 870.6 | 2.7 | | | |
| FH | (60°-80°) | 370.9 | 1.1 | | | G0/660 |
| FVH | (80°-90°) | 55.9 | 0.2 | | | G1/100 |
| BL | (0°-30°) | 14936.5 | 46.0 | B5 | | |
| BM | (30°-60°) | 870.6 | 2.7 | B1/1000 | | |
| BH | (60°-80°) | 370.9 | 1.1 | B1/500 | | G0/660 |
| BVH | (80°-90°) | 55.9 | 0.2 | | | G1/100 |
| UL | (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH | (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B5-U0-G1

Type V Short





REPORT NUMBER: P525697
CATALOG NUMBER: IFLD-L-SA8C-930-U-33

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|----------|
| 0° | 218685.7 |
| 1° | 217829.9 |
| 2° | 215673.6 |
| 3° | 212001.7 |
| 4° | 206651.7 |
| 5° | 199202.8 |
| 6° | 188804.0 |
| 7° | 174570.8 |
| 8° | 156522.3 |
| 9° | 135237.0 |
| 10° | 113650.6 |
| 11° | 90462.4 |
| 12° | 68938.1 |
| 13° | 50942.2 |
| 14° | 38124.2 |
| 15° | 29857.7 |
| 17.5° | 20013.5 |
| 20° | 14467.5 |
| 22.5° | 9538.2 |
| 25° | 5598.6 |
| 27.5° | 3141.2 |
| 30° | 1754.6 |
| 32.5° | 1281.3 |
| 35° | 1085.3 |
| 37.5° | 956.2 |
| 40° | 841.5 |
| 42.5° | 755.4 |
| 45° | 678.9 |
| 47.5° | 626.3 |
| 50° | 583.3 |
| 52.5° | 559.4 |
| 55° | 545.0 |
| 57.5° | 535.5 |
| 60° | 521.1 |
| 62.5° | 492.4 |
| 65° | 459.0 |
| 67.5° | 420.7 |
| 70° | 372.9 |
| 72.5° | 320.3 |
| 75° | 272.5 |
| 77.5° | 229.5 |
| 80° | 191.2 |
| 82.5° | 153.0 |
| 85° | 114.7 |
| 87.5° | 47.8 |



REPORT NUMBER: P525697
CATALOG NUMBER: IFLD-L-SA8C-930-U-33

CANDELA DISTRIBUTION (continued):



(END OF REPORT)