

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P622183

Luminaire Tested: **IFLD-S-SA6A-735-U-66**

Issue Date: 09/20/2022

Test Information

Test Method: LM-79-2019
Report Number: P622183
Test Lab: INNOVATION CENTER(G2)
Issue Date: 09/20/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: IFLD-S-SA6A-735-U-66
Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ Nema 6 distribution lens
Light Source: (96) 3500K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


| | | | |
|-------------------|--------------------------------------|----------------------|-------------------|
| Lumens per Lamp: | N/A | NEMA Type: | 6H x 6V |
| Luminaire Lumens: | 28062.8 lumens | Max Intensity: | 27057.2 candela |
| Efficiency: | N/A | Max Intensity Angle: | 0°H x 0°V |
| Efficacy: | 148.0 lumens/watt | | |
| Luminous Opening: | Rectangular (W 1.5' x L: 1' x H: 0') | | |
| Beam Angle (50%): | 54.2°H x 54.7°V | Field Angle (10%): | 101.7°H x 101.8°V |
| Beam Lumens: | 13492.7 lumens | Field Lumens: | 24627.9 lumens |
| Beam Efficiency: | 48.1% | Field Efficiency: | 87.8% |

Input Watts (W): 189.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P622183
CATALOG NUMBER: IFLD-S-SA6A-735-U-66


Iso-Candela Plot






REPORT NUMBER: P622183
 CATALOG NUMBER: IFLD-S-SA6A-735-U-66

Lumen Table



REPORT NUMBER: P622183
CATALOG NUMBER: IFLD-S-SA6A-735-U-66


Luminous Intensity Polar Plot



— Vertical Distribution Through 0-Deg - - - Horizontal Distribution Through 0-Deg

REPORT NUMBER: P622183
 CATALOG NUMBER: IFLD-S-SA6A-735-U-66

Luminous Intensity Plot



Beam:
 H Angle: 54.2°
 V Angle: 54.7°
 Lumens: 13492.7
 Efficiency: 48.1%

Field:
 H Angle: 101.7°
 V Angle: 101.8°
 Lumens: 24627.9
 Efficiency: 87.8%

Spill:
 Lumens: 3434.9
 Efficiency: 12.2%

- Vertical Distribution through 0-Deg
- - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P622183
 CATALOG NUMBER: IFLD-S-SA6A-735-U-66

FIELD
 BEAM

CANDELA DISTRIBUTION:

| | -90° | -87.5° | -85° | -82.5° | -80° | -77.5° | -75° | -72.5° | -70° | -67.5° | -65° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 90° | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| 87.5° | 0 | 3 | 6 | 12 | 17 | 23 | 29 | 35 | 38 | 40 | 46 |
| 85° | 0 | 6 | 12 | 20 | 32 | 46 | 61 | 69 | 75 | 84 | 89 |
| 82.5° | 0 | 9 | 20 | 32 | 49 | 66 | 89 | 101 | 112 | 124 | 133 |
| 80° | 0 | 12 | 26 | 43 | 63 | 89 | 118 | 133 | 147 | 161 | 173 |
| 77.5° | 0 | 14 | 32 | 52 | 81 | 110 | 144 | 164 | 182 | 199 | 216 |
| 75° | 0 | 17 | 38 | 63 | 95 | 127 | 167 | 193 | 216 | 239 | 265 |
| 72.5° | 0 | 20 | 43 | 72 | 107 | 144 | 190 | 222 | 248 | 280 | 314 |
| 70° | 0 | 23 | 49 | 84 | 118 | 161 | 213 | 248 | 280 | 317 | 346 |
| 67.5° | 0 | 26 | 55 | 89 | 130 | 176 | 231 | 274 | 309 | 343 | 375 |
| 65° | 0 | 26 | 61 | 95 | 138 | 190 | 245 | 297 | 334 | 369 | 407 |
| 62.5° | 0 | 29 | 66 | 101 | 147 | 202 | 260 | 317 | 358 | 395 | 438 |
| 60° | 0 | 32 | 69 | 107 | 159 | 213 | 277 | 337 | 378 | 424 | 470 |
| 57.5° | 0 | 35 | 72 | 112 | 164 | 222 | 288 | 355 | 404 | 453 | 502 |
| 55° | 0 | 38 | 78 | 118 | 170 | 234 | 300 | 372 | 427 | 479 | 533 |
| 52.5° | 0 | 38 | 81 | 121 | 179 | 242 | 311 | 383 | 450 | 507 | 571 |
| 50° | 0 | 40 | 84 | 124 | 185 | 251 | 320 | 398 | 473 | 536 | 603 |
| 47.5° | 0 | 43 | 87 | 127 | 187 | 257 | 332 | 412 | 499 | 565 | 637 |
| 45° | 0 | 43 | 89 | 130 | 193 | 265 | 340 | 421 | 516 | 594 | 669 |
| 42.5° | 0 | 46 | 89 | 133 | 196 | 271 | 349 | 435 | 531 | 623 | 704 |
| 40° | 0 | 49 | 92 | 138 | 202 | 274 | 358 | 447 | 548 | 652 | 735 |
| 37.5° | 0 | 49 | 95 | 141 | 205 | 280 | 363 | 458 | 565 | 672 | 764 |
| 35° | 0 | 52 | 98 | 144 | 208 | 283 | 366 | 470 | 580 | 692 | 796 |
| 32.5° | 0 | 52 | 98 | 150 | 211 | 288 | 372 | 479 | 597 | 715 | 825 |
| 30° | 0 | 52 | 101 | 153 | 211 | 288 | 381 | 487 | 611 | 738 | 853 |
| 27.5° | 0 | 55 | 101 | 153 | 216 | 291 | 386 | 499 | 626 | 764 | 882 |
| 25° | 0 | 55 | 104 | 156 | 219 | 291 | 389 | 507 | 643 | 787 | 908 |
| 22.5° | 0 | 55 | 104 | 159 | 222 | 294 | 392 | 516 | 660 | 807 | 937 |
| 20° | 0 | 58 | 107 | 161 | 225 | 297 | 395 | 525 | 678 | 825 | 960 |
| 17.5° | 0 | 58 | 107 | 161 | 228 | 303 | 398 | 531 | 692 | 842 | 980 |
| 15° | 0 | 61 | 107 | 161 | 228 | 306 | 404 | 533 | 706 | 856 | 1000 |
| 12.5° | 0 | 61 | 107 | 164 | 228 | 306 | 407 | 539 | 721 | 871 | 1015 |
| 10° | 0 | 58 | 110 | 164 | 228 | 309 | 409 | 542 | 729 | 879 | 1029 |
| 7.5° | 0 | 58 | 110 | 164 | 231 | 309 | 409 | 542 | 738 | 888 | 1038 |
| 5° | 0 | 58 | 107 | 164 | 228 | 311 | 409 | 545 | 750 | 897 | 1047 |
| 2.5° | 0 | 58 | 107 | 161 | 228 | 311 | 404 | 539 | 747 | 897 | 1052 |
| 0° | 0 | 58 | 107 | 161 | 225 | 309 | 401 | 533 | 744 | 894 | 1052 |
| -2.5° | 0 | 58 | 107 | 161 | 228 | 311 | 404 | 539 | 747 | 897 | 1052 |
| -5° | 0 | 58 | 107 | 164 | 228 | 311 | 409 | 545 | 750 | 897 | 1047 |
| -7.5° | 0 | 58 | 110 | 164 | 231 | 309 | 409 | 542 | 738 | 888 | 1038 |
| -10° | 0 | 58 | 110 | 164 | 228 | 309 | 409 | 542 | 729 | 879 | 1029 |
| -12.5° | 0 | 61 | 107 | 164 | 228 | 306 | 407 | 539 | 721 | 871 | 1015 |
| -15° | 0 | 61 | 107 | 161 | 228 | 306 | 404 | 533 | 706 | 856 | 1000 |
| -17.5° | 0 | 58 | 107 | 161 | 228 | 303 | 398 | 531 | 692 | 842 | 980 |
| -20° | 0 | 58 | 107 | 161 | 225 | 297 | 395 | 525 | 678 | 825 | 960 |



REPORT NUMBER: P622183
 CATALOG NUMBER: IFLD-S-SA6A-735-U-66

CANDELA DISTRIBUTION (continued):

| | -90° | -87.5° | -85° | -82.5° | -80° | -77.5° | -75° | -72.5° | -70° | -67.5° | -65° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| -22.5° | 0 | 55 | 104 | 159 | 222 | 294 | 392 | 516 | 660 | 807 | 937 |
| -25° | 0 | 55 | 104 | 156 | 219 | 291 | 389 | 507 | 643 | 787 | 908 |
| -27.5° | 0 | 55 | 101 | 153 | 216 | 291 | 386 | 499 | 626 | 764 | 882 |
| -30° | 0 | 52 | 101 | 153 | 211 | 288 | 381 | 487 | 611 | 738 | 853 |
| -32.5° | 0 | 52 | 98 | 150 | 211 | 288 | 372 | 479 | 597 | 715 | 825 |
| -35° | 0 | 52 | 98 | 144 | 208 | 283 | 366 | 470 | 580 | 692 | 796 |
| -37.5° | 0 | 49 | 95 | 141 | 205 | 280 | 363 | 458 | 565 | 672 | 764 |
| -40° | 0 | 49 | 92 | 138 | 202 | 274 | 358 | 447 | 548 | 652 | 735 |
| -42.5° | 0 | 46 | 89 | 133 | 196 | 271 | 349 | 435 | 531 | 623 | 704 |
| -45° | 0 | 43 | 89 | 130 | 193 | 265 | 340 | 421 | 516 | 594 | 669 |
| -47.5° | 0 | 43 | 87 | 127 | 187 | 257 | 332 | 412 | 499 | 565 | 637 |
| -50° | 0 | 40 | 84 | 124 | 185 | 251 | 320 | 398 | 473 | 536 | 603 |
| -52.5° | 0 | 38 | 81 | 121 | 179 | 242 | 311 | 383 | 450 | 507 | 571 |
| -55° | 0 | 38 | 78 | 118 | 170 | 234 | 300 | 372 | 427 | 479 | 533 |
| -57.5° | 0 | 35 | 72 | 112 | 164 | 222 | 288 | 355 | 404 | 453 | 502 |
| -60° | 0 | 32 | 69 | 107 | 159 | 213 | 277 | 337 | 378 | 424 | 470 |
| -62.5° | 0 | 29 | 66 | 101 | 147 | 202 | 260 | 317 | 358 | 395 | 438 |
| -65° | 0 | 26 | 61 | 95 | 138 | 190 | 245 | 297 | 334 | 369 | 407 |
| -67.5° | 0 | 26 | 55 | 89 | 130 | 176 | 231 | 274 | 309 | 343 | 375 |
| -70° | 0 | 23 | 49 | 84 | 118 | 161 | 213 | 248 | 280 | 317 | 346 |
| -72.5° | 0 | 20 | 43 | 72 | 107 | 144 | 190 | 222 | 248 | 280 | 314 |
| -75° | 0 | 17 | 38 | 63 | 95 | 127 | 167 | 193 | 216 | 239 | 265 |
| -77.5° | 0 | 14 | 32 | 52 | 81 | 110 | 144 | 164 | 182 | 199 | 216 |
| -80° | 0 | 12 | 26 | 43 | 63 | 89 | 118 | 133 | 147 | 161 | 173 |
| -82.5° | 0 | 9 | 20 | 32 | 49 | 66 | 89 | 101 | 112 | 124 | 133 |
| -85° | 0 | 6 | 12 | 20 | 32 | 46 | 61 | 69 | 75 | 84 | 89 |
| -87.5° | 0 | 3 | 6 | 12 | 17 | 23 | 29 | 35 | 38 | 40 | 46 |
| -90° | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |



REPORT NUMBER: P622183
 CATALOG NUMBER: IFLD-S-SA6A-735-U-66

CANDELA DISTRIBUTION (continued):

| | -62.5° | -60° | -57.5° | -55° | -52.5° | -50° | -47.5° | -45° | -42.5° | -40° | -37.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 90° | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| 87.5° | 49 | 52 | 55 | 55 | 55 | 52 | 49 | 46 | 52 | 58 | 63 |
| 85° | 95 | 104 | 107 | 112 | 110 | 104 | 101 | 95 | 107 | 118 | 133 |
| 82.5° | 141 | 150 | 156 | 161 | 161 | 156 | 150 | 141 | 159 | 176 | 196 |
| 80° | 185 | 196 | 208 | 216 | 216 | 208 | 199 | 187 | 208 | 234 | 260 |
| 77.5° | 236 | 251 | 262 | 274 | 271 | 268 | 262 | 257 | 277 | 303 | 329 |
| 75° | 288 | 309 | 317 | 329 | 334 | 332 | 332 | 337 | 360 | 392 | 421 |
| 72.5° | 334 | 349 | 366 | 386 | 395 | 401 | 415 | 433 | 456 | 482 | 505 |
| 70° | 372 | 389 | 412 | 433 | 450 | 467 | 487 | 510 | 533 | 559 | 582 |
| 67.5° | 407 | 433 | 456 | 482 | 505 | 531 | 556 | 582 | 608 | 637 | 666 |
| 65° | 444 | 473 | 502 | 531 | 562 | 594 | 626 | 654 | 686 | 724 | 755 |
| 62.5° | 482 | 513 | 548 | 582 | 620 | 657 | 695 | 732 | 776 | 816 | 856 |
| 60° | 516 | 556 | 597 | 640 | 683 | 727 | 767 | 816 | 868 | 914 | 966 |
| 57.5° | 551 | 600 | 646 | 695 | 744 | 793 | 851 | 905 | 966 | 1026 | 1084 |
| 55° | 588 | 646 | 698 | 753 | 807 | 871 | 934 | 1003 | 1070 | 1147 | 1220 |
| 52.5° | 629 | 689 | 750 | 810 | 879 | 949 | 1024 | 1104 | 1191 | 1280 | 1369 |
| 50° | 669 | 735 | 802 | 874 | 951 | 1032 | 1122 | 1217 | 1320 | 1424 | 1534 |
| 47.5° | 706 | 778 | 859 | 937 | 1026 | 1122 | 1225 | 1341 | 1456 | 1586 | 1724 |
| 45° | 747 | 825 | 911 | 1006 | 1104 | 1217 | 1341 | 1468 | 1615 | 1762 | 1923 |
| 42.5° | 787 | 871 | 969 | 1070 | 1191 | 1318 | 1453 | 1615 | 1779 | 1961 | 2157 |
| 40° | 822 | 917 | 1026 | 1147 | 1277 | 1418 | 1586 | 1762 | 1963 | 2180 | 2422 |
| 37.5° | 862 | 966 | 1084 | 1217 | 1367 | 1531 | 1724 | 1929 | 2162 | 2425 | 2716 |
| 35° | 900 | 1015 | 1145 | 1289 | 1456 | 1646 | 1862 | 2102 | 2373 | 2690 | 3045 |
| 32.5° | 937 | 1064 | 1202 | 1361 | 1545 | 1762 | 2007 | 2289 | 2609 | 2972 | 3416 |
| 30° | 975 | 1107 | 1257 | 1430 | 1638 | 1883 | 2165 | 2479 | 2848 | 3307 | 3834 |
| 27.5° | 1009 | 1153 | 1315 | 1505 | 1727 | 1995 | 2315 | 2690 | 3125 | 3641 | 4258 |
| 25° | 1044 | 1194 | 1369 | 1574 | 1822 | 2116 | 2465 | 2877 | 3399 | 4010 | 4743 |
| 22.5° | 1075 | 1234 | 1418 | 1640 | 1909 | 2234 | 2626 | 3096 | 3670 | 4351 | 5213 |
| 20° | 1107 | 1274 | 1470 | 1704 | 1984 | 2341 | 2774 | 3298 | 3950 | 4751 | 5708 |
| 17.5° | 1133 | 1312 | 1519 | 1770 | 2076 | 2451 | 2909 | 3500 | 4204 | 5120 | 6187 |
| 15° | 1159 | 1344 | 1563 | 1828 | 2157 | 2560 | 3056 | 3676 | 4472 | 5469 | 6602 |
| 12.5° | 1179 | 1369 | 1600 | 1880 | 2226 | 2652 | 3183 | 3855 | 4731 | 5798 | 6963 |
| 10° | 1194 | 1393 | 1629 | 1920 | 2283 | 2727 | 3287 | 3999 | 4942 | 6066 | 7262 |
| 7.5° | 1208 | 1410 | 1652 | 1952 | 2327 | 2785 | 3367 | 4111 | 5103 | 6274 | 7493 |
| 5° | 1220 | 1424 | 1669 | 1975 | 2355 | 2828 | 3428 | 4183 | 5218 | 6421 | 7657 |
| 2.5° | 1228 | 1436 | 1684 | 1995 | 2379 | 2874 | 3483 | 4261 | 5328 | 6545 | 7804 |
| 0° | 1228 | 1439 | 1684 | 1995 | 2376 | 2883 | 3491 | 4267 | 5342 | 6542 | 7825 |
| -2.5° | 1228 | 1436 | 1684 | 1995 | 2379 | 2874 | 3483 | 4261 | 5328 | 6545 | 7804 |
| -5° | 1220 | 1424 | 1669 | 1975 | 2355 | 2828 | 3428 | 4183 | 5218 | 6421 | 7657 |
| -7.5° | 1208 | 1410 | 1652 | 1952 | 2327 | 2785 | 3367 | 4111 | 5103 | 6274 | 7493 |
| -10° | 1194 | 1393 | 1629 | 1920 | 2283 | 2727 | 3287 | 3999 | 4942 | 6066 | 7262 |
| -12.5° | 1179 | 1369 | 1600 | 1880 | 2226 | 2652 | 3183 | 3855 | 4731 | 5798 | 6963 |
| -15° | 1159 | 1344 | 1563 | 1828 | 2157 | 2560 | 3056 | 3676 | 4472 | 5469 | 6602 |
| -17.5° | 1133 | 1312 | 1519 | 1770 | 2076 | 2451 | 2909 | 3500 | 4204 | 5120 | 6187 |
| -20° | 1107 | 1274 | 1470 | 1704 | 1984 | 2341 | 2774 | 3298 | 3950 | 4751 | 5708 |



REPORT NUMBER: P622183
 CATALOG NUMBER: IFLD-S-SA6A-735-U-66

CANDELA DISTRIBUTION (continued):

| | -62.5° | -60° | -57.5° | -55° | -52.5° | -50° | -47.5° | -45° | -42.5° | -40° | -37.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| -22.5° | 1075 | 1234 | 1418 | 1640 | 1909 | 2234 | 2626 | 3096 | 3670 | 4351 | 5213 |
| -25° | 1044 | 1194 | 1369 | 1574 | 1822 | 2116 | 2465 | 2877 | 3399 | 4010 | 4743 |
| -27.5° | 1009 | 1153 | 1315 | 1505 | 1727 | 1995 | 2315 | 2690 | 3125 | 3641 | 4258 |
| -30° | 975 | 1107 | 1257 | 1430 | 1638 | 1883 | 2165 | 2479 | 2848 | 3307 | 3834 |
| -32.5° | 937 | 1064 | 1202 | 1361 | 1545 | 1762 | 2007 | 2289 | 2609 | 2972 | 3416 |
| -35° | 900 | 1015 | 1145 | 1289 | 1456 | 1646 | 1862 | 2102 | 2373 | 2690 | 3045 |
| -37.5° | 862 | 966 | 1084 | 1217 | 1367 | 1531 | 1724 | 1929 | 2162 | 2425 | 2716 |
| -40° | 822 | 917 | 1026 | 1147 | 1277 | 1418 | 1586 | 1762 | 1963 | 2180 | 2422 |
| -42.5° | 787 | 871 | 969 | 1070 | 1191 | 1318 | 1453 | 1615 | 1779 | 1961 | 2157 |
| -45° | 747 | 825 | 911 | 1006 | 1104 | 1217 | 1341 | 1468 | 1615 | 1762 | 1923 |
| -47.5° | 706 | 778 | 859 | 937 | 1026 | 1122 | 1225 | 1341 | 1456 | 1586 | 1724 |
| -50° | 669 | 735 | 802 | 874 | 951 | 1032 | 1122 | 1217 | 1320 | 1424 | 1534 |
| -52.5° | 629 | 689 | 750 | 810 | 879 | 949 | 1024 | 1104 | 1191 | 1280 | 1369 |
| -55° | 588 | 646 | 698 | 753 | 807 | 871 | 934 | 1003 | 1070 | 1147 | 1220 |
| -57.5° | 551 | 600 | 646 | 695 | 744 | 793 | 851 | 905 | 966 | 1026 | 1084 |
| -60° | 516 | 556 | 597 | 640 | 683 | 727 | 767 | 816 | 868 | 914 | 966 |
| -62.5° | 482 | 513 | 548 | 582 | 620 | 657 | 695 | 732 | 776 | 816 | 856 |
| -65° | 444 | 473 | 502 | 531 | 562 | 594 | 626 | 654 | 686 | 724 | 755 |
| -67.5° | 407 | 433 | 456 | 482 | 505 | 531 | 556 | 582 | 608 | 637 | 666 |
| -70° | 372 | 389 | 412 | 433 | 450 | 467 | 487 | 510 | 533 | 559 | 582 |
| -72.5° | 334 | 349 | 366 | 386 | 395 | 401 | 415 | 433 | 456 | 482 | 505 |
| -75° | 288 | 309 | 317 | 329 | 334 | 332 | 332 | 337 | 360 | 392 | 421 |
| -77.5° | 236 | 251 | 262 | 274 | 271 | 268 | 262 | 257 | 277 | 303 | 329 |
| -80° | 185 | 196 | 208 | 216 | 216 | 208 | 199 | 187 | 208 | 234 | 260 |
| -82.5° | 141 | 150 | 156 | 161 | 161 | 156 | 150 | 141 | 159 | 176 | 196 |
| -85° | 95 | 104 | 107 | 112 | 110 | 104 | 101 | 95 | 107 | 118 | 133 |
| -87.5° | 49 | 52 | 55 | 55 | 55 | 52 | 49 | 46 | 52 | 58 | 63 |
| -90° | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |



REPORT NUMBER: P622183
 CATALOG NUMBER: IFLD-S-SA6A-735-U-66

CANDELA DISTRIBUTION (continued):

| | -35° | -32.5° | -30° | -27.5° | -25° | -22.5° | -20° | -17.5° | -15° | -12.5° | -10° |
|--------|------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 90° | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| 87.5° | 72 | 72 | 72 | 72 | 69 | 72 | 72 | 75 | 78 | 69 | 61 |
| 85° | 144 | 147 | 147 | 147 | 147 | 147 | 147 | 147 | 147 | 133 | 118 |
| 82.5° | 216 | 225 | 231 | 239 | 245 | 245 | 242 | 239 | 234 | 211 | 185 |
| 80° | 285 | 300 | 309 | 317 | 326 | 323 | 320 | 314 | 311 | 283 | 254 |
| 77.5° | 355 | 372 | 383 | 392 | 401 | 404 | 401 | 401 | 398 | 372 | 340 |
| 75° | 444 | 458 | 470 | 482 | 493 | 499 | 502 | 502 | 502 | 479 | 450 |
| 72.5° | 525 | 542 | 559 | 577 | 591 | 600 | 608 | 614 | 620 | 608 | 591 |
| 70° | 608 | 629 | 649 | 669 | 689 | 704 | 715 | 727 | 732 | 735 | 735 |
| 67.5° | 695 | 721 | 747 | 773 | 796 | 816 | 830 | 845 | 856 | 868 | 874 |
| 65° | 790 | 825 | 856 | 885 | 911 | 937 | 957 | 977 | 995 | 1009 | 1018 |
| 62.5° | 897 | 937 | 975 | 1012 | 1041 | 1073 | 1104 | 1133 | 1156 | 1176 | 1191 |
| 60° | 1015 | 1064 | 1110 | 1156 | 1202 | 1240 | 1280 | 1315 | 1344 | 1369 | 1393 |
| 57.5° | 1147 | 1208 | 1266 | 1326 | 1378 | 1427 | 1476 | 1525 | 1568 | 1603 | 1632 |
| 55° | 1295 | 1369 | 1444 | 1517 | 1589 | 1655 | 1718 | 1782 | 1839 | 1886 | 1926 |
| 52.5° | 1465 | 1554 | 1649 | 1739 | 1837 | 1923 | 2004 | 2090 | 2168 | 2237 | 2295 |
| 50° | 1646 | 1762 | 1886 | 2001 | 2128 | 2249 | 2358 | 2468 | 2577 | 2673 | 2750 |
| 47.5° | 1860 | 1998 | 2159 | 2318 | 2474 | 2638 | 2791 | 2935 | 3085 | 3212 | 3318 |
| 45° | 2090 | 2283 | 2474 | 2687 | 2883 | 3105 | 3316 | 3526 | 3711 | 3895 | 4051 |
| 42.5° | 2364 | 2606 | 2848 | 3122 | 3390 | 3670 | 3967 | 4232 | 4509 | 4780 | 5005 |
| 40° | 2690 | 2975 | 3310 | 3638 | 4010 | 4362 | 4783 | 5155 | 5507 | 5850 | 6141 |
| 37.5° | 3047 | 3425 | 3837 | 4255 | 4760 | 5256 | 5749 | 6216 | 6634 | 7017 | 7323 |
| 35° | 3460 | 3935 | 4425 | 5034 | 5633 | 6239 | 6804 | 7334 | 7810 | 8199 | 8522 |
| 32.5° | 3932 | 4495 | 5172 | 5879 | 6573 | 7245 | 7920 | 8444 | 8940 | 9384 | 9765 |
| 30° | 4434 | 5166 | 5956 | 6746 | 7505 | 8234 | 8914 | 9546 | 10122 | 10621 | 11048 |
| 27.5° | 5022 | 5870 | 6749 | 7597 | 8410 | 9197 | 9970 | 10690 | 11322 | 11846 | 12377 |
| 25° | 5605 | 6576 | 7516 | 8413 | 9292 | 10171 | 11022 | 11832 | 12570 | 13213 | 13787 |
| 22.5° | 6219 | 7234 | 8225 | 9177 | 10174 | 11131 | 12063 | 12985 | 13833 | 14574 | 15220 |
| 20° | 6787 | 7876 | 8888 | 9949 | 11031 | 12068 | 13115 | 14112 | 15058 | 15952 | 16687 |
| 17.5° | 7294 | 8404 | 9508 | 10627 | 11806 | 12982 | 14118 | 15199 | 16278 | 17318 | 18235 |
| 15° | 7747 | 8911 | 10045 | 11264 | 12535 | 13801 | 15067 | 16257 | 17471 | 18624 | 19651 |
| 12.5° | 8147 | 9350 | 10555 | 11852 | 13181 | 14499 | 15886 | 17269 | 18616 | 19858 | 20971 |
| 10° | 8479 | 9727 | 11019 | 12362 | 13743 | 15136 | 16629 | 18166 | 19608 | 20928 | 22139 |
| 7.5° | 8730 | 10013 | 11362 | 12757 | 14213 | 15704 | 17264 | 18829 | 20354 | 21773 | 23041 |
| 5° | 8909 | 10203 | 11590 | 13014 | 14531 | 16087 | 17751 | 19420 | 20977 | 22444 | 23742 |
| 2.5° | 9070 | 10373 | 11786 | 13155 | 14701 | 16315 | 17981 | 19711 | 21303 | 22811 | 24255 |
| 0° | 9113 | 10442 | 11869 | 13276 | 14778 | 16399 | 18097 | 19786 | 21418 | 23056 | 24414 |
| -2.5° | 9070 | 10373 | 11786 | 13155 | 14701 | 16315 | 17981 | 19711 | 21303 | 22811 | 24255 |
| -5° | 8909 | 10203 | 11590 | 13014 | 14531 | 16087 | 17751 | 19420 | 20977 | 22444 | 23742 |
| -7.5° | 8730 | 10013 | 11362 | 12757 | 14213 | 15704 | 17264 | 18829 | 20354 | 21773 | 23041 |
| -10° | 8479 | 9727 | 11019 | 12362 | 13743 | 15136 | 16629 | 18166 | 19608 | 20928 | 22139 |
| -12.5° | 8147 | 9350 | 10555 | 11852 | 13181 | 14499 | 15886 | 17269 | 18616 | 19858 | 20971 |
| -15° | 7747 | 8911 | 10045 | 11264 | 12535 | 13801 | 15067 | 16257 | 17471 | 18624 | 19651 |
| -17.5° | 7294 | 8404 | 9508 | 10627 | 11806 | 12982 | 14118 | 15199 | 16278 | 17318 | 18235 |
| -20° | 6787 | 7876 | 8888 | 9949 | 11031 | 12068 | 13115 | 14112 | 15058 | 15952 | 16687 |



REPORT NUMBER: P622183
 CATALOG NUMBER: IFLD-S-SA6A-735-U-66

CANDELA DISTRIBUTION (continued):

| | -35° | -32.5° | -30° | -27.5° | -25° | -22.5° | -20° | -17.5° | -15° | -12.5° | -10° |
|--------|------|--------|------|--------|-------|--------|-------|--------|-------|--------|-------|
| -22.5° | 6219 | 7234 | 8225 | 9177 | 10174 | 11131 | 12063 | 12985 | 13833 | 14574 | 15220 |
| -25° | 5605 | 6576 | 7516 | 8413 | 9292 | 10171 | 11022 | 11832 | 12570 | 13213 | 13787 |
| -27.5° | 5022 | 5870 | 6749 | 7597 | 8410 | 9197 | 9970 | 10690 | 11322 | 11846 | 12377 |
| -30° | 4434 | 5166 | 5956 | 6746 | 7505 | 8234 | 8914 | 9546 | 10122 | 10621 | 11048 |
| -32.5° | 3932 | 4495 | 5172 | 5879 | 6573 | 7245 | 7920 | 8444 | 8940 | 9384 | 9765 |
| -35° | 3460 | 3935 | 4425 | 5034 | 5633 | 6239 | 6804 | 7334 | 7810 | 8199 | 8522 |
| -37.5° | 3047 | 3425 | 3837 | 4255 | 4760 | 5256 | 5749 | 6216 | 6634 | 7017 | 7323 |
| -40° | 2690 | 2975 | 3310 | 3638 | 4010 | 4362 | 4783 | 5155 | 5507 | 5850 | 6141 |
| -42.5° | 2364 | 2606 | 2848 | 3122 | 3390 | 3670 | 3967 | 4232 | 4509 | 4780 | 5005 |
| -45° | 2090 | 2283 | 2474 | 2687 | 2883 | 3105 | 3316 | 3526 | 3711 | 3895 | 4051 |
| -47.5° | 1860 | 1998 | 2159 | 2318 | 2474 | 2638 | 2791 | 2935 | 3085 | 3212 | 3318 |
| -50° | 1646 | 1762 | 1886 | 2001 | 2128 | 2249 | 2358 | 2468 | 2577 | 2673 | 2750 |
| -52.5° | 1465 | 1554 | 1649 | 1739 | 1837 | 1923 | 2004 | 2090 | 2168 | 2237 | 2295 |
| -55° | 1295 | 1369 | 1444 | 1517 | 1589 | 1655 | 1718 | 1782 | 1839 | 1886 | 1926 |
| -57.5° | 1147 | 1208 | 1266 | 1326 | 1378 | 1427 | 1476 | 1525 | 1568 | 1603 | 1632 |
| -60° | 1015 | 1064 | 1110 | 1156 | 1202 | 1240 | 1280 | 1315 | 1344 | 1369 | 1393 |
| -62.5° | 897 | 937 | 975 | 1012 | 1041 | 1073 | 1104 | 1133 | 1156 | 1176 | 1191 |
| -65° | 790 | 825 | 856 | 885 | 911 | 937 | 957 | 977 | 995 | 1009 | 1018 |
| -67.5° | 695 | 721 | 747 | 773 | 796 | 816 | 830 | 845 | 856 | 868 | 874 |
| -70° | 608 | 629 | 649 | 669 | 689 | 704 | 715 | 727 | 732 | 735 | 735 |
| -72.5° | 525 | 542 | 559 | 577 | 591 | 600 | 608 | 614 | 620 | 608 | 591 |
| -75° | 444 | 458 | 470 | 482 | 493 | 499 | 502 | 502 | 502 | 479 | 450 |
| -77.5° | 355 | 372 | 383 | 392 | 401 | 404 | 401 | 401 | 398 | 372 | 340 |
| -80° | 285 | 300 | 309 | 317 | 326 | 323 | 320 | 314 | 311 | 283 | 254 |
| -82.5° | 216 | 225 | 231 | 239 | 245 | 245 | 242 | 239 | 234 | 211 | 185 |
| -85° | 144 | 147 | 147 | 147 | 147 | 147 | 147 | 147 | 147 | 133 | 118 |
| -87.5° | 72 | 72 | 72 | 72 | 69 | 72 | 72 | 75 | 78 | 69 | 61 |
| -90° | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |



REPORT NUMBER: P622183
 CATALOG NUMBER: IFLD-S-SA6A-735-U-66

CANDELA DISTRIBUTION (continued):

| | -7.5° | -5° | -2.5° | 0° | 2.5° | 5° | 7.5° | 10° | 12.5° | 15° | 17.5° |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 90° | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| 87.5° | 49 | 40 | 38 | 32 | 38 | 40 | 49 | 61 | 69 | 78 | 75 |
| 85° | 101 | 84 | 81 | 75 | 81 | 84 | 101 | 118 | 133 | 147 | 147 |
| 82.5° | 161 | 133 | 127 | 121 | 127 | 133 | 161 | 185 | 211 | 234 | 239 |
| 80° | 228 | 193 | 187 | 182 | 187 | 193 | 228 | 254 | 283 | 311 | 314 |
| 77.5° | 309 | 277 | 265 | 257 | 265 | 277 | 309 | 340 | 372 | 398 | 401 |
| 75° | 418 | 386 | 378 | 369 | 378 | 386 | 418 | 450 | 479 | 502 | 502 |
| 72.5° | 571 | 556 | 533 | 513 | 533 | 556 | 571 | 591 | 608 | 620 | 614 |
| 70° | 738 | 744 | 738 | 729 | 738 | 744 | 738 | 735 | 735 | 732 | 727 |
| 67.5° | 876 | 882 | 882 | 885 | 882 | 882 | 876 | 874 | 868 | 856 | 845 |
| 65° | 1026 | 1029 | 1038 | 1041 | 1038 | 1029 | 1026 | 1018 | 1009 | 995 | 977 |
| 62.5° | 1199 | 1208 | 1214 | 1214 | 1214 | 1208 | 1199 | 1191 | 1176 | 1156 | 1133 |
| 60° | 1407 | 1418 | 1433 | 1436 | 1433 | 1418 | 1407 | 1393 | 1369 | 1344 | 1315 |
| 57.5° | 1655 | 1669 | 1690 | 1695 | 1690 | 1669 | 1655 | 1632 | 1603 | 1568 | 1525 |
| 55° | 1955 | 1975 | 1986 | 1981 | 1986 | 1975 | 1955 | 1926 | 1886 | 1839 | 1782 |
| 52.5° | 2344 | 2379 | 2402 | 2390 | 2402 | 2379 | 2344 | 2295 | 2237 | 2168 | 2090 |
| 50° | 2814 | 2857 | 2886 | 2877 | 2886 | 2857 | 2814 | 2750 | 2673 | 2577 | 2468 |
| 47.5° | 3402 | 3463 | 3512 | 3514 | 3512 | 3463 | 3402 | 3318 | 3212 | 3085 | 2935 |
| 45° | 4175 | 4264 | 4330 | 4319 | 4330 | 4264 | 4175 | 4051 | 3895 | 3711 | 3526 |
| 42.5° | 5178 | 5302 | 5400 | 5391 | 5400 | 5302 | 5178 | 5005 | 4780 | 4509 | 4232 |
| 40° | 6357 | 6510 | 6640 | 6674 | 6640 | 6510 | 6357 | 6141 | 5850 | 5507 | 5155 |
| 37.5° | 7571 | 7767 | 7931 | 7914 | 7931 | 7767 | 7571 | 7323 | 7017 | 6634 | 6216 |
| 35° | 8790 | 8995 | 9157 | 9171 | 9157 | 8995 | 8790 | 8522 | 8199 | 7810 | 7334 |
| 32.5° | 10068 | 10295 | 10486 | 10512 | 10486 | 10295 | 10068 | 9765 | 9384 | 8940 | 8444 |
| 30° | 11400 | 11673 | 11901 | 11947 | 11901 | 11673 | 11400 | 11048 | 10621 | 10122 | 9546 |
| 27.5° | 12801 | 13126 | 13343 | 13426 | 13343 | 13126 | 12801 | 12377 | 11846 | 11322 | 10690 |
| 25° | 14245 | 14600 | 14842 | 14977 | 14842 | 14600 | 14245 | 13787 | 13213 | 12570 | 11832 |
| 22.5° | 15753 | 16174 | 16488 | 16638 | 16488 | 16174 | 15753 | 15220 | 14574 | 13833 | 12985 |
| 20° | 17310 | 17768 | 18134 | 18290 | 18134 | 17768 | 17310 | 16687 | 15952 | 15058 | 14112 |
| 17.5° | 18895 | 19455 | 19861 | 20060 | 19861 | 19455 | 18895 | 18235 | 17318 | 16278 | 15199 |
| 15° | 20435 | 21029 | 21470 | 21683 | 21470 | 21029 | 20435 | 19651 | 18624 | 17471 | 16257 |
| 12.5° | 21862 | 22491 | 22932 | 23240 | 22932 | 22491 | 21862 | 20971 | 19858 | 18616 | 17269 |
| 10° | 23136 | 23823 | 24269 | 24589 | 24269 | 23823 | 23136 | 22139 | 20928 | 19608 | 18166 |
| 7.5° | 24091 | 24958 | 25463 | 25777 | 25463 | 24958 | 24091 | 23041 | 21773 | 20354 | 18829 |
| 5° | 24823 | 25780 | 26238 | 26535 | 26238 | 25780 | 24823 | 23742 | 22444 | 20977 | 19420 |
| 2.5° | 25359 | 26115 | 26688 | 26985 | 26688 | 26115 | 25359 | 24255 | 22811 | 21303 | 19711 |
| 0° | 25570 | 26458 | 26864 | 27057 | 26864 | 26458 | 25570 | 24414 | 23056 | 21418 | 19786 |
| -2.5° | 25359 | 26115 | 26688 | 26985 | 26688 | 26115 | 25359 | 24255 | 22811 | 21303 | 19711 |
| -5° | 24823 | 25780 | 26238 | 26535 | 26238 | 25780 | 24823 | 23742 | 22444 | 20977 | 19420 |
| -7.5° | 24091 | 24958 | 25463 | 25777 | 25463 | 24958 | 24091 | 23041 | 21773 | 20354 | 18829 |
| -10° | 23136 | 23823 | 24269 | 24589 | 24269 | 23823 | 23136 | 22139 | 20928 | 19608 | 18166 |
| -12.5° | 21862 | 22491 | 22932 | 23240 | 22932 | 22491 | 21862 | 20971 | 19858 | 18616 | 17269 |
| -15° | 20435 | 21029 | 21470 | 21683 | 21470 | 21029 | 20435 | 19651 | 18624 | 17471 | 16257 |
| -17.5° | 18895 | 19455 | 19861 | 20060 | 19861 | 19455 | 18895 | 18235 | 17318 | 16278 | 15199 |
| -20° | 17310 | 17768 | 18134 | 18290 | 18134 | 17768 | 17310 | 16687 | 15952 | 15058 | 14112 |



REPORT NUMBER: P622183
 CATALOG NUMBER: IFLD-S-SA6A-735-U-66

CANDELA DISTRIBUTION (continued):

| | -7.5° | -5° | -2.5° | 0° | 2.5° | 5° | 7.5° | 10° | 12.5° | 15° | 17.5° |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| -22.5° | 15753 | 16174 | 16488 | 16638 | 16488 | 16174 | 15753 | 15220 | 14574 | 13833 | 12985 |
| -25° | 14245 | 14600 | 14842 | 14977 | 14842 | 14600 | 14245 | 13787 | 13213 | 12570 | 11832 |
| -27.5° | 12801 | 13126 | 13343 | 13426 | 13343 | 13126 | 12801 | 12377 | 11846 | 11322 | 10690 |
| -30° | 11400 | 11673 | 11901 | 11947 | 11901 | 11673 | 11400 | 11048 | 10621 | 10122 | 9546 |
| -32.5° | 10068 | 10295 | 10486 | 10512 | 10486 | 10295 | 10068 | 9765 | 9384 | 8940 | 8444 |
| -35° | 8790 | 8995 | 9157 | 9171 | 9157 | 8995 | 8790 | 8522 | 8199 | 7810 | 7334 |
| -37.5° | 7571 | 7767 | 7931 | 7914 | 7931 | 7767 | 7571 | 7323 | 7017 | 6634 | 6216 |
| -40° | 6357 | 6510 | 6640 | 6674 | 6640 | 6510 | 6357 | 6141 | 5850 | 5507 | 5155 |
| -42.5° | 5178 | 5302 | 5400 | 5391 | 5400 | 5302 | 5178 | 5005 | 4780 | 4509 | 4232 |
| -45° | 4175 | 4264 | 4330 | 4319 | 4330 | 4264 | 4175 | 4051 | 3895 | 3711 | 3526 |
| -47.5° | 3402 | 3463 | 3512 | 3514 | 3512 | 3463 | 3402 | 3318 | 3212 | 3085 | 2935 |
| -50° | 2814 | 2857 | 2886 | 2877 | 2886 | 2857 | 2814 | 2750 | 2673 | 2577 | 2468 |
| -52.5° | 2344 | 2379 | 2402 | 2390 | 2402 | 2379 | 2344 | 2295 | 2237 | 2168 | 2090 |
| -55° | 1955 | 1975 | 1986 | 1981 | 1986 | 1975 | 1955 | 1926 | 1886 | 1839 | 1782 |
| -57.5° | 1655 | 1669 | 1690 | 1695 | 1690 | 1669 | 1655 | 1632 | 1603 | 1568 | 1525 |
| -60° | 1407 | 1418 | 1433 | 1436 | 1433 | 1418 | 1407 | 1393 | 1369 | 1344 | 1315 |
| -62.5° | 1199 | 1208 | 1214 | 1214 | 1214 | 1208 | 1199 | 1191 | 1176 | 1156 | 1133 |
| -65° | 1026 | 1029 | 1038 | 1041 | 1038 | 1029 | 1026 | 1018 | 1009 | 995 | 977 |
| -67.5° | 876 | 882 | 882 | 885 | 882 | 882 | 876 | 874 | 868 | 856 | 845 |
| -70° | 738 | 744 | 738 | 729 | 738 | 744 | 738 | 735 | 735 | 732 | 727 |
| -72.5° | 571 | 556 | 533 | 513 | 533 | 556 | 571 | 591 | 608 | 620 | 614 |
| -75° | 418 | 386 | 378 | 369 | 378 | 386 | 418 | 450 | 479 | 502 | 502 |
| -77.5° | 309 | 277 | 265 | 257 | 265 | 277 | 309 | 340 | 372 | 398 | 401 |
| -80° | 228 | 193 | 187 | 182 | 187 | 193 | 228 | 254 | 283 | 311 | 314 |
| -82.5° | 161 | 133 | 127 | 121 | 127 | 133 | 161 | 185 | 211 | 234 | 239 |
| -85° | 101 | 84 | 81 | 75 | 81 | 84 | 101 | 118 | 133 | 147 | 147 |
| -87.5° | 49 | 40 | 38 | 32 | 38 | 40 | 49 | 61 | 69 | 78 | 75 |
| -90° | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |



REPORT NUMBER: P622183
 CATALOG NUMBER: IFLD-S-SA6A-735-U-66

CANDELA DISTRIBUTION (continued):

| | 20° | 22.5° | 25° | 27.5° | 30° | 32.5° | 35° | 37.5° | 40° | 42.5° | 45° |
|--------|-------|-------|-------|-------|-------|-------|------|-------|------|-------|------|
| 90° | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| 87.5° | 72 | 72 | 69 | 72 | 72 | 72 | 72 | 63 | 58 | 52 | 46 |
| 85° | 147 | 147 | 147 | 147 | 147 | 147 | 144 | 133 | 118 | 107 | 95 |
| 82.5° | 242 | 245 | 245 | 239 | 231 | 225 | 216 | 196 | 176 | 159 | 141 |
| 80° | 320 | 323 | 326 | 317 | 309 | 300 | 285 | 260 | 234 | 208 | 187 |
| 77.5° | 401 | 404 | 401 | 392 | 383 | 372 | 355 | 329 | 303 | 277 | 257 |
| 75° | 502 | 499 | 493 | 482 | 470 | 458 | 444 | 421 | 392 | 360 | 337 |
| 72.5° | 608 | 600 | 591 | 577 | 559 | 542 | 525 | 505 | 482 | 456 | 433 |
| 70° | 715 | 704 | 689 | 669 | 649 | 629 | 608 | 582 | 559 | 533 | 510 |
| 67.5° | 830 | 816 | 796 | 773 | 747 | 721 | 695 | 666 | 637 | 608 | 582 |
| 65° | 957 | 937 | 911 | 885 | 856 | 825 | 790 | 755 | 724 | 686 | 654 |
| 62.5° | 1104 | 1073 | 1041 | 1012 | 975 | 937 | 897 | 856 | 816 | 776 | 732 |
| 60° | 1280 | 1240 | 1202 | 1156 | 1110 | 1064 | 1015 | 966 | 914 | 868 | 816 |
| 57.5° | 1476 | 1427 | 1378 | 1326 | 1266 | 1208 | 1147 | 1084 | 1026 | 966 | 905 |
| 55° | 1718 | 1655 | 1589 | 1517 | 1444 | 1369 | 1295 | 1220 | 1147 | 1070 | 1003 |
| 52.5° | 2004 | 1923 | 1837 | 1739 | 1649 | 1554 | 1465 | 1369 | 1280 | 1191 | 1104 |
| 50° | 2358 | 2249 | 2128 | 2001 | 1886 | 1762 | 1646 | 1534 | 1424 | 1320 | 1217 |
| 47.5° | 2791 | 2638 | 2474 | 2318 | 2159 | 1998 | 1860 | 1724 | 1586 | 1456 | 1341 |
| 45° | 3316 | 3105 | 2883 | 2687 | 2474 | 2283 | 2090 | 1923 | 1762 | 1615 | 1468 |
| 42.5° | 3967 | 3670 | 3390 | 3122 | 2848 | 2606 | 2364 | 2157 | 1961 | 1779 | 1615 |
| 40° | 4783 | 4362 | 4010 | 3638 | 3310 | 2975 | 2690 | 2422 | 2180 | 1963 | 1762 |
| 37.5° | 5749 | 5256 | 4760 | 4255 | 3837 | 3425 | 3047 | 2716 | 2425 | 2162 | 1929 |
| 35° | 6804 | 6239 | 5633 | 5034 | 4425 | 3935 | 3460 | 3045 | 2690 | 2373 | 2102 |
| 32.5° | 7920 | 7245 | 6573 | 5879 | 5172 | 4495 | 3932 | 3416 | 2972 | 2609 | 2289 |
| 30° | 8914 | 8234 | 7505 | 6746 | 5956 | 5166 | 4434 | 3834 | 3307 | 2848 | 2479 |
| 27.5° | 9970 | 9197 | 8410 | 7597 | 6749 | 5870 | 5022 | 4258 | 3641 | 3125 | 2690 |
| 25° | 11022 | 10171 | 9292 | 8413 | 7516 | 6576 | 5605 | 4743 | 4010 | 3399 | 2877 |
| 22.5° | 12063 | 11131 | 10174 | 9177 | 8225 | 7234 | 6219 | 5213 | 4351 | 3670 | 3096 |
| 20° | 13115 | 12068 | 11031 | 9949 | 8888 | 7876 | 6787 | 5708 | 4751 | 3950 | 3298 |
| 17.5° | 14118 | 12982 | 11806 | 10627 | 9508 | 8404 | 7294 | 6187 | 5120 | 4204 | 3500 |
| 15° | 15067 | 13801 | 12535 | 11264 | 10045 | 8911 | 7747 | 6602 | 5469 | 4472 | 3676 |
| 12.5° | 15886 | 14499 | 13181 | 11852 | 10555 | 9350 | 8147 | 6963 | 5798 | 4731 | 3855 |
| 10° | 16629 | 15136 | 13743 | 12362 | 11019 | 9727 | 8479 | 7262 | 6066 | 4942 | 3999 |
| 7.5° | 17264 | 15704 | 14213 | 12757 | 11362 | 10013 | 8730 | 7493 | 6274 | 5103 | 4111 |
| 5° | 17751 | 16087 | 14531 | 13014 | 11590 | 10203 | 8909 | 7657 | 6421 | 5218 | 4183 |
| 2.5° | 17981 | 16315 | 14701 | 13155 | 11786 | 10373 | 9070 | 7804 | 6545 | 5328 | 4261 |
| 0° | 18097 | 16399 | 14778 | 13276 | 11869 | 10442 | 9113 | 7825 | 6542 | 5342 | 4267 |
| -2.5° | 17981 | 16315 | 14701 | 13155 | 11786 | 10373 | 9070 | 7804 | 6545 | 5328 | 4261 |
| -5° | 17751 | 16087 | 14531 | 13014 | 11590 | 10203 | 8909 | 7657 | 6421 | 5218 | 4183 |
| -7.5° | 17264 | 15704 | 14213 | 12757 | 11362 | 10013 | 8730 | 7493 | 6274 | 5103 | 4111 |
| -10° | 16629 | 15136 | 13743 | 12362 | 11019 | 9727 | 8479 | 7262 | 6066 | 4942 | 3999 |
| -12.5° | 15886 | 14499 | 13181 | 11852 | 10555 | 9350 | 8147 | 6963 | 5798 | 4731 | 3855 |
| -15° | 15067 | 13801 | 12535 | 11264 | 10045 | 8911 | 7747 | 6602 | 5469 | 4472 | 3676 |
| -17.5° | 14118 | 12982 | 11806 | 10627 | 9508 | 8404 | 7294 | 6187 | 5120 | 4204 | 3500 |
| -20° | 13115 | 12068 | 11031 | 9949 | 8888 | 7876 | 6787 | 5708 | 4751 | 3950 | 3298 |



REPORT NUMBER: P622183
 CATALOG NUMBER: IFLD-S-SA6A-735-U-66

CANDELA DISTRIBUTION (continued):

| | 20° | 22.5° | 25° | 27.5° | 30° | 32.5° | 35° | 37.5° | 40° | 42.5° | 45° |
|--------|-------|-------|-------|-------|------|-------|------|-------|------|-------|------|
| -22.5° | 12063 | 11131 | 10174 | 9177 | 8225 | 7234 | 6219 | 5213 | 4351 | 3670 | 3096 |
| -25° | 11022 | 10171 | 9292 | 8413 | 7516 | 6576 | 5605 | 4743 | 4010 | 3399 | 2877 |
| -27.5° | 9970 | 9197 | 8410 | 7597 | 6749 | 5870 | 5022 | 4258 | 3641 | 3125 | 2690 |
| -30° | 8914 | 8234 | 7505 | 6746 | 5956 | 5166 | 4434 | 3834 | 3307 | 2848 | 2479 |
| -32.5° | 7920 | 7245 | 6573 | 5879 | 5172 | 4495 | 3932 | 3416 | 2972 | 2609 | 2289 |
| -35° | 6804 | 6239 | 5633 | 5034 | 4425 | 3935 | 3460 | 3045 | 2690 | 2373 | 2102 |
| -37.5° | 5749 | 5256 | 4760 | 4255 | 3837 | 3425 | 3047 | 2716 | 2425 | 2162 | 1929 |
| -40° | 4783 | 4362 | 4010 | 3638 | 3310 | 2975 | 2690 | 2422 | 2180 | 1963 | 1762 |
| -42.5° | 3967 | 3670 | 3390 | 3122 | 2848 | 2606 | 2364 | 2157 | 1961 | 1779 | 1615 |
| -45° | 3316 | 3105 | 2883 | 2687 | 2474 | 2283 | 2090 | 1923 | 1762 | 1615 | 1468 |
| -47.5° | 2791 | 2638 | 2474 | 2318 | 2159 | 1998 | 1860 | 1724 | 1586 | 1456 | 1341 |
| -50° | 2358 | 2249 | 2128 | 2001 | 1886 | 1762 | 1646 | 1534 | 1424 | 1320 | 1217 |
| -52.5° | 2004 | 1923 | 1837 | 1739 | 1649 | 1554 | 1465 | 1369 | 1280 | 1191 | 1104 |
| -55° | 1718 | 1655 | 1589 | 1517 | 1444 | 1369 | 1295 | 1220 | 1147 | 1070 | 1003 |
| -57.5° | 1476 | 1427 | 1378 | 1326 | 1266 | 1208 | 1147 | 1084 | 1026 | 966 | 905 |
| -60° | 1280 | 1240 | 1202 | 1156 | 1110 | 1064 | 1015 | 966 | 914 | 868 | 816 |
| -62.5° | 1104 | 1073 | 1041 | 1012 | 975 | 937 | 897 | 856 | 816 | 776 | 732 |
| -65° | 957 | 937 | 911 | 885 | 856 | 825 | 790 | 755 | 724 | 686 | 654 |
| -67.5° | 830 | 816 | 796 | 773 | 747 | 721 | 695 | 666 | 637 | 608 | 582 |
| -70° | 715 | 704 | 689 | 669 | 649 | 629 | 608 | 582 | 559 | 533 | 510 |
| -72.5° | 608 | 600 | 591 | 577 | 559 | 542 | 525 | 505 | 482 | 456 | 433 |
| -75° | 502 | 499 | 493 | 482 | 470 | 458 | 444 | 421 | 392 | 360 | 337 |
| -77.5° | 401 | 404 | 401 | 392 | 383 | 372 | 355 | 329 | 303 | 277 | 257 |
| -80° | 320 | 323 | 326 | 317 | 309 | 300 | 285 | 260 | 234 | 208 | 187 |
| -82.5° | 242 | 245 | 245 | 239 | 231 | 225 | 216 | 196 | 176 | 159 | 141 |
| -85° | 147 | 147 | 147 | 147 | 147 | 147 | 144 | 133 | 118 | 107 | 95 |
| -87.5° | 72 | 72 | 69 | 72 | 72 | 72 | 72 | 63 | 58 | 52 | 46 |
| -90° | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |



REPORT NUMBER: P622183
 CATALOG NUMBER: IFLD-S-SA6A-735-U-66

CANDELA DISTRIBUTION (continued):

| | 47.5° | 50° | 52.5° | 55° | 57.5° | 60° | 62.5° | 65° | 67.5° | 70° | 72.5° |
|--------|-------|------|-------|------|-------|------|-------|------|-------|-----|-------|
| 90° | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| 87.5° | 49 | 52 | 55 | 55 | 55 | 52 | 49 | 46 | 40 | 38 | 35 |
| 85° | 101 | 104 | 110 | 112 | 107 | 104 | 95 | 89 | 84 | 75 | 69 |
| 82.5° | 150 | 156 | 161 | 161 | 156 | 150 | 141 | 133 | 124 | 112 | 101 |
| 80° | 199 | 208 | 216 | 216 | 208 | 196 | 185 | 173 | 161 | 147 | 133 |
| 77.5° | 262 | 268 | 271 | 274 | 262 | 251 | 236 | 216 | 199 | 182 | 164 |
| 75° | 332 | 332 | 334 | 329 | 317 | 309 | 288 | 265 | 239 | 216 | 193 |
| 72.5° | 415 | 401 | 395 | 386 | 366 | 349 | 334 | 314 | 280 | 248 | 222 |
| 70° | 487 | 467 | 450 | 433 | 412 | 389 | 372 | 346 | 317 | 280 | 248 |
| 67.5° | 556 | 531 | 505 | 482 | 456 | 433 | 407 | 375 | 343 | 309 | 274 |
| 65° | 626 | 594 | 562 | 531 | 502 | 473 | 444 | 407 | 369 | 334 | 297 |
| 62.5° | 695 | 657 | 620 | 582 | 548 | 513 | 482 | 438 | 395 | 358 | 317 |
| 60° | 767 | 727 | 683 | 640 | 597 | 556 | 516 | 470 | 424 | 378 | 337 |
| 57.5° | 851 | 793 | 744 | 695 | 646 | 600 | 551 | 502 | 453 | 404 | 355 |
| 55° | 934 | 871 | 807 | 753 | 698 | 646 | 588 | 533 | 479 | 427 | 372 |
| 52.5° | 1024 | 949 | 879 | 810 | 750 | 689 | 629 | 571 | 507 | 450 | 383 |
| 50° | 1122 | 1032 | 951 | 874 | 802 | 735 | 669 | 603 | 536 | 473 | 398 |
| 47.5° | 1225 | 1122 | 1026 | 937 | 859 | 778 | 706 | 637 | 565 | 499 | 412 |
| 45° | 1341 | 1217 | 1104 | 1006 | 911 | 825 | 747 | 669 | 594 | 516 | 421 |
| 42.5° | 1453 | 1318 | 1191 | 1070 | 969 | 871 | 787 | 704 | 623 | 531 | 435 |
| 40° | 1586 | 1418 | 1277 | 1147 | 1026 | 917 | 822 | 735 | 652 | 548 | 447 |
| 37.5° | 1724 | 1531 | 1367 | 1217 | 1084 | 966 | 862 | 764 | 672 | 565 | 458 |
| 35° | 1862 | 1646 | 1456 | 1289 | 1145 | 1015 | 900 | 796 | 692 | 580 | 470 |
| 32.5° | 2007 | 1762 | 1545 | 1361 | 1202 | 1064 | 937 | 825 | 715 | 597 | 479 |
| 30° | 2165 | 1883 | 1638 | 1430 | 1257 | 1107 | 975 | 853 | 738 | 611 | 487 |
| 27.5° | 2315 | 1995 | 1727 | 1505 | 1315 | 1153 | 1009 | 882 | 764 | 626 | 499 |
| 25° | 2465 | 2116 | 1822 | 1574 | 1369 | 1194 | 1044 | 908 | 787 | 643 | 507 |
| 22.5° | 2626 | 2234 | 1909 | 1640 | 1418 | 1234 | 1075 | 937 | 807 | 660 | 516 |
| 20° | 2774 | 2341 | 1984 | 1704 | 1470 | 1274 | 1107 | 960 | 825 | 678 | 525 |
| 17.5° | 2909 | 2451 | 2076 | 1770 | 1519 | 1312 | 1133 | 980 | 842 | 692 | 531 |
| 15° | 3056 | 2560 | 2157 | 1828 | 1563 | 1344 | 1159 | 1000 | 856 | 706 | 533 |
| 12.5° | 3183 | 2652 | 2226 | 1880 | 1600 | 1369 | 1179 | 1015 | 871 | 721 | 539 |
| 10° | 3287 | 2727 | 2283 | 1920 | 1629 | 1393 | 1194 | 1029 | 879 | 729 | 542 |
| 7.5° | 3367 | 2785 | 2327 | 1952 | 1652 | 1410 | 1208 | 1038 | 888 | 738 | 542 |
| 5° | 3428 | 2828 | 2355 | 1975 | 1669 | 1424 | 1220 | 1047 | 897 | 750 | 545 |
| 2.5° | 3483 | 2874 | 2379 | 1995 | 1684 | 1436 | 1228 | 1052 | 897 | 747 | 539 |
| 0° | 3491 | 2883 | 2376 | 1995 | 1684 | 1439 | 1228 | 1052 | 894 | 744 | 533 |
| -2.5° | 3483 | 2874 | 2379 | 1995 | 1684 | 1436 | 1228 | 1052 | 897 | 747 | 539 |
| -5° | 3428 | 2828 | 2355 | 1975 | 1669 | 1424 | 1220 | 1047 | 897 | 750 | 545 |
| -7.5° | 3367 | 2785 | 2327 | 1952 | 1652 | 1410 | 1208 | 1038 | 888 | 738 | 542 |
| -10° | 3287 | 2727 | 2283 | 1920 | 1629 | 1393 | 1194 | 1029 | 879 | 729 | 542 |
| -12.5° | 3183 | 2652 | 2226 | 1880 | 1600 | 1369 | 1179 | 1015 | 871 | 721 | 539 |
| -15° | 3056 | 2560 | 2157 | 1828 | 1563 | 1344 | 1159 | 1000 | 856 | 706 | 533 |
| -17.5° | 2909 | 2451 | 2076 | 1770 | 1519 | 1312 | 1133 | 980 | 842 | 692 | 531 |
| -20° | 2774 | 2341 | 1984 | 1704 | 1470 | 1274 | 1107 | 960 | 825 | 678 | 525 |



REPORT NUMBER: P622183
 CATALOG NUMBER: IFLD-S-SA6A-735-U-66

CANDELA DISTRIBUTION (continued):

| | 47.5° | 50° | 52.5° | 55° | 57.5° | 60° | 62.5° | 65° | 67.5° | 70° | 72.5° |
|--------|-------|------|-------|------|-------|------|-------|-----|-------|-----|-------|
| -22.5° | 2626 | 2234 | 1909 | 1640 | 1418 | 1234 | 1075 | 937 | 807 | 660 | 516 |
| -25° | 2465 | 2116 | 1822 | 1574 | 1369 | 1194 | 1044 | 908 | 787 | 643 | 507 |
| -27.5° | 2315 | 1995 | 1727 | 1505 | 1315 | 1153 | 1009 | 882 | 764 | 626 | 499 |
| -30° | 2165 | 1883 | 1638 | 1430 | 1257 | 1107 | 975 | 853 | 738 | 611 | 487 |
| -32.5° | 2007 | 1762 | 1545 | 1361 | 1202 | 1064 | 937 | 825 | 715 | 597 | 479 |
| -35° | 1862 | 1646 | 1456 | 1289 | 1145 | 1015 | 900 | 796 | 692 | 580 | 470 |
| -37.5° | 1724 | 1531 | 1367 | 1217 | 1084 | 966 | 862 | 764 | 672 | 565 | 458 |
| -40° | 1586 | 1418 | 1277 | 1147 | 1026 | 917 | 822 | 735 | 652 | 548 | 447 |
| -42.5° | 1453 | 1318 | 1191 | 1070 | 969 | 871 | 787 | 704 | 623 | 531 | 435 |
| -45° | 1341 | 1217 | 1104 | 1006 | 911 | 825 | 747 | 669 | 594 | 516 | 421 |
| -47.5° | 1225 | 1122 | 1026 | 937 | 859 | 778 | 706 | 637 | 565 | 499 | 412 |
| -50° | 1122 | 1032 | 951 | 874 | 802 | 735 | 669 | 603 | 536 | 473 | 398 |
| -52.5° | 1024 | 949 | 879 | 810 | 750 | 689 | 629 | 571 | 507 | 450 | 383 |
| -55° | 934 | 871 | 807 | 753 | 698 | 646 | 588 | 533 | 479 | 427 | 372 |
| -57.5° | 851 | 793 | 744 | 695 | 646 | 600 | 551 | 502 | 453 | 404 | 355 |
| -60° | 767 | 727 | 683 | 640 | 597 | 556 | 516 | 470 | 424 | 378 | 337 |
| -62.5° | 695 | 657 | 620 | 582 | 548 | 513 | 482 | 438 | 395 | 358 | 317 |
| -65° | 626 | 594 | 562 | 531 | 502 | 473 | 444 | 407 | 369 | 334 | 297 |
| -67.5° | 556 | 531 | 505 | 482 | 456 | 433 | 407 | 375 | 343 | 309 | 274 |
| -70° | 487 | 467 | 450 | 433 | 412 | 389 | 372 | 346 | 317 | 280 | 248 |
| -72.5° | 415 | 401 | 395 | 386 | 366 | 349 | 334 | 314 | 280 | 248 | 222 |
| -75° | 332 | 332 | 334 | 329 | 317 | 309 | 288 | 265 | 239 | 216 | 193 |
| -77.5° | 262 | 268 | 271 | 274 | 262 | 251 | 236 | 216 | 199 | 182 | 164 |
| -80° | 199 | 208 | 216 | 216 | 208 | 196 | 185 | 173 | 161 | 147 | 133 |
| -82.5° | 150 | 156 | 161 | 161 | 156 | 150 | 141 | 133 | 124 | 112 | 101 |
| -85° | 101 | 104 | 110 | 112 | 107 | 104 | 95 | 89 | 84 | 75 | 69 |
| -87.5° | 49 | 52 | 55 | 55 | 55 | 52 | 49 | 46 | 40 | 38 | 35 |
| -90° | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 | 0 |



REPORT NUMBER: P622183
 CATALOG NUMBER: IFLD-S-SA6A-735-U-66

CANDELA DISTRIBUTION (continued):

| | 75° | 77.5° | 80° | 82.5° | 85° | 87.5° | 90° |
|--------|-----|-------|-----|-------|-----|-------|-----|
| 90° | 0 | 0 | 0 | 0 | 0 | 0 | 0 |
| 87.5° | 29 | 23 | 17 | 12 | 6 | 3 | 0 |
| 85° | 61 | 46 | 32 | 20 | 12 | 6 | 0 |
| 82.5° | 89 | 66 | 49 | 32 | 20 | 9 | 0 |
| 80° | 118 | 89 | 63 | 43 | 26 | 12 | 0 |
| 77.5° | 144 | 110 | 81 | 52 | 32 | 14 | 0 |
| 75° | 167 | 127 | 95 | 63 | 38 | 17 | 0 |
| 72.5° | 190 | 144 | 107 | 72 | 43 | 20 | 0 |
| 70° | 213 | 161 | 118 | 84 | 49 | 23 | 0 |
| 67.5° | 231 | 176 | 130 | 89 | 55 | 26 | 0 |
| 65° | 245 | 190 | 138 | 95 | 61 | 26 | 0 |
| 62.5° | 260 | 202 | 147 | 101 | 66 | 29 | 0 |
| 60° | 277 | 213 | 159 | 107 | 69 | 32 | 0 |
| 57.5° | 288 | 222 | 164 | 112 | 72 | 35 | 0 |
| 55° | 300 | 234 | 170 | 118 | 78 | 38 | 0 |
| 52.5° | 311 | 242 | 179 | 121 | 81 | 38 | 0 |
| 50° | 320 | 251 | 185 | 124 | 84 | 40 | 0 |
| 47.5° | 332 | 257 | 187 | 127 | 87 | 43 | 0 |
| 45° | 340 | 265 | 193 | 130 | 89 | 43 | 0 |
| 42.5° | 349 | 271 | 196 | 133 | 89 | 46 | 0 |
| 40° | 358 | 274 | 202 | 138 | 92 | 49 | 0 |
| 37.5° | 363 | 280 | 205 | 141 | 95 | 49 | 0 |
| 35° | 366 | 283 | 208 | 144 | 98 | 52 | 0 |
| 32.5° | 372 | 288 | 211 | 150 | 98 | 52 | 0 |
| 30° | 381 | 288 | 211 | 153 | 101 | 52 | 0 |
| 27.5° | 386 | 291 | 216 | 153 | 101 | 55 | 0 |
| 25° | 389 | 291 | 219 | 156 | 104 | 55 | 0 |
| 22.5° | 392 | 294 | 222 | 159 | 104 | 55 | 0 |
| 20° | 395 | 297 | 225 | 161 | 107 | 58 | 0 |
| 17.5° | 398 | 303 | 228 | 161 | 107 | 58 | 0 |
| 15° | 404 | 306 | 228 | 161 | 107 | 61 | 0 |
| 12.5° | 407 | 306 | 228 | 164 | 107 | 61 | 0 |
| 10° | 409 | 309 | 228 | 164 | 110 | 58 | 0 |
| 7.5° | 409 | 309 | 231 | 164 | 110 | 58 | 0 |
| 5° | 409 | 311 | 228 | 164 | 107 | 58 | 0 |
| 2.5° | 404 | 311 | 228 | 161 | 107 | 58 | 0 |
| 0° | 401 | 309 | 225 | 161 | 107 | 58 | 0 |
| -2.5° | 404 | 311 | 228 | 161 | 107 | 58 | 0 |
| -5° | 409 | 311 | 228 | 164 | 107 | 58 | 0 |
| -7.5° | 409 | 309 | 231 | 164 | 110 | 58 | 0 |
| -10° | 409 | 309 | 228 | 164 | 110 | 58 | 0 |
| -12.5° | 407 | 306 | 228 | 164 | 107 | 61 | 0 |
| -15° | 404 | 306 | 228 | 161 | 107 | 61 | 0 |
| -17.5° | 398 | 303 | 228 | 161 | 107 | 58 | 0 |
| -20° | 395 | 297 | 225 | 161 | 107 | 58 | 0 |



REPORT NUMBER: P622183
 CATALOG NUMBER: IFLD-S-SA6A-735-U-66

CANDELA DISTRIBUTION (continued):

| | 75° | 77.5° | 80° | 82.5° | 85° | 87.5° | 90° |
|--------|-----|-------|-----|-------|-----|-------|-----|
| -22.5° | 392 | 294 | 222 | 159 | 104 | 55 | 0 |
| -25° | 389 | 291 | 219 | 156 | 104 | 55 | 0 |
| -27.5° | 386 | 291 | 216 | 153 | 101 | 55 | 0 |
| -30° | 381 | 288 | 211 | 153 | 101 | 52 | 0 |
| -32.5° | 372 | 288 | 211 | 150 | 98 | 52 | 0 |
| -35° | 366 | 283 | 208 | 144 | 98 | 52 | 0 |
| -37.5° | 363 | 280 | 205 | 141 | 95 | 49 | 0 |
| -40° | 358 | 274 | 202 | 138 | 92 | 49 | 0 |
| -42.5° | 349 | 271 | 196 | 133 | 89 | 46 | 0 |
| -45° | 340 | 265 | 193 | 130 | 89 | 43 | 0 |
| -47.5° | 332 | 257 | 187 | 127 | 87 | 43 | 0 |
| -50° | 320 | 251 | 185 | 124 | 84 | 40 | 0 |
| -52.5° | 311 | 242 | 179 | 121 | 81 | 38 | 0 |
| -55° | 300 | 234 | 170 | 118 | 78 | 38 | 0 |
| -57.5° | 288 | 222 | 164 | 112 | 72 | 35 | 0 |
| -60° | 277 | 213 | 159 | 107 | 69 | 32 | 0 |
| -62.5° | 260 | 202 | 147 | 101 | 66 | 29 | 0 |
| -65° | 245 | 190 | 138 | 95 | 61 | 26 | 0 |
| -67.5° | 231 | 176 | 130 | 89 | 55 | 26 | 0 |
| -70° | 213 | 161 | 118 | 84 | 49 | 23 | 0 |
| -72.5° | 190 | 144 | 107 | 72 | 43 | 20 | 0 |
| -75° | 167 | 127 | 95 | 63 | 38 | 17 | 0 |
| -77.5° | 144 | 110 | 81 | 52 | 32 | 14 | 0 |
| -80° | 118 | 89 | 63 | 43 | 26 | 12 | 0 |
| -82.5° | 89 | 66 | 49 | 32 | 20 | 9 | 0 |
| -85° | 61 | 46 | 32 | 20 | 12 | 6 | 0 |
| -87.5° | 29 | 23 | 17 | 12 | 6 | 3 | 0 |
| -90° | 0 | 0 | 0 | 0 | 0 | 0 | 0 |

(END OF REPORT)