

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P722958

Luminaire Tested: **IFLD-L-SA7B-750-U-11**

Issue Date: 01/11/2023

Test Information

Test Method: LM-79-2019
Report Number: P722958
Test Lab: INNOVATION CENTER(G2)
Issue Date: 01/11/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: IFLD-L-SA7B-750-U-11
Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ Nema 1 distribution lens
Light Source: (112) 5000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A	NEMA Type: 1H x 1V
Luminaire Lumens: 19212.4 lumens	Max Intensity: 575827.6 candela
Efficiency: N/A	Max Intensity Angle: 0°H x 0°V
Efficacy: 68.4 lumens/watt	
Luminous Opening: Rectangular (W 2' x L: 1' x H: 0')	
Beam Angle (50%): 8.3°H x 8.9°V	Field Angle (10%): 14.9°H x 14.6°V
Beam Lumens: 6472.7 lumens	Field Lumens: 10224 lumens
Beam Efficiency: 33.7%	Field Efficiency: 53.2%

Input Watts (W): 281
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P722958
CATALOG NUMBER: IFLD-L-SA7B-750-U-11

Iso-Candela Plot






REPORT NUMBER: P722958
 CATALOG NUMBER: IFLD-L-SA7B-750-U-11

Lumen Table

90	0.1	0.7	2.6	6.0	10.5	6.0	2.6	0.7	0.1										
80	0.1	0.7	2.6	6.0	10.5	6.0	2.6	0.7	0.1										
70	0.4	0.5	1.3	2.7	4.1	5.1	8.4	15.4	15.4	8.4	5.1	4.1	2.7	1.3	0.5	0.4			
60		1.0	2.4	4.9	7.6	9.9	13.3	18.8	18.8	13.3	9.9	7.6	4.9	2.4	1.0				
50	1.3	1.7	3.6	7.5	12.5	18.5	24.1	29.5	29.5	24.1	18.5	12.5	7.5	3.6	1.7	1.3			
40		2.7	5.1	10.7	19.3	25.9	28.8	30.6	30.6	28.8	25.9	19.3	10.7	5.1	2.7				
30	2.6	3.9	7.1	15.1	23.7	27.2	36.0	48.0	48.0	36.0	27.2	23.7	15.1	7.1	3.9	2.6			
20		5.3	9.9	19.8	26.1	35.0	70.1	134.7	134.7	70.1	35.0	26.1	19.8	9.9	5.3				
10	3.0	6.0	12.1	22.4	27.3	46.0	139.6	3751.1	3751.1	139.6	46.0	27.3	22.4	12.1	6.0	3.0			
0		6.0	12.1	22.4	27.3	46.0	139.6	3751.1	3751.1	139.6	46.0	27.3	22.4	12.1	6.0				
-10	2.6	5.3	9.9	19.8	26.1	35.0	70.1	134.7	134.7	70.1	35.0	26.1	19.8	9.9	5.3	2.6			
-20		3.9	7.1	15.1	23.7	27.2	36.0	48.0	48.0	36.0	27.2	23.7	15.1	7.1	3.9				
-30	1.3	2.7	5.1	10.7	19.3	25.9	28.8	30.6	30.6	28.8	25.9	19.3	10.7	5.1	2.7	1.3			
-40		1.7	3.6	7.5	12.5	18.5	24.1	29.5	29.5	24.1	18.5	12.5	7.5	3.6	1.7				
-50	0.4	1.0	2.4	4.9	7.6	9.9	13.3	18.8	18.8	13.3	9.9	7.6	4.9	2.4	1.0	0.4			
-60		0.5	1.3	2.7	4.1	5.1	8.4	15.4	15.4	8.4	5.1	4.1	2.7	1.3	0.5				
-70	0.1	0.7	2.6	6.0	10.5	6.0	2.6	0.7	0.1							0.1			
-80		0.1	0.7	2.6	6.0	10.5	6.0	2.6	0.7	0.1									
-90	0.1	0.7	2.6	6.0	10.5	6.0	2.6	0.7	0.1										
	-90	-80	-70	-60	-50	-40	-30	-20	-10	0	10	20	30	40	50	60	70	80	90

REPORT NUMBER: P722958
CATALOG NUMBER: IFLD-L-SA7B-750-U-11


Luminous Intensity Polar Plot



— Vertical Distribution Through 0-Deg - - - Horizontal Distribution Through 0-Deg

REPORT NUMBER: P722958
CATALOG NUMBER: IFLD-L-SA7B-750-U-11

Luminous Intensity Plot



Beam:
H Angle: 8.3°
V Angle: 8.9°
Lumens: 6472.7
Efficiency: 33.7%

Field:
H Angle: 14.9°
V Angle: 14.6°
Lumens: 10224
Efficiency: 53.2%

Spill:
Lumens: 8988.4
Efficiency: 46.8%

— Vertical Distribution through 0-Deg
- - Horizontal Distribution through 0-Deg



REPORT NUMBER: P722958
 CATALOG NUMBER: IFLD-L-SA7B-750-U-11

FIELD
 BEAM

CANDELA DISTRIBUTION:

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
82.5°	15.1	15.1	15.1	15.1	15.1	15.1	15.1	10.0	10.0	10.0	10.0
80°	40.1	40.1	40.1	40.1	40.1	40.1	35.1	35.1	30.1	25.1	25.1
77.5°	75.3	80.3	85.3	80.3	75.3	75.3	70.3	60.2	55.2	45.2	40.1
75°	125.5	135.5	140.5	135.5	130.5	125.5	115.4	100.4	85.3	70.3	60.2
72.5°	225.8	230.8	230.8	220.8	205.8	195.7	180.7	150.6	125.5	100.4	85.3
70°	391.4	406.5	411.5	361.3	316.2	276.0	235.9	200.7	160.6	125.5	110.4
67.5°	752.8	732.7	697.6	562.1	436.6	326.2	250.9	220.8	185.7	150.6	140.5
65°	567.1	552.0	532.0	461.7	391.4	316.2	266.0	235.9	210.8	180.7	175.6
62.5°	476.8	476.8	466.7	421.6	376.4	321.2	286.1	266.0	240.9	215.8	215.8
60°	496.8	506.9	496.8	451.7	401.5	351.3	321.2	301.1	276.0	261.0	261.0
57.5°	562.1	567.1	552.0	501.8	451.7	396.5	366.3	341.3	316.2	301.1	301.1
55°	647.4	642.4	622.3	572.1	521.9	466.7	436.6	401.5	366.3	351.3	351.3
52.5°	727.7	732.7	712.6	667.5	612.3	557.0	521.9	476.8	436.6	421.6	411.5
50°	843.1	848.1	833.1	787.9	742.7	687.5	632.3	572.1	526.9	506.9	486.8
47.5°	943.5	943.5	928.4	898.3	863.2	813.0	752.8	697.6	647.4	612.3	577.1
45°	988.6	988.6	978.6	963.5	943.5	898.3	838.1	777.9	742.7	722.7	692.5
42.5°	1068.9	1068.9	1043.8	1013.7	988.6	943.5	888.3	823.0	813.0	792.9	772.8
40°	1199.4	1154.2	1114.1	1079.0	1038.8	988.6	938.5	893.3	873.2	848.1	828.0
37.5°	1319.9	1259.6	1199.4	1144.2	1099.0	1058.9	993.7	958.5	933.4	903.3	883.2
35°	908.3	888.3	913.4	943.5	988.6	1058.9	1104.1	1053.9	998.7	963.5	938.5
32.5°	868.2	868.2	873.2	873.2	863.2	858.2	903.3	1008.7	1114.1	1058.9	1008.7
30°	963.5	983.6	988.6	978.6	943.5	898.3	873.2	868.2	918.4	1063.9	1104.1
27.5°	1244.6	1259.6	1249.6	1214.5	1139.2	1033.8	968.6	898.3	883.2	883.2	1043.8
25°	1686.2	1681.2	1641.0	1560.7	1445.3	1304.8	1164.3	1018.7	943.5	898.3	893.3
22.5°	1937.1	1937.1	1907.0	1861.8	1786.6	1646.1	1450.3	1254.6	1068.9	963.5	903.3
20°	2278.4	2288.4	2253.3	2168.0	2032.5	1907.0	1761.5	1530.6	1289.7	1079.0	958.5
17.5°	2920.7	2910.7	2830.4	2654.8	2418.9	2203.1	1977.3	1801.6	1545.7	1274.7	1048.9
15°	4095.1	4064.9	3839.1	3432.6	2991.0	2609.6	2278.4	1987.3	1786.6	1480.4	1204.4
12.5°	6403.5	6318.2	5706.0	4742.4	3894.3	3116.5	2624.7	2233.2	1937.1	1681.2	1355.0
10°	12014.2	11923.9	10041.9	6935.5	5329.6	3904.4	3011.1	2469.1	2082.7	1826.7	1500.5
7.5°	41281.8	35696.3	22096.3	13529.8	7045.9	4837.8	3507.9	2730.0	2243.2	1917.1	1626.0
5°	231114.9	191263.4	101558.5	27721.9	11171.1	6002.1	3984.7	2945.8	2353.7	1982.3	1701.3
2.5°	498578.5	411859.6	198098.5	50239.8	13765.6	6759.9	4260.7	3046.2	2408.9	2012.4	1746.4
0°	575827.6	452770.1	202324.1	54375.0	14423.0	7061.0	4381.1	3091.4	2434.0	2032.5	1761.5



REPORT NUMBER: P722958
 CATALOG NUMBER: IFLD-L-SA7B-750-U-11

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	5.0	5.0	5.0	5.0	5.0
85°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
82.5°	10.0	10.0	10.0	10.0	10.0	10.0	5.0	5.0	5.0	5.0	5.0
80°	20.1	20.1	20.1	20.1	20.1	15.1	15.1	15.1	10.0	10.0	10.0
77.5°	40.1	40.1	35.1	35.1	30.1	30.1	30.1	25.1	20.1	20.1	15.1
75°	60.2	60.2	60.2	55.2	50.2	45.2	45.2	40.1	35.1	30.1	30.1
72.5°	85.3	85.3	85.3	80.3	75.3	70.3	60.2	55.2	50.2	45.2	40.1
70°	110.4	110.4	110.4	105.4	105.4	100.4	90.3	80.3	70.3	60.2	55.2
67.5°	140.5	140.5	140.5	130.5	125.5	120.4	115.4	105.4	95.4	80.3	70.3
65°	175.6	175.6	175.6	160.6	150.6	145.5	135.5	125.5	110.4	100.4	85.3
62.5°	220.8	220.8	210.8	195.7	180.7	165.6	155.6	145.5	130.5	115.4	100.4
60°	261.0	261.0	255.9	235.9	215.8	190.7	180.7	165.6	150.6	135.5	115.4
57.5°	301.1	301.1	291.1	271.0	250.9	230.8	210.8	195.7	175.6	155.6	135.5
55°	346.3	341.3	326.2	306.1	286.1	266.0	250.9	230.8	210.8	185.7	155.6
52.5°	401.5	386.4	361.3	341.3	316.2	296.1	281.0	261.0	240.9	210.8	175.6
50°	466.7	441.6	406.5	376.4	351.3	331.2	311.1	291.1	271.0	235.9	200.7
47.5°	547.0	506.9	466.7	426.6	391.4	366.3	341.3	321.2	291.1	255.9	220.8
45°	642.4	582.1	537.0	486.8	446.6	406.5	376.4	351.3	311.1	271.0	235.9
42.5°	737.7	687.5	622.3	557.0	506.9	456.7	416.5	376.4	336.2	291.1	250.9
40°	803.0	762.8	717.6	647.4	577.1	516.9	461.7	406.5	356.3	311.1	266.0
37.5°	853.1	823.0	782.9	732.7	662.4	587.2	511.9	441.6	381.4	331.2	286.1
35°	908.3	873.2	833.1	792.9	737.7	657.4	562.1	481.8	411.5	351.3	311.1
32.5°	968.6	918.4	878.2	833.1	792.9	727.7	627.3	526.9	441.6	381.4	341.3
30°	1038.8	973.6	918.4	873.2	828.0	767.8	692.5	577.1	486.8	421.6	371.4
27.5°	1114.1	1018.7	958.5	908.3	863.2	808.0	737.7	637.3	542.0	461.7	401.5
25°	1043.8	1094.0	998.7	943.5	893.3	838.1	777.9	712.6	602.2	511.9	441.6
22.5°	898.3	1073.9	1068.9	988.6	928.4	878.2	843.1	772.8	672.5	562.1	476.8
20°	908.3	958.5	1144.2	1033.8	973.6	938.5	903.3	838.1	737.7	607.2	511.9
17.5°	938.5	918.4	1053.9	1104.1	1033.8	988.6	963.5	903.3	797.9	667.5	567.1
15°	1018.7	933.4	973.6	1164.3	1089.0	1038.8	1023.8	948.5	853.1	732.7	622.3
12.5°	1089.0	958.5	938.5	1124.1	1139.2	1084.0	1048.9	983.6	898.3	787.9	672.5
10°	1204.4	1018.7	953.5	1079.0	1189.4	1124.1	1068.9	1013.7	933.4	838.1	722.7
7.5°	1294.8	1053.9	958.5	1043.8	1239.6	1154.2	1089.0	1028.8	963.5	878.2	762.8
5°	1334.9	1068.9	953.5	1013.7	1294.8	1189.4	1114.1	1043.8	983.6	903.3	782.9
2.5°	1355.0	1073.9	948.5	988.6	1350.0	1234.5	1124.1	1043.8	983.6	908.3	782.9
0°	1365.0	1063.9	948.5	1003.7	1390.1	1279.7	1129.2	1043.8	978.6	903.3	772.8



REPORT NUMBER: P722958
 CATALOG NUMBER: IFLD-L-SA7B-750-U-11

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	5.0	5.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	0.0	0.0
82.5°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
80°	10.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
77.5°	15.1	15.1	10.0	10.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
75°	25.1	20.1	20.1	15.1	15.1	10.0	5.0	5.0	5.0	5.0	5.0
72.5°	35.1	30.1	25.1	20.1	20.1	15.1	10.0	5.0	5.0	5.0	5.0
70°	45.2	40.1	30.1	25.1	25.1	20.1	15.1	10.0	5.0	5.0	5.0
67.5°	60.2	50.2	40.1	30.1	30.1	25.1	20.1	15.1	10.0	5.0	5.0
65°	75.3	60.2	50.2	40.1	35.1	30.1	25.1	20.1	15.1	5.0	5.0
62.5°	85.3	75.3	60.2	50.2	45.2	35.1	30.1	25.1	15.1	10.0	5.0
60°	100.4	85.3	70.3	60.2	55.2	45.2	35.1	30.1	20.1	15.1	5.0
57.5°	115.4	95.4	80.3	70.3	65.2	55.2	45.2	35.1	25.1	15.1	10.0
55°	130.5	110.4	90.3	85.3	75.3	65.2	55.2	40.1	30.1	20.1	10.0
52.5°	145.5	120.4	105.4	100.4	90.3	75.3	60.2	50.2	35.1	25.1	15.1
50°	165.6	135.5	120.4	115.4	100.4	85.3	70.3	60.2	45.2	30.1	15.1
47.5°	185.7	150.6	140.5	130.5	115.4	100.4	80.3	70.3	50.2	35.1	20.1
45°	200.7	175.6	160.6	150.6	130.5	115.4	95.4	80.3	55.2	40.1	20.1
42.5°	210.8	195.7	185.7	170.6	150.6	125.5	105.4	90.3	65.2	45.2	25.1
40°	235.9	220.8	205.8	190.7	170.6	140.5	120.4	100.4	75.3	50.2	25.1
37.5°	261.0	240.9	225.8	210.8	190.7	160.6	140.5	110.4	85.3	55.2	30.1
35°	286.1	266.0	245.9	230.8	210.8	185.7	155.6	125.5	95.4	60.2	35.1
32.5°	311.1	286.1	266.0	245.9	235.9	205.8	170.6	135.5	105.4	65.2	35.1
30°	336.2	306.1	286.1	271.0	261.0	230.8	190.7	150.6	115.4	75.3	40.1
27.5°	361.3	326.2	301.1	301.1	291.1	255.9	205.8	165.6	125.5	80.3	45.2
25°	386.4	346.3	336.2	331.2	326.2	281.0	225.8	180.7	130.5	90.3	45.2
22.5°	411.5	381.4	366.3	361.3	351.3	306.1	245.9	190.7	140.5	95.4	50.2
20°	451.7	421.6	401.5	386.4	381.4	336.2	266.0	205.8	150.6	95.4	50.2
17.5°	501.8	456.7	431.6	416.5	406.5	361.3	286.1	220.8	155.6	95.4	50.2
15°	547.0	496.8	461.7	441.6	431.6	391.4	301.1	225.8	160.6	95.4	50.2
12.5°	592.2	532.0	491.8	471.7	456.7	421.6	316.2	230.8	160.6	95.4	50.2
10°	632.3	567.1	526.9	496.8	476.8	431.6	321.2	235.9	160.6	95.4	50.2
7.5°	667.5	597.2	542.0	496.8	476.8	441.6	321.2	240.9	160.6	95.4	55.2
5°	672.5	597.2	537.0	496.8	481.8	446.6	326.2	240.9	160.6	90.3	50.2
2.5°	677.5	597.2	537.0	496.8	481.8	446.6	326.2	240.9	160.6	90.3	50.2
0°	672.5	592.2	532.0	496.8	481.8	446.6	326.2	240.9	155.6	85.3	50.2



REPORT NUMBER: P722958
 CATALOG NUMBER: IFLD-L-SA7B-750-U-11

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°
90°	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0
80°	5.0	0.0	0.0	0.0
77.5°	5.0	0.0	0.0	0.0
75°	5.0	5.0	0.0	0.0
72.5°	5.0	5.0	0.0	0.0
70°	5.0	5.0	0.0	0.0
67.5°	5.0	5.0	0.0	0.0
65°	5.0	5.0	0.0	0.0
62.5°	5.0	5.0	0.0	0.0
60°	5.0	5.0	0.0	0.0
57.5°	5.0	5.0	5.0	0.0
55°	5.0	5.0	5.0	0.0
52.5°	5.0	5.0	5.0	0.0
50°	5.0	5.0	5.0	0.0
47.5°	5.0	5.0	5.0	0.0
45°	5.0	5.0	5.0	0.0
42.5°	10.0	5.0	5.0	0.0
40°	10.0	5.0	5.0	0.0
37.5°	15.1	5.0	5.0	0.0
35°	15.1	5.0	5.0	0.0
32.5°	15.1	5.0	5.0	0.0
30°	15.1	5.0	5.0	0.0
27.5°	20.1	5.0	5.0	0.0
25°	20.1	5.0	5.0	0.0
22.5°	20.1	5.0	5.0	0.0
20°	20.1	5.0	5.0	0.0
17.5°	20.1	5.0	5.0	0.0
15°	25.1	5.0	5.0	0.0
12.5°	25.1	5.0	5.0	0.0
10°	25.1	5.0	5.0	0.0
7.5°	25.1	5.0	5.0	0.0
5°	25.1	5.0	5.0	0.0
2.5°	25.1	5.0	5.0	0.0
0°	25.1	5.0	5.0	0.0

(END OF REPORT)