

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P507852

Luminaire Tested: **UFLD-S-CA1-50-740-U-33**

Issue Date: 3/30/2021

Test Information

Test Method: LM-79-08
Report Number: P507852
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2101-110-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 3/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: UFLD-S-CA1-50-740-U-33
Description: UTILITY FLOOD SMALL, 3X3 OPTIC
Light Source: (2) 4000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	5788 lumens	Max Intensity:	29825.3 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 1°V
Efficacy:	112.0 lumens/watt		
Luminous Opening:	Rectangular (W 0.67' x L: 0.5' x H: 0')		

Beam Angle (50%):	21.6°H x 21.3°V	Field Angle (10%):	46.5°H x 46.6°V
Beam Lumens:	2417.3 lumens	Field Lumens:	5016.8 lumens
Beam Efficiency:	41.8%	Field Efficiency:	86.7%


Input Watts (W): 51.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P507852

CATALOG NUMBER: UFLD-S-CA1-50-740-U-33

Iso-Candela Plot





REPORT NUMBER: P507852

CATALOG NUMBER: UFLD-S-CA1-50-740-U-33


Lumen Table

90	1.0	2.8		3.2		2.3		1.0		2.3		3.2		2.8		1.0
80	1.0	2.8		3.2		2.3		1.0		2.3		3.2		2.8		1.0
70	0.9	0.4	0.3	0.3	0.3	0.5	0.5	0.2	0.2	0.5	0.5	0.3	0.3	0.3	0.4	0.9
60		0.2	0.1	0.2	0.4	0.6	0.5	0.3	0.3	0.5	0.6	0.4	0.2	0.1	0.2	
50	0.6	0.1	0.0	0.1	0.4	0.8	0.9	0.9	0.9	0.9	0.8	0.4	0.1	0.0	0.1	0.6
40		0.0	0.0	0.1	0.6	1.1	2.4	4.9	4.9	2.4	1.1	0.6	0.1	0.0	0.0	
30	0.4	0.0	0.0	0.1	0.6	5.7	33.2	64.8	64.8	33.2	5.7	0.6	0.1	0.0	0.0	0.4
20		0.0	0.0	0.1	1.6	31.9	117.5	244.7	244.7	117.5	31.9	1.6	0.1	0.0	0.0	
10	0.4	0.0	0.0	0.1	3.9	60.3	232.6	653.3	653.3	232.6	60.3	3.9	0.1	0.0	0.0	0.4
0		0.0	0.0	0.1	3.9	60.3	224.7	621.4	621.4	224.7	60.3	3.9	0.1	0.0	0.0	
-10	0.4	0.0	0.0	0.1	3.9	60.3	224.7	621.4	621.4	224.7	60.3	3.9	0.1	0.0	0.0	0.4
-20		0.0	0.0	0.1	1.6	31.4	116.0	222.2	222.2	116.0	31.4	1.6	0.1	0.0	0.0	
-30	0.4	0.0	0.0	0.1	1.6	31.4	116.0	222.2	222.2	116.0	31.4	1.6	0.1	0.0	0.0	0.4
-40		0.0	0.0	0.1	0.7	5.2	32.6	66.1	66.1	32.6	5.2	0.7	0.1	0.0	0.0	
-50	0.6	0.0	0.0	0.1	0.5	1.1	2.3	4.8	4.8	2.3	1.1	0.5	0.1	0.0	0.0	0.6
-60		0.1	0.0	0.1	0.4	0.7	0.9	0.9	0.9	0.9	0.7	0.4	0.1	0.0	0.1	
-70	0.9	0.2	0.1	0.2	0.4	0.5	0.5	0.3	0.3	0.5	0.5	0.4	0.2	0.1	0.2	0.9
-80		0.4	0.3	0.3	0.4	0.5	0.5	0.2	0.2	0.5	0.5	0.4	0.3	0.3	0.4	
-90	1.0	2.8		3.2		2.3		1.0		2.3		3.2		2.8		1.0

REPORT NUMBER: P507852

CATALOG NUMBER: UFLD-S-CA1-50-740-U-33

Luminous Intensity Polar Plot




— Vertical Distribution Through 0-Deg - - - Horizontal Distribution Through 1-Deg

REPORT NUMBER: P507852

CATALOG NUMBER: UFLD-S-CA1-50-740-U-33

Luminous Intensity Plot



Beam:
 H Angle: 21.6°
 V Angle: 21.3°
 Lumens: 2417.3
 Efficiency: 41.8%

Field:
 H Angle: 46.5°
 V Angle: 46.6°
 Lumens: 5016.8
 Efficiency: 86.7%

Spill:
 Lumens: 771.2
 Efficiency: 13.3%

- Vertical Distribution through 0-Deg
- - - Horizontal Distribution through 1-Deg



REPORT NUMBER: P507852

CATALOG NUMBER: UFLD-S-CA1-50-740-U-33

FIELD
 BEAM

CANDELA DISTRIBUTION:

	0°	1°	3°	5°	7°	9°	11°	13°	15°	17°	19.5°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	3.0	14.0	18.9	13.0	12.0	14.0	16.9	20.9	24.9	31.9
75°	1.0	2.0	4.0	8.0	11.0	15.0	18.9	19.9	18.9	16.9	14.0
65°	4.0	4.0	5.0	6.0	8.0	10.0	12.0	14.0	16.9	18.9	20.9
55°	5.0	5.0	6.0	6.0	8.0	9.0	11.0	12.0	14.0	15.0	16.9
47.5°	23.9	23.9	24.9	23.9	23.9	24.9	25.9	25.9	24.9	24.9	22.9
42.5°	35.9	35.9	35.9	35.9	36.9	36.9	37.9	37.9	38.9	38.9	37.9
37.5°	42.9	42.9	42.9	42.9	43.9	43.9	42.9	42.9	42.9	42.9	41.9
33°	133.6	144.5	135.6	127.6	103.7	85.7	83.7	75.8	63.8	54.8	45.9
29°	937.0	950.0	893.2	842.3	757.6	643.0	528.3	394.7	269.1	155.5	98.7
25.5°	2037.5	2066.4	2010.6	1911.9	1795.3	1595.9	1385.6	1159.3	884.2	645.9	397.7
22.5°	3235.7	3217.8	3183.9	3012.4	2843.0	2606.7	2343.6	2023.6	1668.7	1304.9	884.2
19.5°	4531.6	4585.4	4478.8	4268.5	3997.3	3682.3	3338.4	2975.6	2542.9	2095.3	1530.1
17°	6233.2	6096.6	5988.0	5619.2	5228.4	4776.8	4271.4	3746.1	3275.6	2769.2	2109.3
15°	8283.7	8517.0	8133.2	7419.4	6592.1	5850.4	5186.5	4463.8	3875.7	3289.6	2570.8
13°	11996.9	11708.8	11238.3	10352.1	8723.3	7520.1	6283.1	5347.0	4480.8	3790.0	2991.5
11°	15310.4	15310.4	14591.7	13552.0	11757.7	9717.2	7668.7	6233.2	5182.5	4292.4	3370.3
9°	19046.5	19134.3	17796.5	16292.3	14536.9	12115.5	9565.6	7380.6	5895.3	4799.8	3710.2
7°	24690.6	24357.7	22771.7	19743.3	16883.4	14497.0	11482.6	8629.6	6584.1	5260.3	4031.2
5°	28184.5	27786.8	26585.6	24201.2	19992.5	15972.3	13135.3	9904.6	7290.9	5644.1	4287.4
3°	28835.5	28398.9	28124.7	26323.4	22501.6	17295.1	14124.2	10759.8	7772.3	5914.2	4468.8
1°	29825.3	29381.7	28540.4	27246.5	23482.5	18061.7	14558.8	11158.6	8000.6	6068.7	4559.5
0°	29427.6	28437.7	28609.2	27292.4	23529.3	18046.7	14551.8	11151.6	7988.6	6074.7	4568.5
-1°	28728.8	28316.1	28647.1	27003.3	23297.1	17859.3	14446.1	11022.0	7920.9	6041.8	4557.5
-3°	28859.4	28752.7	27961.2	25703.4	21579.5	16745.8	13762.3	10339.2	7548.0	5870.4	4452.9
-5°	27027.2	26701.2	25493.1	22717.9	18255.1	15250.6	12339.8	9224.7	7000.8	5567.3	4277.4
-7°	22703.9	22006.1	20834.9	17814.5	15593.5	13262.9	10521.6	8022.5	6354.8	5193.5	4028.2
-9°	16701.0	16517.6	16021.1	14938.6	13036.6	10836.6	8614.7	6971.9	5704.9	4720.0	3729.2
-11°	13348.6	13507.1	12581.1	11668.0	10130.8	8450.2	7180.2	6036.8	5099.8	4242.5	3392.2
-13°	9926.5	9867.7	9403.2	8716.3	7800.2	6879.2	6029.9	5204.5	4461.8	3796.9	3019.4
-15°	7443.4	7457.3	7292.9	6880.2	6337.9	5707.9	5100.8	4447.9	3879.7	3309.5	2582.8
-17°	6012.9	5930.2	5814.5	5568.3	5197.5	4757.9	4258.5	3799.9	3312.5	2801.1	2117.3
-19.5°	4586.4	4595.4	4464.8	4305.3	4055.1	3796.0	3436.1	3041.3	2601.7	2112.3	1485.3
-22.5°	3397.2	3362.3	3296.5	3170.9	2934.7	2674.5	2389.4	2033.5	1671.7	1292.9	840.3
-25.5°	2098.3	2150.2	2103.3	1994.7	1812.2	1573.0	1347.7	1072.6	838.3	602.1	350.9
-29°	891.2	904.1	856.3	816.4	715.7	594.1	477.5	353.9	236.3	131.6	90.7
-33°	158.5	141.6	137.6	125.6	102.7	89.7	84.7	70.8	61.8	56.8	49.8
-37.5°	49.8	49.8	50.8	50.8	49.8	49.8	48.8	48.8	47.8	47.8	45.9
-42.5°	39.9	38.9	39.9	39.9	38.9	38.9	38.9	37.9	36.9	36.9	33.9
-47.5°	20.9	20.9	20.9	21.9	21.9	22.9	21.9	21.9	22.9	20.9	19.9
-55°	6.0	6.0	6.0	7.0	8.0	10.0	11.0	13.0	14.0	15.9	17.9
-65°	4.0	4.0	5.0	6.0	8.0	11.0	12.0	14.0	16.9	19.9	20.9
-75°	2.0	2.0	4.0	8.0	11.0	15.0	18.9	19.9	18.9	16.9	14.0
-85°	0.0	3.0	14.0	18.9	13.0	12.0	15.0	16.9	20.9	24.9	31.9
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P507852

CATALOG NUMBER: UFLD-S-CA1-50-740-U-33

CANDELA DISTRIBUTION (continued):

	22.5°	25.5°	29°	33°	37.5°	42.5°	47.5°	55°	65°	75°	85°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	39.9	46.9	52.8	58.8	63.8	68.8	69.8	67.8	61.8	55.8	52.8
75°	13.0	13.0	14.0	15.9	18.9	22.9	30.9	41.9	50.8	53.8	52.8
65°	20.9	18.9	15.0	13.0	12.0	12.0	11.0	15.9	29.9	46.9	51.8
55°	19.9	20.9	19.9	16.9	13.0	8.0	5.0	3.0	11.0	35.9	51.8
47.5°	21.9	21.9	20.9	18.9	14.0	8.0	3.0	0.0	5.0	27.9	51.8
42.5°	34.9	31.9	27.9	19.9	14.0	7.0	1.0	0.0	2.0	23.9	50.8
37.5°	40.9	38.9	34.9	26.9	15.9	6.0	0.0	0.0	0.0	18.9	50.8
33°	41.9	39.9	35.9	30.9	17.9	5.0	0.0	0.0	0.0	15.9	50.8
29°	56.8	40.9	33.9	28.9	19.9	7.0	0.0	0.0	0.0	14.0	50.8
25.5°	171.5	69.8	37.9	26.9	18.9	7.0	0.0	0.0	0.0	12.0	50.8
22.5°	449.6	178.4	52.8	25.9	16.9	7.0	0.0	0.0	0.0	10.0	50.8
19.5°	882.2	405.7	105.7	28.9	15.9	7.0	0.0	0.0	0.0	9.0	50.8
17°	1321.8	663.9	198.4	35.9	15.0	7.0	0.0	0.0	0.0	8.0	50.8
15°	1675.7	900.1	298.1	44.9	15.0	6.0	0.0	0.0	0.0	7.0	50.8
13°	2042.5	1169.3	417.7	58.8	15.0	6.0	0.0	0.0	0.0	6.0	50.8
11°	2366.5	1402.5	538.3	74.8	14.0	6.0	0.0	0.0	0.0	6.0	50.8
9°	2651.6	1631.8	656.9	93.7	14.0	6.0	0.0	0.0	0.0	5.0	50.8
7°	2892.8	1817.2	759.6	115.6	14.0	5.0	0.0	0.0	0.0	5.0	50.8
5°	3078.2	1967.8	843.3	134.6	14.0	5.0	0.0	0.0	0.0	5.0	50.8
3°	3196.9	2059.5	903.1	147.5	14.0	5.0	0.0	0.0	0.0	5.0	50.8
1°	3263.6	2113.3	932.0	153.5	14.0	5.0	0.0	0.0	0.0	4.0	50.8
0°	3274.6	2119.3	936.0	154.5	14.0	5.0	0.0	0.0	0.0	4.0	50.8
-1°	3266.6	2114.3	931.0	152.5	14.0	5.0	0.0	0.0	0.0	5.0	50.8
-3°	3206.8	2063.5	902.1	145.5	15.0	5.0	0.0	0.0	0.0	5.0	50.8
-5°	3076.2	1959.8	842.3	129.6	15.9	6.0	0.0	0.0	0.0	5.0	50.8
-7°	2910.8	1809.3	755.6	111.6	16.9	6.0	0.0	0.0	0.0	5.0	50.8
-9°	2666.5	1620.9	645.9	91.7	16.9	7.0	0.0	0.0	0.0	6.0	50.8
-11°	2376.5	1390.6	521.3	72.8	17.9	8.0	0.0	0.0	0.0	6.0	50.8
-13°	2046.5	1144.4	398.7	55.8	18.9	8.0	0.0	0.0	0.0	7.0	50.8
-15°	1664.7	881.2	284.1	44.9	19.9	9.0	0.0	0.0	0.0	8.0	50.8
-17°	1282.9	630.0	183.4	37.9	19.9	9.0	0.0	0.0	0.0	9.0	50.8
-19.5°	829.4	364.8	96.7	30.9	19.9	9.0	0.0	0.0	0.0	10.0	50.8
-22.5°	402.7	156.5	50.8	28.9	18.9	8.0	0.0	0.0	0.0	11.0	50.8
-25.5°	145.5	64.8	39.9	29.9	18.9	8.0	0.0	0.0	0.0	13.0	50.8
-29°	55.8	43.9	37.9	30.9	16.9	5.0	0.0	0.0	0.0	15.0	50.8
-33°	45.9	42.9	36.9	29.9	14.0	4.0	0.0	0.0	0.0	17.9	51.8
-37.5°	42.9	38.9	31.9	22.9	13.0	5.0	0.0	0.0	0.0	20.9	51.8
-42.5°	30.9	27.9	23.9	18.9	13.0	7.0	2.0	0.0	2.0	25.9	51.8
-47.5°	18.9	19.9	19.9	17.9	14.0	9.0	4.0	0.0	6.0	29.9	51.8
-55°	19.9	20.9	19.9	16.9	13.0	9.0	6.0	4.0	13.0	37.9	52.8
-65°	20.9	18.9	15.9	13.0	13.0	13.0	12.0	15.9	30.9	48.8	52.8
-75°	13.0	13.0	15.0	16.9	19.9	23.9	30.9	41.9	51.8	56.8	53.8
-85°	39.9	46.9	52.8	58.8	63.8	67.8	69.8	67.8	61.8	57.8	53.8
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P507852

CATALOG NUMBER: UFLD-S-CA1-50-740-U-33

CANDELA DISTRIBUTION (continued):

	90°
90°	0.0
85°	0.0
75°	0.0
65°	0.0
55°	0.0
47.5°	0.0
42.5°	0.0
37.5°	0.0
33°	0.0
29°	0.0
25.5°	0.0
22.5°	0.0
19.5°	0.0
17°	0.0
15°	0.0
13°	0.0
11°	0.0
9°	0.0
7°	0.0
5°	0.0
3°	0.0
1°	0.0
0°	0.0
-1°	0.0
-3°	0.0
-5°	0.0
-7°	0.0
-9°	0.0
-11°	0.0
-13°	0.0
-15°	0.0
-17°	0.0
-19.5°	0.0
-22.5°	0.0
-25.5°	0.0
-29°	0.0
-33°	0.0
-37.5°	0.0
-42.5°	0.0
-47.5°	0.0
-55°	0.0
-65°	0.0
-75°	0.0
-85°	0.0
-90°	0.0

(END OF REPORT)