

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P507853

Luminaire Tested: **UFLD-S-CA1-50-750-U-33**

Issue Date: 3/30/2021

Test Information

Test Method: LM-79-08
Report Number: P507853
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2101-110-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 3/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: UFLD-S-CA1-50-750-U-33
Description: UTILITY FLOOD SMALL, 3X3 OPTIC
Light Source: (2) 5000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5891 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 0.5' x H: 0')

NEMA Type: 4H x 4V
Max Intensity: 30356.1 candela
Max Intensity Angle: 0°H x 1°V

Beam Angle (50%): 21.6°H x 21.3°V
Beam Lumens: 2460.3 lumens
Beam Efficiency: 41.8%

Field Angle (10%): 46.5°H x 46.6°V
Field Lumens: 5106 lumens
Field Efficiency: 86.7%


Input Watts (W): 51.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P507853

CATALOG NUMBER: UFLD-S-CA1-50-750-U-33

Iso-Candela Plot





REPORT NUMBER: P507853

CATALOG NUMBER: UFLD-S-CA1-50-750-U-33


Lumen Table

90	1.0	2.8		3.3		2.3		1.0	2.3		3.3		2.8		1.0				
80	1.0	2.8		3.3		2.3		1.0	2.3		3.3		2.8		1.0				
70	0.9	0.4	0.3	0.3	0.3	0.5	0.5	0.2	0.2	0.5	0.5	0.3	0.3	0.3	0.4	0.9			
60		0.2	0.1	0.2	0.4	0.6	0.5	0.3	0.3	0.5	0.6	0.4	0.2	0.1	0.2				
50	0.6	0.1	0.0	0.1	0.4	0.8	0.9	0.9	0.9	0.9	0.8	0.4	0.1	0.0	0.1	0.6			
40		0.0	0.0	0.1	0.6	1.1	2.4	5.0	5.0	2.4	1.1	0.6	0.1	0.0	0.0				
30	0.4	0.0	0.0	0.1	0.6	5.8	33.8	65.9	65.9	33.8	5.8	0.6	0.1	0.0	0.0	0.4			
20		0.0	0.0	0.1	1.6	32.4	119.6	249.0	249.0	119.6	32.4	1.6	0.1	0.0	0.0				
10	0.4	0.0	0.0	0.1	3.9	61.4	236.8	664.9	664.9	236.8	61.4	3.9	0.1	0.0	0.0	0.4			
0		0.0	0.0	0.1	3.9	61.4	228.7	632.4	632.4	228.7	61.4	3.9	0.1	0.0	0.0				
-10	0.4	0.0	0.0	0.1	3.9	61.4	228.7	632.4	632.4	228.7	61.4	3.9	0.1	0.0	0.0	0.4			
-20		0.0	0.0	0.1	1.6	32.0	118.1	226.2	226.2	118.1	32.0	1.6	0.1	0.0	0.0				
-30	0.4	0.0	0.0	0.1	1.6	32.0	118.1	226.2	226.2	118.1	32.0	1.6	0.1	0.0	0.0	0.4			
-40		0.0	0.0	0.1	0.7	5.3	33.2	67.3	67.3	33.2	5.3	0.7	0.1	0.0	0.0				
-50	0.6	0.0	0.0	0.1	0.5	1.2	2.4	4.9	4.9	2.4	1.2	0.5	0.1	0.0	0.0	0.6			
-60		0.1	0.0	0.1	0.4	0.7	0.9	0.9	0.9	0.9	0.7	0.4	0.1	0.0	0.1				
-70	0.9	0.2	0.1	0.2	0.4	0.6	0.5	0.3	0.3	0.5	0.6	0.4	0.2	0.1	0.2	0.9			
-80		0.4	0.3	0.3	0.4	0.5	0.5	0.2	0.2	0.5	0.5	0.4	0.3	0.3	0.4				
-90	1.0	2.8		3.3		2.4		1.0	2.4		3.3		2.8		1.0				
	-90	-80	-70	-60	-50	-40	-30	-20	-10	0	10	20	30	40	50	60	70	80	90

REPORT NUMBER: P507853

CATALOG NUMBER: UFLD-S-CA1-50-750-U-33


Luminous Intensity Polar Plot



REPORT NUMBER: P507853

CATALOG NUMBER: UFLD-S-CA1-50-750-U-33

Luminous Intensity Plot



Beam:
H Angle: 21.6°
V Angle: 21.3°
Lumens: 2460.3
Efficiency: 41.8%

Field:
H Angle: 46.5°
V Angle: 46.6°
Lumens: 5106
Efficiency: 86.7%

Spill:
Lumens: 785
Efficiency: 13.3%

— Vertical Distribution through 0-Deg
- - Horizontal Distribution through 1-Deg



REPORT NUMBER: P507853

CATALOG NUMBER: UFLD-S-CA1-50-750-U-33

FIELD
 BEAM

CANDELA DISTRIBUTION:

	0°	1°	3°	5°	7°	9°	11°	13°	15°	17°	19.5°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	3.0	14.2	19.3	13.2	12.2	14.2	17.2	21.3	25.4	32.5
75°	1.0	2.0	4.1	8.1	11.2	15.2	19.3	20.3	19.3	17.2	14.2
65°	4.1	4.1	5.1	6.1	8.1	10.1	12.2	14.2	17.2	19.3	21.3
55°	5.1	5.1	6.1	6.1	8.1	9.1	11.2	12.2	14.2	15.2	17.2
47.5°	24.3	24.3	25.4	24.3	24.3	25.4	26.4	26.4	25.4	25.4	23.3
42.5°	36.5	36.5	36.5	36.5	37.5	37.5	38.6	38.6	39.6	39.6	38.6
37.5°	43.6	43.6	43.6	43.6	44.6	44.6	43.6	43.6	43.6	43.6	42.6
33°	136.0	147.1	138.0	129.9	105.5	87.3	85.2	77.1	64.9	55.8	46.7
29°	953.7	966.9	909.1	857.3	771.1	654.4	537.7	401.8	273.9	158.3	100.4
25.5°	2073.8	2103.2	2046.4	1946.0	1827.2	1624.3	1410.3	1180.0	899.9	657.4	404.8
22.5°	3293.3	3275.0	3240.6	3066.0	2893.6	2653.1	2385.3	2059.6	1698.4	1328.1	899.9
19.5°	4612.3	4667.0	4558.5	4344.4	4068.4	3747.8	3397.8	3028.5	2588.2	2132.6	1557.4
17°	6344.1	6205.1	6094.6	5719.2	5321.4	4861.8	4347.5	3812.8	3333.9	2818.5	2146.8
15°	8431.1	8668.5	8277.9	7551.5	6709.4	5954.5	5278.8	4543.3	3944.7	3348.1	2616.6
13°	12210.4	11917.2	11438.3	10536.4	8878.5	7654.0	6394.9	5442.2	4560.5	3857.4	3044.7
11°	15582.9	15582.9	14851.3	13793.1	11966.9	9890.1	7805.1	6344.1	5274.8	4368.8	3430.3
9°	19385.5	19474.8	18113.2	16582.2	14795.5	12331.1	9735.9	7511.9	6000.2	4885.2	3776.2
7°	25130.0	24791.1	23177.0	20094.7	17183.9	14755.0	11686.9	8783.2	6701.3	5353.9	4102.9
5°	28686.1	28281.3	27058.7	24631.9	20348.3	16256.5	13369.1	10080.8	7420.6	5744.5	4363.7
3°	29348.6	28904.2	28625.2	26791.9	22902.0	17602.9	14375.5	10951.3	7910.6	6019.5	4548.3
1°	30356.1	29904.6	29048.3	27731.4	23900.3	18383.1	14817.9	11357.2	8143.0	6176.7	4640.7
0°	29951.3	28943.8	29118.3	27778.1	23948.0	18367.9	14810.8	11350.1	8130.8	6182.8	4649.8
-1°	29240.1	28820.0	29156.9	27483.8	23711.6	18177.1	14703.2	11218.2	8061.8	6149.3	4638.6
-3°	29373.0	29264.4	28458.8	26160.8	21963.5	17043.8	14007.2	10523.2	7682.4	5974.8	4532.1
-5°	27508.2	27176.4	25946.7	23122.2	18579.9	15522.0	12559.4	9388.9	7125.4	5666.4	4353.5
-7°	23108.0	22397.8	21205.6	18131.5	15871.0	13498.9	10708.8	8165.3	6467.9	5285.9	4099.9
-9°	16998.2	16811.5	16306.3	15204.4	13268.6	11029.4	8768.0	7095.9	5806.4	4804.0	3795.5
-11°	13586.2	13747.5	12805.0	11875.6	10311.1	8600.6	7308.0	6144.3	5190.6	4318.0	3452.6
-13°	10103.1	10043.3	9570.5	8871.4	7939.0	7001.6	6137.2	5297.1	4541.2	3864.5	3073.1
-15°	7575.8	7590.0	7422.6	7002.6	6450.7	5809.5	5191.6	4527.0	3948.7	3368.4	2628.8
-17°	6119.9	6035.7	5918.0	5667.4	5290.0	4842.6	4334.3	3867.6	3371.4	2851.0	2155.0
-19.5°	4668.1	4677.2	4544.3	4381.9	4127.3	3863.5	3497.2	3095.5	2648.0	2149.9	1511.7
-22.5°	3457.7	3422.2	3355.2	3227.4	2986.9	2722.1	2431.9	2069.7	1701.4	1315.9	855.3
-25.5°	2135.7	2188.4	2140.8	2030.2	1844.5	1601.0	1371.7	1091.7	853.3	612.8	357.1
-29°	907.0	920.2	871.5	830.9	728.5	604.7	486.0	360.2	240.5	133.9	92.3
-33°	161.3	144.1	140.0	127.8	104.5	91.3	86.2	72.0	62.9	57.8	50.7
-37.5°	50.7	50.7	51.7	51.7	50.7	50.7	49.7	49.7	48.7	48.7	46.7
-42.5°	40.6	39.6	40.6	40.6	39.6	39.6	39.6	38.6	37.5	37.5	34.5
-47.5°	21.3	21.3	21.3	22.3	22.3	23.3	22.3	22.3	23.3	21.3	20.3
-55°	6.1	6.1	6.1	7.1	8.1	10.1	11.2	13.2	14.2	16.2	18.3
-65°	4.1	4.1	5.1	6.1	8.1	11.2	12.2	14.2	17.2	20.3	21.3
-75°	2.0	2.0	4.1	8.1	11.2	15.2	19.3	20.3	19.3	17.2	14.2
-85°	0.0	3.0	14.2	19.3	13.2	12.2	15.2	17.2	21.3	25.4	32.5
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P507853

CATALOG NUMBER: UFLD-S-CA1-50-750-U-33

CANDELA DISTRIBUTION (continued):

	22.5°	25.5°	29°	33°	37.5°	42.5°	47.5°	55°	65°	75°	85°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	40.6	47.7	53.8	59.9	64.9	70.0	71.0	69.0	62.9	56.8	53.8
75°	13.2	13.2	14.2	16.2	19.3	23.3	31.5	42.6	51.7	54.8	53.8
65°	21.3	19.3	15.2	13.2	12.2	12.2	11.2	16.2	30.4	47.7	52.8
55°	20.3	21.3	20.3	17.2	13.2	8.1	5.1	3.0	11.2	36.5	52.8
47.5°	22.3	22.3	21.3	19.3	14.2	8.1	3.0	0.0	5.1	28.4	52.8
42.5°	35.5	32.5	28.4	20.3	14.2	7.1	1.0	0.0	2.0	24.3	51.7
37.5°	41.6	39.6	35.5	27.4	16.2	6.1	0.0	0.0	0.0	19.3	51.7
33°	42.6	40.6	36.5	31.5	18.3	5.1	0.0	0.0	0.0	16.2	51.7
29°	57.8	41.6	34.5	29.4	20.3	7.1	0.0	0.0	0.0	14.2	51.7
25.5°	174.5	71.0	38.6	27.4	19.3	7.1	0.0	0.0	0.0	12.2	51.7
22.5°	457.6	181.6	53.8	26.4	17.2	7.1	0.0	0.0	0.0	10.1	51.7
19.5°	897.9	412.9	107.5	29.4	16.2	7.1	0.0	0.0	0.0	9.1	51.7
17°	1345.3	675.7	201.9	36.5	15.2	7.1	0.0	0.0	0.0	8.1	51.7
15°	1705.5	916.2	303.4	45.7	15.2	6.1	0.0	0.0	0.0	7.1	51.7
13°	2078.9	1190.1	425.1	59.9	15.2	6.1	0.0	0.0	0.0	6.1	51.7
11°	2408.6	1427.5	547.9	76.1	14.2	6.1	0.0	0.0	0.0	6.1	51.7
9°	2698.8	1660.9	668.6	95.4	14.2	6.1	0.0	0.0	0.0	5.1	51.7
7°	2944.3	1849.6	773.1	117.7	14.2	5.1	0.0	0.0	0.0	5.1	51.7
5°	3133.0	2002.8	858.3	137.0	14.2	5.1	0.0	0.0	0.0	5.1	51.7
3°	3253.7	2096.1	919.2	150.2	14.2	5.1	0.0	0.0	0.0	5.1	51.7
1°	3321.7	2150.9	948.6	156.2	14.2	5.1	0.0	0.0	0.0	4.1	51.7
0°	3332.9	2157.0	952.7	157.3	14.2	5.1	0.0	0.0	0.0	4.1	51.7
-1°	3324.8	2151.9	947.6	155.2	14.2	5.1	0.0	0.0	0.0	5.1	51.7
-3°	3263.9	2100.2	918.2	148.1	15.2	5.1	0.0	0.0	0.0	5.1	51.7
-5°	3131.0	1994.7	857.3	131.9	16.2	6.1	0.0	0.0	0.0	5.1	51.7
-7°	2962.6	1841.5	769.0	113.6	17.2	6.1	0.0	0.0	0.0	5.1	51.7
-9°	2714.0	1649.7	657.4	93.3	17.2	7.1	0.0	0.0	0.0	6.1	51.7
-11°	2418.7	1415.3	530.6	74.1	18.3	8.1	0.0	0.0	0.0	6.1	51.7
-13°	2082.9	1164.7	405.8	56.8	19.3	8.1	0.0	0.0	0.0	7.1	51.7
-15°	1694.3	896.9	289.2	45.7	20.3	9.1	0.0	0.0	0.0	8.1	51.7
-17°	1305.8	641.2	186.7	38.6	20.3	9.1	0.0	0.0	0.0	9.1	51.7
-19.5°	844.1	371.3	98.4	31.5	20.3	9.1	0.0	0.0	0.0	10.1	51.7
-22.5°	409.9	159.3	51.7	29.4	19.3	8.1	0.0	0.0	0.0	11.2	51.7
-25.5°	148.1	65.9	40.6	30.4	19.3	8.1	0.0	0.0	0.0	13.2	51.7
-29°	56.8	44.6	38.6	31.5	17.2	5.1	0.0	0.0	0.0	15.2	51.7
-33°	46.7	43.6	37.5	30.4	14.2	4.1	0.0	0.0	0.0	18.3	52.8
-37.5°	43.6	39.6	32.5	23.3	13.2	5.1	0.0	0.0	0.0	21.3	52.8
-42.5°	31.5	28.4	24.3	19.3	13.2	7.1	2.0	0.0	2.0	26.4	52.8
-47.5°	19.3	20.3	20.3	18.3	14.2	9.1	4.1	0.0	6.1	30.4	52.8
-55°	20.3	21.3	20.3	17.2	13.2	9.1	6.1	4.1	13.2	38.6	53.8
-65°	21.3	19.3	16.2	13.2	13.2	13.2	12.2	16.2	31.5	49.7	53.8
-75°	13.2	13.2	15.2	17.2	20.3	24.3	31.5	42.6	52.8	57.8	54.8
-85°	40.6	47.7	53.8	59.9	64.9	69.0	71.0	69.0	62.9	58.8	54.8
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P507853

CATALOG NUMBER: UFLD-S-CA1-50-750-U-33

CANDELA DISTRIBUTION (continued):

	90°
90°	0.0
85°	0.0
75°	0.0
65°	0.0
55°	0.0
47.5°	0.0
42.5°	0.0
37.5°	0.0
33°	0.0
29°	0.0
25.5°	0.0
22.5°	0.0
19.5°	0.0
17°	0.0
15°	0.0
13°	0.0
11°	0.0
9°	0.0
7°	0.0
5°	0.0
3°	0.0
1°	0.0
0°	0.0
-1°	0.0
-3°	0.0
-5°	0.0
-7°	0.0
-9°	0.0
-11°	0.0
-13°	0.0
-15°	0.0
-17°	0.0
-19.5°	0.0
-22.5°	0.0
-25.5°	0.0
-29°	0.0
-33°	0.0
-37.5°	0.0
-42.5°	0.0
-47.5°	0.0
-55°	0.0
-65°	0.0
-75°	0.0
-85°	0.0
-90°	0.0

(END OF REPORT)