

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P623062

Luminaire Tested: **IFLD-S-SA6C-735-U-33**

Issue Date: 10/13/2022

Test Information

Test Method: LM-79-2019
Report Number: P623062
Test Lab: INNOVATION CENTER(G2)
Issue Date: 10/13/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: IFLD-S-SA6C-735-U-33
Description: Infrastructure Flood – Middle Tier Light Square Luminaire w/ Nema 3 distribution lens
Light Source: (96) 3500K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A	NEMA Type:	3H x 3V
Luminaire Lumens:	42643 lumens	Max Intensity:	396800 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	132.6 lumens/watt		
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')		


Beam Angle (50%):	13.8°H x 13.8°V	Field Angle (10%):	31.4°H x 31.4°V
Beam Lumens:	9324.8 lumens	Field Lumens:	21712.1 lumens
Beam Efficiency:	21.9%	Field Efficiency:	50.9%

Input Watts (W): 321.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P623062
CATALOG NUMBER: IFLD-S-SA6C-735-U-33

Iso-Candela Plot






REPORT NUMBER: P623062
 CATALOG NUMBER: IFLD-S-SA6C-735-U-33

Lumen Table

90	0.7	5.5		14.6		23.8		27.7		23.8		14.6		5.5		0.7
80	0.7	5.5		14.6		23.8		27.7		23.8		14.6		5.5		0.7
70	2.5	2.8	5.9	9.8	13.9	17.6	20.3	21.7	21.7	20.3	17.6	13.9	9.8	5.9	2.8	2.5
60		4.4	9.1	14.8	20.4	25.4	29.2	31.3	31.3	29.2	25.4	20.4	14.8	9.1	4.4	
50	4.6	5.9	12.0	18.9	26.2	33.7	40.7	45.1	45.1	40.7	33.7	26.2	18.9	12.0	5.9	4.6
40		7.3	14.3	22.7	33.2	47.5	65.0	79.8	79.8	65.0	47.5	33.2	22.7	14.3	7.3	
30	6.1	8.3	16.1	26.3	43.0	76.0	155.1	265.4	265.4	155.1	76.0	43.0	26.3	16.1	8.3	6.1
20		9.0	17.4	29.9	55.3	146.2	525.8	1305.6	1305.6	525.8	146.2	55.3	29.9	17.4	9.0	
10	6.7	9.3	18.1	32.2	66.1	243.6	1272.2	5585.9	5585.9	1272.2	243.6	66.1	32.2	18.1	9.3	6.7
0		9.3	18.1	32.2	66.1	243.6	1272.2	5585.9	5585.9	1272.2	243.6	66.1	32.2	18.1	9.3	
-10	6.1	9.0	17.4	29.9	55.3	146.2	525.8	1305.6	1305.6	525.8	146.2	55.3	29.9	17.4	9.0	6.1
-20		8.3	16.1	26.3	43.0	76.0	155.1	265.4	265.4	155.1	76.0	43.0	26.3	16.1	8.3	
-30	4.6	7.3	14.3	22.7	33.2	47.5	65.0	79.8	79.8	65.0	47.5	33.2	22.7	14.3	7.3	4.6
-40		5.9	12.0	18.9	26.2	33.7	40.7	45.1	45.1	40.7	33.7	26.2	18.9	12.0	5.9	
-50	2.5	4.4	9.1	14.8	20.4	25.4	29.2	31.3	31.3	29.2	25.4	20.4	14.8	9.1	4.4	2.5
-60		2.8	5.9	9.8	13.9	17.6	20.3	21.7	21.7	20.3	17.6	13.9	9.8	5.9	2.8	
-70	0.7	5.5		14.6		23.8		27.7		23.8		14.6		5.5		0.7
-80		5.5		14.6		23.8		27.7		23.8		14.6		5.5		
-90	0.7	5.5		14.6		23.8		27.7		23.8		14.6		5.5		0.7

REPORT NUMBER: P623062
CATALOG NUMBER: IFLD-S-SA6C-735-U-33


Luminous Intensity Polar Plot



— Vertical Distribution Through 0-Deg - - - Horizontal Distribution Through 0-Deg

REPORT NUMBER: P623062
 CATALOG NUMBER: IFLD-S-SA6C-735-U-33

Luminous Intensity Plot



Beam:
 H Angle: 13.8°
 V Angle: 13.8°
 Lumens: 9324.8
 Efficiency: 21.9%

Field:
 H Angle: 31.4°
 V Angle: 31.4°
 Lumens: 21712.1
 Efficiency: 50.9%

Spill:
 Lumens: 20930.9
 Efficiency: 49.1%

— Vertical Distribution through 0-Deg
 - - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P623062
 CATALOG NUMBER: IFLD-S-SA6C-735-U-33

FIELD
 BEAM

CANDELA DISTRIBUTION:

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	35.5	35.5	35.5	35.5	35.5	35.5	35.5	35.5	35.5	31.1	31.1
85°	79.9	79.9	79.9	79.9	79.9	79.9	75.4	75.4	75.4	71.0	71.0
82.5°	133.1	133.1	133.1	133.1	128.7	128.7	128.7	124.2	124.2	119.8	119.8
80°	204.1	204.1	204.1	204.1	199.6	195.2	195.2	190.8	186.3	181.9	177.5
77.5°	279.5	279.5	279.5	275.1	275.1	270.6	266.2	261.7	257.3	248.4	244.0
75°	368.2	368.2	368.2	363.8	359.3	354.9	350.5	341.6	337.2	328.3	319.4
72.5°	461.4	461.4	461.4	456.9	452.5	443.6	439.2	430.3	421.4	408.1	399.3
70°	550.1	550.1	550.1	545.7	536.8	532.4	523.5	514.6	505.7	492.4	479.1
67.5°	638.8	638.8	638.8	630.0	625.5	621.1	612.2	598.9	590.0	576.7	559.0
65°	723.1	723.1	718.7	714.2	709.8	700.9	692.1	683.2	669.9	656.6	638.8
62.5°	807.4	807.4	803.0	798.5	794.1	785.2	771.9	763.0	745.3	732.0	714.2
60°	878.4	878.4	874.0	869.5	865.1	856.2	847.3	834.0	820.7	807.4	789.7
57.5°	953.8	953.8	949.4	944.9	936.1	927.2	918.3	905.0	887.3	869.5	856.2
55°	1038.1	1038.1	1033.7	1024.8	1015.9	1007.0	993.7	976.0	958.2	940.5	918.3
52.5°	1117.9	1117.9	1113.5	1104.6	1095.8	1086.9	1069.1	1055.8	1033.7	1011.5	984.9
50°	1215.5	1215.5	1206.7	1197.8	1188.9	1171.2	1153.4	1131.3	1109.1	1082.5	1060.3
47.5°	1326.5	1326.5	1317.6	1308.7	1291.0	1273.2	1246.6	1220.0	1193.4	1162.3	1126.8
45°	1481.7	1481.7	1468.4	1450.7	1428.5	1397.4	1361.9	1326.5	1286.5	1251.0	1211.1
42.5°	1672.5	1672.5	1654.7	1632.6	1601.5	1561.6	1512.8	1464.0	1410.7	1353.1	1299.8
40°	1872.1	1872.1	1849.9	1827.8	1792.3	1743.5	1690.2	1628.1	1561.6	1486.2	1419.6
37.5°	2147.2	2147.2	2116.1	2076.2	2023.0	1956.4	1876.6	1805.6	1730.2	1645.9	1557.1
35°	2555.3	2555.3	2506.5	2440.0	2355.7	2244.8	2125.0	2023.0	1907.6	1805.6	1708.0
32.5°	3158.6	3158.6	3074.4	2976.8	2834.8	2657.3	2484.3	2320.2	2147.2	2000.8	1858.8
30°	4108.0	4108.0	3966.0	3788.6	3549.0	3242.9	2985.6	2719.4	2466.6	2253.6	2058.4
27.5°	5687.3	5620.8	5425.6	5101.7	4658.1	4108.0	3713.2	3265.1	2910.2	2564.2	2311.3
25°	8349.1	8224.9	7856.7	7248.9	6428.2	5518.8	4800.1	4037.0	3495.8	3003.4	2608.5
22.5°	12674.5	12448.2	11773.9	10673.7	9187.6	7732.5	6406.0	5230.4	4263.3	3575.7	3003.4
20°	19258.0	18863.1	17700.8	15819.8	13282.3	11033.1	8668.5	6925.1	5376.8	4263.3	3495.8
17.5°	29150.9	28467.7	26466.9	23241.7	19258.0	15593.6	11991.3	9121.0	6925.1	5230.4	4037.0
15°	43950.4	42752.6	39256.8	33698.1	27314.3	21502.7	16387.7	11991.3	8668.5	6406.0	4800.1
12.5°	68798.1	66375.8	59375.4	48457.6	38280.8	28729.4	21502.7	15593.6	11033.1	7732.5	5518.8
10°	109851.5	104847.4	90655.7	69175.1	52836.3	38280.8	27314.3	19258.0	13282.3	9187.6	6428.2
7.5°	176396.0	165655.7	136309.6	100140.5	69175.1	48457.6	33698.1	23241.7	15819.8	10673.7	7248.9
5°	268178.5	246564.8	192308.9	136309.6	90655.7	59375.4	39256.8	26466.9	17700.8	11773.9	7856.7
2.5°	358164.3	320912.7	246564.8	165655.7	104847.4	66375.8	42752.6	28467.7	18863.1	12448.2	8224.9
0°	396800.0	358164.3	268178.5	176396.0	109851.5	68798.1	43950.4	29150.9	19258.0	12674.5	8349.1



REPORT NUMBER: P623062
 CATALOG NUMBER: IFLD-S-SA6C-735-U-33

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	31.1	31.1	31.1	31.1	26.6	26.6	26.6	26.6	22.2	22.2	22.2
85°	71.0	66.5	66.5	62.1	62.1	57.7	57.7	53.2	53.2	48.8	44.4
82.5°	115.3	110.9	106.5	102.0	102.0	97.6	93.2	84.3	79.9	75.4	71.0
80°	173.0	164.1	159.7	150.8	146.4	137.5	128.7	124.2	115.3	110.9	102.0
77.5°	235.1	226.3	221.8	208.5	199.6	190.8	181.9	168.6	159.7	146.4	133.1
75°	306.1	297.2	283.9	270.6	261.7	248.4	235.1	221.8	204.1	190.8	177.5
72.5°	386.0	372.6	359.3	341.6	323.8	310.5	288.4	270.6	257.3	239.6	221.8
70°	465.8	452.5	434.8	417.0	394.8	377.1	354.9	332.7	310.5	288.4	266.2
67.5°	545.7	527.9	510.2	488.0	465.8	443.6	421.4	394.8	368.2	341.6	315.0
65°	621.1	603.3	581.2	559.0	536.8	510.2	483.6	456.9	425.9	394.8	368.2
62.5°	696.5	674.3	652.1	630.0	603.3	576.7	550.1	514.6	483.6	452.5	417.0
60°	767.5	745.3	723.1	696.5	669.9	638.8	607.8	576.7	541.2	505.7	470.2
57.5°	834.0	811.8	789.7	758.6	732.0	700.9	665.4	634.4	594.5	559.0	519.0
55°	896.1	874.0	847.3	820.7	794.1	758.6	723.1	687.6	647.7	607.8	563.4
52.5°	958.2	931.6	905.0	878.4	847.3	816.3	780.8	740.9	700.9	656.6	612.2
50°	1029.2	998.2	962.7	931.6	896.1	865.1	829.6	789.7	749.7	700.9	656.6
47.5°	1095.8	1064.7	1029.2	989.3	953.8	913.9	874.0	838.5	794.1	749.7	700.9
45°	1171.2	1126.8	1091.3	1051.4	1007.0	962.7	922.7	878.4	838.5	789.7	740.9
42.5°	1251.0	1202.2	1153.4	1104.6	1064.7	1015.9	967.1	922.7	874.0	829.6	780.8
40°	1344.2	1286.5	1224.4	1171.2	1117.9	1069.1	1015.9	962.7	913.9	865.1	816.3
37.5°	1464.0	1384.1	1304.3	1237.7	1175.6	1117.9	1064.7	1007.0	953.8	896.1	847.3
35°	1605.9	1495.0	1401.9	1308.7	1237.7	1171.2	1104.6	1051.4	989.3	931.6	878.4
32.5°	1747.9	1628.1	1508.3	1401.9	1304.3	1224.4	1153.4	1091.3	1029.2	962.7	905.0
30°	1894.3	1761.2	1628.1	1495.0	1384.1	1286.5	1202.2	1126.8	1064.7	998.2	931.6
27.5°	2080.6	1894.3	1747.9	1605.9	1464.0	1344.2	1251.0	1171.2	1095.8	1029.2	958.2
25°	2311.3	2058.4	1858.8	1708.0	1557.1	1419.6	1299.8	1211.1	1126.8	1060.3	984.9
22.5°	2564.2	2253.6	2000.8	1805.6	1645.9	1486.2	1353.1	1251.0	1162.3	1082.5	1011.5
20°	2910.2	2466.6	2147.2	1907.6	1730.2	1561.6	1410.7	1286.5	1193.4	1109.1	1033.7
17.5°	3265.1	2719.4	2320.2	2023.0	1805.6	1628.1	1464.0	1326.5	1220.0	1131.3	1055.8
15°	3713.2	2985.6	2484.3	2125.0	1876.6	1690.2	1512.8	1361.9	1246.6	1153.4	1069.1
12.5°	4108.0	3242.9	2657.3	2244.8	1956.4	1743.5	1561.6	1397.4	1273.2	1171.2	1086.9
10°	4658.1	3549.0	2834.8	2355.7	2023.0	1792.3	1601.5	1428.5	1291.0	1188.9	1095.8
7.5°	5101.7	3788.6	2976.8	2440.0	2076.2	1827.8	1632.6	1450.7	1308.7	1197.8	1104.6
5°	5425.6	3966.0	3074.4	2506.5	2116.1	1849.9	1654.7	1468.4	1317.6	1206.7	1113.5
2.5°	5620.8	4108.0	3158.6	2555.3	2147.2	1872.1	1672.5	1481.7	1326.5	1215.5	1117.9
0°	5687.3	4108.0	3158.6	2555.3	2147.2	1872.1	1672.5	1481.7	1326.5	1215.5	1117.9



REPORT NUMBER: P623062
 CATALOG NUMBER: IFLD-S-SA6C-735-U-33

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	22.2	17.7	17.7	17.7	13.3	13.3	13.3	8.9	8.9	8.9	4.4
85°	39.9	39.9	35.5	31.1	31.1	26.6	22.2	22.2	17.7	13.3	13.3
82.5°	66.5	62.1	57.7	53.2	48.8	39.9	35.5	31.1	26.6	22.2	17.7
80°	93.2	88.7	79.9	71.0	66.5	57.7	53.2	44.4	35.5	31.1	26.6
77.5°	124.2	115.3	106.5	97.6	84.3	75.4	66.5	57.7	48.8	39.9	31.1
75°	164.1	146.4	133.1	119.8	106.5	93.2	79.9	71.0	57.7	48.8	35.5
72.5°	204.1	186.3	164.1	146.4	128.7	115.3	97.6	84.3	71.0	57.7	44.4
70°	244.0	221.8	199.6	177.5	155.3	133.1	115.3	97.6	79.9	66.5	53.2
67.5°	283.9	261.7	235.1	208.5	186.3	159.7	133.1	115.3	93.2	75.4	57.7
65°	332.7	301.7	270.6	244.0	212.9	186.3	155.3	128.7	106.5	84.3	66.5
62.5°	381.5	346.0	310.5	275.1	244.0	208.5	177.5	146.4	119.8	97.6	71.0
60°	430.3	390.4	350.5	310.5	270.6	235.1	199.6	164.1	133.1	106.5	79.9
57.5°	479.1	434.8	390.4	346.0	301.7	261.7	221.8	186.3	146.4	115.3	88.7
55°	523.5	479.1	430.3	381.5	332.7	283.9	244.0	204.1	164.1	124.2	93.2
52.5°	563.4	519.0	470.2	417.0	368.2	315.0	266.2	221.8	177.5	133.1	102.0
50°	607.8	559.0	505.7	452.5	394.8	341.6	288.4	239.6	190.8	146.4	110.9
47.5°	647.7	594.5	541.2	483.6	425.9	368.2	310.5	257.3	204.1	159.7	115.3
45°	687.6	634.4	576.7	514.6	456.9	394.8	332.7	270.6	221.8	168.6	124.2
42.5°	723.1	665.4	607.8	550.1	483.6	421.4	354.9	288.4	235.1	181.9	128.7
40°	758.6	700.9	638.8	576.7	510.2	443.6	377.1	310.5	248.4	190.8	137.5
37.5°	794.1	732.0	669.9	603.3	536.8	465.8	394.8	323.8	261.7	199.6	146.4
35°	820.7	758.6	696.5	630.0	559.0	488.0	417.0	341.6	270.6	208.5	150.8
32.5°	847.3	789.7	723.1	652.1	581.2	510.2	434.8	359.3	283.9	221.8	159.7
30°	874.0	811.8	745.3	674.3	603.3	527.9	452.5	372.6	297.2	226.3	164.1
27.5°	896.1	834.0	767.5	696.5	621.1	545.7	465.8	386.0	306.1	235.1	173.0
25°	918.3	856.2	789.7	714.2	638.8	559.0	479.1	399.3	319.4	244.0	177.5
22.5°	940.5	869.5	807.4	732.0	656.6	576.7	492.4	408.1	328.3	248.4	181.9
20°	958.2	887.3	820.7	745.3	669.9	590.0	505.7	421.4	337.2	257.3	186.3
17.5°	976.0	905.0	834.0	763.0	683.2	598.9	514.6	430.3	341.6	261.7	190.8
15°	993.7	918.3	847.3	771.9	692.1	612.2	523.5	439.2	350.5	266.2	195.2
12.5°	1007.0	927.2	856.2	785.2	700.9	621.1	532.4	443.6	354.9	270.6	195.2
10°	1015.9	936.1	865.1	794.1	709.8	625.5	536.8	452.5	359.3	275.1	199.6
7.5°	1024.8	944.9	869.5	798.5	714.2	630.0	545.7	456.9	363.8	275.1	204.1
5°	1033.7	949.4	874.0	803.0	718.7	638.8	550.1	461.4	368.2	279.5	204.1
2.5°	1038.1	953.8	878.4	807.4	723.1	638.8	550.1	461.4	368.2	279.5	204.1
0°	1038.1	953.8	878.4	807.4	723.1	638.8	550.1	461.4	368.2	279.5	204.1



REPORT NUMBER: P623062
 CATALOG NUMBER: IFLD-S-SA6C-735-U-33

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°
90°	0.0	0.0	0.0	0.0
87.5°	4.4	4.4	0.0	0.0
85°	8.9	4.4	4.4	0.0
82.5°	13.3	8.9	4.4	0.0
80°	17.7	13.3	4.4	0.0
77.5°	22.2	13.3	8.9	0.0
75°	26.6	17.7	8.9	0.0
72.5°	31.1	22.2	8.9	0.0
70°	35.5	22.2	13.3	0.0
67.5°	39.9	26.6	13.3	0.0
65°	48.8	31.1	13.3	0.0
62.5°	53.2	31.1	17.7	0.0
60°	57.7	35.5	17.7	0.0
57.5°	62.1	39.9	17.7	0.0
55°	66.5	39.9	22.2	0.0
52.5°	71.0	44.4	22.2	0.0
50°	75.4	48.8	22.2	0.0
47.5°	79.9	53.2	22.2	0.0
45°	84.3	53.2	26.6	0.0
42.5°	93.2	57.7	26.6	0.0
40°	97.6	57.7	26.6	0.0
37.5°	102.0	62.1	26.6	0.0
35°	102.0	62.1	31.1	0.0
32.5°	106.5	66.5	31.1	0.0
30°	110.9	66.5	31.1	0.0
27.5°	115.3	71.0	31.1	0.0
25°	119.8	71.0	31.1	0.0
22.5°	119.8	71.0	31.1	0.0
20°	124.2	75.4	35.5	0.0
17.5°	124.2	75.4	35.5	0.0
15°	128.7	75.4	35.5	0.0
12.5°	128.7	79.9	35.5	0.0
10°	128.7	79.9	35.5	0.0
7.5°	133.1	79.9	35.5	0.0
5°	133.1	79.9	35.5	0.0
2.5°	133.1	79.9	35.5	0.0
0°	133.1	79.9	35.5	0.0

(END OF REPORT)