

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P386839

Luminaire Tested: GAW-SA2C-735-U-SLL

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-2019
Report Number: P386839
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-26)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: STREETWORKS
Catalog Number: GAW-SA2C-735-U-SLL
Description: GALLEON WALL LUMINAIRE
(2) 70 CRI, 3500K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT
ELIMINATOR LEFT OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12186.8 lumens
Efficiency: N/A
Efficacy: 107.8 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B2 - U0 - G3


Input Watts (W): 113
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P386839
 CATALOG NUMBER: GAW-SA2C-735-U-SLL

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 11.7 fc
 Type III - Medium - N/A

REPORT NUMBER: P386839
CATALOG NUMBER: GAW-SA2C-735-U-SLL

Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P386839
 CATALOG NUMBER: GAW-SA2C-735-U-SLL


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 2146.4 | 0.0 | 2146.4 |
| | % Fixture | 17.6 | 0.0 | 17.6 |
| Street Side | Lumens | 10040.4 | 0.0 | 10040.4 |
| | % Fixture | 82.4 | 0.0 | 82.4 |
| Total | Lumens | 12186.8 | 0.0 | 12186.8 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

Coefficient of Utilization

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 286.5 | 2.4 |
| 10°-20° | 595.3 | 4.9 |
| 20°-30° | 846.6 | 6.9 |
| 30°-40° | 1219.9 | 10.0 |
| 40°-50° | 1719.2 | 14.1 |
| 50°-60° | 2390.0 | 19.6 |
| 60°-70° | 2890.3 | 23.7 |
| 70°-80° | 1776.6 | 14.6 |
| 80°-90° | 462.3 | 3.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 12186.8 | 100.0 |
| 0°-180° | 12186.8 | 100.0 |




REPORT NUMBER: P386839
 CATALOG NUMBER: GAW-SA2C-735-U-SLL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1210.0 | 9.9 | | | |
| FM (30°-60°) | 4354.9 | 35.7 | | | |
| FH (60°-80°) | 4065.1 | 33.4 | | | G2/5000 |
| FVH (80°-90°) | 410.4 | 3.4 | | | G3/500 |
| BL (0°-30°) | 518.4 | 4.3 | B2/1000 | | |
| BM (30°-60°) | 974.3 | 8.0 | B1/1000 | | |
| BH (60°-80°) | 601.8 | 4.9 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 51.9 | 0.4 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G3
 Type III Medium





REPORT NUMBER: P386839

CATALOG NUMBER: GAW-SA2C-735-U-SLL

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° | 50° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 |
| 2.5° | 3957.4 | 4009.5 | 4045.5 | 4081.1 | 4108.9 | 4136.2 | 4176.1 | 4216.1 | 4223.9 | 4231.2 | 4215.6 |
| 5° | 3934.0 | 4061.1 | 4169.3 | 4277.0 | 4376.8 | 4476.8 | 4536.7 | 4596.6 | 4608.8 | 4621.0 | 4583.5 |
| 7.5° | 3682.0 | 3869.6 | 4057.2 | 4244.8 | 4416.8 | 4588.8 | 4693.6 | 4797.9 | 4821.7 | 4845.1 | 4783.7 |
| 10° | 3395.5 | 3613.8 | 3844.3 | 4074.8 | 4301.3 | 4527.9 | 4679.4 | 4830.9 | 4861.2 | 4891.4 | 4814.9 |
| 12.5° | 3177.8 | 3416.0 | 3662.0 | 3908.2 | 4147.3 | 4386.1 | 4543.0 | 4699.9 | 4737.5 | 4774.9 | 4719.4 |
| 15° | 3094.0 | 3355.1 | 3586.5 | 3818.0 | 4026.5 | 4234.6 | 4363.2 | 4491.3 | 4506.9 | 4522.1 | 4513.3 |
| 17.5° | 3177.8 | 3465.7 | 3675.2 | 3884.3 | 3997.8 | 4110.8 | 4162.5 | 4213.7 | 4230.7 | 4247.3 | 4269.6 |
| 20° | 3422.9 | 3733.7 | 3881.3 | 4028.5 | 4023.6 | 4018.3 | 3993.4 | 3968.1 | 3963.7 | 3959.3 | 4022.7 |
| 22.5° | 3772.7 | 4133.7 | 4192.7 | 4251.1 | 4114.3 | 3977.3 | 3894.0 | 3810.2 | 3793.6 | 3776.6 | 3843.8 |
| 25° | 4183.4 | 4567.9 | 4557.1 | 4545.9 | 4285.2 | 4024.1 | 3865.2 | 3706.4 | 3687.9 | 3669.4 | 3726.9 |
| 27.5° | 4630.2 | 4997.6 | 4927.4 | 4857.2 | 4503.1 | 4148.8 | 3918.4 | 3687.9 | 3669.4 | 3650.9 | 3701.6 |
| 30° | 4979.5 | 5312.8 | 5200.3 | 5087.8 | 4686.7 | 4285.7 | 4012.0 | 3738.1 | 3707.9 | 3677.2 | 3739.5 |
| 32.5° | 5275.4 | 5558.9 | 5407.8 | 5256.8 | 4835.8 | 4414.9 | 4118.6 | 3822.4 | 3775.1 | 3727.9 | 3811.2 |
| 35° | 5583.3 | 5804.4 | 5592.0 | 5379.1 | 4968.8 | 4558.1 | 4244.8 | 3931.1 | 3873.0 | 3815.1 | 3929.6 |
| 37.5° | 5929.6 | 6113.4 | 5808.4 | 5502.9 | 5118.5 | 4734.0 | 4433.8 | 4133.2 | 4073.8 | 4014.3 | 4160.5 |
| 40° | 6295.6 | 6448.6 | 6041.7 | 5634.9 | 5282.1 | 4929.4 | 4695.5 | 4461.2 | 4404.6 | 4347.6 | 4525.0 |
| 42.5° | 6615.7 | 6727.3 | 6259.1 | 5790.8 | 5479.5 | 5167.6 | 5002.9 | 4837.8 | 4837.3 | 4836.3 | 5016.1 |
| 45° | 6856.9 | 6953.9 | 6440.3 | 5926.3 | 5672.0 | 5417.1 | 5331.3 | 5245.6 | 5314.3 | 5383.0 | 5545.7 |
| 47.5° | 7057.2 | 7123.0 | 6592.3 | 6061.3 | 5892.2 | 5723.1 | 5735.8 | 5748.4 | 5888.3 | 6028.1 | 6132.8 |
| 50° | 7286.1 | 7233.1 | 6730.2 | 6226.9 | 6174.7 | 6122.6 | 6236.6 | 6350.2 | 6510.9 | 6671.3 | 6742.4 |
| 52.5° | 7534.1 | 7393.3 | 6917.3 | 6440.8 | 6499.3 | 6557.7 | 6789.7 | 7021.6 | 7183.8 | 7346.1 | 7372.9 |
| 55° | 7980.0 | 7764.1 | 7261.3 | 6758.0 | 6870.5 | 6982.6 | 7323.1 | 7663.3 | 7789.9 | 7916.6 | 7926.4 |
| 57.5° | 8482.4 | 8290.8 | 7743.1 | 7195.6 | 7316.4 | 7437.2 | 7830.4 | 8223.1 | 8360.0 | 8496.4 | 8477.5 |
| 60° | 8675.8 | 8685.0 | 8200.7 | 7715.9 | 7837.7 | 7959.5 | 8342.5 | 8725.5 | 8882.8 | 9039.7 | 8997.8 |
| 62.5° | 8480.8 | 8709.4 | 8450.7 | 8191.4 | 8302.1 | 8412.2 | 8787.4 | 9162.5 | 9323.8 | 9485.1 | 9412.0 |
| 65° | 8095.4 | 8322.0 | 8438.0 | 8553.9 | 8590.5 | 8627.0 | 8977.3 | 9327.1 | 9451.0 | 9574.2 | 9537.2 |
| 67.5° | 7605.3 | 7788.5 | 8216.3 | 8643.6 | 8570.0 | 8496.4 | 8660.6 | 8824.9 | 8952.0 | 9079.1 | 9058.2 |
| 70° | 7037.7 | 7256.0 | 7826.5 | 8397.1 | 8035.5 | 7673.5 | 7605.8 | 7538.1 | 7675.4 | 7812.4 | 7727.5 |
| 72.5° | 6019.8 | 6349.2 | 6957.7 | 7565.8 | 6899.8 | 6233.7 | 6002.3 | 5770.9 | 5944.8 | 6118.7 | 5983.8 |
| 75° | 4546.9 | 4984.0 | 5656.4 | 6328.2 | 5533.6 | 4738.9 | 4430.0 | 4121.0 | 4270.7 | 4420.2 | 4327.7 |
| 77.5° | 3162.2 | 3710.3 | 4372.5 | 5034.6 | 4226.8 | 3418.5 | 3189.0 | 2959.0 | 3003.8 | 3048.1 | 3032.6 |
| 80° | 2156.0 | 2516.5 | 2978.4 | 3439.9 | 2902.0 | 2364.1 | 2382.1 | 2399.7 | 2378.7 | 2357.2 | 2388.4 |
| 82.5° | 1352.1 | 1605.9 | 1962.6 | 2318.8 | 2033.2 | 1747.7 | 1911.5 | 2075.1 | 1994.7 | 1913.8 | 1944.1 |
| 85° | 761.6 | 916.5 | 1265.4 | 1613.7 | 1504.1 | 1394.0 | 1490.0 | 1585.5 | 1460.8 | 1336.0 | 1391.1 |
| 87.5° | 145.2 | 241.7 | 700.1 | 1158.2 | 1051.5 | 944.7 | 821.0 | 697.2 | 532.1 | 366.9 | 535.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386839
 CATALOG NUMBER: GAW-SA2C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° | 50° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386839

CATALOG NUMBER: GAW-SA2C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° | 105° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 |
| 2.5° | 4200.0 | 4191.7 | 4183.4 | 4153.7 | 4123.5 | 4078.7 | 4041.6 | 3977.3 | 3942.3 | 3889.1 | 3836.0 |
| 5° | 4545.4 | 4492.8 | 4440.2 | 4349.6 | 4258.5 | 4157.1 | 4040.7 | 3911.5 | 3814.1 | 3687.4 | 3560.8 |
| 7.5° | 4722.3 | 4599.6 | 4476.2 | 4302.3 | 4127.9 | 3971.0 | 3786.8 | 3615.4 | 3469.1 | 3304.4 | 3139.7 |
| 10° | 4738.4 | 4554.2 | 4369.6 | 4143.5 | 3916.9 | 3726.4 | 3514.5 | 3324.0 | 3148.6 | 2959.5 | 2770.0 |
| 12.5° | 4663.3 | 4467.5 | 4271.1 | 4022.1 | 3772.7 | 3556.4 | 3328.4 | 3114.9 | 2920.5 | 2712.5 | 2504.0 |
| 15° | 4504.5 | 4348.1 | 4191.2 | 3957.9 | 3724.4 | 3506.2 | 3285.0 | 3032.1 | 2812.4 | 2599.4 | 2386.0 |
| 17.5° | 4291.6 | 4217.5 | 4143.0 | 3974.4 | 3805.3 | 3616.3 | 3401.9 | 3105.2 | 2847.9 | 2616.5 | 2385.0 |
| 20° | 4085.5 | 4112.8 | 4139.5 | 4072.4 | 4005.1 | 3853.6 | 3666.5 | 3333.2 | 3004.8 | 2702.3 | 2399.1 |
| 22.5° | 3910.6 | 4041.6 | 4172.2 | 4224.4 | 4276.0 | 4184.9 | 4038.7 | 3653.3 | 3218.7 | 2823.5 | 2428.4 |
| 25° | 3783.9 | 4001.2 | 4218.5 | 4391.9 | 4564.9 | 4524.5 | 4412.0 | 4042.1 | 3502.2 | 2998.5 | 2494.2 |
| 27.5° | 3752.2 | 4018.7 | 4285.2 | 4554.2 | 4822.7 | 4860.2 | 4829.0 | 4451.9 | 3840.4 | 3215.7 | 2590.7 |
| 30° | 3801.9 | 4071.8 | 4341.3 | 4668.7 | 4995.7 | 5145.2 | 5187.1 | 4793.4 | 4226.8 | 3469.1 | 2711.0 |
| 32.5° | 3894.5 | 4159.1 | 4423.6 | 4780.3 | 5136.4 | 5362.5 | 5496.0 | 5105.8 | 4496.2 | 3660.2 | 2823.5 |
| 35° | 4044.1 | 4291.6 | 4539.2 | 4910.4 | 5281.6 | 5574.0 | 5817.7 | 5428.3 | 4735.5 | 3793.6 | 2851.3 |
| 37.5° | 4306.2 | 4519.1 | 4732.0 | 5075.1 | 5417.6 | 5796.6 | 6162.6 | 5783.5 | 4994.2 | 3922.3 | 2849.8 |
| 40° | 4702.3 | 4852.9 | 5002.9 | 5292.8 | 5582.3 | 6059.3 | 6553.3 | 6179.6 | 5280.2 | 4061.7 | 2843.1 |
| 42.5° | 5195.9 | 5273.4 | 5350.3 | 5579.8 | 5809.3 | 6333.6 | 6908.0 | 6567.0 | 5553.0 | 4191.2 | 2829.4 |
| 45° | 5707.9 | 5728.4 | 5748.9 | 5893.7 | 6037.9 | 6551.0 | 7149.7 | 6857.9 | 5791.3 | 4303.7 | 2815.7 |
| 47.5° | 6237.1 | 6166.9 | 6096.9 | 6154.3 | 6211.8 | 6717.5 | 7322.2 | 7078.6 | 6030.5 | 4428.5 | 2826.0 |
| 50° | 6813.5 | 6618.1 | 6422.7 | 6392.6 | 6362.3 | 6884.2 | 7525.4 | 7359.2 | 6318.0 | 4610.3 | 2902.4 |
| 52.5° | 7399.2 | 7077.1 | 6755.1 | 6635.7 | 6515.8 | 7082.9 | 7794.8 | 7708.6 | 6728.2 | 4891.9 | 3055.0 |
| 55° | 7936.1 | 7526.3 | 7116.6 | 6955.8 | 6795.0 | 7387.0 | 8123.7 | 8221.7 | 7254.0 | 5252.0 | 3249.4 |
| 57.5° | 8457.9 | 7993.6 | 7529.2 | 7380.2 | 7231.1 | 7833.8 | 8540.3 | 8682.1 | 7785.1 | 5597.4 | 3409.2 |
| 60° | 8955.9 | 8496.4 | 8036.5 | 7917.1 | 7797.3 | 8389.3 | 8990.5 | 8887.2 | 8058.9 | 5759.1 | 3458.9 |
| 62.5° | 9338.9 | 8973.5 | 8608.0 | 8545.2 | 8481.9 | 8951.0 | 9336.4 | 8807.3 | 7885.0 | 5599.8 | 3314.7 |
| 65° | 9500.2 | 9292.1 | 9083.6 | 9142.6 | 9201.0 | 9375.9 | 9422.7 | 8573.5 | 7338.3 | 5153.5 | 2968.8 |
| 67.5° | 9036.8 | 9079.1 | 9121.6 | 9369.1 | 9616.1 | 9495.8 | 9166.4 | 8112.5 | 6560.2 | 4521.1 | 2482.0 |
| 70° | 7642.3 | 7896.6 | 8150.6 | 8736.2 | 9321.3 | 9054.3 | 8479.9 | 7285.2 | 5623.7 | 3792.6 | 1961.2 |
| 72.5° | 5848.3 | 6134.3 | 6419.8 | 7289.0 | 8157.8 | 7911.8 | 7208.2 | 5983.8 | 4508.9 | 3028.7 | 1547.9 |
| 75° | 4234.6 | 4557.7 | 4880.2 | 5839.1 | 6797.9 | 6456.4 | 5391.7 | 4284.3 | 3424.7 | 2311.9 | 1198.6 |
| 77.5° | 3016.5 | 3232.8 | 3449.2 | 4396.4 | 5343.1 | 4786.6 | 3589.0 | 2883.0 | 2370.4 | 1606.9 | 842.9 |
| 80° | 2419.6 | 2353.4 | 2287.0 | 2814.8 | 3342.5 | 3249.8 | 2373.8 | 1851.5 | 1640.6 | 1076.8 | 513.1 |
| 82.5° | 1973.8 | 1812.0 | 1650.2 | 1898.8 | 2147.3 | 2133.6 | 1647.3 | 1358.5 | 1221.0 | 748.4 | 275.8 |
| 85° | 1445.6 | 1380.8 | 1316.0 | 1535.8 | 1755.5 | 1567.9 | 1115.8 | 863.4 | 952.1 | 551.0 | 150.1 |
| 87.5° | 705.0 | 805.4 | 905.3 | 1164.5 | 1423.2 | 1068.5 | 338.7 | 167.6 | 231.9 | 152.5 | 72.6 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386839
 CATALOG NUMBER: GAW-SA2C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° | 105° |
|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386839
 CATALOG NUMBER: GAW-SA2C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° | 160° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 |
| 2.5° | 3796.6 | 3756.6 | 3711.3 | 3666.0 | 3614.3 | 3562.2 | 3531.5 | 3500.3 | 3466.7 | 3433.1 | 3395.1 |
| 5° | 3476.9 | 3393.1 | 3298.1 | 3203.1 | 3109.0 | 3015.0 | 2964.4 | 2913.7 | 2860.1 | 2806.0 | 2759.2 |
| 7.5° | 3018.0 | 2895.7 | 2764.1 | 2632.1 | 2515.1 | 2397.7 | 2325.1 | 2252.0 | 2185.8 | 2119.0 | 2063.0 |
| 10° | 2614.1 | 2458.1 | 2326.0 | 2193.6 | 2105.4 | 2017.2 | 1950.4 | 1883.7 | 1819.3 | 1754.5 | 1692.7 |
| 12.5° | 2348.0 | 2192.1 | 2108.3 | 2024.5 | 1951.4 | 1878.3 | 1801.3 | 1723.9 | 1635.7 | 1547.0 | 1482.2 |
| 15° | 2244.2 | 2102.5 | 2009.4 | 1915.8 | 1817.9 | 1719.5 | 1625.0 | 1530.5 | 1426.2 | 1321.9 | 1248.3 |
| 17.5° | 2199.4 | 2013.8 | 1883.7 | 1753.1 | 1623.9 | 1494.9 | 1385.2 | 1275.6 | 1161.6 | 1047.5 | 973.0 |
| 20° | 2152.2 | 1905.1 | 1730.6 | 1555.7 | 1390.1 | 1224.4 | 1100.2 | 975.9 | 874.1 | 772.3 | 715.3 |
| 22.5° | 2109.2 | 1789.6 | 1570.9 | 1351.6 | 1155.7 | 959.9 | 838.0 | 715.7 | 653.3 | 591.0 | 568.1 |
| 25° | 2091.7 | 1688.7 | 1419.8 | 1150.9 | 944.3 | 737.2 | 650.4 | 563.7 | 539.9 | 515.5 | 503.8 |
| 27.5° | 2094.7 | 1598.7 | 1292.6 | 986.2 | 800.1 | 613.9 | 554.4 | 495.1 | 480.4 | 465.3 | 458.0 |
| 30° | 2105.8 | 1500.7 | 1172.7 | 844.9 | 691.4 | 537.9 | 499.4 | 460.4 | 444.8 | 429.3 | 420.0 |
| 32.5° | 2118.5 | 1413.0 | 1080.2 | 746.9 | 621.7 | 496.0 | 464.3 | 432.2 | 417.1 | 402.0 | 392.8 |
| 35° | 2096.5 | 1341.4 | 1016.9 | 692.3 | 576.9 | 461.0 | 434.1 | 406.9 | 390.3 | 373.7 | 365.0 |
| 37.5° | 2059.5 | 1269.2 | 967.7 | 665.6 | 547.7 | 429.3 | 409.8 | 389.8 | 372.8 | 355.2 | 346.9 |
| 40° | 2025.9 | 1208.3 | 931.1 | 653.3 | 531.6 | 409.3 | 392.8 | 376.1 | 358.6 | 340.6 | 330.9 |
| 42.5° | 1998.7 | 1167.4 | 895.1 | 622.7 | 516.9 | 410.7 | 387.3 | 363.5 | 346.4 | 329.4 | 318.6 |
| 45° | 1978.2 | 1140.6 | 866.8 | 592.9 | 503.3 | 413.7 | 383.9 | 354.2 | 337.1 | 319.6 | 307.0 |
| 47.5° | 1976.2 | 1126.5 | 846.9 | 567.1 | 477.5 | 387.3 | 375.2 | 363.0 | 338.2 | 312.8 | 298.2 |
| 50° | 2003.1 | 1103.6 | 823.5 | 542.8 | 452.6 | 362.5 | 379.0 | 395.1 | 352.7 | 309.9 | 291.4 |
| 52.5° | 2059.1 | 1063.1 | 786.4 | 509.6 | 422.4 | 334.7 | 360.5 | 385.9 | 349.4 | 312.3 | 288.5 |
| 55° | 2126.8 | 1003.7 | 730.4 | 456.5 | 382.5 | 307.9 | 330.9 | 353.2 | 330.4 | 307.0 | 278.2 |
| 57.5° | 2169.2 | 928.7 | 659.7 | 390.8 | 337.6 | 284.5 | 297.7 | 310.4 | 301.1 | 291.9 | 262.7 |
| 60° | 2143.9 | 828.8 | 580.3 | 331.3 | 298.2 | 265.1 | 262.7 | 259.7 | 273.4 | 287.0 | 253.4 |
| 62.5° | 2020.1 | 725.5 | 510.2 | 294.8 | 269.9 | 244.6 | 239.3 | 233.3 | 255.8 | 277.7 | 242.2 |
| 65° | 1811.1 | 653.3 | 465.8 | 278.2 | 250.4 | 222.6 | 216.8 | 211.0 | 217.8 | 224.6 | 208.1 |
| 67.5° | 1545.5 | 609.0 | 440.5 | 271.9 | 238.2 | 204.1 | 197.4 | 190.5 | 189.0 | 187.6 | 181.8 |
| 70° | 1271.7 | 581.8 | 423.9 | 266.0 | 225.1 | 183.7 | 177.4 | 171.1 | 169.1 | 166.6 | 162.2 |
| 72.5° | 1063.1 | 578.4 | 422.0 | 265.6 | 214.4 | 163.3 | 157.3 | 151.5 | 149.1 | 146.2 | 142.8 |
| 75° | 870.7 | 542.8 | 400.5 | 258.2 | 199.8 | 140.8 | 135.5 | 130.1 | 128.1 | 125.7 | 122.8 |
| 77.5° | 646.1 | 449.2 | 336.7 | 224.1 | 171.1 | 117.9 | 112.5 | 106.7 | 106.2 | 105.2 | 102.8 |
| 80° | 419.1 | 325.0 | 240.7 | 156.4 | 124.8 | 92.5 | 88.2 | 83.3 | 83.8 | 84.3 | 82.4 |
| 82.5° | 232.9 | 189.6 | 147.1 | 104.7 | 85.3 | 65.8 | 63.8 | 61.4 | 62.8 | 63.8 | 61.4 |
| 85° | 122.8 | 95.5 | 78.9 | 62.4 | 49.2 | 36.1 | 36.1 | 35.6 | 37.5 | 39.5 | 37.5 |
| 87.5° | 53.1 | 33.6 | 28.7 | 23.4 | 13.2 | 2.4 | 2.9 | 2.9 | 3.9 | 4.9 | 4.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386839
 CATALOG NUMBER: GAW-SA2C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° | 160° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386839
 CATALOG NUMBER: GAW-SA2C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° | 215° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 |
| 2.5° | 3356.5 | 3321.0 | 3285.0 | 3245.5 | 3252.8 | 3222.6 | 3192.3 | 3173.4 | 3154.4 | 3148.6 | 3142.6 |
| 5° | 2712.5 | 2672.0 | 2631.1 | 2594.5 | 2626.2 | 2604.8 | 2583.3 | 2580.4 | 2577.0 | 2577.0 | 2576.5 |
| 7.5° | 2006.9 | 1963.6 | 1919.7 | 1889.5 | 1920.7 | 1916.8 | 1912.9 | 1933.8 | 1954.8 | 1971.9 | 1988.4 |
| 10° | 1630.8 | 1578.2 | 1525.0 | 1480.2 | 1472.4 | 1450.0 | 1427.1 | 1432.0 | 1436.3 | 1454.9 | 1473.4 |
| 12.5° | 1417.4 | 1354.5 | 1291.7 | 1239.1 | 1215.2 | 1178.2 | 1140.6 | 1117.2 | 1093.8 | 1096.3 | 1098.2 |
| 15° | 1174.2 | 1113.4 | 1051.9 | 1006.7 | 991.5 | 962.8 | 934.0 | 904.8 | 875.0 | 862.9 | 850.2 |
| 17.5° | 898.0 | 849.2 | 800.1 | 769.8 | 769.8 | 761.6 | 753.3 | 738.6 | 723.5 | 711.4 | 698.7 |
| 20° | 658.2 | 632.4 | 606.1 | 593.4 | 597.4 | 597.8 | 597.8 | 605.2 | 612.5 | 608.5 | 604.7 |
| 22.5° | 544.8 | 535.5 | 526.2 | 520.9 | 522.8 | 523.3 | 523.8 | 530.6 | 537.0 | 541.8 | 546.2 |
| 25° | 491.6 | 485.8 | 479.9 | 478.0 | 482.4 | 482.8 | 482.8 | 487.3 | 491.6 | 496.5 | 501.4 |
| 27.5° | 450.3 | 447.8 | 445.4 | 441.9 | 446.3 | 446.3 | 445.8 | 450.7 | 455.0 | 459.5 | 463.4 |
| 30° | 410.7 | 411.7 | 412.2 | 411.3 | 414.2 | 416.1 | 417.6 | 420.9 | 423.9 | 427.3 | 430.7 |
| 32.5° | 383.0 | 381.5 | 380.1 | 379.0 | 385.4 | 388.8 | 392.2 | 395.7 | 398.6 | 400.0 | 401.5 |
| 35° | 356.1 | 352.7 | 349.4 | 346.9 | 352.7 | 357.2 | 361.6 | 367.9 | 373.7 | 374.7 | 375.7 |
| 37.5° | 338.2 | 333.8 | 329.4 | 326.4 | 328.9 | 330.9 | 332.8 | 339.6 | 346.4 | 350.3 | 353.8 |
| 40° | 321.1 | 316.7 | 312.3 | 309.9 | 311.3 | 311.9 | 312.3 | 315.7 | 318.6 | 326.0 | 332.8 |
| 42.5° | 307.5 | 302.1 | 296.8 | 293.8 | 294.8 | 295.7 | 296.3 | 295.7 | 295.3 | 302.1 | 308.9 |
| 45° | 293.8 | 287.9 | 282.1 | 278.7 | 279.2 | 279.2 | 279.2 | 278.2 | 276.7 | 280.1 | 283.6 |
| 47.5° | 283.0 | 276.3 | 269.4 | 266.0 | 265.1 | 264.1 | 263.1 | 262.7 | 261.6 | 264.1 | 266.0 |
| 50° | 272.3 | 265.1 | 257.3 | 253.4 | 250.9 | 250.0 | 248.9 | 248.5 | 247.5 | 250.0 | 251.9 |
| 52.5° | 264.1 | 255.3 | 246.5 | 240.2 | 237.8 | 236.4 | 234.8 | 235.3 | 235.3 | 236.4 | 236.8 |
| 55° | 249.5 | 241.7 | 233.3 | 229.0 | 224.6 | 223.7 | 222.6 | 224.1 | 225.1 | 225.1 | 225.1 |
| 57.5° | 233.3 | 226.1 | 218.3 | 215.4 | 211.5 | 211.5 | 211.0 | 213.0 | 214.4 | 215.4 | 216.3 |
| 60° | 219.3 | 211.0 | 202.7 | 200.3 | 198.8 | 198.3 | 197.8 | 200.3 | 202.2 | 204.1 | 206.1 |
| 62.5° | 206.1 | 197.4 | 188.5 | 185.6 | 185.2 | 185.6 | 185.6 | 188.1 | 190.0 | 192.0 | 193.9 |
| 65° | 191.4 | 182.7 | 173.4 | 170.5 | 171.5 | 172.9 | 174.4 | 176.4 | 177.8 | 179.8 | 181.8 |
| 67.5° | 175.4 | 168.1 | 160.3 | 157.3 | 157.8 | 159.8 | 161.8 | 163.3 | 164.2 | 166.2 | 168.1 |
| 70° | 157.8 | 151.5 | 145.2 | 143.3 | 142.8 | 145.2 | 147.1 | 148.1 | 149.1 | 151.5 | 153.5 |
| 72.5° | 138.8 | 133.5 | 128.1 | 126.7 | 127.2 | 128.6 | 130.1 | 131.5 | 132.5 | 135.0 | 136.9 |
| 75° | 119.4 | 114.5 | 109.6 | 108.7 | 109.6 | 111.1 | 112.5 | 113.6 | 114.5 | 117.4 | 119.9 |
| 77.5° | 100.3 | 95.0 | 89.1 | 88.7 | 90.2 | 91.6 | 92.5 | 94.0 | 95.5 | 99.4 | 103.3 |
| 80° | 80.4 | 74.6 | 68.2 | 67.7 | 69.2 | 70.6 | 72.1 | 73.6 | 75.1 | 79.9 | 84.3 |
| 82.5° | 59.0 | 52.1 | 45.3 | 44.3 | 49.2 | 50.6 | 52.1 | 54.6 | 56.6 | 60.9 | 65.3 |
| 85° | 35.6 | 28.7 | 21.9 | 21.4 | 25.8 | 28.3 | 30.7 | 33.6 | 36.1 | 39.9 | 43.9 |
| 87.5° | 3.9 | 2.0 | 0.0 | 0.0 | 0.5 | 2.4 | 4.4 | 6.9 | 9.3 | 13.2 | 16.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386839
 CATALOG NUMBER: GAW-SA2C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° | 215° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386839
 CATALOG NUMBER: GAW-SA2C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° | 270° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 |
| 2.5° | 3121.2 | 3099.3 | 3121.7 | 3143.7 | 3152.9 | 3162.2 | 3138.3 | 3113.9 | 3151.9 | 3189.4 | 3199.2 |
| 5° | 2557.0 | 2537.0 | 2552.1 | 2566.8 | 2534.1 | 2501.5 | 2498.0 | 2494.2 | 2522.5 | 2550.7 | 2555.1 |
| 7.5° | 1982.1 | 1975.7 | 1989.9 | 2004.0 | 1962.6 | 1920.7 | 1900.2 | 1879.7 | 1886.6 | 1893.4 | 1892.4 |
| 10° | 1477.8 | 1481.7 | 1499.3 | 1516.3 | 1484.1 | 1451.9 | 1437.8 | 1423.7 | 1439.3 | 1454.4 | 1468.6 |
| 12.5° | 1107.0 | 1115.2 | 1133.8 | 1151.8 | 1138.6 | 1125.0 | 1126.5 | 1127.9 | 1146.0 | 1163.5 | 1179.1 |
| 15° | 860.0 | 869.7 | 882.8 | 895.5 | 896.0 | 896.0 | 908.7 | 920.9 | 919.4 | 918.0 | 928.7 |
| 17.5° | 711.9 | 724.6 | 726.0 | 727.5 | 727.9 | 728.4 | 727.5 | 726.4 | 719.2 | 711.9 | 720.1 |
| 20° | 609.6 | 613.9 | 617.8 | 621.2 | 616.8 | 612.0 | 599.8 | 587.6 | 582.7 | 577.8 | 585.6 |
| 22.5° | 554.4 | 562.2 | 558.4 | 554.0 | 545.2 | 535.9 | 526.7 | 516.9 | 516.5 | 515.5 | 519.9 |
| 25° | 508.2 | 514.5 | 507.7 | 500.9 | 494.6 | 488.2 | 481.9 | 475.5 | 475.1 | 474.6 | 476.6 |
| 27.5° | 469.7 | 475.5 | 469.2 | 462.8 | 457.5 | 452.1 | 447.2 | 442.5 | 441.4 | 440.5 | 441.0 |
| 30° | 436.5 | 441.9 | 436.5 | 430.7 | 426.9 | 422.4 | 419.1 | 415.6 | 415.1 | 414.6 | 414.6 |
| 32.5° | 406.9 | 412.2 | 408.3 | 404.4 | 401.0 | 397.6 | 395.1 | 392.8 | 390.3 | 387.9 | 382.5 |
| 35° | 381.0 | 386.4 | 383.9 | 381.0 | 377.2 | 373.2 | 368.8 | 363.9 | 357.6 | 350.8 | 347.9 |
| 37.5° | 359.1 | 364.5 | 362.0 | 359.6 | 354.2 | 348.9 | 341.1 | 332.8 | 330.9 | 328.4 | 327.9 |
| 40° | 341.6 | 349.8 | 344.9 | 339.6 | 331.3 | 323.1 | 319.1 | 315.3 | 314.2 | 313.3 | 312.3 |
| 42.5° | 322.0 | 334.7 | 326.0 | 317.2 | 309.4 | 301.6 | 300.6 | 299.7 | 299.2 | 298.6 | 298.6 |
| 45° | 297.7 | 311.3 | 302.6 | 293.3 | 289.0 | 284.5 | 284.5 | 284.5 | 285.0 | 285.0 | 286.0 |
| 47.5° | 274.8 | 283.0 | 278.7 | 274.3 | 271.9 | 269.4 | 269.9 | 270.5 | 271.9 | 272.9 | 275.3 |
| 50° | 255.3 | 258.2 | 259.2 | 259.7 | 258.2 | 256.7 | 257.8 | 258.2 | 259.7 | 260.7 | 262.7 |
| 52.5° | 241.1 | 245.6 | 245.6 | 245.1 | 245.1 | 245.1 | 246.0 | 247.1 | 248.5 | 250.0 | 251.9 |
| 55° | 231.9 | 238.2 | 236.4 | 234.4 | 234.8 | 234.8 | 235.8 | 236.8 | 238.2 | 239.3 | 242.2 |
| 57.5° | 223.2 | 230.0 | 228.0 | 226.1 | 226.1 | 226.1 | 226.6 | 227.1 | 228.6 | 229.5 | 231.5 |
| 60° | 213.0 | 219.7 | 217.8 | 215.4 | 215.9 | 216.3 | 216.8 | 216.8 | 217.8 | 218.3 | 218.3 |
| 62.5° | 200.7 | 207.6 | 205.6 | 203.2 | 204.6 | 205.6 | 205.6 | 205.6 | 206.6 | 207.0 | 205.6 |
| 65° | 188.1 | 194.5 | 192.5 | 190.5 | 192.5 | 193.9 | 194.9 | 195.4 | 194.9 | 194.5 | 193.0 |
| 67.5° | 174.4 | 180.7 | 178.9 | 176.4 | 178.9 | 180.7 | 182.7 | 184.2 | 182.7 | 181.2 | 179.3 |
| 70° | 159.8 | 166.2 | 163.7 | 161.3 | 163.7 | 166.2 | 168.1 | 170.0 | 168.1 | 166.2 | 165.6 |
| 72.5° | 144.2 | 151.5 | 148.6 | 145.7 | 148.6 | 151.5 | 152.5 | 153.5 | 152.0 | 150.6 | 149.6 |
| 75° | 127.2 | 134.5 | 132.1 | 129.1 | 131.5 | 134.0 | 134.5 | 135.0 | 135.0 | 134.5 | 131.5 |
| 77.5° | 109.2 | 115.0 | 113.6 | 112.1 | 113.6 | 115.0 | 115.0 | 115.0 | 115.5 | 115.5 | 111.6 |
| 80° | 87.7 | 91.1 | 91.6 | 92.1 | 92.5 | 93.1 | 92.5 | 92.1 | 91.1 | 90.2 | 87.7 |
| 82.5° | 65.3 | 65.3 | 69.2 | 72.6 | 72.6 | 72.1 | 71.6 | 70.6 | 68.7 | 66.2 | 60.9 |
| 85° | 41.4 | 39.0 | 45.3 | 51.2 | 51.2 | 50.6 | 49.7 | 48.2 | 44.3 | 39.9 | 35.6 |
| 87.5° | 14.1 | 11.6 | 18.0 | 24.3 | 24.9 | 24.9 | 23.9 | 22.9 | 19.0 | 14.7 | 11.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386839
 CATALOG NUMBER: GAW-SA2C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° | 270° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386839
 CATALOG NUMBER: GAW-SA2C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° | 325° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 |
| 2.5° | 3213.9 | 3220.1 | 3226.0 | 3273.8 | 3321.0 | 3376.6 | 3432.1 | 3474.5 | 3516.4 | 3559.7 | 3603.1 |
| 5° | 2570.2 | 2578.0 | 2585.8 | 2643.7 | 2701.2 | 2778.7 | 2856.2 | 2922.9 | 2989.7 | 3068.2 | 3146.6 |
| 7.5° | 1905.1 | 1922.2 | 1938.7 | 2000.6 | 2062.0 | 2145.3 | 2228.1 | 2315.3 | 2402.1 | 2504.4 | 2606.7 |
| 10° | 1496.3 | 1528.5 | 1560.1 | 1623.5 | 1686.8 | 1769.2 | 1851.0 | 1942.1 | 2033.2 | 2134.1 | 2234.4 |
| 12.5° | 1211.3 | 1254.2 | 1296.6 | 1372.5 | 1448.5 | 1547.0 | 1644.9 | 1746.2 | 1847.1 | 1935.8 | 2024.5 |
| 15° | 957.0 | 1003.7 | 1050.0 | 1130.4 | 1210.8 | 1318.9 | 1426.7 | 1537.2 | 1647.3 | 1753.6 | 1859.8 |
| 17.5° | 746.4 | 785.0 | 822.9 | 891.2 | 958.8 | 1063.7 | 1168.4 | 1284.3 | 1400.4 | 1529.9 | 1659.1 |
| 20° | 602.2 | 618.3 | 634.4 | 683.6 | 732.4 | 817.6 | 902.4 | 1020.7 | 1139.2 | 1294.1 | 1449.0 |
| 22.5° | 527.7 | 535.9 | 543.7 | 567.7 | 591.0 | 646.1 | 700.7 | 805.4 | 909.7 | 1078.7 | 1247.3 |
| 25° | 482.8 | 489.1 | 495.5 | 511.1 | 526.7 | 553.0 | 579.3 | 652.9 | 726.4 | 892.6 | 1058.3 |
| 27.5° | 442.5 | 452.1 | 461.4 | 468.8 | 475.5 | 493.6 | 511.1 | 559.3 | 607.6 | 762.5 | 916.9 |
| 30° | 413.1 | 416.6 | 420.0 | 431.2 | 441.9 | 460.4 | 479.0 | 512.5 | 546.2 | 677.3 | 807.9 |
| 32.5° | 379.0 | 383.9 | 388.8 | 400.5 | 412.2 | 429.3 | 446.3 | 473.5 | 500.4 | 612.5 | 724.0 |
| 35° | 348.4 | 353.2 | 358.1 | 369.8 | 381.0 | 399.5 | 417.6 | 440.5 | 462.8 | 560.3 | 657.8 |
| 37.5° | 329.4 | 334.2 | 339.1 | 349.4 | 359.1 | 377.6 | 395.7 | 413.7 | 431.2 | 521.4 | 611.5 |
| 40° | 313.3 | 318.2 | 323.1 | 332.8 | 342.0 | 360.1 | 377.6 | 392.8 | 407.8 | 492.1 | 576.4 |
| 42.5° | 299.2 | 304.6 | 309.9 | 319.6 | 328.9 | 344.9 | 361.0 | 381.0 | 400.5 | 466.8 | 532.5 |
| 45° | 287.5 | 292.8 | 297.7 | 308.4 | 319.1 | 334.7 | 350.3 | 378.1 | 405.9 | 453.6 | 501.4 |
| 47.5° | 276.7 | 282.6 | 287.9 | 299.7 | 311.3 | 330.9 | 349.8 | 373.2 | 396.1 | 443.4 | 490.6 |
| 50° | 266.5 | 273.4 | 280.1 | 294.3 | 307.9 | 340.6 | 372.8 | 376.1 | 379.0 | 435.1 | 490.6 |
| 52.5° | 256.7 | 264.5 | 272.3 | 289.9 | 307.0 | 344.9 | 383.0 | 370.8 | 358.1 | 419.5 | 480.9 |
| 55° | 247.1 | 253.8 | 260.2 | 281.6 | 303.0 | 330.9 | 358.6 | 342.5 | 326.0 | 390.3 | 454.6 |
| 57.5° | 233.9 | 241.1 | 248.0 | 270.9 | 293.8 | 313.3 | 332.3 | 317.7 | 302.6 | 357.2 | 411.3 |
| 60° | 220.2 | 228.6 | 236.8 | 266.0 | 294.8 | 291.4 | 287.5 | 284.5 | 281.2 | 320.1 | 359.1 |
| 62.5° | 208.1 | 216.8 | 225.5 | 263.6 | 301.6 | 278.2 | 254.9 | 257.3 | 259.2 | 287.9 | 316.7 |
| 65° | 195.9 | 204.6 | 213.0 | 231.9 | 250.9 | 241.7 | 232.4 | 236.4 | 239.7 | 268.0 | 296.3 |
| 67.5° | 182.2 | 190.0 | 197.4 | 203.7 | 210.0 | 211.0 | 211.9 | 215.9 | 219.7 | 253.4 | 286.5 |
| 70° | 167.1 | 173.4 | 179.8 | 184.2 | 188.1 | 190.0 | 191.4 | 196.3 | 201.2 | 237.8 | 274.3 |
| 72.5° | 150.1 | 155.5 | 160.3 | 164.2 | 168.1 | 169.6 | 170.5 | 175.4 | 180.3 | 219.3 | 258.2 |
| 75° | 131.5 | 135.9 | 139.9 | 143.3 | 146.6 | 148.6 | 150.6 | 154.0 | 157.3 | 199.8 | 241.7 |
| 77.5° | 111.1 | 115.5 | 119.4 | 122.3 | 124.8 | 126.7 | 128.1 | 132.5 | 136.9 | 172.5 | 207.6 |
| 80° | 86.7 | 92.1 | 96.9 | 99.4 | 101.4 | 101.8 | 101.8 | 105.8 | 109.6 | 135.0 | 159.8 |
| 82.5° | 61.4 | 67.3 | 72.6 | 74.6 | 76.5 | 76.5 | 76.5 | 80.9 | 85.3 | 102.3 | 118.9 |
| 85° | 36.1 | 42.4 | 48.2 | 50.2 | 52.1 | 53.1 | 53.6 | 55.5 | 57.0 | 69.2 | 80.9 |
| 87.5° | 11.2 | 16.5 | 21.4 | 22.5 | 23.4 | 25.4 | 27.2 | 27.8 | 27.8 | 36.1 | 44.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386839
 CATALOG NUMBER: GAW-SA2C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° | 325° |
|--------|------|------|------|------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386839

CATALOG NUMBER: GAW-SA2C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 | 3712.8 |
| 2.5° | 3652.8 | 3702.5 | 3760.5 | 3818.0 | 3867.2 | 3916.4 | 3957.4 |
| 5° | 3246.5 | 3346.3 | 3468.6 | 3590.5 | 3699.1 | 3807.7 | 3934.0 |
| 7.5° | 2735.8 | 2865.0 | 3023.3 | 3181.6 | 3335.1 | 3488.2 | 3682.0 |
| 10° | 2366.1 | 2497.1 | 2664.7 | 2831.8 | 3004.3 | 3176.3 | 3395.5 |
| 12.5° | 2131.2 | 2237.4 | 2399.7 | 2561.9 | 2764.5 | 2966.8 | 3177.8 |
| 15° | 1976.2 | 2092.2 | 2250.0 | 2407.9 | 2629.6 | 2851.3 | 3094.0 |
| 17.5° | 1811.1 | 1962.6 | 2164.8 | 2367.0 | 2629.6 | 2891.7 | 3177.8 |
| 20° | 1638.1 | 1826.7 | 2088.7 | 2350.9 | 2704.7 | 3057.9 | 3422.9 |
| 22.5° | 1465.6 | 1683.9 | 2020.1 | 2355.8 | 2818.2 | 3280.1 | 3772.7 |
| 25° | 1310.2 | 1562.1 | 1978.2 | 2393.8 | 2983.3 | 3572.4 | 4183.4 |
| 27.5° | 1192.3 | 1467.1 | 1961.2 | 2454.7 | 3192.9 | 3931.1 | 4630.2 |
| 30° | 1087.5 | 1367.2 | 1940.7 | 2514.2 | 3394.6 | 4274.5 | 4979.5 |
| 32.5° | 996.9 | 1269.8 | 1901.2 | 2532.1 | 3535.4 | 4538.6 | 5275.4 |
| 35° | 925.8 | 1193.7 | 1834.9 | 2476.1 | 3623.6 | 4771.0 | 5583.3 |
| 37.5° | 864.3 | 1117.2 | 1759.4 | 2401.6 | 3702.1 | 5002.5 | 5929.6 |
| 40° | 805.9 | 1035.4 | 1694.6 | 2353.4 | 3810.2 | 5267.1 | 6295.6 |
| 42.5° | 750.4 | 968.1 | 1642.4 | 2316.8 | 3910.6 | 5503.8 | 6615.7 |
| 45° | 709.0 | 916.5 | 1596.2 | 2275.4 | 3975.3 | 5675.3 | 6856.9 |
| 47.5° | 688.5 | 885.8 | 1571.3 | 2256.4 | 4040.1 | 5823.5 | 7057.2 |
| 50° | 685.6 | 880.4 | 1599.6 | 2318.8 | 4180.5 | 6041.7 | 7286.1 |
| 52.5° | 685.1 | 889.2 | 1681.0 | 2472.8 | 4441.2 | 6409.1 | 7534.1 |
| 55° | 674.9 | 894.6 | 1777.9 | 2660.8 | 4791.0 | 6920.7 | 7980.0 |
| 57.5° | 643.7 | 876.1 | 1877.8 | 2879.1 | 5160.8 | 7442.1 | 8482.4 |
| 60° | 595.4 | 831.3 | 1960.1 | 3088.6 | 5409.3 | 7729.5 | 8675.8 |
| 62.5° | 535.0 | 752.7 | 1987.5 | 3221.7 | 5402.5 | 7583.4 | 8480.8 |
| 65° | 483.3 | 670.4 | 1897.8 | 3124.6 | 5129.2 | 7133.2 | 8095.4 |
| 67.5° | 437.6 | 588.1 | 1673.6 | 2758.7 | 4637.5 | 6515.8 | 7605.3 |
| 70° | 404.4 | 534.0 | 1384.8 | 2235.5 | 4022.1 | 5808.4 | 7037.7 |
| 72.5° | 383.5 | 508.2 | 1129.0 | 1749.2 | 3264.0 | 4778.3 | 6019.8 |
| 75° | 354.7 | 467.7 | 885.8 | 1303.3 | 2498.0 | 3692.8 | 4546.9 |
| 77.5° | 301.1 | 394.2 | 667.5 | 940.9 | 1832.9 | 2724.6 | 3162.2 |
| 80° | 232.4 | 304.6 | 459.0 | 613.4 | 1261.4 | 1909.5 | 2156.0 |
| 82.5° | 165.6 | 212.4 | 278.2 | 344.0 | 838.0 | 1331.6 | 1352.1 |
| 85° | 102.3 | 123.7 | 159.3 | 194.9 | 554.4 | 914.0 | 761.6 |
| 87.5° | 55.0 | 65.8 | 84.3 | 102.3 | 177.4 | 252.4 | 145.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 92.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 95° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 97.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 100° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 102.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 105° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 107.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 110° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P386839
 CATALOG NUMBER: GAW-SA2C-735-U-SLL

CANDELA DISTRIBUTION (continued):

| | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|--------|------|------|------|------|------|------|------|
| 112.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 115° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 117.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 120° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 122.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 125° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 127.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 130° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 132.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 135° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 137.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 140° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 142.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 145° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 147.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 150° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 152.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 155° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 157.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 160° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 162.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 165° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 167.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 170° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 172.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 175° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 177.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 180° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

(END OF REPORT)