

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P386895

Luminaire Tested: GAW-SA2C-760-U-SLL

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-2019
Report Number: P386895
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-26)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: STREETWORKS
Catalog Number: GAW-SA2C-760-U-SLL
Description: GALLEON WALL LUMINAIRE
(2) 70 CRI, 5700K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT
ELIMINATOR LEFT OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12972 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B2 - U0 - G3


Input Watts (W): 113
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P386895
 CATALOG NUMBER: GAW-SA2C-760-U-SLL

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 12.4 fc
 Type III - Medium - N/A

REPORT NUMBER: P386895
CATALOG NUMBER: GAW-SA2C-760-U-SLL

Luminous Intensity Polar Plot



— Vertical Plane Through 75-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P386895
 CATALOG NUMBER: GAW-SA2C-760-U-SLL


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2284.7	0.0	2284.7
	% Fixture	17.6	0.0	17.6
Street Side	Lumens	10687.3	0.0	10687.3
	% Fixture	82.4	0.0	82.4
Total	Lumens	12972.0	0.0	12972.0
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	305.0	2.4
10°-20°	633.6	4.9
20°-30°	901.1	6.9
30°-40°	1298.5	10.0
40°-50°	1830.0	14.1
50°-60°	2544.0	19.6
60°-70°	3076.5	23.7
70°-80°	1891.1	14.6
80°-90°	492.1	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	12972.0	100.0
0°-180°	12972.0	100.0




REPORT NUMBER: P386895
 CATALOG NUMBER: GAW-SA2C-760-U-SLL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1288.0	9.9			
FM (30°-60°)	4635.5	35.7			
FH (60°-80°)	4327.0	33.4			G2/5000
FVH (80°-90°)	436.8	3.4			G3/500
BL (0°-30°)	551.8	4.3	B2/1000		
BM (30°-60°)	1037.1	8.0	B2/2500		
BH (60°-80°)	640.5	4.9	B2/1000		G2/1000
BVH (80°-90°)	55.3	0.4			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type III Medium





REPORT NUMBER: P386895

CATALOG NUMBER: GAW-SA2C-760-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0
2.5°	4212.3	4267.8	4306.2	4344.1	4373.6	4402.7	4445.2	4487.7	4496.0	4503.8	4487.2
5°	4187.4	4322.8	4437.9	4552.6	4658.9	4765.2	4829.0	4892.8	4905.7	4918.7	4878.8
7.5°	3919.3	4119.0	4318.7	4518.3	4701.4	4884.5	4996.0	5107.0	5132.4	5157.3	5091.9
10°	3614.4	3846.7	4092.0	4337.3	4578.5	4819.7	4980.9	5142.2	5174.4	5206.6	5125.1
12.5°	3382.5	3636.1	3898.0	4160.0	4414.6	4668.7	4835.7	5002.7	5042.7	5082.6	5023.5
15°	3293.3	3571.3	3817.7	4064.0	4286.0	4507.4	4644.4	4780.8	4797.4	4813.4	4804.1
17.5°	3382.5	3689.0	3912.0	4134.5	4255.4	4375.7	4430.7	4485.1	4503.3	4520.9	4544.8
20°	3643.4	3974.3	4131.4	4288.1	4282.9	4277.2	4250.7	4223.7	4219.1	4214.4	4281.8
22.5°	4015.8	4400.1	4462.8	4525.1	4379.3	4233.6	4144.9	4055.7	4038.1	4019.9	4091.5
25°	4453.0	4862.2	4850.8	4838.8	4561.4	4283.4	4114.3	3945.2	3925.5	3905.8	3967.0
27.5°	4928.6	5319.6	5244.9	5170.2	4793.2	4416.2	4170.8	3925.5	3905.8	3886.1	3940.1
30°	5300.4	5655.2	5535.4	5415.6	4988.7	4561.9	4270.4	3978.9	3946.8	3914.1	3980.5
32.5°	5615.2	5917.1	5756.3	5595.5	5147.4	4699.3	4384.0	4068.7	4018.4	3968.1	4056.7
35°	5943.0	6178.5	5952.3	5725.7	5289.0	4851.8	4518.3	4184.3	4122.6	4060.9	4182.8
37.5°	6311.8	6507.3	6182.6	5857.4	5448.2	5039.0	4719.6	4399.6	4336.3	4273.0	4428.6
40°	6701.3	6864.1	6431.0	5998.0	5622.5	5247.0	4998.1	4748.6	4688.4	4627.8	4816.5
42.5°	7042.0	7160.8	6662.4	6163.9	5832.5	5500.6	5325.3	5149.5	5149.0	5147.9	5339.3
45°	7298.7	7401.9	6855.3	6308.1	6037.4	5766.2	5674.9	5583.6	5656.7	5729.9	5903.1
47.5°	7511.9	7581.9	7017.1	6451.8	6271.8	6091.9	6105.3	6118.8	6267.7	6416.5	6528.0
50°	7755.6	7699.1	7163.9	6628.1	6572.6	6517.1	6638.5	6759.3	6930.5	7101.1	7176.8
52.5°	8019.6	7869.7	7363.0	6855.8	6918.0	6980.3	7227.1	7474.0	7646.7	7819.4	7847.9
55°	8494.2	8264.4	7729.2	7193.4	7313.2	7432.5	7795.0	8157.1	8291.9	8426.7	8437.1
57.5°	9028.9	8825.1	8242.1	7659.2	7787.8	7916.4	8334.9	8753.0	8898.7	9043.9	9023.7
60°	9234.8	9244.6	8729.1	8213.1	8342.7	8472.4	8880.0	9287.7	9455.2	9622.2	9577.6
62.5°	9027.3	9270.6	8995.2	8719.3	8837.0	8954.2	9353.5	9752.9	9924.6	10096.2	10018.4
65°	8617.1	8858.2	8981.7	9105.1	9144.0	9182.9	9555.8	9928.2	10059.9	10191.1	10151.7
67.5°	8095.3	8290.3	8745.7	9200.5	9122.2	9043.9	9218.7	9393.5	9528.8	9664.2	9641.9
70°	7491.1	7723.5	8330.8	8938.1	8553.3	8167.9	8095.9	8023.8	8170.0	8315.8	8225.5
72.5°	6407.7	6758.3	7406.1	8053.3	7344.4	6635.4	6389.0	6142.7	6327.8	6513.0	6369.3
75°	4839.9	5305.1	6020.8	6736.0	5890.1	5044.2	4715.4	4386.6	4545.8	4705.0	4606.5
77.5°	3365.9	3949.4	4654.2	5359.0	4499.1	3638.7	3394.5	3149.7	3197.4	3244.6	3228.0
80°	2294.9	2678.7	3170.4	3661.5	3089.0	2516.4	2535.6	2554.3	2532.0	2509.1	2542.3
82.5°	1439.2	1709.4	2089.1	2468.2	2164.3	1860.3	2034.6	2208.9	2123.3	2037.2	2069.3
85°	810.6	975.5	1346.9	1717.7	1601.0	1483.8	1586.0	1687.6	1554.9	1422.1	1480.7
87.5°	154.6	257.2	745.3	1232.8	1119.2	1005.6	873.9	742.2	566.3	390.5	570.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386895
 CATALOG NUMBER: GAW-SA2C-760-U-SLL

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386895

CATALOG NUMBER: GAW-SA2C-760-U-SLL

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0
2.5°	4470.6	4461.8	4453.0	4421.3	4389.2	4341.5	4302.1	4233.6	4196.3	4139.7	4083.2
5°	4838.3	4782.3	4726.3	4629.8	4532.8	4425.0	4301.0	4163.6	4059.9	3925.0	3790.2
7.5°	5026.6	4895.9	4764.7	4579.5	4393.9	4226.9	4030.8	3848.3	3692.7	3517.4	3342.1
10°	5043.7	4847.7	4651.1	4410.5	4169.3	3966.5	3740.9	3538.1	3351.4	3150.2	2948.4
12.5°	4963.8	4755.3	4546.3	4281.3	4015.8	3785.5	3542.8	3315.6	3108.7	2887.2	2665.3
15°	4794.8	4628.3	4461.3	4212.9	3964.4	3732.1	3496.6	3227.5	2993.5	2766.9	2539.7
17.5°	4568.1	4489.3	4409.9	4230.5	4050.5	3849.3	3621.1	3305.2	3031.4	2785.1	2538.7
20°	4348.7	4377.8	4406.3	4334.7	4263.2	4101.9	3902.7	3548.0	3198.4	2876.3	2553.7
22.5°	4162.5	4302.1	4441.1	4496.5	4551.5	4454.5	4298.9	3888.7	3426.1	3005.5	2584.9
25°	4027.7	4259.0	4490.3	4675.0	4859.1	4816.0	4696.2	4302.6	3727.9	3191.7	2654.9
27.5°	3994.0	4277.7	4561.4	4847.7	5133.4	5173.4	5140.2	4738.7	4087.9	3423.0	2757.6
30°	4046.9	4334.2	4621.0	4969.5	5317.5	5476.8	5521.4	5102.3	4499.1	3692.7	2885.7
32.5°	4145.4	4427.0	4708.7	5088.3	5467.4	5708.1	5850.2	5434.8	4785.9	3896.0	3005.5
35°	4304.7	4568.1	4831.6	5226.8	5622.0	5933.2	6192.5	5778.1	5040.6	4038.1	3035.0
37.5°	4583.7	4810.3	5037.0	5402.1	5766.7	6170.2	6559.7	6156.2	5316.0	4175.0	3033.5
40°	5005.3	5165.6	5325.3	5633.9	5942.0	6449.7	6975.6	6577.8	5620.4	4323.3	3026.2
42.5°	5530.7	5613.2	5695.1	5939.4	6183.7	6741.7	7353.2	6990.1	5910.9	4461.3	3011.7
45°	6075.8	6097.6	6119.3	6273.4	6426.9	6973.0	7610.4	7299.8	6164.5	4581.1	2997.2
47.5°	6639.0	6564.3	6489.6	6550.8	6612.0	7150.4	7794.0	7534.7	6419.1	4713.9	3008.1
50°	7252.6	7044.6	6836.6	6804.5	6772.3	7327.8	8010.3	7833.4	6725.1	4907.3	3089.5
52.5°	7876.0	7533.1	7190.3	7063.3	6935.7	7539.4	8297.1	8205.3	7161.8	5207.1	3251.8
55°	8447.5	8011.3	7575.1	7404.0	7232.9	7863.0	8647.2	8751.4	7721.4	5590.3	3458.8
57.5°	9002.9	8508.7	8014.4	7855.7	7697.0	8338.6	9090.6	9241.5	8286.7	5958.1	3628.9
60°	9533.0	9043.9	8554.3	8427.3	8299.7	8929.8	9569.8	9459.9	8578.2	6130.2	3681.8
62.5°	9940.6	9551.7	9162.7	9095.8	9028.4	9527.8	9938.0	9374.8	8393.0	5960.6	3528.3
65°	10112.3	9890.8	9668.9	9731.6	9793.9	9980.0	10029.8	9125.9	7811.1	5485.6	3160.0
67.5°	9619.1	9664.2	9709.3	9972.8	10235.7	10107.6	9757.0	8635.2	6982.9	4812.4	2641.9
70°	8134.8	8405.5	8675.7	9299.1	9922.0	9637.8	9026.3	7754.6	5986.1	4037.0	2087.5
72.5°	6225.1	6529.6	6833.5	7758.7	8683.5	8421.6	7672.7	6369.3	4799.4	3223.8	1647.7
75°	4507.4	4851.3	5194.6	6215.3	7236.0	6872.4	5739.2	4560.3	3645.5	2460.9	1275.8
77.5°	3210.9	3441.1	3671.4	4679.6	5687.3	5095.0	3820.2	3068.7	2523.1	1710.5	897.2
80°	2575.5	2505.0	2434.5	2996.1	3557.8	3459.3	2526.8	1970.8	1746.2	1146.2	546.1
82.5°	2101.0	1928.8	1756.6	2021.1	2285.6	2271.1	1753.5	1445.9	1299.7	796.6	293.5
85°	1538.8	1469.8	1400.8	1634.7	1868.6	1669.0	1187.7	919.0	1013.4	586.6	159.7
87.5°	750.5	857.3	963.6	1239.5	1514.9	1137.4	360.4	178.4	246.9	162.3	77.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386895
 CATALOG NUMBER: GAW-SA2C-760-U-SLL

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386895

CATALOG NUMBER: GAW-SA2C-760-U-SLL

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0
2.5°	4041.2	3998.7	3950.4	3902.2	3847.2	3791.7	3759.0	3725.9	3690.1	3654.3	3613.8
5°	3701.0	3611.8	3510.6	3409.5	3309.4	3209.3	3155.4	3101.4	3044.4	2986.8	2937.0
7.5°	3212.4	3082.2	2942.2	2801.7	2677.2	2552.2	2474.9	2397.1	2326.6	2255.5	2195.9
10°	2782.5	2616.5	2476.0	2334.9	2241.0	2147.1	2076.1	2005.0	1936.6	1867.6	1801.7
12.5°	2499.3	2333.3	2244.1	2154.9	2077.1	1999.3	1917.4	1834.9	1741.0	1646.7	1577.7
15°	2388.8	2237.9	2138.8	2039.3	1935.0	1830.3	1729.6	1629.0	1518.0	1407.1	1328.7
17.5°	2341.1	2143.5	2005.0	1866.0	1728.6	1591.2	1474.5	1357.8	1236.4	1115.1	1035.7
20°	2290.8	2027.9	1842.2	1656.0	1479.7	1303.3	1171.1	1038.8	930.4	822.0	761.4
22.5°	2245.2	1904.9	1672.1	1438.7	1230.2	1021.7	892.0	761.9	695.5	629.1	604.7
25°	2226.5	1797.6	1511.3	1225.0	1005.1	784.7	692.4	600.1	574.6	548.7	536.3
27.5°	2229.6	1701.6	1375.9	1049.7	851.6	653.5	590.2	526.9	511.4	495.3	487.5
30°	2241.5	1597.4	1248.3	899.3	735.9	572.6	531.6	490.1	473.5	456.9	447.1
32.5°	2255.0	1504.0	1149.8	795.1	661.8	528.0	494.3	460.0	443.9	427.9	418.0
35°	2231.7	1427.8	1082.4	737.0	614.1	490.6	462.1	433.1	415.4	397.8	388.5
37.5°	2192.3	1351.0	1030.0	708.5	582.9	456.9	436.2	414.9	396.8	378.1	369.3
40°	2156.5	1286.2	991.1	695.5	565.8	435.7	418.0	400.4	381.7	362.5	352.2
42.5°	2127.4	1242.6	952.7	662.8	550.3	437.2	412.3	386.9	368.7	350.6	339.2
45°	2105.6	1214.1	922.6	631.2	535.7	440.3	408.7	377.0	358.9	340.2	326.7
47.5°	2103.6	1199.1	901.4	603.7	508.3	412.3	399.3	386.4	359.9	333.0	317.4
50°	2132.1	1174.7	876.5	577.8	481.8	385.9	403.5	420.6	375.5	329.9	310.1
52.5°	2191.7	1131.7	837.1	542.5	449.7	356.3	383.8	410.8	371.9	332.4	307.0
55°	2263.8	1068.4	777.4	486.0	407.1	327.8	352.2	376.0	351.6	326.7	296.1
57.5°	2309.0	988.5	702.2	415.9	359.4	302.9	316.9	330.4	320.5	310.7	279.5
60°	2282.0	882.2	617.7	352.7	317.4	282.1	279.5	276.4	291.0	305.5	269.7
62.5°	2150.3	772.2	543.0	313.8	287.3	260.4	254.6	248.4	272.3	295.6	257.8
65°	1927.8	695.5	495.8	296.1	266.6	237.0	230.8	224.6	231.8	239.1	221.5
67.5°	1645.1	648.3	468.8	289.4	253.6	217.3	210.0	202.8	201.2	199.7	193.4
70°	1353.6	619.2	451.2	283.2	239.6	195.5	188.8	182.0	180.0	177.4	172.7
72.5°	1131.7	615.6	449.1	282.7	228.2	173.7	167.5	161.3	158.7	155.6	152.0
75°	926.8	577.8	426.3	274.9	212.6	149.9	144.2	138.5	136.4	133.8	130.7
77.5°	687.7	478.2	358.4	238.6	182.0	125.5	119.8	113.6	113.1	112.0	109.4
80°	446.0	345.9	256.2	166.5	132.8	98.5	93.9	88.7	89.2	89.7	87.6
82.5°	247.9	201.7	156.6	111.5	90.8	70.0	67.9	65.3	66.9	67.9	65.3
85°	130.7	101.7	84.0	66.4	52.4	38.4	38.4	37.9	39.9	42.0	39.9
87.5°	56.5	35.8	30.6	24.9	14.0	2.6	3.1	3.1	4.1	5.2	4.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386895
 CATALOG NUMBER: GAW-SA2C-760-U-SLL

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386895

CATALOG NUMBER: GAW-SA2C-760-U-SLL

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0
2.5°	3572.9	3535.0	3496.6	3454.6	3462.4	3430.2	3398.1	3377.9	3357.6	3351.4	3345.2
5°	2887.2	2844.2	2800.6	2761.7	2795.4	2772.6	2749.8	2746.7	2743.0	2743.0	2742.5
7.5°	2136.2	2090.1	2043.4	2011.3	2044.4	2040.3	2036.2	2058.5	2080.8	2098.9	2116.5
10°	1735.9	1679.9	1623.3	1575.6	1567.3	1543.5	1519.1	1524.3	1528.9	1548.6	1568.3
12.5°	1508.7	1441.8	1374.9	1318.9	1293.5	1254.1	1214.1	1189.2	1164.3	1166.9	1169.0
15°	1249.9	1185.1	1119.7	1071.5	1055.4	1024.8	994.2	963.1	931.5	918.5	905.0
17.5°	955.8	904.0	851.6	819.4	819.4	810.6	801.8	786.2	770.2	757.2	743.7
20°	700.7	673.2	645.2	631.7	635.8	636.4	636.4	644.1	651.9	647.8	643.6
22.5°	579.8	570.0	560.1	554.4	556.5	557.0	557.5	564.8	571.5	576.7	581.4
25°	523.3	517.1	510.9	508.8	513.4	514.0	514.0	518.6	523.3	528.5	533.7
27.5°	479.2	476.6	474.0	470.4	475.1	475.1	474.5	479.7	484.4	489.1	493.2
30°	437.2	438.2	438.8	437.7	440.8	442.9	444.5	448.1	451.2	454.8	458.5
32.5°	407.6	406.1	404.5	403.5	410.2	413.9	417.5	421.1	424.2	425.8	427.4
35°	379.1	375.5	371.9	369.3	375.5	380.2	384.8	391.6	397.8	398.8	399.9
37.5°	359.9	355.3	350.6	347.5	350.1	352.2	354.2	361.5	368.7	372.9	376.5
40°	341.8	337.1	332.4	329.9	331.4	331.9	332.4	336.1	339.2	347.0	354.2
42.5°	327.3	321.6	315.8	312.7	313.8	314.8	315.3	314.8	314.3	321.6	328.8
45°	312.7	306.5	300.3	296.7	297.2	297.2	297.2	296.1	294.6	298.2	301.8
47.5°	301.3	294.1	286.8	283.2	282.1	281.1	280.1	279.5	278.5	281.1	283.2
50°	289.9	282.1	273.8	269.7	267.1	266.1	265.0	264.5	263.5	266.1	268.1
52.5°	281.1	271.8	262.4	255.7	253.1	251.5	250.0	250.5	250.5	251.5	252.1
55°	265.5	257.2	248.4	243.8	239.1	238.1	237.0	238.6	239.6	239.6	239.6
57.5°	248.4	240.6	232.3	229.2	225.1	225.1	224.6	226.6	228.2	229.2	230.3
60°	233.4	224.6	215.8	213.2	211.6	211.1	210.6	213.2	215.2	217.3	219.4
62.5°	219.4	210.0	200.7	197.6	197.1	197.6	197.6	200.2	202.3	204.3	206.4
65°	203.8	194.5	184.6	181.5	182.6	184.1	185.7	187.7	189.3	191.4	193.4
67.5°	186.7	178.9	170.6	167.5	168.0	170.1	172.2	173.7	174.8	176.9	178.9
70°	168.0	161.3	154.6	152.5	152.0	154.6	156.6	157.7	158.7	161.3	163.4
72.5°	147.8	142.1	136.4	134.8	135.4	136.9	138.5	140.0	141.1	143.7	145.7
75°	127.1	121.9	116.7	115.7	116.7	118.2	119.8	120.8	121.9	125.0	127.6
77.5°	106.8	101.1	94.9	94.4	95.9	97.5	98.5	100.1	101.7	105.8	110.0
80°	85.6	79.4	72.6	72.1	73.6	75.2	76.8	78.3	79.9	85.1	89.7
82.5°	62.8	55.5	48.2	47.2	52.4	53.9	55.5	58.1	60.2	64.8	69.5
85°	37.9	30.6	23.3	22.8	27.5	30.1	32.7	35.8	38.4	42.5	46.7
87.5°	4.1	2.1	0.0	0.0	0.5	2.6	4.7	7.3	9.9	14.0	17.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386895
 CATALOG NUMBER: GAW-SA2C-760-U-SLL

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386895
 CATALOG NUMBER: GAW-SA2C-760-U-SLL

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0
2.5°	3322.4	3299.0	3322.9	3346.2	3356.1	3365.9	3340.5	3314.6	3355.0	3395.0	3405.3
5°	2721.8	2700.5	2716.6	2732.2	2697.4	2662.7	2659.0	2654.9	2685.0	2715.0	2719.7
7.5°	2109.8	2103.1	2118.1	2133.1	2089.1	2044.4	2022.7	2000.9	2008.1	2015.4	2014.4
10°	1573.0	1577.2	1595.8	1614.0	1579.8	1545.5	1530.5	1515.4	1532.0	1548.1	1563.2
12.5°	1178.3	1187.2	1206.9	1226.0	1212.0	1197.5	1199.1	1200.6	1219.8	1238.5	1255.1
15°	915.4	925.8	939.8	953.2	953.8	953.8	967.2	980.2	978.7	977.1	988.5
17.5°	757.7	771.2	772.8	774.3	774.8	775.4	774.3	773.3	765.5	757.7	766.5
20°	648.8	653.5	657.6	661.3	656.6	651.4	638.4	625.5	620.3	615.1	623.4
22.5°	590.2	598.5	594.4	589.7	580.3	570.5	560.6	550.3	549.8	548.7	553.4
25°	540.9	547.7	540.4	533.2	526.4	519.7	512.9	506.2	505.7	505.1	507.2
27.5°	500.0	506.2	499.4	492.7	487.0	481.3	476.1	470.9	469.9	468.8	469.4
30°	464.7	470.4	464.7	458.5	454.3	449.7	446.0	442.4	441.9	441.4	441.4
32.5°	433.1	438.8	434.6	430.5	426.8	423.2	420.6	418.0	415.4	412.8	407.1
35°	405.6	411.3	408.7	405.6	401.4	397.3	392.6	387.4	380.7	373.4	370.3
37.5°	382.2	387.9	385.3	382.8	377.0	371.3	363.0	354.2	352.2	349.6	349.0
40°	363.6	372.4	367.2	361.5	352.7	343.9	339.7	335.6	334.5	333.5	332.4
42.5°	342.8	356.3	347.0	337.6	329.3	321.0	320.0	319.0	318.4	317.9	317.9
45°	316.9	331.4	322.1	312.2	307.5	302.9	302.9	302.9	303.4	303.4	304.4
47.5°	292.5	301.3	296.7	292.0	289.4	286.8	287.3	287.8	289.4	290.4	293.0
50°	271.8	274.9	275.9	276.4	274.9	273.3	274.4	274.9	276.4	277.5	279.5
52.5°	256.7	261.4	261.4	260.9	260.9	260.9	261.9	262.9	264.5	266.1	268.1
55°	246.9	253.6	251.5	249.5	250.0	250.0	251.0	252.1	253.6	254.6	257.8
57.5°	237.5	244.8	242.7	240.6	240.6	240.6	241.2	241.7	243.2	244.3	246.4
60°	226.6	233.9	231.8	229.2	229.8	230.3	230.8	230.8	231.8	232.3	232.3
62.5°	213.7	220.9	218.9	216.3	217.8	218.9	218.9	218.9	219.9	220.4	218.9
65°	200.2	206.9	204.9	202.8	204.9	206.4	207.5	208.0	207.5	206.9	205.4
67.5°	185.7	192.4	190.3	187.7	190.3	192.4	194.5	196.0	194.5	192.9	190.9
70°	170.1	176.9	174.3	171.7	174.3	176.9	178.9	181.0	178.9	176.9	176.3
72.5°	153.5	161.3	158.2	155.1	158.2	161.3	162.3	163.4	161.8	160.3	159.2
75°	135.4	143.1	140.5	137.4	140.0	142.6	143.1	143.7	143.7	143.1	140.0
77.5°	116.2	122.4	120.8	119.3	120.8	122.4	122.4	122.4	122.9	122.9	118.8
80°	93.4	97.0	97.5	98.0	98.5	99.1	98.5	98.0	97.0	95.9	93.4
82.5°	69.5	69.5	73.6	77.3	77.3	76.8	76.2	75.2	73.1	70.5	64.8
85°	44.1	41.5	48.2	54.5	54.5	53.9	52.9	51.3	47.2	42.5	37.9
87.5°	15.0	12.4	19.2	25.9	26.5	26.5	25.4	24.4	20.2	15.6	11.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386895
 CATALOG NUMBER: GAW-SA2C-760-U-SLL

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386895
 CATALOG NUMBER: GAW-SA2C-760-U-SLL

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0
2.5°	3420.9	3427.6	3433.9	3484.7	3535.0	3594.1	3653.2	3698.4	3743.0	3789.1	3835.3
5°	2735.8	2744.1	2752.4	2814.1	2875.3	2957.8	3040.2	3111.3	3182.3	3265.8	3349.3
7.5°	2027.9	2046.0	2063.6	2129.5	2194.9	2283.5	2371.7	2464.5	2556.9	2665.8	2774.7
10°	1592.7	1627.0	1660.7	1728.1	1795.5	1883.2	1970.3	2067.3	2164.3	2271.6	2378.4
12.5°	1289.3	1335.0	1380.1	1461.0	1541.9	1646.7	1750.9	1858.8	1966.1	2060.5	2154.9
15°	1018.6	1068.4	1117.7	1203.2	1288.8	1403.9	1518.6	1636.3	1753.5	1866.6	1979.6
17.5°	794.5	835.5	876.0	948.6	1020.7	1132.2	1243.7	1367.1	1490.6	1628.5	1765.9
20°	641.0	658.1	675.3	727.6	779.5	870.3	960.5	1086.5	1212.6	1377.5	1542.4
22.5°	561.7	570.5	578.8	604.2	629.1	687.7	745.8	857.3	968.3	1148.3	1327.7
25°	514.0	520.7	527.4	544.0	560.6	588.6	616.7	695.0	773.3	950.1	1126.5
27.5°	470.9	481.3	491.1	498.9	506.2	525.4	544.0	595.4	646.7	811.7	976.1
30°	439.8	443.4	447.1	459.0	470.4	490.1	509.8	545.6	581.4	720.9	859.9
32.5°	403.5	408.7	413.9	426.3	438.8	456.9	475.1	504.1	532.6	651.9	770.7
35°	370.8	376.0	381.2	393.6	405.6	425.3	444.5	468.8	492.7	596.4	700.2
37.5°	350.6	355.8	361.0	371.9	382.2	401.9	421.1	440.3	459.0	554.9	650.9
40°	333.5	338.7	343.9	354.2	364.1	383.3	401.9	418.0	434.1	523.8	613.5
42.5°	318.4	324.1	329.9	340.2	350.1	367.2	384.3	405.6	426.3	496.9	566.9
45°	306.0	311.7	316.9	328.3	339.7	356.3	372.9	402.5	432.0	482.8	533.7
47.5°	294.6	300.8	306.5	319.0	331.4	352.2	372.4	397.3	421.6	472.0	522.3
50°	283.7	291.0	298.2	313.3	327.8	362.5	396.8	400.4	403.5	463.1	522.3
52.5°	273.3	281.6	289.9	308.6	326.7	367.2	407.6	394.7	381.2	446.5	511.9
55°	262.9	270.2	276.9	299.8	322.6	352.2	381.7	364.6	347.0	415.4	483.9
57.5°	248.9	256.7	264.0	288.4	312.7	333.5	353.7	338.1	322.1	380.2	437.7
60°	234.4	243.2	252.1	283.2	313.8	310.1	306.0	302.9	299.3	340.7	382.2
62.5°	221.5	230.8	240.1	280.6	321.0	296.1	271.2	273.8	275.9	306.5	337.1
65°	208.5	217.8	226.6	246.9	267.1	257.2	247.4	251.5	255.2	285.2	315.3
67.5°	194.0	202.3	210.0	216.8	223.5	224.6	225.6	229.8	233.9	269.7	305.0
70°	177.9	184.6	191.4	196.0	200.2	202.3	203.8	209.0	214.2	253.1	292.0
72.5°	159.7	165.4	170.6	174.8	178.9	180.5	181.5	186.7	191.9	233.4	274.9
75°	140.0	144.7	148.8	152.5	156.1	158.2	160.3	163.9	167.5	212.6	257.2
77.5°	118.2	122.9	127.1	130.2	132.8	134.8	136.4	141.1	145.7	183.6	220.9
80°	92.3	98.0	103.2	105.8	107.9	108.4	108.4	112.5	116.7	143.7	170.1
82.5°	65.3	71.6	77.3	79.4	81.4	81.4	81.4	86.1	90.8	108.9	126.5
85°	38.4	45.1	51.3	53.4	55.5	56.5	57.0	59.1	60.7	73.6	86.1
87.5°	11.9	17.6	22.8	23.9	24.9	27.0	29.0	29.6	29.6	38.4	47.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386895
 CATALOG NUMBER: GAW-SA2C-760-U-SLL

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386895

CATALOG NUMBER: GAW-SA2C-760-U-SLL

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0	3952.0
2.5°	3888.2	3941.1	4002.8	4064.0	4116.4	4168.8	4212.3
5°	3455.6	3562.0	3692.1	3821.8	3937.5	4053.1	4187.4
7.5°	2912.1	3049.6	3218.1	3386.7	3550.0	3712.9	3919.3
10°	2518.5	2658.0	2836.4	3014.3	3197.9	3381.0	3614.4
12.5°	2268.5	2381.6	2554.3	2727.0	2942.7	3158.0	3382.5
15°	2103.6	2227.0	2395.0	2563.1	2799.1	3035.0	3293.3
17.5°	1927.8	2089.1	2304.3	2519.5	2799.1	3078.1	3382.5
20°	1743.6	1944.4	2223.4	2502.4	2878.9	3254.9	3643.4
22.5°	1560.0	1792.4	2150.3	2507.6	2999.8	3491.4	4015.8
25°	1394.6	1662.7	2105.6	2548.0	3175.6	3802.6	4453.0
27.5°	1269.1	1561.6	2087.5	2612.9	3398.6	4184.3	4928.6
30°	1157.6	1455.3	2065.7	2676.1	3613.3	4550.0	5300.4
32.5°	1061.1	1351.6	2023.7	2695.3	3763.2	4831.1	5615.2
35°	985.4	1270.6	1953.2	2635.7	3857.1	5078.5	5943.0
37.5°	920.1	1189.2	1872.8	2556.3	3940.6	5324.8	6311.8
40°	857.8	1102.1	1803.8	2505.0	4055.7	5606.4	6701.3
42.5°	798.7	1030.5	1748.3	2466.1	4162.5	5858.5	7042.0
45°	754.6	975.5	1699.0	2422.0	4231.5	6041.0	7298.7
47.5°	732.8	942.9	1672.6	2401.8	4300.5	6198.7	7511.9
50°	729.7	937.2	1702.7	2468.2	4449.9	6431.0	7755.6
52.5°	729.2	946.5	1789.3	2632.1	4727.3	6822.1	8019.6
55°	718.3	952.2	1892.5	2832.3	5099.7	7366.7	8494.2
57.5°	685.1	932.5	1998.8	3064.6	5493.4	7921.6	9028.9
60°	633.8	884.8	2086.5	3287.6	5757.9	8227.6	9234.8
62.5°	569.5	801.3	2115.5	3429.2	5750.6	8072.0	9027.3
65°	514.5	713.6	2020.1	3326.0	5459.6	7592.8	8617.1
67.5°	465.7	626.0	1781.5	2936.5	4936.3	6935.7	8095.3
70°	430.5	568.4	1474.0	2379.5	4281.3	6182.6	7491.1
72.5°	408.2	540.9	1201.7	1861.9	3474.3	5086.2	6407.7
75°	377.6	497.9	942.9	1387.3	2659.0	3930.7	4839.9
77.5°	320.5	419.6	710.5	1001.5	1951.1	2900.2	3365.9
80°	247.4	324.1	488.6	653.0	1342.7	2032.5	2294.9
82.5°	176.3	226.1	296.1	366.2	892.0	1417.4	1439.2
85°	108.9	131.7	169.6	207.5	590.2	973.0	810.6
87.5°	58.6	70.0	89.7	108.9	188.8	268.7	154.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386895
CATALOG NUMBER: GAW-SA2C-760-U-SLL

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)