

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P507769

Luminaire Tested: **UFLD-CA2-90-750-U-33**

Issue Date: 3/30/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P507769  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2101-110-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 3/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: UFLD-CA2-90-750-U-33  
Description: UTILITY FLOOD, 3X3 OPTIC  
Light Source: (8) 5000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	11928 lumens	Max Intensity:	59482.6 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x -1°V
Efficacy:	133.3 lumens/watt		
Luminous Opening:	Rectangular (W 1.25' x L: 0.67' x H: 0')		
Beam Angle (50%):	22°H x 21.9°V	Field Angle (10%):	47.1°H x 46.9°V
Beam Lumens:	5085.4 lumens	Field Lumens:	10318.4 lumens
Beam Efficiency:	42.6%	Field Efficiency:	86.5%


Input Watts (W): 89.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P507769

CATALOG NUMBER: UFLD-CA2-90-750-U-33

### Iso-Candela Plot





REPORT NUMBER: P507769  
 CATALOG NUMBER: UFLD-CA2-90-750-U-33


### Lumen Table

90	2.1	5.4		6.1		4.4		2.1		4.4		6.1		5.4		2.1			
80	2.1	5.4		6.1		4.4		2.1		4.4		6.1		5.4		2.1			
70	1.9	0.8	0.6	0.5	0.6	1.0	1.0	0.4	0.4	1.0	1.0	0.6	0.5	0.6	0.8	1.9			
60		0.4	0.2	0.3	0.7	1.1	1.0	0.6	0.6	1.0	1.1	0.7	0.3	0.2	0.4				
50	1.4	0.2	0.0	0.2	0.9	1.5	1.9	2.0	2.0	1.9	1.5	0.9	0.2	0.0	0.2	1.4			
40		0.1	0.0	0.2	1.3	2.5	5.5	10.8	10.8	5.5	2.5	1.3	0.2	0.0	0.1				
30	1.2	0.1	0.0	0.3	1.7	13.1	74.3	143.8	143.8	74.3	13.1	1.7	0.3	0.0	0.1	1.2			
20		0.1	0.0	0.6	4.3	69.6	254.4	514.5	514.5	254.4	69.6	4.3	0.6	0.0	0.1				
10	1.1	0.0	0.1	0.9	9.3	127.7	487.6	1334.3	1334.3	487.6	127.7	9.3	0.9	0.1	0.0	1.1			
0		0.0	0.1	0.9	8.9	123.5	467.7	1271.9	1271.9	467.7	123.5	8.9	0.9	0.1	0.0				
-10	1.2	0.1	0.0	0.7	3.9	60.8	230.0	451.4	451.4	230.0	60.8	3.9	0.7	0.0	0.1	1.2			
-20		0.1	0.0	0.3	1.6	9.8	58.7	120.4	120.4	58.7	9.8	1.6	0.3	0.0	0.1				
-30	1.5	0.1	0.0	0.2	1.1	2.3	4.2	8.1	8.1	4.2	2.3	1.1	0.2	0.0	0.1	1.5			
-40		0.2	0.0	0.3	0.8	1.4	1.7	1.8	1.8	1.7	1.4	0.8	0.3	0.0	0.2				
-50	2.0	0.4	0.2	0.4	0.7	1.1	0.9	0.6	0.6	0.9	1.1	0.7	0.4	0.2	0.4	2.0			
-60		0.8	0.6	0.6	0.7	1.0	1.0	0.4	0.4	1.0	1.0	0.7	0.6	0.6	0.8				
-70	2.2	5.5		6.2		4.4		2.1		4.4		6.2		5.5		2.2			
-80		5.5		6.2		4.4		2.1		4.4		6.2		5.5					
-90	2.2	5.5		6.2		4.4		2.1		4.4		6.2		5.5		2.2			
	-90	-80	-70	-60	-50	-40	-30	-20	-10	0	10	20	30	40	50	60	70	80	90

REPORT NUMBER: P507769

CATALOG NUMBER: UFLD-CA2-90-750-U-33


### Luminous Intensity Polar Plot



REPORT NUMBER: P507769

CATALOG NUMBER: UFLD-CA2-90-750-U-33

### Luminous Intensity Plot



**Beam:**  
 H Angle: 22°  
 V Angle: 21.9°  
 Lumens: 5085.4  
 Efficiency: 42.6%

**Field:**  
 H Angle: 47.1°  
 V Angle: 46.9°  
 Lumens: 10318.4  
 Efficiency: 86.5%

**Spill:**  
 Lumens: 1609.6  
 Efficiency: 13.5%

— Vertical Distribution through 0-Deg  
 - - Horizontal Distribution through -1-Deg



REPORT NUMBER: P507769

CATALOG NUMBER: UFLD-CA2-90-750-U-33

FIELD  
 BEAM

**CANDELA DISTRIBUTION:**

	0°	1°	3°	5°	7°	9°	11°	13°	15°	17°	19.5°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	7.0	28.8	38.0	26.0	22.5	26.7	30.9	38.7	45.7	59.1
75°	2.8	3.5	8.4	16.2	23.2	30.9	38.7	40.8	38.7	33.8	27.4
65°	7.7	7.7	9.1	12.0	16.2	21.1	25.3	29.5	34.5	39.4	42.2
55°	10.6	11.3	12.0	14.1	16.2	19.7	22.5	25.3	28.1	31.7	35.9
47.5°	49.2	49.9	49.9	49.2	49.9	50.6	53.5	52.0	50.6	50.6	47.8
42.5°	79.5	80.2	79.5	80.2	80.9	81.6	82.3	81.6	80.9	80.9	78.8
37.5°	102.0	102.7	102.7	102.7	102.7	100.6	99.9	98.5	97.1	95.7	94.2
33°	296.8	327.8	289.8	275.0	246.2	213.1	198.3	185.7	154.7	129.4	109.0
29°	1951.1	1997.5	1911.7	1792.8	1646.5	1434.8	1175.3	952.3	655.5	391.8	238.4
25.5°	4514.1	4550.6	4504.2	4315.0	3934.5	3604.6	3043.4	2541.9	2018.6	1489.0	907.3
22.5°	7187.5	7132.6	6999.7	6784.5	6392.0	5894.0	5209.7	4476.8	3725.6	2916.8	1972.9
19.5°	10273.8	10121.8	9812.4	9386.8	8902.2	8161.6	7383.0	6577.7	5671.1	4648.4	3358.5
17°	13521.8	13331.2	13033.0	12422.5	11637.5	10454.5	9396.7	8248.8	7149.5	6015.0	4596.4
15°	17459.8	17744.0	16928.1	15654.3	14292.7	12770.6	11295.0	9732.9	8362.1	7098.2	5558.5
13°	24623.4	24430.0	22898.8	21005.4	18542.3	15790.1	13538.0	11478.6	9699.1	8132.8	6396.2
11°	31315.7	31407.2	29713.5	27285.6	24035.4	20219.8	16578.5	13379.0	11119.9	9258.8	7199.4
9°	38815.5	38349.2	36683.7	33534.8	29580.6	24736.6	20084.7	15700.8	12528.0	10283.6	7936.5
7°	49796.1	50125.3	46886.4	41320.8	34921.8	29529.2	23927.8	18303.1	13939.6	11209.2	8539.3
5°	56935.1	56194.4	54453.7	49196.2	40608.3	32958.7	26955.0	20563.7	15411.0	11987.8	9040.8
3°	58281.3	58302.4	57461.9	53583.6	45826.4	35915.6	29019.3	22249.6	16550.4	12577.2	9371.4
1°	58206.7	58116.0	58168.7	55188.7	47847.9	37584.6	29995.6	23109.1	17077.2	12786.1	9550.0
0°	58298.9	58346.7	58357.9	55263.9	47982.2	37610.7	30011.0	23185.8	17066.0	12762.2	9546.5
-1°	59482.6	59364.4	58136.4	54964.3	47378.7	37115.5	29725.5	22862.2	16901.4	12671.5	9495.9
-3°	58315.7	58455.0	56641.8	52184.7	43832.5	34933.7	28246.3	21681.3	15962.4	12257.9	9219.4
-5°	54289.1	53717.3	51581.2	46432.7	38012.3	31500.7	25602.5	19506.6	14595.8	11587.6	8812.2
-7°	45718.1	45032.4	42176.1	36950.2	32242.7	27403.7	22106.8	17004.1	13143.4	10707.7	8249.5
-9°	33977.2	34495.6	32536.7	30783.3	26973.3	22647.7	18173.0	14242.0	11785.2	9725.9	7565.2
-11°	27869.3	27951.6	26464.8	24143.7	21068.7	17694.0	14734.4	12309.9	10332.1	8585.7	6778.8
-13°	20340.7	20744.5	19510.8	17972.6	16091.1	13939.6	12196.7	10479.1	8974.0	7565.2	5925.7
-15°	15177.5	15248.5	14536.7	13723.7	12725.6	11506.7	10158.4	8843.2	7665.1	6508.8	4973.4
-17°	12031.4	11805.6	11567.2	10958.1	10270.2	9323.5	8348.0	7422.4	6422.9	5367.2	3976.0
-19.5°	8790.4	8803.1	8747.5	8220.0	7819.8	7270.5	6548.1	5752.0	4845.3	3906.4	2771.9
-22.5°	6338.5	6247.1	6131.1	5766.7	5452.3	4919.9	4346.7	3689.0	3007.5	2320.3	1519.2
-25.5°	3793.1	3782.6	3688.3	3464.0	3222.0	2814.1	2359.0	1912.4	1482.7	1033.2	597.1
-29°	1510.8	1509.4	1434.8	1292.7	1171.1	995.9	774.4	535.9	378.4	226.5	168.8
-33°	211.0	211.0	203.3	197.6	180.1	166.0	156.1	134.3	121.7	112.5	99.9
-37.5°	95.7	96.4	95.7	96.4	95.0	95.0	94.2	93.5	92.8	92.1	90.0
-42.5°	76.0	76.0	75.3	75.3	76.0	76.0	76.0	76.0	74.6	73.9	69.6
-47.5°	39.4	40.1	40.1	40.1	42.9	47.1	43.6	42.9	45.0	41.5	39.4
-55°	11.3	11.3	12.0	14.1	16.2	19.7	22.5	25.3	28.1	30.9	35.2
-65°	7.0	7.7	8.4	12.0	16.2	21.1	24.6	29.5	34.5	39.4	42.2
-75°	2.8	3.5	8.4	16.2	22.5	30.9	38.7	40.8	38.7	33.8	28.1
-85°	0.7	7.0	28.8	38.0	26.0	23.2	26.7	30.9	38.7	46.4	59.1
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P507769

CATALOG NUMBER: UFLD-CA2-90-750-U-33

**CANDELA DISTRIBUTION (continued):**

	22.5°	25.5°	29°	33°	37.5°	42.5°	47.5°	55°	65°	75°	85°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	74.6	87.2	100.6	113.2	123.8	132.9	136.4	134.3	123.8	121.0	127.3
75°	23.9	23.9	26.0	28.8	34.5	42.2	56.3	78.1	99.9	116.8	125.9
65°	41.5	36.6	29.5	23.9	21.1	20.4	19.7	28.8	57.7	101.3	124.5
55°	40.8	42.2	40.1	33.8	23.9	14.8	8.4	6.3	23.2	78.8	123.8
47.5°	45.0	44.3	41.5	36.6	27.4	15.5	4.9	0.0	11.3	65.4	123.1
42.5°	73.1	64.7	55.6	41.5	27.4	14.8	3.5	0.0	4.9	57.7	123.1
37.5°	91.4	86.5	76.0	57.0	32.4	13.4	1.4	0.0	0.7	51.3	122.4
33°	97.8	91.4	83.7	72.4	38.7	12.7	1.4	0.0	1.4	46.4	122.4
29°	137.9	99.9	84.4	73.1	47.8	18.3	0.0	0.0	1.4	42.2	122.4
25.5°	397.4	175.1	99.2	73.1	52.8	23.2	0.0	0.0	1.4	38.7	122.4
22.5°	1031.8	422.7	138.6	77.4	55.6	28.1	0.7	0.0	1.4	36.6	121.7
19.5°	1958.8	908.0	268.7	92.1	59.8	33.8	3.5	0.0	1.4	34.5	121.7
17°	2904.1	1509.4	476.9	112.5	64.0	39.4	5.6	0.0	0.7	33.1	121.7
15°	3665.8	2001.0	685.8	133.6	67.5	43.6	7.7	0.0	0.7	31.7	121.7
13°	4386.1	2560.9	939.7	165.3	71.0	47.1	10.6	0.0	0.7	30.9	121.7
11°	5073.9	3042.0	1187.2	202.6	74.6	50.6	13.4	0.0	0.7	30.2	121.7
9°	5667.6	3496.3	1429.9	246.9	78.8	54.2	16.2	0.0	0.7	29.5	121.7
7°	6153.6	3883.2	1648.6	291.2	83.0	56.3	19.0	0.0	0.0	28.8	121.0
5°	6520.7	4176.5	1790.7	330.6	85.8	58.4	21.1	0.0	0.0	28.8	121.0
3°	6716.2	4355.1	1904.7	358.0	87.9	59.1	22.5	0.0	0.0	28.1	121.0
1°	6830.2	4445.8	1946.2	367.8	88.6	59.8	23.2	0.0	0.0	28.1	121.0
0°	6826.7	4429.7	1949.0	369.3	88.6	60.5	23.9	0.0	0.0	28.8	121.0
-1°	6790.1	4400.1	1931.4	362.2	88.6	59.8	23.2	0.0	0.0	28.8	121.0
-3°	6607.2	4272.1	1844.2	337.6	87.2	59.1	22.5	0.0	0.0	28.8	121.0
-5°	6307.6	4006.3	1706.3	305.3	85.1	59.1	21.8	0.0	0.0	29.5	121.0
-7°	5853.9	3685.5	1523.4	259.5	82.3	57.7	20.4	0.0	0.0	29.5	121.0
-9°	5346.1	3274.1	1287.1	218.0	79.5	56.3	18.3	0.0	0.7	30.2	121.7
-11°	4677.9	2759.2	1036.7	177.9	76.7	54.2	16.9	0.0	0.7	30.9	121.7
-13°	3951.4	2218.3	777.9	148.4	74.6	51.3	14.1	0.0	0.7	32.4	121.7
-15°	3184.7	1690.8	541.6	125.9	71.0	47.8	11.3	0.0	1.4	33.1	121.7
-17°	2430.1	1203.4	348.9	106.9	67.5	44.3	8.4	0.0	1.4	33.8	121.7
-19.5°	1549.5	700.5	192.7	87.2	62.6	38.0	4.2	0.0	2.1	35.9	121.7
-22.5°	727.3	288.4	118.2	75.3	56.3	29.5	0.7	0.0	2.1	38.0	122.4
-25.5°	270.8	137.2	91.4	72.4	51.3	21.8	0.0	0.0	2.8	40.8	122.4
-29°	116.8	93.5	80.9	70.3	43.6	14.8	0.0	0.0	3.5	44.3	122.4
-33°	93.5	87.2	79.5	65.4	33.1	9.8	1.4	0.0	4.2	48.5	123.1
-37.5°	86.5	80.2	69.6	49.2	26.7	12.0	2.8	0.0	4.9	54.2	123.1
-42.5°	63.3	59.1	47.1	37.3	26.7	15.5	4.9	0.0	9.1	61.2	123.8
-47.5°	38.7	40.1	39.4	35.9	27.4	16.9	7.7	0.0	15.5	68.9	124.5
-55°	40.1	41.5	40.1	33.8	26.0	17.6	13.4	7.7	26.7	83.0	125.2
-65°	41.5	37.3	30.9	25.3	23.2	23.2	22.5	28.8	60.5	104.8	126.6
-75°	24.6	24.6	27.4	30.9	36.6	44.3	57.7	78.1	102.7	121.0	127.3
-85°	75.3	87.9	101.3	113.2	124.5	132.9	136.4	134.3	126.6	125.9	128.7
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P507769

CATALOG NUMBER: UFLD-CA2-90-750-U-33

**CANDELA DISTRIBUTION (continued):**

	90°
90°	0.0
85°	0.0
75°	0.0
65°	0.0
55°	0.0
47.5°	0.0
42.5°	0.0
37.5°	0.0
33°	0.0
29°	0.0
25.5°	0.0
22.5°	0.0
19.5°	0.0
17°	0.0
15°	0.0
13°	0.0
11°	0.0
9°	0.0
7°	0.0
5°	0.0
3°	0.0
1°	0.0
0°	0.0
-1°	0.0
-3°	0.0
-5°	0.0
-7°	0.0
-9°	0.0
-11°	0.0
-13°	0.0
-15°	0.0
-17°	0.0
-19.5°	0.0
-22.5°	0.0
-25.5°	0.0
-29°	0.0
-33°	0.0
-37.5°	0.0
-42.5°	0.0
-47.5°	0.0
-55°	0.0
-65°	0.0
-75°	0.0
-85°	0.0
-90°	0.0

(END OF REPORT)