

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P386756

Luminaire Tested: GAW-SA2C-722-U-SLR-HSS

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-2019  
Report Number: P386756  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-28)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: STREETWORKS  
Catalog Number: GAW-SA2C-722-U-SLR-HSS  
Description: GALLEON WALL LUMINAIRE  
(2) 70 CRI, 2200K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT  
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8044 lumens  
Efficiency: N/A  
Efficacy: 72.5 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')  
IES Classification: Type IV - Medium  
BUG Rating: B1 - U0 - G2


Input Watts (W): 111  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P386756  
 CATALOG NUMBER: GAW-SA2C-722-U-SLR-HSS

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 26.2 fc  
 Type IV - Medium - N/A

REPORT NUMBER: P386756  
CATALOG NUMBER: GAW-SA2C-722-U-SLR-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 345-Deg Lateral    - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P386756  
 CATALOG NUMBER: GAW-SA2C-722-U-SLR-HSS


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	973.6	0.0	973.6
	% Fixture	12.1	0.0	12.1
<b>Street Side</b>	Lumens	7070.4	0.0	7070.4
	% Fixture	87.9	0.0	87.9
<b>Total</b>	Lumens	8044.0	0.0	8044.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	201.1	2.5
10°-20°	400.3	5.0
20°-30°	568.4	7.1
30°-40°	839.6	10.4
40°-50°	1210.9	15.1
50°-60°	1699.8	21.1
60°-70°	1981.5	24.6
70°-80°	1013.0	12.6
80°-90°	129.4	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8044.0	100.0
0°-180°	8044.0	100.0

**Coefficient of Utilization**




REPORT NUMBER: P386756  
 CATALOG NUMBER: GAW-SA2C-722-U-SLR-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	882.3	11.0			
FM (30°-60°)	3309.4	41.1			
FH (60°-80°)	2757.2	34.3			G2/5000
FVH (80°-90°)	121.5	1.5			G2/225
BL (0°-30°)	287.6	3.6	B1/500		
BM (30°-60°)	440.9	5.5	B1/1000		
BH (60°-80°)	237.3	2.9	B1/500		G1/500
BVH (80°-90°)	7.9	0.1			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B1-U0-G2**  
 Type IV Medium





REPORT NUMBER: P386756

CATALOG NUMBER: GAW-SA2C-722-U-SLR-HSS

**CANDELA DISTRIBUTION (FULL):**

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3
2.5°	2869.2	2847.1	2822.7	2743.0	2669.1	2584.5	2515.5	2467.5	2407.3	2329.2	2309.4
5°	2848.6	2825.0	2748.4	2571.2	2416.1	2265.1	2119.6	2034.2	1928.3	1820.8	1794.1
7.5°	2641.7	2616.9	2506.4	2263.6	2054.8	1836.8	1647.8	1530.8	1411.1	1312.8	1260.6
10°	2426.3	2399.3	2275.1	1980.5	1723.3	1526.2	1387.5	1275.9	1162.7	1057.5	973.7
12.5°	2278.1	2242.7	2107.8	1773.9	1549.9	1416.1	1286.5	1152.8	999.6	886.8	794.6
15°	2216.0	2175.6	2033.1	1694.3	1488.5	1331.5	1162.7	998.4	818.9	689.8	605.2
17.5°	2264.0	2211.4	2058.6	1689.0	1411.5	1197.7	984.3	791.5	596.8	466.1	405.9
20°	2427.1	2358.1	2164.2	1687.4	1318.2	1038.8	768.3	550.3	393.3	316.3	284.7
22.5°	2684.0	2592.9	2315.8	1699.6	1221.7	871.9	554.9	373.8	295.3	255.3	236.7
25°	2994.2	2888.6	2534.2	1742.7	1137.1	709.6	403.2	295.3	249.2	219.9	204.3
27.5°	3289.1	3203.4	2810.1	1804.8	1071.6	578.5	327.3	250.4	213.0	193.6	181.0
30°	3583.7	3475.8	3093.2	1878.7	992.7	489.7	287.7	228.3	190.9	170.3	162.3
32.5°	3797.9	3708.3	3315.0	1932.1	908.5	431.8	257.2	208.8	178.3	157.4	145.6
35°	4049.8	3948.4	3505.2	1943.9	854.4	395.2	231.3	187.9	154.7	136.0	123.5
37.5°	4321.8	4195.7	3724.7	1918.0	812.1	377.3	211.9	178.3	144.4	125.4	112.0
40°	4622.9	4480.4	3935.4	1880.6	770.5	371.2	197.0	171.1	136.4	117.0	103.3
42.5°	4940.0	4771.9	4118.0	1841.4	744.3	350.2	195.5	163.9	130.3	109.4	95.7
45°	5206.3	5036.0	4305.5	1828.4	725.6	327.3	202.0	158.9	126.1	103.3	89.9
47.5°	5418.6	5257.4	4497.5	1857.4	714.9	306.4	184.1	165.4	123.9	97.9	85.0
50°	5672.0	5489.5	4768.1	1943.9	699.3	285.4	166.5	189.4	123.9	94.5	80.8
52.5°	5989.8	5809.2	5069.9	2078.0	668.0	256.5	149.8	189.8	125.0	89.9	75.5
55°	6389.6	6258.5	5500.9	2225.1	618.1	213.8	129.6	163.1	120.4	81.6	70.5
57.5°	6773.0	6665.9	5893.8	2325.7	551.4	166.9	112.8	131.5	110.1	71.6	62.9
59°	6877.8	6760.8	6037.9	2330.3	501.5	145.6	104.4	108.6	107.8	67.1	58.3
60°	6877.8	6753.5	6079.4	2305.9	465.3	133.8	99.1	96.8	112.4	64.0	55.6
62.5°	6753.1	6578.6	5944.5	2140.9	379.6	113.9	86.5	80.0	101.0	57.5	49.2
65°	6494.0	6239.8	5484.9	1842.5	338.4	104.4	74.7	65.5	70.1	50.7	43.1
67.5°	6061.9	5717.4	4822.2	1488.5	322.0	101.7	64.4	55.6	53.0	43.4	37.7
70°	5300.8	4918.6	4017.7	1170.3	307.9	100.6	54.1	46.9	42.7	36.6	32.0
72.5°	3858.1	3459.5	2852.4	915.0	299.5	102.9	43.4	39.3	35.1	28.6	24.8
75°	2206.8	1945.8	1603.2	604.4	255.3	98.3	33.5	32.8	25.2	20.6	17.1
77.5°	1140.2	1105.5	960.7	232.1	122.3	43.1	22.1	19.1	14.9	12.6	10.3
80°	492.0	486.6	421.1	67.1	32.4	24.0	12.6	8.0	6.9	5.3	4.2
82.5°	170.0	170.0	149.8	22.5	14.5	11.8	1.5	0.0	0.0	0.0	0.0
85°	34.3	38.5	27.1	0.0	5.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386756  
 CATALOG NUMBER: GAW-SA2C-722-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3
2.5°	2285.3	2239.2	2236.2	2207.2	2171.0	2154.6	2145.1	2161.9	2182.5	2184.7	2215.6
5°	1773.9	1725.5	1745.7	1694.3	1704.6	1694.3	1677.5	1680.6	1689.7	1661.1	1696.6
7.5°	1245.8	1209.2	1232.4	1218.7	1237.0	1244.2	1233.9	1218.7	1173.7	1168.4	1199.3
10°	939.0	897.4	872.7	846.8	852.5	864.3	860.5	849.4	820.9	822.4	852.1
12.5°	754.5	708.0	658.9	595.2	579.6	588.4	579.6	573.1	545.7	548.0	574.3
15°	572.4	534.3	482.8	431.8	403.9	406.6	382.2	365.1	347.9	327.3	343.4
17.5°	386.4	363.2	347.9	332.7	299.5	291.9	261.0	227.9	214.9	205.4	212.3
20°	273.6	261.0	254.9	254.2	235.1	225.6	195.5	174.9	168.4	166.5	170.7
22.5°	228.6	219.5	210.7	205.8	196.3	185.2	162.3	152.1	147.5	145.2	148.2
25°	198.9	192.1	182.9	174.5	170.7	158.9	142.5	134.9	131.9	129.6	131.1
27.5°	176.8	170.7	160.1	154.7	151.7	141.4	127.3	121.2	118.5	117.8	117.4
30°	159.3	153.6	143.7	137.6	132.2	123.1	114.7	108.6	105.9	105.2	104.4
32.5°	141.8	137.2	130.7	124.6	118.9	110.5	103.3	98.3	94.1	93.4	93.0
35°	119.7	115.1	111.7	111.3	105.9	97.9	92.6	86.1	82.7	81.6	81.9
37.5°	106.3	100.2	92.6	95.3	93.7	88.0	80.8	74.3	70.9	70.1	70.1
40°	97.9	91.5	82.7	78.1	82.7	81.6	70.1	63.6	60.2	59.8	59.1
42.5°	89.9	83.5	73.5	65.9	68.2	71.6	60.6	54.5	51.1	50.3	49.2
45°	84.2	77.4	66.3	57.5	53.0	60.2	51.8	44.2	42.3	40.8	40.0
47.5°	78.9	72.4	59.8	49.9	42.3	43.4	41.5	36.2	33.9	32.4	32.0
50°	74.3	67.5	54.1	42.7	35.1	32.0	33.5	28.6	26.7	25.2	24.4
52.5°	69.0	62.5	48.0	37.0	29.3	25.2	25.5	22.5	20.6	19.4	19.1
55°	64.8	58.3	43.1	32.4	25.9	20.6	18.3	17.5	16.4	15.6	15.2
57.5°	59.1	53.0	38.1	27.4	22.1	16.8	14.1	14.1	13.7	13.0	12.6
59°	55.6	50.3	35.1	24.8	20.2	14.5	12.6	13.0	12.6	11.8	11.4
60°	53.0	48.0	32.8	22.9	19.1	13.3	11.4	12.2	11.8	11.1	10.7
62.5°	46.9	43.4	28.2	19.1	16.8	10.7	9.5	10.3	10.3	9.9	9.5
65°	41.2	37.3	24.0	16.0	15.6	9.1	7.6	9.1	9.5	8.8	8.0
67.5°	35.8	32.0	21.0	13.0	14.5	7.2	5.7	7.6	10.3	8.0	7.2
70°	30.5	26.7	16.4	10.3	15.2	5.0	4.6	6.9	12.2	8.8	6.9
72.5°	23.6	20.6	11.4	7.6	16.4	3.4	3.4	5.7	13.7	9.5	6.5
75°	16.4	13.3	6.9	4.6	13.3	2.3	2.3	5.3	13.0	8.8	6.1
77.5°	9.5	7.2	2.3	0.4	6.9	0.0	0.4	3.8	9.1	5.3	2.7
80°	3.4	1.5	0.0	0.0	4.2	0.0	0.0	0.0	0.8	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P386756

CATALOG NUMBER: GAW-SA2C-722-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3
2.5°	2223.6	2275.1	2321.2	2390.9	2473.6	2568.9	2650.8	2738.8	2821.5	2855.8	2879.5
5°	1703.8	1767.5	1841.8	1944.3	2080.7	2248.8	2406.2	2584.1	2775.4	2871.1	2961.0
7.5°	1204.6	1269.4	1361.6	1470.6	1635.6	1835.7	2041.5	2287.3	2546.4	2697.7	2846.7
10°	866.2	945.8	1032.0	1181.0	1348.6	1538.4	1750.3	2024.7	2313.5	2481.2	2660.7
12.5°	589.5	680.2	810.6	977.5	1174.5	1360.5	1544.5	1806.3	2141.7	2307.8	2500.3
15°	353.6	403.9	541.9	735.1	976.7	1208.4	1410.0	1672.6	2030.0	2233.5	2433.6
17.5°	218.0	241.2	316.3	474.8	728.6	1021.7	1298.0	1627.2	2046.0	2293.7	2507.9
20°	173.8	182.9	206.9	280.5	482.8	815.9	1171.8	1618.1	2176.7	2481.6	2711.4
22.5°	150.9	159.7	175.7	203.9	303.7	610.9	1052.2	1626.5	2364.2	2763.2	3031.5
25°	133.0	140.6	155.9	179.1	222.6	430.2	924.1	1663.8	2608.5	3112.7	3397.7
27.5°	118.9	125.4	139.5	160.8	190.9	300.3	778.9	1709.2	2898.1	3470.1	3751.4
30°	105.9	111.7	124.2	144.0	165.8	230.9	619.6	1740.0	3188.1	3751.4	4004.0
32.5°	94.9	99.1	110.5	127.3	144.0	184.1	471.0	1735.1	3403.4	3985.4	4185.8
35°	83.5	87.6	97.6	112.0	125.4	152.1	370.4	1642.5	3590.9	4228.1	4393.9
37.5°	70.9	76.2	85.7	98.7	107.8	133.8	299.5	1530.8	3781.1	4505.5	4626.0
40°	60.2	65.5	73.9	88.0	93.7	126.9	230.2	1394.8	3994.9	4815.7	4880.5
42.5°	49.9	54.9	63.6	75.8	88.4	109.4	170.3	1239.3	4200.3	5081.0	5112.6
45°	40.4	45.3	54.5	66.7	94.5	90.7	131.9	1072.7	4366.1	5301.6	5311.9
47.5°	32.0	36.6	46.1	62.9	88.0	72.4	94.1	942.0	4505.1	5473.9	5446.8
50°	24.8	28.6	38.5	72.0	77.0	59.8	71.3	898.6	4629.8	5580.6	5510.4
52.5°	19.4	22.9	31.6	67.5	59.8	49.5	59.8	939.4	4800.5	5669.0	5546.3
55°	15.6	19.1	24.8	38.5	40.8	41.9	51.1	977.5	5095.1	5876.3	5757.8
57.5°	13.0	16.4	20.2	27.1	30.9	35.4	45.3	981.7	5442.2	6220.8	6108.7
59°	11.8	14.9	18.3	24.0	27.1	32.4	42.7	958.8	5564.6	6346.2	6290.1
60°	11.1	14.1	17.1	22.1	25.2	30.5	41.2	937.1	5569.9	6341.6	6367.5
62.5°	9.5	12.6	15.2	18.7	21.3	25.9	37.0	856.7	5344.3	6133.9	6321.0
65°	8.4	11.1	13.7	16.0	18.3	23.2	33.5	710.0	4959.0	5798.9	6002.8
67.5°	7.6	9.5	12.6	14.1	16.4	20.6	29.7	506.1	4477.7	5389.3	5521.5
70°	6.9	9.1	11.4	13.0	14.9	17.9	25.5	290.8	3781.1	4789.4	4883.6
72.5°	6.5	8.8	10.3	12.2	13.3	16.0	23.2	136.8	2768.6	3836.7	4082.5
75°	5.7	8.0	9.5	11.4	12.6	14.5	19.8	65.5	1841.4	2776.6	3055.9
77.5°	3.4	6.5	8.8	10.3	11.1	12.6	16.4	37.7	1175.3	1921.8	2263.6
80°	0.0	2.3	6.5	8.8	9.5	10.7	12.6	29.7	628.8	1097.9	1317.8
82.5°	0.0	0.0	4.6	6.9	6.5	7.2	9.5	18.7	283.5	717.6	808.7
85°	0.0	0.0	1.5	5.3	4.6	3.4	6.5	6.5	62.1	363.2	453.1
87.5°	0.0	0.0	0.0	0.4	2.3	1.5	2.7	0.8	0.4	27.1	109.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386756

CATALOG NUMBER: GAW-SA2C-722-U-SLR-HSS

**CANDELA DISTRIBUTION (continued):**

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3	2620.3
2.5°	2962.1	2990.3	3038.0	3060.5	3049.4	3002.5	2946.5	2889.4	2855.8	2869.2
5°	3144.3	3289.5	3373.3	3401.2	3354.7	3249.5	3111.9	2930.5	2866.1	2848.6
7.5°	3144.3	3417.5	3590.6	3621.0	3517.4	3311.2	3053.2	2770.1	2676.0	2641.7
10°	3033.8	3405.7	3647.0	3695.3	3550.5	3242.2	2896.6	2573.4	2461.8	2426.3
12.5°	2909.2	3309.7	3563.9	3630.6	3511.7	3173.6	2788.0	2440.4	2309.0	2278.1
15°	2832.6	3191.6	3401.9	3450.3	3400.0	3133.6	2762.1	2400.4	2245.7	2216.0
17.5°	2860.0	3100.1	3175.9	3204.1	3238.1	3119.5	2832.6	2488.1	2292.2	2264.0
20°	2963.3	3003.7	2964.4	2999.9	3091.3	3133.3	3000.6	2700.0	2464.8	2427.1
22.5°	3138.6	2953.8	2843.6	2857.7	2969.0	3178.6	3257.5	3002.5	2731.2	2684.0
25°	3342.8	2994.2	2776.6	2764.0	2878.3	3238.4	3492.2	3331.8	3046.4	2994.2
27.5°	3599.7	3084.9	2762.8	2750.3	2846.7	3294.5	3687.3	3657.2	3378.3	3289.1
30°	3797.9	3174.0	2803.6	2774.7	2878.3	3333.3	3844.0	3933.5	3642.8	3583.7
32.5°	3940.0	3279.2	2869.9	2828.0	2967.5	3400.4	3964.8	4186.6	3887.4	3797.9
35°	4048.2	3393.5	2977.0	2908.0	3090.2	3502.1	4078.0	4456.0	4147.7	4049.8
37.5°	4149.6	3554.0	3144.3	3062.0	3282.6	3666.0	4197.6	4761.6	4438.8	4321.8
40°	4291.0	3735.7	3402.3	3329.1	3606.2	3889.3	4347.0	5080.2	4770.0	4622.9
42.5°	4432.4	3930.9	3666.4	3686.2	4009.7	4160.7	4539.8	5417.1	5097.0	4940.0
45°	4561.5	4132.1	4042.5	4134.0	4384.3	4458.3	4731.5	5611.8	5358.0	5206.3
47.5°	4676.6	4383.6	4416.4	4659.9	4810.4	4727.7	4874.8	5779.9	5552.4	5418.6
50°	4810.4	4709.0	4909.1	5253.6	5300.8	4971.6	5005.1	5978.8	5779.5	5672.0
52.5°	4956.7	5052.0	5454.8	5758.5	5743.3	5236.4	5136.2	6201.7	6090.8	5989.8
55°	5122.9	5329.0	5935.3	6231.1	6218.1	5532.2	5353.4	6477.2	6481.1	6389.6
57.5°	5369.4	5567.6	6261.6	6613.3	6635.0	5873.6	5721.6	6785.9	6833.9	6773.0
59°	5546.3	5722.3	6390.7	6773.0	6861.4	6137.7	5990.6	6965.0	6933.4	6877.8
60°	5677.4	5820.6	6454.8	6856.4	6992.9	6316.8	6189.1	7070.2	6945.2	6877.8
62.5°	6001.7	6034.8	6570.2	6950.9	7144.1	6714.7	6747.8	7249.3	6863.3	6753.1
65°	6152.9	6170.1	6568.7	6781.7	6997.8	7024.5	7254.7	7254.7	6663.2	6494.0
67.5°	6089.7	6007.0	6242.9	6220.8	6436.5	6840.4	7445.2	6988.7	6280.6	6061.9
70°	5575.2	5257.0	5152.2	5161.8	5326.8	5949.8	7067.9	6205.9	5556.6	5300.8
72.5°	4638.9	3875.6	3616.8	3912.2	3955.2	4572.6	6023.4	4673.6	4097.8	3858.1
75°	3731.2	2732.0	2311.3	2623.0	2696.2	3346.3	4659.5	2910.7	2393.6	2206.8
77.5°	2680.5	1961.0	1658.5	1636.7	1731.3	2122.2	3306.3	1464.9	1221.7	1140.2
80°	1522.8	1290.7	1389.8	1311.3	1358.9	1326.9	1570.8	642.5	526.3	492.0
82.5°	919.2	762.9	826.2	687.9	870.4	758.0	605.2	205.8	178.7	170.0
85°	597.9	416.9	217.2	145.6	299.9	484.4	135.3	56.0	43.1	34.3
87.5°	206.2	106.3	10.7	4.6	32.0	90.3	5.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)