

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P386840

Luminaire Tested: GAW-SA2C-740-U-SLR-HSS

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-2019
Report Number: P386840
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-28)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: STREETWORKS
Catalog Number: GAW-SA2C-740-U-SLR-HSS
Description: GALLEON WALL LUMINAIRE
(2) 70 CRI, 4000K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10942 lumens
Efficiency: N/A
Efficacy: 96.8 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Medium
BUG Rating: B1 - U0 - G2

Input Watts (W): 113
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT






REPORT NUMBER: P386840
 CATALOG NUMBER: GAW-SA2C-740-U-SLR-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 8.9 fc
 Type IV - Medium - N/A

REPORT NUMBER: P386840
CATALOG NUMBER: GAW-SA2C-740-U-SLR-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 345-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P386840
 CATALOG NUMBER: GAW-SA2C-740-U-SLR-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1324.3	0.0	1324.3
	% Fixture	12.1	0.0	12.1
Street Side	Lumens	9617.7	0.0	9617.7
	% Fixture	87.9	0.0	87.9
Total	Lumens	10942.0	0.0	10942.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	273.6	2.5
10°-20°	544.5	5.0
20°-30°	773.2	7.1
30°-40°	1142.1	10.4
40°-50°	1647.1	15.1
50°-60°	2312.2	21.1
60°-70°	2695.4	24.6
70°-80°	1377.9	12.6
80°-90°	176.0	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10942.0	100.0
0°-180°	10942.0	100.0

Coefficient of Utilization




REPORT NUMBER: P386840
 CATALOG NUMBER: GAW-SA2C-740-U-SLR-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1200.1	11.0			
FM (30°-60°)	4501.7	41.1			
FH (60°-80°)	3750.5	34.3			G2/5000
FVH (80°-90°)	165.3	1.5			G2/225
BL (0°-30°)	391.2	3.6	B1/500		
BM (30°-60°)	599.7	5.5	B1/1000		
BH (60°-80°)	322.8	2.9	B1/500		G1/500
BVH (80°-90°)	10.7	0.1			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2
 Type IV Medium





REPORT NUMBER: P386840

CATALOG NUMBER: GAW-SA2C-740-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3
2.5°	3902.8	3872.8	3839.6	3731.3	3630.7	3515.6	3421.8	3356.5	3274.6	3168.3	3141.3
5°	3874.8	3842.7	3738.5	3497.5	3286.5	3081.2	2883.2	2767.1	2623.0	2476.8	2440.5
7.5°	3593.4	3559.7	3409.3	3079.1	2795.1	2498.6	2241.4	2082.3	1919.5	1785.8	1714.8
10°	3300.5	3263.7	3094.7	2694.0	2344.1	2076.1	1887.4	1735.5	1581.6	1438.5	1324.4
12.5°	3098.8	3050.6	2867.1	2413.0	2108.2	1926.3	1750.0	1568.1	1359.7	1206.3	1080.8
15°	3014.3	2959.4	2765.5	2304.7	2024.8	1811.2	1581.6	1358.1	1114.0	938.3	823.2
17.5°	3079.7	3008.1	2800.3	2297.4	1920.1	1629.2	1339.0	1076.7	811.8	634.0	552.1
20°	3301.5	3207.7	2943.8	2295.4	1793.1	1413.1	1045.0	748.5	535.0	430.3	387.2
22.5°	3650.9	3527.0	3150.2	2311.9	1661.9	1186.0	754.8	508.5	401.7	347.3	321.9
25°	4072.9	3929.3	3447.2	2370.5	1546.8	965.2	548.4	401.7	339.0	299.1	277.8
27.5°	4474.1	4357.4	3822.5	2455.0	1457.7	786.9	445.3	340.6	289.8	263.3	246.2
30°	4874.8	4728.1	4207.6	2555.6	1350.4	666.1	391.4	310.5	259.7	231.7	220.8
32.5°	5166.1	5044.3	4509.3	2628.2	1235.8	587.3	349.9	284.1	242.6	214.1	198.0
35°	5508.8	5370.9	4768.0	2644.2	1162.2	537.6	314.7	255.6	210.5	185.1	168.0
37.5°	5878.9	5707.3	5066.6	2609.0	1104.7	513.2	288.2	242.6	196.5	170.5	152.4
40°	6288.4	6094.5	5353.2	2558.2	1048.2	504.9	268.0	232.7	185.6	159.1	140.5
42.5°	6719.7	6491.1	5601.5	2504.8	1012.4	476.4	265.9	222.9	177.3	148.8	130.1
45°	7082.0	6850.3	5856.6	2487.2	987.0	445.3	274.7	216.2	171.6	140.5	122.3
47.5°	7370.8	7151.5	6117.8	2526.6	972.5	416.8	250.4	225.0	168.5	133.2	115.6
50°	7715.5	7467.2	6485.9	2644.2	951.2	388.3	226.5	257.6	168.5	128.6	109.9
52.5°	8147.8	7902.1	6896.4	2826.7	908.7	348.9	203.7	258.2	170.0	122.3	102.6
55°	8691.6	8513.2	7482.7	3026.8	840.8	290.8	176.2	221.9	163.8	110.9	95.9
57.5°	9213.1	9067.4	8017.2	3163.6	750.1	227.0	153.4	178.8	149.8	97.5	85.5
59°	9355.6	9196.5	8213.1	3169.9	682.2	198.0	142.0	147.7	146.7	91.2	79.3
60°	9355.6	9186.6	8269.6	3136.7	632.9	181.9	134.8	131.7	152.9	87.1	75.7
62.5°	9186.1	8948.7	8086.1	2912.2	516.3	155.0	117.7	108.9	137.4	78.3	66.9
65°	8833.6	8487.8	7460.9	2506.3	460.3	142.0	101.6	89.2	95.4	68.9	58.6
67.5°	8245.8	7777.2	6559.5	2024.8	438.0	138.4	87.6	75.7	72.1	59.1	51.3
70°	7210.6	6690.6	5465.2	1591.9	418.8	136.9	73.6	63.8	58.1	49.8	43.5
72.5°	5248.0	4705.8	3880.0	1244.6	407.4	140.0	59.1	53.4	47.7	38.9	33.7
75°	3001.9	2646.8	2180.8	822.1	347.3	133.7	45.6	44.6	34.2	28.0	23.3
77.5°	1551.0	1503.8	1306.8	315.7	166.4	58.6	30.1	25.9	20.2	17.1	14.0
80°	669.2	662.0	572.8	91.2	44.1	32.7	17.1	10.9	9.3	7.3	5.7
82.5°	231.2	231.2	203.7	30.6	19.7	16.1	2.1	0.0	0.0	0.0	0.0
85°	46.7	52.4	36.8	0.0	6.7	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386840

CATALOG NUMBER: GAW-SA2C-740-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3
2.5°	3108.7	3046.0	3041.8	3002.4	2953.2	2930.9	2917.9	2940.7	2968.7	2971.8	3013.8
5°	2413.0	2347.2	2374.7	2304.7	2318.7	2304.7	2281.9	2286.0	2298.5	2259.6	2307.8
7.5°	1694.6	1644.8	1676.4	1657.8	1682.6	1692.5	1678.5	1657.8	1596.6	1589.3	1631.3
10°	1277.3	1220.8	1187.1	1151.8	1159.6	1175.7	1170.5	1155.5	1116.6	1118.7	1159.1
12.5°	1026.4	963.1	896.3	809.7	788.4	800.4	788.4	779.6	742.3	745.4	781.2
15°	778.6	726.8	656.8	587.3	549.5	553.1	519.9	496.6	473.3	445.3	467.1
17.5°	525.6	494.0	473.3	452.5	407.4	397.1	355.1	310.0	292.4	279.4	288.7
20°	372.2	355.1	346.8	345.8	319.8	306.9	265.9	237.9	229.1	226.5	232.2
22.5°	311.0	298.6	286.7	279.9	267.0	251.9	220.8	206.8	200.6	197.5	201.6
25°	270.6	261.3	248.8	237.4	232.2	216.2	193.9	183.5	179.4	176.2	178.3
27.5°	240.5	232.2	217.7	210.5	206.3	192.3	173.1	164.8	161.2	160.2	159.7
30°	216.7	208.9	195.4	187.1	179.9	167.4	156.0	147.7	144.1	143.1	142.0
32.5°	192.8	186.6	177.8	169.5	161.7	150.3	140.5	133.7	128.0	127.0	126.5
35°	162.8	156.5	151.9	151.4	144.1	133.2	126.0	117.2	112.5	110.9	111.5
37.5°	144.6	136.3	126.0	129.6	127.5	119.7	109.9	101.1	96.4	95.4	95.4
40°	133.2	124.4	112.5	106.3	112.5	110.9	95.4	86.6	81.9	81.4	80.3
42.5°	122.3	113.5	100.0	89.7	92.8	97.5	82.4	74.1	69.5	68.4	66.9
45°	114.6	105.2	90.2	78.3	72.1	81.9	70.5	60.1	57.5	55.5	54.4
47.5°	107.3	98.5	81.4	67.9	57.5	59.1	56.5	49.2	46.1	44.1	43.5
50°	101.1	91.8	73.6	58.1	47.7	43.5	45.6	38.9	36.3	34.2	33.2
52.5°	93.8	85.0	65.3	50.3	39.9	34.2	34.7	30.6	28.0	26.4	25.9
55°	88.1	79.3	58.6	44.1	35.2	28.0	24.9	23.8	22.3	21.3	20.7
57.5°	80.3	72.1	51.8	37.3	30.1	22.8	19.2	19.2	18.7	17.6	17.1
59°	75.7	68.4	47.7	33.7	27.5	19.7	17.1	17.6	17.1	16.1	15.6
60°	72.1	65.3	44.6	31.1	25.9	18.1	15.6	16.6	16.1	15.0	14.5
62.5°	63.8	59.1	38.4	25.9	22.8	14.5	13.0	14.0	14.0	13.5	13.0
65°	56.0	50.8	32.7	21.8	21.3	12.4	10.4	12.4	13.0	11.9	10.9
67.5°	48.7	43.5	28.5	17.6	19.7	9.8	7.8	10.4	14.0	10.9	9.8
70°	41.5	36.3	22.3	14.0	20.7	6.7	6.2	9.3	16.6	11.9	9.3
72.5°	32.1	28.0	15.6	10.4	22.3	4.7	4.7	7.8	18.7	13.0	8.8
75°	22.3	18.1	9.3	6.2	18.1	3.1	3.1	7.3	17.6	11.9	8.3
77.5°	13.0	9.8	3.1	0.5	9.3	0.0	0.5	5.2	12.4	7.3	3.6
80°	4.7	2.1	0.0	0.0	5.7	0.0	0.0	0.0	1.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386840

CATALOG NUMBER: GAW-SA2C-740-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3
2.5°	3024.7	3094.7	3157.4	3252.3	3364.8	3494.4	3605.8	3725.6	3838.0	3884.7	3916.8
5°	2317.6	2404.2	2505.3	2644.7	2830.3	3058.9	3273.0	3515.1	3775.3	3905.4	4027.8
7.5°	1638.6	1726.7	1852.1	2000.4	2224.9	2497.0	2776.9	3111.3	3463.8	3669.6	3872.3
10°	1178.3	1286.6	1403.8	1606.4	1834.5	2092.7	2380.9	2754.1	3147.0	3375.1	3619.3
12.5°	801.9	925.3	1102.6	1329.6	1597.6	1850.6	2101.0	2457.1	2913.3	3139.3	3401.0
15°	481.1	549.5	737.1	999.9	1328.6	1643.8	1918.0	2275.1	2761.4	3038.2	3310.3
17.5°	296.5	328.1	430.3	645.9	991.1	1389.8	1765.6	2213.5	2783.1	3120.1	3411.4
20°	236.4	248.8	281.5	381.5	656.8	1109.8	1594.0	2201.0	2960.9	3375.6	3688.2
22.5°	205.3	217.2	239.0	277.3	413.1	831.0	1431.2	2212.4	3216.0	3758.7	4123.7
25°	180.9	191.3	212.0	243.6	302.7	585.2	1257.1	2263.2	3548.3	4234.1	4621.8
27.5°	161.7	170.5	189.7	218.8	259.7	408.5	1059.6	2324.9	3942.2	4720.3	5102.9
30°	144.1	151.9	169.0	195.9	225.5	314.1	842.9	2366.9	4336.7	5102.9	5446.6
32.5°	129.1	134.8	150.3	173.1	195.9	250.4	640.7	2360.2	4629.6	5421.2	5693.8
35°	113.5	119.2	132.7	152.4	170.5	206.8	503.9	2234.2	4884.6	5751.4	5976.8
37.5°	96.4	103.7	116.6	134.3	146.7	181.9	407.4	2082.3	5143.3	6128.7	6292.5
40°	81.9	89.2	100.6	119.7	127.5	172.6	313.1	1897.2	5434.1	6550.7	6638.8
42.5°	67.9	74.6	86.6	103.2	120.3	148.8	231.7	1685.8	5713.5	6911.5	6954.5
45°	54.9	61.7	74.1	90.7	128.6	123.4	179.4	1459.2	5939.0	7211.6	7225.6
47.5°	43.5	49.8	62.7	85.5	119.7	98.5	128.0	1281.4	6128.2	7445.9	7409.1
50°	33.7	38.9	52.4	98.0	104.7	81.4	96.9	1222.3	6297.7	7591.1	7495.7
52.5°	26.4	31.1	43.0	91.8	81.4	67.4	81.4	1277.8	6530.0	7711.3	7544.4
55°	21.3	25.9	33.7	52.4	55.5	57.0	69.5	1329.6	6930.7	7993.3	7832.1
57.5°	17.6	22.3	27.5	36.8	42.0	48.2	61.7	1335.3	7402.9	8461.9	8309.5
59°	16.1	20.2	24.9	32.7	36.8	44.1	58.1	1304.2	7569.3	8632.5	8556.3
60°	15.0	19.2	23.3	30.1	34.2	41.5	56.0	1274.7	7576.5	8626.3	8661.5
62.5°	13.0	17.1	20.7	25.4	29.0	35.2	50.3	1165.3	7269.7	8343.7	8598.3
65°	11.4	15.0	18.7	21.8	24.9	31.6	45.6	965.7	6745.6	7888.1	8165.4
67.5°	10.4	13.0	17.1	19.2	22.3	28.0	40.4	688.4	6090.9	7330.8	7510.7
70°	9.3	12.4	15.6	17.6	20.2	24.4	34.7	395.5	5143.3	6514.9	6643.0
72.5°	8.8	11.9	14.0	16.6	18.1	21.8	31.6	186.1	3766.0	5219.0	5553.3
75°	7.8	10.9	13.0	15.6	17.1	19.7	27.0	89.2	2504.8	3776.9	4156.8
77.5°	4.7	8.8	11.9	14.0	15.0	17.1	22.3	51.3	1598.7	2614.2	3079.1
80°	0.0	3.1	8.8	11.9	13.0	14.5	17.1	40.4	855.3	1493.4	1792.5
82.5°	0.0	0.0	6.2	9.3	8.8	9.8	13.0	25.4	385.7	976.1	1100.0
85°	0.0	0.0	2.1	7.3	6.2	4.7	8.8	8.8	84.5	494.0	616.3
87.5°	0.0	0.0	0.0	0.5	3.1	2.1	3.6	1.0	0.5	36.8	149.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P386840

CATALOG NUMBER: GAW-SA2C-740-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3	3564.3
2.5°	4029.3	4067.7	4132.5	4163.1	4148.0	4084.3	4008.1	3930.3	3884.7	3902.8
5°	4277.1	4474.6	4588.6	4626.5	4563.2	4420.2	4233.0	3986.3	3898.7	3874.8
7.5°	4277.1	4648.8	4884.1	4925.6	4784.6	4504.1	4153.2	3768.1	3640.0	3593.4
10°	4126.8	4632.7	4960.8	5026.7	4829.7	4410.3	3940.2	3500.6	3348.7	3300.5
12.5°	3957.3	4502.1	4847.8	4938.5	4776.8	4317.0	3792.4	3319.7	3140.8	3098.8
15°	3853.1	4341.4	4627.5	4693.4	4624.9	4262.6	3757.2	3265.2	3054.8	3014.3
17.5°	3890.4	4217.0	4320.1	4358.5	4404.6	4243.4	3853.1	3384.5	3118.0	3079.7
20°	4030.9	4085.8	4032.4	4080.6	4205.0	4262.1	4081.7	3672.7	3352.8	3301.5
22.5°	4269.3	4017.9	3868.1	3887.3	4038.6	4323.8	4431.1	4084.3	3715.2	3650.9
25°	4547.2	4072.9	3776.9	3759.8	3915.3	4405.1	4750.4	4532.1	4143.9	4072.9
27.5°	4896.6	4196.2	3758.2	3741.1	3872.3	4481.3	5015.8	4974.8	4595.4	4474.1
30°	5166.1	4317.5	3813.7	3774.3	3915.3	4534.2	5228.8	5350.7	4955.1	4874.8
32.5°	5359.5	4460.6	3903.9	3846.8	4036.6	4625.4	5393.2	5694.9	5287.9	5166.1
35°	5506.7	4616.1	4049.5	3955.7	4203.5	4763.9	5547.1	6061.3	5642.0	5508.8
37.5°	5644.6	4834.4	4277.1	4165.1	4465.3	4986.8	5709.9	6477.1	6038.0	5878.9
40°	5836.9	5081.6	4628.0	4528.5	4905.4	5290.5	5913.1	6910.4	6488.5	6288.4
42.5°	6029.2	5347.0	4987.3	5014.2	5454.3	5659.6	6175.4	7368.7	6933.2	6719.7
45°	6204.9	5620.7	5498.9	5623.3	5963.9	6064.5	6436.1	7633.6	7288.3	7082.0
47.5°	6361.5	5962.9	6007.4	6338.7	6543.4	6430.9	6631.0	7862.2	7552.7	7370.8
50°	6543.4	6405.5	6677.7	7146.3	7210.6	6762.7	6808.3	8132.8	7861.7	7715.5
52.5°	6742.5	6872.1	7420.0	7833.1	7812.4	7123.0	6986.6	8436.0	8285.2	8147.8
55°	6968.5	7248.9	8073.7	8475.9	8458.3	7525.2	7282.1	8810.8	8816.0	8691.6
57.5°	7303.9	7573.4	8517.4	8995.9	9025.4	7989.7	7782.9	9230.7	9296.0	9213.1
59°	7544.4	7783.9	8693.1	9213.1	9333.3	8348.9	8148.8	9474.3	9431.3	9355.6
60°	7722.7	7917.6	8780.2	9326.6	9512.2	8592.6	8418.9	9617.4	9447.4	9355.6
62.5°	8163.9	8209.0	8937.3	9455.1	9717.9	9133.7	9178.8	9861.0	9335.9	9186.1
65°	8369.7	8393.0	8935.2	9225.0	9518.9	9555.2	9868.3	9868.3	9063.8	8833.6
67.5°	8283.6	8171.1	8492.0	8461.9	8755.3	9304.8	10127.5	9506.5	8543.3	8245.8
70°	7583.8	7151.0	7008.4	7021.4	7245.8	8093.4	9614.3	8441.7	7558.4	7210.6
72.5°	6310.2	5271.9	4919.9	5321.6	5380.2	6220.0	8193.4	6357.3	5574.1	5248.0
75°	5075.4	3716.2	3143.9	3568.0	3667.5	4551.8	6338.2	3959.3	3255.9	3001.9
77.5°	3646.2	2667.6	2256.0	2226.4	2355.0	2886.8	4497.4	1992.6	1661.9	1551.0
80°	2071.4	1755.7	1890.5	1783.7	1848.5	1805.0	2136.7	874.0	715.9	669.2
82.5°	1250.3	1037.8	1123.8	935.7	1184.0	1031.0	823.2	279.9	243.1	231.2
85°	813.3	567.1	295.5	198.0	408.0	658.9	184.0	76.2	58.6	46.7
87.5°	280.4	144.6	14.5	6.2	43.5	122.9	6.7	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)