

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P721926

Luminaire Tested: **CST-CA8-430-740-U-T5R**

Issue Date: 10/25/2023

Test Information

Test Method: LM-79-08
Report Number: P721926
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-151-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: CST-CA8-430-740-U-T5R
Description: CELESTEON HIGH MAST LUMINAIRE
Light Source: (8) 4000K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 69790 lumens
Efficiency: N/A
Efficacy: 160.8 lumens/watt
Luminous Opening: Circular (Dia: 2.08' x H: 0')
IES Classification: Type V - Short
BUG Rating: B5 - U0 - G5


Input Watts (W): 434.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P721926
 CATALOG NUMBER: CST-CA8-430-740-U-T5R

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 5.7 fc
 Type V - Short - N/A

REPORT NUMBER: P721926
CATALOG NUMBER: CST-CA8-430-740-U-T5R

Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P721926
 CATALOG NUMBER: CST-CA8-430-740-U-T5R


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	34895.0	0.0	34895.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	34895.0	0.0	34895.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	69790.0	0.0	69790.0
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	489.0	0.7
10°-20°	1515.5	2.2
20°-30°	2875.9	4.1
30°-40°	4995.1	7.2
40°-50°	8694.4	12.5
50°-60°	14853.5	21.3
60°-70°	21874.7	31.3
70°-80°	13905.3	19.9
80°-90°	586.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	69790.0	100.0
0°-180°	69790.0	100.0



REPORT NUMBER: P721926


CATALOG NUMBER: CST-CA8-430-740-U-T5R

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	2440.2	3.5			
FM (30°-60°)	14271.5	20.4			
FH (60°-80°)	17890.0	25.6			G5
FVH (80°-90°)	293.3	0.4			G3/500
BL (0°-30°)	2440.2	3.5	B3/2500		
BM (30°-60°)	14271.5	20.4	B5		
BH (60°-80°)	17890.0	25.6	B5		G5
BVH (80°-90°)	293.3	0.4			G3/500
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B5-U0-G5

Type V Short



REPORT NUMBER: P721926
CATALOG NUMBER: CST-CA8-430-740-U-T5R

CANDELA DISTRIBUTION (FULL):

	0°
0°	5133.4
2.5°	5134.8
5°	5124.6
7.5°	5116.1
10°	5124.7
12.5°	5179.8
15°	5286.0
17.5°	5434.6
20°	5636.3
22.5°	5874.5
25°	6155.2
27.5°	6459.4
30°	6817.1
32.5°	7256.6
35°	7833.9
37.5°	8498.3
40°	9236.7
42.5°	10066.5
45°	11051.3
47.5°	12187.1
50°	13502.6
52.5°	14923.5
55°	16482.3
57.5°	18039.0
60°	19587.0
62.5°	21139.6
65°	22988.0
67.5°	23380.6
70°	21540.4
72.5°	18321.1
75°	13910.0
77.5°	8504.1
80°	2699.2
82.5°	458.2
85°	258.9
87.5°	93.7
90°	0.0

(END OF REPORT)