

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P256604

Luminaire Tested: **CST-10-4-D-U-T5R**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P256604
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1808-894-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: CST-10-4-D-U-T5R
Description: CELESTEON HIGH MAST LUMINAIRE
(10) 70 CRI, 4000K LEDS AND TYPE V ROUND OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 46332 lumens
Efficiency: N/A
Efficacy: 150.4 lumens/watt
Luminous Opening: Circular (Dia: 2.08' x H: 0')
IES Classification: Type V - Short - Full Cutoff
BUG Rating: B5 - U0 - G5


Input Watts (W): 308
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P256604
 CATALOG NUMBER: CST-10-4-D-U-T5R

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 30 foot mounting height. Maximum calculated value = 3.4 fc
 Type V - Short - Full Cutoff

REPORT NUMBER: P256604

CATALOG NUMBER: CST-10-4-D-U-T5R

Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P256604

CATALOG NUMBER: CST-10-4-D-U-T5R


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	23166.0	0.0	23166.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	23166.0	0.0	23166.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	46332.0	0.0	46332.0
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	290.9	0.6
10°-20°	932.3	2.0
20°-30°	1803.5	3.9
30°-40°	3146.2	6.8
40°-50°	5584.6	12.1
50°-60°	9618.6	20.8
60°-70°	14284.8	30.8
70°-80°	10024.4	21.6
80°-90°	646.7	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	46332.0	100.0
0°-180°	46332.0	100.0



REPORT NUMBER: P256604


CATALOG NUMBER: CST-10-4-D-U-T5R

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1513.4	3.3			
FM	(30°-60°)	9174.7	19.8			
FH	(60°-80°)	12154.6	26.2			G5
FVH	(80°-90°)	323.3	0.7			G3/500
BL	(0°-30°)	1513.4	3.3	B3/2500		
BM	(30°-60°)	9174.7	19.8	B5		
BH	(60°-80°)	12154.6	26.2	B5		G5
BVH	(80°-90°)	323.3	0.7			G3/500
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B5-U0-G5

Type V Short





REPORT NUMBER: P256604

CATALOG NUMBER: CST-10-4-D-U-T5R

CANDELA DISTRIBUTION (FULL):

	0°
0°	3022.2
2.5°	3026.3
5°	3029.1
7.5°	3045.6
10°	3087.0
12.5°	3151.8
15°	3245.6
17.5°	3369.8
20°	3514.6
22.5°	3677.4
25°	3858.1
27.5°	4058.1
30°	4289.8
32.5°	4574.0
35°	4927.1
37.5°	5350.5
40°	5831.9
42.5°	6422.3
45°	7110.6
47.5°	7873.4
50°	8728.6
52.5°	9673.4
55°	10666.6
57.5°	11681.8
60°	12692.9
62.5°	13683.2
65°	14825.3
67.5°	15457.1
70°	14378.4
72.5°	12417.0
75°	9942.4
77.5°	6952.0
80°	3127.0
82.5°	569.7
85°	173.8
87.5°	75.9
90°	0.0

(END OF REPORT)