

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P256593

Luminaire Tested: **CST-8-3-D-U-T5R-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P256593
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1808-894-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: CST-8-3-D-U-T5R-7030
Description: CELESTEON HIGH MAST LUMINAIRE
(8) 70 CRI, 3000K LEDS AND TYPE V ROUND OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 32792 lumens
Efficiency: N/A
Efficacy: 145.1 lumens/watt
Luminous Opening: Circular (Dia: 2.08' x H: 0')
IES Classification: Type V - Short - Full Cutoff
BUG Rating: B5 - U0 - G4


Input Watts (W): 226
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P256593
 CATALOG NUMBER: CST-8-3-D-U-T5R-7030

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd
 - - - 1/2 Max cd




Based on 30 foot mounting height. Maximum calculated value = 2.4 fc
 Type V - Short - Full Cutoff

REPORT NUMBER: P256593

CATALOG NUMBER: CST-8-3-D-U-T5R-7030

Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P256593

CATALOG NUMBER: CST-8-3-D-U-T5R-7030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	16396.0	0.0	16396.0
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	16396.0	0.0	16396.0
	% Fixture	50.0	0.0	50.0
Total	Lumens	32792.0	0.0	32792.0
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	205.9	0.6
10°-20°	659.8	2.0
20°-30°	1276.5	3.9
30°-40°	2226.7	6.8
40°-50°	3952.6	12.1
50°-60°	6807.7	20.8
60°-70°	10110.3	30.8
70°-80°	7094.9	21.6
80°-90°	457.7	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	32792.0	100.0
0°-180°	32792.0	100.0



REPORT NUMBER: P256593


CATALOG NUMBER: CST-8-3-D-U-T5R-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1071.1	3.3			
FM	(30°-60°)	6493.5	19.8			
FH	(60°-80°)	8602.6	26.2			G4/12000
FVH	(80°-90°)	228.8	0.7			G3/500
BL	(0°-30°)	1071.1	3.3	B3/2500		
BM	(30°-60°)	6493.5	19.8	B4/8500		
BH	(60°-80°)	8602.6	26.2	B5		G4/12000
BVH	(80°-90°)	228.8	0.7			G3/500
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B5-U0-G4

Type V Short





REPORT NUMBER: P256593

CATALOG NUMBER: CST-8-3-D-U-T5R-7030

CANDELA DISTRIBUTION (FULL):

	0°
0°	2139.0
2.5°	2141.9
5°	2143.9
7.5°	2155.6
10°	2184.9
12.5°	2230.7
15°	2297.1
17.5°	2385.0
20°	2487.5
22.5°	2602.7
25°	2730.6
27.5°	2872.1
30°	3036.2
32.5°	3237.3
35°	3487.2
37.5°	3786.9
40°	4127.6
42.5°	4545.4
45°	5032.6
47.5°	5572.5
50°	6177.7
52.5°	6846.5
55°	7549.4
57.5°	8267.9
60°	8983.5
62.5°	9684.5
65°	10492.8
67.5°	10939.9
70°	10176.5
72.5°	8788.3
75°	7036.9
77.5°	4920.3
80°	2213.2
82.5°	403.2
85°	123.0
87.5°	53.7
90°	0.0

(END OF REPORT)