

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P363313

Luminaire Tested: NVN-SA3D-727-U-T4W-HSS

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-2019
Report Number: P363313
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-19)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: STREETWORKS
Catalog Number: NVN-SA3D-727-U-T4W-HSS
Description: NAVION ROADWAY AND AREA LUMINAIRE
(3) 70 CRI, 2700K, 1200mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV WIDE OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14242 lumens
Efficiency: N/A
Efficacy: 74.6 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G3


Input Watts (W): 191
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P363313
 CATALOG NUMBER: NVN-SA3D-727-U-T4W-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 5.2 fc
 Type IV - Short - N/A

REPORT NUMBER: P363313
CATALOG NUMBER: NVN-SA3D-727-U-T4W-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 46-Deg Lateral - - - Horizontal Cone Through 69-Deg Vertical



REPORT NUMBER: P363313
 CATALOG NUMBER: NVN-SA3D-727-U-T4W-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 1461.6 | 0.0 | 1461.6 |
| | % Fixture | 10.3 | 0.0 | 10.3 |
| Street Side | Lumens | 12780.4 | 0.0 | 12780.4 |
| | % Fixture | 89.7 | 0.0 | 89.7 |
| Total | Lumens | 14242.0 | 0.0 | 14242.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 142.0 | 1.0 |
| 10°-20° | 430.9 | 3.0 |
| 20°-30° | 677.7 | 4.8 |
| 30°-40° | 971.8 | 6.8 |
| 40°-50° | 1679.6 | 11.8 |
| 50°-60° | 3318.2 | 23.3 |
| 60°-70° | 4637.5 | 32.6 |
| 70°-80° | 2240.4 | 15.7 |
| 80°-90° | 144.0 | 1.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 14242.0 | 100.0 |
| 0°-180° | 14242.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P363313
 CATALOG NUMBER: NVN-SA3D-727-U-T4W-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 865.4 | 6.1 | | | |
| FM (30°-60°) | 5237.1 | 36.8 | | | |
| FH (60°-80°) | 6535.1 | 45.9 | | | G3/7500 |
| FVH (80°-90°) | 142.8 | 1.0 | | | G2/225 |
| BL (0°-30°) | 385.2 | 2.7 | B1/500 | | |
| BM (30°-60°) | 732.4 | 5.1 | B1/1000 | | |
| BH (60°-80°) | 342.7 | 2.4 | B1/500 | | G1/500 |
| BVH (80°-90°) | 1.2 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G3

Type IV Short





REPORT NUMBER: P363313

CATALOG NUMBER: NVN-SA3D-727-U-T4W-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 46° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|---------|---------|---------|---------|--------|--------|--------|
| 0° | 1427.0 | 1427.0 | 1427.0 | 1427.0 | 1427.0 | 1427.0 | 1427.0 | 1427.0 | 1427.0 | 1427.0 | 1427.0 |
| 2.5° | 1585.3 | 1583.3 | 1573.9 | 1569.9 | 1547.2 | 1533.8 | 1528.5 | 1511.8 | 1487.8 | 1463.7 | 1437.0 |
| 5° | 1765.5 | 1764.9 | 1747.5 | 1730.8 | 1688.1 | 1648.0 | 1640.7 | 1601.9 | 1547.9 | 1497.1 | 1446.4 |
| 7.5° | 1949.8 | 1941.2 | 1923.8 | 1891.8 | 1829.7 | 1765.5 | 1759.5 | 1704.8 | 1628.0 | 1554.5 | 1481.8 |
| 10° | 2106.1 | 2100.8 | 2078.1 | 2029.3 | 1956.5 | 1883.7 | 1876.4 | 1809.0 | 1722.1 | 1632.0 | 1539.2 |
| 12.5° | 2227.6 | 2223.6 | 2193.6 | 2132.8 | 2055.4 | 1979.9 | 1969.9 | 1909.8 | 1817.0 | 1716.1 | 1606.6 |
| 15° | 2301.8 | 2299.8 | 2263.0 | 2198.3 | 2122.1 | 2056.7 | 2048.0 | 1995.3 | 1909.1 | 1803.6 | 1680.1 |
| 17.5° | 2319.1 | 2319.8 | 2281.7 | 2216.3 | 2153.5 | 2106.8 | 2100.1 | 2060.0 | 1987.9 | 1883.1 | 1753.5 |
| 20° | 2280.4 | 2288.4 | 2254.3 | 2197.6 | 2158.9 | 2134.1 | 2128.8 | 2104.8 | 2044.0 | 1945.2 | 1812.3 |
| 22.5° | 2225.6 | 2229.6 | 2206.3 | 2168.2 | 2152.2 | 2156.9 | 2154.2 | 2140.8 | 2089.4 | 1998.6 | 1870.4 |
| 25° | 2192.2 | 2192.2 | 2178.2 | 2146.2 | 2156.9 | 2185.6 | 2186.2 | 2183.6 | 2142.8 | 2064.0 | 1941.2 |
| 27.5° | 2190.9 | 2186.9 | 2170.9 | 2146.8 | 2176.2 | 2220.3 | 2223.0 | 2241.0 | 2215.6 | 2143.5 | 2029.3 |
| 30° | 2244.3 | 2239.7 | 2205.6 | 2174.2 | 2211.6 | 2259.0 | 2265.7 | 2305.1 | 2292.4 | 2229.6 | 2127.5 |
| 32.5° | 2369.2 | 2352.5 | 2277.0 | 2225.6 | 2253.7 | 2310.4 | 2319.1 | 2381.9 | 2401.9 | 2335.8 | 2222.3 |
| 35° | 2540.1 | 2487.4 | 2378.5 | 2323.1 | 2325.8 | 2385.2 | 2393.2 | 2485.4 | 2544.8 | 2433.3 | 2295.7 |
| 37.5° | 2775.9 | 2749.8 | 2572.9 | 2424.6 | 2436.6 | 2526.8 | 2550.2 | 2650.3 | 2633.6 | 2486.7 | 2379.2 |
| 40° | 3292.7 | 3252.0 | 3063.7 | 2709.1 | 2542.8 | 2641.6 | 2649.0 | 2702.4 | 2703.7 | 2607.6 | 2552.8 |
| 42.5° | 3996.5 | 3979.8 | 3781.5 | 3225.3 | 2751.8 | 2718.4 | 2731.8 | 2821.9 | 2922.8 | 2862.7 | 2860.0 |
| 45° | 4775.8 | 4767.1 | 4556.8 | 3910.4 | 3174.5 | 2970.2 | 2986.9 | 3107.7 | 3300.7 | 3314.1 | 3398.9 |
| 47.5° | 5402.8 | 5398.8 | 5277.9 | 4675.0 | 3821.6 | 3396.9 | 3402.2 | 3530.4 | 3869.6 | 4037.3 | 4172.8 |
| 50° | 5974.4 | 5993.8 | 5898.3 | 5502.3 | 4703.0 | 4065.3 | 4052.6 | 4138.1 | 4683.0 | 4957.4 | 5125.7 |
| 52.5° | 6769.0 | 6796.4 | 6528.7 | 6274.2 | 5627.8 | 4894.7 | 4884.6 | 4974.1 | 5660.6 | 5866.2 | 5896.3 |
| 55° | 7470.9 | 7424.1 | 7212.4 | 7139.0 | 6755.7 | 5919.0 | 5916.3 | 5995.1 | 6606.1 | 6693.6 | 6749.0 |
| 57.5° | 7780.7 | 7762.7 | 7864.8 | 8033.1 | 7937.0 | 7129.6 | 7123.6 | 7063.5 | 7452.2 | 7461.5 | 7631.8 |
| 60° | 7976.3 | 7998.4 | 8311.6 | 8830.4 | 9070.1 | 8432.4 | 8393.7 | 8027.1 | 8260.1 | 8239.4 | 8421.7 |
| 62.5° | 7829.4 | 7872.8 | 8436.4 | 9301.2 | 9918.2 | 9569.6 | 9514.9 | 8909.9 | 8950.6 | 8879.2 | 9048.8 |
| 65° | 7049.5 | 7116.9 | 8040.5 | 9212.4 | 10338.9 | 10458.4 | 10403.0 | 9689.1 | 9498.8 | 9381.3 | 9287.2 |
| 67.5° | 5724.0 | 5764.1 | 6728.3 | 8439.8 | 10149.2 | 10988.6 | 10977.2 | 10372.3 | 9912.8 | 9296.5 | 8566.0 |
| 69° | 4730.4 | 4769.8 | 5698.0 | 7626.4 | 9731.9 | 11102.1 | 11124.2 | 10591.3 | 9834.0 | 8781.0 | 7589.7 |
| 70° | 4006.5 | 4048.6 | 4913.4 | 6929.3 | 9247.8 | 11049.4 | 11088.8 | 10570.6 | 9608.3 | 8184.0 | 6733.0 |
| 72.5° | 2101.4 | 2137.5 | 3024.9 | 4773.8 | 7539.0 | 10145.9 | 10265.4 | 9677.1 | 8144.6 | 5943.7 | 3981.2 |
| 75° | 660.4 | 681.1 | 1181.3 | 2495.4 | 5161.8 | 7888.9 | 7916.3 | 7591.1 | 5783.4 | 3269.3 | 1658.0 |
| 77.5° | 251.7 | 245.7 | 393.3 | 919.5 | 2609.6 | 4967.4 | 5135.0 | 4743.7 | 3035.0 | 1155.9 | 382.6 |
| 80° | 135.6 | 136.2 | 204.3 | 380.6 | 1116.5 | 2552.8 | 2694.4 | 2299.1 | 1078.4 | 360.6 | 88.1 |
| 82.5° | 58.8 | 61.4 | 114.9 | 201.7 | 512.8 | 941.5 | 1012.3 | 842.7 | 412.0 | 242.4 | 32.7 |
| 85° | 12.7 | 14.0 | 55.4 | 109.5 | 209.0 | 264.4 | 277.1 | 273.1 | 262.4 | 188.3 | 12.7 |
| 87.5° | 0.0 | 0.0 | 24.7 | 39.4 | 52.8 | 60.1 | 52.8 | 68.8 | 144.9 | 126.9 | 6.7 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P363313

CATALOG NUMBER: NVN-SA3D-727-U-T4W-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1427.0 | 1427.0 | 1427.0 | 1427.0 | 1427.0 | 1427.0 | 1427.0 | 1427.0 | 1427.0 | 1427.0 | 1427.0 |
| 2.5° | 1428.3 | 1416.3 | 1395.6 | 1372.9 | 1356.9 | 1340.2 | 1326.8 | 1320.8 | 1314.1 | 1309.5 | 1315.5 |
| 5° | 1425.7 | 1402.3 | 1362.2 | 1323.5 | 1295.4 | 1272.7 | 1254.0 | 1246.7 | 1239.4 | 1234.0 | 1233.3 |
| 7.5° | 1449.0 | 1416.3 | 1354.9 | 1298.1 | 1254.7 | 1224.0 | 1198.6 | 1187.9 | 1179.3 | 1175.3 | 1171.9 |
| 10° | 1493.8 | 1451.7 | 1369.6 | 1295.4 | 1239.4 | 1187.3 | 1132.5 | 1090.4 | 1063.1 | 1050.4 | 1045.7 |
| 12.5° | 1551.9 | 1499.1 | 1397.6 | 1309.5 | 1228.0 | 1127.8 | 1011.7 | 911.5 | 846.7 | 825.3 | 812.7 |
| 15° | 1620.0 | 1554.5 | 1434.3 | 1327.5 | 1186.6 | 1003.6 | 806.6 | 675.8 | 615.7 | 603.7 | 590.3 |
| 17.5° | 1685.4 | 1613.3 | 1478.4 | 1330.8 | 1095.8 | 802.0 | 591.0 | 502.2 | 478.8 | 486.8 | 488.8 |
| 20° | 1742.8 | 1671.4 | 1521.8 | 1301.5 | 930.9 | 601.6 | 457.4 | 435.4 | 444.1 | 459.4 | 462.1 |
| 22.5° | 1800.9 | 1727.5 | 1561.9 | 1224.0 | 719.8 | 456.7 | 412.0 | 417.3 | 426.0 | 441.4 | 444.1 |
| 25° | 1871.7 | 1795.6 | 1599.3 | 1081.8 | 540.2 | 388.6 | 391.3 | 399.3 | 408.0 | 422.0 | 423.4 |
| 27.5° | 1953.2 | 1881.7 | 1624.0 | 896.8 | 400.7 | 357.2 | 365.9 | 378.0 | 386.6 | 400.0 | 402.7 |
| 30° | 2061.4 | 1995.3 | 1632.0 | 705.2 | 335.9 | 329.2 | 333.2 | 347.9 | 360.6 | 372.6 | 374.6 |
| 32.5° | 2162.9 | 2107.4 | 1605.3 | 532.2 | 311.2 | 303.2 | 303.2 | 311.8 | 326.5 | 337.9 | 340.6 |
| 35° | 2256.3 | 2220.3 | 1519.8 | 389.3 | 292.5 | 279.1 | 272.4 | 272.4 | 281.8 | 291.1 | 293.8 |
| 37.5° | 2379.9 | 2378.5 | 1381.6 | 310.5 | 274.4 | 259.1 | 245.1 | 234.4 | 231.0 | 233.0 | 234.4 |
| 40° | 2591.6 | 2593.6 | 1201.3 | 278.5 | 259.1 | 238.4 | 217.0 | 197.7 | 179.6 | 173.6 | 172.9 |
| 42.5° | 2922.1 | 2892.1 | 1012.3 | 263.1 | 245.7 | 217.0 | 185.0 | 158.9 | 130.9 | 122.2 | 121.5 |
| 45° | 3447.0 | 3268.7 | 812.0 | 249.1 | 231.7 | 193.0 | 152.9 | 117.5 | 94.8 | 88.1 | 88.1 |
| 47.5° | 4211.5 | 3763.5 | 629.0 | 233.7 | 213.0 | 165.6 | 115.5 | 84.8 | 69.4 | 66.1 | 66.8 |
| 50° | 5002.2 | 4248.3 | 482.1 | 214.3 | 190.3 | 136.9 | 85.5 | 61.4 | 52.8 | 52.8 | 53.4 |
| 52.5° | 5703.3 | 4603.5 | 375.9 | 193.6 | 162.3 | 107.5 | 64.8 | 48.1 | 44.1 | 43.4 | 44.1 |
| 55° | 6359.7 | 4832.6 | 287.8 | 169.6 | 128.9 | 80.1 | 49.4 | 39.4 | 36.7 | 35.4 | 34.7 |
| 57.5° | 6992.7 | 4946.1 | 215.7 | 136.9 | 93.5 | 58.1 | 39.4 | 33.4 | 30.7 | 28.7 | 28.0 |
| 60° | 7414.1 | 4853.9 | 148.2 | 100.8 | 64.8 | 42.1 | 32.7 | 28.7 | 25.4 | 23.4 | 22.7 |
| 62.5° | 7651.8 | 4602.2 | 95.5 | 72.8 | 46.1 | 31.4 | 26.0 | 24.0 | 19.4 | 17.4 | 17.4 |
| 65° | 7555.7 | 4186.8 | 66.8 | 52.1 | 33.4 | 23.4 | 19.4 | 19.4 | 14.0 | 11.4 | 10.7 |
| 67.5° | 6695.6 | 3537.1 | 50.7 | 38.7 | 24.0 | 17.4 | 14.7 | 16.7 | 8.7 | 5.3 | 5.3 |
| 69° | 5760.7 | 2931.5 | 43.4 | 32.1 | 20.0 | 14.0 | 12.7 | 15.4 | 6.0 | 4.0 | 3.3 |
| 70° | 5006.8 | 2528.8 | 39.4 | 28.0 | 16.7 | 12.0 | 11.4 | 14.7 | 6.0 | 3.3 | 2.7 |
| 72.5° | 2995.6 | 1410.3 | 30.0 | 20.0 | 10.7 | 9.3 | 9.3 | 16.7 | 6.0 | 3.3 | 2.7 |
| 75° | 1210.6 | 496.8 | 22.0 | 14.0 | 8.0 | 8.0 | 11.4 | 21.4 | 5.3 | 2.7 | 2.0 |
| 77.5° | 274.4 | 108.8 | 12.7 | 8.7 | 5.3 | 8.0 | 13.4 | 16.7 | 3.3 | 1.3 | 0.0 |
| 80° | 66.8 | 26.7 | 8.0 | 5.3 | 3.3 | 6.0 | 10.0 | 9.3 | 0.7 | 0.0 | 0.0 |
| 82.5° | 22.0 | 9.3 | 3.3 | 2.7 | 0.7 | 2.0 | 4.7 | 2.7 | 0.0 | 0.0 | 0.0 |
| 85° | 9.3 | 5.3 | 1.3 | 0.7 | 0.0 | 0.0 | 0.7 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 6.0 | 2.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength




Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 CIE $R_a = 71.5$
 $R_g = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)