

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P360042

Luminaire Tested: NVN-SA2C-730-U-SL3-HSS

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-2019
Report Number: P360042
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-23)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: STREETWORKS
Catalog Number: NVN-SA2C-730-U-SL3-HSS
Description: NAVION ROADWAY AND AREA LUMINAIRE
(2) 70 CRI, 3000K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III
SPILL LIGHT ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11190 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B1 - U0 - G2


Input Watts (W): 113
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P360042
 CATALOG NUMBER: NVN-SA2C-730-U-SL3-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 8.4 fc
 Type III - Medium - N/A

REPORT NUMBER: P360042
CATALOG NUMBER: NVN-SA2C-730-U-SL3-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 58-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P360042
 CATALOG NUMBER: NVN-SA2C-730-U-SL3-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 957.6 | 0.0 | 957.6 |
| | % Fixture | 8.6 | 0.0 | 8.6 |
| Street Side | Lumens | 10232.4 | 0.0 | 10232.4 |
| | % Fixture | 91.4 | 0.0 | 91.4 |
| Total | Lumens | 11190.0 | 0.0 | 11190.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 270.3 | 2.4 |
| 10°-20° | 567.3 | 5.1 |
| 20°-30° | 745.8 | 6.7 |
| 30°-40° | 987.7 | 8.8 |
| 40°-50° | 1476.4 | 13.2 |
| 50°-60° | 2365.1 | 21.1 |
| 60°-70° | 2981.2 | 26.6 |
| 70°-80° | 1608.0 | 14.4 |
| 80°-90° | 188.2 | 1.7 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 11190.0 | 100.0 |
| 0°-180° | 11190.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P360042
 CATALOG NUMBER: NVN-SA2C-730-U-SL3-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1198.7 | 10.7 | | | |
| FM (30°-60°) | 4463.9 | 39.9 | | | |
| FH (60°-80°) | 4383.2 | 39.2 | | | G2/5000 |
| FVH (80°-90°) | 186.6 | 1.7 | | | G2/225 |
| BL (0°-30°) | 384.7 | 3.4 | B1/500 | | |
| BM (30°-60°) | 365.3 | 3.3 | B1/1000 | | |
| BH (60°-80°) | 205.9 | 1.8 | B1/500 | | G1/500 |
| BVH (80°-90°) | 1.6 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2
 Type III Medium





REPORT NUMBER: P360042

CATALOG NUMBER: NVN-SA2C-730-U-SL3-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 58° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|---------|---------|--------|--------|--------|
| 0° | 3305.5 | 3305.5 | 3305.5 | 3305.5 | 3305.5 | 3305.5 | 3305.5 | 3305.5 | 3305.5 | 3305.5 | 3305.5 |
| 2.5° | 3579.5 | 3570.7 | 3567.4 | 3561.9 | 3540.4 | 3519.5 | 3478.1 | 3466.5 | 3440.4 | 3378.5 | 3312.9 |
| 5° | 3582.3 | 3581.9 | 3591.6 | 3589.3 | 3581.9 | 3572.1 | 3542.3 | 3527.0 | 3482.8 | 3394.3 | 3274.3 |
| 7.5° | 3409.7 | 3418.5 | 3440.4 | 3458.1 | 3478.6 | 3505.1 | 3508.8 | 3493.9 | 3457.6 | 3362.2 | 3203.1 |
| 10° | 3178.0 | 3191.9 | 3222.7 | 3257.5 | 3311.1 | 3364.1 | 3411.6 | 3409.7 | 3397.1 | 3303.1 | 3117.5 |
| 12.5° | 2945.8 | 2962.1 | 2997.4 | 3049.1 | 3124.9 | 3211.5 | 3296.2 | 3307.8 | 3328.7 | 3250.1 | 3038.4 |
| 15° | 2742.5 | 2756.4 | 2791.3 | 2854.6 | 2948.6 | 3064.9 | 3189.1 | 3210.6 | 3264.5 | 3208.7 | 2972.3 |
| 17.5° | 2569.8 | 2578.7 | 2604.3 | 2674.5 | 2783.4 | 2924.4 | 3085.9 | 3127.7 | 3208.2 | 3176.1 | 2915.1 |
| 20° | 2449.3 | 2450.7 | 2467.5 | 2516.8 | 2625.7 | 2783.4 | 2978.8 | 3038.9 | 3148.7 | 3148.2 | 2856.0 |
| 22.5° | 2389.8 | 2385.1 | 2388.4 | 2416.8 | 2496.8 | 2648.9 | 2871.8 | 2943.0 | 3095.2 | 3124.5 | 2796.0 |
| 25° | 2378.6 | 2374.9 | 2365.6 | 2369.3 | 2417.7 | 2531.2 | 2763.9 | 2846.2 | 3048.2 | 3110.0 | 2743.9 |
| 27.5° | 2413.5 | 2417.2 | 2401.4 | 2384.6 | 2388.4 | 2454.9 | 2668.0 | 2763.4 | 3010.0 | 3110.0 | 2707.1 |
| 30° | 2483.8 | 2485.6 | 2474.0 | 2452.1 | 2422.8 | 2433.5 | 2601.5 | 2696.9 | 2990.9 | 3131.5 | 2683.8 |
| 32.5° | 2561.5 | 2571.7 | 2570.3 | 2552.6 | 2510.7 | 2467.5 | 2585.7 | 2672.7 | 2989.5 | 3178.9 | 2681.5 |
| 35° | 2657.8 | 2669.4 | 2689.0 | 2685.2 | 2641.5 | 2570.3 | 2639.6 | 2708.0 | 3017.0 | 3257.1 | 2706.6 |
| 37.5° | 2760.1 | 2777.8 | 2819.7 | 2839.7 | 2811.3 | 2730.8 | 2760.6 | 2809.5 | 3090.5 | 3383.6 | 2770.4 |
| 40° | 2859.3 | 2879.3 | 2955.6 | 3034.2 | 3012.8 | 2930.0 | 2943.9 | 2983.0 | 3221.3 | 3565.6 | 2891.4 |
| 42.5° | 2956.5 | 2986.3 | 3098.4 | 3227.8 | 3253.4 | 3187.3 | 3194.7 | 3225.9 | 3415.3 | 3815.9 | 3089.1 |
| 45° | 3072.8 | 3106.3 | 3272.4 | 3432.0 | 3500.4 | 3471.6 | 3503.2 | 3523.7 | 3668.9 | 4146.7 | 3355.7 |
| 47.5° | 3243.6 | 3282.2 | 3486.0 | 3667.9 | 3788.0 | 3806.6 | 3870.3 | 3883.8 | 3989.5 | 4532.0 | 3703.3 |
| 50° | 3576.7 | 3587.4 | 3771.7 | 3936.9 | 4110.0 | 4221.6 | 4294.2 | 4304.5 | 4377.5 | 4953.1 | 4137.4 |
| 52.5° | 3996.0 | 4003.0 | 4107.2 | 4217.9 | 4414.7 | 4642.7 | 4812.6 | 4827.0 | 4842.4 | 5363.5 | 4566.0 |
| 55° | 4412.4 | 4411.5 | 4480.3 | 4545.5 | 4770.7 | 5102.0 | 5470.5 | 5479.3 | 5369.1 | 5752.9 | 4893.5 |
| 57.5° | 4672.5 | 4697.6 | 4802.3 | 4886.1 | 5200.6 | 5625.4 | 6136.8 | 6169.4 | 5922.3 | 6041.4 | 5217.4 |
| 60° | 4589.7 | 4601.8 | 4834.0 | 5143.9 | 5736.2 | 6369.5 | 6811.0 | 6819.4 | 6338.3 | 6329.4 | 5626.8 |
| 62.5° | 3910.4 | 3916.9 | 4281.7 | 4920.5 | 6007.5 | 7334.5 | 7624.4 | 7488.0 | 6816.6 | 6729.1 | 6116.8 |
| 65° | 2680.1 | 2722.5 | 3027.2 | 3816.8 | 5509.1 | 7939.8 | 8883.5 | 8657.8 | 7545.7 | 7305.2 | 6559.8 |
| 67.5° | 1578.3 | 1569.4 | 1720.2 | 2301.8 | 4046.2 | 7537.8 | 10476.2 | 10251.9 | 8540.1 | 7690.9 | 6429.9 |
| 70° | 1078.1 | 1072.0 | 1129.7 | 1393.6 | 2284.1 | 5847.4 | 10977.3 | 11430.0 | 9418.1 | 7431.3 | 5533.8 |
| 72.5° | 769.6 | 772.9 | 858.0 | 1082.7 | 1434.0 | 3406.9 | 9440.0 | 10511.5 | 9143.1 | 6478.3 | 4206.3 |
| 75° | 522.5 | 531.4 | 653.3 | 888.3 | 1257.2 | 1733.2 | 6698.9 | 7990.6 | 7445.2 | 4708.3 | 2417.7 |
| 77.5° | 281.0 | 290.8 | 434.6 | 715.6 | 1136.7 | 1204.2 | 4309.1 | 5499.4 | 4676.7 | 2116.6 | 700.7 |
| 80° | 117.3 | 122.8 | 203.3 | 520.2 | 982.2 | 1057.6 | 2535.4 | 3334.8 | 1992.9 | 417.4 | 156.3 |
| 82.5° | 50.7 | 53.5 | 84.7 | 310.4 | 734.2 | 892.9 | 1342.4 | 1604.3 | 604.0 | 91.7 | 78.6 |
| 85° | 9.8 | 10.2 | 34.9 | 164.2 | 468.6 | 503.9 | 870.1 | 852.9 | 271.3 | 39.6 | 57.2 |
| 87.5° | 0.0 | 0.0 | 8.4 | 51.6 | 137.7 | 274.5 | 530.9 | 524.4 | 92.1 | 19.1 | 21.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P360042
 CATALOG NUMBER: NVN-SA2C-730-U-SL3-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 3305.5 | 3305.5 | 3305.5 | 3305.5 | 3305.5 | 3305.5 | 3305.5 | 3305.5 | 3305.5 | 3305.5 | 3305.5 |
| 2.5° | 3279.4 | 3247.3 | 3179.8 | 3096.6 | 3032.8 | 2962.5 | 2906.7 | 2836.0 | 2805.3 | 2806.7 | 2789.9 |
| 5° | 3205.9 | 3139.8 | 2990.5 | 2802.0 | 2656.8 | 2507.0 | 2378.1 | 2249.7 | 2173.9 | 2149.2 | 2125.9 |
| 7.5° | 3100.7 | 2996.1 | 2757.8 | 2467.5 | 2221.8 | 1981.7 | 1772.8 | 1589.0 | 1472.7 | 1415.9 | 1395.0 |
| 10° | 2982.1 | 2835.1 | 2490.3 | 2107.8 | 1757.0 | 1432.2 | 1161.4 | 925.9 | 832.0 | 768.2 | 751.9 |
| 12.5° | 2877.9 | 2678.7 | 2228.8 | 1738.8 | 1322.4 | 930.6 | 672.4 | 525.8 | 462.0 | 436.9 | 432.7 |
| 15° | 2779.7 | 2532.6 | 1977.0 | 1404.7 | 915.7 | 572.8 | 427.6 | 377.8 | 362.9 | 358.7 | 358.7 |
| 17.5° | 2687.1 | 2393.5 | 1730.9 | 1075.8 | 605.8 | 401.6 | 354.1 | 342.9 | 338.3 | 337.8 | 338.3 |
| 20° | 2590.3 | 2254.4 | 1489.0 | 788.2 | 423.0 | 340.1 | 327.1 | 321.1 | 319.7 | 319.7 | 319.7 |
| 22.5° | 2497.7 | 2115.2 | 1253.5 | 563.0 | 339.2 | 310.4 | 303.8 | 299.7 | 298.3 | 297.8 | 296.9 |
| 25° | 2408.8 | 1983.1 | 1023.7 | 397.8 | 297.8 | 284.3 | 278.7 | 273.1 | 268.9 | 266.6 | 265.2 |
| 27.5° | 2335.8 | 1865.4 | 809.6 | 319.2 | 268.9 | 257.3 | 250.3 | 242.0 | 231.7 | 227.1 | 225.2 |
| 30° | 2277.6 | 1757.9 | 624.0 | 269.4 | 242.0 | 230.3 | 219.6 | 205.2 | 190.3 | 182.4 | 181.9 |
| 32.5° | 2232.0 | 1652.3 | 473.7 | 238.2 | 217.8 | 203.3 | 188.0 | 169.8 | 152.6 | 143.8 | 143.3 |
| 35° | 2209.7 | 1559.2 | 362.0 | 215.4 | 196.4 | 178.2 | 159.1 | 139.1 | 122.4 | 114.0 | 113.1 |
| 37.5° | 2224.6 | 1480.6 | 282.4 | 196.4 | 178.2 | 157.3 | 134.9 | 114.0 | 99.1 | 91.7 | 91.2 |
| 40° | 2279.0 | 1430.3 | 229.4 | 180.1 | 162.9 | 137.3 | 113.1 | 93.5 | 81.0 | 74.9 | 74.4 |
| 42.5° | 2394.9 | 1411.7 | 195.9 | 166.6 | 148.0 | 118.7 | 94.0 | 77.2 | 65.6 | 61.4 | 60.5 |
| 45° | 2588.4 | 1439.2 | 173.1 | 153.5 | 132.6 | 101.0 | 77.7 | 63.3 | 53.0 | 49.8 | 49.3 |
| 47.5° | 2846.2 | 1511.3 | 156.8 | 141.0 | 118.7 | 85.1 | 64.7 | 51.2 | 43.3 | 40.0 | 39.6 |
| 50° | 3178.4 | 1625.7 | 143.3 | 128.4 | 105.6 | 72.1 | 53.5 | 40.5 | 33.5 | 31.2 | 31.2 |
| 52.5° | 3540.0 | 1762.1 | 131.2 | 116.8 | 92.6 | 60.0 | 43.3 | 31.2 | 26.5 | 23.7 | 23.7 |
| 55° | 3838.7 | 1881.2 | 118.2 | 107.9 | 76.8 | 49.8 | 33.0 | 23.7 | 19.5 | 18.1 | 18.1 |
| 57.5° | 4137.0 | 2008.2 | 103.3 | 92.6 | 61.4 | 40.5 | 25.1 | 17.7 | 14.4 | 13.5 | 13.5 |
| 60° | 4523.6 | 2163.6 | 88.9 | 75.4 | 48.4 | 30.7 | 18.6 | 12.6 | 10.7 | 10.2 | 10.2 |
| 62.5° | 4948.9 | 2254.8 | 75.8 | 60.5 | 37.7 | 22.8 | 13.5 | 8.4 | 7.9 | 7.9 | 7.4 |
| 65° | 5209.0 | 2125.9 | 63.7 | 48.4 | 29.3 | 17.2 | 8.8 | 6.0 | 7.0 | 6.5 | 5.6 |
| 67.5° | 4877.2 | 1664.4 | 52.1 | 37.7 | 22.8 | 13.0 | 5.6 | 4.2 | 7.4 | 6.0 | 4.7 |
| 70° | 4038.3 | 1165.1 | 40.5 | 26.5 | 18.1 | 11.2 | 3.7 | 2.8 | 7.9 | 6.0 | 3.7 |
| 72.5° | 3022.1 | 779.8 | 32.1 | 17.7 | 13.5 | 9.8 | 3.3 | 1.4 | 7.0 | 5.1 | 3.3 |
| 75° | 1651.3 | 314.1 | 25.6 | 11.2 | 8.4 | 7.0 | 2.3 | 0.9 | 4.7 | 3.7 | 2.3 |
| 77.5° | 434.6 | 82.8 | 18.6 | 7.4 | 4.7 | 2.8 | 1.4 | 0.5 | 2.3 | 1.9 | 0.9 |
| 80° | 110.7 | 32.1 | 12.1 | 5.1 | 3.3 | 1.4 | 0.0 | 0.0 | 0.5 | 0.0 | 0.0 |
| 82.5° | 59.1 | 13.5 | 7.4 | 3.7 | 1.9 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 44.7 | 8.8 | 4.2 | 2.3 | 0.5 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 17.2 | 2.8 | 1.4 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-2-R4

Test Date: 10/03/2019

Luminaire Tested: SA1C-730-U-5WQ

Data in this report applies to families of products SA1C-730-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-2-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: MCGRAW-EDISON
 Catalog Number: **SA1C-730-U-5WQ**
 Description: MCGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-2-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. (1) 70 CRI, 3000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2993
 CIE u': 0.2508
 CIE v': 0.5215
 Duv: 0.0000
 CIE x: 0.4374
 CIE y: 0.4043
 CIE z: 0.1583
 Peak Wavelength (nm): 593
 Dominant Wavelength (nm): 582
 Purity: 53

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.8 | | |
| R1: | 67.5 | R9: | -38.3 |
| R2: | 82.9 | R10: | 62.5 |
| R3: | 94.7 | R11: | 63.7 |
| R4: | 67.7 | R12: | 57.8 |
| R5: | 67.9 | R13: | 70.4 |
| R6: | 77.6 | R14: | 97.3 |
| R7: | 76.0 | | |
| R8: | 40.5 | | |

Rf: 75.7
 Rg: 93.9



Test Conditions

Stabilization Time: 53M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-2-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-2-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-2-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 8494.8

S/P: 1.23

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3101.5 M/P: 0.45

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2397 | NR | 490 | 24908 | NR | 620 | 118784 | NR | 750 | 5037 | NR | 880 | 2677 | NR |
| 365 | 2084 | NR | 495 | 30998 | NR | 625 | 108951 | NR | 755 | 4413 | NR | 885 | 2940 | NR |
| 370 | 2143 | NR | 500 | 37103 | NR | 630 | 99573 | NR | 760 | 4189 | NR | 890 | 3116 | NR |
| 375 | 2413 | NR | 505 | 42987 | NR | 635 | 90444 | NR | 765 | 3677 | NR | 895 | 3345 | NR |
| 380 | 2172 | NR | 510 | 48702 | NR | 640 | 80749 | NR | 770 | 3366 | NR | 900 | 2312 | NR |
| 385 | 1997 | NR | 515 | 53741 | NR | 645 | 71664 | NR | 775 | 3211 | NR | 905 | 2829 | NR |
| 390 | 1830 | NR | 520 | 57283 | NR | 650 | 63936 | NR | 780 | 2682 | NR | 910 | 2783 | NR |
| 395 | 1861 | NR | 525 | 61876 | NR | 655 | 56611 | NR | 785 | 2804 | NR | 915 | 2662 | NR |
| 400 | 1717 | NR | 530 | 65398 | NR | 660 | 49763 | NR | 790 | 2581 | NR | 920 | 3047 | NR |
| 405 | 1761 | NR | 535 | 69597 | NR | 665 | 42891 | NR | 795 | 2711 | NR | 925 | 2256 | NR |
| 410 | 2680 | NR | 540 | 74214 | NR | 670 | 36939 | NR | 800 | 2609 | NR | 930 | 2976 | NR |
| 415 | 4374 | NR | 545 | 79911 | NR | 675 | 31946 | NR | 805 | 2581 | NR | 935 | 3503 | NR |
| 420 | 8071 | NR | 550 | 86153 | NR | 680 | 27385 | NR | 810 | 2404 | NR | 940 | 4226 | NR |
| 425 | 15169 | NR | 555 | 93952 | NR | 685 | 23504 | NR | 815 | 2556 | NR | 945 | 2930 | NR |
| 430 | 26038 | NR | 560 | 102904 | NR | 690 | 20210 | NR | 820 | 2742 | NR | 950 | 2115 | NR |
| 435 | 41316 | NR | 565 | 112009 | NR | 695 | 17459 | NR | 825 | 2014 | NR | 955 | 2634 | NR |
| 440 | 59674 | NR | 570 | 121662 | NR | 700 | 15207 | NR | 830 | 2488 | NR | 960 | 4200 | NR |
| 445 | 72751 | NR | 575 | 130476 | NR | 705 | 13322 | NR | 835 | 2625 | NR | 965 | 1982 | NR |
| 450 | 65091 | NR | 580 | 137926 | NR | 710 | 11676 | NR | 840 | 2754 | NR | 970 | 3613 | NR |
| 455 | 44894 | NR | 585 | 143406 | NR | 715 | 10626 | NR | 845 | 2708 | NR | 975 | 4034 | NR |
| 460 | 32712 | NR | 590 | 147039 | NR | 720 | 9416 | NR | 850 | 2608 | NR | 980 | 3922 | NR |
| 465 | 25296 | NR | 595 | 147365 | NR | 725 | 8333 | NR | 855 | 2605 | NR | 985 | 1909 | NR |
| 470 | 19318 | NR | 600 | 145800 | NR | 730 | 7134 | NR | 860 | 1765 | NR | 990 | 3617 | NR |
| 475 | 17265 | NR | 605 | 141363 | NR | 735 | 6437 | NR | 865 | 2581 | NR | 995 | 4767 | NR |
| 480 | 18260 | NR | 610 | 134199 | NR | 740 | 5834 | NR | 870 | 3016 | NR | 1000 | 2528 | NR |
| 485 | 20845 | NR | 615 | 127683 | NR | 745 | 5500 | NR | 875 | 3952 | NR | | | |

REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Summary

$R_f = 75.7$
 $R_g = 93.9$
 CIE $R_a = 71.8$
 $R_9 = -38.3$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 67 | CES51 = 87 | CES76 = 63 |
| CES02 = 63 | CES27 = 88 | CES52 = 86 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 78 | CES78 = 67 |
| CES04 = 71 | CES29 = 66 | CES54 = 84 | CES79 = 87 |
| CES05 = 49 | CES30 = 73 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 70 | CES56 = 75 | CES81 = 71 |
| CES07 = 41 | CES32 = 65 | CES57 = 74 | CES82 = 94 |
| CES08 = 40 | CES33 = 73 | CES58 = 76 | CES83 = 90 |
| CES09 = 29 | CES34 = 79 | CES59 = 85 | CES84 = 89 |
| CES10 = 76 | CES35 = 89 | CES60 = 93 | CES85 = 77 |
| CES11 = 59 | CES36 = 97 | CES61 = 84 | CES86 = 61 |
| CES12 = 65 | CES37 = 87 | CES62 = 91 | CES87 = 78 |
| CES13 = 43 | CES38 = 81 | CES63 = 77 | CES88 = 77 |
| CES14 = 74 | CES39 = 95 | CES64 = 72 | CES89 = 67 |
| CES15 = 71 | CES40 = 92 | CES65 = 68 | CES90 = 76 |
| CES16 = 47 | CES41 = 88 | CES66 = 69 | CES91 = 89 |
| CES17 = 50 | CES42 = 89 | CES67 = 67 | CES92 = 58 |
| CES18 = 56 | CES43 = 79 | CES68 = 72 | CES93 = 74 |
| CES19 = 73 | CES44 = 99 | CES69 = 81 | CES94 = 49 |
| CES20 = 66 | CES45 = 85 | CES70 = 66 | CES95 = 68 |
| CES21 = 87 | CES46 = 80 | CES71 = 67 | CES96 = 76 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 69 | CES73 = 59 | CES98 = 75 |
| CES24 = 91 | CES49 = 80 | CES74 = 95 | CES99 = 62 |
| CES25 = 73 | CES50 = 87 | CES75 = 69 | |



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-2-R4

TM-30-18

Measure Comparisons



(END OF REPORT)