

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P359205

Luminaire Tested: NVN-SA5C-740-U-T3R

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-2019
Report Number: P359205
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-10)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: STREETWORKS
Catalog Number: NVN-SA5C-740-U-T3R
Description: NAVION ROADWAY AND AREA LUMINAIRE
(5) 70 CRI, 4000K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III
ROADWAY OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 36343 lumens
Efficiency: N/A
Efficacy: 130.3 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1.5' x H: 0')
IES Classification: Type IV - Medium
BUG Rating: B3 - U0 - G5


Input Watts (W): 279
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P359205
 CATALOG NUMBER: NVN-SA5C-740-U-T3R

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 7.2 fc
 Type IV - Medium - N/A

REPORT NUMBER: P359205
CATALOG NUMBER: NVN-SA5C-740-U-T3R

Luminous Intensity Polar Plot



— Vertical Plane Through 55-Deg Lateral - - - Horizontal Cone Through 72.5-Deg Vertical

REPORT NUMBER: P359205
 CATALOG NUMBER: NVN-SA5C-740-U-T3R


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 6755.0 | 0.0 | 6755.0 |
| | % Fixture | 18.6 | 0.0 | 18.6 |
| Street Side | Lumens | 29588.0 | 0.0 | 29588.0 |
| | % Fixture | 81.4 | 0.0 | 81.4 |
| Total | Lumens | 36343.0 | 0.0 | 36343.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 580.0 | 1.6 |
| 10°-20° | 1544.3 | 4.2 |
| 20°-30° | 2546.1 | 7.0 |
| 30°-40° | 3766.4 | 10.4 |
| 40°-50° | 5257.1 | 14.5 |
| 50°-60° | 6844.9 | 18.8 |
| 60°-70° | 8412.1 | 23.1 |
| 70°-80° | 6594.1 | 18.1 |
| 80°-90° | 798.0 | 2.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 36343.0 | 100.0 |
| 0°-180° | 36343.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P359205
 CATALOG NUMBER: NVN-SA5C-740-U-T3R

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 2811.9 | 7.7 | | | |
| FM (30°-60°) | 12858.9 | 35.4 | | | |
| FH (60°-80°) | 13300.3 | 36.6 | | | G5 |
| FVH (80°-90°) | 617.0 | 1.7 | | | G4/750 |
| BL (0°-30°) | 1858.6 | 5.1 | B3/2500 | | |
| BM (30°-60°) | 3009.4 | 8.3 | B3/5000 | | |
| BH (60°-80°) | 1705.9 | 4.7 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 181.0 | 0.5 | | | G2/225 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G5
 Type IV Medium





REPORT NUMBER: P359205
 CATALOG NUMBER: NVN-SA5C-740-U-T3R

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 54° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 6410.1 | 6410.1 | 6410.1 | 6410.1 | 6410.1 | 6410.1 | 6410.1 | 6410.1 | 6410.1 | 6410.1 | 6410.1 |
| 2.5° | 6201.4 | 6186.7 | 6205.1 | 6230.9 | 6259.1 | 6297.2 | 6319.3 | 6329.1 | 6367.2 | 6381.9 | 6413.8 |
| 5° | 5914.2 | 5906.8 | 5937.5 | 5981.7 | 6044.3 | 6132.7 | 6203.9 | 6217.4 | 6318.1 | 6389.3 | 6454.3 |
| 7.5° | 5705.5 | 5705.5 | 5741.1 | 5793.9 | 5863.9 | 5982.9 | 6083.6 | 6102.0 | 6272.6 | 6426.1 | 6546.4 |
| 10° | 5539.8 | 5545.9 | 5587.7 | 5650.3 | 5732.5 | 5859.0 | 5992.8 | 6013.6 | 6260.4 | 6512.0 | 6703.5 |
| 12.5° | 5429.3 | 5444.1 | 5482.1 | 5538.6 | 5640.5 | 5793.9 | 5963.3 | 5991.5 | 6286.1 | 6634.8 | 6892.5 |
| 15° | 5499.3 | 5523.9 | 5527.5 | 5550.9 | 5607.3 | 5774.3 | 5980.5 | 6010.0 | 6341.4 | 6760.0 | 7107.4 |
| 17.5° | 5806.2 | 5814.8 | 5776.7 | 5727.6 | 5700.6 | 5807.4 | 6032.0 | 6062.7 | 6407.7 | 6883.9 | 7313.6 |
| 20° | 6272.6 | 6267.7 | 6185.5 | 6052.9 | 5915.4 | 5932.6 | 6116.7 | 6148.7 | 6497.3 | 6993.2 | 7519.8 |
| 22.5° | 6861.9 | 6844.7 | 6718.2 | 6474.0 | 6239.5 | 6141.3 | 6265.3 | 6292.3 | 6632.3 | 7149.1 | 7740.8 |
| 25° | 7576.3 | 7538.2 | 7371.3 | 7043.5 | 6698.6 | 6445.7 | 6488.7 | 6514.5 | 6828.7 | 7323.4 | 7943.3 |
| 27.5° | 8330.0 | 8291.9 | 8079.6 | 7683.1 | 7224.0 | 6829.9 | 6796.8 | 6818.9 | 7052.1 | 7452.3 | 8093.1 |
| 30° | 9118.0 | 9077.5 | 8883.6 | 8439.2 | 7781.3 | 7227.7 | 7084.0 | 7092.6 | 7209.2 | 7522.3 | 8215.8 |
| 32.5° | 9909.8 | 9871.7 | 9654.5 | 9138.9 | 8386.4 | 7654.8 | 7291.5 | 7280.4 | 7303.8 | 7594.7 | 8354.5 |
| 35° | 10712.6 | 10727.3 | 10473.2 | 9902.4 | 9056.7 | 8129.9 | 7537.0 | 7513.7 | 7462.1 | 7743.2 | 8550.9 |
| 37.5° | 11571.9 | 11562.0 | 11233.1 | 10636.5 | 9757.6 | 8645.4 | 7889.3 | 7885.6 | 7707.6 | 8024.3 | 8859.0 |
| 40° | 12146.3 | 12152.5 | 11952.4 | 11387.7 | 10465.9 | 9216.2 | 8341.0 | 8332.4 | 8099.2 | 8445.4 | 9262.9 |
| 42.5° | 12371.0 | 12411.5 | 12463.0 | 12104.6 | 11207.3 | 9877.9 | 8879.9 | 8867.6 | 8645.4 | 9049.3 | 9737.9 |
| 45° | 12386.9 | 12467.9 | 12787.1 | 12741.7 | 11958.5 | 10635.3 | 9568.5 | 9534.2 | 9374.6 | 9852.1 | 10305.1 |
| 47.5° | 12249.4 | 12332.9 | 12863.2 | 13121.0 | 12630.0 | 11434.4 | 10373.8 | 10346.8 | 10209.3 | 10856.2 | 10918.8 |
| 50° | 11948.7 | 12028.5 | 12706.1 | 13306.3 | 13182.4 | 12202.8 | 11301.8 | 11230.6 | 11157.0 | 12016.2 | 11621.0 |
| 52.5° | 11385.3 | 11538.7 | 12496.2 | 13350.5 | 13512.6 | 12885.3 | 12277.7 | 12231.0 | 12271.5 | 13240.1 | 12324.3 |
| 55° | 10051.0 | 10222.8 | 11954.8 | 13313.7 | 13756.8 | 13458.6 | 13253.6 | 13251.1 | 13461.0 | 14524.0 | 13079.3 |
| 57.5° | 9303.4 | 9424.9 | 10852.5 | 13251.1 | 14046.5 | 14028.1 | 14219.6 | 14242.9 | 14651.7 | 15922.2 | 13869.8 |
| 60° | 8881.1 | 9008.8 | 10294.0 | 13019.1 | 14495.8 | 14764.6 | 15205.3 | 15252.0 | 15862.0 | 17470.1 | 14821.1 |
| 62.5° | 8496.9 | 8636.8 | 9947.8 | 12546.5 | 15024.9 | 15817.9 | 16386.2 | 16427.9 | 17143.6 | 19061.0 | 15740.5 |
| 65° | 7840.2 | 7998.5 | 9440.9 | 12235.9 | 15506.1 | 17191.5 | 17887.5 | 17915.7 | 18615.4 | 20727.9 | 16443.9 |
| 67.5° | 6912.2 | 7057.0 | 8484.6 | 11549.8 | 15862.0 | 18859.7 | 19883.4 | 19899.4 | 20074.9 | 21905.1 | 16803.6 |
| 70° | 5828.3 | 5883.5 | 7122.1 | 10133.2 | 15441.0 | 20419.8 | 22070.9 | 22074.5 | 21405.5 | 22658.8 | 16744.6 |
| 72.5° | 4095.0 | 4225.1 | 5170.3 | 7670.8 | 13269.5 | 20229.6 | 23206.3 | 23248.1 | 22024.2 | 22278.3 | 15406.6 |
| 75° | 2511.5 | 2649.0 | 3243.1 | 4648.6 | 8418.4 | 15909.9 | 21441.1 | 21730.8 | 20864.2 | 19863.8 | 12585.8 |
| 77.5° | 1679.3 | 1730.8 | 2116.2 | 2710.4 | 3813.9 | 9153.6 | 16484.4 | 17029.4 | 17332.6 | 14486.0 | 8048.9 |
| 80° | 936.6 | 1034.8 | 1403.1 | 1684.2 | 1696.4 | 3637.1 | 9884.0 | 10011.7 | 9643.4 | 5768.1 | 2483.3 |
| 82.5° | 495.9 | 549.9 | 936.6 | 989.4 | 925.6 | 1217.7 | 3683.8 | 3687.5 | 3081.1 | 1546.7 | 737.7 |
| 85° | 384.2 | 429.6 | 642.0 | 603.9 | 472.6 | 540.1 | 1215.2 | 1281.5 | 1048.3 | 633.4 | 240.6 |
| 87.5° | 191.5 | 238.1 | 435.8 | 383.0 | 185.4 | 154.7 | 434.5 | 464.0 | 413.7 | 248.0 | 87.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P359205

CATALOG NUMBER: NVN-SA5C-740-U-T3R

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 6410.1 | 6410.1 | 6410.1 | 6410.1 | 6410.1 | 6410.1 | 6410.1 | 6410.1 | 6410.1 | 6410.1 | 6410.1 |
| 2.5° | 6426.1 | 6437.1 | 6450.6 | 6435.9 | 6431.0 | 6411.4 | 6378.2 | 6370.8 | 6353.7 | 6354.9 | 6364.7 |
| 5° | 6482.5 | 6501.0 | 6493.6 | 6437.1 | 6369.6 | 6275.1 | 6176.9 | 6093.4 | 6038.2 | 6034.5 | 6030.8 |
| 7.5° | 6590.6 | 6602.8 | 6545.2 | 6384.3 | 6195.3 | 5976.8 | 5770.6 | 5590.1 | 5480.9 | 5453.9 | 5447.7 |
| 10° | 6760.0 | 6757.5 | 6599.2 | 6275.1 | 5898.2 | 5507.9 | 5176.5 | 4926.0 | 4780.0 | 4737.0 | 4726.0 |
| 12.5° | 6949.0 | 6920.8 | 6617.6 | 6076.2 | 5478.4 | 4937.1 | 4517.3 | 4238.6 | 4086.4 | 4037.3 | 4025.0 |
| 15° | 7144.2 | 7074.2 | 6572.2 | 5779.2 | 4962.9 | 4322.1 | 3881.4 | 3623.6 | 3541.4 | 3514.4 | 3509.5 |
| 17.5° | 7325.9 | 7190.8 | 6442.0 | 5376.5 | 4374.9 | 3709.6 | 3365.9 | 3262.8 | 3282.4 | 3318.0 | 3319.2 |
| 20° | 7503.8 | 7269.4 | 6233.4 | 4868.4 | 3755.0 | 3205.1 | 3088.4 | 3164.6 | 3257.8 | 3330.3 | 3340.1 |
| 22.5° | 7679.4 | 7324.6 | 5964.5 | 4281.6 | 3200.2 | 2921.5 | 3003.7 | 3142.5 | 3249.3 | 3327.8 | 3341.3 |
| 25° | 7826.7 | 7338.1 | 5593.8 | 3655.6 | 2814.7 | 2814.7 | 2963.2 | 3094.6 | 3200.2 | 3277.5 | 3291.0 |
| 27.5° | 7880.7 | 7247.3 | 5070.9 | 3076.2 | 2620.8 | 2765.6 | 2906.8 | 3016.0 | 3105.6 | 3187.9 | 3202.6 |
| 30° | 7901.6 | 7079.1 | 4467.0 | 2610.9 | 2541.0 | 2712.8 | 2830.7 | 2924.0 | 3008.7 | 3086.0 | 3099.5 |
| 32.5° | 7905.2 | 6876.6 | 3826.2 | 2347.0 | 2485.7 | 2657.6 | 2736.1 | 2818.4 | 2909.2 | 2939.9 | 2944.8 |
| 35° | 7928.6 | 6637.2 | 3151.1 | 2212.0 | 2434.2 | 2606.0 | 2668.6 | 2727.6 | 2580.3 | 2591.3 | 2601.1 |
| 37.5° | 7996.1 | 6400.3 | 2586.4 | 2135.9 | 2401.0 | 2579.0 | 2653.9 | 2440.3 | 2324.9 | 2297.9 | 2294.2 |
| 40° | 8122.5 | 6147.4 | 2167.8 | 2074.5 | 2388.8 | 2592.5 | 2559.4 | 2278.3 | 2079.4 | 1930.9 | 1908.8 |
| 42.5° | 8298.1 | 5874.9 | 1900.2 | 2034.0 | 2397.4 | 2657.6 | 2428.0 | 2122.4 | 1792.2 | 1696.4 | 1684.2 |
| 45° | 8495.7 | 5588.9 | 1755.4 | 2005.8 | 2426.8 | 2707.9 | 2401.0 | 1914.9 | 1658.4 | 1586.0 | 1579.8 |
| 47.5° | 8687.2 | 5239.1 | 1680.5 | 1993.5 | 2467.3 | 2667.4 | 2286.9 | 1851.1 | 1594.6 | 1556.5 | 1560.2 |
| 50° | 8906.9 | 4923.6 | 1635.1 | 1980.0 | 2502.9 | 2641.6 | 2158.0 | 1818.0 | 1570.0 | 1616.6 | 1665.7 |
| 52.5° | 9092.3 | 4597.1 | 1594.6 | 1953.0 | 2516.4 | 2596.2 | 2124.8 | 1824.1 | 1570.0 | 1659.6 | 1706.3 |
| 55° | 9312.0 | 4350.3 | 1547.9 | 1896.5 | 2490.6 | 2467.3 | 2101.5 | 1860.9 | 1588.4 | 1531.9 | 1536.9 |
| 57.5° | 9595.5 | 4269.3 | 1496.4 | 1808.1 | 2404.7 | 2279.5 | 2090.5 | 1896.5 | 1577.4 | 1541.8 | 1554.0 |
| 60° | 9988.4 | 4355.3 | 1475.5 | 1692.8 | 2270.9 | 2132.2 | 2091.7 | 1878.1 | 1500.0 | 1438.7 | 1439.9 |
| 62.5° | 10362.7 | 4451.0 | 1474.3 | 1620.3 | 2106.4 | 2000.9 | 2063.5 | 1818.0 | 1460.8 | 1425.2 | 1438.7 |
| 65° | 10485.5 | 4354.0 | 1415.3 | 1539.3 | 1921.1 | 1843.7 | 2011.9 | 1754.1 | 1431.3 | 1377.3 | 1374.8 |
| 67.5° | 10321.0 | 4053.3 | 1296.3 | 1408.0 | 1708.7 | 1660.8 | 1944.4 | 1678.0 | 1384.6 | 1340.5 | 1333.1 |
| 70° | 9832.5 | 3381.8 | 1149.0 | 1234.9 | 1466.9 | 1454.6 | 1837.6 | 1589.6 | 1322.0 | 1284.0 | 1252.1 |
| 72.5° | 8517.8 | 2409.6 | 968.5 | 1027.4 | 1194.4 | 1233.7 | 1690.3 | 1474.3 | 1233.7 | 1151.4 | 1102.3 |
| 75° | 6995.7 | 1783.6 | 795.4 | 807.7 | 907.1 | 1013.9 | 1487.8 | 1339.2 | 1129.3 | 989.4 | 951.3 |
| 77.5° | 4284.1 | 1091.3 | 633.4 | 638.3 | 650.6 | 808.9 | 1225.1 | 1188.2 | 996.7 | 824.9 | 797.9 |
| 80° | 1387.1 | 595.3 | 457.9 | 481.2 | 444.4 | 592.9 | 947.6 | 1011.5 | 855.6 | 689.9 | 660.4 |
| 82.5° | 527.8 | 347.4 | 309.3 | 325.3 | 308.1 | 397.7 | 691.1 | 810.2 | 700.9 | 567.1 | 461.5 |
| 85° | 255.3 | 196.4 | 182.9 | 205.0 | 190.3 | 203.8 | 441.9 | 596.6 | 531.5 | 369.5 | 343.7 |
| 87.5° | 90.8 | 87.2 | 70.0 | 94.5 | 81.0 | 72.4 | 135.0 | 300.7 | 351.1 | 254.1 | 227.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021

Test Information

Test Method: LM-79-08
 Report Number: SP1-2101-121-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1
 Measurement Geometry: 4π
 Issue Date: 03/05/2021
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: STREETWORKS
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

Spectral Parameters

| | | | | | |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K): | 3905 | CRI (Ra): | 71.2 | R9: | -29.7 |
| CIE u': | 0.2273 | R1: | 68.9 | R10: | 46.2 |
| CIE v': | 0.5024 | R2: | 77.0 | R11: | 68.8 |
| Duv: | -0.0008 | R3: | 84.0 | R12: | 45.6 |
| CIE x: | 0.3841 | R4: | 71.6 | R13: | 69.5 |
| CIE y: | 0.3774 | R5: | 68.9 | R14: | 90.7 |
| CIE z: | 0.2385 | R6: | 68.3 | | |
| Peak Wavelength (nm): | 443 | R7: | 78.7 | | |
| Dominant Wavelength (nm): | 579 | R8: | 52.2 | | |
| Purity: | 28.7 | | | | |
| Rf: | 71.7 | | | | |
| Rg: | 96.9 | | | | |



Test Conditions

Stabilization Time: 211M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.8/312%
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 1/31/2021 | 7/31/2021 |
| Power Meter | IN0071 | 12/1/2020 | 12/1/2021 |
| AC Power Source | IN0063 | 12/1/2020 | 12/1/2021 |
| DC Power Source | IN0208 | 12/1/2020 | 12/1/2021 |
| Sphere Thermometer | IN0085 | 12/1/2020 | 12/1/2021 |
| Room Thermometer | IN0046 | 12/1/2020 | 12/1/2021 |

REPORT NUMBER: SP1-2101-121-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 2.7 | 620 | 97577 | 25.4 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 4.8 | 625 | 90158 | 19.9 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 8.0 | 630 | 82240 | 14.9 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 13.3 | 635 | 74361 | 11.2 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 20.2 | 640 | 66994 | 8.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 28.5 | 645 | 60405 | 5.8 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 37.4 | 650 | 53806 | 3.9 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 44.9 | 655 | 47610 | 2.7 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 52.6 | 660 | 42018 | 1.8 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 58.4 | 665 | 36742 | 1.2 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.0 | 540 | 96845 | 63.1 | 670 | 32105 | 0.7 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.0 | 545 | 100829 | 67.1 | 675 | 27946 | 0.5 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 0.1 | 550 | 105648 | 71.8 | 680 | 24146 | 0.3 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 0.2 | 555 | 110017 | 75.1 | 685 | 21191 | 0.2 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 0.5 | 560 | 114586 | 77.9 | 690 | 18544 | 0.1 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 1.2 | 565 | 118987 | 79.1 | 695 | 16058 | 0.1 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 2.1 | 570 | 122326 | 79.5 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 2.9 | 575 | 125968 | 78.4 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 2.7 | 580 | 127613 | 75.8 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 2.0 | 585 | 129466 | 71.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 1.5 | 590 | 128813 | 66.6 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 1.3 | 595 | 126387 | 59.9 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 1.0 | 600 | 123477 | 53.2 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 1.1 | 605 | 118718 | 46.0 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 1.2 | 610 | 112091 | 38.5 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 1.7 | 615 | 105039 | 31.7 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: 10425.8 S/P: 1.47

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 29.3 | 620 | 97577 | 1.2 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 43.0 | 625 | 90158 | 0.8 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 60.8 | 630 | 82240 | 0.5 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 81.1 | 635 | 74361 | 0.3 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 99.6 | 640 | 66994 | 0.2 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 113.9 | 645 | 60405 | 0.1 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 122.6 | 650 | 53806 | 0.1 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 125.0 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 123.1 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.1 | 535 | 94097 | 117.3 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 107.0 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.9 | 545 | 100829 | 96.7 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 3.0 | 550 | 105648 | 86.4 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 9.3 | 555 | 110017 | 75.2 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 23.0 | 560 | 114586 | 64.0 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 45.7 | 565 | 118987 | 53.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 75.5 | 570 | 122326 | 43.2 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 93.8 | 575 | 125968 | 34.3 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 79.3 | 580 | 127613 | 26.3 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 51.3 | 585 | 129466 | 19.8 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 35.6 | 590 | 128813 | 14.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 26.0 | 595 | 126387 | 10.1 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 19.3 | 600 | 123477 | 7.0 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 16.8 | 605 | 118718 | 4.7 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 17.7 | 610 | 112091 | 3.0 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 21.4 | 615 | 105039 | 1.9 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

REPORT NUMBER: SP1-2101-121-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: 3927.2 M/P: 0.55

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2304 | 0.0 | 490 | 19043 | 15.8 | 620 | 97577 | 0.1 | 750 | 4830 | 0.0 | 880 | 3505 | 0.0 |
| 365 | 2150 | 0.0 | 495 | 26606 | 22.0 | 625 | 90158 | 0.0 | 755 | 4664 | 0.0 | 885 | 2991 | 0.0 |
| 370 | 2146 | 0.0 | 500 | 36376 | 29.2 | 630 | 82240 | 0.0 | 760 | 4006 | 0.0 | 890 | 2327 | 0.0 |
| 375 | 2332 | 0.0 | 505 | 47714 | 36.6 | 635 | 74361 | 0.0 | 765 | 3715 | 0.0 | 895 | 2775 | 0.0 |
| 380 | 2527 | 0.0 | 510 | 58741 | 42.2 | 640 | 66994 | 0.0 | 770 | 3696 | 0.0 | 900 | 2141 | 0.0 |
| 385 | 2304 | 0.0 | 515 | 68716 | 44.9 | 645 | 60405 | 0.0 | 775 | 3117 | 0.0 | 905 | 2421 | 0.0 |
| 390 | 2064 | 0.0 | 520 | 77136 | 44.9 | 650 | 53806 | 0.0 | 780 | 3062 | 0.0 | 910 | 2200 | 0.0 |
| 395 | 1856 | 0.0 | 525 | 83567 | 42.4 | 655 | 47610 | 0.0 | 785 | 2907 | 0.0 | 915 | 2716 | 0.0 |
| 400 | 1856 | 0.0 | 530 | 89283 | 38.6 | 660 | 42018 | 0.0 | 790 | 2655 | 0.0 | 920 | 2656 | 0.0 |
| 405 | 2374 | 0.0 | 535 | 94097 | 33.9 | 665 | 36742 | 0.0 | 795 | 2467 | 0.0 | 925 | 2671 | 0.0 |
| 410 | 4084 | 0.2 | 540 | 96845 | 28.3 | 670 | 32105 | 0.0 | 800 | 2609 | 0.0 | 930 | 3292 | 0.0 |
| 415 | 8543 | 0.6 | 545 | 100829 | 23.4 | 675 | 27946 | 0.0 | 805 | 2293 | 0.0 | 935 | 3188 | 0.0 |
| 420 | 18394 | 2.1 | 550 | 105648 | 19.0 | 680 | 24146 | 0.0 | 810 | 2188 | 0.0 | 940 | 1997 | 0.0 |
| 425 | 37987 | 5.9 | 555 | 110017 | 14.8 | 685 | 21191 | 0.0 | 815 | 2386 | 0.0 | 945 | 2623 | 0.0 |
| 430 | 67605 | 14.3 | 560 | 114586 | 11.3 | 690 | 18544 | 0.0 | 820 | 2712 | 0.0 | 950 | 2969 | 0.0 |
| 435 | 102160 | 27.3 | 565 | 118987 | 8.4 | 695 | 16058 | 0.0 | 825 | 2473 | 0.0 | 955 | 2277 | 0.0 |
| 440 | 135103 | 45.1 | 570 | 122326 | 6.0 | 700 | 14133 | 0.0 | 830 | 1969 | 0.0 | 960 | 4267 | 0.0 |
| 445 | 140126 | 55.3 | 575 | 125968 | 4.2 | 705 | 12309 | 0.0 | 835 | 1917 | 0.0 | 965 | 2034 | 0.0 |
| 450 | 102339 | 47.2 | 580 | 127613 | 2.9 | 710 | 11142 | 0.0 | 840 | 2248 | 0.0 | 970 | 3586 | 0.0 |
| 455 | 58751 | 30.8 | 585 | 129466 | 1.9 | 715 | 10143 | 0.0 | 845 | 2266 | 0.0 | 975 | 2505 | 0.0 |
| 460 | 36892 | 21.7 | 590 | 128813 | 1.3 | 720 | 9072 | 0.0 | 850 | 2558 | 0.0 | 980 | 2666 | 0.0 |
| 465 | 24637 | 16.1 | 595 | 126387 | 0.8 | 725 | 8130 | 0.0 | 855 | 2767 | 0.0 | 985 | 2934 | 0.0 |
| 470 | 16738 | 12.0 | 600 | 123477 | 0.5 | 730 | 7149 | 0.0 | 860 | 2826 | 0.0 | 990 | 4120 | 0.0 |
| 475 | 13456 | 10.3 | 605 | 118718 | 0.3 | 735 | 6311 | 0.0 | 865 | 2385 | 0.0 | 995 | 3858 | 0.0 |
| 480 | 13081 | 10.5 | 610 | 112091 | 0.2 | 740 | 5711 | 0.0 | 870 | 3194 | 0.0 | 1000 | 3405 | 0.0 |
| 485 | 14734 | 12.1 | 615 | 105039 | 0.1 | 745 | 5111 | 0.0 | 875 | 3189 | 0.0 | | | |

Summary

$R_f = 71.7$
 $R_g = 96.9$
 CIE $R_a = 71.2$
 $R_g = -29.7$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)