

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P359451

Luminaire Tested: NVN-SA5D-740-U-SL2

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-2019  
Report Number: P359451  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: STREETWORKS  
Catalog Number: NVN-SA5D-740-U-SL2  
Description: NAVION ROADWAY AND AREA LUMINAIRE  
(5) 70 CRI, 4000K, 1200mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II  
SPILL LIGHT ELIMINATOR OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 38426 lumens  
Efficiency: N/A  
Efficacy: 120.1 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1.5' x H: 0')  
IES Classification: Type III - Medium  
BUG Rating: B4 - U0 - G5


Input Watts (W): 320  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P359451  
 CATALOG NUMBER: NVN-SA5D-740-U-SL2

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 9.8 fc  
 Type III - Medium - N/A

REPORT NUMBER: P359451  
CATALOG NUMBER: NVN-SA5D-740-U-SL2

### Luminous Intensity Polar Plot



— Vertical Plane Through 66-Deg Lateral      - - - Horizontal Cone Through 71-Deg Vertical

REPORT NUMBER: P359451  
 CATALOG NUMBER: NVN-SA5D-740-U-SL2

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 7121.4   | 0.0    | 7121.4  |
|                    | % Fixture | 18.5     | 0.0    | 18.5    |
| <b>Street Side</b> | Lumens    | 31304.6  | 0.0    | 31304.6 |
|                    | % Fixture | 81.5     | 0.0    | 81.5    |
| <b>Total</b>       | Lumens    | 38426.0  | 0.0    | 38426.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 774.8   | 2.0       |
| 10°-20°   | 1858.4  | 4.8       |
| 20°-30°   | 2496.3  | 6.5       |
| 30°-40°   | 3283.9  | 8.5       |
| 40°-50°   | 4777.1  | 12.4      |
| 50°-60°   | 7462.4  | 19.4      |
| 60°-70°   | 9347.9  | 24.3      |
| 70°-80°   | 7130.3  | 18.6      |
| 80°-90°   | 1294.8  | 3.4       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 38426.0 | 100.0     |
| 0°-180°   | 38426.0 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P359451  
 CATALOG NUMBER: NVN-SA5D-740-U-SL2

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|---------|-----------|-------------------------|------|---------|
|                |         |           | B                       | U    | G       |
| FL (0°-30°)    | 3107.3  | 8.1       |                         |      |         |
| FM (30°-60°)   | 13066.8 | 34.0      |                         |      |         |
| FH (60°-80°)   | 13975.9 | 36.4      |                         |      | G5      |
| FVH (80°-90°)  | 1154.6  | 3.0       |                         |      | G5      |
| BL (0°-30°)    | 2022.3  | 5.3       | B3/2500                 |      |         |
| BM (30°-60°)   | 2456.7  | 6.4       | B2/2500                 |      |         |
| BH (60°-80°)   | 2502.3  | 6.5       | B4/5000                 |      | G4/5000 |
| BVH (80°-90°)  | 140.2   | 0.4       |                         |      | G2/225  |
| UL (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0     | 0.0       |                         | U0/0 |         |

**BUG Rating: B4-U0-G5**  
 Type III Medium





REPORT NUMBER: P359451

CATALOG NUMBER: NVN-SA5D-740-U-SL2

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 15°     | 25°     | 35°     | 45°     | 55°     | 65°     | 66°     | 75°     | 85°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 8802.7  | 8802.7  | 8802.7  | 8802.7  | 8802.7  | 8802.7  | 8802.7  | 8802.7  | 8802.7  | 8802.7  | 8802.7  |
| 2.5°  | 8639.5  | 8626.2  | 8666.0  | 8707.1  | 8723.1  | 8749.6  | 8789.4  | 8811.9  | 8810.6  | 8814.6  | 8801.3  |
| 5°    | 8066.3  | 8049.1  | 8128.7  | 8193.7  | 8318.4  | 8459.0  | 8630.2  | 8752.2  | 8754.9  | 8823.9  | 8842.5  |
| 7.5°  | 7523.7  | 7511.8  | 7603.3  | 7708.1  | 7852.7  | 8067.7  | 8344.9  | 8607.6  | 8623.5  | 8810.6  | 8875.6  |
| 10°   | 7088.6  | 7085.9  | 7174.8  | 7288.9  | 7457.4  | 7697.5  | 8015.9  | 8400.7  | 8424.5  | 8746.9  | 8880.9  |
| 12.5° | 6748.9  | 6754.2  | 6831.2  | 6961.2  | 7139.0  | 7389.7  | 7734.7  | 8168.5  | 8207.0  | 8646.1  | 8850.4  |
| 15°   | 6498.2  | 6519.4  | 6581.8  | 6713.1  | 6888.2  | 7143.0  | 7497.2  | 7953.6  | 8011.9  | 8533.3  | 8833.2  |
| 17.5° | 6354.9  | 6378.8  | 6422.6  | 6531.3  | 6695.9  | 6941.3  | 7276.9  | 7777.1  | 7830.2  | 8447.1  | 8834.5  |
| 20°   | 6312.4  | 6332.3  | 6357.5  | 6423.9  | 6563.2  | 6786.1  | 7103.2  | 7617.9  | 7675.0  | 8378.1  | 8847.8  |
| 22.5° | 6396.0  | 6410.6  | 6413.3  | 6408.0  | 6492.9  | 6674.6  | 6977.1  | 7501.2  | 7562.2  | 8333.0  | 8857.0  |
| 25°   | 6575.1  | 6595.0  | 6580.4  | 6531.3  | 6503.5  | 6614.9  | 6912.1  | 7424.2  | 7485.2  | 8299.8  | 8838.5  |
| 27.5° | 6844.4  | 6847.1  | 6835.2  | 6771.5  | 6640.1  | 6621.6  | 6892.2  | 7379.1  | 7437.5  | 8261.4  | 8800.0  |
| 30°   | 7210.6  | 7227.9  | 7206.6  | 7120.4  | 6905.5  | 6727.7  | 6916.1  | 7335.3  | 7388.4  | 8212.3  | 8737.6  |
| 32.5° | 7639.1  | 7681.6  | 7680.3  | 7590.0  | 7282.3  | 6965.2  | 7014.3  | 7308.8  | 7349.9  | 8160.5  | 8662.0  |
| 35°   | 8083.6  | 8142.0  | 8250.7  | 8212.3  | 7831.5  | 7340.6  | 7202.7  | 7351.2  | 7379.1  | 8153.9  | 8609.0  |
| 37.5° | 8545.3  | 8603.6  | 8827.9  | 8931.3  | 8485.6  | 7877.9  | 7499.8  | 7501.2  | 7514.4  | 8234.8  | 8605.0  |
| 40°   | 9028.2  | 9090.5  | 9427.5  | 9696.8  | 9333.3  | 8558.5  | 7978.8  | 7814.3  | 7799.7  | 8433.8  | 8683.2  |
| 42.5° | 9704.8  | 9760.5  | 10165.2 | 10508.8 | 10274.0 | 9430.2  | 8640.8  | 8297.2  | 8266.7  | 8823.9  | 8934.0  |
| 45°   | 10560.5 | 10608.3 | 11038.1 | 11405.6 | 11284.9 | 10425.2 | 9472.6  | 8961.9  | 8956.5  | 9474.0  | 9442.1  |
| 47.5° | 11578.1 | 11615.3 | 12001.3 | 12356.9 | 12400.7 | 11570.1 | 10518.1 | 9987.4  | 9901.2  | 10365.5 | 10228.9 |
| 50°   | 12638.1 | 12679.3 | 12942.0 | 13324.0 | 13649.1 | 13102.5 | 11863.3 | 11243.8 | 11128.4 | 11542.3 | 11343.3 |
| 52.5° | 13340.0 | 13394.4 | 13622.6 | 14106.8 | 15052.7 | 14782.1 | 13454.1 | 12766.8 | 12591.7 | 12968.5 | 12815.9 |
| 55°   | 13026.9 | 13148.9 | 13497.8 | 14274.0 | 16175.1 | 17347.9 | 15416.3 | 14543.3 | 14345.6 | 14658.7 | 14568.5 |
| 57.5° | 11603.3 | 11770.5 | 12246.8 | 13444.8 | 16333.0 | 19608.6 | 18382.8 | 16635.5 | 16496.2 | 16406.0 | 16447.1 |
| 60°   | 9001.7  | 9162.2  | 9752.6  | 11314.1 | 15233.2 | 21259.0 | 22847.1 | 19214.6 | 19012.9 | 18159.9 | 18197.0 |
| 62.5° | 6370.8  | 6289.9  | 6694.5  | 7836.8  | 12378.1 | 21452.7 | 27927.0 | 22664.0 | 22000.7 | 20011.9 | 19848.8 |
| 65°   | 4858.4  | 4839.8  | 5021.6  | 5385.1  | 7497.2  | 19135.0 | 30953.2 | 28461.7 | 27425.5 | 22190.4 | 21805.6 |
| 67.5° | 3992.0  | 3958.9  | 4138.0  | 4667.3  | 4827.9  | 12344.9 | 31019.6 | 35188.1 | 34170.5 | 24902.2 | 24069.0 |
| 70°   | 3282.3  | 3245.1  | 3412.3  | 4095.5  | 4461.7  | 6260.7  | 26106.8 | 39127.0 | 39072.6 | 28335.7 | 25777.8 |
| 71°   | 2942.6  | 2916.1  | 3116.4  | 3875.3  | 4383.4  | 5217.9  | 22540.6 | 39137.6 | 39300.8 | 29497.8 | 25676.9 |
| 72.5° | 2396.0  | 2405.3  | 2617.6  | 3449.4  | 4325.0  | 4607.6  | 16566.5 | 37313.4 | 37658.4 | 30605.6 | 24760.2 |
| 75°   | 1592.0  | 1600.0  | 1878.6  | 2653.4  | 4193.7  | 4508.1  | 9105.1  | 31310.1 | 31944.3 | 29942.3 | 22593.7 |
| 77.5° | 1069.3  | 1066.7  | 1256.4  | 1820.2  | 3653.7  | 4508.1  | 5338.6  | 23417.6 | 24114.1 | 23824.9 | 17418.2 |
| 80°   | 736.3   | 731.0   | 865.0   | 1256.4  | 2766.2  | 4562.5  | 4127.4  | 16411.3 | 16622.2 | 12866.3 | 7079.3  |
| 82.5° | 451.1   | 455.1   | 565.2   | 887.6   | 1882.6  | 4106.1  | 3896.5  | 8948.6  | 8719.1  | 3608.6  | 1768.5  |
| 85°   | 258.7   | 257.4   | 360.9   | 601.0   | 1208.6  | 3465.3  | 3799.7  | 3851.4  | 3533.0  | 1086.6  | 639.5   |
| 87.5° | 92.9    | 99.5    | 193.7   | 333.0   | 692.5   | 2413.3  | 3223.9  | 2003.3  | 1805.6  | 490.9   | 289.2   |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P359451

CATALOG NUMBER: NVN-SA5D-740-U-SL2

**CANDELA DISTRIBUTION (continued):**

|       | 90°     | 95°     | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 8802.7  | 8802.7  | 8802.7 | 8802.7 | 8802.7 | 8802.7 | 8802.7 | 8802.7 | 8802.7 | 8802.7 | 8802.7 |
| 2.5°  | 8792.0  | 8800.0  | 8790.7 | 8737.6 | 8692.5 | 8619.6 | 8578.4 | 8521.4 | 8504.1 | 8496.2 | 8517.4 |
| 5°    | 8825.2  | 8827.9  | 8749.6 | 8610.3 | 8453.7 | 8269.3 | 8136.6 | 7973.5 | 7896.5 | 7863.3 | 7884.6 |
| 7.5°  | 8855.7  | 8843.8  | 8672.6 | 8406.0 | 8116.7 | 7795.7 | 7510.4 | 7249.1 | 7096.5 | 7034.2 | 7039.5 |
| 10°   | 8859.7  | 8809.3  | 8534.7 | 8122.1 | 7673.6 | 7202.7 | 6764.8 | 6361.5 | 6106.8 | 5941.0 | 5991.4 |
| 12.5° | 8818.6  | 8733.7  | 8331.7 | 7754.6 | 7132.3 | 6490.2 | 5898.5 | 5293.5 | 4930.0 | 4761.5 | 4766.8 |
| 15°   | 8786.7  | 8632.8  | 8082.3 | 7322.1 | 6486.2 | 5635.8 | 4827.9 | 4116.7 | 3729.4 | 3556.9 | 3476.0 |
| 17.5° | 8760.2  | 8524.0  | 7793.0 | 6835.2 | 5723.4 | 4644.8 | 3673.6 | 3039.5 | 2827.2 | 2776.8 | 2755.6 |
| 20°   | 8723.1  | 8408.6  | 7470.6 | 6271.3 | 4854.4 | 3535.7 | 2682.6 | 2369.5 | 2370.8 | 2429.2 | 2437.1 |
| 22.5° | 8671.3  | 8277.3  | 7127.0 | 5638.5 | 3921.7 | 2575.1 | 2102.8 | 2012.6 | 2104.1 | 2215.6 | 2235.5 |
| 25°   | 8594.4  | 8122.1  | 6744.9 | 4939.3 | 2990.4 | 1979.4 | 1796.4 | 1792.4 | 1903.8 | 2020.6 | 2037.8 |
| 27.5° | 8485.6  | 7919.1  | 6320.4 | 4188.4 | 2203.6 | 1682.3 | 1609.3 | 1637.1 | 1719.4 | 1804.3 | 1810.9 |
| 30°   | 8339.6  | 7682.9  | 5852.1 | 3396.4 | 1727.4 | 1497.8 | 1489.9 | 1515.1 | 1565.5 | 1625.2 | 1630.5 |
| 32.5° | 8179.1  | 7442.8  | 5351.9 | 2629.5 | 1479.3 | 1398.3 | 1406.3 | 1418.2 | 1442.1 | 1466.0 | 1471.3 |
| 35°   | 8033.2  | 7197.3  | 4839.8 | 1998.0 | 1361.2 | 1333.3 | 1328.0 | 1325.4 | 1328.0 | 1320.1 | 1321.4 |
| 37.5° | 7939.0  | 6994.4  | 4306.5 | 1590.7 | 1293.5 | 1276.3 | 1260.4 | 1240.5 | 1217.9 | 1204.6 | 1207.3 |
| 40°   | 7904.5  | 6843.1  | 3766.5 | 1374.5 | 1237.8 | 1225.9 | 1195.4 | 1152.9 | 1126.4 | 1118.4 | 1118.4 |
| 42.5° | 7997.3  | 6764.8  | 3245.1 | 1265.7 | 1191.4 | 1171.5 | 1121.1 | 1072.0 | 1052.1 | 1050.7 | 1049.4 |
| 45°   | 8281.3  | 6796.7  | 2748.9 | 1206.0 | 1148.9 | 1110.4 | 1044.1 | 1003.0 | 989.7  | 992.4  | 991.0  |
| 47.5° | 8790.7  | 6997.0  | 2324.4 | 1166.2 | 1106.5 | 1056.1 | 981.8  | 948.6  | 932.7  | 932.7  | 934.0  |
| 50°   | 9657.0  | 7465.3  | 1986.1 | 1133.0 | 1070.6 | 1005.6 | 936.7  | 895.5  | 874.3  | 873.0  | 873.0  |
| 52.5° | 10918.7 | 8303.8  | 1775.1 | 1105.1 | 1030.8 | 960.5  | 891.5  | 839.8  | 814.6  | 809.3  | 806.6  |
| 55°   | 12500.2 | 9505.8  | 1716.7 | 1086.6 | 977.8  | 911.4  | 837.1  | 785.4  | 757.5  | 745.6  | 744.3  |
| 57.5° | 14268.7 | 10967.8 | 1832.2 | 1064.0 | 923.4  | 853.1  | 777.4  | 728.4  | 699.2  | 684.6  | 683.3  |
| 60°   | 16058.4 | 12563.8 | 2303.2 | 1032.2 | 878.3  | 789.4  | 716.4  | 671.3  | 642.1  | 626.2  | 623.5  |
| 62.5° | 17850.7 | 14246.1 | 3265.0 | 1029.5 | 846.4  | 728.4  | 654.1  | 615.6  | 587.7  | 570.5  | 566.5  |
| 65°   | 19872.6 | 16087.6 | 4358.2 | 1099.8 | 835.8  | 672.6  | 590.4  | 559.9  | 536.0  | 520.1  | 518.7  |
| 67.5° | 22194.4 | 18166.5 | 4253.4 | 1244.4 | 871.6  | 622.2  | 530.7  | 506.8  | 489.6  | 476.3  | 475.0  |
| 70°   | 23283.6 | 17841.5 | 2644.1 | 1346.6 | 922.1  | 573.1  | 473.6  | 456.4  | 443.1  | 433.8  | 429.9  |
| 71°   | 22827.2 | 16940.6 | 2216.9 | 1334.7 | 916.7  | 551.9  | 451.1  | 437.8  | 424.5  | 416.6  | 412.6  |
| 72.5° | 21582.8 | 15449.4 | 1849.4 | 1241.8 | 857.0  | 513.4  | 421.9  | 408.6  | 396.7  | 387.4  | 384.7  |
| 75°   | 19367.2 | 13797.7 | 1480.6 | 992.4  | 683.3  | 433.8  | 370.1  | 355.6  | 346.3  | 341.0  | 335.7  |
| 77.5° | 14236.8 | 9846.8  | 1144.9 | 784.1  | 502.8  | 354.2  | 315.8  | 305.1  | 295.9  | 287.9  | 283.9  |
| 80°   | 5454.1  | 3814.3  | 770.8  | 585.1  | 368.8  | 279.9  | 254.7  | 249.4  | 240.1  | 234.8  | 234.8  |
| 82.5° | 1468.7  | 1139.6  | 411.3  | 354.2  | 246.8  | 204.3  | 195.0  | 192.4  | 184.4  | 173.8  | 175.1  |
| 85°   | 594.4   | 502.8   | 230.8  | 195.0  | 151.2  | 120.7  | 131.3  | 132.7  | 123.4  | 110.1  | 111.4  |
| 87.5° | 261.4   | 213.6   | 128.7  | 86.2   | 66.3   | 46.4   | 59.7   | 59.7   | 54.4   | 45.1   | 41.1   |
| 90°   | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

MCGRAW, INVUE, LUMARK AND STREETWORKS

DATA VALID FOR LUMINAIRES UTILIZING SA LIGHT ENGINES

Report Number: SP1-2101-121-2

Luminaire Tested: IFLD-S-SA2A-740-U-T3R-HSS

Test Date: 03/05/2021

**Test Information**

Test Method: LM-79-08  
 Report Number: SP1-2101-121-2  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry: 4π  
 Issue Date: 03/05/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **IFLD-S-SA2A-740-U-T3R-HSS**  
 Description: STREETWORKS INF FLOOD

SHIELD, DRIVER PROGRAMMED @ 615mA.

**Spectral Parameters**

|                           |         |           |      |      |       |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K):                  | 3905    | CRI (Ra): | 71.2 | R9:  | -29.7 |
| CIE u':                   | 0.2273  | R1:       | 68.9 | R10: | 46.2  |
| CIE v':                   | 0.5024  | R2:       | 77.0 | R11: | 68.8  |
| Duv:                      | -0.0008 | R3:       | 84.0 | R12: | 45.6  |
| CIE x:                    | 0.3841  | R4:       | 71.6 | R13: | 69.5  |
| CIE y:                    | 0.3774  | R5:       | 68.9 | R14: | 90.7  |
| CIE z:                    | 0.2385  | R6:       | 68.3 |      |       |
| Peak Wavelength (nm):     | 443     | R7:       | 78.7 |      |       |
| Dominant Wavelength (nm): | 579     | R8:       | 52.2 |      |       |
| Purity:                   | 28.7    |           |      |      |       |
| Rf:                       | 71.7    |           |      |      |       |
| Rg:                       | 96.9    |           |      |      |       |



**Test Conditions**

Stabilization Time: 211M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.8/312%  
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-2

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2101-121-2

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-2

**Photopic Flux vs. Wavelength**



#####

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 2.7           | 620    | 97577         | 25.4          | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 4.8           | 625    | 90158         | 19.9          | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 8.0           | 630    | 82240         | 14.9          | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 13.3          | 635    | 74361         | 11.2          | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 20.2          | 640    | 66994         | 8.0           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 28.5          | 645    | 60405         | 5.8           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 37.4          | 650    | 53806         | 3.9           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 44.9          | 655    | 47610         | 2.7           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 52.6          | 660    | 42018         | 1.8           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.0           | 535    | 94097         | 58.4          | 665    | 36742         | 1.2           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.0           | 540    | 96845         | 63.1          | 670    | 32105         | 0.7           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.0           | 545    | 100829        | 67.1          | 675    | 27946         | 0.5           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 0.1           | 550    | 105648        | 71.8          | 680    | 24146         | 0.3           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 0.2           | 555    | 110017        | 75.1          | 685    | 21191         | 0.2           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 0.5           | 560    | 114586        | 77.9          | 690    | 18544         | 0.1           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 1.2           | 565    | 118987        | 79.1          | 695    | 16058         | 0.1           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 2.1           | 570    | 122326        | 79.5          | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 2.9           | 575    | 125968        | 78.4          | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 2.7           | 580    | 127613        | 75.8          | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 2.0           | 585    | 129466        | 71.9          | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 1.5           | 590    | 128813        | 66.6          | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 1.3           | 595    | 126387        | 59.9          | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 1.0           | 600    | 123477        | 53.2          | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 1.1           | 605    | 118718        | 46.0          | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 1.2           | 610    | 112091        | 38.5          | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 1.7           | 615    | 105039        | 31.7          | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

REPORT NUMBER: SP1-2101-121-2

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: 10425.8 S/P: 1.47**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 29.3          | 620    | 97577         | 1.2           | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 43.0          | 625    | 90158         | 0.8           | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 60.8          | 630    | 82240         | 0.5           | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 81.1          | 635    | 74361         | 0.3           | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 99.6          | 640    | 66994         | 0.2           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 113.9         | 645    | 60405         | 0.1           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 122.6         | 650    | 53806         | 0.1           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 125.0         | 655    | 47610         | 0.0           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 123.1         | 660    | 42018         | 0.0           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.1           | 535    | 94097         | 117.3         | 665    | 36742         | 0.0           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.2           | 540    | 96845         | 107.0         | 670    | 32105         | 0.0           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.9           | 545    | 100829        | 96.7          | 675    | 27946         | 0.0           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 3.0           | 550    | 105648        | 86.4          | 680    | 24146         | 0.0           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 9.3           | 555    | 110017        | 75.2          | 685    | 21191         | 0.0           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 23.0          | 560    | 114586        | 64.0          | 690    | 18544         | 0.0           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 45.7          | 565    | 118987        | 53.4          | 695    | 16058         | 0.0           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 75.5          | 570    | 122326        | 43.2          | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 93.8          | 575    | 125968        | 34.3          | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 79.3          | 580    | 127613        | 26.3          | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 51.3          | 585    | 129466        | 19.8          | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 35.6          | 590    | 128813        | 14.3          | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 26.0          | 595    | 126387        | 10.1          | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 19.3          | 600    | 123477        | 7.0           | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 16.8          | 605    | 118718        | 4.7           | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 17.7          | 610    | 112091        | 3.0           | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 21.4          | 615    | 105039        | 1.9           | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

REPORT NUMBER: SP1-2101-121-2

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 3927.2 M/P: 0.55**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2304          | 0.0           | 490    | 19043         | 15.8          | 620    | 97577         | 0.1           | 750    | 4830          | 0.0           | 880    | 3505          | 0.0           |
| 365    | 2150          | 0.0           | 495    | 26606         | 22.0          | 625    | 90158         | 0.0           | 755    | 4664          | 0.0           | 885    | 2991          | 0.0           |
| 370    | 2146          | 0.0           | 500    | 36376         | 29.2          | 630    | 82240         | 0.0           | 760    | 4006          | 0.0           | 890    | 2327          | 0.0           |
| 375    | 2332          | 0.0           | 505    | 47714         | 36.6          | 635    | 74361         | 0.0           | 765    | 3715          | 0.0           | 895    | 2775          | 0.0           |
| 380    | 2527          | 0.0           | 510    | 58741         | 42.2          | 640    | 66994         | 0.0           | 770    | 3696          | 0.0           | 900    | 2141          | 0.0           |
| 385    | 2304          | 0.0           | 515    | 68716         | 44.9          | 645    | 60405         | 0.0           | 775    | 3117          | 0.0           | 905    | 2421          | 0.0           |
| 390    | 2064          | 0.0           | 520    | 77136         | 44.9          | 650    | 53806         | 0.0           | 780    | 3062          | 0.0           | 910    | 2200          | 0.0           |
| 395    | 1856          | 0.0           | 525    | 83567         | 42.4          | 655    | 47610         | 0.0           | 785    | 2907          | 0.0           | 915    | 2716          | 0.0           |
| 400    | 1856          | 0.0           | 530    | 89283         | 38.6          | 660    | 42018         | 0.0           | 790    | 2655          | 0.0           | 920    | 2656          | 0.0           |
| 405    | 2374          | 0.0           | 535    | 94097         | 33.9          | 665    | 36742         | 0.0           | 795    | 2467          | 0.0           | 925    | 2671          | 0.0           |
| 410    | 4084          | 0.2           | 540    | 96845         | 28.3          | 670    | 32105         | 0.0           | 800    | 2609          | 0.0           | 930    | 3292          | 0.0           |
| 415    | 8543          | 0.6           | 545    | 100829        | 23.4          | 675    | 27946         | 0.0           | 805    | 2293          | 0.0           | 935    | 3188          | 0.0           |
| 420    | 18394         | 2.1           | 550    | 105648        | 19.0          | 680    | 24146         | 0.0           | 810    | 2188          | 0.0           | 940    | 1997          | 0.0           |
| 425    | 37987         | 5.9           | 555    | 110017        | 14.8          | 685    | 21191         | 0.0           | 815    | 2386          | 0.0           | 945    | 2623          | 0.0           |
| 430    | 67605         | 14.3          | 560    | 114586        | 11.3          | 690    | 18544         | 0.0           | 820    | 2712          | 0.0           | 950    | 2969          | 0.0           |
| 435    | 102160        | 27.3          | 565    | 118987        | 8.4           | 695    | 16058         | 0.0           | 825    | 2473          | 0.0           | 955    | 2277          | 0.0           |
| 440    | 135103        | 45.1          | 570    | 122326        | 6.0           | 700    | 14133         | 0.0           | 830    | 1969          | 0.0           | 960    | 4267          | 0.0           |
| 445    | 140126        | 55.3          | 575    | 125968        | 4.2           | 705    | 12309         | 0.0           | 835    | 1917          | 0.0           | 965    | 2034          | 0.0           |
| 450    | 102339        | 47.2          | 580    | 127613        | 2.9           | 710    | 11142         | 0.0           | 840    | 2248          | 0.0           | 970    | 3586          | 0.0           |
| 455    | 58751         | 30.8          | 585    | 129466        | 1.9           | 715    | 10143         | 0.0           | 845    | 2266          | 0.0           | 975    | 2505          | 0.0           |
| 460    | 36892         | 21.7          | 590    | 128813        | 1.3           | 720    | 9072          | 0.0           | 850    | 2558          | 0.0           | 980    | 2666          | 0.0           |
| 465    | 24637         | 16.1          | 595    | 126387        | 0.8           | 725    | 8130          | 0.0           | 855    | 2767          | 0.0           | 985    | 2934          | 0.0           |
| 470    | 16738         | 12.0          | 600    | 123477        | 0.5           | 730    | 7149          | 0.0           | 860    | 2826          | 0.0           | 990    | 4120          | 0.0           |
| 475    | 13456         | 10.3          | 605    | 118718        | 0.3           | 735    | 6311          | 0.0           | 865    | 2385          | 0.0           | 995    | 3858          | 0.0           |
| 480    | 13081         | 10.5          | 610    | 112091        | 0.2           | 740    | 5711          | 0.0           | 870    | 3194          | 0.0           | 1000   | 3405          | 0.0           |
| 485    | 14734         | 12.1          | 615    | 105039        | 0.1           | 745    | 5111          | 0.0           | 875    | 3189          | 0.0           |        |               |               |

**Summary**

$R_f = 71.7$   
 $R_g = 96.9$   
 CIE  $R_a = 71.2$   
 $R_g = -29.7$



**Color Vector Graphics**





**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 86 | CES76 = 45 |
| CES02 = 61 | CES27 = 80 | CES52 = 87 | CES77 = 68 |
| CES03 = 30 | CES28 = 79 | CES53 = 74 | CES78 = 49 |
| CES04 = 70 | CES29 = 51 | CES54 = 81 | CES79 = 77 |
| CES05 = 47 | CES30 = 60 | CES55 = 80 | CES80 = 75 |
| CES06 = 50 | CES31 = 56 | CES56 = 69 | CES81 = 75 |
| CES07 = 40 | CES32 = 52 | CES57 = 67 | CES82 = 90 |
| CES08 = 39 | CES33 = 62 | CES58 = 69 | CES83 = 85 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 87 |
| CES10 = 74 | CES35 = 81 | CES60 = 91 | CES85 = 83 |
| CES11 = 57 | CES36 = 92 | CES61 = 85 | CES86 = 72 |
| CES12 = 63 | CES37 = 74 | CES62 = 81 | CES87 = 77 |
| CES13 = 42 | CES38 = 69 | CES63 = 72 | CES88 = 77 |
| CES14 = 74 | CES39 = 92 | CES64 = 69 | CES89 = 72 |
| CES15 = 71 | CES40 = 86 | CES65 = 64 | CES90 = 75 |
| CES16 = 46 | CES41 = 84 | CES66 = 63 | CES91 = 91 |
| CES17 = 49 | CES42 = 75 | CES67 = 60 | CES92 = 66 |
| CES18 = 56 | CES43 = 70 | CES68 = 67 | CES93 = 80 |
| CES19 = 72 | CES44 = 98 | CES69 = 77 | CES94 = 56 |
| CES20 = 65 | CES45 = 80 | CES70 = 57 | CES95 = 72 |
| CES21 = 86 | CES46 = 77 | CES71 = 53 | CES96 = 78 |
| CES22 = 78 | CES47 = 74 | CES72 = 84 | CES97 = 83 |
| CES23 = 92 | CES48 = 66 | CES73 = 47 | CES98 = 73 |
| CES24 = 91 | CES49 = 76 | CES74 = 96 | CES99 = 63 |
| CES25 = 72 | CES50 = 85 | CES75 = 52 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)