

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: STREETWORKS

Report Number: P892374

Luminaire Tested: **NVN-SA4C-750-U-T1**

Issue Date: 10/28/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P892374  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-042-5)  
Test Lab: INNOVATIONS CENTER  
Issue Date: 10/28/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: STREETWORKS  
Catalog Number: NVN-SA4C-750-U-T1  
Description: NAVION ROADWAY AND AREA LUMINAIRE  
(4) 70 CRI, 5000K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE I OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 28765 lumens  
Efficiency: N/A  
Efficacy: 127.8 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1.5' x H: 0')  
IES Classification: Type I - Short  
BUG Rating: B4 - U0 - G4


Input Watts (W): 225  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P892374  
 CATALOG NUMBER: NVN-SA4C-750-U-T1

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 8.6 fc  
 Type I - Short - N/A

REPORT NUMBER: P892374  
CATALOG NUMBER: NVN-SA4C-750-U-T1

### Luminous Intensity Polar Plot



REPORT NUMBER: P892374  
 CATALOG NUMBER: NVN-SA4C-750-U-T1


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 14382.5  | 0.0    | 14382.5 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Street Side</b> | Lumens    | 14382.5  | 0.0    | 14382.5 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Total</b>       | Lumens    | 28765.0  | 0.0    | 28765.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 507.7   | 1.8       |
| 10°-20°   | 1624.4  | 5.6       |
| 20°-30°   | 2718.8  | 9.5       |
| 30°-40°   | 3683.2  | 12.8      |
| 40°-50°   | 4665.4  | 16.2      |
| 50°-60°   | 5828.3  | 20.3      |
| 60°-70°   | 6850.9  | 23.8      |
| 70°-80°   | 2620.8  | 9.1       |
| 80°-90°   | 265.5   | 0.9       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 28765.0 | 100.0     |
| 0°-180°   | 28765.0 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P892374  
 CATALOG NUMBER: NVN-SA4C-750-U-T1

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 2425.4 | 8.4       |                         |      |         |
| FM (30°-60°)   | 7088.5 | 24.6      |                         |      |         |
| FH (60°-80°)   | 4735.8 | 16.5      |                         |      | G2/5000 |
| FVH (80°-90°)  | 132.8  | 0.5       |                         |      | G2/225  |
| BL (0°-30°)    | 2425.4 | 8.4       | B3/2500                 |      |         |
| BM (30°-60°)   | 7088.5 | 24.6      | B4/8500                 |      |         |
| BH (60°-80°)   | 4735.8 | 16.5      | B4/5000                 |      | G4/5000 |
| BVH (80°-90°)  | 132.8  | 0.5       |                         |      | G2/225  |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B4-U0-G4**

Type I Short



REPORT NUMBER: P892374

CATALOG NUMBER: NVN-SA4C-750-U-T1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°     | 75°     | 85°     | 90°     |
|-------|--------|--------|--------|--------|--------|--------|--------|---------|---------|---------|---------|
| 0°    | 5092.3 | 5092.3 | 5092.3 | 5092.3 | 5092.3 | 5092.3 | 5092.3 | 5092.3  | 5092.3  | 5092.3  | 5092.3  |
| 2.5°  | 5157.6 | 5154.4 | 5156.0 | 5154.4 | 5159.2 | 5156.0 | 5136.9 | 5121.0  | 5108.2  | 5109.8  | 5105.0  |
| 5°    | 5267.5 | 5269.1 | 5270.7 | 5262.7 | 5273.9 | 5267.5 | 5237.2 | 5211.8  | 5186.3  | 5176.7  | 5173.5  |
| 7.5°  | 5358.3 | 5366.3 | 5371.0 | 5379.0 | 5398.1 | 5398.1 | 5382.2 | 5345.6  | 5289.8  | 5258.0  | 5256.4  |
| 10°   | 5449.1 | 5455.5 | 5469.8 | 5495.3 | 5527.1 | 5557.4 | 5551.0 | 5501.7  | 5430.0  | 5375.8  | 5363.1  |
| 12.5° | 5481.0 | 5488.9 | 5536.7 | 5610.0 | 5681.7 | 5740.6 | 5740.6 | 5700.8  | 5608.4  | 5525.6  | 5501.7  |
| 15°   | 5369.5 | 5383.8 | 5469.8 | 5625.9 | 5813.9 | 5942.9 | 5971.5 | 5915.8  | 5817.0  | 5689.6  | 5660.9  |
| 17.5° | 5148.0 | 5183.1 | 5308.9 | 5539.9 | 5852.1 | 6119.7 | 6202.5 | 6175.4  | 6048.0  | 5885.5  | 5852.1  |
| 20°   | 4910.7 | 4948.9 | 5082.7 | 5388.6 | 5820.2 | 6223.2 | 6463.7 | 6470.1  | 6312.4  | 6076.7  | 6027.3  |
| 22.5° | 4649.5 | 4678.2 | 4850.2 | 5208.6 | 5724.7 | 6247.1 | 6688.3 | 6798.2  | 6584.8  | 6267.8  | 6197.7  |
| 25°   | 4356.4 | 4388.3 | 4568.3 | 4955.3 | 5544.7 | 6220.0 | 6893.8 | 7135.9  | 6869.9  | 6471.7  | 6382.5  |
| 27.5° | 4076.1 | 4088.8 | 4281.5 | 4675.0 | 5307.3 | 6149.9 | 7045.1 | 7446.5  | 7185.3  | 6640.5  | 6527.4  |
| 30°   | 3806.9 | 3837.1 | 4007.6 | 4396.2 | 5035.0 | 6013.0 | 7175.7 | 7800.1  | 7524.6  | 6817.3  | 6672.4  |
| 32.5° | 3521.8 | 3558.4 | 3743.2 | 4136.6 | 4762.6 | 5807.5 | 7255.4 | 8187.2  | 7997.6  | 7104.1  | 6949.5  |
| 35°   | 3247.8 | 3271.7 | 3458.0 | 3840.3 | 4496.6 | 5568.6 | 7269.7 | 8623.6  | 8607.7  | 7538.9  | 7333.4  |
| 37.5° | 2967.5 | 3002.5 | 3190.5 | 3556.8 | 4214.6 | 5315.3 | 7198.0 | 9087.1  | 9343.6  | 8142.6  | 7921.2  |
| 40°   | 2698.3 | 2728.5 | 2913.3 | 3282.8 | 3894.5 | 5006.3 | 7027.6 | 9510.8  | 10202.1 | 8763.8  | 8450.0  |
| 42.5° | 2405.2 | 2413.1 | 2615.4 | 2991.3 | 3580.7 | 4647.9 | 6782.3 | 9888.3  | 11159.4 | 9596.8  | 9206.6  |
| 45°   | 2072.3 | 2093.0 | 2280.9 | 2650.5 | 3220.7 | 4246.5 | 6449.4 | 10200.5 | 12373.2 | 10751.7 | 10219.6 |
| 47.5° | 1739.4 | 1756.9 | 1928.9 | 2293.7 | 2827.3 | 3786.2 | 5936.5 | 10474.5 | 13618.8 | 12218.7 | 11521.0 |
| 50°   | 1414.4 | 1424.0 | 1564.2 | 1887.5 | 2384.5 | 3302.0 | 5301.0 | 10562.1 | 15026.8 | 14295.7 | 13405.3 |
| 52.5° | 1118.2 | 1132.5 | 1239.2 | 1492.5 | 1911.4 | 2730.1 | 4614.4 | 10345.5 | 16670.6 | 16758.2 | 15503.1 |
| 55°   | 906.3  | 911.1  | 990.7  | 1177.1 | 1494.1 | 2131.2 | 3786.2 | 9741.8  | 18438.7 | 19913.7 | 18312.8 |
| 57.5° | 780.5  | 783.7  | 828.3  | 931.8  | 1150.0 | 1607.2 | 2937.2 | 8599.7  | 20026.7 | 23610.6 | 21552.7 |
| 60°   | 708.8  | 710.4  | 735.9  | 796.4  | 911.1  | 1232.9 | 2104.1 | 6987.8  | 21594.1 | 27724.9 | 25579.4 |
| 62.5° | 664.2  | 664.2  | 681.7  | 715.2  | 770.9  | 946.1  | 1524.3 | 5041.3  | 22667.7 | 31899.8 | 30542.7 |
| 65°   | 621.2  | 621.2  | 633.9  | 657.8  | 688.1  | 774.1  | 1126.1 | 3287.6  | 22640.6 | 34940.5 | 35534.6 |
| 67.5° | 571.8  | 571.8  | 581.4  | 605.3  | 622.8  | 665.8  | 869.7  | 2153.5  | 20337.3 | 34873.6 | 38258.4 |
| 70°   | 512.9  | 512.9  | 525.6  | 546.3  | 560.7  | 587.8  | 686.5  | 1473.4  | 14940.8 | 29776.5 | 34024.6 |
| 72.5° | 454.0  | 455.6  | 463.5  | 484.2  | 495.4  | 511.3  | 570.2  | 1032.2  | 9165.2  | 20275.2 | 23790.6 |
| 75°   | 388.7  | 391.8  | 399.8  | 420.5  | 430.1  | 436.4  | 481.0  | 735.9   | 4636.7  | 10931.6 | 12446.4 |
| 77.5° | 313.8  | 320.2  | 324.9  | 347.2  | 353.6  | 363.2  | 396.6  | 532.0   | 2035.6  | 3927.9  | 3963.0  |
| 80°   | 229.4  | 237.3  | 251.7  | 272.4  | 277.2  | 283.5  | 302.6  | 377.5   | 922.3   | 1793.5  | 1948.0  |
| 82.5° | 168.8  | 180.0  | 162.5  | 189.5  | 189.5  | 181.6  | 213.4  | 253.3   | 423.7   | 1776.0  | 2124.8  |
| 85°   | 92.4   | 94.0   | 84.4   | 97.2   | 103.5  | 101.9  | 113.1  | 124.2   | 205.5   | 1185.1  | 1221.7  |
| 87.5° | 22.3   | 23.9   | 25.5   | 30.3   | 36.6   | 36.6   | 39.8   | 35.0    | 66.9    | 383.9   | 219.8   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-4-R4

Test Date: 10/02/2019

Luminaire Tested: SA1C-750-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .



**Test Information**

Test Method: LM-79-2008  
 Report Number: SP1-1908-441-4-R4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/28/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGRAW-EDISON  
 Catalog Number: **SA1C-750-U-5WQ**  
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

\*\*\*THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.\*\*\*TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

**Spectral Parameters**

|                           |        |           |      |      |       |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K):                  | 4884   | CRI (Ra): | 73.5 | R9:  | -28.4 |
| CIE u':                   | 0.2101 | R1:       | 70.5 | R10: | 48.6  |
| CIE v':                   | 0.4904 | R2:       | 77.7 | R11: | 73.2  |
| Duv:                      | 0.0037 | R3:       | 84.6 | R12: | 50.7  |
| CIE x:                    | 0.3493 | R4:       | 74.7 | R13: | 71.2  |
| CIE y:                    | 0.3624 | R5:       | 71.9 | R14: | 91.4  |
| CIE z:                    | 0.2884 | R6:       | 70.7 |      |       |
| Peak Wavelength (nm):     | 444    | R7:       | 81.2 |      |       |
| Dominant Wavelength (nm): | 571    | R8:       | 56.9 |      |       |
| Purity:                   | 13.7   |           |      |      |       |
| Rf:                       | 74.9   |           |      |      |       |
| Rg:                       | 96.3   |           |      |      |       |



**Test Conditions**

Stabilization Time: 240M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.0./44%  
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-4-R4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/28/2019        | 12/28/2019           |
| Power Meter                    | IN0071                | 12/5/2018        | 12/5/2019            |
| AC Power Source                | IN0063                | 12/5/2018        | 12/5/2019            |
| DC Power Source                | IN0208                | 12/5/2018        | 12/5/2019            |
| Sphere Thermometer             | IN0085                | 12/5/2018        | 12/5/2019            |
| Room Thermometer               | IN0046                | 12/5/2018        | 12/5/2019            |

REPORT NUMBER: SP1-1908-441-4-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-4-R4

**Photopic Flux vs. Wavelength**



#####

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W}/\text{nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 2945                                 | NR                             | 490               | 37941                                | NR                             | 620               | 88803                                | NR                             | 750               | 3908                                 | NR                             | 880               | 2997                                 | NR                             |
| 365               | 2596                                 | NR                             | 495               | 48525                                | NR                             | 625               | 80578                                | NR                             | 755               | 3988                                 | NR                             | 885               | 2927                                 | NR                             |
| 370               | 2732                                 | NR                             | 500               | 60609                                | NR                             | 630               | 73127                                | NR                             | 760               | 3335                                 | NR                             | 890               | 2649                                 | NR                             |
| 375               | 2894                                 | NR                             | 505               | 72036                                | NR                             | 635               | 66244                                | NR                             | 765               | 3438                                 | NR                             | 895               | 2828                                 | NR                             |
| 380               | 2822                                 | NR                             | 510               | 82168                                | NR                             | 640               | 59440                                | NR                             | 770               | 3427                                 | NR                             | 900               | 1407                                 | NR                             |
| 385               | 2394                                 | NR                             | 515               | 90898                                | NR                             | 645               | 52864                                | NR                             | 775               | 2759                                 | NR                             | 905               | 2224                                 | NR                             |
| 390               | 2370                                 | NR                             | 520               | 97142                                | NR                             | 650               | 47085                                | NR                             | 780               | 2340                                 | NR                             | 910               | 2905                                 | NR                             |
| 395               | 2267                                 | NR                             | 525               | 103255                               | NR                             | 655               | 41789                                | NR                             | 785               | 2412                                 | NR                             | 915               | 3350                                 | NR                             |
| 400               | 2262                                 | NR                             | 530               | 106697                               | NR                             | 660               | 37064                                | NR                             | 790               | 1999                                 | NR                             | 920               | 3114                                 | NR                             |
| 405               | 3000                                 | NR                             | 535               | 110081                               | NR                             | 665               | 32299                                | NR                             | 795               | 2054                                 | NR                             | 925               | 2834                                 | NR                             |
| 410               | 5324                                 | NR                             | 540               | 112494                               | NR                             | 670               | 28142                                | NR                             | 800               | 2331                                 | NR                             | 930               | 2271                                 | NR                             |
| 415               | 10725                                | NR                             | 545               | 115513                               | NR                             | 675               | 24505                                | NR                             | 805               | 2648                                 | NR                             | 935               | 2228                                 | NR                             |
| 420               | 22128                                | NR                             | 550               | 117203                               | NR                             | 680               | 21162                                | NR                             | 810               | 2485                                 | NR                             | 940               | 2833                                 | NR                             |
| 425               | 44095                                | NR                             | 555               | 119753                               | NR                             | 685               | 18400                                | NR                             | 815               | 2409                                 | NR                             | 945               | 2941                                 | NR                             |
| 430               | 77002                                | NR                             | 560               | 122602                               | NR                             | 690               | 16065                                | NR                             | 820               | 2221                                 | NR                             | 950               | 2323                                 | NR                             |
| 435               | 119881                               | NR                             | 565               | 124314                               | NR                             | 695               | 13860                                | NR                             | 825               | 1562                                 | NR                             | 955               | 1667                                 | NR                             |
| 440               | 164454                               | NR                             | 570               | 126775                               | NR                             | 700               | 12177                                | NR                             | 830               | 2249                                 | NR                             | 960               | 749                                  | NR                             |
| 445               | 179997                               | NR                             | 575               | 127511                               | NR                             | 705               | 10757                                | NR                             | 835               | 2573                                 | NR                             | 965               | 2669                                 | NR                             |
| 450               | 142822                               | NR                             | 580               | 127577                               | NR                             | 710               | 9601                                 | NR                             | 840               | 2764                                 | NR                             | 970               | 3968                                 | NR                             |
| 455               | 90008                                | NR                             | 585               | 126153                               | NR                             | 715               | 8944                                 | NR                             | 845               | 3109                                 | NR                             | 975               | 3886                                 | NR                             |
| 460               | 60557                                | NR                             | 590               | 123678                               | NR                             | 720               | 7947                                 | NR                             | 850               | 2963                                 | NR                             | 980               | 2788                                 | NR                             |
| 465               | 43305                                | NR                             | 595               | 119774                               | NR                             | 725               | 7062                                 | NR                             | 855               | 2336                                 | NR                             | 985               | 3496                                 | NR                             |
| 470               | 31089                                | NR                             | 600               | 115733                               | NR                             | 730               | 6004                                 | NR                             | 860               | 2118                                 | NR                             | 990               | 2913                                 | NR                             |
| 475               | 26278                                | NR                             | 605               | 109231                               | NR                             | 735               | 5594                                 | NR                             | 865               | 3144                                 | NR                             | 995               | 4659                                 | NR                             |
| 480               | 27060                                | NR                             | 610               | 102408                               | NR                             | 740               | 5165                                 | NR                             | 870               | 3069                                 | NR                             | 1000              | 1308                                 | NR                             |
| 485               | 30698                                | NR                             | 615               | 96015                                | NR                             | 745               | 4687                                 | NR                             | 875               | 3311                                 | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-1908-441-4-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13493.5 S/P: 1.77

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2945          | NR            | 490    | 37941         | NR            | 620    | 88803         | NR            | 750    | 3908          | NR            | 880    | 2997          | NR            |
| 365    | 2596          | NR            | 495    | 48525         | NR            | 625    | 80578         | NR            | 755    | 3988          | NR            | 885    | 2927          | NR            |
| 370    | 2732          | NR            | 500    | 60609         | NR            | 630    | 73127         | NR            | 760    | 3335          | NR            | 890    | 2649          | NR            |
| 375    | 2894          | NR            | 505    | 72036         | NR            | 635    | 66244         | NR            | 765    | 3438          | NR            | 895    | 2828          | NR            |
| 380    | 2822          | NR            | 510    | 82168         | NR            | 640    | 59440         | NR            | 770    | 3427          | NR            | 900    | 1407          | NR            |
| 385    | 2394          | NR            | 515    | 90898         | NR            | 645    | 52864         | NR            | 775    | 2759          | NR            | 905    | 2224          | NR            |
| 390    | 2370          | NR            | 520    | 97142         | NR            | 650    | 47085         | NR            | 780    | 2340          | NR            | 910    | 2905          | NR            |
| 395    | 2267          | NR            | 525    | 103255        | NR            | 655    | 41789         | NR            | 785    | 2412          | NR            | 915    | 3350          | NR            |
| 400    | 2262          | NR            | 530    | 106697        | NR            | 660    | 37064         | NR            | 790    | 1999          | NR            | 920    | 3114          | NR            |
| 405    | 3000          | NR            | 535    | 110081        | NR            | 665    | 32299         | NR            | 795    | 2054          | NR            | 925    | 2834          | NR            |
| 410    | 5324          | NR            | 540    | 112494        | NR            | 670    | 28142         | NR            | 800    | 2331          | NR            | 930    | 2271          | NR            |
| 415    | 10725         | NR            | 545    | 115513        | NR            | 675    | 24505         | NR            | 805    | 2648          | NR            | 935    | 2228          | NR            |
| 420    | 22128         | NR            | 550    | 117203        | NR            | 680    | 21162         | NR            | 810    | 2485          | NR            | 940    | 2833          | NR            |
| 425    | 44095         | NR            | 555    | 119753        | NR            | 685    | 18400         | NR            | 815    | 2409          | NR            | 945    | 2941          | NR            |
| 430    | 77002         | NR            | 560    | 122602        | NR            | 690    | 16065         | NR            | 820    | 2221          | NR            | 950    | 2323          | NR            |
| 435    | 119881        | NR            | 565    | 124314        | NR            | 695    | 13860         | NR            | 825    | 1562          | NR            | 955    | 1667          | NR            |
| 440    | 164454        | NR            | 570    | 126775        | NR            | 700    | 12177         | NR            | 830    | 2249          | NR            | 960    | 749           | NR            |
| 445    | 179997        | NR            | 575    | 127511        | NR            | 705    | 10757         | NR            | 835    | 2573          | NR            | 965    | 2669          | NR            |
| 450    | 142822        | NR            | 580    | 127577        | NR            | 710    | 9601          | NR            | 840    | 2764          | NR            | 970    | 3968          | NR            |
| 455    | 90008         | NR            | 585    | 126153        | NR            | 715    | 8944          | NR            | 845    | 3109          | NR            | 975    | 3886          | NR            |
| 460    | 60557         | NR            | 590    | 123678        | NR            | 720    | 7947          | NR            | 850    | 2963          | NR            | 980    | 2788          | NR            |
| 465    | 43305         | NR            | 595    | 119774        | NR            | 725    | 7062          | NR            | 855    | 2336          | NR            | 985    | 3496          | NR            |
| 470    | 31089         | NR            | 600    | 115733        | NR            | 730    | 6004          | NR            | 860    | 2118          | NR            | 990    | 2913          | NR            |
| 475    | 26278         | NR            | 605    | 109231        | NR            | 735    | 5594          | NR            | 865    | 3144          | NR            | 995    | 4659          | NR            |
| 480    | 27060         | NR            | 610    | 102408        | NR            | 740    | 5165          | NR            | 870    | 3069          | NR            | 1000   | 1308          | NR            |
| 485    | 30698         | NR            | 615    | 96015         | NR            | 745    | 4687          | NR            | 875    | 3311          | NR            |        |               |               |

REPORT NUMBER: SP1-1908-441-4-R4

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 5378.9 M/P: 0.71**

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2945          | NR            | 490    | 37941         | NR            | 620    | 88803         | NR            | 750    | 3908          | NR            | 880    | 2997          | NR            |
| 365    | 2596          | NR            | 495    | 48525         | NR            | 625    | 80578         | NR            | 755    | 3988          | NR            | 885    | 2927          | NR            |
| 370    | 2732          | NR            | 500    | 60609         | NR            | 630    | 73127         | NR            | 760    | 3335          | NR            | 890    | 2649          | NR            |
| 375    | 2894          | NR            | 505    | 72036         | NR            | 635    | 66244         | NR            | 765    | 3438          | NR            | 895    | 2828          | NR            |
| 380    | 2822          | NR            | 510    | 82168         | NR            | 640    | 59440         | NR            | 770    | 3427          | NR            | 900    | 1407          | NR            |
| 385    | 2394          | NR            | 515    | 90898         | NR            | 645    | 52864         | NR            | 775    | 2759          | NR            | 905    | 2224          | NR            |
| 390    | 2370          | NR            | 520    | 97142         | NR            | 650    | 47085         | NR            | 780    | 2340          | NR            | 910    | 2905          | NR            |
| 395    | 2267          | NR            | 525    | 103255        | NR            | 655    | 41789         | NR            | 785    | 2412          | NR            | 915    | 3350          | NR            |
| 400    | 2262          | NR            | 530    | 106697        | NR            | 660    | 37064         | NR            | 790    | 1999          | NR            | 920    | 3114          | NR            |
| 405    | 3000          | NR            | 535    | 110081        | NR            | 665    | 32299         | NR            | 795    | 2054          | NR            | 925    | 2834          | NR            |
| 410    | 5324          | NR            | 540    | 112494        | NR            | 670    | 28142         | NR            | 800    | 2331          | NR            | 930    | 2271          | NR            |
| 415    | 10725         | NR            | 545    | 115513        | NR            | 675    | 24505         | NR            | 805    | 2648          | NR            | 935    | 2228          | NR            |
| 420    | 22128         | NR            | 550    | 117203        | NR            | 680    | 21162         | NR            | 810    | 2485          | NR            | 940    | 2833          | NR            |
| 425    | 44095         | NR            | 555    | 119753        | NR            | 685    | 18400         | NR            | 815    | 2409          | NR            | 945    | 2941          | NR            |
| 430    | 77002         | NR            | 560    | 122602        | NR            | 690    | 16065         | NR            | 820    | 2221          | NR            | 950    | 2323          | NR            |
| 435    | 119881        | NR            | 565    | 124314        | NR            | 695    | 13860         | NR            | 825    | 1562          | NR            | 955    | 1667          | NR            |
| 440    | 164454        | NR            | 570    | 126775        | NR            | 700    | 12177         | NR            | 830    | 2249          | NR            | 960    | 749           | NR            |
| 445    | 179997        | NR            | 575    | 127511        | NR            | 705    | 10757         | NR            | 835    | 2573          | NR            | 965    | 2669          | NR            |
| 450    | 142822        | NR            | 580    | 127577        | NR            | 710    | 9601          | NR            | 840    | 2764          | NR            | 970    | 3968          | NR            |
| 455    | 90008         | NR            | 585    | 126153        | NR            | 715    | 8944          | NR            | 845    | 3109          | NR            | 975    | 3886          | NR            |
| 460    | 60557         | NR            | 590    | 123678        | NR            | 720    | 7947          | NR            | 850    | 2963          | NR            | 980    | 2788          | NR            |
| 465    | 43305         | NR            | 595    | 119774        | NR            | 725    | 7062          | NR            | 855    | 2336          | NR            | 985    | 3496          | NR            |
| 470    | 31089         | NR            | 600    | 115733        | NR            | 730    | 6004          | NR            | 860    | 2118          | NR            | 990    | 2913          | NR            |
| 475    | 26278         | NR            | 605    | 109231        | NR            | 735    | 5594          | NR            | 865    | 3144          | NR            | 995    | 4659          | NR            |
| 480    | 27060         | NR            | 610    | 102408        | NR            | 740    | 5165          | NR            | 870    | 3069          | NR            | 1000   | 1308          | NR            |
| 485    | 30698         | NR            | 615    | 96015         | NR            | 745    | 4687          | NR            | 875    | 3311          | NR            |        |               |               |

REPORT NUMBER: SP1-1908-441-4-R4



TM-30-18

**Summary**

$R_f = 74.9$   
 $R_g = 96.3$   
 CIE  $R_a = 73.5$   
 $R_g = -28.4$



**Color Vector Graphics**



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 61 | CES51 = 90 | CES76 = 52 |
| CES02 = 60 | CES27 = 84 | CES52 = 91 | CES77 = 71 |
| CES03 = 30 | CES28 = 81 | CES53 = 79 | CES78 = 54 |
| CES04 = 69 | CES29 = 58 | CES54 = 83 | CES79 = 80 |
| CES05 = 46 | CES30 = 67 | CES55 = 83 | CES80 = 77 |
| CES06 = 50 | CES31 = 63 | CES56 = 73 | CES81 = 77 |
| CES07 = 39 | CES32 = 59 | CES57 = 72 | CES82 = 90 |
| CES08 = 38 | CES33 = 69 | CES58 = 73 | CES83 = 86 |
| CES09 = 29 | CES34 = 69 | CES59 = 88 | CES84 = 88 |
| CES10 = 73 | CES35 = 83 | CES60 = 93 | CES85 = 84 |
| CES11 = 56 | CES36 = 95 | CES61 = 88 | CES86 = 75 |
| CES12 = 61 | CES37 = 78 | CES62 = 85 | CES87 = 78 |
| CES13 = 41 | CES38 = 76 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 93 | CES64 = 74 | CES89 = 75 |
| CES15 = 70 | CES40 = 86 | CES65 = 67 | CES90 = 77 |
| CES16 = 46 | CES41 = 87 | CES66 = 69 | CES91 = 89 |
| CES17 = 49 | CES42 = 78 | CES67 = 67 | CES92 = 66 |
| CES18 = 55 | CES43 = 75 | CES68 = 73 | CES93 = 80 |
| CES19 = 71 | CES44 = 99 | CES69 = 81 | CES94 = 57 |
| CES20 = 64 | CES45 = 83 | CES70 = 63 | CES95 = 71 |
| CES21 = 85 | CES46 = 81 | CES71 = 60 | CES96 = 78 |
| CES22 = 77 | CES47 = 80 | CES72 = 86 | CES97 = 85 |
| CES23 = 91 | CES48 = 72 | CES73 = 53 | CES98 = 75 |
| CES24 = 90 | CES49 = 81 | CES74 = 96 | CES99 = 62 |
| CES25 = 71 | CES50 = 89 | CES75 = 58 |            |





REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Measure Comparisons



(END OF REPORT)