

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P364047

Luminaire Tested: NVN-SA5B-750-U-SLR-HSS

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-2019
Report Number: P364047
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-28)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: STREETWORKS
Catalog Number: NVN-SA5B-750-U-SLR-HSS
Description: NAVION ROADWAY AND AREA LUMINAIRE
(5) 70 CRI, 5000K, 800mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 21506 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1.5' x H: 0')
IES Classification: Type IV - Medium
BUG Rating: B2 - U0 - G3


Input Watts (W): 210
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P364047
 CATALOG NUMBER: NVN-SA5B-750-U-SLR-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 11.2 fc
 Type IV - Medium - N/A

REPORT NUMBER: P364047
CATALOG NUMBER: NVN-SA5B-750-U-SLR-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 345-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P364047
 CATALOG NUMBER: NVN-SA5B-750-U-SLR-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 2602.9 | 0.0 | 2602.9 |
| | % Fixture | 12.1 | 0.0 | 12.1 |
| Street Side | Lumens | 18903.1 | 0.0 | 18903.1 |
| | % Fixture | 87.9 | 0.0 | 87.9 |
| Total | Lumens | 21506.0 | 0.0 | 21506.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 537.7 | 2.5 |
| 10°-20° | 1070.2 | 5.0 |
| 20°-30° | 1519.7 | 7.1 |
| 30°-40° | 2244.7 | 10.4 |
| 40°-50° | 3237.3 | 15.1 |
| 50°-60° | 4544.6 | 21.1 |
| 60°-70° | 5297.6 | 24.6 |
| 70°-80° | 2708.3 | 12.6 |
| 80°-90° | 345.9 | 1.6 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 21506.0 | 100.0 |
| 0°-180° | 21506.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P364047
 CATALOG NUMBER: NVN-SA5B-750-U-SLR-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 2358.8 | 11.0 | | | |
| FM (30°-60°) | 8847.9 | 41.1 | | | |
| FH (60°-80°) | 7371.5 | 34.3 | | | G3/7500 |
| FVH (80°-90°) | 324.9 | 1.5 | | | G3/500 |
| BL (0°-30°) | 768.8 | 3.6 | B2/1000 | | |
| BM (30°-60°) | 1178.7 | 5.5 | B2/2500 | | |
| BH (60°-80°) | 634.4 | 2.9 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 21.0 | 0.1 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G3
 Type IV Medium





REPORT NUMBER: P364047
 CATALOG NUMBER: NVN-SA5B-750-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 |
| 2.5° | 7670.8 | 7611.7 | 7546.5 | 7333.6 | 7136.0 | 6909.8 | 6725.4 | 6597.0 | 6436.0 | 6227.1 | 6174.2 |
| 5° | 7615.8 | 7552.7 | 7347.9 | 6874.1 | 6459.4 | 6056.0 | 5666.8 | 5438.6 | 5155.3 | 4868.0 | 4796.7 |
| 7.5° | 7062.6 | 6996.4 | 6700.9 | 6051.9 | 5493.6 | 4910.8 | 4405.5 | 4092.7 | 3772.8 | 3509.9 | 3370.3 |
| 10° | 6487.0 | 6414.6 | 6082.5 | 5294.9 | 4607.2 | 4080.5 | 3709.6 | 3411.1 | 3108.5 | 2827.3 | 2603.1 |
| 12.5° | 6090.6 | 5995.9 | 5635.2 | 4742.7 | 4143.6 | 3786.0 | 3439.6 | 3082.0 | 2672.4 | 2370.8 | 2124.3 |
| 15° | 5924.6 | 5816.6 | 5435.5 | 4529.8 | 3979.6 | 3559.8 | 3108.5 | 2669.4 | 2189.5 | 1844.1 | 1617.9 |
| 17.5° | 6052.9 | 5912.3 | 5503.8 | 4515.5 | 3773.8 | 3202.2 | 2631.7 | 2116.1 | 1595.5 | 1246.0 | 1085.1 |
| 20° | 6489.0 | 6304.6 | 5786.0 | 4511.4 | 3524.2 | 2777.4 | 2054.0 | 1471.2 | 1051.4 | 845.6 | 761.1 |
| 22.5° | 7175.7 | 6932.2 | 6191.5 | 4544.0 | 3266.4 | 2331.1 | 1483.4 | 999.5 | 789.6 | 682.6 | 632.7 |
| 25° | 8005.0 | 7722.8 | 6775.3 | 4659.2 | 3040.2 | 1897.1 | 1077.9 | 789.6 | 666.3 | 587.9 | 546.1 |
| 27.5° | 8793.6 | 8564.4 | 7512.9 | 4825.2 | 2865.0 | 1546.6 | 875.2 | 669.4 | 569.5 | 517.6 | 483.9 |
| 30° | 9581.2 | 9292.8 | 8269.9 | 5022.9 | 2654.1 | 1309.2 | 769.2 | 610.3 | 510.4 | 455.4 | 434.0 |
| 32.5° | 10153.8 | 9914.3 | 8862.9 | 5165.5 | 2428.9 | 1154.3 | 687.7 | 558.3 | 476.8 | 420.8 | 389.2 |
| 35° | 10827.2 | 10556.2 | 9371.3 | 5197.1 | 2284.2 | 1056.5 | 618.4 | 502.3 | 413.6 | 363.7 | 330.1 |
| 37.5° | 11554.7 | 11217.4 | 9958.1 | 5127.8 | 2171.1 | 1008.7 | 566.5 | 476.8 | 386.1 | 335.2 | 299.5 |
| 40° | 12359.5 | 11978.5 | 10521.6 | 5028.0 | 2060.1 | 992.3 | 526.7 | 457.5 | 364.7 | 312.8 | 276.1 |
| 42.5° | 13207.2 | 12757.9 | 11009.6 | 4923.0 | 1989.8 | 936.3 | 522.7 | 438.1 | 348.4 | 292.4 | 255.7 |
| 45° | 13919.4 | 13464.0 | 11510.8 | 4888.4 | 1939.9 | 875.2 | 540.0 | 424.9 | 337.2 | 276.1 | 240.4 |
| 47.5° | 14486.9 | 14055.9 | 12024.3 | 4965.8 | 1911.3 | 819.1 | 492.1 | 442.2 | 331.1 | 261.8 | 227.2 |
| 50° | 15164.4 | 14676.4 | 12747.7 | 5197.1 | 1869.6 | 763.1 | 445.2 | 506.4 | 331.1 | 252.7 | 216.0 |
| 52.5° | 16014.1 | 15531.2 | 13554.6 | 5555.7 | 1786.0 | 685.7 | 400.4 | 507.4 | 334.2 | 240.4 | 201.7 |
| 55° | 17082.9 | 16732.4 | 14706.9 | 5949.0 | 1652.6 | 571.6 | 346.4 | 436.1 | 322.0 | 218.0 | 188.5 |
| 57.5° | 18107.8 | 17821.5 | 15757.4 | 6218.0 | 1474.3 | 446.3 | 301.6 | 351.5 | 294.4 | 191.5 | 168.1 |
| 59° | 18388.0 | 18075.2 | 16142.5 | 6230.2 | 1340.8 | 389.2 | 279.2 | 290.4 | 288.3 | 179.3 | 155.9 |
| 60° | 18388.0 | 18055.9 | 16253.5 | 6165.0 | 1244.0 | 357.6 | 264.9 | 258.8 | 300.6 | 171.2 | 148.8 |
| 62.5° | 18054.9 | 17588.2 | 15892.9 | 5723.8 | 1014.8 | 304.6 | 231.3 | 214.0 | 270.0 | 153.8 | 131.4 |
| 65° | 17362.0 | 16682.5 | 14664.2 | 4926.1 | 904.7 | 279.2 | 199.7 | 175.2 | 187.5 | 135.5 | 115.1 |
| 67.5° | 16206.7 | 15285.6 | 12892.4 | 3979.6 | 860.9 | 272.0 | 172.2 | 148.8 | 141.6 | 116.1 | 100.9 |
| 70° | 14172.1 | 13150.2 | 10741.6 | 3128.9 | 823.2 | 269.0 | 144.7 | 125.3 | 114.1 | 97.8 | 85.6 |
| 72.5° | 10314.7 | 9249.0 | 7626.0 | 2446.2 | 800.8 | 275.1 | 116.1 | 104.9 | 93.7 | 76.4 | 66.2 |
| 75° | 5900.1 | 5202.2 | 4286.3 | 1615.9 | 682.6 | 262.9 | 89.7 | 87.6 | 67.2 | 55.0 | 45.8 |
| 77.5° | 3048.4 | 2955.7 | 2568.5 | 620.5 | 327.0 | 115.1 | 59.1 | 50.9 | 39.7 | 33.6 | 27.5 |
| 80° | 1315.3 | 1301.1 | 1125.8 | 179.3 | 86.6 | 64.2 | 33.6 | 21.4 | 18.3 | 14.3 | 11.2 |
| 82.5° | 454.4 | 454.4 | 400.4 | 60.1 | 38.7 | 31.6 | 4.1 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 91.7 | 102.9 | 72.3 | 0.0 | 13.2 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P364047
 CATALOG NUMBER: NVN-SA5B-750-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 |
| 2.5° | 6110.0 | 5986.7 | 5978.5 | 5901.1 | 5804.3 | 5760.5 | 5735.0 | 5779.9 | 5834.9 | 5841.0 | 5923.5 |
| 5° | 4742.7 | 4613.3 | 4667.3 | 4529.8 | 4557.3 | 4529.8 | 4484.9 | 4493.1 | 4517.5 | 4441.1 | 4535.9 |
| 7.5° | 3330.6 | 3232.8 | 3294.9 | 3258.2 | 3307.2 | 3326.5 | 3299.0 | 3258.2 | 3138.0 | 3123.8 | 3206.3 |
| 10° | 2510.4 | 2399.4 | 2333.1 | 2263.9 | 2279.1 | 2310.7 | 2300.5 | 2271.0 | 2194.6 | 2198.7 | 2278.1 |
| 12.5° | 2017.3 | 1893.0 | 1761.6 | 1591.4 | 1549.7 | 1573.1 | 1549.7 | 1532.3 | 1459.0 | 1465.1 | 1535.4 |
| 15° | 1530.3 | 1428.4 | 1290.9 | 1154.3 | 1080.0 | 1087.1 | 1021.9 | 976.0 | 930.2 | 875.2 | 918.0 |
| 17.5° | 1033.1 | 971.0 | 930.2 | 889.4 | 800.8 | 780.4 | 697.9 | 609.3 | 574.6 | 549.2 | 567.5 |
| 20° | 731.5 | 697.9 | 681.6 | 679.6 | 628.6 | 603.2 | 522.7 | 467.6 | 450.3 | 445.2 | 456.4 |
| 22.5° | 611.3 | 586.9 | 563.4 | 550.2 | 524.7 | 495.2 | 434.0 | 406.5 | 394.3 | 388.2 | 396.3 |
| 25° | 531.8 | 513.5 | 489.0 | 466.6 | 456.4 | 424.9 | 381.0 | 360.7 | 352.5 | 346.4 | 350.5 |
| 27.5° | 472.7 | 456.4 | 427.9 | 413.6 | 405.5 | 378.0 | 340.3 | 324.0 | 316.9 | 314.8 | 313.8 |
| 30° | 425.9 | 410.6 | 384.1 | 367.8 | 353.5 | 329.1 | 306.7 | 290.4 | 283.2 | 281.2 | 279.2 |
| 32.5° | 379.0 | 366.8 | 349.5 | 333.2 | 317.9 | 295.5 | 276.1 | 262.9 | 251.7 | 249.6 | 248.6 |
| 35° | 319.9 | 307.7 | 298.5 | 297.5 | 283.2 | 261.8 | 247.6 | 230.3 | 221.1 | 218.0 | 219.1 |
| 37.5° | 284.3 | 268.0 | 247.6 | 254.7 | 250.6 | 235.4 | 216.0 | 198.7 | 189.5 | 187.5 | 187.5 |
| 40° | 261.8 | 244.5 | 221.1 | 208.9 | 221.1 | 218.0 | 187.5 | 170.1 | 161.0 | 160.0 | 157.9 |
| 42.5° | 240.4 | 223.1 | 196.6 | 176.3 | 182.4 | 191.5 | 162.0 | 145.7 | 136.5 | 134.5 | 131.4 |
| 45° | 225.2 | 206.8 | 177.3 | 153.8 | 141.6 | 161.0 | 138.6 | 118.2 | 113.1 | 109.0 | 107.0 |
| 47.5° | 210.9 | 193.6 | 160.0 | 133.5 | 113.1 | 116.1 | 111.1 | 96.8 | 90.7 | 86.6 | 85.6 |
| 50° | 198.7 | 180.3 | 144.7 | 114.1 | 93.7 | 85.6 | 89.7 | 76.4 | 71.3 | 67.2 | 65.2 |
| 52.5° | 184.4 | 167.1 | 128.4 | 98.8 | 78.5 | 67.2 | 68.3 | 60.1 | 55.0 | 52.0 | 50.9 |
| 55° | 173.2 | 155.9 | 115.1 | 86.6 | 69.3 | 55.0 | 48.9 | 46.9 | 43.8 | 41.8 | 40.8 |
| 57.5° | 157.9 | 141.6 | 101.9 | 73.4 | 59.1 | 44.8 | 37.7 | 37.7 | 36.7 | 34.6 | 33.6 |
| 59° | 148.8 | 134.5 | 93.7 | 66.2 | 54.0 | 38.7 | 33.6 | 34.6 | 33.6 | 31.6 | 30.6 |
| 60° | 141.6 | 128.4 | 87.6 | 61.1 | 50.9 | 35.7 | 30.6 | 32.6 | 31.6 | 29.5 | 28.5 |
| 62.5° | 125.3 | 116.1 | 75.4 | 50.9 | 44.8 | 28.5 | 25.5 | 27.5 | 27.5 | 26.5 | 25.5 |
| 65° | 110.0 | 99.8 | 64.2 | 42.8 | 41.8 | 24.5 | 20.4 | 24.5 | 25.5 | 23.4 | 21.4 |
| 67.5° | 95.8 | 85.6 | 56.0 | 34.6 | 38.7 | 19.4 | 15.3 | 20.4 | 27.5 | 21.4 | 19.4 |
| 70° | 81.5 | 71.3 | 43.8 | 27.5 | 40.8 | 13.2 | 12.2 | 18.3 | 32.6 | 23.4 | 18.3 |
| 72.5° | 63.2 | 55.0 | 30.6 | 20.4 | 43.8 | 9.2 | 9.2 | 15.3 | 36.7 | 25.5 | 17.3 |
| 75° | 43.8 | 35.7 | 18.3 | 12.2 | 35.7 | 6.1 | 6.1 | 14.3 | 34.6 | 23.4 | 16.3 |
| 77.5° | 25.5 | 19.4 | 6.1 | 1.0 | 18.3 | 0.0 | 1.0 | 10.2 | 24.5 | 14.3 | 7.1 |
| 80° | 9.2 | 4.1 | 0.0 | 0.0 | 11.2 | 0.0 | 0.0 | 0.0 | 2.0 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P364047
 CATALOG NUMBER: NVN-SA5B-750-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|---------|---------|---------|
| 0° | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 |
| 2.5° | 5944.9 | 6082.5 | 6205.8 | 6392.2 | 6613.3 | 6868.0 | 7087.0 | 7322.4 | 7543.5 | 7635.2 | 7698.4 |
| 5° | 4555.2 | 4725.4 | 4924.1 | 5198.1 | 5562.9 | 6012.2 | 6433.0 | 6908.7 | 7420.2 | 7675.9 | 7916.4 |
| 7.5° | 3220.6 | 3393.8 | 3640.3 | 3931.7 | 4372.9 | 4907.7 | 5457.9 | 6115.1 | 6807.9 | 7212.4 | 7610.7 |
| 10° | 2315.8 | 2528.8 | 2759.0 | 3157.4 | 3605.7 | 4113.1 | 4679.5 | 5413.1 | 6185.4 | 6633.7 | 7113.5 |
| 12.5° | 1576.1 | 1818.6 | 2167.1 | 2613.3 | 3140.1 | 3637.3 | 4129.4 | 4829.3 | 5725.9 | 6170.1 | 6684.6 |
| 15° | 945.5 | 1080.0 | 1448.8 | 1965.3 | 2611.3 | 3230.7 | 3769.7 | 4471.7 | 5427.4 | 5971.4 | 6506.3 |
| 17.5° | 582.8 | 644.9 | 845.6 | 1269.5 | 1948.0 | 2731.5 | 3470.2 | 4350.4 | 5470.1 | 6132.4 | 6705.0 |
| 20° | 464.6 | 489.0 | 553.2 | 749.9 | 1290.9 | 2181.3 | 3132.9 | 4326.0 | 5819.6 | 6634.7 | 7249.0 |
| 22.5° | 403.5 | 426.9 | 469.7 | 545.1 | 812.0 | 1633.2 | 2813.0 | 4348.4 | 6320.9 | 7387.6 | 8104.9 |
| 25° | 355.6 | 376.0 | 416.7 | 478.9 | 595.0 | 1150.3 | 2470.7 | 4448.3 | 6974.0 | 8321.9 | 9084.0 |
| 27.5° | 317.9 | 335.2 | 372.9 | 430.0 | 510.4 | 802.8 | 2082.5 | 4569.5 | 7748.3 | 9277.6 | 10029.5 |
| 30° | 283.2 | 298.5 | 332.1 | 385.1 | 443.2 | 617.4 | 1656.6 | 4652.0 | 8523.6 | 10029.5 | 10704.9 |
| 32.5° | 253.7 | 264.9 | 295.5 | 340.3 | 385.1 | 492.1 | 1259.3 | 4638.8 | 9099.3 | 10655.0 | 11190.9 |
| 35° | 223.1 | 234.3 | 260.8 | 299.5 | 335.2 | 406.5 | 990.3 | 4391.2 | 9600.5 | 11304.0 | 11747.2 |
| 37.5° | 189.5 | 203.8 | 229.2 | 263.9 | 288.3 | 357.6 | 800.8 | 4092.7 | 10108.9 | 12045.7 | 12367.7 |
| 40° | 161.0 | 175.2 | 197.7 | 235.4 | 250.6 | 339.3 | 615.4 | 3729.0 | 10680.5 | 12875.1 | 13048.3 |
| 42.5° | 133.5 | 146.7 | 170.1 | 202.7 | 236.4 | 292.4 | 455.4 | 3313.3 | 11229.6 | 13584.2 | 13668.7 |
| 45° | 108.0 | 121.2 | 145.7 | 178.3 | 252.7 | 242.5 | 352.5 | 2868.0 | 11672.8 | 14174.1 | 14201.6 |
| 47.5° | 85.6 | 97.8 | 123.3 | 168.1 | 235.4 | 193.6 | 251.7 | 2518.6 | 12044.7 | 14634.6 | 14562.3 |
| 50° | 66.2 | 76.4 | 102.9 | 192.6 | 205.8 | 160.0 | 190.5 | 2402.4 | 12377.9 | 14919.9 | 14732.4 |
| 52.5° | 52.0 | 61.1 | 84.6 | 180.3 | 160.0 | 132.4 | 160.0 | 2511.4 | 12834.3 | 15156.3 | 14828.2 |
| 55° | 41.8 | 50.9 | 66.2 | 102.9 | 109.0 | 112.1 | 136.5 | 2613.3 | 13621.9 | 15710.5 | 15393.6 |
| 57.5° | 34.6 | 43.8 | 54.0 | 72.3 | 82.5 | 94.8 | 121.2 | 2624.5 | 14550.0 | 16631.5 | 16332.0 |
| 59° | 31.6 | 39.7 | 48.9 | 64.2 | 72.3 | 86.6 | 114.1 | 2563.4 | 14877.1 | 16966.7 | 16817.0 |
| 60° | 29.5 | 37.7 | 45.8 | 59.1 | 67.2 | 81.5 | 110.0 | 2505.3 | 14891.4 | 16954.5 | 17023.8 |
| 62.5° | 25.5 | 33.6 | 40.8 | 49.9 | 57.1 | 69.3 | 98.8 | 2290.4 | 14288.2 | 16399.2 | 16899.5 |
| 65° | 22.4 | 29.5 | 36.7 | 42.8 | 48.9 | 62.1 | 89.7 | 1898.1 | 13258.2 | 15503.7 | 16048.8 |
| 67.5° | 20.4 | 25.5 | 33.6 | 37.7 | 43.8 | 55.0 | 79.5 | 1353.0 | 11971.4 | 14408.4 | 14762.0 |
| 70° | 18.3 | 24.5 | 30.6 | 34.6 | 39.7 | 47.9 | 68.3 | 777.4 | 10108.9 | 12804.8 | 13056.4 |
| 72.5° | 17.3 | 23.4 | 27.5 | 32.6 | 35.7 | 42.8 | 62.1 | 365.8 | 7401.9 | 10257.7 | 10914.8 |
| 75° | 15.3 | 21.4 | 25.5 | 30.6 | 33.6 | 38.7 | 53.0 | 175.2 | 4923.0 | 7423.3 | 8170.1 |
| 77.5° | 9.2 | 17.3 | 23.4 | 27.5 | 29.5 | 33.6 | 43.8 | 100.9 | 3142.1 | 5138.0 | 6051.9 |
| 80° | 0.0 | 6.1 | 17.3 | 23.4 | 25.5 | 28.5 | 33.6 | 79.5 | 1681.1 | 2935.3 | 3523.1 |
| 82.5° | 0.0 | 0.0 | 12.2 | 18.3 | 17.3 | 19.4 | 25.5 | 49.9 | 758.0 | 1918.5 | 2162.0 |
| 85° | 0.0 | 0.0 | 4.1 | 14.3 | 12.2 | 9.2 | 17.3 | 17.3 | 166.1 | 971.0 | 1211.4 |
| 87.5° | 0.0 | 0.0 | 0.0 | 1.0 | 6.1 | 4.1 | 7.1 | 2.0 | 1.0 | 72.3 | 293.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P364047
 CATALOG NUMBER: NVN-SA5B-750-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 | 7005.5 |
| 2.5° | 7919.4 | 7994.8 | 8122.2 | 8182.3 | 8152.8 | 8027.4 | 7877.7 | 7724.8 | 7635.2 | 7670.8 |
| 5° | 8406.4 | 8794.6 | 9018.8 | 9093.1 | 8968.8 | 8687.6 | 8319.8 | 7834.9 | 7662.7 | 7615.8 |
| 7.5° | 8406.4 | 9137.0 | 9599.5 | 9681.0 | 9403.9 | 8852.7 | 8162.9 | 7405.9 | 7154.3 | 7062.6 |
| 10° | 8111.0 | 9105.4 | 9750.3 | 9879.7 | 9492.5 | 8668.3 | 7744.2 | 6880.2 | 6581.7 | 6487.0 |
| 12.5° | 7777.8 | 8848.6 | 9528.2 | 9706.5 | 9388.6 | 8484.9 | 7453.8 | 6524.6 | 6173.1 | 6090.6 |
| 15° | 7573.0 | 8532.8 | 9095.2 | 9224.6 | 9090.1 | 8377.9 | 7384.5 | 6417.7 | 6004.0 | 5924.6 |
| 17.5° | 7646.4 | 8288.3 | 8491.0 | 8566.4 | 8657.1 | 8340.2 | 7573.0 | 6652.0 | 6128.3 | 6052.9 |
| 20° | 7922.5 | 8030.5 | 7925.6 | 8020.3 | 8264.8 | 8376.9 | 8022.3 | 7218.5 | 6589.9 | 6489.0 |
| 22.5° | 8391.2 | 7897.0 | 7602.6 | 7640.3 | 7937.8 | 8498.1 | 8709.0 | 8027.4 | 7302.0 | 7175.7 |
| 25° | 8937.3 | 8005.0 | 7423.3 | 7389.6 | 7695.3 | 8658.1 | 9336.6 | 8907.7 | 8144.6 | 8005.0 |
| 27.5° | 9624.0 | 8247.5 | 7386.6 | 7353.0 | 7610.7 | 8807.9 | 9858.3 | 9777.8 | 9032.0 | 8793.6 |
| 30° | 10153.8 | 8485.9 | 7495.6 | 7418.2 | 7695.3 | 8911.8 | 10277.0 | 10516.5 | 9739.1 | 9581.2 |
| 32.5° | 10533.8 | 8767.1 | 7672.9 | 7560.8 | 7933.7 | 9091.1 | 10600.0 | 11193.0 | 10393.2 | 10153.8 |
| 35° | 10823.1 | 9072.8 | 7959.2 | 7774.8 | 8261.8 | 9363.1 | 10902.6 | 11913.3 | 11089.0 | 10827.2 |
| 37.5° | 11094.1 | 9501.7 | 8406.4 | 8186.4 | 8776.3 | 9801.2 | 11222.5 | 12730.4 | 11867.4 | 11554.7 |
| 40° | 11472.1 | 9987.7 | 9096.2 | 8900.6 | 9641.3 | 10398.3 | 11621.9 | 13582.1 | 12752.8 | 12359.5 |
| 42.5° | 11850.1 | 10509.3 | 9802.3 | 9855.2 | 10720.2 | 11123.7 | 12137.4 | 14482.8 | 13627.0 | 13207.2 |
| 45° | 12195.5 | 11047.3 | 10807.8 | 11052.4 | 11721.7 | 11919.4 | 12649.9 | 15003.4 | 14324.9 | 13919.4 |
| 47.5° | 12503.2 | 11719.7 | 11807.3 | 12458.4 | 12860.8 | 12639.7 | 13033.0 | 15452.7 | 14844.5 | 14486.9 |
| 50° | 12860.8 | 12589.8 | 13124.7 | 14045.7 | 14172.1 | 13291.8 | 13381.4 | 15984.6 | 15451.7 | 15164.4 |
| 52.5° | 13252.0 | 13506.8 | 14583.7 | 15395.7 | 15354.9 | 13999.9 | 13731.9 | 16580.6 | 16284.1 | 16014.1 |
| 55° | 13696.3 | 14247.4 | 15868.4 | 16659.0 | 16624.4 | 14790.5 | 14312.7 | 17317.2 | 17327.4 | 17082.9 |
| 57.5° | 14355.4 | 14885.2 | 16740.5 | 17680.9 | 17739.0 | 15703.4 | 15296.9 | 18142.5 | 18270.8 | 18107.8 |
| 59° | 14828.2 | 15298.9 | 17085.9 | 18107.8 | 18344.2 | 16409.4 | 16016.2 | 18621.3 | 18536.8 | 18388.0 |
| 60° | 15178.7 | 15561.8 | 17257.1 | 18331.0 | 18695.7 | 16888.3 | 16547.0 | 18902.5 | 18568.3 | 18388.0 |
| 62.5° | 16045.7 | 16134.3 | 17565.8 | 18583.6 | 19100.2 | 17951.9 | 18040.6 | 19381.4 | 18349.3 | 18054.9 |
| 65° | 16450.2 | 16496.0 | 17561.7 | 18131.3 | 18708.9 | 18780.3 | 19395.6 | 19395.6 | 17814.4 | 17362.0 |
| 67.5° | 16281.1 | 16060.0 | 16690.6 | 16631.5 | 17208.2 | 18288.2 | 19905.1 | 18684.5 | 16791.5 | 16206.7 |
| 70° | 14905.6 | 14054.9 | 13774.7 | 13800.2 | 14241.3 | 15907.1 | 18896.4 | 16591.8 | 14855.7 | 14172.1 |
| 72.5° | 12402.3 | 10361.6 | 9669.8 | 10459.4 | 10574.5 | 12225.1 | 16103.8 | 12495.0 | 10955.6 | 10314.7 |
| 75° | 9975.5 | 7304.1 | 6179.3 | 7012.7 | 7208.3 | 8946.4 | 12457.3 | 7781.9 | 6399.3 | 5900.1 |
| 77.5° | 7166.5 | 5242.9 | 4434.0 | 4375.9 | 4628.6 | 5673.9 | 8839.5 | 3916.4 | 3266.4 | 3048.4 |
| 80° | 4071.3 | 3450.8 | 3715.7 | 3505.8 | 3633.2 | 3547.6 | 4199.7 | 1717.8 | 1407.0 | 1315.3 |
| 82.5° | 2457.4 | 2039.7 | 2208.8 | 1839.0 | 2327.0 | 2026.5 | 1617.9 | 550.2 | 477.8 | 454.4 |
| 85° | 1598.6 | 1114.6 | 580.7 | 389.2 | 801.8 | 1294.9 | 361.7 | 149.8 | 115.1 | 91.7 |
| 87.5° | 551.2 | 284.3 | 28.5 | 12.2 | 85.6 | 241.5 | 13.2 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-4-R4

Test Date: 10/02/2019

Luminaire Tested: SA1C-750-U-5WQ

Data in this report applies to families of products SA1C-760-U-5WQ .

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-4-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-750-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K): | 4884 | CRI (Ra): | 73.5 | R9: | -28.4 |
| CIE u': | 0.2101 | R1: | 70.5 | R10: | 48.6 |
| CIE v': | 0.4904 | R2: | 77.7 | R11: | 73.2 |
| Duv: | 0.0037 | R3: | 84.6 | R12: | 50.7 |
| CIE x: | 0.3493 | R4: | 74.7 | R13: | 71.2 |
| CIE y: | 0.3624 | R5: | 71.9 | R14: | 91.4 |
| CIE z: | 0.2884 | R6: | 70.7 | | |
| Peak Wavelength (nm): | 444 | R7: | 81.2 | | |
| Dominant Wavelength (nm): | 571 | R8: | 56.9 | | |
| Purity: | 13.7 | | | | |
| Rf: | 74.9 | | | | |
| Rg: | 96.3 | | | | |



Test Conditions

Stabilization Time: 240M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0./44%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-4-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-4-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-4-R4

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 13493.5 S/P: 1.77

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5378.9 M/P: 0.71

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2945 | NR | 490 | 37941 | NR | 620 | 88803 | NR | 750 | 3908 | NR | 880 | 2997 | NR |
| 365 | 2596 | NR | 495 | 48525 | NR | 625 | 80578 | NR | 755 | 3988 | NR | 885 | 2927 | NR |
| 370 | 2732 | NR | 500 | 60609 | NR | 630 | 73127 | NR | 760 | 3335 | NR | 890 | 2649 | NR |
| 375 | 2894 | NR | 505 | 72036 | NR | 635 | 66244 | NR | 765 | 3438 | NR | 895 | 2828 | NR |
| 380 | 2822 | NR | 510 | 82168 | NR | 640 | 59440 | NR | 770 | 3427 | NR | 900 | 1407 | NR |
| 385 | 2394 | NR | 515 | 90898 | NR | 645 | 52864 | NR | 775 | 2759 | NR | 905 | 2224 | NR |
| 390 | 2370 | NR | 520 | 97142 | NR | 650 | 47085 | NR | 780 | 2340 | NR | 910 | 2905 | NR |
| 395 | 2267 | NR | 525 | 103255 | NR | 655 | 41789 | NR | 785 | 2412 | NR | 915 | 3350 | NR |
| 400 | 2262 | NR | 530 | 106697 | NR | 660 | 37064 | NR | 790 | 1999 | NR | 920 | 3114 | NR |
| 405 | 3000 | NR | 535 | 110081 | NR | 665 | 32299 | NR | 795 | 2054 | NR | 925 | 2834 | NR |
| 410 | 5324 | NR | 540 | 112494 | NR | 670 | 28142 | NR | 800 | 2331 | NR | 930 | 2271 | NR |
| 415 | 10725 | NR | 545 | 115513 | NR | 675 | 24505 | NR | 805 | 2648 | NR | 935 | 2228 | NR |
| 420 | 22128 | NR | 550 | 117203 | NR | 680 | 21162 | NR | 810 | 2485 | NR | 940 | 2833 | NR |
| 425 | 44095 | NR | 555 | 119753 | NR | 685 | 18400 | NR | 815 | 2409 | NR | 945 | 2941 | NR |
| 430 | 77002 | NR | 560 | 122602 | NR | 690 | 16065 | NR | 820 | 2221 | NR | 950 | 2323 | NR |
| 435 | 119881 | NR | 565 | 124314 | NR | 695 | 13860 | NR | 825 | 1562 | NR | 955 | 1667 | NR |
| 440 | 164454 | NR | 570 | 126775 | NR | 700 | 12177 | NR | 830 | 2249 | NR | 960 | 749 | NR |
| 445 | 179997 | NR | 575 | 127511 | NR | 705 | 10757 | NR | 835 | 2573 | NR | 965 | 2669 | NR |
| 450 | 142822 | NR | 580 | 127577 | NR | 710 | 9601 | NR | 840 | 2764 | NR | 970 | 3968 | NR |
| 455 | 90008 | NR | 585 | 126153 | NR | 715 | 8944 | NR | 845 | 3109 | NR | 975 | 3886 | NR |
| 460 | 60557 | NR | 590 | 123678 | NR | 720 | 7947 | NR | 850 | 2963 | NR | 980 | 2788 | NR |
| 465 | 43305 | NR | 595 | 119774 | NR | 725 | 7062 | NR | 855 | 2336 | NR | 985 | 3496 | NR |
| 470 | 31089 | NR | 600 | 115733 | NR | 730 | 6004 | NR | 860 | 2118 | NR | 990 | 2913 | NR |
| 475 | 26278 | NR | 605 | 109231 | NR | 735 | 5594 | NR | 865 | 3144 | NR | 995 | 4659 | NR |
| 480 | 27060 | NR | 610 | 102408 | NR | 740 | 5165 | NR | 870 | 3069 | NR | 1000 | 1308 | NR |
| 485 | 30698 | NR | 615 | 96015 | NR | 745 | 4687 | NR | 875 | 3311 | NR | | | |

REPORT NUMBER: SP1-1908-441-4-R4


TM-30-18

Summary

$R_f = 74.9$
 $R_g = 96.3$
 CIE $R_a = 73.5$
 $R_g = -28.4$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 61 | CES51 = 90 | CES76 = 52 |
| CES02 = 60 | CES27 = 84 | CES52 = 91 | CES77 = 71 |
| CES03 = 30 | CES28 = 81 | CES53 = 79 | CES78 = 54 |
| CES04 = 69 | CES29 = 58 | CES54 = 83 | CES79 = 80 |
| CES05 = 46 | CES30 = 67 | CES55 = 83 | CES80 = 77 |
| CES06 = 50 | CES31 = 63 | CES56 = 73 | CES81 = 77 |
| CES07 = 39 | CES32 = 59 | CES57 = 72 | CES82 = 90 |
| CES08 = 38 | CES33 = 69 | CES58 = 73 | CES83 = 86 |
| CES09 = 29 | CES34 = 69 | CES59 = 88 | CES84 = 88 |
| CES10 = 73 | CES35 = 83 | CES60 = 93 | CES85 = 84 |
| CES11 = 56 | CES36 = 95 | CES61 = 88 | CES86 = 75 |
| CES12 = 61 | CES37 = 78 | CES62 = 85 | CES87 = 78 |
| CES13 = 41 | CES38 = 76 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 93 | CES64 = 74 | CES89 = 75 |
| CES15 = 70 | CES40 = 86 | CES65 = 67 | CES90 = 77 |
| CES16 = 46 | CES41 = 87 | CES66 = 69 | CES91 = 89 |
| CES17 = 49 | CES42 = 78 | CES67 = 67 | CES92 = 66 |
| CES18 = 55 | CES43 = 75 | CES68 = 73 | CES93 = 80 |
| CES19 = 71 | CES44 = 99 | CES69 = 81 | CES94 = 57 |
| CES20 = 64 | CES45 = 83 | CES70 = 63 | CES95 = 71 |
| CES21 = 85 | CES46 = 81 | CES71 = 60 | CES96 = 78 |
| CES22 = 77 | CES47 = 80 | CES72 = 86 | CES97 = 85 |
| CES23 = 91 | CES48 = 72 | CES73 = 53 | CES98 = 75 |
| CES24 = 90 | CES49 = 81 | CES74 = 96 | CES99 = 62 |
| CES25 = 71 | CES50 = 89 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-4-R4

TM-30-18

Measure Comparisons



(END OF REPORT)