

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P256594

Luminaire Tested: **CST-10-3-D-U-T5R-7030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P256594
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1808-894-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: CST-10-3-D-U-T5R-7030
Description: CELESTEON HIGH MAST LUMINAIRE
(10) 70 CRI, 3000K LEDS AND TYPE V ROUND OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 33157 lumens
Efficiency: N/A
Efficacy: 156.4 lumens/watt
Luminous Opening: Circular (Dia: 2.08' x H: 0')
IES Classification: Type V - Short - Full Cutoff
BUG Rating: B5 - U0 - G4

Input Watts (W): 212
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P256594

CATALOG NUMBER: CST-10-3-D-U-T5R-7030

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd
 - - - 1/2 Max cd




Based on 30 foot mounting height. Maximum calculated value = 2.4 fc
 Type V - Short - Full Cutoff

REPORT NUMBER: P256594

CATALOG NUMBER: CST-10-3-D-U-T5R-7030

Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P256594

CATALOG NUMBER: CST-10-3-D-U-T5R-7030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	16578.5	0.0	16578.5
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	16578.5	0.0	16578.5
	% Fixture	50.0	0.0	50.0
Total	Lumens	33157.0	0.0	33157.0
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.2	0.6
10°-20°	667.2	2.0
20°-30°	1290.7	3.9
30°-40°	2251.5	6.8
40°-50°	3996.6	12.1
50°-60°	6883.5	20.8
60°-70°	10222.8	30.8
70°-80°	7173.9	21.6
80°-90°	462.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	33157.0	100.0
0°-180°	33157.0	100.0



REPORT NUMBER: P256594


CATALOG NUMBER: CST-10-3-D-U-T5R-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1083.0	3.3			
FM	(30°-60°)	6565.8	19.8			
FH	(60°-80°)	8698.3	26.2			G4/12000
FVH	(80°-90°)	231.4	0.7			G3/500
BL	(0°-30°)	1083.0	3.3	B3/2500		
BM	(30°-60°)	6565.8	19.8	B4/8500		
BH	(60°-80°)	8698.3	26.2	B5		G4/12000
BVH	(80°-90°)	231.4	0.7			G3/500
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B5-U0-G4

Type V Short





REPORT NUMBER: P256594

CATALOG NUMBER: CST-10-3-D-U-T5R-7030

CANDELA DISTRIBUTION (FULL):

0°	
0°	2162.8
2.5°	2165.7
5°	2167.7
7.5°	2179.6
10°	2209.2
12.5°	2255.6
15°	2322.7
17.5°	2411.5
20°	2515.2
22.5°	2631.7
25°	2761.0
27.5°	2904.1
30°	3070.0
32.5°	3273.3
35°	3526.0
37.5°	3829.0
40°	4173.6
42.5°	4596.0
45°	5088.6
47.5°	5634.5
50°	6246.5
52.5°	6922.7
55°	7633.4
57.5°	8359.9
60°	9083.5
62.5°	9792.3
65°	10609.6
67.5°	11061.7
70°	10289.8
72.5°	8886.1
75°	7115.2
77.5°	4975.1
80°	2237.8
82.5°	407.7
85°	124.4
87.5°	54.3
90°	0.0

(END OF REPORT)