

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P256612

Luminaire Tested: **CST-10-4-D-U-T5R-7050**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P256612
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1808-894-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: CST-10-4-D-U-T5R-7050
Description: CELESTEON HIGH MAST LUMINAIRE
(10) 70 CRI, 5000K LEDS AND TYPE V ROUND OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 46803 lumens
Efficiency: N/A
Efficacy: 152.0 lumens/watt
Luminous Opening: Circular (Dia: 2.08' x H: 0')
IES Classification: Type V - Short - Full Cutoff
BUG Rating: B5 - U0 - G5


Input Watts (W): 308
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P256612
 CATALOG NUMBER: CST-10-4-D-U-T5R-7050

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 30 foot mounting height. Maximum calculated value = 3.4 fc
 Type V - Short - Full Cutoff

REPORT NUMBER: P256612

CATALOG NUMBER: CST-10-4-D-U-T5R-7050

Luminous Intensity Polar Plot



— Vertical Plane Through 0-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P256612

CATALOG NUMBER: CST-10-4-D-U-T5R-7050


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	23401.5	0.0	23401.5
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	23401.5	0.0	23401.5
	% Fixture	50.0	0.0	50.0
Total	Lumens	46803.0	0.0	46803.0
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.8	0.6
10°-20°	941.8	2.0
20°-30°	1821.9	3.9
30°-40°	3178.1	6.8
40°-50°	5641.4	12.1
50°-60°	9716.4	20.8
60°-70°	14430.1	30.8
70°-80°	10126.3	21.6
80°-90°	653.2	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	46803.0	100.0
0°-180°	46803.0	100.0



REPORT NUMBER: P256612


CATALOG NUMBER: CST-10-4-D-U-T5R-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1528.7	3.3			
FM	(30°-60°)	9268.0	19.8			
FH	(60°-80°)	12278.2	26.2			G5
FVH	(80°-90°)	326.6	0.7			G3/500
BL	(0°-30°)	1528.7	3.3	B3/2500		
BM	(30°-60°)	9268.0	19.8	B5		
BH	(60°-80°)	12278.2	26.2	B5		G5
BVH	(80°-90°)	326.6	0.7			G3/500
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B5-U0-G5

Type V Short





REPORT NUMBER: P256612

CATALOG NUMBER: CST-10-4-D-U-T5R-7050

CANDELA DISTRIBUTION (FULL):

0°	
0°	3052.9
2.5°	3057.1
5°	3059.9
7.5°	3076.6
10°	3118.4
12.5°	3183.9
15°	3278.6
17.5°	3404.0
20°	3550.3
22.5°	3714.8
25°	3897.3
27.5°	4099.3
30°	4333.4
32.5°	4620.4
35°	4977.2
37.5°	5404.9
40°	5891.2
42.5°	6487.6
45°	7182.9
47.5°	7953.4
50°	8817.3
52.5°	9771.8
55°	10775.0
57.5°	11800.5
60°	12821.9
62.5°	13822.3
65°	14976.1
67.5°	15614.2
70°	14524.6
72.5°	12543.2
75°	10043.5
77.5°	7022.6
80°	3158.8
82.5°	575.5
85°	175.6
87.5°	76.6
90°	0.0

(END OF REPORT)