

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P363450

Luminaire Tested: NVN-SA2C-727-U-SL2-HSS

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-2019  
Report Number: P363450  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: STREETWORKS  
Catalog Number: NVN-SA2C-727-U-SL2-HSS  
Description: NAVION ROADWAY AND AREA LUMINAIRE  
(2) 70 CRI, 2700K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II  
SPILL LIGHT ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9874 lumens  
Efficiency: N/A  
Efficacy: 87.4 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')  
IES Classification: Type III - Medium  
BUG Rating: B1 - U0 - G2


Input Watts (W): 113  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P363450  
 CATALOG NUMBER: NVN-SA2C-727-U-SL2-HSS

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 25 fc  
 Type III - Medium - N/A

REPORT NUMBER: P363450  
CATALOG NUMBER: NVN-SA2C-727-U-SL2-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 65-Deg Lateral      - - - Horizontal Cone Through 69-Deg Vertical

REPORT NUMBER: P363450  
 CATALOG NUMBER: NVN-SA2C-727-U-SL2-HSS


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 1163.9   | 0.0    | 1163.9 |
|                    | % Fixture | 11.8     | 0.0    | 11.8   |
| <b>Street Side</b> | Lumens    | 8710.1   | 0.0    | 8710.1 |
|                    | % Fixture | 88.2     | 0.0    | 88.2   |
| <b>Total</b>       | Lumens    | 9874.0   | 0.0    | 9874.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 208.6  | 2.1       |
| 10°-20°   | 456.7  | 4.6       |
| 20°-30°   | 632.6  | 6.4       |
| 30°-40°   | 882.0  | 8.9       |
| 40°-50°   | 1371.0 | 13.9      |
| 50°-60°   | 2201.0 | 22.3      |
| 60°-70°   | 2489.7 | 25.2      |
| 70°-80°   | 1462.2 | 14.8      |
| 80°-90°   | 170.1  | 1.7       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 9874.0 | 100.0     |
| 0°-180°   | 9874.0 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P363450  
 CATALOG NUMBER: NVN-SA2C-727-U-SL2-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|----------------|--------|-----------|-------------------------|------|---------|
|                |        |           | B                       | U    | G       |
| FL (0°-30°)    | 899.8  | 9.1       |                         |      |         |
| FM (30°-60°)   | 4032.3 | 40.8      |                         |      |         |
| FH (60°-80°)   | 3611.8 | 36.6      |                         |      | G2/5000 |
| FVH (80°-90°)  | 166.3  | 1.7       |                         |      | G2/225  |
| BL (0°-30°)    | 398.2  | 4.0       | B1/500                  |      |         |
| BM (30°-60°)   | 421.8  | 4.3       | B1/1000                 |      |         |
| BH (60°-80°)   | 340.1  | 3.4       | B1/500                  |      | G1/500  |
| BVH (80°-90°)  | 3.8    | 0.0       |                         |      | G0/10   |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G2**  
 Type III Medium





REPORT NUMBER: P363450  
 CATALOG NUMBER: NVN-SA2C-727-U-SL2-HSS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 64°     | 65°     | 75°    | 85°    |
|-------|--------|--------|--------|--------|--------|--------|--------|---------|---------|--------|--------|
| 0°    | 2495.2 | 2495.2 | 2495.2 | 2495.2 | 2495.2 | 2495.2 | 2495.2 | 2495.2  | 2495.2  | 2495.2 | 2495.2 |
| 2.5°  | 2517.3 | 2511.1 | 2516.1 | 2526.9 | 2532.4 | 2532.4 | 2536.5 | 2531.5  | 2533.2  | 2521.1 | 2503.5 |
| 5°    | 2359.8 | 2350.2 | 2364.0 | 2394.5 | 2432.1 | 2464.3 | 2511.9 | 2537.0  | 2539.5  | 2539.9 | 2519.4 |
| 7.5°  | 2190.2 | 2181.4 | 2201.9 | 2237.8 | 2286.3 | 2346.0 | 2429.2 | 2501.9  | 2506.0  | 2545.3 | 2530.3 |
| 10°   | 2052.3 | 2046.0 | 2069.8 | 2108.3 | 2165.1 | 2232.0 | 2333.9 | 2435.0  | 2447.1  | 2534.0 | 2528.6 |
| 12.5° | 1942.8 | 1937.8 | 1960.4 | 2004.7 | 2062.7 | 2136.7 | 2243.2 | 2360.6  | 2376.9  | 2508.5 | 2520.2 |
| 15°   | 1863.0 | 1862.2 | 1881.0 | 1923.6 | 1988.0 | 2056.9 | 2165.9 | 2291.7  | 2310.5  | 2481.0 | 2519.0 |
| 17.5° | 1821.2 | 1822.5 | 1836.3 | 1872.6 | 1927.8 | 1996.3 | 2100.8 | 2233.6  | 2254.1  | 2456.3 | 2525.3 |
| 20°   | 1817.1 | 1818.3 | 1825.8 | 1846.3 | 1891.0 | 1951.6 | 2047.7 | 2184.7  | 2206.1  | 2437.9 | 2535.3 |
| 22.5° | 1853.8 | 1853.0 | 1855.1 | 1853.0 | 1878.1 | 1924.0 | 2012.6 | 2147.1  | 2171.8  | 2425.8 | 2543.2 |
| 25°   | 1924.4 | 1923.2 | 1922.4 | 1906.9 | 1890.2 | 1914.8 | 1998.0 | 2125.8  | 2149.2  | 2417.0 | 2547.8 |
| 27.5° | 2022.6 | 2021.8 | 2020.5 | 1995.1 | 1944.9 | 1929.5 | 1999.7 | 2117.9  | 2137.5  | 2409.9 | 2547.0 |
| 30°   | 2151.7 | 2157.6 | 2155.9 | 2120.4 | 2042.3 | 1974.2 | 2017.2 | 2113.7  | 2130.8  | 2396.2 | 2538.2 |
| 32.5° | 2303.4 | 2315.1 | 2324.3 | 2286.3 | 2188.5 | 2062.7 | 2057.7 | 2118.3  | 2130.8  | 2385.7 | 2522.3 |
| 35°   | 2460.9 | 2476.0 | 2509.8 | 2496.4 | 2367.7 | 2196.0 | 2127.5 | 2145.9  | 2156.3  | 2391.6 | 2514.8 |
| 37.5° | 2615.9 | 2633.9 | 2707.4 | 2746.3 | 2602.6 | 2372.3 | 2236.1 | 2214.0  | 2219.4  | 2427.1 | 2523.2 |
| 40°   | 2796.0 | 2823.2 | 2934.7 | 2997.4 | 2882.9 | 2608.4 | 2398.7 | 2331.0  | 2333.1  | 2505.2 | 2562.0 |
| 42.5° | 3032.5 | 3060.5 | 3181.2 | 3279.4 | 3198.8 | 2906.7 | 2619.3 | 2509.8  | 2507.7  | 2651.4 | 2653.5 |
| 45°   | 3320.8 | 3350.0 | 3474.9 | 3584.0 | 3547.6 | 3260.2 | 2901.7 | 2770.9  | 2768.4  | 2882.1 | 2826.9 |
| 47.5° | 3647.5 | 3676.3 | 3787.9 | 3900.3 | 3939.6 | 3673.0 | 3261.4 | 3127.3  | 3121.5  | 3202.5 | 3094.7 |
| 50°   | 3927.9 | 3946.7 | 4049.4 | 4200.7 | 4377.8 | 4180.2 | 3708.9 | 3579.8  | 3573.6  | 3628.3 | 3487.9 |
| 52.5° | 4029.8 | 4040.7 | 4145.1 | 4357.0 | 4799.0 | 4867.1 | 4296.8 | 4130.5  | 4125.9  | 4149.7 | 4011.4 |
| 55°   | 3823.4 | 3843.0 | 3971.3 | 4285.5 | 5027.1 | 5643.4 | 5038.8 | 4812.4  | 4777.7  | 4726.3 | 4558.8 |
| 57.5° | 3261.0 | 3292.4 | 3430.2 | 3848.1 | 4920.6 | 6259.3 | 6129.3 | 5583.6  | 5532.7  | 5218.5 | 5003.7 |
| 60°   | 2443.4 | 2481.8 | 2596.3 | 3047.1 | 4351.9 | 6478.6 | 7320.9 | 6443.1  | 6328.2  | 5610.4 | 5412.8 |
| 62.5° | 1676.7 | 1695.9 | 1773.6 | 2067.3 | 3205.0 | 6119.3 | 8317.8 | 7594.2  | 7384.4  | 6036.6 | 5855.2 |
| 65°   | 1280.6 | 1287.3 | 1319.0 | 1420.1 | 1908.6 | 4970.7 | 8714.3 | 9112.9  | 8859.3  | 6546.3 | 6314.4 |
| 67.5° | 1032.0 | 1026.6 | 1070.4 | 1215.0 | 1278.1 | 3032.5 | 8251.8 | 10549.8 | 10431.1 | 7227.7 | 6776.5 |
| 69°   | 910.0  | 902.5  | 947.2  | 1115.1 | 1200.4 | 2004.7 | 7376.9 | 10876.1 | 10883.6 | 7587.5 | 6808.3 |
| 70°   | 818.9  | 823.9  | 868.2  | 1055.8 | 1174.1 | 1573.5 | 6541.3 | 10792.9 | 10852.3 | 7722.0 | 6617.7 |
| 72.5° | 546.9  | 560.3  | 649.3  | 876.6  | 1128.9 | 1190.8 | 3949.6 | 9261.7  | 9489.8  | 7419.1 | 5677.7 |
| 75°   | 308.3  | 318.4  | 424.1  | 661.0  | 1063.8 | 1133.9 | 2086.1 | 6823.3  | 7043.9  | 6204.1 | 4378.3 |
| 77.5° | 151.2  | 156.7  | 239.8  | 426.6  | 889.5  | 1080.5 | 1183.2 | 4634.8  | 4886.7  | 4049.4 | 2476.4 |
| 80°   | 63.9   | 66.9   | 119.9  | 263.2  | 635.9  | 1031.2 | 878.7  | 2852.4  | 2883.7  | 1586.4 | 659.7  |
| 82.5° | 24.7   | 25.5   | 50.6   | 164.2  | 404.0  | 803.9  | 734.9  | 1352.5  | 1319.9  | 298.7  | 150.4  |
| 85°   | 2.9    | 3.3    | 18.4   | 98.6   | 224.8  | 413.6  | 597.1  | 582.8   | 539.4   | 59.3   | 77.3   |
| 87.5° | 0.0    | 0.0    | 1.3    | 30.1   | 66.9   | 193.9  | 310.4  | 241.9   | 218.1   | 19.2   | 40.1   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0    | 0.0    |



REPORT NUMBER: P363450  
 CATALOG NUMBER: NVN-SA2C-727-U-SL2-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 2495.2 | 2495.2 | 2495.2 | 2495.2 | 2495.2 | 2495.2 | 2495.2 | 2495.2 | 2495.2 | 2495.2 | 2495.2 |
| 2.5°  | 2488.9 | 2484.7 | 2462.2 | 2429.6 | 2398.7 | 2360.2 | 2323.5 | 2301.3 | 2283.8 | 2272.1 | 2285.9 |
| 5°    | 2495.6 | 2477.2 | 2408.7 | 2320.9 | 2234.9 | 2137.9 | 2047.7 | 1971.2 | 1941.2 | 1907.7 | 1922.8 |
| 7.5°  | 2493.5 | 2458.8 | 2335.6 | 2179.3 | 2021.4 | 1858.0 | 1703.4 | 1584.3 | 1522.5 | 1461.9 | 1477.4 |
| 10°   | 2483.1 | 2424.6 | 2237.8 | 2006.3 | 1769.9 | 1535.0 | 1315.7 | 1149.0 | 1055.8 | 971.4  | 983.5  |
| 12.5° | 2460.1 | 2378.6 | 2122.5 | 1808.3 | 1492.0 | 1182.4 | 925.5  | 712.0  | 597.5  | 546.9  | 553.2  |
| 15°   | 2446.3 | 2333.9 | 2000.5 | 1607.7 | 1195.4 | 823.5  | 565.7  | 420.7  | 368.5  | 351.8  | 353.9  |
| 17.5° | 2439.6 | 2290.9 | 1874.3 | 1378.4 | 892.0  | 524.4  | 365.6  | 322.6  | 311.3  | 308.3  | 309.2  |
| 20°   | 2432.9 | 2247.4 | 1744.4 | 1151.5 | 614.6  | 352.6  | 300.4  | 287.9  | 283.7  | 279.9  | 280.8  |
| 22.5° | 2421.6 | 2205.6 | 1604.8 | 921.7  | 414.5  | 286.2  | 270.7  | 258.6  | 249.9  | 245.3  | 246.1  |
| 25°   | 2407.9 | 2161.8 | 1462.3 | 686.5  | 302.5  | 255.3  | 240.7  | 223.5  | 213.1  | 204.7  | 205.1  |
| 27.5° | 2385.7 | 2107.9 | 1315.3 | 499.7  | 254.0  | 228.5  | 208.9  | 190.1  | 172.6  | 162.9  | 162.9  |
| 30°   | 2354.8 | 2046.9 | 1151.9 | 357.6  | 227.7  | 202.2  | 178.4  | 155.0  | 136.2  | 127.4  | 126.6  |
| 32.5° | 2320.5 | 1983.4 | 986.9  | 271.2  | 206.8  | 177.6  | 150.4  | 125.8  | 109.0  | 101.9  | 101.5  |
| 35°   | 2291.3 | 1914.8 | 822.3  | 227.3  | 185.9  | 153.8  | 124.1  | 103.2  | 89.8   | 84.0   | 83.6   |
| 37.5° | 2272.5 | 1846.3 | 661.8  | 203.1  | 167.1  | 131.6  | 104.0  | 85.2   | 75.6   | 71.0   | 70.6   |
| 40°   | 2269.6 | 1795.3 | 515.2  | 184.7  | 149.6  | 112.0  | 86.9   | 72.3   | 63.5   | 58.5   | 58.1   |
| 42.5° | 2307.6 | 1766.1 | 395.3  | 169.2  | 131.6  | 94.8   | 74.0   | 61.8   | 52.6   | 47.6   | 47.2   |
| 45°   | 2407.4 | 1775.3 | 304.2  | 155.4  | 113.6  | 80.2   | 62.7   | 51.4   | 43.0   | 39.3   | 38.4   |
| 47.5° | 2589.6 | 1838.8 | 241.9  | 141.6  | 96.5   | 68.1   | 53.5   | 42.6   | 35.5   | 31.8   | 31.3   |
| 50°   | 2913.8 | 1988.0 | 202.2  | 126.6  | 80.6   | 58.1   | 44.3   | 34.7   | 28.8   | 25.5   | 25.1   |
| 52.5° | 3344.2 | 2253.7 | 180.5  | 112.0  | 66.9   | 49.3   | 36.3   | 27.6   | 22.6   | 20.1   | 19.6   |
| 55°   | 3818.8 | 2575.4 | 166.3  | 96.1   | 54.7   | 40.9   | 28.8   | 21.7   | 17.5   | 15.5   | 14.6   |
| 57.5° | 4282.2 | 2854.1 | 152.9  | 80.6   | 45.5   | 33.4   | 23.0   | 17.1   | 13.8   | 11.7   | 11.3   |
| 60°   | 4707.9 | 3110.2 | 137.5  | 64.8   | 37.2   | 26.3   | 18.0   | 13.4   | 10.9   | 8.8    | 8.8    |
| 62.5° | 5163.7 | 3308.2 | 116.2  | 50.6   | 30.5   | 20.1   | 14.6   | 12.1   | 8.8    | 7.5    | 7.1    |
| 65°   | 5646.7 | 3455.3 | 91.1   | 39.3   | 23.8   | 15.0   | 12.1   | 12.5   | 7.1    | 5.4    | 5.0    |
| 67.5° | 6003.5 | 3426.1 | 67.3   | 30.9   | 18.4   | 11.7   | 11.7   | 13.4   | 6.3    | 4.2    | 3.8    |
| 69°   | 5925.0 | 3188.3 | 56.4   | 26.7   | 15.9   | 10.0   | 10.9   | 13.4   | 5.8    | 3.8    | 3.3    |
| 70°   | 5697.3 | 2925.1 | 49.7   | 23.8   | 14.2   | 9.2    | 10.4   | 13.0   | 5.4    | 3.8    | 3.3    |
| 72.5° | 4744.7 | 2203.1 | 38.9   | 18.0   | 11.3   | 7.5    | 8.8    | 11.3   | 5.4    | 3.8    | 2.9    |
| 75°   | 3569.0 | 1410.1 | 29.7   | 13.0   | 8.4    | 5.8    | 6.7    | 8.4    | 5.4    | 3.3    | 2.9    |
| 77.5° | 1942.0 | 508.5  | 21.3   | 8.8    | 5.8    | 4.6    | 4.6    | 6.3    | 5.0    | 2.5    | 1.7    |
| 80°   | 499.3  | 127.9  | 13.4   | 5.8    | 4.6    | 3.3    | 2.9    | 4.2    | 2.9    | 0.4    | 0.0    |
| 82.5° | 123.3  | 28.8   | 7.1    | 4.2    | 3.3    | 1.3    | 1.3    | 2.1    | 1.3    | 0.0    | 0.0    |
| 85°   | 67.7   | 14.2   | 4.6    | 2.9    | 1.7    | 0.0    | 0.0    | 0.4    | 0.0    | 0.0    | 0.0    |
| 87.5° | 34.7   | 4.2    | 1.3    | 0.8    | 0.4    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

**Test Information**

Test Method: LM-79-2008  
 Report Number: SP1-1908-441-1-R4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/28/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGRAW-EDISON  
 Catalog Number: **SA1C-727-U-5WQ**  
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

\*\*\*THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.\*\*\*TESTED IN  
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

**Spectral Parameters**

CCT (K): 2741  
 CIE u': 0.2605  
 CIE v': 0.5272  
 Duv: 0.0005  
 CIE x: 0.4573  
 CIE y: 0.4113  
 CIE z: 0.1313  
 Peak Wavelength (nm): 602  
 Dominant Wavelength (nm): 583  
 Purity: 61.2

|           |      |      |       |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 |      |       |
| R1:       | 69.2 | R9:  | -16.1 |
| R2:       | 79.4 | R10: | 51.4  |
| R3:       | 87.8 | R11: | 63.1  |
| R4:       | 69.4 | R12: | 42.0  |
| R5:       | 66.4 | R13: | 70.2  |
| R6:       | 69.8 | R14: | 92.4  |
| R7:       | 79.8 |      |       |
| R8:       | 50.1 |      |       |

Rf: 69.9  
 Rg: 98.3



**Test Conditions**

Stabilization Time: 56M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.3./42%  
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/28/2019        | 12/28/2019           |
| Power Meter                    | IN0071                | 12/5/2018        | 12/5/2019            |
| AC Power Source                | IN0063                | 12/5/2018        | 12/5/2019            |
| DC Power Source                | IN0208                | 12/5/2018        | 12/5/2019            |
| Sphere Thermometer             | IN0085                | 12/5/2018        | 12/5/2019            |
| Room Thermometer               | IN0046                | 12/5/2018        | 12/5/2019            |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

**Photopic Flux vs. Wavelength**



**Photopic Lumens: 6211.7**

| $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360            | 2044                              | 0.0                         | 490            | 7179                              | 1.0                         | 620            | 118034                            | 30.7                        | 750            | 8362                              | 0.0                         | 880            | 3128                              | 0.0                         |
| 365            | 2016                              | 0.0                         | 495            | 10476                             | 1.9                         | 625            | 111884                            | 24.7                        | 755            | 7635                              | 0.0                         | 885            | 3110                              | 0.0                         |
| 370            | 2020                              | 0.0                         | 500            | 15549                             | 3.4                         | 630            | 106119                            | 19.2                        | 760            | 6582                              | 0.0                         | 890            | 2632                              | 0.0                         |
| 375            | 2137                              | 0.0                         | 505            | 22477                             | 6.3                         | 635            | 99706                             | 15.0                        | 765            | 5777                              | 0.0                         | 895            | 2709                              | 0.0                         |
| 380            | 2046                              | 0.0                         | 510            | 30417                             | 10.4                        | 640            | 92142                             | 11.0                        | 770            | 5474                              | 0.0                         | 900            | 2016                              | 0.0                         |
| 385            | 1925                              | 0.0                         | 515            | 39274                             | 16.3                        | 645            | 84987                             | 8.2                         | 775            | 4977                              | 0.0                         | 905            | 1748                              | 0.0                         |
| 390            | 1893                              | 0.0                         | 520            | 47282                             | 22.9                        | 650            | 78016                             | 5.7                         | 780            | 4723                              | 0.0                         | 910            | 2046                              | 0.0                         |
| 395            | 1695                              | 0.0                         | 525            | 55413                             | 29.7                        | 655            | 71541                             | 4.1                         | 785            | 4219                              | 0.0                         | 915            | 1844                              | 0.0                         |
| 400            | 1633                              | 0.0                         | 530            | 62377                             | 36.7                        | 660            | 64863                             | 2.7                         | 790            | 3969                              | 0.0                         | 920            | 2734                              | 0.0                         |
| 405            | 2065                              | 0.0                         | 535            | 68520                             | 42.5                        | 665            | 58485                             | 1.9                         | 795            | 4122                              | 0.0                         | 925            | 2307                              | 0.0                         |
| 410            | 3449                              | 0.0                         | 540            | 73435                             | 47.8                        | 670            | 51641                             | 1.1                         | 800            | 2864                              | 0.0                         | 930            | 2039                              | 0.0                         |
| 415            | 7117                              | 0.0                         | 545            | 78677                             | 52.4                        | 675            | 46030                             | 0.8                         | 805            | 3151                              | 0.0                         | 935            | 1784                              | 0.0                         |
| 420            | 13992                             | 0.0                         | 550            | 83331                             | 56.6                        | 680            | 40590                             | 0.5                         | 810            | 3022                              | 0.0                         | 940            | 2464                              | 0.0                         |
| 425            | 25176                             | 0.1                         | 555            | 89120                             | 60.9                        | 685            | 35691                             | 0.3                         | 815            | 3471                              | 0.0                         | 945            | 2794                              | 0.0                         |
| 430            | 38151                             | 0.3                         | 560            | 94613                             | 64.3                        | 690            | 31631                             | 0.2                         | 820            | 2749                              | 0.0                         | 950            | 3090                              | 0.0                         |
| 435            | 49673                             | 0.6                         | 565            | 99818                             | 66.4                        | 695            | 27437                             | 0.1                         | 825            | 2729                              | 0.0                         | 955            | 1866                              | 0.0                         |
| 440            | 57273                             | 0.9                         | 570            | 106526                            | 69.3                        | 700            | 24589                             | 0.1                         | 830            | 2282                              | 0.0                         | 960            | 3110                              | 0.0                         |
| 445            | 54802                             | 1.1                         | 575            | 111610                            | 69.4                        | 705            | 21832                             | 0.0                         | 835            | 3140                              | 0.0                         | 965            | 3880                              | 0.0                         |
| 450            | 39184                             | 1.0                         | 580            | 117163                            | 69.6                        | 710            | 19500                             | 0.0                         | 840            | 2365                              | 0.0                         | 970            | 3243                              | 0.0                         |
| 455            | 22506                             | 0.8                         | 585            | 122201                            | 67.9                        | 715            | 17870                             | 0.0                         | 845            | 3024                              | 0.0                         | 975            | 2014                              | 0.0                         |
| 460            | 13692                             | 0.6                         | 590            | 125662                            | 65.0                        | 720            | 15924                             | 0.0                         | 850            | 2510                              | 0.0                         | 980            | 1688                              | 0.0                         |
| 465            | 9446                              | 0.5                         | 595            | 127415                            | 60.4                        | 725            | 14268                             | 0.0                         | 855            | 2739                              | 0.0                         | 985            | 2827                              | 0.0                         |
| 470            | 6698                              | 0.4                         | 600            | 129155                            | 55.7                        | 730            | 12438                             | 0.0                         | 860            | 3515                              | 0.0                         | 990            | 4172                              | 0.0                         |
| 475            | 5328                              | 0.4                         | 605            | 128057                            | 49.6                        | 735            | 11255                             | 0.0                         | 865            | 3600                              | 0.0                         | 995            | 3177                              | 0.0                         |
| 480            | 5081                              | 0.5                         | 610            | 126031                            | 43.3                        | 740            | 9951                              | 0.0                         | 870            | 3609                              | 0.0                         | 1000           | 3241                              | 0.0                         |
| 485            | 5579                              | 0.7                         | 615            | 123059                            | 37.1                        | 745            | 8870                              | 0.0                         | 875            | 3208                              | 0.0                         |                |                                   |                             |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2044          | 0.0           | 490    | 7179          | 6.0           | 620    | 118034        | 0.1           | 750    | 8362          | 0.0           | 880    | 3128          | 0.0           |
| 365    | 2016          | 0.0           | 495    | 10476         | 8.6           | 625    | 111884        | 0.1           | 755    | 7635          | 0.0           | 885    | 3110          | 0.0           |
| 370    | 2020          | 0.0           | 500    | 15549         | 12.5          | 630    | 106119        | 0.0           | 760    | 6582          | 0.0           | 890    | 2632          | 0.0           |
| 375    | 2137          | 0.0           | 505    | 22477         | 17.3          | 635    | 99706         | 0.0           | 765    | 5777          | 0.0           | 895    | 2709          | 0.0           |
| 380    | 2046          | 0.0           | 510    | 30417         | 21.8          | 640    | 92142         | 0.0           | 770    | 5474          | 0.0           | 900    | 2016          | 0.0           |
| 385    | 1925          | 0.0           | 515    | 39274         | 25.7          | 645    | 84987         | 0.0           | 775    | 4977          | 0.0           | 905    | 1748          | 0.0           |
| 390    | 1893          | 0.0           | 520    | 47282         | 27.5          | 650    | 78016         | 0.0           | 780    | 4723          | 0.0           | 910    | 2046          | 0.0           |
| 395    | 1695          | 0.0           | 525    | 55413         | 28.1          | 655    | 71541         | 0.0           | 785    | 4219          | 0.0           | 915    | 1844          | 0.0           |
| 400    | 1633          | 0.0           | 530    | 62377         | 27.0          | 660    | 64863         | 0.0           | 790    | 3969          | 0.0           | 920    | 2734          | 0.0           |
| 405    | 2065          | 0.0           | 535    | 68520         | 24.7          | 665    | 58485         | 0.0           | 795    | 4122          | 0.0           | 925    | 2307          | 0.0           |
| 410    | 3449          | 0.1           | 540    | 73435         | 21.5          | 670    | 51641         | 0.0           | 800    | 2864          | 0.0           | 930    | 2039          | 0.0           |
| 415    | 7117          | 0.5           | 545    | 78677         | 18.3          | 675    | 46030         | 0.0           | 805    | 3151          | 0.0           | 935    | 1784          | 0.0           |
| 420    | 13992         | 1.6           | 550    | 83331         | 15.0          | 680    | 40590         | 0.0           | 810    | 3022          | 0.0           | 940    | 2464          | 0.0           |
| 425    | 25176         | 3.9           | 555    | 89120         | 12.0          | 685    | 35691         | 0.0           | 815    | 3471          | 0.0           | 945    | 2794          | 0.0           |
| 430    | 38151         | 8.1           | 560    | 94613         | 9.3           | 690    | 31631         | 0.0           | 820    | 2749          | 0.0           | 950    | 3090          | 0.0           |
| 435    | 49673         | 13.3          | 565    | 99818         | 7.0           | 695    | 27437         | 0.0           | 825    | 2729          | 0.0           | 955    | 1866          | 0.0           |
| 440    | 57273         | 19.1          | 570    | 106526        | 5.2           | 700    | 24589         | 0.0           | 830    | 2282          | 0.0           | 960    | 3110          | 0.0           |
| 445    | 54802         | 21.6          | 575    | 111610        | 3.7           | 705    | 21832         | 0.0           | 835    | 3140          | 0.0           | 965    | 3880          | 0.0           |
| 450    | 39184         | 18.1          | 580    | 117163        | 2.6           | 710    | 19500         | 0.0           | 840    | 2365          | 0.0           | 970    | 3243          | 0.0           |
| 455    | 22506         | 11.8          | 585    | 122201        | 1.8           | 715    | 17870         | 0.0           | 845    | 3024          | 0.0           | 975    | 2014          | 0.0           |
| 460    | 13692         | 8.1           | 590    | 125662        | 1.2           | 720    | 15924         | 0.0           | 850    | 2510          | 0.0           | 980    | 1688          | 0.0           |
| 465    | 9446          | 6.2           | 595    | 127415        | 0.8           | 725    | 14268         | 0.0           | 855    | 2739          | 0.0           | 985    | 2827          | 0.0           |
| 470    | 6698          | 4.8           | 600    | 129155        | 0.5           | 730    | 12438         | 0.0           | 860    | 3515          | 0.0           | 990    | 4172          | 0.0           |
| 475    | 5328          | 4.1           | 605    | 128057        | 0.4           | 735    | 11255         | 0.0           | 865    | 3600          | 0.0           | 995    | 3177          | 0.0           |
| 480    | 5081          | 4.1           | 610    | 126031        | 0.2           | 740    | 9951          | 0.0           | 870    | 3609          | 0.0           | 1000   | 3241          | 0.0           |
| 485    | 5579          | 4.6           | 615    | 123059        | 0.1           | 745    | 8870          | 0.0           | 875    | 3208          | 0.0           |        |               |               |

REPORT NUMBER: SP1-1908-441-1-R4

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: 2145.7 M/P: 0.35**

| $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360            | 2044                              | 0.0                         | 490            | 7179                              | 11.1                        | 620            | 118034                            | 1.5                         | 750            | 8362                              | 0.0                         | 880            | 3128                              | 0.0                         |
| 365            | 2016                              | 0.0                         | 495            | 10476                             | 16.9                        | 625            | 111884                            | 0.9                         | 755            | 7635                              | 0.0                         | 885            | 3110                              | 0.0                         |
| 370            | 2020                              | 0.0                         | 500            | 15549                             | 26.0                        | 630            | 106119                            | 0.6                         | 760            | 6582                              | 0.0                         | 890            | 2632                              | 0.0                         |
| 375            | 2137                              | 0.0                         | 505            | 22477                             | 38.2                        | 635            | 99706                             | 0.4                         | 765            | 5777                              | 0.0                         | 895            | 2709                              | 0.0                         |
| 380            | 2046                              | 0.0                         | 510            | 30417                             | 51.6                        | 640            | 92142                             | 0.2                         | 770            | 5474                              | 0.0                         | 900            | 2016                              | 0.0                         |
| 385            | 1925                              | 0.0                         | 515            | 39274                             | 65.1                        | 645            | 84987                             | 0.1                         | 775            | 4977                              | 0.0                         | 905            | 1748                              | 0.0                         |
| 390            | 1893                              | 0.0                         | 520            | 47282                             | 75.2                        | 650            | 78016                             | 0.1                         | 780            | 4723                              | 0.0                         | 910            | 2046                              | 0.0                         |
| 395            | 1695                              | 0.0                         | 525            | 55413                             | 82.9                        | 655            | 71541                             | 0.1                         | 785            | 4219                              | 0.0                         | 915            | 1844                              | 0.0                         |
| 400            | 1633                              | 0.0                         | 530            | 62377                             | 86.0                        | 660            | 64863                             | 0.0                         | 790            | 3969                              | 0.0                         | 920            | 2734                              | 0.0                         |
| 405            | 2065                              | 0.1                         | 535            | 68520                             | 85.4                        | 665            | 58485                             | 0.0                         | 795            | 4122                              | 0.0                         | 925            | 2307                              | 0.0                         |
| 410            | 3449                              | 0.2                         | 540            | 73435                             | 81.1                        | 670            | 51641                             | 0.0                         | 800            | 2864                              | 0.0                         | 930            | 2039                              | 0.0                         |
| 415            | 7117                              | 0.7                         | 545            | 78677                             | 75.4                        | 675            | 46030                             | 0.0                         | 805            | 3151                              | 0.0                         | 935            | 1784                              | 0.0                         |
| 420            | 13992                             | 2.3                         | 550            | 83331                             | 68.1                        | 680            | 40590                             | 0.0                         | 810            | 3022                              | 0.0                         | 940            | 2464                              | 0.0                         |
| 425            | 25176                             | 6.2                         | 555            | 89120                             | 60.9                        | 685            | 35691                             | 0.0                         | 815            | 3471                              | 0.0                         | 945            | 2794                              | 0.0                         |
| 430            | 38151                             | 13.0                        | 560            | 94613                             | 52.9                        | 690            | 31631                             | 0.0                         | 820            | 2749                              | 0.0                         | 950            | 3090                              | 0.0                         |
| 435            | 49673                             | 22.2                        | 565            | 99818                             | 44.8                        | 695            | 27437                             | 0.0                         | 825            | 2729                              | 0.0                         | 955            | 1866                              | 0.0                         |
| 440            | 57273                             | 32.0                        | 570            | 106526                            | 37.6                        | 700            | 24589                             | 0.0                         | 830            | 2282                              | 0.0                         | 960            | 3110                              | 0.0                         |
| 445            | 54802                             | 36.7                        | 575            | 111610                            | 30.4                        | 705            | 21832                             | 0.0                         | 835            | 3140                              | 0.0                         | 965            | 3880                              | 0.0                         |
| 450            | 39184                             | 30.4                        | 580            | 117163                            | 24.1                        | 710            | 19500                             | 0.0                         | 840            | 2365                              | 0.0                         | 970            | 3243                              | 0.0                         |
| 455            | 22506                             | 19.7                        | 585            | 122201                            | 18.7                        | 715            | 17870                             | 0.0                         | 845            | 3024                              | 0.0                         | 975            | 2014                              | 0.0                         |
| 460            | 13692                             | 13.2                        | 590            | 125662                            | 14.0                        | 720            | 15924                             | 0.0                         | 850            | 2510                              | 0.0                         | 980            | 1688                              | 0.0                         |
| 465            | 9446                              | 10.0                        | 595            | 127415                            | 10.2                        | 725            | 14268                             | 0.0                         | 855            | 2739                              | 0.0                         | 985            | 2827                              | 0.0                         |
| 470            | 6698                              | 7.7                         | 600            | 129155                            | 7.3                         | 730            | 12438                             | 0.0                         | 860            | 3515                              | 0.0                         | 990            | 4172                              | 0.0                         |
| 475            | 5328                              | 6.7                         | 605            | 128057                            | 5.0                         | 735            | 11255                             | 0.0                         | 865            | 3600                              | 0.0                         | 995            | 3177                              | 0.0                         |
| 480            | 5081                              | 6.9                         | 610            | 126031                            | 3.4                         | 740            | 9951                              | 0.0                         | 870            | 3609                              | 0.0                         | 1000           | 3241                              | 0.0                         |
| 485            | 5579                              | 8.1                         | 615            | 123059                            | 2.3                         | 745            | 8870                              | 0.0                         | 875            | 3208                              | 0.0                         |                |                                   |                             |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

**Summary**

$R_f = 69.9$   
 $R_g = 98.3$   
 $CIE R_a = 71.5$   
 $R_9 = -16.1$



**Color Vector Graphics**





REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 |            |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)