

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P362731

Luminaire Tested: NVN-SA3C-727-U-T3R-HSS

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-2019
Report Number: P362731
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-11)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: STREETWORKS
Catalog Number: NVN-SA3C-727-U-T3R-HSS
Description: NAVION ROADWAY AND AREA LUMINAIRE
(3) 70 CRI, 2700K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE III
ROADWAY OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13772 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1.5' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B1 - U0 - G3


Input Watts (W): 166
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P362731
 CATALOG NUMBER: NVN-SA3C-727-U-T3R-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 6.8 fc
 Type III - Medium - N/A

REPORT NUMBER: P362731
CATALOG NUMBER: NVN-SA3C-727-U-T3R-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 55-Deg Lateral - - - Horizontal Cone Through 71-Deg Vertical

REPORT NUMBER: P362731
 CATALOG NUMBER: NVN-SA3C-727-U-T3R-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 1090.4 | 0.0 | 1090.4 |
| | % Fixture | 7.9 | 0.0 | 7.9 |
| Street Side | Lumens | 12681.6 | 0.0 | 12681.6 |
| | % Fixture | 92.1 | 0.0 | 92.1 |
| Total | Lumens | 13772.0 | 0.0 | 13772.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 226.5 | 1.6 |
| 10°-20° | 511.2 | 3.7 |
| 20°-30° | 821.6 | 6.0 |
| 30°-40° | 1395.9 | 10.1 |
| 40°-50° | 2166.6 | 15.7 |
| 50°-60° | 2913.0 | 21.2 |
| 60°-70° | 3563.6 | 25.9 |
| 70°-80° | 2083.5 | 15.1 |
| 80°-90° | 90.1 | 0.7 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 13772.0 | 100.0 |
| 0°-180° | 13772.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P362731
 CATALOG NUMBER: NVN-SA3C-727-U-T3R-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1068.5 | 7.8 | | | |
| FM (30°-60°) | 6023.5 | 43.7 | | | |
| FH (60°-80°) | 5501.0 | 39.9 | | | G3/7500 |
| FVH (80°-90°) | 88.6 | 0.6 | | | G1/100 |
| BL (0°-30°) | 490.8 | 3.6 | B1/500 | | |
| BM (30°-60°) | 452.1 | 3.3 | B1/1000 | | |
| BH (60°-80°) | 146.1 | 1.1 | B1/500 | | G1/500 |
| BVH (80°-90°) | 1.4 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G3
 Type III Medium





REPORT NUMBER: P362731
 CATALOG NUMBER: NVN-SA3C-727-U-T3R-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 54° | 55° | 65° | 75° | 85° |
|-------|--------|--------|--------|--------|--------|--------|---------|---------|--------|---------|--------|
| 0° | 2656.0 | 2656.0 | 2656.0 | 2656.0 | 2656.0 | 2656.0 | 2656.0 | 2656.0 | 2656.0 | 2656.0 | 2656.0 |
| 2.5° | 2578.1 | 2581.2 | 2592.3 | 2597.2 | 2609.0 | 2628.8 | 2638.7 | 2639.3 | 2655.4 | 2661.5 | 2666.5 |
| 5° | 2395.6 | 2414.2 | 2432.7 | 2452.5 | 2488.4 | 2536.0 | 2583.0 | 2587.3 | 2639.3 | 2677.6 | 2698.0 |
| 7.5° | 2238.6 | 2255.3 | 2277.5 | 2309.1 | 2359.8 | 2434.6 | 2513.1 | 2522.4 | 2620.7 | 2707.9 | 2753.7 |
| 10° | 2077.2 | 2090.8 | 2122.9 | 2169.3 | 2239.2 | 2339.4 | 2445.1 | 2460.6 | 2604.0 | 2748.7 | 2829.1 |
| 12.5° | 1904.6 | 1912.7 | 1951.6 | 2018.4 | 2121.1 | 2248.5 | 2387.6 | 2408.0 | 2593.5 | 2795.7 | 2918.2 |
| 15° | 1773.5 | 1777.2 | 1814.4 | 1883.6 | 2001.1 | 2166.8 | 2343.1 | 2367.8 | 2596.0 | 2852.0 | 3015.3 |
| 17.5° | 1740.1 | 1742.0 | 1761.8 | 1809.4 | 1913.3 | 2093.9 | 2307.8 | 2338.1 | 2603.4 | 2907.0 | 3113.0 |
| 20° | 1875.6 | 1862.6 | 1842.2 | 1834.8 | 1879.3 | 2050.0 | 2286.8 | 2320.8 | 2613.3 | 2955.9 | 3200.8 |
| 22.5° | 2247.2 | 2208.9 | 2124.2 | 2011.0 | 1942.4 | 2053.1 | 2292.4 | 2326.4 | 2644.8 | 3015.9 | 3302.2 |
| 25° | 2798.8 | 2745.6 | 2601.6 | 2378.9 | 2165.0 | 2142.1 | 2338.7 | 2373.4 | 2706.1 | 3087.6 | 3399.3 |
| 27.5° | 3426.5 | 3373.9 | 3197.7 | 2879.8 | 2515.0 | 2318.3 | 2445.1 | 2477.3 | 2797.0 | 3151.3 | 3473.5 |
| 30° | 4027.6 | 4012.7 | 3804.9 | 3443.8 | 2955.3 | 2604.0 | 2582.4 | 2609.6 | 2864.4 | 3189.6 | 3532.2 |
| 32.5° | 4537.1 | 4513.6 | 4346.7 | 3995.4 | 3459.3 | 2947.2 | 2743.8 | 2751.8 | 2915.1 | 3239.1 | 3608.9 |
| 35° | 5009.6 | 4980.5 | 4833.9 | 4501.9 | 3976.2 | 3366.5 | 2992.4 | 2980.6 | 3025.8 | 3338.7 | 3720.2 |
| 37.5° | 5422.0 | 5448.6 | 5286.0 | 4970.0 | 4440.0 | 3802.5 | 3327.5 | 3292.3 | 3198.9 | 3500.7 | 3881.6 |
| 40° | 5767.1 | 5767.1 | 5682.4 | 5418.9 | 4940.9 | 4253.3 | 3706.6 | 3660.2 | 3459.3 | 3750.5 | 4086.3 |
| 42.5° | 5891.4 | 5918.0 | 5949.5 | 5800.5 | 5389.3 | 4722.0 | 4129.0 | 4080.7 | 3826.0 | 4104.9 | 4344.8 |
| 45° | 5898.8 | 5940.9 | 6102.3 | 6101.6 | 5794.3 | 5187.7 | 4605.1 | 4582.3 | 4295.9 | 4560.0 | 4665.1 |
| 47.5° | 5794.3 | 5846.9 | 6112.8 | 6263.7 | 6115.2 | 5621.2 | 5125.8 | 5097.4 | 4848.2 | 5117.8 | 5000.3 |
| 50° | 5632.9 | 5691.0 | 6000.2 | 6327.4 | 6333.5 | 5998.4 | 5674.3 | 5631.7 | 5456.0 | 5755.3 | 5346.6 |
| 52.5° | 5344.1 | 5456.7 | 5899.4 | 6342.2 | 6477.0 | 6324.3 | 6196.3 | 6177.7 | 6136.3 | 6369.4 | 5622.4 |
| 55° | 4726.3 | 4851.3 | 5646.5 | 6347.1 | 6610.0 | 6613.0 | 6685.4 | 6690.3 | 6773.8 | 6943.3 | 5827.7 |
| 57.5° | 4434.5 | 4505.0 | 5205.0 | 6370.6 | 6807.2 | 6940.8 | 7183.8 | 7222.2 | 7351.4 | 7488.1 | 6062.1 |
| 60° | 4250.8 | 4334.3 | 4987.3 | 6338.5 | 7117.0 | 7370.6 | 7645.8 | 7658.7 | 7797.3 | 8050.2 | 6379.3 |
| 62.5° | 4104.2 | 4186.5 | 4850.0 | 6214.8 | 7465.2 | 7887.5 | 8097.2 | 8098.4 | 8202.3 | 8719.9 | 6739.8 |
| 65° | 3742.5 | 3811.7 | 4572.4 | 6075.7 | 7695.2 | 8399.0 | 8621.6 | 8613.5 | 8698.3 | 9426.1 | 7158.5 |
| 67.5° | 3219.3 | 3272.5 | 4005.3 | 5548.2 | 7608.7 | 8864.0 | 9413.1 | 9386.5 | 9283.9 | 10036.4 | 7323.0 |
| 70° | 2489.0 | 2508.2 | 3156.9 | 4623.7 | 6797.3 | 9042.7 | 10178.1 | 10164.5 | 9643.2 | 9927.0 | 6720.0 |
| 71° | 2057.4 | 2120.5 | 2782.1 | 4080.7 | 6253.8 | 8877.6 | 10252.3 | 10260.3 | 9552.9 | 9628.9 | 6305.1 |
| 72.5° | 1194.7 | 1248.5 | 2016.6 | 3134.0 | 5309.5 | 8188.7 | 9867.6 | 9925.8 | 9131.1 | 8758.2 | 5385.5 |
| 75° | 256.0 | 273.9 | 747.6 | 1516.9 | 2920.6 | 5739.3 | 7788.6 | 7995.8 | 7442.3 | 5958.2 | 3245.9 |
| 77.5° | 178.1 | 192.3 | 320.3 | 688.3 | 965.3 | 2835.9 | 4838.3 | 5072.0 | 4446.2 | 2239.2 | 1038.9 |
| 80° | 141.0 | 157.1 | 249.8 | 340.1 | 261.0 | 914.6 | 2266.4 | 2409.2 | 1482.9 | 499.7 | 175.0 |
| 82.5° | 78.5 | 93.4 | 194.8 | 183.7 | 100.2 | 173.8 | 634.5 | 717.3 | 296.8 | 100.8 | 41.4 |
| 85° | 22.9 | 27.8 | 125.5 | 133.6 | 42.7 | 33.4 | 108.2 | 134.2 | 56.3 | 26.6 | 18.6 |
| 87.5° | 0.0 | 0.0 | 60.6 | 51.3 | 12.4 | 4.9 | 9.9 | 11.1 | 11.1 | 11.1 | 12.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P362731
 CATALOG NUMBER: NVN-SA3C-727-U-T3R-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2656.0 | 2656.0 | 2656.0 | 2656.0 | 2656.0 | 2656.0 | 2656.0 | 2656.0 | 2656.0 | 2656.0 | 2656.0 |
| 2.5° | 2666.5 | 2670.8 | 2655.4 | 2635.0 | 2613.3 | 2586.7 | 2558.9 | 2537.2 | 2536.6 | 2526.1 | 2515.6 |
| 5° | 2699.3 | 2696.8 | 2654.1 | 2589.2 | 2512.5 | 2432.7 | 2356.7 | 2270.7 | 2242.3 | 2207.0 | 2195.3 |
| 7.5° | 2759.9 | 2742.6 | 2652.3 | 2510.0 | 2341.8 | 2174.9 | 2002.3 | 1828.6 | 1754.4 | 1687.6 | 1675.8 |
| 10° | 2835.9 | 2803.2 | 2640.5 | 2391.3 | 2082.7 | 1774.8 | 1514.4 | 1278.2 | 1174.3 | 1094.5 | 1090.8 |
| 12.5° | 2915.1 | 2865.0 | 2607.7 | 2212.0 | 1743.2 | 1310.4 | 1010.4 | 777.9 | 691.4 | 635.7 | 640.7 |
| 15° | 2997.9 | 2923.1 | 2537.2 | 1970.2 | 1356.7 | 889.2 | 620.9 | 484.2 | 449.6 | 435.3 | 439.1 |
| 17.5° | 3082.7 | 2963.3 | 2438.9 | 1678.9 | 975.2 | 573.9 | 429.8 | 391.4 | 391.4 | 394.5 | 395.8 |
| 20° | 3156.3 | 2985.0 | 2294.2 | 1352.4 | 661.1 | 418.0 | 376.0 | 370.4 | 373.5 | 378.5 | 379.1 |
| 22.5° | 3229.2 | 2986.2 | 2105.6 | 1021.6 | 462.6 | 366.1 | 358.0 | 355.6 | 357.4 | 363.0 | 363.6 |
| 25° | 3288.6 | 2971.4 | 1869.4 | 726.6 | 369.2 | 345.1 | 341.4 | 340.1 | 341.4 | 348.2 | 348.2 |
| 27.5° | 3312.7 | 2917.6 | 1581.2 | 510.8 | 330.8 | 321.6 | 320.3 | 321.6 | 323.4 | 328.4 | 329.0 |
| 30° | 3315.2 | 2823.6 | 1267.1 | 369.8 | 299.9 | 290.0 | 292.5 | 296.8 | 295.0 | 293.7 | 295.0 |
| 32.5° | 3321.4 | 2714.7 | 961.0 | 304.2 | 273.9 | 258.5 | 255.4 | 255.4 | 248.0 | 243.6 | 241.2 |
| 35° | 3341.8 | 2586.7 | 696.9 | 273.3 | 247.4 | 229.4 | 217.7 | 204.1 | 189.8 | 182.4 | 180.6 |
| 37.5° | 3373.9 | 2452.5 | 499.0 | 252.9 | 223.9 | 203.4 | 181.2 | 157.1 | 136.7 | 131.1 | 131.1 |
| 40° | 3432.7 | 2314.0 | 369.2 | 236.8 | 205.3 | 180.0 | 146.6 | 115.0 | 96.5 | 93.4 | 93.4 |
| 42.5° | 3525.4 | 2168.1 | 294.4 | 222.6 | 189.2 | 155.8 | 111.9 | 83.5 | 69.9 | 68.0 | 67.4 |
| 45° | 3621.9 | 2007.3 | 257.2 | 209.0 | 171.9 | 128.0 | 82.9 | 61.8 | 53.8 | 51.9 | 51.9 |
| 47.5° | 3718.4 | 1836.0 | 239.3 | 196.0 | 155.2 | 99.6 | 61.8 | 48.9 | 45.1 | 45.1 | 45.8 |
| 50° | 3800.0 | 1657.3 | 226.3 | 181.8 | 133.6 | 75.4 | 48.9 | 41.4 | 40.2 | 42.7 | 43.3 |
| 52.5° | 3820.4 | 1481.7 | 210.3 | 163.9 | 107.0 | 57.5 | 40.2 | 36.5 | 36.5 | 36.5 | 36.5 |
| 55° | 3808.0 | 1345.6 | 189.2 | 141.6 | 79.2 | 45.8 | 34.6 | 32.2 | 31.5 | 31.5 | 31.5 |
| 57.5° | 3850.1 | 1265.2 | 151.5 | 110.1 | 56.9 | 37.1 | 30.3 | 28.4 | 27.2 | 26.6 | 26.6 |
| 60° | 3934.8 | 1212.7 | 108.2 | 79.2 | 42.7 | 30.9 | 26.0 | 24.1 | 22.3 | 21.0 | 21.0 |
| 62.5° | 4047.4 | 1166.9 | 80.4 | 58.7 | 32.8 | 24.7 | 21.6 | 19.8 | 17.3 | 16.1 | 16.1 |
| 65° | 4133.9 | 1085.3 | 61.2 | 43.9 | 24.7 | 19.8 | 16.7 | 16.1 | 12.4 | 11.1 | 10.5 |
| 67.5° | 4001.6 | 905.9 | 49.5 | 32.2 | 18.6 | 15.5 | 13.0 | 12.4 | 7.4 | 6.2 | 6.2 |
| 70° | 3432.1 | 630.8 | 39.6 | 23.5 | 13.6 | 12.4 | 10.5 | 8.0 | 5.6 | 4.9 | 4.9 |
| 71° | 3112.4 | 526.9 | 35.9 | 19.8 | 11.7 | 11.7 | 9.9 | 6.8 | 4.9 | 4.3 | 4.3 |
| 72.5° | 2585.5 | 374.1 | 30.3 | 15.5 | 10.5 | 12.4 | 10.5 | 6.2 | 4.9 | 4.3 | 3.7 |
| 75° | 1500.8 | 156.5 | 21.0 | 10.5 | 8.0 | 14.8 | 13.6 | 5.6 | 3.7 | 3.1 | 3.1 |
| 77.5° | 451.4 | 57.5 | 11.7 | 6.8 | 6.2 | 13.0 | 15.5 | 4.9 | 1.9 | 0.6 | 0.6 |
| 80° | 82.2 | 24.7 | 7.4 | 4.3 | 4.3 | 8.0 | 11.7 | 2.5 | 0.0 | 0.0 | 0.0 |
| 82.5° | 29.1 | 12.4 | 4.3 | 2.5 | 1.9 | 3.7 | 5.6 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 16.7 | 8.7 | 2.5 | 1.2 | 0.0 | 0.6 | 1.2 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 11.1 | 2.5 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 CIE $R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics




REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)