

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P363740

Luminaire Tested: NVN-SA4C-727-U-SL4-HSS

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-2019  
Report Number: P363740  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: STREETWORKS  
Catalog Number: NVN-SA4C-727-U-SL4-HSS  
Description: NAVION ROADWAY AND AREA LUMINAIRE  
(4) 70 CRI, 2700K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV  
SPILL LIGHT ELIMINATOR OPTICS WITH HOUSE SIDE SHIELD  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 19750 lumens  
Efficiency: N/A  
Efficacy: 87.8 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B2 - U0 - G4


Input Watts (W): 225  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P363740  
 CATALOG NUMBER: NVN-SA4C-727-U-SL4-HSS

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 6.1 fc  
 Type IV - Short - N/A

REPORT NUMBER: P363740  
CATALOG NUMBER: NVN-SA4C-727-U-SL4-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 38-Deg Lateral    - - - Horizontal Cone Through 72.5-Deg Vertical

REPORT NUMBER: P363740  
 CATALOG NUMBER: NVN-SA4C-727-U-SL4-HSS


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 1662.0   | 0.0    | 1662.0  |
|                    | % Fixture | 8.4      | 0.0    | 8.4     |
| <b>Street Side</b> | Lumens    | 18088.0  | 0.0    | 18088.0 |
|                    | % Fixture | 91.6     | 0.0    | 91.6    |
| <b>Total</b>       | Lumens    | 19750.0  | 0.0    | 19750.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 309.5   | 1.6       |
| 10°-20°   | 756.8   | 3.8       |
| 20°-30°   | 1203.7  | 6.1       |
| 30°-40°   | 1809.7  | 9.2       |
| 40°-50°   | 2760.8  | 14.0      |
| 50°-60°   | 3901.9  | 19.8      |
| 60°-70°   | 4894.3  | 24.8      |
| 70°-80°   | 3659.6  | 18.5      |
| 80°-90°   | 453.8   | 2.3       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 19750.0 | 100.0     |
| 0°-180°   | 19750.0 | 100.0     |

**Coefficient of Utilization**




REPORT NUMBER: P363740  
 CATALOG NUMBER: NVN-SA4C-727-U-SL4-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens | % Fixture | Zone Rating/Lumen Limit |      |          |
|----------------|--------|-----------|-------------------------|------|----------|
|                |        |           | B                       | U    | G        |
| FL (0°-30°)    | 1678.3 | 8.5       |                         |      |          |
| FM (30°-60°)   | 7628.3 | 38.6      |                         |      |          |
| FH (60°-80°)   | 8331.8 | 42.2      |                         |      | G4/12000 |
| FVH (80°-90°)  | 449.5  | 2.3       |                         |      | G3/500   |
| BL (0°-30°)    | 591.8  | 3.0       | B2/1000                 |      |          |
| BM (30°-60°)   | 844.0  | 4.3       | B1/1000                 |      |          |
| BH (60°-80°)   | 222.0  | 1.1       | B1/500                  |      | G1/500   |
| BVH (80°-90°)  | 4.2    | 0.0       |                         |      | G0/10    |
| UL (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |          |
| UH (100°-180°) | 0.0    | 0.0       |                         | U0/0 |          |

**BUG Rating: B2-U0-G4**  
 Type IV Short





REPORT NUMBER: P363740  
 CATALOG NUMBER: NVN-SA4C-727-U-SL4-HSS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°     | 25°     | 35°     | 38°     | 45°     | 55°     | 65°     | 75°    | 85°    |
|-------|--------|--------|---------|---------|---------|---------|---------|---------|---------|--------|--------|
| 0°    | 3632.0 | 3632.0 | 3632.0  | 3632.0  | 3632.0  | 3632.0  | 3632.0  | 3632.0  | 3632.0  | 3632.0 | 3632.0 |
| 2.5°  | 3855.1 | 3855.9 | 3846.9  | 3832.1  | 3813.2  | 3803.4  | 3787.0  | 3760.7  | 3732.8  | 3682.8 | 3628.7 |
| 5°    | 3933.8 | 3933.8 | 3922.3  | 3902.6  | 3872.3  | 3863.3  | 3832.1  | 3790.3  | 3732.8  | 3651.6 | 3560.6 |
| 7.5°  | 3925.6 | 3927.2 | 3911.7  | 3891.2  | 3860.8  | 3852.6  | 3814.9  | 3768.1  | 3696.8  | 3598.3 | 3481.9 |
| 10°   | 3882.9 | 3887.1 | 3874.7  | 3864.9  | 3837.0  | 3828.0  | 3792.7  | 3746.0  | 3674.6  | 3569.6 | 3435.9 |
| 12.5° | 3839.5 | 3843.6 | 3847.7  | 3856.7  | 3839.5  | 3836.2  | 3808.3  | 3768.9  | 3700.9  | 3591.8 | 3440.8 |
| 15°   | 3811.6 | 3819.8 | 3849.3  | 3884.6  | 3888.7  | 3885.4  | 3867.4  | 3830.5  | 3761.6  | 3648.4 | 3476.1 |
| 17.5° | 3811.6 | 3824.7 | 3886.2  | 3953.5  | 3977.3  | 3979.7  | 3964.2  | 3912.5  | 3830.5  | 3709.1 | 3508.9 |
| 20°   | 3843.6 | 3861.6 | 3957.6  | 4052.7  | 4092.1  | 4092.1  | 4061.8  | 3989.6  | 3893.6  | 3764.0 | 3531.1 |
| 22.5° | 3925.6 | 3949.4 | 4070.0  | 4179.9  | 4221.7  | 4212.7  | 4171.7  | 4066.7  | 3959.2  | 3826.4 | 3559.0 |
| 25°   | 4087.2 | 4105.2 | 4230.7  | 4341.5  | 4366.9  | 4346.4  | 4294.7  | 4160.2  | 4042.9  | 3910.8 | 3609.8 |
| 27.5° | 4295.5 | 4298.0 | 4427.6  | 4521.1  | 4505.5  | 4491.6  | 4426.8  | 4277.5  | 4163.5  | 4031.4 | 3697.6 |
| 30°   | 4524.4 | 4524.4 | 4638.4  | 4709.7  | 4662.2  | 4650.7  | 4585.9  | 4419.4  | 4317.7  | 4195.5 | 3822.3 |
| 32.5° | 4745.8 | 4755.7 | 4848.4  | 4893.5  | 4840.2  | 4828.7  | 4765.5  | 4599.0  | 4522.7  | 4445.6 | 4016.6 |
| 35°   | 4959.9 | 4967.3 | 5055.1  | 5079.7  | 5028.8  | 5032.1  | 4987.0  | 4845.9  | 4817.2  | 4807.3 | 4309.5 |
| 37.5° | 5167.4 | 5169.1 | 5258.5  | 5274.1  | 5248.6  | 5276.5  | 5280.6  | 5155.9  | 5209.3  | 5288.8 | 4722.0 |
| 40°   | 5356.9 | 5358.5 | 5447.1  | 5487.3  | 5530.8  | 5566.9  | 5598.9  | 5532.4  | 5708.8  | 5893.3 | 5213.4 |
| 42.5° | 5508.6 | 5525.9 | 5638.2  | 5714.5  | 5829.3  | 5898.2  | 5985.2  | 5981.9  | 6303.4  | 6580.7 | 5807.2 |
| 45°   | 5642.3 | 5671.9 | 5828.5  | 5962.2  | 6159.1  | 6269.0  | 6405.1  | 6511.8  | 6972.7  | 7345.9 | 6408.4 |
| 47.5° | 5818.7 | 5846.6 | 6025.4  | 6244.4  | 6506.9  | 6651.2  | 6876.8  | 7107.3  | 7708.5  | 8097.3 | 6995.7 |
| 50°   | 6067.2 | 6054.9 | 6231.3  | 6545.4  | 6882.5  | 7072.0  | 7393.5  | 7738.8  | 8438.5  | 8751.8 | 7341.0 |
| 52.5° | 6332.1 | 6327.2 | 6457.6  | 6872.7  | 7325.4  | 7546.9  | 7971.8  | 8391.7  | 9136.5  | 9202.9 | 7499.3 |
| 55°   | 6660.2 | 6625.0 | 6734.9  | 7245.9  | 7851.2  | 8089.1  | 8589.4  | 9038.1  | 9692.6  | 9457.2 | 7578.9 |
| 57.5° | 7003.9 | 6945.7 | 7050.7  | 7661.7  | 8444.2  | 8725.6  | 9273.5  | 9668.0  | 10062.5 | 9631.1 | 7578.1 |
| 60°   | 7359.1 | 7290.2 | 7414.8  | 8181.8  | 9180.8  | 9506.4  | 10015.0 | 10093.7 | 10407.8 | 9718.9 | 7522.3 |
| 62.5° | 7656.0 | 7615.0 | 7800.3  | 8737.9  | 10003.5 | 10323.4 | 10575.2 | 10480.8 | 10699.0 | 9786.9 | 7391.9 |
| 65°   | 7970.1 | 7972.6 | 8272.0  | 9386.7  | 10877.8 | 11093.6 | 11114.9 | 10982.8 | 10942.6 | 9773.0 | 6950.6 |
| 67.5° | 8395.0 | 8434.4 | 8933.9  | 10267.6 | 11728.4 | 11894.9 | 11893.3 | 11526.6 | 11120.6 | 9218.5 | 5972.1 |
| 70°   | 8844.5 | 8937.2 | 9696.7  | 11275.6 | 12656.9 | 12825.9 | 12738.9 | 11872.8 | 10471.0 | 7454.2 | 4226.6 |
| 72.5° | 8769.0 | 8929.8 | 10120.8 | 11911.3 | 13323.7 | 13452.5 | 12887.4 | 11022.2 | 8276.1  | 4332.4 | 1799.6 |
| 75°   | 6765.2 | 6951.4 | 9280.0  | 11281.4 | 12624.1 | 12508.4 | 11073.0 | 8577.1  | 4522.7  | 1209.0 | 405.2  |
| 77.5° | 3573.7 | 3673.0 | 6130.4  | 8594.3  | 9843.5  | 9601.6  | 7800.3  | 4758.1  | 1378.8  | 299.4  | 182.1  |
| 80°   | 1871.8 | 1894.7 | 2671.5  | 4876.2  | 6075.4  | 6077.1  | 4622.8  | 2089.9  | 568.4   | 153.4  | 122.2  |
| 82.5° | 1002.3 | 1022.0 | 1411.6  | 2253.2  | 3183.3  | 2885.6  | 1770.0  | 1150.0  | 330.6   | 86.9   | 117.3  |
| 85°   | 241.1  | 245.2  | 800.5   | 1029.4  | 1251.7  | 894.0   | 525.8   | 965.4   | 89.4    | 50.9   | 95.1   |
| 87.5° | 92.7   | 94.3   | 296.9   | 445.4   | 319.1   | 206.7   | 246.1   | 360.1   | 11.5    | 19.7   | 14.8   |
| 90°   | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    |



REPORT NUMBER: P363740  
 CATALOG NUMBER: NVN-SA4C-727-U-SL4-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°    | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 3632.0 | 3632.0 | 3632.0 | 3632.0 | 3632.0 | 3632.0 | 3632.0 | 3632.0 | 3632.0 | 3632.0 | 3632.0 |
| 2.5°  | 3595.9 | 3574.5 | 3522.0 | 3455.6 | 3396.6 | 3353.9 | 3289.9 | 3248.1 | 3220.2 | 3219.4 | 3208.7 |
| 5°    | 3504.8 | 3461.4 | 3348.2 | 3213.6 | 3091.4 | 2981.5 | 2851.9 | 2749.4 | 2673.1 | 2660.8 | 2634.6 |
| 7.5°  | 3407.2 | 3335.9 | 3162.0 | 2952.0 | 2746.9 | 2538.6 | 2296.6 | 2146.5 | 2017.8 | 1956.2 | 1949.7 |
| 10°   | 3347.3 | 3247.3 | 3000.4 | 2696.9 | 2375.4 | 2036.6 | 1720.0 | 1501.0 | 1342.7 | 1297.6 | 1264.0 |
| 12.5° | 3335.0 | 3203.0 | 2875.7 | 2457.4 | 1998.1 | 1550.2 | 1200.0 | 967.0  | 840.7  | 800.5  | 789.9  |
| 15°   | 3347.3 | 3182.5 | 2770.7 | 2220.4 | 1615.8 | 1099.9 | 805.5  | 670.1  | 622.6  | 611.1  | 610.2  |
| 17.5° | 3354.7 | 3157.9 | 2651.8 | 1957.1 | 1245.1 | 785.8  | 616.8  | 577.4  | 570.1  | 569.2  | 570.9  |
| 20°   | 3353.9 | 3120.1 | 2509.9 | 1663.4 | 926.0  | 617.6  | 557.8  | 549.6  | 547.9  | 548.7  | 547.9  |
| 22.5° | 3348.2 | 3075.8 | 2354.0 | 1360.8 | 699.7  | 552.0  | 532.3  | 527.4  | 526.6  | 526.6  | 526.6  |
| 25°   | 3358.8 | 3040.6 | 2182.6 | 1071.2 | 576.6  | 521.7  | 509.4  | 505.3  | 504.4  | 504.4  | 502.8  |
| 27.5° | 3397.4 | 3020.9 | 1994.8 | 824.3  | 520.8  | 494.6  | 484.8  | 483.9  | 481.5  | 480.7  | 482.3  |
| 30°   | 3459.7 | 3020.9 | 1788.9 | 641.4  | 487.2  | 466.7  | 459.3  | 457.7  | 456.9  | 456.0  | 456.9  |
| 32.5° | 3569.6 | 3043.9 | 1564.2 | 533.1  | 455.2  | 435.5  | 430.6  | 433.1  | 430.6  | 430.6  | 430.6  |
| 35°   | 3768.1 | 3112.8 | 1328.8 | 465.1  | 421.6  | 405.2  | 400.3  | 403.6  | 401.9  | 401.9  | 401.1  |
| 37.5° | 4057.7 | 3240.7 | 1091.7 | 424.1  | 392.1  | 374.8  | 368.3  | 373.2  | 371.6  | 371.6  | 370.7  |
| 40°   | 4410.4 | 3426.9 | 866.2  | 392.9  | 363.4  | 345.3  | 339.6  | 342.0  | 337.9  | 337.9  | 339.6  |
| 42.5° | 4845.9 | 3663.1 | 669.3  | 362.5  | 334.7  | 317.4  | 314.1  | 311.7  | 304.3  | 300.2  | 301.0  |
| 45°   | 5329.8 | 3909.2 | 521.7  | 333.0  | 307.6  | 293.6  | 288.7  | 282.2  | 269.9  | 261.7  | 262.5  |
| 47.5° | 5762.1 | 4098.7 | 424.1  | 304.3  | 283.0  | 272.3  | 264.9  | 252.6  | 234.6  | 224.7  | 225.6  |
| 50°   | 5989.3 | 4127.4 | 360.9  | 275.6  | 260.0  | 249.3  | 238.7  | 219.8  | 198.5  | 187.8  | 187.0  |
| 52.5° | 6047.5 | 3992.9 | 314.1  | 249.3  | 237.0  | 224.7  | 210.8  | 185.4  | 161.6  | 150.1  | 148.5  |
| 55°   | 6068.9 | 3787.8 | 272.3  | 224.7  | 212.4  | 198.5  | 180.4  | 151.7  | 129.6  | 118.1  | 117.3  |
| 57.5° | 5998.3 | 3481.9 | 239.5  | 202.6  | 187.8  | 170.6  | 148.5  | 121.4  | 100.1  | 91.0   | 91.0   |
| 60°   | 5841.6 | 3067.6 | 214.1  | 178.8  | 162.4  | 142.7  | 119.8  | 94.3   | 74.6   | 67.3   | 67.3   |
| 62.5° | 5529.1 | 2531.2 | 190.3  | 154.2  | 138.6  | 118.1  | 96.8   | 71.4   | 52.5   | 48.4   | 49.2   |
| 65°   | 4939.4 | 1920.1 | 166.5  | 132.1  | 118.1  | 97.6   | 75.5   | 50.9   | 35.3   | 35.3   | 36.9   |
| 67.5° | 4028.1 | 1333.7 | 141.9  | 112.4  | 101.7  | 79.6   | 57.4   | 35.3   | 24.6   | 27.9   | 31.2   |
| 70°   | 2666.6 | 748.0  | 121.4  | 92.7   | 86.9   | 63.2   | 42.7   | 23.8   | 19.7   | 26.2   | 32.0   |
| 72.5° | 1006.4 | 291.2  | 101.7  | 74.6   | 75.5   | 48.4   | 30.3   | 18.0   | 18.0   | 28.7   | 37.7   |
| 75°   | 280.5  | 142.7  | 73.0   | 55.0   | 59.1   | 35.3   | 22.1   | 15.6   | 17.2   | 32.8   | 44.3   |
| 77.5° | 164.9  | 105.0  | 47.6   | 32.0   | 40.2   | 24.6   | 14.8   | 12.3   | 14.8   | 27.9   | 42.7   |
| 80°   | 132.9  | 55.8   | 27.9   | 16.4   | 22.1   | 13.9   | 9.8    | 7.4    | 4.1    | 10.7   | 22.1   |
| 82.5° | 132.9  | 33.6   | 13.1   | 11.5   | 11.5   | 7.4    | 4.9    | 3.3    | 0.8    | 0.0    | 5.7    |
| 85°   | 89.4   | 13.9   | 8.2    | 7.4    | 5.7    | 2.5    | 1.6    | 0.8    | 0.0    | 0.0    | 0.0    |
| 87.5° | 14.8   | 5.7    | 3.3    | 1.6    | 0.8    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

**Test Information**

Test Method: LM-79-2008  
 Report Number: SP1-1908-441-1-R4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/28/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGRAW-EDISON  
 Catalog Number: **SA1C-727-U-5WQ**  
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE


\*\*\*THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.\*\*\*TESTED IN  
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

**Spectral Parameters**

CCT (K): 2741  
 CIE u': 0.2605  
 CIE v': 0.5272  
 Duv: 0.0005  
 CIE x: 0.4573  
 CIE y: 0.4113  
 CIE z: 0.1313  
 Peak Wavelength (nm): 602  
 Dominant Wavelength (nm): 583  
 Purity: 61.2

|           |      |      |       |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 |      |       |
| R1:       | 69.2 | R9:  | -16.1 |
| R2:       | 79.4 | R10: | 51.4  |
| R3:       | 87.8 | R11: | 63.1  |
| R4:       | 69.4 | R12: | 42.0  |
| R5:       | 66.4 | R13: | 70.2  |
| R6:       | 69.8 | R14: | 92.4  |
| R7:       | 79.8 |      |       |
| R8:       | 50.1 |      |       |

Rf: 69.9  
 Rg: 98.3



**Test Conditions**


Stabilization Time: 56M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.3./42%  
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/28/2019        | 12/28/2019           |
| Power Meter                    | IN0071                | 12/5/2018        | 12/5/2019            |
| AC Power Source                | IN0063                | 12/5/2018        | 12/5/2019            |
| DC Power Source                | IN0208                | 12/5/2018        | 12/5/2019            |
| Sphere Thermometer             | IN0085                | 12/5/2018        | 12/5/2019            |
| Room Thermometer               | IN0046                | 12/5/2018        | 12/5/2019            |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

**Photopic Flux vs. Wavelength**




**Photopic Lumens: 6211.7**

| $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360            | 2044                              | 0.0                         | 490            | 7179                              | 1.0                         | 620            | 118034                            | 30.7                        | 750            | 8362                              | 0.0                         | 880            | 3128                              | 0.0                         |
| 365            | 2016                              | 0.0                         | 495            | 10476                             | 1.9                         | 625            | 111884                            | 24.7                        | 755            | 7635                              | 0.0                         | 885            | 3110                              | 0.0                         |
| 370            | 2020                              | 0.0                         | 500            | 15549                             | 3.4                         | 630            | 106119                            | 19.2                        | 760            | 6582                              | 0.0                         | 890            | 2632                              | 0.0                         |
| 375            | 2137                              | 0.0                         | 505            | 22477                             | 6.3                         | 635            | 99706                             | 15.0                        | 765            | 5777                              | 0.0                         | 895            | 2709                              | 0.0                         |
| 380            | 2046                              | 0.0                         | 510            | 30417                             | 10.4                        | 640            | 92142                             | 11.0                        | 770            | 5474                              | 0.0                         | 900            | 2016                              | 0.0                         |
| 385            | 1925                              | 0.0                         | 515            | 39274                             | 16.3                        | 645            | 84987                             | 8.2                         | 775            | 4977                              | 0.0                         | 905            | 1748                              | 0.0                         |
| 390            | 1893                              | 0.0                         | 520            | 47282                             | 22.9                        | 650            | 78016                             | 5.7                         | 780            | 4723                              | 0.0                         | 910            | 2046                              | 0.0                         |
| 395            | 1695                              | 0.0                         | 525            | 55413                             | 29.7                        | 655            | 71541                             | 4.1                         | 785            | 4219                              | 0.0                         | 915            | 1844                              | 0.0                         |
| 400            | 1633                              | 0.0                         | 530            | 62377                             | 36.7                        | 660            | 64863                             | 2.7                         | 790            | 3969                              | 0.0                         | 920            | 2734                              | 0.0                         |
| 405            | 2065                              | 0.0                         | 535            | 68520                             | 42.5                        | 665            | 58485                             | 1.9                         | 795            | 4122                              | 0.0                         | 925            | 2307                              | 0.0                         |
| 410            | 3449                              | 0.0                         | 540            | 73435                             | 47.8                        | 670            | 51641                             | 1.1                         | 800            | 2864                              | 0.0                         | 930            | 2039                              | 0.0                         |
| 415            | 7117                              | 0.0                         | 545            | 78677                             | 52.4                        | 675            | 46030                             | 0.8                         | 805            | 3151                              | 0.0                         | 935            | 1784                              | 0.0                         |
| 420            | 13992                             | 0.0                         | 550            | 83331                             | 56.6                        | 680            | 40590                             | 0.5                         | 810            | 3022                              | 0.0                         | 940            | 2464                              | 0.0                         |
| 425            | 25176                             | 0.1                         | 555            | 89120                             | 60.9                        | 685            | 35691                             | 0.3                         | 815            | 3471                              | 0.0                         | 945            | 2794                              | 0.0                         |
| 430            | 38151                             | 0.3                         | 560            | 94613                             | 64.3                        | 690            | 31631                             | 0.2                         | 820            | 2749                              | 0.0                         | 950            | 3090                              | 0.0                         |
| 435            | 49673                             | 0.6                         | 565            | 99818                             | 66.4                        | 695            | 27437                             | 0.1                         | 825            | 2729                              | 0.0                         | 955            | 1866                              | 0.0                         |
| 440            | 57273                             | 0.9                         | 570            | 106526                            | 69.3                        | 700            | 24589                             | 0.1                         | 830            | 2282                              | 0.0                         | 960            | 3110                              | 0.0                         |
| 445            | 54802                             | 1.1                         | 575            | 111610                            | 69.4                        | 705            | 21832                             | 0.0                         | 835            | 3140                              | 0.0                         | 965            | 3880                              | 0.0                         |
| 450            | 39184                             | 1.0                         | 580            | 117163                            | 69.6                        | 710            | 19500                             | 0.0                         | 840            | 2365                              | 0.0                         | 970            | 3243                              | 0.0                         |
| 455            | 22506                             | 0.8                         | 585            | 122201                            | 67.9                        | 715            | 17870                             | 0.0                         | 845            | 3024                              | 0.0                         | 975            | 2014                              | 0.0                         |
| 460            | 13692                             | 0.6                         | 590            | 125662                            | 65.0                        | 720            | 15924                             | 0.0                         | 850            | 2510                              | 0.0                         | 980            | 1688                              | 0.0                         |
| 465            | 9446                              | 0.5                         | 595            | 127415                            | 60.4                        | 725            | 14268                             | 0.0                         | 855            | 2739                              | 0.0                         | 985            | 2827                              | 0.0                         |
| 470            | 6698                              | 0.4                         | 600            | 129155                            | 55.7                        | 730            | 12438                             | 0.0                         | 860            | 3515                              | 0.0                         | 990            | 4172                              | 0.0                         |
| 475            | 5328                              | 0.4                         | 605            | 128057                            | 49.6                        | 735            | 11255                             | 0.0                         | 865            | 3600                              | 0.0                         | 995            | 3177                              | 0.0                         |
| 480            | 5081                              | 0.5                         | 610            | 126031                            | 43.3                        | 740            | 9951                              | 0.0                         | 870            | 3609                              | 0.0                         | 1000           | 3241                              | 0.0                         |
| 485            | 5579                              | 0.7                         | 615            | 123059                            | 37.1                        | 745            | 8870                              | 0.0                         | 875            | 3208                              | 0.0                         |                |                                   |                             |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength




Scotopic Lumens: 6474.3 S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360    | 2044          | 0.0           | 490    | 7179          | 6.0           | 620    | 118034        | 0.1           | 750    | 8362          | 0.0           | 880    | 3128          | 0.0           |
| 365    | 2016          | 0.0           | 495    | 10476         | 8.6           | 625    | 111884        | 0.1           | 755    | 7635          | 0.0           | 885    | 3110          | 0.0           |
| 370    | 2020          | 0.0           | 500    | 15549         | 12.5          | 630    | 106119        | 0.0           | 760    | 6582          | 0.0           | 890    | 2632          | 0.0           |
| 375    | 2137          | 0.0           | 505    | 22477         | 17.3          | 635    | 99706         | 0.0           | 765    | 5777          | 0.0           | 895    | 2709          | 0.0           |
| 380    | 2046          | 0.0           | 510    | 30417         | 21.8          | 640    | 92142         | 0.0           | 770    | 5474          | 0.0           | 900    | 2016          | 0.0           |
| 385    | 1925          | 0.0           | 515    | 39274         | 25.7          | 645    | 84987         | 0.0           | 775    | 4977          | 0.0           | 905    | 1748          | 0.0           |
| 390    | 1893          | 0.0           | 520    | 47282         | 27.5          | 650    | 78016         | 0.0           | 780    | 4723          | 0.0           | 910    | 2046          | 0.0           |
| 395    | 1695          | 0.0           | 525    | 55413         | 28.1          | 655    | 71541         | 0.0           | 785    | 4219          | 0.0           | 915    | 1844          | 0.0           |
| 400    | 1633          | 0.0           | 530    | 62377         | 27.0          | 660    | 64863         | 0.0           | 790    | 3969          | 0.0           | 920    | 2734          | 0.0           |
| 405    | 2065          | 0.0           | 535    | 68520         | 24.7          | 665    | 58485         | 0.0           | 795    | 4122          | 0.0           | 925    | 2307          | 0.0           |
| 410    | 3449          | 0.1           | 540    | 73435         | 21.5          | 670    | 51641         | 0.0           | 800    | 2864          | 0.0           | 930    | 2039          | 0.0           |
| 415    | 7117          | 0.5           | 545    | 78677         | 18.3          | 675    | 46030         | 0.0           | 805    | 3151          | 0.0           | 935    | 1784          | 0.0           |
| 420    | 13992         | 1.6           | 550    | 83331         | 15.0          | 680    | 40590         | 0.0           | 810    | 3022          | 0.0           | 940    | 2464          | 0.0           |
| 425    | 25176         | 3.9           | 555    | 89120         | 12.0          | 685    | 35691         | 0.0           | 815    | 3471          | 0.0           | 945    | 2794          | 0.0           |
| 430    | 38151         | 8.1           | 560    | 94613         | 9.3           | 690    | 31631         | 0.0           | 820    | 2749          | 0.0           | 950    | 3090          | 0.0           |
| 435    | 49673         | 13.3          | 565    | 99818         | 7.0           | 695    | 27437         | 0.0           | 825    | 2729          | 0.0           | 955    | 1866          | 0.0           |
| 440    | 57273         | 19.1          | 570    | 106526        | 5.2           | 700    | 24589         | 0.0           | 830    | 2282          | 0.0           | 960    | 3110          | 0.0           |
| 445    | 54802         | 21.6          | 575    | 111610        | 3.7           | 705    | 21832         | 0.0           | 835    | 3140          | 0.0           | 965    | 3880          | 0.0           |
| 450    | 39184         | 18.1          | 580    | 117163        | 2.6           | 710    | 19500         | 0.0           | 840    | 2365          | 0.0           | 970    | 3243          | 0.0           |
| 455    | 22506         | 11.8          | 585    | 122201        | 1.8           | 715    | 17870         | 0.0           | 845    | 3024          | 0.0           | 975    | 2014          | 0.0           |
| 460    | 13692         | 8.1           | 590    | 125662        | 1.2           | 720    | 15924         | 0.0           | 850    | 2510          | 0.0           | 980    | 1688          | 0.0           |
| 465    | 9446          | 6.2           | 595    | 127415        | 0.8           | 725    | 14268         | 0.0           | 855    | 2739          | 0.0           | 985    | 2827          | 0.0           |
| 470    | 6698          | 4.8           | 600    | 129155        | 0.5           | 730    | 12438         | 0.0           | 860    | 3515          | 0.0           | 990    | 4172          | 0.0           |
| 475    | 5328          | 4.1           | 605    | 128057        | 0.4           | 735    | 11255         | 0.0           | 865    | 3600          | 0.0           | 995    | 3177          | 0.0           |
| 480    | 5081          | 4.1           | 610    | 126031        | 0.2           | 740    | 9951          | 0.0           | 870    | 3609          | 0.0           | 1000   | 3241          | 0.0           |
| 485    | 5579          | 4.6           | 615    | 123059        | 0.1           | 745    | 8870          | 0.0           | 875    | 3208          | 0.0           |        |               |               |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35


| $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) | $\lambda$ (nm) | Power ( $\mu\text{W}/\text{nm}$ ) | Lumens ( $\phi/\text{nm}$ ) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360            | 2044                              | 0.0                         | 490            | 7179                              | 11.1                        | 620            | 118034                            | 1.5                         | 750            | 8362                              | 0.0                         | 880            | 3128                              | 0.0                         |
| 365            | 2016                              | 0.0                         | 495            | 10476                             | 16.9                        | 625            | 111884                            | 0.9                         | 755            | 7635                              | 0.0                         | 885            | 3110                              | 0.0                         |
| 370            | 2020                              | 0.0                         | 500            | 15549                             | 26.0                        | 630            | 106119                            | 0.6                         | 760            | 6582                              | 0.0                         | 890            | 2632                              | 0.0                         |
| 375            | 2137                              | 0.0                         | 505            | 22477                             | 38.2                        | 635            | 99706                             | 0.4                         | 765            | 5777                              | 0.0                         | 895            | 2709                              | 0.0                         |
| 380            | 2046                              | 0.0                         | 510            | 30417                             | 51.6                        | 640            | 92142                             | 0.2                         | 770            | 5474                              | 0.0                         | 900            | 2016                              | 0.0                         |
| 385            | 1925                              | 0.0                         | 515            | 39274                             | 65.1                        | 645            | 84987                             | 0.1                         | 775            | 4977                              | 0.0                         | 905            | 1748                              | 0.0                         |
| 390            | 1893                              | 0.0                         | 520            | 47282                             | 75.2                        | 650            | 78016                             | 0.1                         | 780            | 4723                              | 0.0                         | 910            | 2046                              | 0.0                         |
| 395            | 1695                              | 0.0                         | 525            | 55413                             | 82.9                        | 655            | 71541                             | 0.1                         | 785            | 4219                              | 0.0                         | 915            | 1844                              | 0.0                         |
| 400            | 1633                              | 0.0                         | 530            | 62377                             | 86.0                        | 660            | 64863                             | 0.0                         | 790            | 3969                              | 0.0                         | 920            | 2734                              | 0.0                         |
| 405            | 2065                              | 0.1                         | 535            | 68520                             | 85.4                        | 665            | 58485                             | 0.0                         | 795            | 4122                              | 0.0                         | 925            | 2307                              | 0.0                         |
| 410            | 3449                              | 0.2                         | 540            | 73435                             | 81.1                        | 670            | 51641                             | 0.0                         | 800            | 2864                              | 0.0                         | 930            | 2039                              | 0.0                         |
| 415            | 7117                              | 0.7                         | 545            | 78677                             | 75.4                        | 675            | 46030                             | 0.0                         | 805            | 3151                              | 0.0                         | 935            | 1784                              | 0.0                         |
| 420            | 13992                             | 2.3                         | 550            | 83331                             | 68.1                        | 680            | 40590                             | 0.0                         | 810            | 3022                              | 0.0                         | 940            | 2464                              | 0.0                         |
| 425            | 25176                             | 6.2                         | 555            | 89120                             | 60.9                        | 685            | 35691                             | 0.0                         | 815            | 3471                              | 0.0                         | 945            | 2794                              | 0.0                         |
| 430            | 38151                             | 13.0                        | 560            | 94613                             | 52.9                        | 690            | 31631                             | 0.0                         | 820            | 2749                              | 0.0                         | 950            | 3090                              | 0.0                         |
| 435            | 49673                             | 22.2                        | 565            | 99818                             | 44.8                        | 695            | 27437                             | 0.0                         | 825            | 2729                              | 0.0                         | 955            | 1866                              | 0.0                         |
| 440            | 57273                             | 32.0                        | 570            | 106526                            | 37.6                        | 700            | 24589                             | 0.0                         | 830            | 2282                              | 0.0                         | 960            | 3110                              | 0.0                         |
| 445            | 54802                             | 36.7                        | 575            | 111610                            | 30.4                        | 705            | 21832                             | 0.0                         | 835            | 3140                              | 0.0                         | 965            | 3880                              | 0.0                         |
| 450            | 39184                             | 30.4                        | 580            | 117163                            | 24.1                        | 710            | 19500                             | 0.0                         | 840            | 2365                              | 0.0                         | 970            | 3243                              | 0.0                         |
| 455            | 22506                             | 19.7                        | 585            | 122201                            | 18.7                        | 715            | 17870                             | 0.0                         | 845            | 3024                              | 0.0                         | 975            | 2014                              | 0.0                         |
| 460            | 13692                             | 13.2                        | 590            | 125662                            | 14.0                        | 720            | 15924                             | 0.0                         | 850            | 2510                              | 0.0                         | 980            | 1688                              | 0.0                         |
| 465            | 9446                              | 10.0                        | 595            | 127415                            | 10.2                        | 725            | 14268                             | 0.0                         | 855            | 2739                              | 0.0                         | 985            | 2827                              | 0.0                         |
| 470            | 6698                              | 7.7                         | 600            | 129155                            | 7.3                         | 730            | 12438                             | 0.0                         | 860            | 3515                              | 0.0                         | 990            | 4172                              | 0.0                         |
| 475            | 5328                              | 6.7                         | 605            | 128057                            | 5.0                         | 735            | 11255                             | 0.0                         | 865            | 3600                              | 0.0                         | 995            | 3177                              | 0.0                         |
| 480            | 5081                              | 6.9                         | 610            | 126031                            | 3.4                         | 740            | 9951                              | 0.0                         | 870            | 3609                              | 0.0                         | 1000           | 3241                              | 0.0                         |
| 485            | 5579                              | 8.1                         | 615            | 123059                            | 2.3                         | 745            | 8870                              | 0.0                         | 875            | 3208                              | 0.0                         |                |                                   |                             |

REPORT NUMBER: SP1-1908-441-1-R4





TM-30-18

**Summary**

$R_f = 69.9$   
 $R_g = 98.3$   
 $CIE R_a = 71.5$   
 $R_g = -16.1$



**Color Vector Graphics**






REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

**Individual Sample Fidelity Index ( $R_{f,i}$ )**




|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 |            |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18



Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)