

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P364028

Luminaire Tested: NVN-SA4C-727-U-SLR-HSS

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-2019
Report Number: P364028
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-28)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: STREETWORKS
Catalog Number: NVN-SA4C-727-U-SLR-HSS
Description: NAVION ROADWAY AND AREA LUMINAIRE
(4) 70 CRI, 2700K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 18062 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1.5' x H: 0')
IES Classification: Type IV - Medium
BUG Rating: B2 - U0 - G3


Input Watts (W): 225
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P364028
 CATALOG NUMBER: NVN-SA4C-727-U-SLR-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 9.4 fc
 Type IV - Medium - N/A

REPORT NUMBER: P364028
CATALOG NUMBER: NVN-SA4C-727-U-SLR-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 345-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P364028
 CATALOG NUMBER: NVN-SA4C-727-U-SLR-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 2186.1 | 0.0 | 2186.1 |
| | % Fixture | 12.1 | 0.0 | 12.1 |
| Street Side | Lumens | 15875.9 | 0.0 | 15875.9 |
| | % Fixture | 87.9 | 0.0 | 87.9 |
| Total | Lumens | 18062.0 | 0.0 | 18062.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 451.6 | 2.5 |
| 10°-20° | 898.8 | 5.0 |
| 20°-30° | 1276.3 | 7.1 |
| 30°-40° | 1885.2 | 10.4 |
| 40°-50° | 2718.9 | 15.1 |
| 50°-60° | 3816.8 | 21.1 |
| 60°-70° | 4449.3 | 24.6 |
| 70°-80° | 2274.6 | 12.6 |
| 80°-90° | 290.5 | 1.6 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 18062.0 | 100.0 |
| 0°-180° | 18062.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P364028
 CATALOG NUMBER: NVN-SA4C-727-U-SLR-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1981.1 | 11.0 | | | |
| FM (30°-60°) | 7431.0 | 41.1 | | | |
| FH (60°-80°) | 6191.0 | 34.3 | | | G3/7500 |
| FVH (80°-90°) | 272.8 | 1.5 | | | G3/500 |
| BL (0°-30°) | 645.7 | 3.6 | B2/1000 | | |
| BM (30°-60°) | 989.9 | 5.5 | B1/1000 | | |
| BH (60°-80°) | 532.8 | 2.9 | B2/1000 | | G2/1000 |
| BVH (80°-90°) | 17.7 | 0.1 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B2-U0-G3
 Type IV Medium





REPORT NUMBER: P364028
 CATALOG NUMBER: NVN-SA4C-727-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 1° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° |
|-------|---------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 |
| 2.5° | 6442.4 | 6392.8 | 6338.0 | 6159.2 | 5993.2 | 5803.2 | 5648.4 | 5540.5 | 5405.3 | 5229.9 | 5185.4 |
| 5° | 6396.2 | 6343.2 | 6171.2 | 5773.3 | 5425.0 | 5086.2 | 4759.3 | 4567.6 | 4329.7 | 4088.4 | 4028.5 |
| 7.5° | 5931.6 | 5876.0 | 5627.8 | 5082.7 | 4613.8 | 4124.4 | 3700.0 | 3437.3 | 3168.6 | 2947.8 | 2830.6 |
| 10° | 5448.1 | 5387.4 | 5108.4 | 4447.0 | 3869.4 | 3427.0 | 3115.5 | 2864.8 | 2610.7 | 2374.5 | 2186.3 |
| 12.5° | 5115.3 | 5035.7 | 4732.8 | 3983.2 | 3480.1 | 3179.7 | 2888.8 | 2588.4 | 2244.5 | 1991.2 | 1784.1 |
| 15° | 4975.8 | 4885.1 | 4565.1 | 3804.4 | 3342.3 | 2989.7 | 2610.7 | 2241.9 | 1838.9 | 1548.8 | 1358.8 |
| 17.5° | 5083.6 | 4965.5 | 4622.4 | 3792.4 | 3169.4 | 2689.4 | 2210.2 | 1777.2 | 1340.0 | 1046.5 | 911.3 |
| 20° | 5449.8 | 5295.0 | 4859.4 | 3789.0 | 2959.8 | 2332.6 | 1725.1 | 1235.6 | 883.1 | 710.2 | 639.2 |
| 22.5° | 6026.6 | 5822.1 | 5200.0 | 3816.3 | 2743.3 | 1957.8 | 1245.9 | 839.4 | 663.2 | 573.3 | 531.4 |
| 25° | 6723.1 | 6486.1 | 5690.3 | 3913.0 | 2553.4 | 1593.3 | 905.3 | 663.2 | 559.6 | 493.7 | 458.6 |
| 27.5° | 7385.4 | 7192.9 | 6309.8 | 4052.5 | 2406.2 | 1298.9 | 735.0 | 562.2 | 478.3 | 434.7 | 406.4 |
| 30° | 8046.8 | 7804.7 | 6945.6 | 4218.5 | 2229.0 | 1099.6 | 646.0 | 512.6 | 428.7 | 382.5 | 364.5 |
| 32.5° | 8527.7 | 8326.6 | 7443.6 | 4338.3 | 2039.9 | 969.5 | 577.6 | 468.9 | 400.5 | 353.4 | 326.9 |
| 35° | 9093.3 | 8865.7 | 7870.6 | 4364.8 | 1918.4 | 887.3 | 519.4 | 421.9 | 347.4 | 305.5 | 277.2 |
| 37.5° | 9704.3 | 9421.0 | 8363.4 | 4306.6 | 1823.5 | 847.1 | 475.8 | 400.5 | 324.3 | 281.5 | 251.6 |
| 40° | 10380.3 | 10060.2 | 8836.6 | 4222.8 | 1730.2 | 833.4 | 442.4 | 384.2 | 306.3 | 262.7 | 231.9 |
| 42.5° | 11092.2 | 10714.8 | 9246.5 | 4134.7 | 1671.1 | 786.4 | 439.0 | 367.9 | 292.6 | 245.6 | 214.8 |
| 45° | 11690.3 | 11307.8 | 9667.5 | 4105.6 | 1629.2 | 735.0 | 453.5 | 356.8 | 283.2 | 231.9 | 201.9 |
| 47.5° | 12166.9 | 11805.0 | 10098.7 | 4170.6 | 1605.3 | 688.0 | 413.3 | 371.4 | 278.1 | 219.9 | 190.8 |
| 50° | 12736.0 | 12326.1 | 10706.3 | 4364.8 | 1570.2 | 640.9 | 373.9 | 425.3 | 278.1 | 212.2 | 181.4 |
| 52.5° | 13449.6 | 13044.0 | 11384.0 | 4666.0 | 1500.0 | 575.9 | 336.3 | 426.1 | 280.7 | 201.9 | 169.4 |
| 55° | 14347.2 | 14052.9 | 12351.8 | 4996.3 | 1387.9 | 480.0 | 290.9 | 366.2 | 270.4 | 183.1 | 158.3 |
| 57.5° | 15208.0 | 14967.6 | 13234.0 | 5222.2 | 1238.2 | 374.8 | 253.3 | 295.2 | 247.3 | 160.9 | 141.2 |
| 59° | 15443.3 | 15180.6 | 13557.4 | 5232.5 | 1126.1 | 326.9 | 234.5 | 243.9 | 242.2 | 150.6 | 130.9 |
| 60° | 15443.3 | 15164.4 | 13650.7 | 5177.7 | 1044.8 | 300.3 | 222.5 | 217.3 | 252.4 | 143.8 | 124.9 |
| 62.5° | 15163.5 | 14771.6 | 13347.8 | 4807.2 | 852.3 | 255.8 | 194.2 | 179.7 | 226.8 | 129.2 | 110.4 |
| 65° | 14581.7 | 14010.9 | 12315.8 | 4137.2 | 759.8 | 234.5 | 167.7 | 147.2 | 157.4 | 113.8 | 96.7 |
| 67.5° | 13611.3 | 12837.8 | 10827.8 | 3342.3 | 723.1 | 228.5 | 144.6 | 124.9 | 118.9 | 97.5 | 84.7 |
| 70° | 11902.5 | 11044.3 | 9021.4 | 2627.8 | 691.4 | 225.9 | 121.5 | 105.2 | 95.8 | 82.1 | 71.9 |
| 72.5° | 8662.9 | 7767.9 | 6404.8 | 2054.5 | 672.6 | 231.0 | 97.5 | 88.1 | 78.7 | 64.2 | 55.6 |
| 75° | 4955.2 | 4369.1 | 3599.9 | 1357.1 | 573.3 | 220.8 | 75.3 | 73.6 | 56.5 | 46.2 | 38.5 |
| 77.5° | 2560.2 | 2482.3 | 2157.2 | 521.1 | 274.7 | 96.7 | 49.6 | 42.8 | 33.4 | 28.2 | 23.1 |
| 80° | 1104.7 | 1092.7 | 945.5 | 150.6 | 72.7 | 53.9 | 28.2 | 18.0 | 15.4 | 12.0 | 9.4 |
| 82.5° | 381.6 | 381.6 | 336.3 | 50.5 | 32.5 | 26.5 | 3.4 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 77.0 | 86.4 | 60.8 | 0.0 | 11.1 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P364028
 CATALOG NUMBER: NVN-SA4C-727-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 |
| 2.5° | 5131.5 | 5028.0 | 5021.1 | 4956.1 | 4874.8 | 4838.0 | 4816.6 | 4854.3 | 4900.5 | 4905.6 | 4974.9 |
| 5° | 3983.2 | 3874.5 | 3919.9 | 3804.4 | 3827.5 | 3804.4 | 3766.7 | 3773.6 | 3794.1 | 3729.9 | 3809.5 |
| 7.5° | 2797.2 | 2715.1 | 2767.3 | 2736.5 | 2777.5 | 2793.8 | 2770.7 | 2736.5 | 2635.5 | 2623.5 | 2692.8 |
| 10° | 2108.4 | 2015.1 | 1959.5 | 1901.3 | 1914.2 | 1940.7 | 1932.1 | 1907.3 | 1843.1 | 1846.6 | 1913.3 |
| 12.5° | 1694.2 | 1589.9 | 1479.5 | 1336.6 | 1301.5 | 1321.2 | 1301.5 | 1286.9 | 1225.3 | 1230.5 | 1289.5 |
| 15° | 1285.2 | 1199.7 | 1084.1 | 969.5 | 907.0 | 913.0 | 858.2 | 819.7 | 781.2 | 735.0 | 771.0 |
| 17.5° | 867.7 | 815.5 | 781.2 | 747.0 | 672.6 | 655.5 | 586.1 | 511.7 | 482.6 | 461.2 | 476.6 |
| 20° | 614.4 | 586.1 | 572.5 | 570.7 | 528.0 | 506.6 | 439.0 | 392.8 | 378.2 | 373.9 | 383.3 |
| 22.5° | 513.4 | 492.9 | 473.2 | 462.1 | 440.7 | 415.9 | 364.5 | 341.4 | 331.1 | 326.0 | 332.9 |
| 25° | 446.7 | 431.3 | 410.7 | 391.9 | 383.3 | 356.8 | 320.0 | 302.9 | 296.1 | 290.9 | 294.4 |
| 27.5° | 397.0 | 383.3 | 359.4 | 347.4 | 340.6 | 317.5 | 285.8 | 272.1 | 266.1 | 264.4 | 263.5 |
| 30° | 357.7 | 344.8 | 322.6 | 308.9 | 296.9 | 276.4 | 257.6 | 243.9 | 237.9 | 236.2 | 234.5 |
| 32.5° | 318.3 | 308.0 | 293.5 | 279.8 | 267.0 | 248.1 | 231.9 | 220.8 | 211.4 | 209.6 | 208.8 |
| 35° | 268.7 | 258.4 | 250.7 | 249.9 | 237.9 | 219.9 | 207.9 | 193.4 | 185.7 | 183.1 | 184.0 |
| 37.5° | 238.7 | 225.0 | 207.9 | 213.9 | 210.5 | 197.7 | 181.4 | 166.9 | 159.2 | 157.4 | 157.4 |
| 40° | 219.9 | 205.4 | 185.7 | 175.4 | 185.7 | 183.1 | 157.4 | 142.9 | 135.2 | 134.3 | 132.6 |
| 42.5° | 201.9 | 187.4 | 165.1 | 148.0 | 153.2 | 160.9 | 136.1 | 122.4 | 114.7 | 112.9 | 110.4 |
| 45° | 189.1 | 173.7 | 148.9 | 129.2 | 118.9 | 135.2 | 116.4 | 99.3 | 95.0 | 91.6 | 89.8 |
| 47.5° | 177.1 | 162.6 | 134.3 | 112.1 | 95.0 | 97.5 | 93.3 | 81.3 | 76.2 | 72.7 | 71.9 |
| 50° | 166.9 | 151.5 | 121.5 | 95.8 | 78.7 | 71.9 | 75.3 | 64.2 | 59.9 | 56.5 | 54.8 |
| 52.5° | 154.9 | 140.3 | 107.8 | 83.0 | 65.9 | 56.5 | 57.3 | 50.5 | 46.2 | 43.6 | 42.8 |
| 55° | 145.5 | 130.9 | 96.7 | 72.7 | 58.2 | 46.2 | 41.1 | 39.4 | 36.8 | 35.1 | 34.2 |
| 57.5° | 132.6 | 118.9 | 85.6 | 61.6 | 49.6 | 37.6 | 31.7 | 31.7 | 30.8 | 29.1 | 28.2 |
| 59° | 124.9 | 112.9 | 78.7 | 55.6 | 45.4 | 32.5 | 28.2 | 29.1 | 28.2 | 26.5 | 25.7 |
| 60° | 118.9 | 107.8 | 73.6 | 51.3 | 42.8 | 29.9 | 25.7 | 27.4 | 26.5 | 24.8 | 24.0 |
| 62.5° | 105.2 | 97.5 | 63.3 | 42.8 | 37.6 | 24.0 | 21.4 | 23.1 | 23.1 | 22.2 | 21.4 |
| 65° | 92.4 | 83.9 | 53.9 | 35.9 | 35.1 | 20.5 | 17.1 | 20.5 | 21.4 | 19.7 | 18.0 |
| 67.5° | 80.4 | 71.9 | 47.1 | 29.1 | 32.5 | 16.3 | 12.8 | 17.1 | 23.1 | 18.0 | 16.3 |
| 70° | 68.5 | 59.9 | 36.8 | 23.1 | 34.2 | 11.1 | 10.3 | 15.4 | 27.4 | 19.7 | 15.4 |
| 72.5° | 53.1 | 46.2 | 25.7 | 17.1 | 36.8 | 7.7 | 7.7 | 12.8 | 30.8 | 21.4 | 14.5 |
| 75° | 36.8 | 29.9 | 15.4 | 10.3 | 29.9 | 5.1 | 5.1 | 12.0 | 29.1 | 19.7 | 13.7 |
| 77.5° | 21.4 | 16.3 | 5.1 | 0.9 | 15.4 | 0.0 | 0.9 | 8.6 | 20.5 | 12.0 | 6.0 |
| 80° | 7.7 | 3.4 | 0.0 | 0.0 | 9.4 | 0.0 | 0.0 | 0.0 | 1.7 | 0.0 | 0.0 |
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P364028
 CATALOG NUMBER: NVN-SA4C-727-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

| | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° | 275° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|---------|---------|---------|
| 0° | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 |
| 2.5° | 4992.9 | 5108.4 | 5212.0 | 5368.5 | 5554.2 | 5768.1 | 5952.1 | 6149.8 | 6335.5 | 6412.5 | 6465.5 |
| 5° | 3825.8 | 3968.6 | 4135.5 | 4365.7 | 4672.0 | 5049.4 | 5402.8 | 5802.4 | 6231.9 | 6446.7 | 6648.6 |
| 7.5° | 2704.8 | 2850.3 | 3057.3 | 3302.1 | 3672.6 | 4121.8 | 4583.9 | 5135.8 | 5717.7 | 6057.4 | 6391.9 |
| 10° | 1945.0 | 2123.8 | 2317.2 | 2651.8 | 3028.3 | 3454.4 | 3930.1 | 4546.2 | 5194.8 | 5571.3 | 5974.4 |
| 12.5° | 1323.7 | 1527.4 | 1820.0 | 2194.8 | 2637.2 | 3054.8 | 3468.1 | 4055.9 | 4808.9 | 5182.0 | 5614.1 |
| 15° | 794.1 | 907.0 | 1216.8 | 1650.6 | 2193.1 | 2713.4 | 3166.0 | 3755.6 | 4558.2 | 5015.1 | 5464.4 |
| 17.5° | 489.4 | 541.6 | 710.2 | 1066.2 | 1636.1 | 2294.1 | 2914.4 | 3653.8 | 4594.2 | 5150.3 | 5631.2 |
| 20° | 390.2 | 410.7 | 464.6 | 629.8 | 1084.1 | 1832.0 | 2631.2 | 3633.2 | 4887.7 | 5572.2 | 6088.2 |
| 22.5° | 338.8 | 358.5 | 394.5 | 457.8 | 682.0 | 1371.7 | 2362.5 | 3652.0 | 5308.6 | 6204.5 | 6806.9 |
| 25° | 298.6 | 315.7 | 350.0 | 402.2 | 499.7 | 966.1 | 2075.0 | 3735.9 | 5857.1 | 6989.2 | 7629.3 |
| 27.5° | 267.0 | 281.5 | 313.2 | 361.1 | 428.7 | 674.3 | 1749.0 | 3837.7 | 6507.5 | 7791.8 | 8423.3 |
| 30° | 237.9 | 250.7 | 279.0 | 323.4 | 372.2 | 518.5 | 1391.3 | 3907.0 | 7158.6 | 8423.3 | 8990.6 |
| 32.5° | 213.1 | 222.5 | 248.1 | 285.8 | 323.4 | 413.3 | 1057.6 | 3895.9 | 7642.1 | 8948.7 | 9398.8 |
| 35° | 187.4 | 196.8 | 219.1 | 251.6 | 281.5 | 341.4 | 831.7 | 3688.0 | 8063.1 | 9493.8 | 9866.0 |
| 37.5° | 159.2 | 171.1 | 192.5 | 221.6 | 242.2 | 300.3 | 672.6 | 3437.3 | 8490.1 | 10116.7 | 10387.1 |
| 40° | 135.2 | 147.2 | 166.0 | 197.7 | 210.5 | 284.9 | 516.8 | 3131.8 | 8970.1 | 10813.2 | 10958.7 |
| 42.5° | 112.1 | 123.2 | 142.9 | 170.3 | 198.5 | 245.6 | 382.5 | 2782.7 | 9431.3 | 11408.8 | 11479.8 |
| 45° | 90.7 | 101.8 | 122.4 | 149.7 | 212.2 | 203.7 | 296.1 | 2408.7 | 9803.5 | 11904.2 | 11927.3 |
| 47.5° | 71.9 | 82.1 | 103.5 | 141.2 | 197.7 | 162.6 | 211.4 | 2115.2 | 10115.9 | 12291.0 | 12230.2 |
| 50° | 55.6 | 64.2 | 86.4 | 161.7 | 172.8 | 134.3 | 160.0 | 2017.7 | 10395.7 | 12530.6 | 12373.1 |
| 52.5° | 43.6 | 51.3 | 71.0 | 151.5 | 134.3 | 111.2 | 134.3 | 2109.3 | 10779.0 | 12729.1 | 12453.6 |
| 55° | 35.1 | 42.8 | 55.6 | 86.4 | 91.6 | 94.1 | 114.7 | 2194.8 | 11440.5 | 13194.6 | 12928.5 |
| 57.5° | 29.1 | 36.8 | 45.4 | 60.8 | 69.3 | 79.6 | 101.8 | 2204.2 | 12220.0 | 13968.1 | 13716.6 |
| 59° | 26.5 | 33.4 | 41.1 | 53.9 | 60.8 | 72.7 | 95.8 | 2152.9 | 12494.7 | 14249.7 | 14123.9 |
| 60° | 24.8 | 31.7 | 38.5 | 49.6 | 56.5 | 68.5 | 92.4 | 2104.1 | 12506.6 | 14239.4 | 14297.6 |
| 62.5° | 21.4 | 28.2 | 34.2 | 41.9 | 47.9 | 58.2 | 83.0 | 1923.6 | 12000.1 | 13773.0 | 14193.2 |
| 65° | 18.8 | 24.8 | 30.8 | 35.9 | 41.1 | 52.2 | 75.3 | 1594.1 | 11135.0 | 13020.9 | 13478.7 |
| 67.5° | 17.1 | 21.4 | 28.2 | 31.7 | 36.8 | 46.2 | 66.7 | 1136.3 | 10054.3 | 12101.0 | 12398.0 |
| 70° | 15.4 | 20.5 | 25.7 | 29.1 | 33.4 | 40.2 | 57.3 | 652.9 | 8490.1 | 10754.2 | 10965.6 |
| 72.5° | 14.5 | 19.7 | 23.1 | 27.4 | 29.9 | 35.9 | 52.2 | 307.2 | 6216.5 | 8615.0 | 9166.9 |
| 75° | 12.8 | 18.0 | 21.4 | 25.7 | 28.2 | 32.5 | 44.5 | 147.2 | 4134.7 | 6234.5 | 6861.7 |
| 77.5° | 7.7 | 14.5 | 19.7 | 23.1 | 24.8 | 28.2 | 36.8 | 84.7 | 2638.9 | 4315.2 | 5082.7 |
| 80° | 0.0 | 5.1 | 14.5 | 19.7 | 21.4 | 24.0 | 28.2 | 66.7 | 1411.9 | 2465.2 | 2958.9 |
| 82.5° | 0.0 | 0.0 | 10.3 | 15.4 | 14.5 | 16.3 | 21.4 | 41.9 | 636.6 | 1611.2 | 1815.8 |
| 85° | 0.0 | 0.0 | 3.4 | 12.0 | 10.3 | 7.7 | 14.5 | 14.5 | 139.5 | 815.5 | 1017.4 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.9 | 5.1 | 3.4 | 6.0 | 1.7 | 0.9 | 60.8 | 246.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P364028
 CATALOG NUMBER: NVN-SA4C-727-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

| | 285° | 295° | 305° | 315° | 325° | 335° | 345° | 355° | 359° | 360° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 | 5883.7 |
| 2.5° | 6651.2 | 6714.5 | 6821.5 | 6872.0 | 6847.2 | 6741.9 | 6616.1 | 6487.8 | 6412.5 | 6442.4 |
| 5° | 7060.2 | 7386.2 | 7574.5 | 7637.0 | 7532.6 | 7296.4 | 6987.5 | 6580.2 | 6435.6 | 6396.2 |
| 7.5° | 7060.2 | 7673.7 | 8062.2 | 8130.7 | 7897.9 | 7435.0 | 6855.7 | 6219.9 | 6008.6 | 5931.6 |
| 10° | 6812.1 | 7647.2 | 8188.9 | 8297.5 | 7972.4 | 7280.1 | 6504.0 | 5778.4 | 5527.7 | 5448.1 |
| 12.5° | 6532.3 | 7431.6 | 8002.3 | 8152.1 | 7885.1 | 7126.1 | 6260.2 | 5479.8 | 5184.6 | 5115.3 |
| 15° | 6360.3 | 7166.3 | 7638.7 | 7747.3 | 7634.4 | 7036.3 | 6202.0 | 5389.9 | 5042.5 | 4975.8 |
| 17.5° | 6421.9 | 6961.0 | 7131.2 | 7194.6 | 7270.7 | 7004.6 | 6360.3 | 5586.7 | 5146.9 | 5083.6 |
| 20° | 6653.8 | 6744.5 | 6656.3 | 6735.9 | 6941.3 | 7035.4 | 6737.6 | 6062.5 | 5534.5 | 5449.8 |
| 22.5° | 7047.4 | 6632.4 | 6385.1 | 6416.8 | 6666.6 | 7137.2 | 7314.4 | 6741.9 | 6132.7 | 6026.6 |
| 25° | 7506.0 | 6723.1 | 6234.5 | 6206.3 | 6463.0 | 7271.6 | 7841.5 | 7481.2 | 6840.3 | 6723.1 |
| 27.5° | 8082.8 | 6926.7 | 6203.7 | 6175.5 | 6391.9 | 7397.4 | 8279.6 | 8212.0 | 7585.6 | 7385.4 |
| 30° | 8527.7 | 7127.0 | 6295.2 | 6230.2 | 6463.0 | 7484.6 | 8631.3 | 8832.3 | 8179.5 | 8046.8 |
| 32.5° | 8846.9 | 7363.1 | 6444.1 | 6350.0 | 6663.2 | 7635.2 | 8902.5 | 9400.5 | 8728.8 | 8527.7 |
| 35° | 9089.9 | 7619.8 | 6684.6 | 6529.7 | 6938.7 | 7863.7 | 9156.6 | 10005.5 | 9313.2 | 9093.3 |
| 37.5° | 9317.5 | 7980.1 | 7060.2 | 6875.4 | 7370.8 | 8231.7 | 9425.3 | 10691.7 | 9967.0 | 9704.3 |
| 40° | 9635.0 | 8388.2 | 7639.5 | 7475.2 | 8097.3 | 8733.1 | 9760.8 | 11407.1 | 10710.6 | 10380.3 |
| 42.5° | 9952.4 | 8826.4 | 8232.5 | 8277.0 | 9003.5 | 9342.3 | 10193.7 | 12163.5 | 11444.7 | 11092.2 |
| 45° | 10242.5 | 9278.1 | 9077.1 | 9282.4 | 9844.6 | 10010.6 | 10624.1 | 12600.8 | 12030.9 | 11690.3 |
| 47.5° | 10500.9 | 9842.9 | 9916.5 | 10463.3 | 10801.3 | 10615.6 | 10945.9 | 12978.1 | 12467.3 | 12166.9 |
| 50° | 10801.3 | 10573.7 | 11022.9 | 11796.4 | 11902.5 | 11163.2 | 11238.5 | 13424.8 | 12977.3 | 12736.0 |
| 52.5° | 11129.8 | 11343.8 | 12248.2 | 12930.2 | 12896.0 | 11757.9 | 11532.9 | 13925.4 | 13676.4 | 13449.6 |
| 55° | 11502.9 | 11965.8 | 13327.2 | 13991.2 | 13962.1 | 12421.9 | 12020.6 | 14544.0 | 14552.6 | 14347.2 |
| 57.5° | 12056.5 | 12501.5 | 14059.7 | 14849.5 | 14898.3 | 13188.6 | 12847.2 | 15237.1 | 15344.9 | 15208.0 |
| 59° | 12453.6 | 12848.9 | 14349.8 | 15208.0 | 15406.5 | 13781.6 | 13451.3 | 15639.3 | 15568.3 | 15443.3 |
| 60° | 12747.9 | 13069.7 | 14493.5 | 15395.4 | 15701.7 | 14183.8 | 13897.1 | 15875.5 | 15594.8 | 15443.3 |
| 62.5° | 13476.1 | 13550.6 | 14752.8 | 15607.6 | 16041.5 | 15077.1 | 15151.5 | 16277.6 | 15410.8 | 15163.5 |
| 65° | 13815.8 | 13854.3 | 14749.4 | 15227.7 | 15712.9 | 15772.8 | 16289.6 | 16289.6 | 14961.6 | 14581.7 |
| 67.5° | 13673.8 | 13488.1 | 14017.8 | 13968.1 | 14452.5 | 15359.5 | 16717.4 | 15692.3 | 14102.5 | 13611.3 |
| 70° | 12518.6 | 11804.1 | 11568.8 | 11590.2 | 11960.7 | 13359.7 | 15870.3 | 13934.8 | 12476.7 | 11902.5 |
| 72.5° | 10416.2 | 8702.3 | 8121.3 | 8784.4 | 8881.1 | 10267.3 | 13524.9 | 10494.1 | 9201.1 | 8662.9 |
| 75° | 8378.0 | 6134.4 | 5189.7 | 5889.7 | 6053.9 | 7513.7 | 10462.4 | 6535.7 | 5374.5 | 4955.2 |
| 77.5° | 6018.9 | 4403.3 | 3723.9 | 3675.2 | 3887.4 | 4765.3 | 7423.9 | 3289.2 | 2743.3 | 2560.2 |
| 80° | 3419.3 | 2898.2 | 3120.7 | 2944.4 | 3051.4 | 2979.5 | 3527.1 | 1442.7 | 1181.7 | 1104.7 |
| 82.5° | 2063.9 | 1713.1 | 1855.1 | 1544.5 | 1954.4 | 1701.9 | 1358.8 | 462.1 | 401.3 | 381.6 |
| 85° | 1342.6 | 936.1 | 487.7 | 326.9 | 673.4 | 1087.6 | 303.8 | 125.8 | 96.7 | 77.0 |
| 87.5° | 462.9 | 238.7 | 24.0 | 10.3 | 71.9 | 202.8 | 11.1 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information


Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2
 Rf: 69.9
 Rg: 98.3

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4


TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 CIE $R_a = 71.5$
 $R_g = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)