

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: STREETWORKS

Report Number: P362592

Luminaire Tested: NVN-SA2D-727-U-T2R-HSS

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-2019
Report Number: P362592
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-9)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: STREETWORKS
Catalog Number: NVN-SA2D-727-U-T2R-HSS
Description: NAVION ROADWAY AND AREA LUMINAIRE
(2) 70 CRI, 2700K, 1200mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE II
ROADWAY OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10780 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type II - Medium
BUG Rating: B1 - U0 - G2


Input Watts (W): 129
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT



REPORT NUMBER: P362592
 CATALOG NUMBER: NVN-SA2D-727-U-T2R-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 8 fc
 Type II - Medium - N/A

REPORT NUMBER: P362592
CATALOG NUMBER: NVN-SA2D-727-U-T2R-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 76-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P362592
 CATALOG NUMBER: NVN-SA2D-727-U-T2R-HSS


FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 535.3 | 0.0 | 535.3 |
| | % Fixture | 5.0 | 0.0 | 5.0 |
| Street Side | Lumens | 10244.7 | 0.0 | 10244.7 |
| | % Fixture | 95.0 | 0.0 | 95.0 |
| Total | Lumens | 10780.0 | 0.0 | 10780.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 113.7 | 1.1 |
| 10°-20° | 450.8 | 4.2 |
| 20°-30° | 917.2 | 8.5 |
| 30°-40° | 1591.9 | 14.8 |
| 40°-50° | 2249.1 | 20.9 |
| 50°-60° | 2550.6 | 23.7 |
| 60°-70° | 2115.5 | 19.6 |
| 70°-80° | 766.3 | 7.1 |
| 80°-90° | 24.9 | 0.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 10780.0 | 100.0 |
| 0°-180° | 10780.0 | 100.0 |

Coefficient of Utilization




REPORT NUMBER: P362592
 CATALOG NUMBER: NVN-SA2D-727-U-T2R-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1301.1 | 12.1 | | | |
| FM (30°-60°) | 6141.1 | 57.0 | | | |
| FH (60°-80°) | 2778.4 | 25.8 | | | G2/5000 |
| FVH (80°-90°) | 24.1 | 0.2 | | | G1/100 |
| BL (0°-30°) | 180.5 | 1.7 | B1/500 | | |
| BM (30°-60°) | 250.5 | 2.3 | B1/1000 | | |
| BH (60°-80°) | 103.4 | 1.0 | B0/110 | | G0/110 |
| BVH (80°-90°) | 0.8 | 0.0 | | | G0/10 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B1-U0-G2
 Type II Medium





REPORT NUMBER: P362592

CATALOG NUMBER: NVN-SA2D-727-U-T2R-HSS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 76° | 85° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 914.5 | 914.5 | 914.5 | 914.5 | 914.5 | 914.5 | 914.5 | 914.5 | 914.5 | 914.5 | 914.5 |
| 2.5° | 1365.1 | 1334.4 | 1341.5 | 1321.6 | 1285.7 | 1212.0 | 1149.2 | 1089.7 | 1020.3 | 1017.9 | 960.7 |
| 5° | 1840.7 | 1814.7 | 1811.4 | 1771.3 | 1706.1 | 1580.9 | 1459.1 | 1320.2 | 1165.3 | 1153.9 | 1032.5 |
| 7.5° | 2272.4 | 2251.7 | 2244.1 | 2196.4 | 2075.0 | 1953.1 | 1794.4 | 1590.4 | 1348.1 | 1327.3 | 1129.4 |
| 10° | 2604.0 | 2594.1 | 2596.0 | 2562.0 | 2458.1 | 2344.7 | 2136.4 | 1876.1 | 1555.4 | 1523.3 | 1245.6 |
| 12.5° | 2855.3 | 2857.7 | 2874.7 | 2853.9 | 2795.8 | 2711.7 | 2489.2 | 2180.8 | 1785.0 | 1741.1 | 1378.3 |
| 15° | 3040.0 | 3051.8 | 3083.0 | 3109.0 | 3104.7 | 3032.0 | 2827.9 | 2490.2 | 2028.7 | 1980.1 | 1526.1 |
| 17.5° | 3159.5 | 3172.7 | 3218.1 | 3275.7 | 3328.6 | 3311.6 | 3154.8 | 2788.7 | 2275.3 | 2219.1 | 1684.4 |
| 20° | 3264.4 | 3280.0 | 3328.6 | 3404.6 | 3503.4 | 3524.6 | 3421.7 | 3078.3 | 2521.4 | 2452.9 | 1847.8 |
| 22.5° | 3491.6 | 3491.1 | 3520.8 | 3565.2 | 3659.2 | 3714.0 | 3648.9 | 3347.0 | 2764.6 | 2693.3 | 2014.5 |
| 25° | 3902.5 | 3886.9 | 3876.5 | 3841.6 | 3862.3 | 3896.4 | 3860.0 | 3598.3 | 3009.3 | 2937.0 | 2183.6 |
| 27.5° | 4390.9 | 4400.3 | 4316.3 | 4222.3 | 4149.5 | 4114.6 | 4055.1 | 3831.2 | 3244.5 | 3165.2 | 2349.0 |
| 30° | 4906.2 | 4909.1 | 4809.9 | 4689.9 | 4529.8 | 4397.0 | 4294.1 | 4053.6 | 3486.4 | 3399.9 | 2509.6 |
| 32.5° | 5371.0 | 5352.6 | 5254.3 | 5090.9 | 4888.8 | 4739.5 | 4525.5 | 4302.1 | 3742.4 | 3658.8 | 2688.1 |
| 35° | 5739.4 | 5717.7 | 5598.2 | 5449.4 | 5239.7 | 5089.5 | 4832.1 | 4550.1 | 4011.6 | 3929.9 | 2867.1 |
| 37.5° | 6008.7 | 5983.2 | 5860.4 | 5707.3 | 5526.4 | 5439.0 | 5187.7 | 4819.8 | 4305.4 | 4217.6 | 3055.6 |
| 40° | 6102.2 | 6080.0 | 6003.0 | 5891.1 | 5745.6 | 5725.7 | 5565.1 | 5130.1 | 4625.2 | 4531.7 | 3269.1 |
| 42.5° | 6046.5 | 6024.7 | 5997.3 | 5959.6 | 5899.1 | 5918.0 | 5921.3 | 5483.9 | 4980.4 | 4888.3 | 3504.8 |
| 45° | 5825.4 | 5806.0 | 5834.4 | 5889.6 | 5964.7 | 6058.3 | 6246.3 | 5864.1 | 5377.2 | 5278.9 | 3777.3 |
| 47.5° | 5500.0 | 5485.8 | 5564.2 | 5702.1 | 5921.8 | 6179.7 | 6543.4 | 6263.7 | 5822.6 | 5731.4 | 4117.4 |
| 50° | 5037.1 | 5034.7 | 5191.5 | 5443.3 | 5781.0 | 6238.2 | 6850.4 | 6718.1 | 6441.3 | 6345.5 | 4590.2 |
| 52.5° | 4316.3 | 4321.0 | 4629.4 | 5032.3 | 5534.0 | 6198.6 | 7047.8 | 7302.0 | 7161.2 | 7061.5 | 4999.8 |
| 55° | 3630.0 | 3658.3 | 3877.0 | 4458.0 | 5155.2 | 6051.2 | 7115.8 | 7574.5 | 7558.4 | 7464.0 | 5227.4 |
| 57.5° | 2957.8 | 3009.3 | 3220.0 | 3762.7 | 4602.0 | 5711.6 | 7078.5 | 7692.6 | 7854.1 | 7781.9 | 5527.8 |
| 60° | 2229.5 | 2253.1 | 2495.9 | 3003.2 | 3892.1 | 5091.9 | 6807.9 | 7756.8 | 8258.4 | 8208.4 | 5963.8 |
| 62.5° | 1418.4 | 1477.5 | 1692.9 | 2182.2 | 3030.6 | 4231.2 | 6351.6 | 7755.9 | 8764.3 | 8791.7 | 6526.4 |
| 65° | 747.2 | 816.2 | 930.5 | 1352.3 | 2082.6 | 3270.0 | 5665.3 | 7683.1 | 9385.0 | 9423.2 | 6966.1 |
| 67.5° | 402.9 | 422.7 | 483.2 | 701.9 | 1207.8 | 2215.3 | 4656.8 | 7324.2 | 9744.4 | 9795.0 | 7027.5 |
| 70° | 294.7 | 305.6 | 328.3 | 388.3 | 607.9 | 1286.7 | 3398.0 | 6510.3 | 9281.1 | 9262.2 | 6243.9 |
| 72.5° | 226.3 | 243.3 | 260.3 | 284.4 | 349.5 | 686.8 | 2115.6 | 5098.0 | 7405.4 | 7280.7 | 4667.2 |
| 75° | 178.5 | 181.4 | 205.5 | 227.2 | 262.2 | 391.1 | 939.5 | 2969.1 | 4519.9 | 4224.6 | 2420.3 |
| 77.5° | 142.6 | 144.5 | 158.7 | 177.6 | 210.7 | 257.0 | 291.0 | 1168.1 | 1443.0 | 1287.6 | 525.2 |
| 80° | 84.5 | 89.3 | 118.1 | 137.0 | 174.8 | 162.0 | 106.3 | 253.6 | 225.3 | 204.1 | 88.3 |
| 82.5° | 47.2 | 51.0 | 66.6 | 108.2 | 121.9 | 77.5 | 52.9 | 68.5 | 52.9 | 51.5 | 25.0 |
| 85° | 0.0 | 2.4 | 43.0 | 67.1 | 49.6 | 17.0 | 22.2 | 22.7 | 15.6 | 14.6 | 9.9 |
| 87.5° | 0.0 | 0.0 | 13.2 | 12.8 | 1.9 | 2.8 | 5.2 | 7.6 | 6.1 | 6.1 | 5.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P362592
 CATALOG NUMBER: NVN-SA2D-727-U-T2R-HSS

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0° | 914.5 | 914.5 | 914.5 | 914.5 | 914.5 | 914.5 | 914.5 | 914.5 | 914.5 | 914.5 | 914.5 |
| 2.5° | 932.4 | 906.9 | 858.7 | 811.5 | 771.8 | 739.2 | 709.9 | 698.1 | 688.7 | 687.3 | 679.7 |
| 5° | 974.0 | 922.5 | 830.4 | 754.8 | 704.3 | 668.4 | 637.7 | 618.8 | 604.1 | 598.5 | 593.3 |
| 7.5° | 1036.8 | 958.9 | 826.6 | 739.7 | 679.2 | 618.8 | 562.1 | 500.7 | 462.4 | 447.8 | 439.3 |
| 10° | 1113.3 | 1007.0 | 840.8 | 735.4 | 629.6 | 502.1 | 408.1 | 330.2 | 298.5 | 288.1 | 285.3 |
| 12.5° | 1202.6 | 1067.0 | 865.3 | 709.0 | 523.8 | 356.6 | 281.5 | 255.1 | 248.0 | 244.7 | 244.7 |
| 15° | 1305.1 | 1132.7 | 882.8 | 632.5 | 387.3 | 269.7 | 243.7 | 231.4 | 223.9 | 219.6 | 220.1 |
| 17.5° | 1409.9 | 1196.9 | 874.3 | 521.5 | 285.8 | 240.0 | 220.6 | 207.4 | 197.0 | 192.7 | 191.8 |
| 20° | 1515.7 | 1256.4 | 827.1 | 388.3 | 241.8 | 217.8 | 196.0 | 181.4 | 171.0 | 166.7 | 165.8 |
| 22.5° | 1625.3 | 1307.0 | 743.9 | 284.8 | 217.3 | 193.2 | 171.9 | 157.3 | 147.4 | 143.6 | 141.7 |
| 25° | 1732.1 | 1348.1 | 627.7 | 230.5 | 194.1 | 170.0 | 149.7 | 136.0 | 127.1 | 123.3 | 122.8 |
| 27.5° | 1831.7 | 1374.0 | 493.1 | 203.6 | 173.8 | 149.3 | 130.8 | 118.6 | 111.0 | 108.2 | 107.7 |
| 30° | 1921.5 | 1376.4 | 364.6 | 183.7 | 155.9 | 131.3 | 114.3 | 103.4 | 96.8 | 94.0 | 93.1 |
| 32.5° | 2012.2 | 1356.6 | 265.5 | 165.8 | 139.3 | 115.7 | 99.2 | 90.7 | 86.0 | 83.6 | 83.6 |
| 35° | 2097.7 | 1310.8 | 206.9 | 150.2 | 123.3 | 100.6 | 87.4 | 81.2 | 78.4 | 76.0 | 76.0 |
| 37.5° | 2181.3 | 1245.1 | 175.7 | 136.5 | 108.2 | 87.9 | 77.0 | 73.2 | 70.9 | 68.5 | 68.5 |
| 40° | 2266.3 | 1162.4 | 159.7 | 123.8 | 95.9 | 77.9 | 68.5 | 65.2 | 62.8 | 60.9 | 60.5 |
| 42.5° | 2370.7 | 1067.0 | 149.3 | 111.9 | 85.0 | 69.0 | 60.5 | 56.7 | 54.8 | 52.9 | 52.0 |
| 45° | 2491.6 | 984.8 | 140.8 | 100.1 | 76.0 | 61.4 | 52.4 | 48.7 | 45.8 | 43.5 | 43.0 |
| 47.5° | 2665.9 | 925.3 | 129.4 | 87.4 | 67.5 | 53.4 | 45.3 | 41.1 | 36.8 | 34.5 | 34.0 |
| 50° | 2888.4 | 876.2 | 114.8 | 76.0 | 59.0 | 45.3 | 37.8 | 32.6 | 28.8 | 26.5 | 26.5 |
| 52.5° | 2998.9 | 812.0 | 101.6 | 66.1 | 49.6 | 38.3 | 30.7 | 24.6 | 22.7 | 20.3 | 20.3 |
| 55° | 3043.3 | 762.8 | 88.3 | 56.2 | 41.1 | 31.6 | 24.1 | 18.9 | 17.5 | 16.1 | 15.6 |
| 57.5° | 3168.0 | 748.7 | 77.0 | 47.7 | 34.0 | 25.0 | 18.4 | 14.2 | 13.2 | 11.3 | 11.3 |
| 60° | 3368.8 | 755.7 | 66.6 | 40.6 | 27.4 | 19.4 | 13.7 | 10.9 | 9.9 | 8.0 | 8.0 |
| 62.5° | 3585.6 | 746.8 | 56.2 | 35.0 | 21.3 | 14.2 | 9.4 | 8.0 | 8.0 | 4.7 | 4.3 |
| 65° | 3627.1 | 665.1 | 48.2 | 28.8 | 16.5 | 10.4 | 6.1 | 5.2 | 7.1 | 0.9 | 0.0 |
| 67.5° | 3366.4 | 515.8 | 41.6 | 22.2 | 12.3 | 8.0 | 4.7 | 2.4 | 6.1 | 0.0 | 0.0 |
| 70° | 2691.9 | 327.8 | 33.5 | 16.1 | 9.4 | 6.6 | 3.8 | 0.9 | 4.7 | 0.0 | 0.0 |
| 72.5° | 1903.5 | 190.4 | 26.5 | 11.3 | 8.0 | 5.2 | 2.8 | 0.0 | 2.8 | 0.0 | 0.0 |
| 75° | 962.6 | 101.6 | 16.5 | 8.5 | 6.1 | 3.8 | 1.9 | 0.0 | 0.5 | 0.0 | 0.0 |
| 77.5° | 208.3 | 47.2 | 10.4 | 6.1 | 4.3 | 2.4 | 0.9 | 0.0 | 0.0 | 0.0 | 0.0 |
| 80° | 45.3 | 20.8 | 6.6 | 3.8 | 2.4 | 1.4 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 82.5° | 16.5 | 10.9 | 3.3 | 1.9 | 0.9 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 85° | 9.0 | 5.7 | 1.9 | 0.9 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 87.5° | 4.7 | 1.9 | 0.5 | 0.5 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2008: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGRAW-EDISON

Report Number: SP1-1908-441-1-R4

Test Date: 08/20/2019

Luminaire Tested: SA1C-727-U-5WQ

Test Information

Test Method: LM-79-2008
 Report Number: SP1-1908-441-1-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-727-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-1-R3. TO UPDATE THE CATALOG NUMBER.TESTED IN
 SITU. (1) 70 CRI, 2700K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2741
 CIE u': 0.2605
 CIE v': 0.5272
 Duv: 0.0005
 CIE x: 0.4573
 CIE y: 0.4113
 CIE z: 0.1313
 Peak Wavelength (nm): 602
 Dominant Wavelength (nm): 583
 Purity: 61.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 71.5 | | |
| R1: | 69.2 | R9: | -16.1 |
| R2: | 79.4 | R10: | 51.4 |
| R3: | 87.8 | R11: | 63.1 |
| R4: | 69.4 | R12: | 42.0 |
| R5: | 66.4 | R13: | 70.2 |
| R6: | 69.8 | R14: | 92.4 |
| R7: | 79.8 | | |
| R8: | 50.1 | | |

Rf: 69.9
 Rg: 98.3



Test Conditions

Stabilization Time: 56M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.3./42%
 Sphere Temperature (°C): 25.7

REPORT NUMBER: SP1-1908-441-1-R4

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-1-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-1-R4

Photopic Flux vs. Wavelength



Photopic Lumens: 6211.7

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 1.0 | 620 | 118034 | 30.7 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 1.9 | 625 | 111884 | 24.7 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 3.4 | 630 | 106119 | 19.2 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 6.3 | 635 | 99706 | 15.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 10.4 | 640 | 92142 | 11.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 16.3 | 645 | 84987 | 8.2 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 22.9 | 650 | 78016 | 5.7 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 29.7 | 655 | 71541 | 4.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 36.7 | 660 | 64863 | 2.7 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 42.5 | 665 | 58485 | 1.9 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.0 | 540 | 73435 | 47.8 | 670 | 51641 | 1.1 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.0 | 545 | 78677 | 52.4 | 675 | 46030 | 0.8 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 0.0 | 550 | 83331 | 56.6 | 680 | 40590 | 0.5 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 0.1 | 555 | 89120 | 60.9 | 685 | 35691 | 0.3 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 0.3 | 560 | 94613 | 64.3 | 690 | 31631 | 0.2 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 0.6 | 565 | 99818 | 66.4 | 695 | 27437 | 0.1 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 0.9 | 570 | 106526 | 69.3 | 700 | 24589 | 0.1 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 1.1 | 575 | 111610 | 69.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 1.0 | 580 | 117163 | 69.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 0.8 | 585 | 122201 | 67.9 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 0.6 | 590 | 125662 | 65.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 0.5 | 595 | 127415 | 60.4 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 0.4 | 600 | 129155 | 55.7 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 0.4 | 605 | 128057 | 49.6 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 0.5 | 610 | 126031 | 43.3 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 0.7 | 615 | 123059 | 37.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Scotopic Flux vs. Wavelength



Scotopic Lumens: 6474.3

S/P: 1.04

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 6.0 | 620 | 118034 | 0.1 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 8.6 | 625 | 111884 | 0.1 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 12.5 | 630 | 106119 | 0.0 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 17.3 | 635 | 99706 | 0.0 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 21.8 | 640 | 92142 | 0.0 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 25.7 | 645 | 84987 | 0.0 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 27.5 | 650 | 78016 | 0.0 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 28.1 | 655 | 71541 | 0.0 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 27.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.0 | 535 | 68520 | 24.7 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.1 | 540 | 73435 | 21.5 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.5 | 545 | 78677 | 18.3 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 1.6 | 550 | 83331 | 15.0 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 3.9 | 555 | 89120 | 12.0 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 8.1 | 560 | 94613 | 9.3 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 13.3 | 565 | 99818 | 7.0 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 19.1 | 570 | 106526 | 5.2 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 21.6 | 575 | 111610 | 3.7 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 18.1 | 580 | 117163 | 2.6 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 11.8 | 585 | 122201 | 1.8 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 8.1 | 590 | 125662 | 1.2 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 6.2 | 595 | 127415 | 0.8 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 4.8 | 600 | 129155 | 0.5 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 4.1 | 605 | 128057 | 0.4 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 4.1 | 610 | 126031 | 0.2 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 4.6 | 615 | 123059 | 0.1 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 2145.7 M/P: 0.35

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 2044 | 0.0 | 490 | 7179 | 11.1 | 620 | 118034 | 1.5 | 750 | 8362 | 0.0 | 880 | 3128 | 0.0 |
| 365 | 2016 | 0.0 | 495 | 10476 | 16.9 | 625 | 111884 | 0.9 | 755 | 7635 | 0.0 | 885 | 3110 | 0.0 |
| 370 | 2020 | 0.0 | 500 | 15549 | 26.0 | 630 | 106119 | 0.6 | 760 | 6582 | 0.0 | 890 | 2632 | 0.0 |
| 375 | 2137 | 0.0 | 505 | 22477 | 38.2 | 635 | 99706 | 0.4 | 765 | 5777 | 0.0 | 895 | 2709 | 0.0 |
| 380 | 2046 | 0.0 | 510 | 30417 | 51.6 | 640 | 92142 | 0.2 | 770 | 5474 | 0.0 | 900 | 2016 | 0.0 |
| 385 | 1925 | 0.0 | 515 | 39274 | 65.1 | 645 | 84987 | 0.1 | 775 | 4977 | 0.0 | 905 | 1748 | 0.0 |
| 390 | 1893 | 0.0 | 520 | 47282 | 75.2 | 650 | 78016 | 0.1 | 780 | 4723 | 0.0 | 910 | 2046 | 0.0 |
| 395 | 1695 | 0.0 | 525 | 55413 | 82.9 | 655 | 71541 | 0.1 | 785 | 4219 | 0.0 | 915 | 1844 | 0.0 |
| 400 | 1633 | 0.0 | 530 | 62377 | 86.0 | 660 | 64863 | 0.0 | 790 | 3969 | 0.0 | 920 | 2734 | 0.0 |
| 405 | 2065 | 0.1 | 535 | 68520 | 85.4 | 665 | 58485 | 0.0 | 795 | 4122 | 0.0 | 925 | 2307 | 0.0 |
| 410 | 3449 | 0.2 | 540 | 73435 | 81.1 | 670 | 51641 | 0.0 | 800 | 2864 | 0.0 | 930 | 2039 | 0.0 |
| 415 | 7117 | 0.7 | 545 | 78677 | 75.4 | 675 | 46030 | 0.0 | 805 | 3151 | 0.0 | 935 | 1784 | 0.0 |
| 420 | 13992 | 2.3 | 550 | 83331 | 68.1 | 680 | 40590 | 0.0 | 810 | 3022 | 0.0 | 940 | 2464 | 0.0 |
| 425 | 25176 | 6.2 | 555 | 89120 | 60.9 | 685 | 35691 | 0.0 | 815 | 3471 | 0.0 | 945 | 2794 | 0.0 |
| 430 | 38151 | 13.0 | 560 | 94613 | 52.9 | 690 | 31631 | 0.0 | 820 | 2749 | 0.0 | 950 | 3090 | 0.0 |
| 435 | 49673 | 22.2 | 565 | 99818 | 44.8 | 695 | 27437 | 0.0 | 825 | 2729 | 0.0 | 955 | 1866 | 0.0 |
| 440 | 57273 | 32.0 | 570 | 106526 | 37.6 | 700 | 24589 | 0.0 | 830 | 2282 | 0.0 | 960 | 3110 | 0.0 |
| 445 | 54802 | 36.7 | 575 | 111610 | 30.4 | 705 | 21832 | 0.0 | 835 | 3140 | 0.0 | 965 | 3880 | 0.0 |
| 450 | 39184 | 30.4 | 580 | 117163 | 24.1 | 710 | 19500 | 0.0 | 840 | 2365 | 0.0 | 970 | 3243 | 0.0 |
| 455 | 22506 | 19.7 | 585 | 122201 | 18.7 | 715 | 17870 | 0.0 | 845 | 3024 | 0.0 | 975 | 2014 | 0.0 |
| 460 | 13692 | 13.2 | 590 | 125662 | 14.0 | 720 | 15924 | 0.0 | 850 | 2510 | 0.0 | 980 | 1688 | 0.0 |
| 465 | 9446 | 10.0 | 595 | 127415 | 10.2 | 725 | 14268 | 0.0 | 855 | 2739 | 0.0 | 985 | 2827 | 0.0 |
| 470 | 6698 | 7.7 | 600 | 129155 | 7.3 | 730 | 12438 | 0.0 | 860 | 3515 | 0.0 | 990 | 4172 | 0.0 |
| 475 | 5328 | 6.7 | 605 | 128057 | 5.0 | 735 | 11255 | 0.0 | 865 | 3600 | 0.0 | 995 | 3177 | 0.0 |
| 480 | 5081 | 6.9 | 610 | 126031 | 3.4 | 740 | 9951 | 0.0 | 870 | 3609 | 0.0 | 1000 | 3241 | 0.0 |
| 485 | 5579 | 8.1 | 615 | 123059 | 2.3 | 745 | 8870 | 0.0 | 875 | 3208 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Summary

$R_f = 69.9$
 $R_g = 98.3$
 CIE $R_a = 71.5$
 $R_9 = -16.1$



Color Vector Graphics



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 54 | CES51 = 77 | CES76 = 48 |
| CES02 = 63 | CES27 = 74 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 66 | CES78 = 56 |
| CES04 = 71 | CES29 = 44 | CES54 = 77 | CES79 = 81 |
| CES05 = 50 | CES30 = 46 | CES55 = 74 | CES80 = 80 |
| CES06 = 52 | CES31 = 50 | CES56 = 63 | CES81 = 73 |
| CES07 = 42 | CES32 = 49 | CES57 = 60 | CES82 = 91 |
| CES08 = 41 | CES33 = 53 | CES58 = 63 | CES83 = 84 |
| CES09 = 29 | CES34 = 66 | CES59 = 85 | CES84 = 90 |
| CES10 = 77 | CES35 = 82 | CES60 = 89 | CES85 = 87 |
| CES11 = 60 | CES36 = 78 | CES61 = 85 | CES86 = 65 |
| CES12 = 66 | CES37 = 75 | CES62 = 69 | CES87 = 78 |
| CES13 = 43 | CES38 = 53 | CES63 = 68 | CES88 = 73 |
| CES14 = 74 | CES39 = 91 | CES64 = 68 | CES89 = 68 |
| CES15 = 71 | CES40 = 85 | CES65 = 65 | CES90 = 68 |
| CES16 = 48 | CES41 = 76 | CES66 = 62 | CES91 = 91 |
| CES17 = 50 | CES42 = 76 | CES67 = 60 | CES92 = 71 |
| CES18 = 57 | CES43 = 65 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 57 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 78 |
| CES21 = 88 | CES46 = 70 | CES71 = 57 | CES96 = 80 |
| CES22 = 80 | CES47 = 63 | CES72 = 86 | CES97 = 79 |
| CES23 = 92 | CES48 = 51 | CES73 = 52 | CES98 = 71 |
| CES24 = 91 | CES49 = 68 | CES74 = 90 | CES99 = 64 |
| CES25 = 73 | CES50 = 77 | CES75 = 58 | |



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-1-R4

TM-30-18

Measure Comparisons



(END OF REPORT)